# C7620

Freestanding / Semi Built-in

# LIEBHERR

# **Refrigeration and Freezing**







### home.liebherr.com

Energy consumption (kWh / y)  Estimated Yearly Energy Cost in US \$  Sound rating dB(A)  Total capacity cu.ft. (I)  Efrigerator capacity cu.ft. (I)  Freezer capacity cu. ft. (I)  Electronic control  Touch display  Defrost type  Automatic  Interior light  Number of shelves  Aumber of GasyFreash drawers  Number of freezer drawers  Refrigerator Temperature range °F (°C)  Internal Water Dispenser  No  Water filter  Ice cube stock lbs. (kg)  Product dimensions  in inch (H / W / D)  Net weight lbs. (kg)  Net Weight lbs. (kg)  Net Weight lbs. (kg)  Net Weight lbs. (kg)  Pool tags A (90)  Net weight lbs. (kg)  15 (425)  16 (425)  17 (425)  18 (425)  19 (4287)  10 (28		C7620
Sound rating dB(A)  Total capacity cu.ft. (I)  Refrigerator capacity cu.ft. (I)  Freezer capacity cu. ft. (I)  Defrost type  Automatic  Interior light  Number of shelves  Number of EasyFreash drawers  Number of freezer drawers  Refrigerator Temperature range °F (°C)  Internal Water Dispenser  No  Water filter  Ice cube output lbs. (kg)/24h  Ice cube stock lbs. (kg)  Product dimensions  in inch (H / W / D)  Net weight lbs. (kg)  10 (287)  10 (	Energy consumption (kWh / y)	305
Total capacity cu.ft. (I)  Refrigerator capacity cu.ft. (I)  Freezer capacity cu.ft. (I)  Freezer capacity cu.ft. (I)  Lelectronic control  Defrost type  Automatic  Interior light  Number of shelves  Aumber of door racks  Number of EasyFreash drawers  Number of freezer drawers  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Touch display  Automatic  Ceiling LED  Number of shelves  4  Number of door racks  2 + VarioBox  Number of Freezer drawers  3  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  Lee Cube output lbs. (kg)/24h  20 ice cubes per batch  Lee cube stock lbs. (kg)  Door hinges  Right, reversible  Product dimensions  In inch (H / W / D)  73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  188.5 / 74.5 / 67.5  Cut out dimensions  In inch (H / W / D)  188 / 76.2 / 60.9  Net weight lbs. (kg)  198.4 (90)	Estimated Yearly Energy Cost in US \$	43
Refrigerator capacity cu.ft. (I)  Freezer capacity cu. ft. (I)  Freezer capacity cu. ft. (I)  Electronic control  Touch display  Defrost type  Automatic  Interior light  Ceiling LED  Number of shelves  4  Number of door racks  2 + VarioBox  Number of EasyFreash drawers  1  Number of freezer drawers  3  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  Ice Cube output lbs. (kg)/24h  Ice cube stock lbs. (kg)  Door hinges  Right, reversible  Product dimensions  in inch (H / W / D)  T3 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  T4 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Sound rating dB(A)	36
Freezer capacity cu. ft. (I)  Electronic control  Touch display  Defrost type  Automatic  Interior light  Ceiling LED  Number of shelves  4  Number of door racks  2 + VarioBox  Number of EasyFreash drawers  1  Number of freezer drawers  3  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  Ice cube output lbs. (kg)/24h  20 ice cubes per batch  Ice cube stock lbs. (kg)  Door hinges  Right, reversible  Product dimensions  in inch (H / W / D)  73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  74 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Total capacity cu.ft. (l)	15 (425)
Electronic control  Defrost type Automatic  Interior light Ceiling LED  Number of shelves 4  Number of door racks 2 + VarioBox  Number of EasyFreash drawers 1  Number of freezer drawers 3  Refrigerator Temperature range °F (°C) 34 to 46°F (2 to 9°C)  Freezer temperature range °F (°C)  Internal Water Dispenser No  Water filter No  Ice Cube output lbs. (kg)/24h 20 ice cubes per batch Ice cube stock lbs. (kg) 40 ice cubes  Product dimensions  in inch (H / W / D) 73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D) 74 / 30 / 24  in cm (H / W / D) Net weight lbs. (kg) 198.4 (90)	Refrigerator capacity cu.ft. (l)	10 (287)
Defrost type  Automatic  Interior light  Ceiling LED  Number of shelves  4  Number of door racks  Number of EasyFreash drawers  1  Number of freezer drawers  3  Refrigerator Temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  Ice Cube output lbs. (kg)/24h  Ice cube stock lbs. (kg)  Door hinges  Product dimensions  in inch (H / W / D)  Ta 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Ta 1/6 / 24  In cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Freezer capacity cu. ft. (l)	4.9 (138)
Interior light  Number of shelves  4  Number of door racks  2 + VarioBox  Number of EasyFreash drawers  1  Number of freezer drawers  3  Refrigerator Temperature range °F (°C)  5 to -15°F (-15 to -26°C)  Internal Water Dispenser  No  Water filter  No  IceMaker  Ice cube output lbs. (kg)/24h  20 ice cubes per batch  Ice cube stock lbs. (kg)  Door hinges  Right, reversible  Product dimensions  in inch (H / W / D)  73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  74 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Electronic control	Touch display
Number of shelves  Number of door racks  2 + VarioBox  Number of EasyFreash drawers  1  Number of freezer drawers  3  Refrigerator Temperature range °F (°C)  5 to -15°F (-15 to -26°C)  Internal Water Dispenser  No  Water filter  No  IceMaker  EasyTwist-Ice  Ice cube output lbs. (kg)/24h  20 ice cubes per batch  Ice cube stock lbs. (kg)  40 ice cubes  Product dimensions  in inch (H / W / D)  73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  74 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Defrost type	Automatic
Number of door racks  Number of EasyFreash drawers  Number of Feezer drawers  Refrigerator Temperature range °F (°C)  Sto -15°F (-15 to -26°C)  Internal Water Dispenser  No  Water filter  No  IceMaker  EasyTwist-Ice Ice cube output lbs. (kg)/24h  20 ice cubes per batch Ice cube stock lbs. (kg)  40 ice cubes  Product dimensions  in inch (H / W / D)  T3 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  T4 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Interior light	Ceiling LED
Number of EasyFreash drawers  Number of freezer drawers  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  IceMaker  Ice cube output lbs. (kg)/24h  Ice cube stock lbs. (kg)  Door hinges  Product dimensions  in inch (H / W / D)  T3 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D)  T4 / 30 / 24  in cm (H / W / D)  Native in com (H / W / D)  Refrigerator Temperature range °F (°C)  Sto -15°F (-15 to -26°C)  No  No  No  PasyTwist-Ice  20 ice cubes per batch  40 ice cubes  Product dimensions  in inch (H / W / D)  T3 1/6 / 29 7/16 / 26 5/8  In cm (H / W / D)  T4 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  198.4 (90)	Number of shelves	4
Number of freezer drawers  Refrigerator Temperature range °F (°C)  Freezer temperature range °F (°C)  Internal Water Dispenser  No  Water filter  No  IceMaker  Ice cube output lbs. (kg)/24h  Ice cube stock lbs. (kg)  Door hinges  Product dimensions  in inch (H / W / D)  Table 185.5 / 74.5 / 67.5  Cut out dimensions  in inch (H / W / D)  Table 24 / 30 / 24  in cm (H / W / D)  Net weight lbs. (kg)  134 to 46°F ( 2 to 9°C)  5 to -15°F (-15 to -26°C)  15 to -15°F (-15 to -26°C)  16 to -15°F (-15 to -26°C)  16 to -15°F (-15 to -26°C)  18 ay Twist-Ice  20 ice cubes per batch  40 ice cubes  Right, reversible  Product dimensions  in inch (H / W / D)  Table 27 / 16 / 26 5/8  In cm (H / W / D)  Table 34 to 46°F ( 2 to 9°C)  Table 40°C)  Table 40°	Number of door racks	2 + VarioBox
Refrigerator Temperature range °F (°C) 34 to 46°F ( 2 to 9°C)  Freezer temperature range °F (°C) 5 to -15°F (-15 to -26°C)  Internal Water Dispenser No  Water filter No  IceMaker EasyTwist-Ice Ice cube output lbs. (kg)/24h 20 ice cubes per batch Ice cube stock lbs. (kg) 40 ice cubes  Door hinges Right, reversible  Product dimensions  in inch (H / W / D) 73 1/6 / 29 7/16 / 26 5/8  in cm (H / W / D) 185.5 / 74.5 / 67.5  Cut out dimensions  in inch (H / W / D) 74 / 30 / 24  in cm (H / W / D) 188 / 76.2 / 60.9  Net weight lbs. (kg) 198.4 (90)	Number of EasyFreash drawers	1
Freezer temperature range °F (°C)         5 to -15°F (-15 to -26°C)           Internal Water Dispenser         No           Water filter         No           Ice Maker         EasyTwist-Ice           Ice cube output lbs. (kg)/24h         20 ice cubes per batch           Ice cube stock lbs. (kg)         40 ice cubes           Door hinges         Right, reversible           Product dimensions         in inch (H / W / D)         73 1/6 / 29 7/16 / 26 5/8           in cm (H / W / D)         185.5 / 74.5 / 67.5           Cut out dimensions         in inch (H / W / D)         74 / 30 / 24           in cm (H / W / D)         188 / 76.2 / 60.9           Net weight lbs. (kg)         198.4 (90)	Number of freezer drawers	3
Internal Water Dispenser No Water filter No IceMaker EasyTwist-Ice Ice cube output lbs. (kg)/24h 20 ice cubes per batch Ice cube stock lbs. (kg) 40 ice cubes Door hinges Right, reversible  Product dimensions in inch (H / W / D) 73 1/6 / 29 7/16 / 26 5/8 in cm (H / W / D) 185.5 / 74.5 / 67.5  Cut out dimensions in inch (H / W / D) 74 / 30 / 24 in cm (H / W / D) 188 / 76.2 / 60.9 Net weight lbs. (kg) 198.4 (90)	Refrigerator Temperature range °F (°C)	34 to 46°F ( 2 to 9°C)
Water filter         No           IceMaker         EasyTwist-Ice           Ice cube output lbs. (kg)/24h         20 ice cubes per batch           Ice cube stock lbs. (kg)         40 ice cubes           Door hinges         Right, reversible           Product dimensions           in inch (H / W / D)         73 1/6 / 29 7/16 / 26 5/8           in cm (H / W / D)         185.5 / 74.5 / 67.5           Cut out dimensions           in inch (H / W / D)         74 / 30 / 24           in cm (H / W / D)         188 / 76.2 / 60.9           Net weight lbs. (kg)         198.4 (90)	Freezer temperature range °F (°C)	5 to -15°F (-15 to -26°C)
IceMaker         EasyTwist-Ice           Ice cube output lbs. (kg)/24h         20 ice cubes per batch           Ice cube stock lbs. (kg)         40 ice cubes           Door hinges         Right, reversible           Product dimensions           in inch (H / W / D)         73 1/6 / 29 7/16 / 26 5/8           in cm (H / W / D)         185.5 / 74.5 / 67.5           Cut out dimensions           in inch (H / W / D)         74 / 30 / 24           in cm (H / W / D)         188 / 76.2 / 60.9           Net weight lbs. (kg)         198.4 (90)	Internal Water Dispenser	No
Ce cube output lbs. (kg)/24h   20 ice cubes per batch   Ce cube stock lbs. (kg)   40 ice cubes	Water filter	No
Lee cube stock lbs. (kg)	IceMaker	EasyTwist-Ice
Door hinges       Right, reversible         Product dimensions       In inch (H / W / D)       73 1/6 / 29 7/16 / 26 5/8         in cm (H / W / D)       185.5 / 74.5 / 67.5         Cut out dimensions       In inch (H / W / D)       74 / 30 / 24         in cm (H / W / D)       188 / 76.2 / 60.9         Net weight lbs. (kg)       198.4 (90)	Ice cube output lbs. (kg)/24h	20 ice cubes per batch
Product dimensions in inch (H / W / D) 73 1/6 / 29 7/16 / 26 5/8 in cm (H / W / D) 185.5 / 74.5 / 67.5  Cut out dimensions in inch (H / W / D) 74 / 30 / 24 in cm (H / W / D) 188 / 76.2 / 60.9  Net weight lbs. (kg) 198.4 (90)	Ice cube stock lbs. (kg)	40 ice cubes
$\begin{array}{llllllllllllllllllllllllllllllllllll$	Door hinges	Right, reversible
$\begin{array}{lll} \text{in cm (H/W/D)} & 185.5  /  74.5  /  67.5 \\ \hline \textbf{Cut out dimensions} \\ \text{in inch (H/W/D)} & 74  /  30  /  24 \\ \text{in cm (H/W/D)} & 188  /  76.2  /  60.9 \\ \\ \text{Net weight lbs. (kg)} & 198.4  (90) \\ \hline \end{array}$	Product dimensions	
Cut out dimensions       in inch (H / W / D)     74 / 30 / 24       in cm (H / W / D)     188 / 76.2 / 60.9       Net weight lbs. (kg)     198.4 (90)	in inch (H/W/D)	73 1/6 / 29 7/16 / 26 5/8
in inch (H / W / D) 74 / 30 / 24 in cm (H / W / D) 188 / 76.2 / 60.9 Net weight lbs. (kg) 198.4 (90)	in cm (H/W/D)	185.5 / 74.5 / 67.5
in cm (H / W / D) 188 / 76.2 / 60.9  Net weight lbs. (kg) 198.4 (90)	Cut out dimensions	
Net weight lbs. (kg) 198.4 (90)	in inch (H / W / D)	74 / 30 / 24
	in cm (H/W/D)	188 / 76.2 / 60.9
Voltage V / Hz 115/60	Net weight lbs. (kg)	198.4 (90)
	Voltage V / Hz	115/60

<sup>\*</sup> Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.



Accessories	
FreshAir activated carbon filter	9882460

### **Features**



DuoCooling independent refrigeration systems provide precise temperature control and superior performance, efficiency and food preservation.



The guarantee of market freshness in your home. Whether it's unpackaged vegetables or fruit, Easy Fresh ensures that your food is preserved for a longer period of time.



The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



The energy efficient LED ceiling light not only emits virtually no heat for the optimal storage of wines, but is dimmable for a pleasant ambient light within the cabinet, as well as a cool glow for the room.



Noise levels are kept to a minimum thanks to virtually silent, speed-controlled, and sound absorbing compressors.



SmartSteel finish significantly reduces the visibility of fingerprints, is easy to clean, and is scratch resistant.



Want to be prepared for the future of the Smart Home? The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.

<sup>\*\*</sup> Noise output - according to EN 60704-3

# **Diagrams**


# (73-1/16") 1855mm (73-1/16") 1020mm (1-3/8") 1030-15/16") 786mm

# (24") 610mm (53-7/8") 1368mm (54-3/8") door 90° open (52-5/16") 1328mm (41-11/16") 1058mm

Allow door swing clearance at locations next to a wall. If the appliance is installed with the hinges next to a wall (4), the distance between the appliance and the wall must be at least  $\frac{1}{2}$ " (13 mm.)

The refrigerator door must open to a minimum of 90° to allow the crispers to open and the shelves to be removed. There is no 90° door limiter available for this model. Height can be increased by 3/8" (10mm) by turning the levelling feet at the front and the height adjustable rollers at the appliance rear.


## Semi built-in look - Cutout Dimensions



The appliances can be used freestanding or semi built-in. If semi built-in, consider the minimum cabinet opening dimensions specified on this image.

The power cord exists the rear of the appliances (A) right side and has a length of 6.5 ft (2m). We suggest the electrical outlet not to be located behind the appliance, so it is easily accessible. This can be located on top of the niche like shown on the image.

### **Ventilation Requirements**



If the appliance is integrated in a fitted kitchen, the following ventilation requirements must be met: - The spacing fins on the back of the appliance are used to ensure sufficient ventilation. These must not lie in cavities or recesses in their final installation position. - Basically, the larger the ventilation gap, the more energy the appliance saves during operation. Do not restrict the air flow.

A cross-sectional air flow of at least 31 in2 (200cm2) per appliance at the airflow inlet (1) and at the airflow outlet (2).

The top ventilation space can be directed in one of the following ways:

- A. Directly over the appliance (2) with a gap between the ceiling of the unit and the cabinet
- B. Above the cabinet and below the ceiling (3).
- C. Through a vent installed in a soffit (4).

Be sure to consider the possibility of having to raise some of the leveling legs in order to level the appliance when installing. If you adjust the height of the appliance – it will effectively reduce air flow. Therefore leave yourself some room for adjustment. The appliance is designed to allow proper air flow when installed up against the wall.