CB7790IM

Freestanding / Semi Built-in

LIEBHERR

Refrigeration and Freezing







home.liebherr.com

	CB7790IN
Energy consumption (kWh / y)	435
Estimated Yearly Energy Cost in US \$	61
Sound rating dB(A)	35
Total capacity cu.ft. (l)	16.8 (476)
Refrigerator capacity cu.ft. (l)	7.4 (209)
BioFresh compartment cu. ft. (l)	4.5 (128)
Freezer capacity cu. ft. (l)	4.9 (139)
Electronic control	Touch & swipe display
Defrost type	Automatic
Interior light	LightTower
Number of shelves	4 + Variosafe
Number of door racks	2 + VarioBox
Number of EasyFreash drawers	2
Number of freezer drawers	3
Refrigerator Temperature range °F (°C)	37 to 46°F (3 to 9°C)
Freezer temperature range °F (°C)	5 to -15°F (-15 to -26°C)
Internal Water Dispenser	Yes
Water filter	Yes
IceMaker	Fixed water connection
Ice cube output lbs. (kg)/24h	2.6 (1.2)
Ice cube stock lbs. (kg)	11.9 (5.4)
Door hinges	Right, reversible
Product dimensions	
in inch (H/W/D)	79 3/8 / 29 7/16 / 26 5/8
in cm (H/W/D)	201.5 / 74.5 / 67.5
Cut out dimensions	
in inch (H/W/D)	80 / 30 / 24
in cm (H/W/D)	203.2 / 76.2 / 60.9
Net weight lbs. (kg)	374.8 (170)
Voltage V / Hz	115/60

^{*} Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.

Subject to modification. For up-to-date information, visit home.liebherr.com Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.



Accessories	
FreshAir activated carbon filter	9882460
30" Top Ventilation grill	9903844

Features



DuoCooling independent refrigeration systems provide precise temperature control and superior performance, efficiency and food preservation.



Preserve just-bought groceries for optimum food freshness, while sealing in flavors and maintaining essential vitamins and minerals.



The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



The cold mist combined with a temperature in the safe of around 32° F (0 °C) gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90min. for 4 seconds and for 8 seconds when the door is opened.



The water dispenser enables drip-free water dispensing and provides fresh, cold water. Simply press the panel with your carafe or glass and enjoy. This also means you get to save on purchasing water bottles and live more sustainably.



VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between 28°F to 57°F (-2°C to 14°C) – and therefore also use this compartment as a further cooling zone.



SmartSteel finish significantly reduces the visibility of fingerprints, is easy to clean, and is scratch resistant.



Want to be prepared for the future of the Smart Home? The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.

^{**} Noise output - according to EN 60704-3

Diagrams


(79-5/16") 2015mm (26-9/16") (1-3/8") (26-9/16") (1-3/8") (26-9/16") (1-3/8") (1-3/8") (1-3/8") (1-3/8") (1-3/8")

(24") 610mm (53-7/8") 1368mm (54-3/8") (54-3/8") 1382mm (41-11/16") 1058mm

Allow door swing clearance at locations next to a wall. If the appliance is installed with the hinges next to a wall (4), the distance between the appliance and the wall must be at least $\frac{1}{2}$ " (13 mm.)

The refrigerator door must open to a minimum of 90° to allow the crispers to open and the shelves to be removed. There is no 90° door limiter available for this model. Height can be increased by 3/8" (10mm) by turning the levelling feet at the front and the height adjustable rollers at the appliance rear.


Semi built-in look - Cutout Dimensions



The appliances can be used freestanding or semi built-in. If semi built-in, consider the minimum cabinet opening dimensions specified on this image.

The power cord exists the rear of the appliances (A) right side and has a length of 6.5 ft (2m). We suggest the electrical outlet not to be located behind the appliance, so it is easily accessible. This can be located on top of the niche like shown on the image.

Ventilation Requirements



If the appliance is integrated in a fitted kitchen, the following ventilation requirements must be met: - The spacing fins on the back of the appliance are used to ensure sufficient ventilation. These must not lie in cavities or recesses in their final installation position. - Basically, the larger the ventilation gap, the more energy the appliance saves during operation. Do not restrict the air flow.

A cross-sectional air flow of at least 31 in2 (200cm2) per appliance at the airflow inlet (1) and at the airflow outlet (2).

The top ventilation space can be directed in one of the following ways:

- A. Directly over the appliance (2) with a gap between the ceiling of the unit and the cabinet
- B. Above the cabinet and below the ceiling (3).
- C. Through a vent installed in a soffit (4).

Be sure to consider the possibility of having to raise some of the leveling legs in order to level the appliance when installing. If you adjust the height of the appliance – it will effectively reduce air flow. Therefore leave yourself some room for adjustment. The appliance is designed to allow proper air flow when installed up against the wall.