


Unique features



Ideal Humidity for Long-term Storage

When humidity level falls below 50%, natural corks begin to shrink, causing oxygen to enter the bottle and resulting in damaged wine. Liebherr wine cabinets guarantee ideal conditions which allows wine corks to remain supple and prevent oxidization, with humidity between 50% – 80% depending on ambient humidity.



Optimum Air Quality with Charcoal Filter

Environmental odours can adversely affect the quality of wine stored over prolonged periods. To protect your prized collection, each Liebherr wine cabinet is equipped with an activated charcoal filter to provide a permanent supply of odourless, fresh air.



UV Protection with Insulated Glass Doors

Our wine cabinets come with insulated glass doors with special UV protection. The double-glazed construction means that most of the damaging UV radiation is reflected away. In addition, LED lights are installed in the interiors to provide illumination without risk of UV exposure.



Pleasant Illumination with Energy Efficient LED Lighting

Integrated LED lights in our wine cabinet interiors ensure pleasant illumination and provide an optimum view of your wine collection. LED lighting is energy efficient and emits less heat than conventional neon lighting, hence it does not influence the interior temperature.



Low Vibration Environment to Minimise Damage

Specially developed compressors provide a low vibration environment for your wine bottles. Coupled with our natural, handcrafted beechwood shelves, you can be rest assured that your exclusive collections are protected from any harmful vibrations.



Intuitive Navigation via LCD Display

Our touch electronic control system is easy to navigate and enables tailored storage options. Temperature can be set between +5°C and +20°C based on your preference. In our multi-temperature models, each wine safe can be controlled independently, with a temperature range of +5°C and +20°C, allowing different types of wine to be stored in one wine cabinet.









WTes 5972

Energy consumption in 365 days/24 h*	245 / 0.671 kWh
Total gross / net capacity	584 / 511 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.5 A
Door	Insulated glazed door, stainless steel frame
Side walls	Stainless steel
Temperature zones	3
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	178
Type of control	LCD display, internal digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED, dimmable
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottom o	compartment) 13
Pull-out shelves on telescopic rails	10
Presentation shelves	1
Door hinges	Right, reversible
Lock	Fitted
Product dimensions (H/W/D)	192 / 70 / 74.2 cm

Energy consumption in 365 days/24 h*	248 / 0.679 kWh
Total gross / net capacity	593 / 526 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.0 A
Door	Insulated glazed door, stainless steel frame
Side walls	Stainless steel
Temperature zones	2
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	211
Type of control	LCD display, internal digital, internal digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED, dimmable
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottor	n compartment) 10
Pull-out shelves on telescopic rails	8
Presentation shelves	1
Door hinges	Right, reversible
Lock	Fitted
Product dimensions (H/W/D)	192 / 70 / 74.2 cm










Diagram














^{*=} Measurements taken at +25°C ambient and +12°C interior temperature tested by Liebherr Germany (not to Australian standards).



WKt 6451



WKb 4612


Energy consumption in 365 days/24 h*	143 / 0.392 kWh
Total gross / net capacity	666 / 625 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.0 A
Door	Full door, terra
Side walls	Terra
Temperature zones	1
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	312
Type of control	MagicEye, external digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottom compartn	nent) 7
Pull-out shelves on telescopic rails	-
Presentation shelves	-
Door hinges	Right, reversible
Lock	Fitted
Product dimensions (H/W/D)	193 / 74.7 / 75.9 cm

Energy consumption in 365 days/24 h*	204 / 0.559 kWh
Total gross / net capacity	453 / 336 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.0 A
Door	Insulated glazed door, black frame
Side walls	Black
Temperature zones	1
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	195
Type of control	MagicEye, external digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottom com	partment) 7
Pull-out shelves on telescopic rails	
Presentation shelves	1
Door hinges	Right, reversible
Lock	Fitted
Product dimensions (H/W/D)	184.2 / 65.7 / 66.3 cm

Wine




Diagram





Diagram




^{*=} Measurements taken at +25°C ambient and +12°C interior temperature tested by Liebherr Germany (not to Australian standards).

Liebherr Barrique Wine Cabinets



WKb 4611






Lock



Product dimensions (H/W/D)

Presentation shelves
Door hinges

Diagram






WKgb 4113

Energy consumption in 365 days/24 h*	204 / 0.558 kWh
Total gross / net capacity	395 / 293 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.0 A
Door	Full glass door with heating function
Side walls	Black
Temperature zones	1
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	168
Type of control	MagicEye, external digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottom compa	rtment) 6
Pull-out shelves on telescopic rails	
Presentation shelves	1
Door hinges	Right
Lock	Fitted
Product dimensions (H/W/D)	164.5 / 65.7 / 66.3 cm



LED






^{*=} Measurements taken at +25°C ambient and +12°C interior temperature tested by Liebherr Germany (not to Australian standards).

Right, reversible Fitted

184.2 / 65.7 / 66.3 cm




WKb 4112







Diagram






WKb 1712

Energy consumption in 365 days/24 h*	149 / 0.408 kWh
Total gross / net capacity	173 / 121 litre
Frequency / Voltage	50 Hz / 220-240 V~
Connection rating	1.0 A
Door	Insulated glazed door, black frame
Side walls	Black
Temperature zones	1
Temperature range	+5°C to +20°C
Max. no. of Bordeaux bottles (0.75 litre)	60
Type of control	MagicEye, external digital
Forced air system	FreshAir activated charcoal filter
Interior light	LED
Child proof function	Yes
Fault: warning signal	Visual and audible
Door open: warning sign	Audible
Shelf material	Beech wood
Total no. of storage shelves (incl. bottom compar	tment) 3
Pull-out shelves on telescopic rails	
Presentation shelves	
Door hinges	Right, reversible
Lock	Fitted
Product dimensions (H/W/D)	85 / 65.7 / 66.3 cm



LED

Diagram



^{*=} Measurements taken at +25°C ambient and +12°C interior temperature tested by Liebherr Germany (not to Australian standards).



For more information please visit us at:



Head Office 1 Stamford Road, Oakleigh Victoria 3166 E-mail: sales@andico.com.au | Tel: 1800 685 899



Visit our social media channels at socialmedia.home.liebherr.com

home.liebherr.com.au