
Treasuring true taste.

Wine Special 2023/2024:

Discover our wine fridges and enjoy wine
in all its perfection.

LIEBHERR


Storing and tempering



Special requirements

Wine fridges must meet the same standards as refrigerators and freezers for storing food. However, the particular requirements of reliable wine storage and tempering demand a lot more in terms of performance. That's why most wine fridges on the market are in energy efficiency class G.

The current EU energy label* for wine fridges:





1. The QR code for identifying the product in EPREL (European Product Database for Energy Labelling).
2. The model identifier for manual identification of the product in the EU database EPREL, using the article number for example.
3. The efficiency scale from "A" to "G". "G" is intended only for wine fridges.
4. Maximum storage capacity.
5. The noise level is now classified into classes "A" to "D".

*In accordance with Regulation EU 2019/2016

Optimum energy efficiency

Liebherr puts a special focus on sustainability. Our wine fridges are among the most energy-efficient in their class. While most manufacturers offer models in class G, most of our wine fridges are already in energy efficiency classes F and E, and one of them is even in class D.

Distribution among efficiency classes in 2023:



**Source: EPREL 2023



Treasuring true taste.

A passion for wine takes you to a world of many different facets. Memories of holidays, meeting winemakers and wine merchants, knowing the details of growing and harvesting: all this sharpens our instinct for the nuances that we appreciate so much. Conserving them requires professional storage – allowing them to unfold before serving means keeping the wine at the right temperature. Just 1°C can make the difference between “OK” and “oh wow”.

Meeting all these conditions perfectly is the task we have set ourselves at Liebherr. Discover our wine fridges – and find out how you can not only store your collection under the perfect conditions, but preserve the very essence of the wine.






Contents

Ideal conditions for wines	6
Constant temperature	10
Correct humidity	12
Reliable UV protection	14
Clean air	16
Do not disturb	18
Security and connectivity	20
Practical accessories	22
The perfect range of wine fridges	24
Freestanding wine fridges	28
Freestanding multi-temperature wine fridges	30
Freestanding wine storage fridges	34
Freestanding wine serving fridges	
for professional use	40
Freestanding compact wine fridge / humidor	44
Fully integrated wine fridges	46
Fully integrated multi-temperature	
wine fridges	50
Fully integrated wine storage fridges	54
Under-worktop wine fridges	55
Brief information on features	56

Qualities that surpass even a wine cellar.

To preserve what connoisseurs treasure, Liebherr wine fridges have some exceptional features. They not only match wine cellars in terms of the five essentials of perfect storage, but surpass them thanks to our engineering expertise.

We take care of every detail.



Constant temperatures protect the character of the wine.



**Temp
Protect
Plus**

Liebherr wine fridges have TempProtect Plus for double temperature protection.

The right humidity keeps corks supple to protect the wine.



**Humidity
Select**

**Humidity
Control**

With HumiditySelect or HumidityControl, the humidity in Liebherr wine fridges can be individually adjusted.

Keeping out ultraviolet light protects the wine from ageing badly.



**UV
Protect**

**UV
Protect
Plus**

Liebherr glass door models have unique double or even triple anti-ultraviolet glazing.

Keeping out foreign odours stops them from spoiling the taste of the wine.



**Fresh
Air**

The FreshAir activated charcoal filter in a Liebherr wine fridge neutralises foreign odours.


Preventing vibrations allows the wine to mature undisturbed.



**Vibrate
Safe**

Liebherr wine fridges have a fully vibration-insulated cooling system.





Perfecting the art of wine storage and tempering.

The new wine fridges from Liebherr not only master the five essentials of wine storage, but achieve a new level of perfection. This can be achieved for treasured wine collections anywhere in the world – with convincing solutions for any home.

Quality

Liebherr wine fridges live up to the responsibility of keeping a valuable wine collection perfect. Quality down to the last detail and an unstinting commitment to perfection are what distinguish Liebherr products.

Perfect climate

Ideal storage conditions are key to bringing out what the winemaker intended. That's why our wine fridges have clever control functions for all the factors that affect these conditions. The only factor we can't control is time.

Convenience and flexibility

Naturally, Liebherr wine fridges aren't as spacious as a wine cellar. But they do make the best use of what space is available and, when it comes to handling, even surpass their inspiration in many respects.

Design and lifestyle

Taking wine storage out of the cellar and into the living area is an exciting prospect with Liebherr wine fridges. The timeless design skilfully displays a passion for great wines.

Security and connectivity

Where a wine cellar might have a padlock on the door, our wine fridges have various functions to do the same job. Alarms, door locks, codes, and a ready-installed or retrofitted network connection set the standards.

Never change the temperature until the perfect moment arrives.

Wines like stability. When storing them, a constant temperature between +10 °C and +12 °C is ideal. This allows the wine to mature patiently until the time comes for it to unveil its full potential. At this point another temperature comes into play: the ideal drinking temperature.

Setting the required storage temperature in a Liebherr wine fridge is easy. The reason why it's so important is due to complex chemistry. As the temperature increases, so does the kinetic energy of the molecules in the wine. This speeds up the maturation process and the alcohol starts to vaporise. Consistency is key, because temperature fluctuations harm the wine.

Wine can only be enjoyed to perfection if served at the right temperature. To a large extent, this is a matter of taste and depends upon the wine. Trial and error, as well as talking to other wine connoisseurs, are the key to success. As a general rule +11 °C to +12 °C is good for white wines – sparkling wines tend to like it a bit cooler – while +17 °C to +18 °C is ideal for reds. Be careful with the commonly used term “room temperature”, which dates from the 20th century, when rooms were generally colder than they are now. These days, red wine served at room temperature will usually be too warm. This is why it's best to leave controlling the temperature to a Liebherr wine fridge with multiple compartments, because they're just as precise and reliable as the engineers who developed them.



Consistently good ageing

If wine is not kept at the right storage temperature, its quality can suffer. The precise electronic control system in all our wine fridges guarantees that the temperature set for the interior is kept constant, even when the ambient temperature fluctuates significantly.



Ideal drinking temperature

In the multi-temperature wine fridges, which have two or three compartments, different wines can be stored perfectly at the drinking temperature they each require. Each compartment can be independently set to between +5°C and +20°C, ensuring truly versatile use of the appliance.





Healthy corks are essential for correct storage.


Cork is a fascinating natural product. To this day, the properties given to it by nature make it the ideal stopper for protecting valuable wines. To ensure that the cork remains supple enough to do its job as a breathable seal, the correct air humidity is essential.



Humidity that preserves taste

We all know that wood expands and contracts, and the bark of the cork oak is no exception. If the humidity is below 50% RH, it has serious effects on wine in storage, because the cork in the neck of the bottle shrinks. Not so much as to let the wine leak out, but too much air permeates through it into the bottle, oxidising the wine and causing unwanted changes to the colour and taste of the wine. However, this kind of mistake when storing wine can be avoided.

Liebherr wine fridges ensure the ideal humidity through a clever combination of the refrigeration system, air circulation control in the appliance, and wooden shelves that act as moisture reservoirs.



Don't let your corks crumble

With HumiditySelect, the humidity can be adjusted in two stages: Standard or High. On models with HumidityControl, this function allows the humidity to be set within a range of 50% to 80% RH* and constantly displays the current value. If it falls below 50% RH*, the appliance indicates this.



Special wood for a special climate

The hand-made wooden shelves have a very special capability: made of permeable beechwood, they absorb and store water, which helps stabilise the climate inside the wine fridge.

Reliable UV protection



For a protected view inside

To minimise the effect of harmful ultraviolet light, all glass doors in Liebherr wine fridges are made of special UV-resistant insulated glass. On models with UV-Protect, the protection comes from a special two-pane construction with a tinted pane on the inside and a metallised Low-E pane on the outside.



Triple protection

For long-term storage, our wine storage fridges with UVProtect Plus offer unprecedented and unique protection against ultraviolet light. Three protective layers consisting of tinted glass and a double layer of vacuum-deposited metal (Low-E).

Safe light

We use high-quality LEDs to ensure even lighting of the interior. That's because their spectrum does not contain any ultraviolet light. And because the LEDs generate very little heat, wines can be lit for lengthy periods without affecting their temperature.



Presented in the best light

The vertically positioned LightColumn evenly illuminates the interior of your Liebherr wine fridge when the door is open. In addition, the dimmable presentation lighting artfully shows off your wines even when the door is closed.



Providing a clear view

Solid door models have a space-saving LED light recessed into the ceiling.

With wine, many things are a matter of taste: including the light.

For centuries, wine led a shadowy existence in cellars. With state-of-the-art Liebherr wine fridges, it now gets the attention we think it deserves: perfectly presented and right at home. But this comes with the responsibility of protecting the wine from harmful elements of the light.

The invisible light in the ultraviolet part of the spectrum causes unwanted chemical reactions in the wine. The consequences are plain to see: red wine become pale and white wines take on a golden yellow colour. Light strike – or “goût de lumière”, as the French call it – destroys the wine’s balance and flattens its aroma. UV protection is also the reason why many wines come in brown or green bottles that act as a light filter – an idea that Liebherr’s engineers have further perfected for the glass door models.

There's a special ingredient for ageing: air.

It's always a marvellous moment when the first glass is poured out of a bottle and the wine unfolds its full bouquet. To ensure that only the wine's own unique aromas come to the fore, protection from external odours is crucial.

During storage, air permeates through the cells of the natural cork and gets into the bottle – and this air consists not only of odourless oxygen, but if the bottles are in a box, the wine can take on the smell of the cardboard too. Food smells can be even more of a problem. When kept at home, especially in unfiltered kitchen air, every wine eventually loses the unique character and the wine spoils.

Besides natural cork, there are other ways of sealing wine bottles. Screw tops in particular have been much improved over the years and are perfectly good at what they are designed to do. However, because screw tops are not as breathable as natural cork, the great wines for collections still mainly have traditional cork stoppers.



Constant fresh air

To ensure that your wine is stored with the optimum air quality, all Liebherr wine fridges have an easy-to-change activated charcoal filter that reliably binds all kinds of odour. Every six months, the appliance reminds you to change the filter.



Up to three filters

Liebherr multi-temperature wine fridges have a separate filter in each compartment. There can be up to three filters, depending on the model.



Nothing to smell here

Liebherr only uses the highest-quality materials, without harmful or unpleasant smells, for example, the natural beechwood shelves, odourless paints and plastics, such as those used in our door seals, guarantee clean air for your wines.

Letting wine mature in peace is a challenging task.

There's a reason why pictures of wine in cellars radiate a pleasant calm. Their underground location effectively prevents vibrations. It's a good thing too, because vibrations make your wine age too fast.

For Liebherr wine fridges, our engineers had to come up with some clever ideas to replicate these conditions in a home environment.

Vibrations from machinery, traffic or people walking by can stir up the sediment in the bottom of the bottle. This increases the reaction of the substances in the wine with each other, which will negatively affect its quality.

Presentation Board



Strength is found in serenity

Specially developed, exceptionally low-vibration compressors, ensure gentle storage in Liebherr wine fridges. The entire refrigeration system is installed with cushioning to prevent the transmission of harmful vibrations. The most noticeable effect of this is how quiet your Liebherr wine fridge is.



Gentle closing

The SoftSystem soft stop mechanism ensures particularly gentle door closing and prevents harmful vibrations. From an opening angle of 45° for freestanding, and 30° for fully integrated appliances, the door closes automatically to maintain the temperature in the appliance.



Optimum location

The wine can mature in peace on the stable, handmade wooden shelves. The shelves have been designed to ensure optimal and safe storage of Bordeaux bottles. However, other bottle shapes can be accommodated just as conveniently. If the bottles are placed directly beside each other, the capacity of the appliance can be fully utilised. In the Vinidor models, the wooden shelves are on telescopic rails. This ensures a good view and easy access to the bottles at the back. The presentation shelf shows off exquisite wines and keeps open bottles at exactly the right temperature.



We protect your treasures.

Protecting a valuable wine collection is a great responsibility. With a wide range of security features, Liebherr wine fridges ensure the maximum possible protection for your treasured wines.



On the alert as soon as it's open

If the door of your Liebherr is open for more than 60 seconds, a door alarm is activated. The door alarm sounds audibly and – depending on the model – is accompanied by pulsing lights.




Everything under control

Securing a wine collection with a door lock is one thing, but it's also important to prevent unauthorised use of the wine fridge. The display lock, which is activated via the menu, ensures reliable security.



Keep your treasures for yourself

Your wine collection is precious, and ought to be protected as such. A mechanical door lock ensures that access to the wine is always under full control.



Full protection

Like a wine cellar, Liebherr wine fridges have everything you need to store your wine under perfect conditions. Nevertheless, there are malfunctions that can occur and give cause for concern. This is why our appliances are equipped with various alarm functions. If something critical happens, they will reliably let you know.

Keep an eye on your wine. Wherever you are.

Even when you're out and about, you want to know that everything is all right in the wine fridge. Our SmartDevice app keeps you in touch with your appliance wherever you are, so that you can take action whenever you need.

Smart
Device


Smart
Device
ready



The latest generation of Liebherr wine fridges are either factory-equipped with a network connection module* or can be retro-fitted with a SmartDeviceBox. A network-connected wine fridge opens up a whole new world. You benefit from all the SmartDevice app options and the integration of the wine fridge into your existing smart home. This allows easy control of the appliance via voice assistant, and access to many functions is also possible while on the move: from basic settings to monitoring and setting the temperature and controlling the presentation light.

In addition, important status and alarm notifications are sent directly to your smartphone, for example, a notification when the door of the wine fridge is left open. As well as simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr wine fridge. You'll also find suitable accessories for your appliance, access to operating instructions and much more besides.

The SmartDevice technology gives you maximum convenience and assurance when storing your wine collection.



It's simple with the app

Show your wine in the best light. From the comfort of your sofa.



Find out more about our SmartDevice network solution here:
home.liebherr.com/getsmart

*Appliances with a built-in SmartDeviceBox are identified by the lowercase "i" behind the model designation (e.g.: WPbli 5231). Availability may vary according to country.

Would you like anything else?

People's requirements when using wine fridges are as diverse as their tastes in wine. We offer a full range of accessories to cater for your individual needs.





Organisational systems

Customise it: accessories for clearly sorting bottles include presentation shelves, bottle holders and additional bottle shelves. Labelling systems provide a clear overview of wine stocks.



Precise fitting – perfect appearance

Connection kits, accessory drawers, and stainless steel frames and fronts with matching handles are just some of the many accessories that can be used for completely individualised and optically perfect integration of the wine appliance.



Accessories and care products

Wine appliances have elements that must be regularly replaced for optimum performance, for example, the FreshAir activated charcoal filter. Care products compatible with Liebherr appliances and materials make cleaning easier and preserve their high-quality appearance.

Other accessory ideas

can be found online with your dream model at home.liebherr.com

Overview of our wine fridge range.





WSbli 7731 GrandCru Selection

Temperature ranges

+5 °C to +20 °C

+5 °C to +20 °C

+5 °C to +20 °C



2
Zones

3
Zones

With two or three temperature zones that can be separately adjusted accurately to the degree from +5 °C to +20 °C, our **multi-temperature wine fridges** offer maximum flexibility of use. That means that red wines, white wines and champagnes can all be stored at their ideal temperature in a single appliance with three temperature zones. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each individual wine collection.

Temperature range

+5 °C to +20 °C



1
Zone

Our **wine storage fridges** replicate the conditions of a wine cellar. A constant temperature is maintained throughout the interior of these appliances. This can be adjusted to between +5 °C and +20 °C, as required. Wine storage fridges are specially designed to hold a large number of bottles for storing and maturing, but they can also keep a larger stock of wine at drinking temperature.

Temperature range

+5 °C to +20 °C




1
Zone

Our **wine serving fridges** are designed for the specific requirements of restaurateurs and caterers, and therefore, for particularly intensive use and smooth customer service. Details designed to optimise security, hygiene and robustness as well as their alluring lighting, make these appliances an attractive and reliable partner for selling and serving wine.



Our **compact appliances** offer refrigeration for special requirements. The fridge is perfect for presenting small quantities of wine bottles. Valuable cigars are kept under optimal storage conditions in the humidor.







Bordeaux bottle size (0.75 l)

All specifications regarding bottle capacity refer to these dimensions.






Freestanding wine fridges

Freestanding compact appliances

	<div>← 75 →</div> 	<div>← 70 →</div> 	<div>← 60 →</div> 	<div>← 43 →</div> 
Width in cm				
Multi-temperature wine fridges		WTes 5872 P. 33	WTes 1672 P. 33	
		WTes 5972 P. 33		
		WTpes 5972 P. 33		
Wine storage fridges	WSbli 7731 P. 36		WPbli 5231 P. 36	WKes 653 P. 45
			WSbli 5231 P. 36	
			WPbli 5031 P. 37	
			WSbli 5031 P. 37	
			WPbl 5001 P. 37	
			WSbl 5001 P. 37	
			WPbl 4601 P. 38	
			WSbl 4601 P. 38	
			WPbl 4201 P. 38	
			WSbl 4201 P. 38	
			WKb 1812 P. 39	
Wine serving fridges	Wfbli 7741 P. 43		Wfbli 5241 P. 43	
			Wfbli 5041 P. 43	
Humidor				ZKes 453 P. 45

Fully integrated wine fridges

Under-worktop wine fridges

					
Niche height in cm					
Multi-temperature wine fridges	EWGgb 3583 P. 50	EWGgb 2383 P. 51	EWGgb 1683 P. 52		UWGgb 1682 P. 55
	EWGgw 3583 P. 50	EWGgw 2383 P. 51	EWGgw 1683 P. 52		UWTes 1672 P. 55
	EWGdf 3553 P. 50	EWGdf 2353 P. 51	EWGdf 1653 P. 52		
Wine storage fridges				WKEgb 582 P. 54	UWKes 1752 P. 55
				WKEgw 582 P. 54	
				WKEes 553 P. 54	



WPbli 5231 GrandCru Selection

Freestanding wine fridges



Key features



LED lighting

Each compartment has dimmable and permanently switchable LED lighting, which guarantees even illumination of the interior. The very low heat generation of the LEDs means that wines can be illuminated for presentation for long periods without any problems.



SoftSystem

The SoftSystem soft stop mechanism cushions the movement when closing the door. This guarantees very gentle closing, and prevents vibrations, which could harm the wine. From an opening angle of 45°, the door also closes automatically.



Presentation shelf

The presentation shelf shows off exquisite wines to perfection and keeps open bottles at exactly the right temperature. Up to six wine bottles can be placed upright on the versatile shelf. Other bottles can be stored lying down behind or beside them.



Touch electronics

The innovative touch electronics with LC display ensure that the temperatures set in the individual compartments are kept constant. The digital temperature display shows the values set accurately to the degree. All the functions can be easily and conveniently adjusted by gently tapping the touch interface.



Aluminium handle with integrated opening mechanism

The tinted insulating glass door guarantees UV protection as well as a perfect view of the bottles. The elegant aluminium handle with integrated opening mechanism guarantees that the door can be opened with minimum force.



Clip-on labelling system

Stable wooden shelves on telescopic rails offer a good view and convenient access. The handmade shelves made from untreated wood are optimally designed for safe storage of bottles. If the bottles are placed directly next to each other, it is possible to make full use of the appliance volume. The flexible clip-on labelling system provides a quick and orderly overview of the wines.



WTes 5872 Vinidor



Detailed model descriptions
can be found at:
home.liebherr.com/wine

Freestanding multi-temperature wine fridges



← 70 →

WTes 5872

Vinidor

Energy efficiency class:	
Energy consumption year / 24 hrs:	206 / 0.564 kWh ¹
Max. Bordeaux bottles 0.75 l:	178
Total volume:	503 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d):	192 / 70 / 74.2 ¹

3 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Presentation Board	LED
Steel Interior								



← 70 →

WTpes 5972

Vinidor

Energy efficiency class:	
Energy consumption year / 24 hrs:	191 / 0.523 kWh ¹
Max. Bordeaux bottles 0.75 l:	155
Total volume:	521 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d):	192 / 70 / 74.2 ¹

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Telescopic Rails	Easy Serve Basket	LED	Steel Interior
---------	-----------------	-----------	------------	--------------	------------------	-------------------	-----	----------------



← 70 →

WTes 5972

Vinidor

Energy efficiency class:	
Energy consumption year / 24 hrs:	191 / 0.523 kWh ¹
Max. Bordeaux bottles 0.75 l:	211
Total volume:	521 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d):	192 / 70 / 74.2 ¹

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Presentation Board	LED
Steel Interior								



← 60 →

WTes 1672

Vinidor

Energy efficiency class:	
Energy consumption year / 24 hrs:	139 / 0.380 kWh ¹
Max. Bordeaux bottles 0.75 l:	34
Total volume:	95 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d):	82.2 / 59.8 / 57.5

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Telescopic Rails	LED	Steel Interior
---------	-----------------	-----------	------------	--------------	------------------	-----	----------------

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Key features



TempProtect Plus

Double protection. With TempProtect Plus, our wine storage fridges constantly measure the temperature with two sensors. This gives you double the assurance that your wines are protected from temperature fluctuations. You're alerted as soon as one of the sensors detects a critical change in temperature, allowing you to take action quickly.



Humidity regulation

With HumiditySelect, the humidity of GrandCru models can be adjusted in two stages: dehumidify or humidify. GrandCru Selection models are equipped with HumidityControl. This function allows the humidity to be set as required within the range of 50% to 80% RH*. If the value falls below 50% RH, the appliance indicates this.



UVProtect Plus

Triple protection. For long-term storage, the wine storage fridges with glass door offer unprecedented protection from ultraviolet light: three protective layers consisting of tinted glass and a double layer of vacuum-deposited metal. Known as Low-E coating, it provides highly efficient protection for your wine against harmful sunlight.



Mechanical door lock

Keep your treasures to yourself. Wine collections are also valuable investments and ought to be protected as such. A mechanical door lock ensures that you always have control of who accesses the wines in your GrandCru Selection wine storage fridge. The lock is flush-mounted and blends unobtrusively into the overall design.



Neck-to-neck storage for maximum bottle capacity

Maximum capacity. A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there is plenty of room even for ever-increasing wine collections. So feel free to keep collecting.



Rear wall panel: Metal, graphite grey

An interior worthy of your wine. The combination of wooden shelves and an elegant metal rear wall panel in graphite grey make the interior of your GrandCru wine storage fridge an eye-catcher even when empty. But the rear wall panel is not just a design element, it also provides sophisticated air circulation and is a stylish element that separates the wine from the technology behind it.



SelfClosing Door with EasyFill loading aid

Lighten the load. The EasyFill loading aid ensures that the door of your wine storage fridge remains open from an angle of 90° for particularly easy stocking. Thanks to the SelfClosing mechanism, the door closes all by itself when opened less than 90° – as gently as valuable wines require.



VibrateSafe

Your wine needs peace and quiet. That's why our wine fridges guarantee gentle storage with particularly quiet compressors specially developed by Liebherr and stable wooden shelves made of solid beechwood. This allows your wine to mature quietly and undisturbed.



Single-sided LightColumn

For a perfect view of your wine: the LED LightColumn runs from the top to the bottom of your glass door appliance. It evenly illuminates the interior of your GrandCru Selection wine storage fridge. A special highlight is the dimmable presentation lighting for attractively showing off your wine collection even when the door is closed.



FreshAir activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine storage fridges have an activated charcoal filter that reliably protects wine from all odours. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every six months to change the filter, which you can easily do yourself.



Security

Protecting a valuable wine collection is a great responsibility. This is why our wine storage fridges come with a comprehensive security package. Sophisticated alarm functions provide audible and optical alerts before the wine can come to any harm.



SmartDevice

Keep an eye on your wine wherever you are. All new wine storage fridges come network-ready or can be integrated into the smart home via the SmartDeviceBox accessory. This way, you benefit from the advantages of the SmartDevice app and have access to your appliance from anywhere. You can change settings on the go, view the temperature and get security information on your smartphone.

* At temperatures in home environments. In very dry or cold environments such as home cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.


Freestanding wine storage fridges



← 75 →

WSbli 7731

GrandCru Selection

Energy efficiency class:	
Energy consumption year / 24 hrs:	102 / 0.279 kWh ¹
Max. Bordeaux bottles 0.75 l:	324
Total volume:	628 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	204.4 / 74.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							



Detailed model descriptions
can be found at:
home.liebherr.com/wine




WSbli 7731 GrandCru Selection



← 60 →

WPbli 5231

GrandCru Selection

Energy efficiency class:	
Energy consumption year / 24 hrs:	115 / 0.315 kWh ¹
Max. Bordeaux bottles 0.75 l:	229
Total volume:	442 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	188.4 / 59.7 / 76.3 ¹


1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
Light Column	Presentation Light	Steel Interior	Smart Device					



← 60 →

WSbli 5231

GrandCru Selection

Energy efficiency class:	
Energy consumption year / 24 hrs:	96 / 0.263 kWh ¹
Max. Bordeaux bottles 0.75 l:	229
Total volume:	433 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	188.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							

Freestanding wine storage fridges



← 60 →

WPbli 5031

GrandCru Selection

Energy efficiency class:	F ^A _G ¹
Energy consumption year / 24 hrs:	111 / 0.304 kWh ¹
Max. Bordeaux bottles 0.75 l:	196
Total volume:	385 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
Light Column	Presentation Light	Steel Interior	Smart Device					



← 60 →

WSbli 5031

GrandCru Selection

Energy efficiency class:	E ^A _G ¹
Energy consumption year / 24 hrs:	97 / 0.265 kWh ¹
Max. Bordeaux bottles 0.75 l:	196
Total volume:	378 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							



← 60 →

WPbli 5001

GrandCru

Energy efficiency class:	F ^A _G ¹
Energy consumption year / 24 hrs:	113 / 0.309 kWh ¹
Max. Bordeaux bottles 0.75 l:	196
Total volume:	385 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							



← 60 →

WSbli 5001

GrandCru

Energy efficiency class:	E ^A _G ¹
Energy consumption year / 24 hrs:	97 / 0.265 kWh ¹
Max. Bordeaux bottles 0.75 l:	196
Total volume:	378 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Freestanding wine storage fridges



← 60 →

WPbl 4601

GrandCru

Energy efficiency class:	<div><div>F</div><div>A</div><div>G</div></div> ¹
Energy consumption year / 24 hrs:	111 / 0.304 kWh ¹
Max. Bordeaux bottles 0.75 l:	166
Total volume:	328 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	148.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							



← 60 →

WSbl 4601

GrandCru

Energy efficiency class:	<div><div>E</div><div>A</div><div>G</div></div> ¹
Energy consumption year / 24 hrs:	84 / 0.230 kWh ¹
Max. Bordeaux bottles 0.75 l:	166
Total volume:	322 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	148.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								



← 60 →

WPbl 4201

GrandCru

Energy efficiency class:	<div><div>E</div><div>A</div><div>G</div></div> ¹
Energy consumption year / 24 hrs:	95 / 0.260 kWh ¹
Max. Bordeaux bottles 0.75 l:	141
Total volume:	272 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	128.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							



← 60 →

WSbl 4201

GrandCru

Energy efficiency class:	<div><div>D</div><div>A</div><div>G</div></div> ¹
Energy consumption year / 24 hrs:	76 / 0.208 kWh ¹
Max. Bordeaux bottles 0.75 l:	141
Total volume:	267 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	128.4 / 59.7 / 76.3 ¹

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



← 60 →

WKb 1812

Vinothek

Energy efficiency class:	G <small>A t G</small>
Energy consumption year / 24 hrs:	123 / 0.337 kWh
Max. Bordeaux bottles 0.75 l:	66
Total volume:	135 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	89 / 60 / 61.3

1
Zone

Humidity
Select

Fresh
Air

UV
Protect

Vibrate
Safe



← 60 →

WKr 1811

Vinothek

Energy efficiency class:	E <small>A t G</small>
Energy consumption year / 24 hrs:	76 / 0.208 kWh
Max. Bordeaux bottles 0.75 l:	66
Total volume:	128 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Door / side walls:	Full door, burgundy / black
Exterior dimensions in cm (h / w / d):	89 / 60 / 61.3

1
Zone

Humidity
Select

Fresh
Air

Vibrate
Safe



WKb 1812 Vinothek



Detailed model descriptions
can be found at:
home.liebherr.com/wine

For special requirements – exactly the right equipment.

For the special requirements of professional use, such as restaurants and catering, our Perfection series is designed for particularly intensive use and smooth service for guests. Details designed to optimise security, hygiene and robustness, as well as their alluring lighting, make Liebherr wine fridges for professional use an attractive and reliable partner for presentation, selling and serving.



WFbli 5241 Perfection

Freestanding wine serving fridges for professional use



Key features



Strong and flexible

The sturdy metal shelves with beech-wood fronts can be moved as required – for a versatile arrangement of the bottles. The struts provide a secure hold and the coated metal is easy to clean.



Ideal for service

For exceptional service, every movement has to be just right. This means the wines must be clearly arranged and easily accessible, as in our EasyServe basket. Fitted at working height, it slides out smoothly on rails.



Attractive inside and out

The full-height LED LightColumns on both sides evenly illuminate the interior and show off the wine selection to its best advantage. A special highlight is the dimmable presentation lighting, which sets an attractive stage for the wines.



Keeping a grip on things

The ergonomic slimline door handle with integrated opening mechanism has been perfected for frequent use and allows the door to be operated quickly and with little effort – even when opening it several times in quick succession.



Quick and secure with a PIN

The electronic door lock is unlocked by entering a PIN. This prevents unauthorised use and it is also more efficient since the convenient unlocking method enables you to open the door more quickly. Do you want even more security? Our SmartDevice app keeps you informed whether the door is open or closed.



Licence to chill

PowerChill automatically cools down newly stored bottles particularly quickly. Even on busy days with the door constantly being opened, the appliance independently generates the ideal serving temperature and automatically switches back to the usual energy-saving mode.

Freestanding wine serving fridges



← 75 →

WFbli 7741

Perfection

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	121 / 0.331 kWh
Max. Bordeaux bottles 0.75 l:	284
Total volume:	642 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	204.4 / 74.7 / 76.3

1 Zone	Temp Protect Plus	Power Chill	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Touch & Swipe-Display	eDoor Lock
Self Closing Door	Easy Fill	Easy Serve Basket	Light Column	Presentation Light	Smart Device			



← 60 →

WFbli 5241

Perfection

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	117 / 0.320 kWh
Max. Bordeaux bottles 0.75 l:	188
Total volume:	459 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	188.4 / 59.7 / 76.3

1 Zone	Temp Protect Plus	Power Chill	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Touch & Swipe-Display	eDoor Lock
Self Closing Door	Easy Fill	Easy Serve Basket	Light Column	Presentation Light	Smart Device			



← 60 →

WFbli 5041

Perfection

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	111 / 0.304 kWh
Max. Bordeaux bottles 0.75 l:	158
Total volume:	398 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3

1 Zone	Temp Protect Plus	Power Chill	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Touch & Swipe-Display	eDoor Lock
Self Closing Door	Easy Fill	Easy Serve Basket	Light Column	Presentation Light	Smart Device			



Detailed model descriptions
can be found at:
home.liebherr.com/wine

Freestanding compact appliances



Detailed model descriptions
can be found at:
home.liebherr.com/wine



← 43 →

WKes 653

GrandCru

Energy efficiency class:	E <small>A 1 6</small>
Energy consumption year / 24 hrs:	78 / 0.213 kWh
Max. Bordeaux bottles 0.75 l:	12
Total volume:	48 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN (+10 °C to +32 °C)
Door / side walls:	Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d):	61.2 / 42.5 / 47.8



← 43 →

ZKes 453

Humidor

Energy consumption year / 24 hrs:	162 / 0.443 kWh
Total net capacity:	39 l
Noise output:	40 dB(A)
Climate rating:	N (+16 °C to +32 °C)
Door / side walls:	Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d):	61.2 / 42.5 / 47.8



Utensil drawer

The handy utensil drawer of the WKes 653 is for keeping wine accessories, or storing treats such as chocolates, to be enjoyed with the wine served at just the right temperature.



Precise humidity

A litre of distilled water can be filled into the integrated water tray of the ZKes 453. Humidity sensors regulate the water requirement and precisely guarantee the selected humidity between 68% and 75%. A visual display gives prompt information when the water needs to be refilled.



EWtdf 3553 Vinidor

Fully integrated wine fridges



Key features



Tinted insulating glass door

The tinted insulating glass door guarantees UV protection as well as a perfect view of the bottles.



SuperSilent

SuperSilent appliances are extremely quiet due to their design and low-noise components.



TipOpen

For integration into handle-free kitchen fronts, the handleless, full-surface insulated glass door with innovative TipOpen technology is the perfect solution. The glass door opens a few centimetres when tapped. If the door is not opened further after three seconds, the SoftSystem closes it again.



Touch electronics

The innovative touch electronics with LC display ensure that the temperatures set in the individual compartments are kept constant. The digital temperature display shows the values set accurately to the degree. All the functions can be easily and conveniently adjusted by gently tapping the touch interface.



LED lighting

Each compartment has dimmable and permanently switchable LED lighting which guarantees evenly distributed illumination of the interior. Because the LEDs generate very little heat, wines can be illuminated for long periods without any problems.



SoftSystem soft stop mechanism

The SoftSystem soft stop mechanism cushions the movement when closing the door. This guarantees very gentle closing, and prevents vibrations that could harm the wine. From an opening angle of 30°, the door also closes automatically.



Presentation shelf

The presentation shelf shows off exquisite wines to perfection and keeps open bottles at exactly the right temperature. Up to six wine bottles can be placed upright on the versatile shelf. Other bottles can be stored lying down behind or beside them.



FreshAir activated charcoal filter

The multi-temperature wine fridges have an easy-to-change FreshAir activated charcoal filter to ensure optimum air quality inside.



Electronic control system

The precise electronic control system has a digital temperature display. The door and temperature alarm reports any irregularities such as a door left open. A child lock prevents unintentional changes to the settings.



Wooden shelves on telescopic rails

Stable wooden shelves on telescopic rails offer a good view and convenient access. The handmade shelves made from untreated wood are optimally designed for safe storage of Bordeaux bottles. If the bottles are placed directly next to each other, it is possible to make full use of the appliance volume.



Clip-on labelling system

The flexible clip-on labelling system provides a quick and orderly overview of the wines.



Side-by-side concept

With the side-by-side concept, refrigerators, freezers and wine fridges can be positioned exactly as you need them. A special system for compensating between appliances with large temperature differences allows numerous combinations.

Fully integrated multi-temperature wine fridges



↑
178
↓

EWTgb 3583

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	178 / 0.487 kWh
Max. Bordeaux bottles 0.75 l:	83
Total volume:	271 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



↑
178
↓

EWTgw 3583

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	178 / 0.487 kWh
Max. Bordeaux bottles 0.75 l:	83
Total volume:	271 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



↑
178
↓

EWTdf 3553

Vinidor

Insulated glass door / fully integrated panel-ready appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	176 / 0.482 kWh
Max. Bordeaux bottles 0.75 l:	80
Total volume:	254 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Presentation Board	LED
Steel Interior								



EWTdf 3553 Vinidor
Stainless steel frame with handle available as an accessory

Fully integrated multi-temperature wine fridges



↑
122
↓

EWTgb 2383

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G <small>A B C D E F G</small>
Energy consumption year / 24 hrs:	160 / 0.438 kWh
Max. Bordeaux bottles 0.75 l:	51
Total volume:	169 l
Noise output / noise class:	31 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



EWTgb 2383 Vinidor



↑
122
↓

EWTgw 2383

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G <small>A B C D E F G</small>
Energy consumption year / 24 hrs:	160 / 0.438 kWh
Max. Bordeaux bottles 0.75 l:	51
Total volume:	169 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



↑
122
↓

EWTdf 2353

Vinidor

Insulated glass door / fully integrated panel-ready appliance

Energy efficiency class:	G <small>A B C D E F G</small>
Energy consumption year / 24 hrs:	158 / 0.432 kWh
Max. Bordeaux bottles 0.75 l:	48
Total volume:	158 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Presentation Board	LED
Steel Interior								

Fully integrated multi-temperature wine fridges



↑
88
↓

EWTGb 1683

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>G</div></div>
Energy consumption year / 24 hrs:	151 / 0.413 kWh
Max. Bordeaux bottles 0.75 l:	33
Total volume:	104 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



↑
88
↓

EWTgw 1683

Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>G</div></div>
Energy consumption year / 24 hrs:	151 / 0.413 kWh
Max. Bordeaux bottles 0.75 l:	33
Total volume:	104 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Presentation Board
LED	Steel Interior							



↑
88
↓

EWTdf 1653

Vinidor

Insulated glass door / fully integrated panel-ready appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>G</div></div>
Energy consumption year / 24 hrs:	150 / 0.411 kWh
Max. Bordeaux bottles 0.75 l:	30
Total volume:	97 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Presentation Board	LED
Steel Interior								



Side-by-side concept

With the side-by-side concept, refrigerators, freezers and wine fridges can be positioned exactly as you need them. A special system for compensating between appliances with large temperature differences allows numerous combinations.



Detailed model descriptions
can be found at:
home.liebherr.com/wine

EWTdf 1653
multi-temperature wine fridge
combined with refrigerator,
full space BioFresh refrigerator
and NoFrost freezer



Fully integrated wine storage fridges



45

WKEgb 582

GrandCru

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>F</div><div>G</div></div>
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Max. Bordeaux bottles 0.75 l:	18
Total volume:	47 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	45.2 / 56 - 57 / at least 55

1 Zone	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Light Column
Steel Interior								



45

WKEgw 582

GrandCru

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>F</div><div>G</div></div>
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Max. Bordeaux bottles 0.75 l:	18
Total volume:	47 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	45.2 / 56 - 57 / at least 55

1 Zone	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open	Light Column
Steel Interior								



45

WKEes 553

GrandCru

Flush / fully integrated appliance

Energy efficiency class:	<div><div>G</div><div>A</div><div>F</div><div>G</div></div>
Energy consumption year / 24 hrs:	140 / 0.383 kWh
Max. Bordeaux bottles 0.75 l:	18
Total volume:	51 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Insulated glass door with stainless steel frame, recessed handle
Aperture dimensions in cm (h / w / d):	45 / 56 / at least 55

1 Zone	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Telescopic Rails	LED	Steel Interior
--------	-----------------	-----------	------------	--------------	------------------	-----	----------------



Accessory drawer

Wine accessories can be kept in the smooth-running accessory drawer directly under the WKE models. A handy inlay provides a safe place for six wine glasses and other items. The accessory drawer is available for 45 cm and 60 cm recesses and comes in black glass, white glass and stainless steel.



82-87

UWTgb 1682

Vinidor

Flush / under-worktop appliance

Energy efficiency class:	G <small>A+ G</small>
Energy consumption year / 24 hrs:	138 / 0.378 kWh
Max. Bordeaux bottles 0.75 l:	34
Total volume:	94 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 / at least 58

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Soft System	Telescopic Rails	Tip Open
LED	Steel Interior						



UWTgb 1682 Vinidor



82-87

UWTes 1672

Vinidor

Flush / under-worktop appliance

Energy efficiency class:	G <small>A+ G</small>
Energy consumption year / 24 hrs:	142 / 0.389 kWh
Max. Bordeaux bottles 0.75 l:	34
Total volume:	94 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Insulated glass door with stainless steel frame
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 / at least 58

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Telescopic Rails	LED	Steel Interior
---------	-----------------	-----------	------------	--------------	------------------	-----	----------------



82-87

UWKes 1752

GrandCru

Flush / under-worktop appliance

Energy efficiency class:	G <small>A+ G</small>
Energy consumption year / 24 hrs:	139 / 0.380 kWh
Max. Bordeaux bottles 0.75 l:	46
Total volume:	110 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Insulated glass door with stainless steel frame
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 - 61 / at least 58

1 Zone	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Telescopic Rails	LED	Steel Interior
--------	-----------------	-----------	------------	--------------	------------------	-----	----------------

Wine

1 Zone	With constant temperature throughout the interior, adjustable from +5 °C to +20 °C.
2 Zones	With two temperature zones, independently and precisely adjustable from +5 °C to +20 °C.
3 Zones	With three temperature zones, independently and precisely adjustable from +5 °C to +20 °C.
Temp Protect Plus	Two sensors constantly measure the temperature in the wine fridge. A notification is sent in the event of a critical change. *
Power Chill	Newly stored bottles are cooled very quickly and automatically to the ideal serving temperature.
Humidity Control	The humidity can be actively regulated in 5% increments between 50% and 80% RH**.
Humidity Select	The humidity can be adjusted between two levels: Standard or High.
Fresh Air	For a pure bouquet, an activated charcoal filter reliably binds all kinds of odours.
UV Protect	Double protection: a tinted glass door with one layer of vacuum-deposited metal provides efficient protection from sunlight.
UV Protect Plus	Triple protection: a tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from sunlight.
Vibrate Safe	The fully vibration-insulated cooling system allows the wine to mature undisturbed.

Design

Steel Interior	Not just an attractive design element, the SmartSteel stainless steel rear wall panel ensures balanced air circulation.
Light Column	LED light column from top to bottom evenly illuminates the interior. On one side or both depending on the series.
Presentation Light	Effectively showcases the wine collection even when the glass door is closed. The brightness can be dimmed using the display. *
LED	Low heat, energy-saving and maintenance-free for optimum illumination.

Convenience and flexibility

Soft System	Very soft door closing, even when fully loaded, automatically below an opening angle of 30°.
Telescopic Rails	Drawers on smooth telescopic rails for convenient opening and closing, and easy removal.
Touch & Swipe-Display	Intuitive fridge control – simply by touching and swiping the colour display.
Touch-Display	A Liebherr is really simple to use with a gentle tap of a finger on the clear touch display.
eDoor Lock	An electronic door lock prevents unauthorised use and only unlocks the wine fridge after a correct PIN has been entered. *
Tip Open	The glass door opens by 7 cm when tapped for easy access and full opening.
Self Closing Door	The door of the wine fridge closes smoothly by itself when opened less than 90°.
Easy Fill	Loading aid for easy stocking of the wine fridge. From an angle of 90°, the door remains open.
Presentation Board	Shows off exquisite wines and presents bottles that have been opened.
Easy Serve Basket	The bottle basket for clearly arranged storage and easy accessibility at the bar.

Connectivity

Smart Device	The integrated SmartDeviceBox enables you to control the appliance and use additional services via computers and mobile devices.
Smart Device ready	The SmartDeviceBox can be retro-fitted so that you can control the appliance and use additional services via computers and mobile devices. Available as an accessory.

Special product groups

Cigar	Innovative features and perfect climate for fine cigars.
-------	--

*Can also be used via SmartDevice/Smart app.
**At temperatures in home environments. In very dry or cold environments such as home cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.

Stay in touch.

Our catalogue programme

Ask your Liebherr dealer for our main catalogues for freestanding and fully integrated appliances. All catalogues can also be downloaded from home.liebherr.com.



SmartDevice app: Your smart helper conveniently operates all Liebherr appliances, sends you important status messages and offers many other services for your Liebherr.



You can download our apps here.



Our complete range of freshness products and a list of Liebherr specialist dealers can be found at: home.liebherr.com



UWTgb 1682

Vinidor

2
Zones

Humidity
Select

Fresh
Air

UV
Protect

Vibrate
Safe

Soft
System

Telescopic
Rails

Tip
Open

LED

Steel
Interior



home.liebherr.com

Products and their details are staged for advertising purposes.
Subject to technical changes. Colours may differ due to media used.
Printed in Germany by Raff & Cantz Druck GmbH. 7901 689-00. 06/23. EN/LEX

