

---

# Freestanding appliances 2023/2024

---

## **LIEBHERR**

Refrigeration and freezing





## Timeless Freshness

---

When it comes to groceries, you care about top quality and an authentic culinary experience. You take detours to visit stalls selling regional cheeses, you appreciate freshly caught fish, and you like to grow your own radishes. Wouldn't it be great if you could still taste this quality, even after several days in the fridge? Almost as if time were standing still? We think it would.

That is what motivates us to constantly develop new and even better solutions that guarantee perfect storage conditions for all kinds of groceries. For long-lasting freshness, to protect valuable vitamins, and for food that tastes as if it had just been bought or harvested. But why not find out for yourself? Check out our 2023 freestanding units.



RDsfe 5220 ◊ Plus series

# Contents

Liebherr Corporate Group	6
Quality	8
Product responsibility	10
World first: BluRoX	14
Freshness technologies	16
EasyFresh	18
BioFresh	19
BioFresh Professional with HydroBreeze	20
BioFresh Professional with Fish & Seafood Safe	22
Design	24
Convenience and flexibility	30
Water and ice	36
Connectivity	40
User interface	42
Flexible accessories	44
Series	46
<b>Freshness centres</b>	<b>48</b>
Side-by-Side fridge-freezers	52
Frenchdoor fridge-freezer	64
<b>Fridge-freezers</b>	<b>66</b>
Fridge-freezers (with bottom freezer)	66
Fridge-freezers (with top freezer)	98
<b>Fridges</b>	<b>100</b>
<b>Freezers</b>	<b>130</b>
<b>Chest freezers</b>	<b>152</b>
<b>Wine Fridges</b>	<b>156</b>
<b>Design &amp; LifeStyle</b>	<b>172</b>

# Global success: The Liebherr Group.

Liebherr is a third-generation, family-owned company founded in 1949 by Hans Liebherr with his ground-breaking invention of the world's first mobile tower crane.

With over 70 years of success, Liebherr is known as a pioneer in high-quality, breakthrough innovations and countless cutting-edge technologies in numerous industries. One of the world's largest manufacturers of construction machinery, Liebherr has expanded its broadly diversified portfolio to 13 product segments including earthmoving, deep foundation machines, mobile and crawler cranes, tower cranes, concrete technology, material handling technology, mining, maritime cranes, aerospace and transportation systems, gear technology and automation systems, components, hotels and refrigeration and freezing. The company currently employs about 48,000 people in more than 140 companies in over 50 countries worldwide.



Mobile cranes



Deep foundation



Earthmoving



Crawler cranes



Refrigeration and freezing



Liebherr-Hausgeräte GmbH, Germany

## Liebherr-Hausgeräte – Specialists in refrigeration and freezing.

Liebherr-Hausgeräte covers the full range of refrigeration and freezing for domestic and commercial use. Headquartered in Germany, Liebherr-Hausgeräte has an impressive range of more than 3,000 products in its portfolio.

## Even the smallest detail deserves the utmost attention.

We prioritise uncompromising quality – down to the tiniest screw. And we have done so from the very start. We have been manufacturing high-quality refrigerators and freezers and selling them worldwide since 1954. However, at heart we are still a family business with deep roots in Germany. It is here that we continue to develop all our products just as before. German engineering – out of loyalty to our founder and with the knowledge built up by generations of engineers.

### Convenience for everybody.

Our new freestanding units are available in different series: Pure, Plus, Prime and Peak. But whatever series you opt for, every single Liebherr comes with uncompromising Liebherr quality. This is because even in the Pure series, every appliance comes with a wide range of features. One example is NoFrost – the automatic defrosting function. Another is our EasyFresh technology for storing fruit and vegetables. Then there is our DuoCooling feature. With two separate refrigerant circuits, it ensures that no air is exchanged between the fridge and freezer compartments. The stored groceries do not dry out and no odours are transferred.



CNbdd 5733 ◊ Plus series

### Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long.

And if, contrary to expectations, a small detail no longer meets your requirements, you or our premium service partners can usually correct it quickly. Because all our appliances are extremely repair-friendly. We keep all essential spare parts in stock for well over 10 years. This practice is not just sustainable, it also saves you money on minor repairs or the purchase of a new appliance.

### We don't just say it. We also guarantee it.

During manufacturing we inspect all components of our refrigerators with great care and test them far more rigorously than required by law – and we do this for the last time just before they are packaged. It is only then that our appliances can relax a little. All of our manufacturing sites are certified in accordance with the international standards for quality ISO 9001, energy management ISO 50001 and environmental management ISO 14001. Therefore, nothing could be easier for us than to guarantee for at least two years that our products are free of material and manufacturing faults and are particularly easy to install.

In short: one thing is certain – you will be able to enjoy your Liebherr for a long time.



EasyFresh for fruit and vegetables from the Pure series upwards.



Magnetic door gasket ensures safe closing.

# Thinking beyond just today.

We are fastidious in adopting a holistic approach to sustainability when designing our appliances. The key elements of this are the durability of our appliances, maximum energy efficiency and reducing food waste. Why do we do all this? Because a holistic approach is needed to protect both people and the environment in equal measure.

## Reducing food waste.

Everyone who stores food in the optimum climate plays a big part in reducing unnecessary food waste. Our appliances make this possible – with a combination of innovative features:

First: Our freshness technologies. DuoCooling in our fridge-freezers, for example, prevents your groceries from drying out faster than need be. Innovative freshness technologies such as BioFresh ensure perfect storage conditions that significantly extend product life and freshness. So there's no need to throw food away before its time, and you don't need to go shopping so often. And the largest zero-degree compartments on the market provide enough space for extra-large amounts of groceries.

Second: Our SmartDevice app also helps you to store your food properly, giving your food a longer shelf life so you can enjoy it for even longer.

Third: Our appliances are intelligent and let you know if perfect storage for your groceries is at risk. For example, by using a door alarm to tell you if the appliance door is still open.



## Efficient in every aspect.

This year's range is also filled with appliances which rank among the most energy-efficient available on the market. And that goes for all our product groups: fridges, freezers and fridge-freezers in the new freestanding appliance generation.

Of course there are plenty of other details, some very minor, that make a significant difference to a Liebherr in terms of efficiency, such as the many energy-saving modes. These include EnergySaver, which increases the standard temperature to +7 °C, or HolidayMode, which only cools those items which really need to be kept chilled when you are on holiday, as well as CleaningMode for energy-efficient cleaning of your appliance.

## Quality for people and the environment.

Responsible handling of resources using durable materials. Our concern for the next generation means we work exclusively with long-life vacuum panels and natural refrigerants, and we will not use any HFO propellants until their environmental effects are fully understood. Even in the manufacturing process, we are mindful of the environment. We predominantly install materials that can be recycled after the appliance is scrapped. We also ensure that excess plastic is consistently reused.



### Liebherr RBa 4250 ◉ Prime series

With this BioFresh fridge, we have managed to achieve the maximum energy efficiency class with a balanced complete package.

Thanks to Interior-Fit, the appliance does not need ventilation gaps on the sides, and thus fits seamlessly into your kitchen. It also has one of the most spacious BioFresh safes on the market.



## For water without plastic.

Our InfinitySpring brings cold, perfectly filtered water right to you in the kitchen. Cutting your need for plastic bottles.

# Perfectly thought out: a powerful, complete package.

Our fridges are real all-rounders. Along with their low power consumption, they also have impressively low noise levels, plenty of space for groceries, a long service life and reliable power reserves for when it really matters. We take account of a great many factors during the development stage and can offer a perfectly balanced appliance. Or to put it another way: all good things come in fours.



## Energy consumption

Our new freestanding units occupy top positions in the efficiency rankings. In this way, they protect the precious resources of our environment and – thanks to low electricity costs – your wallet too.

## Cooling volume

We have the perfect appliance for all family sizes, lifestyles and niche heights. We make sure that we do not waste a single litre of capacity in the extra-large drawers – right down to the smallest detail, for example with the lighting solutions that have been integrated in the housing to save space.

## Noise level

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. Our new freestanding range therefore offers a wide selection of extremely quiet appliances. In some cases, it even reaches the ultra-quiet noise level of 32 db.

## Cooling performance

Intelligent sensor technology constantly adapts the cooling performance to current use, making our freestanding units very energy-efficient and economical in everyday use. At the same time they also have plenty of power in reserve, for example to cool down a large quantity of groceries after the weekly shop.



### High efficiency: This is how economical a Liebherr can be


You can find out how efficient our appliances are using the online tool from the EU-financed projects LABEL2020 and BELT. At this site ([tool.label2020.eu](http://tool.label2020.eu)) you can view and compare the electricity consumption and lots of other product data for electrical appliances. The calculator also takes account of local electricity prices and shows the costs for the entire period of use. The comparison shows that a Liebherr is worth it!



### Performance in balance perfected: Our BluPerformance technology

What is innovative about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size have a considerably greater net capacity. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. And our appliances are now even quieter. We are certain that this technology will appeal not only to fans of new technology.

### The current EU energy label for electronic appliances



1. The QR code for identifying the product in the EU's EPREL database (European Product Database for Energy Labelling).
2. The model identifier for manual identification of the product in the EU's EPREL database, e.g. using the article number.
3. The new A to G efficiency scale. Note: G is solely used for wine fridges.
4. The total volume\* of all freezer compartments.
5. The total volume\* of all cold storage and refrigerator compartments.
6. The noise level is classified in classes A to D.

\* The term "volume" is defined in current Regulation (EU) 2019/2016.

# BluRoX: Cold insulation with innovative vacuum perlite technology.

BluRoX represents a major step towards an energy-efficient and recyclable future. To transform cooling and freezing in a sustainable way, the pioneering BluRoX technology from Liebherr does not simply use conventional polyurethane foam but instead utilises a much more effective form of cold insulation: a vacuum. Finely ground lava stone, known as perlite, stabilises the vacuumed components – with numerous advantages for people and the environment.



The future is circular.




To learn more about this exciting technology and the many advantages of BluRoX, visit: [home.liebherr.com/blurox](https://home.liebherr.com/blurox)

Available from the 2nd quarter of 2023

## Maximum energy efficiency.

BluRoX provides cold insulation that is so effective that Liebherr models with this innovative vacuum insulation can deliver maximum energy efficiency. The first model is currently the most efficient freezer of its type: the Liebherr FNb 5056 with BluRoX technology in the door.



## More volume.

With the same external dimensions, thanks to BluRoX there is around 25 percent more usable space inside. The particularly effective insulating effect of the vacuum enables walls and doors to be thinner compared to freezers made using polyurethane foam, creating valuable space for all the frozen goods you like to have at home.

## Recyclable product design.

BluRoX is a new type of insulation which does not use conventional polyurethane foam. BluRoX delivers cold insulation using a vacuum that is stabilised with finely ground lava stone (perlite). This creates an incomparably energy-efficient and simultaneously recyclable solution: At the end of the lifespan of a BluRoX freezer, the perlite can be reused without significant processing.



## Unveiled in the Liebherr FNb 5056.

BluRoX can first be seen in the Liebherr FNb 5056. In the door of this freezer, the innovative vacuum insulation celebrates a very special world first: in accordance with the new EU energy label, the Liebherr FNb 5056 is the first freezer of its type to be awarded efficiency class "B". And to ensure this remains the case for many years, the high-quality insulation also boasts the durability that Liebherr is renowned for.

## Tasty for longer.

You don't compromise when you're shopping. You look for natural ingredients, the best quality and maximum freshness. Of course, anyone who values good food wants to keep it fresh for as long as possible. That is precisely why we have developed innovative freshness technologies and improve them year after year, so your food still tastes fresh after some time in the refrigerator.



**Full-space BioFresh. Enough space for an entire field.**  
Especially at harvest time, you may need to store a lot of fruit and vegetables at the same time. Our full-space BioFresh refrigerator is ideal for this. At just over 0 °C and with flexible humidity, everything stays crisp and fresh for a long time. And, if it's a smaller harvest this year, the drawers keep dairy, meat and sausages fresh for longer than in the regular fridge compartment. This appliance is rated in the highest Energy Efficiency Class A.



**EasyFresh. Ideal for fruit and vegetables.**  
Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after 7 days.



**BioFresh. Our all-rounder.**  
The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy safe.



**BioFresh Professional with HydroBreeze. Refrigerate like the professionals.**  
A cold mist that covers fruit and vegetables like a protective balm. It ensures crisp freshness and improves structure - the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



**BioFresh Professional with Fish & Seafood Safe. Like freshly caught fish from the market.**  
Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood Safe is therefore ideal to keep these items tasting fresh for longer.



**DuoCooling. No drying out.**  
The two completely separate refrigeration circuits ensure that there is no air exchange between the fridge and freezer compartments. Groceries do not dry out nor spread odour.




**NoFrost. No more defrosting.**  
The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during manual defrosting. The constant optimal freezing remains the same without interruptions.





Specifications made in days are comparisons to the normal fridge compartment.



# Cool and misty. Perfect weather for your vegetables.

Our HydroBreeze feature exemplifies our highest standard of freshness. A cold mist covers fruit and vegetables like a protective balm in the BioFresh Professional Safe. The mist ensures crisp freshness, improves structure and keeps produce with fine leaves fresh for longer. It also creates an optical wow effect in the BioFresh Professional Safe.




### Nature's freshness secret.

The Salinas valley in California is known as the salad bowl of the USA. And that is because of the particularly favourable climatic conditions. Its proximity to the cool waters of the Pacific means a fine, moist mist covers the valley and its fields in summer. This prevents the crops growing here from drying out. It is precisely this idea which inspired our BioFresh Professional with HydroBreeze.



Every time the door is opened, a fresh, cold mist is generated.

Hydro  
Breeze



+8 days

+10 days

+8 days

+12 days

+40 days

+11 days

+12 days



More about  
HydroBreeze

Specifications made in days are comparisons  
to the normal fridge compartment.

# Like freshly caught fish from the market. Our Fish & Seafood Safe.



To keep fish and seafood tasting as fresh as at the market stall, even after a few days, you need a fridge compartment which maintains their freshness; such as our Fish & Seafood Safe. Fish and seafood can be stored here at -2 °C and low humidity. Perfect conditions to enjoy that freshly caught flavour for much longer.



Specifications made in days are comparisons to the normal fridge compartment.



**Flexible use**  
The surface of the BioFresh Professional Safe can be adjusted to individual requirements. The -2 °C can be partially or even completely adjusted to a temperature zone at just above 0 °C. This is the optimal storage environment for meat and dairy products. We have illustrated these four options below:



## Make a statement. In your kitchen.

---

Fridges stopped being uniform white kitchen appliances a long time ago. Now that dining and living areas are no longer clearly separated, design plays an increasingly important role. The new puristic design language of Liebherr appliances catches the eye with its exceptional lines, elegant surfaces and simple silhouette.

A classic, exclusive look that allows our appliances to blend seamlessly into any modern kitchen and yet still stand out. But there's no need to say any more: after all, the design already speaks for itself.

Our appliances are available with a display integrated in the door. Or, for purists, in the interior of the appliance.



XRFbd 5220 ◊ Plus series



### InteriorFit. Fits perfectly.

Make elegant use of niches in the kitchen. With InteriorFit, our freestanding appliances fit into your kitchen without using much space – they don't need a ventilation gap between the appliance and the walls or adjacent furniture. Only the fridge door itself projects into your kitchen. Everything else is invisible.

# Your options: Elegant, elegant or elegant.

Your kitchen is unique. So why should your fridge be off-the-shelf. Choose from appliances with different high-quality materials, restrained colours and ergonomic handle designs. No matter what you choose: you really can't go wrong with these exclusive options.

## Handle solutions

### Handle with opening mechanism

The door handle adapts gently to your hand movement and is thus even easier to open.




### Recessed grip

This handle does not extend into the room. The elegant recess harmonises with your kitchen's slick, handle-free design.



## Door fronts

Choose from one of the designs below. One thing is certain: your appliance will draw the eye.



XRFst 5295 Δ Peak series

## For groceries with the highest requirements.

---

No matter how much you love the exterior of your Liebherr, at some stage you actually have to open it. So it's lucky that its interior is visually appealing as well.

### Design meets functionality.

Traditional and timeless on the one hand, elegant and exclusive on the other. The new design language seamlessly blends into any interior. The interior features elegant glass and stainless steel elements. The precise machining, an eye for detail and the harmonious combination of materials, shapes and colours create an appealing overall appearance. This is subtly highlighted by the new lighting concept.



The LightTower lighting concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.



## We have made simple even simpler.

Fridges and freezers are used every day. That is why we develop freestanding appliances that offer ease of use, clarity and flexibility – from the first opening of the door down to the tiniest feature.

### Sometimes in life we can have everything we want.

The features of the new freestanding appliances give you more space. The divisible glass shelf, with its effortless one-handed operation, creates space for tall containers and carafes. Do you like things to be well organised? With the VarioBox and the VarioSafe you can store smaller objects neatly in the door or interior – always exactly at the height you like.

How about a cold drink? The glass shelf above the BioFresh safe can be converted into a bottle shelf in next to no time.

In our fridge-freezers with VarioTemp, the freezer compartments can be switched variably to another temperature. As a result, the freezer compartment can be used as a fridge or cellar compartment.

In turn, VarioSpace provides enough space in the freezer compartment for even the largest turkey or tallest ice-cream cake. Speaking of cake: For fans of baking, the fridge compartments in our fridges and fridge-freezers are even spacious enough for a full baking tray.

### Full of food. And convenience.

The drawers in the fridge and freezer compartments of our appliances glide in and out smoothly on telescopic rails, so all your groceries are always in perfect reach. Rails also support the pull-out tray with two bottle baskets, which are easy to remove by their built-in handles. And even once you have found all the ingredients and drinks you need, things remain convenient. Thanks to the SoftSystem. This means that our doors always close gently and quietly, even if the force applied is a little too strong.





**Drawers on telescopic rails**  
Pleasantly easy opening and closing – even when fully loaded – ensures that all of the groceries are perfectly accessible.



**FlexSystem**  
Ensures clear order in the BioFresh safe. It is perfect for storing smaller portions of fruit and vegetables or sensitive groceries.



**VarioSafe**  
Allows you to arrange smaller items clearly in the interior – at whatever height you prefer.

## Variable temperature space as required

With VarioTemp, there is flexibility for every situation. The freezer compartment can be adjusted to a variable temperature between  $-2\text{ }^{\circ}\text{C}$  and  $+14\text{ }^{\circ}\text{C}$ .

As a result, you are always perfectly prepared, even for big parties. If necessary, the freezer compartment can be used as an additional cooling zone for appetisers or drinks. Or as a cellar compartment for groceries that are sensitive to cold, such as potatoes, onions and other similar items.

Your family has grown and you are running out of space in your fridge-freezer? Not a problem. VarioTemp allows you to use the freezer compartments as a fridge in your kitchen. If combined with a separate freezer, this means you have enough space to supply even a large family with fresh groceries.



Use as freezer compartment ( $-18\text{ }^{\circ}\text{C}$ )



Use as fridge compartment (between  $-2\text{ }^{\circ}\text{C}$  and  $+9\text{ }^{\circ}\text{C}$ )



Use as cellar compartment ( $+14\text{ }^{\circ}\text{C}$ )



**Freezers that are difficult to open:  
Now a thing of the past.**

Thanks to the new EasyOpen technology, our freezers can be opened smoothly and easily at any time. Even without a handle. How do we do it? With the help of an innovative door gasket and the new BluPerformance technology module, we have managed to reduce the door-opening force by half. Space-saving, simple, convenient.



**SpaceBox**  
Ideal for anything that requires a little more space.



**SoftSystem soft stop mechanism**  
The particularly quiet and soft door closing mechanism is integrated into all models from our Prime series upwards.




**VarioSpace**  
Handy for large frozen items, for example a tiered birthday cake.

## This spring has its source in the fridge.

With the InfinitySpring, we bring a crystal clear, cold water source right into the heart of your kitchen. Because water is healthy. This makes lugging heavy crates and water in plastic bottles a thing of the past. This relieves the strain on your back and on our environment. Simple and sustainable.

### Ice-cold water on tap with no heavy lifting.

The flush-mounted water dispenser is always there when it is needed and almost invisible when it's not. It is suitable for containers of almost any size, including carafes or bottles for soda makers. The integrated filter system ensures perfect water quality. By the way, unlike traditional table-top water filters, this one only needs to be replaced every six months.



### BottleTimer.

Provides extra-fast cooling for drinks. And reminds you via the SmartDevice app not to forget bottles in the freezer compartment.

## Cocktails will run out before the ice does.

You like inviting people around and enjoy having as many guests as possible? Then you will love our ice features. One thing is certain: no drink will remain uncooled at your party.



### Enough ice for even the largest party: the IceTower.

The IceTower in our freezers sets new standards. It combines two large compartments: the automatic IceMaker for up to 8 kilograms of ice cubes, and another spacious compartment – large enough to store a few family pizzas upright, for example. And because this was not convenient enough for us, both of them glide in and out on a pull-out shelf with telescopic rails. We have even included an ice scoop, so your hands stay warm.



### Ice in a jiffy with EasyTwist Ice.

Make a supply of ice cubes quickly – without a fixed water connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. The EasyTwist Ice is simple to clean, and is installed in most of our freestanding appliances in the Pure series. Alternatively, it can be added easily as an accessory.



### Rains ice cubes: the IceMaker.

The IceMaker produces up to 130 ice cubes a day, which automatically drop into two drawers. When MaxIce is activated, it is even possible to speed up the production of ice cubes if more guests arrive than expected. The IceMaker is connected to the fresh water pipe. If no fixed water connection is available, there is also a model with a water tank in the fridge compartment.

## We are already providing what the future will bring.

One thing is clear: Technology will get smarter and smarter in the future. But does a fridge need to be intelligent? It doesn't have to be. But we believe: Another cool head in the household can't do any harm. Thanks to many smart functions, our appliances have proven themselves to be reliable helpers behind the scenes.



### Built-in progress.

Your fridge helps with thoughtful features whenever it can. For example, it reminds you of forgotten drinks in the freezer – thanks to the integrated BottleTimer. Making burst bottles a thing of the past.

NightMode is especially interesting for anyone who is sometimes drawn to the fridge late at night. The interior is then only illuminated with a dimmed light. Then after your midnight snack, you can quickly go back to bed and not wake up from your half-asleep state.



Learn how digitally networked refrigeration makes your everyday life easier:  
[home.liebherr.com/getsmart](http://home.liebherr.com/getsmart)

### Always perfectly networked.

All our new freestanding models are either already networked at the factory or can be retrospectively connected to a WiFi network using a SmartDeviceBox. Appliances with a built-in SmartDeviceBox can be identified by the lower-case "i" behind the model designation (e.g.: RBstd 528i). You therefore benefit from all our SmartDevice app options and from integrating the refrigerator into an existing Smart Home environment.

Important status and alarm notifications are sent directly to your smartphone, for example notification of an open fridge door via door alarm. However, our SmartDevice app has much more to offer. Besides the simple management of appliances and controlling them while on the move, the app also helps with storing food correctly and therefore provides even greater culinary enjoyment and extends shelf-lives. The right accessories for each refrigerator, access to guarantee extensions and much more can also be found here.

In short, our appliances prepare people for tomorrow, today.

### We play it very, very safe.

We take data protection very seriously. For this reason, we have chosen a software partner who shares our high standards: Microsoft. Microsoft, as the first leading provider of cloud services, is certified in accordance with the international standard ISO/IEC 27018, which regulates data protection, and uses AES-256 – the same encryption technology employed in the banking sector.

Availability may vary according to country.



Learn how digitally networked refrigeration makes your everyday life easier:  
[home.liebherr.com/getsmart](http://home.liebherr.com/getsmart)

You can download the SmartDevice app here:



# Refrigerators, that leave all your options open – and your doors closed.

We don't develop refrigerators with the most functions. We develop refrigerators with exactly the right functions to store food safely and give our customers what they really need. To make their lives noticeably easier. And then we implement these features to technical perfection.



Display in the door



Display behind the door

## You can never be too safe.



**Door alarm**  
Alarm when the door is open, visual as well with pulsating LED lighting.



**Temperature alarm**  
Visual and audible warning as soon as the temperature in the freezer compartment reaches a critical level.



**Power failure alarm**  
Visual and audible alarm in case of power failure for safe storage.



**Appliance failure alarm**  
Optical and acoustic warning in case of appliance failure.



**Reminder**  
Automatic reminder for maintenance and care.



**Input lock**  
Prevents all changes to settings or activation of functions.



**DemoMode**  
For optimal presentation of the appliance in showrooms: User interface and lighting on, cooling system off.

## A touch more convenience.



**CleaningMode**  
For a perfect view when cleaning, the lights stay on while the cooling system switches off.



**PartyMode**  
PartyMode activates functions like SuperCool and maximum ice production.



**HolidayMode**  
The fan, SuperCool and SuperFrost are switched off and the fridge temperature is increased to +15 °C to save electricity. The freezer compartment stays switched on.



**EnergySaver**  
Raises the standard temperature to maximum 7 °C to reduce power consumption.



**SabbathMode**  
All lighting and sounds are switched off, reactivating themselves after 80 hours.



**Language settings\***  
Variable language setting for 12 languages on the display.



**Status indicator**  
Be sure everything is OK at all times – thanks to the integrated status display in the appliance door. A blue light indicates everything is OK. If the status is anything but OK, the display flashes red and a warning tone also sounds.

## Core competence cooling.



**Temperature display**  
The display always shows the current temperature value. Flashing items in the menu indicate changes.



**SuperFrost**  
Increased cooling in the freezer compartment for vitamin-preserving freezing.



**SuperCool**  
Increase the cooling performance until the fresh food is as cool as the rest of the contents.



**VarioTemp**  
Variable temperature setting between -2 °C and +14 °C means the entire freezer compartment can also be used for cooling or as a cellar compartment.

## Simply smart with the app.



**NightMode**  
All sounds and noises are switched off – and the lighting is dimmed. For undisturbed quiet.



**BottleTimer**  
Extra fast cooling by activating SuperFrost. The app sends an automatic reminder to take the bottles out of the ice compartment.



**EasyTwist Ice**  
Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the finished ice cubes with a twist.



**IceCubeTimer\*\***  
Faster rate of ice cube production. As soon as the ice cubes are ready, the app sends a notification.

# Practical accessories for every need.

Discover the versatility of the original Liebherr range of accessories for your fridge – and make your daily life a little easier.



## Organisational systems

A fridge compartment design to suit your needs: If you want to sort your groceries clearly, you could use the VarioSafe, VarioBoxes, variable egg trays and the FlexSystem, for example. Additional bottle shelves and clip-on labelling systems provide a clear overview of wine stocks.



VarioBoxes



FlexSystem



Bottle shelf

## Useful help of all kinds

From the practical butter dish to the easy-fill ice cube tray with a lid or the handy freezer tray, the range of accessories offers plenty of smart solutions for serving food and keeping it fresh.



Butter dish



Ice cube tray with lid



FlexCube



### EasyTwist Ice

Ice in a jiffy – without a fixed water connection. Quickly build up a stock of ice cubes with a water tank and a simple twist. Easy to retrofit as an accessory.



### FreshAir activated charcoal filter

Cleans the circulating air and quickly binds unpleasant odours. The filter is easy to replace and ensures optimum air quality.



### SmartDeviceBox

You can retrofit your Liebherr with a SmartDeviceBox to connect it to the internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.

Please note that not all accessories fit all models. To find the accessory range for your appliance, please visit the Liebherr website [home.liebherr.com](http://home.liebherr.com) for details or buy them from your Liebherr dealer.

For a clear overview.  
Even before you  
open the fridge.

○ Pure    ◇ Plus    ◻ Prime    △ Peak

Which appliance is right for me?

A customer question that is not always easy to answer. That's why we have made it easier for you to navigate through our product range, by dividing it into four logically structured series.

○ Pure series

The Pure series is our basic class. Simple, clear and perfectly equipped for all essential needs. Appliances in the Pure series are stripped down to the essentials. But are to the absolute highest level of Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and has many impressive additional details. Above all, Plus means a plus in comfort. The appliances not only provide first-class refrigeration and freezing, they are also just that little bit smarter. They help make operation a little easier.

◻ Prime series

With the Prime series things get much more classy. It makes an unmistakable mark in terms of design and material. Above all, genuine quality materials are used inside the appliances, such as stainless steel. But special lighting solutions also make the appliances in this series particularly appealing.



△ Peak series

The Peak series is our premium series. Here the best is combined with the best. There is no compromise. Innovative Liebherr technology meets exceptional high-end design and convenience all in a class of their own. Appliances in this series are for those who want to have it all.

---

## Freshness centres

---



XRFbd 5220 ◊ Plus series

## Quality in every detail



### BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.



### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



### Fish & Seafood Safe

Love fish? Your Liebherr keeps fish fresh! The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger. Adjust the size of the -2 °C zone as much as you want – and store the remaining meat and dairy products at the optimum 0 °C. An LED display indicates that the -2 °C zone is currently active.



### NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



### LED freezer compartment lighting

When you open the drawers in your Liebherr freezer, not only are you welcomed by the sight of your food, but also by the attractive lighting. This is provided by powerful, long-life, environmentally-friendly LEDs. The lighting makes it even easier to see all of the contents and is also a unique design element.



### Bottle shelf above the BioFresh safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



### DuoCooling

DuoCooling uses two completely separate refrigeration circuits to ensure no air is exchanged between the fridge and freezer compartments. The food neither dries out nor is odour transferred. This means throwing less away, shopping less often, but saving more and greater enjoyment.



### PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



### Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.



### SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



### LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



### IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



### SBSes 8496

PremiumPlus



<b>SWTnes 4285</b>	
Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>187 / 0.512 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>289 l</b>
Volume:	Wine compartment: <b>156.4 l</b> / Freezer compartment: <b>133 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>185 / 60 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for wine and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 2 separately controllable temperature zones, which can be regulated between +5 °C to +20 °C
- Tinted insulated glass door with UV protection
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 4 shelves, of which 4 on telescopic rails and 2 foldable
- Partially-foldable wooden shelf on telescopic rails
- LED lighting permanently on, dimmable

**Key features**

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front and back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



### XRFbs 5295

Peak



<b>SFNbsd 529i</b>	
Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>198 / 0.542 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>277 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as 0 °C</b>
Door / side walls:	<b>BlackSteel / BlackSteel</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **★★★★**

- 7 drawers, of which 4 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

<b>SKBes 4380</b>	
Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>133 / 0.364 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>371 l</b>
Volume:	Fridge: <b>235.7 l</b> / BioFresh compartment: <b>135.8 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>185 / 60 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe, 1 Fish & Seafood-Safe

**Key features**

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**XRFst 5295**

Peak



**SFNstd 529i**

Energy efficiency class:	
Energy consumption year / 24 hrs:	198 / 0.542 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as 0 °C
Door / side walls:	SmartSteel / SmartSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

No Frost	Super Frost	Soft System	Telescopic Rails	Touch & Swipe-Display	Space Box	Vario Space	Easy Open	LED
Ice Tower	Ice Maker	Smart Device						

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 7 drawers, of which 4 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

**SRBstd 529i**

Energy efficiency class:	
Energy consumption year / 24 hrs:	134 / 0.367 kWh <sup>1</sup>
Total volume <sup>2</sup> :	386 l
Volume:	Fridge: 246.2 l / BioFresh compartment: 140.6 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / SmartSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Bio Fresh Professional	Hydro Breeze	Super Cool	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display	Glass & Steel Interior	Light Tower	Infinity Spring
Smart Device								

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, of which 1 with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection

**Key features**

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel



**XRCsd 5255**

Prime



**SBNsdd 5264**

Energy efficiency class:	
Energy consumption year / 24 hrs:	171 / 0.468 kWh <sup>1</sup>
Total volume <sup>2</sup> :	313 l
Volume:	BioFresh compartment: 180.7 l / Freezer compartment: 133 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Bio Fresh	Duo Cooling	No Frost	Super Frost	Vario Temp	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display	Vario Space
Glass & Steel Interior	Ice Maker	Smart Device ready						

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes
- 1 GlassLine storage shelf, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes

**Freezer compartment**

- 4 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 5.4 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

**SRsdd 5250**

Energy efficiency class:	
Energy consumption year / 24 hrs:	99 / 0.271 kWh <sup>1</sup>
Total volume <sup>2</sup> :	401 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Super Cool	Soft System	Touch & Swipe-Display	Glass & Steel Interior	Light Tower	Smart Device ready
------------	------------	-------------	-----------------------	------------------------	-------------	--------------------

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails
- 1 spacious fruit and vegetable drawer on telescopic rails

**Key features**

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



←121→

### XCCsd 5250

Prime



#### SCNsdd 5253

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	331 l
Volume:	Fridge: 228.7 l / Freezer compartment: 103 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Touch & Swipe-Display	Vario Space
Glass & Steel Interior	Light Tower	Smart Device ready						

#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails

#### SCNsdd 5253

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	331 l
Volume:	Fridge: 228.7 l / Freezer compartment: 103 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Touch & Swipe-Display	Vario Space
Glass & Steel Interior	Light Tower	Smart Device ready						

#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails



←123→

### XRFsf 5245

Plus



#### SFNsfe 5247

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as 0 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

No Frost	Super Frost	Touch-Display	Space Box	Vario Space	Easy Open	Ice Tower	Ice Maker	Smart Device ready
----------	-------------	---------------	-----------	-------------	-----------	-----------	-----------	--------------------

#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

#### SRBsfe 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	158 / 0.432 kWh <sup>1</sup>
Total volume <sup>2</sup> :	382 l
Volume:	Fridge: 288.7 l / BioFresh compartment: 93.7 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>

Bio Fresh	Super Cool	Touch-Display	Smart Device ready
-----------	------------	---------------	--------------------

#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



←123→

## XRFsf 5240

Plus



### SFNsfe 5247

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as 0 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

### SRsfe 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	123 / 0.337 kWh <sup>1</sup>
Total volume <sup>2</sup> :	399 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- 1 spacious fruit and vegetable drawer

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



←123→

## XRFsf 5225

Plus



### SFNsfe 5227

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

### SRBsfe 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	158 / 0.432 kWh <sup>1</sup>
Total volume <sup>2</sup> :	382 l
Volume:	Fridge: 288.7 l / BioFresh compartment: 93.7 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



XRFbd 5220 ◊ Plus series



←123→

## XRFbd 5220

Plus



### SFNbde 5227

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	BlackSteel / black
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **4\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

### SRbde 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	123 / 0.337 kWh <sup>1</sup>
Total volume <sup>2</sup> :	399 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / black
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- 1 spacious fruit and vegetable drawer

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



←123→

## XRFsf 5220

Plus



### SFNsf 5227

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

### SRsf 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	123 / 0.337 kWh <sup>1</sup>
Total volume <sup>2</sup> :	399 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- 1 spacious fruit and vegetable drawer

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



←123→

## XRF 5220

Plus



### SFNe 5227

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

#### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal

### SRe 5220

Energy efficiency class:	
Energy consumption year / 24 hrs:	123 / 0.337 kWh <sup>1</sup>
Total volume <sup>2</sup> :	399 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- 1 spacious fruit and vegetable drawer

#### Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



CBNes 6256 PremiumPlus



### BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



### IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frostfree.

## Frenchdoor fridge-freezer



← 91 →

## CBNes 6256 PremiumPlus

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>341 / 0.934 kWh</b>
Total volume <sup>1</sup> :	<b>522 l</b>
Volume: Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 160 l	
Noise output / noise class:	<b>42 dB(A) / D</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Stainless steel / stainless steel</b>
Exterior dimensions in cm (h / w / d):	<b>203.9 / 91 / 61.5</b>



### Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic

### Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, adjustable egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

### Freezer compartment

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir 2.7 kg
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

### Key features

- HardLine
- Aluminium handles
- Front ventilation
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Door hinge left fixed/right fixed

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



CBNes 5778 Premium



### NoFrost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



### SoftTelescopic

The BioFresh safes with SoftTelescopic provide a convenient, self-retracting system with soft closing, making their daily use both practical and secure. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.

## BioFresh NoFrost fridge-freezer



← 70 →



### CBNes 5778 Premium

Energy efficiency class:	<b>C</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>187 / 0.512 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>392 l</b>
Volume: Fridge: <b>168.5 l</b> / BioFresh compartment: <b>112.6 l</b> / Freezer compartment: <b>112 l</b>	
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201 / 70 / 66.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Soft System	Soft-Telescopic Rails	VarioSpace	Smart Device ready
-----------	-------------	----------	------------	-------------	-------------	-----------------------	------------	--------------------

#### Controls

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

#### Freezer compartment **\*\*\***

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

#### Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 70 →

**CBNeS 5775**  
Premium



Energy efficiency class:	<b>B</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>149 / 0.408 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>392 l</b>
Volume: Fridge: <b>168.5 l</b> / BioFresh compartment: <b>112.6 l</b> / Freezer compartment: <b>112 l</b>	
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201 / 70 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe



← 70 →

**CBNeF 5735**  
Comfort



Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>234 / 0.641 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>392 l</b>
Volume: Fridge: <b>168.5 l</b> / BioFresh compartment: <b>112.6 l</b> / Freezer compartment: <b>112 l</b>	
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>201 / 70 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe



← 70 →

**CNeF 5745**  
Comfort



Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>210 / 0.575 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>411 l</b>
Volume: Fridge: <b>299.2 l</b> / Freezer compartment: <b>112 l</b>	
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>201 / 70 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 4 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 2.2 kg
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks



← 70 →

**CNeF 5735**  
Comfort



Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub>
Energy consumption year / 24 hrs:	<b>210 / 0.575 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>410 l</b>
Volume: Fridge: <b>299.2 l</b> / Freezer compartment: <b>112 l</b>	
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>201 / 70 / 66.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

---

# Fridge-freezers

---



CBNstc 579i Δ Peak series

# Range overview by device height and series


△ Peak series

○ Prime series


◇ Plus series

○ Pure series

← 60 →



← 60 →




## Fridge-freezers – BioFresh Professional

NoFrost		
HydroBreeze IceMaker/VarioTemp	CBNstc 579i	
HydroBreeze/Fish & Seafood VarioTemp	CBNstd 578i	


## Fridge-freezers – BioFresh

NoFrost		
IceMaker/VarioTemp	CBNbsd 576i	
EasyTwist-Ice/VarioTemp	CBNbsa 5753	
EasyTwist-Ice/VarioTemp	CBNsda 5753	
VarioTemp	CBNsdb 5753	
EasyTwist-Ice	CBNbda 5723	
EasyTwist-Ice	CBNsfd 5723	
EasyTwist-Ice		CBNsfc 522i
EasyTwist-Ice		CBNsfd 5223


← 60 →



← 60 →



← 60 →



## Fridge-freezers – EasyFresh

NoFrost			
with IceMaker Watertank	CNsdd 5763		
	CNsfd 5743		
with EasyTwist-Ice	CNsdb 5753		
	CNsfd 573i		
	CNbdd 5733		
	CNsfd 5724		
	CNd 5724	CNsfd 5223	
	CNsfd 5723	CNd 5223	
without EasyTwist-Ice	CNsfd 5704	CNd 5224	CNsfd 5023
	CNd 5704	CNsfd 5204	CNd 5023
	CNsfd 5703	CNd 5204	
	CNd 5703	CNsfd 5203	
		CNd 5203	

CNsfd 5723 ◇ Plus series

# Fridge-freezers



○ Pure series



◇ Plus series



◻ Prime series



△ Peak series

	○ Pure series	◇ Plus series	◻ Prime series	△ Peak series	
<b>Freshness technology</b>	EasyFresh on integrated drawer guide	EasyFresh on integrated drawer guide	EasyFresh on telescopic rails	EasyFresh on telescopic rails	
		BioFresh on telescopic rails	BioFresh with SoftTelescopic	BioFresh Professional with SoftTelescopic	
				HydroBreeze	
	DuoCooling	DuoCooling	DuoCooling	DuoCooling	
	FreshAir filter	FreshAir filter	FreshAir filter		
		VarioTemp	VarioTemp		
	NoFrost	NoFrost	NoFrost	NoFrost on telescopic rails	
<b>Comfort and flexibility</b>		Divisible glass shelf	Divisible glass shelf	Divisible glass shelf	
			SoftSystem soft closing mechanism	SoftSystem soft closing mechanism	
		VarioSafe	VarioSafe	VarioSafe	
			VarioBoxes	VarioBoxes	
			Butter dish	Butter dish	
	Egg tray	Egg tray	Adjustable egg tray	Adjustable egg tray	
	Bottle shelf	Bottle shelf	Bottle shelf	Bottle shelf	
			Ice cube tray with lid	Ice cube tray with lid	
				FlexSystem	
<b>Design</b>	Ceiling lighting fridge compartment	Ceiling lighting fridge compartment	LightTower	LightTower	
			Lighting BioFresh safe	Lighting BioFresh safe	
			Freezer compartment lighting	Freezer compartment lighting	
				IceMaker lighting	
				Fan lighting	
			SmartSteel rear wall	SmartSteel rear wall	
				SmartSteel door interior	
	Transparent glass	Transparent glass	Satin finish glass	Satin finish glass	
	Stainless steel look shelves	Stainless steel look shelves	Glass & stainless steel rack	Glass & stainless steel rack	
	Touch display	Touch display	Touch & Swipe display	Touch & Swipe display	
	Display behind the door	Display behind the door or Display in the door	Display behind the door or Display in the door	Display behind the door or Display in the door	
	Recessed handles	Recessed handles	Slimline door handles with opening mechanism	Recessed handles	
	<b>Connectivity (SmartDeviceBox)</b>	can be retrofitted	can be retrofitted or is included with "i" models	can be retrofitted or is included with "i" models	can be retrofitted or is included with "i" models
	<b>Water and ice</b>		IceMaker or EasyTwist-Ice	IceMaker or EasyTwist-Ice	IceMaker
				InfinitySpring	

# Quality in every detail



## BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.



## EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



## Fish & Seafood Safe

Love fish? Your Liebherr keeps fish fresh! The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger. Adjust the size of the -2 °C zone as much as you want – and store the remaining meat and dairy products at the optimum 0 °C. An LED display indicates that the -2 °C zone is currently active.



## SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



## LED ceiling lighting

The LED ceiling lighting illuminates the interior from above – providing a good overview of your food. Another highlight: the LEDs are positioned in front of the glass shelves so that even a full refrigerator is well lit.



## Recessed grip

Special and functional: You can open the appliance very easily using the vertically integrated and ergonomically fitted handle. Additionally, the modern and puristic design fits perfectly into your hands-free kitchen.



## InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables drip-free water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.



## PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



## Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.




## IceMaker with water tank

Whether it's for a party or a spontaneous cocktail, the integrated IceMaker means you always have enough ice cubes in stock. With the IceMaker with water tank, you simply fill the removable water tank with water. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The ice cube separator helps to divide the drawer as you wish, for example, ice cubes on the left, ice cream on the right.



## LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.




## IceMaker with fixed water connection

Are there any ice cubes left? The IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The versatile ice compartment divider lets you choose the amount of ice cubes you want to store; easy and just as you like it.



**Our energy saving fridge-freezers in class A**

That feeling of getting fresh fruit and crisp vegetables out of the fridge just got better. With our class A fridge-freezers, you have the best energy efficiency available and sophisticated freshness technology to keep your food fresher for longer - saving resources twice over.



**VarioTemp**

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C – and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties – or over the long term as a cellar compartment for storing potatoes.



**CBNbsa 5753**  
Prime



Energy efficiency class:	<b>A</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>116 / 0.317 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>362 l</b>
Volume: Fridge: <b>159.9 l</b> / BioFresh compartment: <b>99.2 l</b> / Freezer compartment: <b>103 l</b>	
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>BlackSteel / BlackSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display
Vario Space	Glass & Steel Interior	Light Tower	Easy Twist Ice	Smart Device ready				

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Freezer compartment** **★★★★**

- 3 drawers, VarioSpace
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel



**CBNsda 5753**  
Prime



Energy efficiency class:	<b>A</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>116 / 0.317 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>362 l</b>
Volume: Fridge: <b>159.9 l</b> / BioFresh compartment: <b>99.2 l</b> / Freezer compartment: <b>103 l</b>	
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display
Vario Space	Glass & Steel Interior	Light Tower	Easy Twist Ice	Smart Device ready				

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Freezer compartment** **★★★★**

- 3 drawers, VarioSpace
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel



**CBNbda 5723**  
Plus



Energy efficiency class:	<b>A</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>116 / 0.317 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>360 l</b>
Volume: Fridge: <b>158.8 l</b> / BioFresh compartment: <b>98.9 l</b> / Freezer compartment: <b>103 l</b>	
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>BlackSteel / black</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Touch & Swipe-Display	Vario Space	Easy Twist Ice	Smart Device ready

**Controls**

- LC-Display monochrom/hinter der Tür/ Touch und Swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Freezer compartment** **★★★★**

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

**Key features**

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

**Colour / material options:**

**CBNsda 5723** with Stainless steel front

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

## BioFresh NoFrost fridge-freezers



**CBNstc 579i**  
Peak

Energy efficiency class:	<b>C</b>
Energy consumption year / 24 hrs:	<b>181 / 0.495 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>362 l</b>
Volume: Fridge: <b>160.3 l</b> / BioFresh compartment: <b>98.7 l</b> / Freezer compartment: <b>104 l</b>	
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh Professional	Hydro Breeze	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Touch & Swipe-Display
Vario Space	Glass & Steel Interior	Light Tower	Infinity Spring	Ice Maker	Smart Device			

### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 3 drawers, of which 2 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 5.4 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

### Key features

- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel

### Fridge and BioFresh compartments

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection



**CBNstd 578i**  
Peak

Energy efficiency class:	<b>D</b>
Energy consumption year / 24 hrs:	<b>225 / 0.616 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>359 l</b>
Volume: Fridge: <b>160.3 l</b> / BioFresh compartment: <b>96.1 l</b> / Freezer compartment: <b>103 l</b>	
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh Professional	Hydro Breeze	Fish & Seafood	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System
Soft-Telescopic Rails	Touch & Swipe-Display	Vario Space	Glass & Steel Interior	Light Tower	Smart Device			

### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 3 drawers, of which 2 set on telescopic rails, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

### Key features

- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel

### Fridge and BioFresh compartments

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Fish & Seafood-Safe, 1 FlexSystem



**CBNbsd 576i**  
Prime

Energy efficiency class:	<b>D</b>
Energy consumption year / 24 hrs:	<b>226 / 0.619 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>362 l</b>
Volume: Fridge: <b>159.9 l</b> / BioFresh compartment: <b>99.2 l</b> / Freezer compartment: <b>104 l</b>	
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>BlackSteel / BlackSteel</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display
Vario Space	Glass & Steel Interior	Light Tower	Ice Maker	Smart Device				

### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 3 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 5.4 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

### Key features

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

## BioFresh NoFrost fridge-freezer



**CBNsdb 5753**  
Prime

Energy efficiency class:	<b>B</b>
Energy consumption year / 24 hrs:	<b>144 / 0.394 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>362 l</b>
Volume: Fridge: <b>159.9 l</b> / BioFresh compartment: <b>99.2 l</b> / Freezer compartment: <b>103 l</b>	
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>201.5 / 59.7 / 67.5<sup>1</sup></b>

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Soft-Telescopic Rails	Touch & Swipe-Display
Vario Space	Glass & Steel Interior	Light Tower	Smart Device ready					

### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

### Key features

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

## BioFresh NoFrost fridge-freezers



← 60 →

### CBNsfd 5723

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	226 / 0.619 kWh <sup>1</sup>
Total volume <sup>2</sup> :	360 l
Volume: Fridge: 158.8 l / BioFresh compartment: 98.9 l / Freezer compartment: 103 l	
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings



← 60 →

### CBNsfc 522i

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	170 / 0.465 kWh <sup>1</sup>
Total volume <sup>2</sup> :	320 l
Volume: Fridge: 164.7 l / BioFresh compartment: 52.9 l / Freezer compartment: 103 l	
Noise output / noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 1 BioFresh-Safe on telescopic rails, 1 Fruit & Vegetable-Safe

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

## BioFresh NoFrost fridge-freezer



← 60 →

### CBNsfd 5223

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	213 / 0.583 kWh <sup>1</sup>
Total volume <sup>2</sup> :	320 l
Volume: Fridge: 164.7 l / BioFresh compartment: 52.9 l / Freezer compartment: 103 l	
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 1 BioFresh-Safe on telescopic rails, 1 Fruit & Vegetable-Safe

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

## NoFrost fridge-freezer



← 60 →

### CNsdd 5763

Prime

Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	373 l
Volume: Fridge: 269.5 l / Freezer compartment: 104 l	
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment

- 3 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 5.4 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails

#### Key features

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel



← 60 →

### CNsdb 5753

Prime



Energy efficiency class:	
Energy consumption year / 24 hrs:	129 / 0.353 kWh <sup>1</sup>
Total volume <sup>2</sup> :	372 l
Volume:	Fridge: 269.5 l / Freezer compartment: 103 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Soft System	Touch & Swipe-Display	Vario Space	
Glass & Steel Interior	Light Tower	Easy Twist Ice	Smart Device ready						

#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\*\***

- 3 drawers, VarioSpace
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 Cold storage accumulators
- Safety glass fittings

#### Key features

- Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails



← 60 →

### CNsfd 5743

Plus



Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 104 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Touch & Swipe-Display	Vario Space	Ice Maker Water tank	Smart Device ready
------------	-------------	----------	------------	-------------	-----------------------	-------------	----------------------	--------------------

#### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\*\***

- 3 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 5.4 kg
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails



← 60 →

### CNsfd 573i

Plus



Energy efficiency class:	
Energy consumption year / 24 hrs:	210 / 0.575 kWh <sup>1</sup>
Total volume <sup>2</sup> :	359 l
Volume:	Fridge: 227.1 l / Freezer compartment: 132 l
Noise output / noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Touch & Swipe-Display	Vario Space	Easy Twist Ice	Smart Device
------------	-------------	----------	------------	-------------	-----------------------	-------------	----------------	--------------

#### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment **\*\*\*\***

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings



← 60 →

### CNbdd 5733

Plus



Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / black
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Touch & Swipe-Display	Vario Space	Easy Twist Ice	Smart Device ready
------------	-------------	----------	------------	-------------	-----------------------	-------------	----------------	--------------------

#### Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment **\*\*\*\***

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

## NoFrost fridge-freezers



← 60 →

### CNSfd 5724

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	210 / 0.575 kWh <sup>1</sup>
Total volume <sup>2</sup> :	359 l
Volume:	Fridge: 227.1 l / Freezer compartment: 132 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNd 5724

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	210 / 0.575 kWh <sup>1</sup>
Total volume <sup>2</sup> :	359 l
Volume:	Fridge: 227.1 l / Freezer compartment: 132 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

## NoFrost fridge-freezers



← 60 →

### CNSfd 5723

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNSfd 5704

Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	210 / 0.575 kWh <sup>1</sup>
Total volume <sup>2</sup> :	359 l
Volume:	Fridge: 227.1 l / Freezer compartment: 132 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CND 5704

Pure



Energy efficiency class:	
Energy consumption year / 24 hrs:	210 / 0.575 kWh <sup>1</sup>
Total volume <sup>2</sup> :	359 l
Volume:	Fridge: 227.1 l / Freezer compartment: 132 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNsfd 5703

Pure



Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 103 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CND 5703

Pure



Energy efficiency class:	
Energy consumption year / 24 hrs:	203 / 0.556 kWh <sup>1</sup>
Total volume <sup>2</sup> :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 103 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CND 5224

Plus



Energy efficiency class:	
Energy consumption year / 24 hrs:	202 / 0.553 kWh <sup>1</sup>
Total volume <sup>2</sup> :	319 l
Volume:	Fridge: 187.1 l / Freezer compartment: 132 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →



### CNSfd 5223

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →



### CNd 5223

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →



### CNSfd 5204

Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	202 / 0.553 kWh <sup>1</sup>
Total volume <sup>2</sup> :	319 l
Volume:	Fridge: 187.1 l / Freezer compartment: 132 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →



### CNd 5204

Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	202 / 0.553 kWh <sup>1</sup>
Total volume <sup>2</sup> :	319 l
Volume:	Fridge: 187.1 l / Freezer compartment: 132 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 60 →

### CNSfd 5203

Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNd 5203

Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	201 / 0.550 kWh <sup>1</sup>
Total volume <sup>2</sup> :	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNSfd 5023

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	191 / 0.523 kWh <sup>1</sup>
Total volume <sup>2</sup> :	280 l
Volume:	Fridge: 177 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

### CNd 5023

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	191 / 0.523 kWh <sup>1</sup>
Total volume <sup>2</sup> :	280 l
Volume:	Fridge: 177 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

#### Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

#### Key features

- Vertical recessed handles
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 55 →

**CUef 3331**



← 55 →

**CUel 3331**



← 55 →

**CUel 2831**



← 55 →

**CU 2831**



← 55 →

**CUel 2331**



← 55 →

**CU 2331**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>280 / 0.767 kWh</b>
Total volume <sup>1</sup> :	<b>296 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>84 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>SmartSteel / silver</b>
Exterior dimensions in cm (h / w / d):	<b>181.2 / 55 / 63</b>

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>280 / 0.767 kWh</b>
Total volume <sup>1</sup> :	<b>296 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>84 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>181.2 / 55 / 63</b>

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>240 / 0.657 kWh</b>
Total volume <sup>1</sup> :	<b>265 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>161.2 / 55 / 63</b>

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>240 / 0.657 kWh</b>
Total volume <sup>1</sup> :	<b>265 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>161.2 / 55 / 63</b>

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>241 / 0.660 kWh</b>
Total volume <sup>1</sup> :	<b>210 l</b>
Volume:	Fridge: <b>156.5 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>137.2 / 55 / 63</b>

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>241 / 0.660 kWh</b>
Total volume <sup>1</sup> :	<b>210 l</b>
Volume:	Fridge: <b>156.5 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>137.2 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3.8 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

**Colour / material options:**

**CU 3331** in white



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3.8 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



CUNo 2831

CUkw 2831

CUfb 2831



CUNo 2831

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>240 / 0.657 kWh</b>
Total volume <sup>1</sup> :	<b>265 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>NeonOrange / NeonOrange</b>
Exterior dimensions in cm (h / w / d):	<b>161.2 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



CUkw 2831

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>240 / 0.657 kWh</b>
Total volume <sup>1</sup> :	<b>265 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>KiwiGreen / KiwiGreen</b>
Exterior dimensions in cm (h / w / d):	<b>161.2 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



CUfb 2831

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>240 / 0.657 kWh</b>
Total volume <sup>1</sup> :	<b>265 l</b>
Volume:	Fridge: <b>212.4 l</b> / Freezer compartment: <b>54 l</b>
Noise output / noise class:	<b>39 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>FrozenBlue / FrozenBlue</b>
Exterior dimensions in cm (h / w / d):	<b>161.2 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment** **\*\*\***

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 55 →

**CTel 2931**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>231 / 0.632 kWh</b>
Total volume <sup>1</sup> :	<b>270 l</b>
Volume:	Fridge: <b>218.6 l</b> / Freezer compartment: <b>52 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>157.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 19.54 h
- Freezing capacity in 24 hrs: 3.3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**CT 2931**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>231 / 0.632 kWh</b>
Total volume <sup>1</sup> :	<b>270 l</b>
Volume:	Fridge: <b>218.6 l</b> / Freezer compartment: <b>52 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>157.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 19.54 h
- Freezing capacity in 24 hrs: 3.3 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**CTel 2531**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>212 / 0.580 kWh</b>
Total volume <sup>1</sup> :	<b>233 l</b>
Volume:	Fridge: <b>189.5 l</b> / Freezer compartment: <b>44 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>140.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 17.12 h
- Freezing capacity in 24 hrs: 3.6 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**CT 2531**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>212 / 0.580 kWh</b>
Total volume <sup>1</sup> :	<b>233 l</b>
Volume:	Fridge: <b>189.5 l</b> / Freezer compartment: <b>44 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>140.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 17.12 h
- Freezing capacity in 24 hrs: 3.6 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**CTel 2131**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>198 / 0.542 kWh</b>
Total volume <sup>1</sup> :	<b>196 l</b>
Volume:	Fridge: <b>152.2 l</b> / Freezer compartment: <b>44 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Stainless steel look / silver</b>
Exterior dimensions in cm (h / w / d):	<b>124.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 17.3 h
- Freezing capacity in 24 hrs: 3.7 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**CT 2131**

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>198 / 0.542 kWh</b>
Total volume <sup>1</sup> :	<b>196 l</b>
Volume:	Fridge: <b>152.2 l</b> / Freezer compartment: <b>44 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>124.1 / 55 / 63</b>



**Controls**

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

**Freezer compartment** **4\*\*\*\***

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 17.3 h
- Freezing capacity in 24 hrs: 3.7 kg
- Safety glass fittings

**Key features**

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

---

# Fridges


---



RBsdd 5250 ○ Prime series

# Range overview by device height and series

- △ Peak series
- ◊ Prime series
- ◇ Plus series
- Pure series



## Fridges

BioFresh Professional				
HydroBreeze/Fish & Seafood	RBstd 528i			
	RBbsc 5280			
HydroBreeze	SRBstd 529i			
BioFresh				
	RBbsc 5250			
	RBsdd 5250			
	RBd 5250			
	RBsfe 5221			
	RBe 5221			
	RBsfe 5220			
	RBe 5220			
Full-space BioFresh				RBa 4250
EasyFresh				
	Rd 5250			
Pull-out drawer/bottle basket	RDsfe 5220			
Pull-out drawer/bottle basket	Rsfe 5220			
	Re 5220			
		Rsfe 5020		
		Re 5020		
			Rsfe 4620	
			Re 4620	
				Rf 4200



RDsfe 5220 ◊ Plus series

# Fridges



○ Pure series



◇ Plus series



◻ Prime series



△ Peak series

	○ Pure series	◇ Plus series	◻ Prime series	△ Peak series
<b>Freshness technology</b>	EasyFresh on integrated drawer guide	EasyFresh on integrated drawer guide	EasyFresh on telescopic rails	EasyFresh on telescopic rails
		BioFresh on telescopic rails	BioFresh with SoftTelescopic	BioFresh Professional with SoftTelescopic
				HydroBreeze
	FreshAir filter	FreshAir filter	FreshAir filter	FreshAir filter
<b>Comfort and flexibility</b>		Divisible glass shelf	Divisible glass shelf	Divisible glass shelf
			SoftSystem soft closing mechanism	SoftSystem soft closing mechanism
		VarioSafe	VarioSafe	VarioSafe
			VarioBoxes	VarioBoxes
			Butter dish	Butter dish
	Egg tray	Egg tray	Adjustable egg tray	Adjustable egg tray
	Bottle shelf	Bottle shelf	Bottle shelf	Bottle shelf
				FlexSystem
<b>Design</b>	Ceiling lighting	Ceiling or side lighting	LightTower	LightTower
			Lighting BioFresh safe	Lighting BioFresh safe
				Fan lighting
			SmartSteel rear wall	SmartSteel rear wall
				SmartSteel door interior
	Transparent glass	Transparent glass	Satin finish glass	Satin finish glass
	Stainless steel look shelves	Stainless steel look shelves	Glass & stainless steel rack	Glass & stainless steel rack
	Touch display	Touch display	Touch & Swipe display	Touch & Swipe display
	Display behind the door	Display behind the door	Display behind the door	Display behind the door
	Recessed grip	Recessed grip	Slimline door handle with opening mechanism	Recessed grip
<b>Connectivity (SmartDeviceBox)</b>	can be retrofitted	can be retrofitted	can be retrofitted	can be retrofitted or is included with "i" models
<b>Water</b>				InfinitySpring for SBS-capable models

## Quality in every detail



### Fruit & Vegetable safe

Crunchy salad and strawberries: the most delicate foods deserve a special place so they stay fresh longer – in BioFresh safes. In the Fruit & Vegetable safe the temperature is close to 0°C. Combined here with the constant humidity, thanks to the air-tight closure, unpackaged fruit and vegetables feel particularly at home. You do not have to adjust anything.




### EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



### LED side lighting, single sided

For a quick overview of everything in the refrigerator: the LED side lighting helps you to keep your food in view. The LEDs are positioned so that the light beams go up and down. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.



### Slimline door handle with integrated opening mechanism

Opening made easy: The practical and elegant slimline door handle with an integrated opening mechanism allows you to open the appliance door effortlessly, even when it's opened multiple times in quick succession. The classy, minimalistic handles are also an eye-catcher on your appliance.



### Door shelf

Do you want a safe storage area for your drinks or food? And do you still want to reach them easily? Our height-adjustable door shelves offer you both – thanks to the safety glass shelves and stainless steel rails. The sliding and removable bottle holder also ensures that your bottles are held securely.



### Bottle shelf above the BioFresh safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



### 3 bottle shelf

Now your bottles stay where they should. The 3 bottle shelf securely holds three bottles in your fridge ready to be used. The bottle shelf fits on every glass shelf and is therefore very flexible. And if you need the space for other reasons, simply take the bottle shelf out of the fridge.



### LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



### Door hinge exchange, integrated freezer compartment

Switch the opening direction on your 4\* freezer compartment door quickly and easily: The clever slide control means this can be done in seconds and without any manual skills. Simply slide the control on the 4\* freezer compartment right or left – that's it, done.



### SoftTelescopic

Look forward to opening your BioFresh safes. And this is not just because of the fresh food – but also because opening is so easy, and closing is cushioned. The telescopic rails slide the safe gently towards you. And because these extend fully, you have the best overview of the contents.



### FlexSystem

Small and delicate fruit in the refrigerator can easily roll out of sight or become crushed. That's why your Liebherr comes with the FlexSystem. Two flexibly positionable boxes in the BioFresh safe ensure everything is clearly arranged and organised. And they also safely protect even the smallest raspberry from bruising or from being mixed up with other foods.



### Space for baking tray

Do you want to keep that home-baked fruit pie fresh? Or maybe a prepared pizza to be baked later on? If so, simply slide your baking tray into your Liebherr – it has plenty of space for storing a baking tray. Really convenient – you can slide the baking tray in and out when the door is opened at 90°.



**SRBstd 529i**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	134 / 0.367 kWh <sup>1</sup>
Total volume <sup>2</sup> :	386 l
Volume:	Fridge: 246.2 l / BioFresh compartment: 140.6 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / SmartSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, of which 1 with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection

**Key features**

- Side wall heating left, suitable for combination with other refrigerators, freezers and/ or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**RBstd 528i**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	134 / 0.367 kWh <sup>1</sup>
Total volume <sup>2</sup> :	384 l
Volume:	Fridge: 246.2 l / BioFresh compartment: 137.9 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / SmartSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Fish & Seafood-Safe, 1 Meat & Dairy-Safe, 1 FlexSystem

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**RBbsc 5280**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	107 / 0.293 kWh <sup>1</sup>
Total volume <sup>2</sup> :	384 l
Volume:	Fridge: 246.2 l / BioFresh compartment: 137.9 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Fish & Seafood-Safe, 1 Meat & Dairy-Safe

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



**RBbsc 5250**  
Prime

Energy efficiency class:	
Energy consumption year / 24 hrs:	107 / 0.293 kWh <sup>1</sup>
Total volume <sup>2</sup> :	386 l
Volume:	Fridge: 245.8 l / BioFresh compartment: 140.9 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel



<b>BLU</b>	<b>RBd 5250</b> Prime
Energy efficiency class:	<b>D</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>134 / 0.367 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>386 l</b>
Volume:	Fridge: <b>245.8 l</b> / BioFresh compartment: <b>140.9 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED light panel both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

**Colour / material options:**

**RBsdd 5250** with SmartSteel front

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



<b>BLU</b>	<b>RBsfe 5221</b> Plus
Energy efficiency class:	<b>E</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>205 / 0.561 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>351 l</b>
Volume:	Fridge: <b>223 l</b> / BioFresh compartment: <b>93.9 l</b> / Freezer compartment: <b>34 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SteelFinish / silver</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED light one-sided
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Freezer compartment** **\*\*\*\***

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 5 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



<b>BLU</b>	<b>RBe 5221</b> Plus
Energy efficiency class:	<b>E</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>205 / 0.561 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>351 l</b>
Volume:	Fridge: <b>223 l</b> / BioFresh compartment: <b>93.9 l</b> / Freezer compartment: <b>34 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Integrated bottle shelf
- LED light one-sided
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Freezer compartment** **\*\*\*\***

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 5 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



<b>BLU</b>	<b>RBsfe 5220</b> Plus
Energy efficiency class:	<b>E</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>158 / 0.432 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>382 l</b>
Volume:	Fridge: <b>288.7 l</b> / BioFresh compartment: <b>93.7 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SteelFinish / silver</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

**Key features**

- Vertical recessed handle
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

**Colour / material options:**

**RBe 5220** in white

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



RBa 4250 ◯ Prime series



### BioFresh

BioFresh guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.



### LED lighting

The LED lighting ensures your BioFresh safes are pleasantly lit. This makes it even easier for you to find the food you want. The energy-efficient LED unit is elegantly positioned above the safes to save space.



## RBa 4250 Prime



Energy efficiency class:	<b>A</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>65 / 0.178 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>160 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>125.5 / 59.7 / 67.5<sup>1</sup></b>



### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for BioFresh compartments
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

### Fridge and BioFresh compartments

- LED BioFresh lighting
- 4 BioFresh-Safes on integrated drawer guide

### Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



Bottle basket RDSfe 5220

Do your family and party guests love cold drinks? Often the inside door of the refrigerator isn't enough for bottle cooling. However, your Liebherr will be happy to help. There's plenty of room in the bottle baskets for bottles and Tetrapaks – or even a whole crate of beer. The shelves of the baskets rest on telescopic rails and slide out gently for easy removal.



**Rd 5250**  
Prime



Energy efficiency class:	<b>D</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>99 / 0.271 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>401 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, Removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel both sides
- 1 EasyFresh-Safe on telescopic rails
- 1 spacious fruit and vegetable drawer on telescopic rails

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**RDSfe 5220**  
Plus



Energy efficiency class:	<b>E</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>123 / 0.337 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>399 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SteelFinish / silver</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- Pull-out drawer with partial extension on telescopic rails
- 2 removable bottle baskets
- 1 spacious fruit and vegetable drawer

**Key features**

- Vertical recessed handle
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



**Rsfe 5220**  
Plus



Energy efficiency class:	<b>E</b> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>123 / 0.337 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>399 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>SteelFinish / silver</b>
Exterior dimensions in cm (h / w / d):	<b>185.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

**Fridge compartment**

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails
- 1 spacious fruit and vegetable drawer

**Key features**

- Vertical recessed handle
- Transport handles, front and at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

**Colour / material options:**  
Re 5220 in white



← 60 →

**Rsf 5020**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	117 / 0.320 kWh <sup>1</sup>
Total volume <sup>2</sup> :	348 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



- Controls**
- LC monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge compartment
  - SmartDeviceBox: optional accessory
  - Door alarm: visual and acoustic

- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
  - Plastic door shelves with bottle holder
  - 6 GlassLine storage shelves, of which 1 is divided into two parts
  - VarioSafe
  - Bottle shelf
  - LED ceiling lighting
  - 1 EasyFresh-Safe on running rails

- Key features**
- Vertical recessed handle
  - Transport handles, front and at back
  - Height-adjustable feet at front
  - Reversible door hinging
  - Replaceable door seal



← 60 →

**Re 5020**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	117 / 0.320 kWh <sup>1</sup>
Total volume <sup>2</sup> :	348 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



- Controls**
- LC monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge compartment
  - SmartDeviceBox: optional accessory
  - Door alarm: visual and acoustic

- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
  - Plastic door shelves with bottle holder
  - 6 GlassLine storage shelves, of which 1 is divided into two parts
  - VarioSafe
  - Bottle shelf
  - LED ceiling lighting
  - 1 EasyFresh-Safe on running rails

- Key features**
- Vertical recessed handle
  - Transport handles, front and at back
  - Height-adjustable feet at front
  - Reversible door hinging
  - Replaceable door seal



← 60 →

**Rsf 4620**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	111 / 0.304 kWh <sup>1</sup>
Total volume <sup>2</sup> :	298 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	145.5 / 59.7 / 67.5 <sup>1</sup>



- Controls**
- LC monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge compartment
  - SmartDeviceBox: optional accessory
  - Door alarm: visual and acoustic

- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
  - Plastic door shelves with bottle holder
  - 5 GlassLine storage shelves, of which 1 is divided into two parts
  - Bottle shelf
  - LED ceiling lighting
  - 1 EasyFresh-Safe on running rails

- Key features**
- Vertical recessed handle
  - Transport handles, front and at back
  - Height-adjustable feet at front
  - Reversible door hinging
  - Replaceable door seal

**Colour / material options:**  
Re 4620 in white



← 60 →

**Rf 4200**  
Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	131 / 0.358 kWh <sup>1</sup>
Total volume <sup>2</sup> :	247 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	125.5 / 59.7 / 67.5 <sup>1</sup>



- Controls**
- LC monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge compartment
  - SmartDeviceBox: optional accessory
  - Door alarm: visual and acoustic

- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
  - Plastic door shelves with bottle holder
  - 5 GlassLine storage shelves
  - 3 bottle shelf
  - LED ceiling lighting
  - 1 EasyFresh-Safe on running rails

- Key features**
- Vertical recessed handle
  - Transport handles, front and at back
  - Height-adjustable feet at front
  - Reversible door hinging
  - Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 55 →

**Ksl 2834**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	197 / 0.539 kWh <sup>1</sup>
Total volume <sup>2</sup> :	250 l
Volume:	Fridge: 229.8 l / Freezer compartment: 21 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	silver / silver
Exterior dimensions in cm (h / w / d):	140.2 / 55 / 63 <sup>1</sup>

**Controls**

- Mechanical control in interior, control dial
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment**

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 3 kg

**Key features**

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**K 2834**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	197 / 0.539 kWh <sup>1</sup>
Total volume <sup>2</sup> :	250 l
Volume:	Fridge: 229.8 l / Freezer compartment: 21 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	140.2 / 55 / 63 <sup>1</sup>

**Controls**

- Mechanical control in interior, control dial
- CoolPlus function

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Freezer compartment**

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 3 kg

**Key features**

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging



**Bottle shelf**

The bottle shelf is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



**GlassLine**

The distinctive GlassLine interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



← 55 →

**K 2340**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	126 / 0.345 kWh <sup>1</sup>
Total volume <sup>2</sup> :	214 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	114 / 55 / 63 <sup>1</sup>

**Controls**

- Mechanical control in interior, control dial

**Fridge compartment**

- Plastic door shelves with bottle holder, Egg tray
- 5 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

**Key features**

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Under counter fridges



TP 1760

## Quality in every detail



**Premium GlassLine**

Premium GlassLine door shelves with stainless steel trim. Elegant stainless steel bars help protect taller bottles and jars.



**4-star freezer compartment**

You can freeze fresh food and store frozen food for long periods in appliances with the 4-star freezer compartment. Temperatures of  $-18^{\circ}\text{C}$  and lower ensure food is stored with all the vital vitamins and minerals preserved.



**Slimline door handle**

The slimline door handle is discrete and ergonomically designed for ease of opening. Under counter fridges with manual controls can be further reduced in height by removing the tabletop of the fridge.



**SuperCool function**

The elegant and precise MagicEye control with its digital temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic SuperCool function lowers the refrigerator temperature to  $+2^{\circ}\text{C}$ . It is perfect for quickly cooling freshly stored food.



**GlassLine**

The distinctive GlassLine interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



**Vegetable compartments**

Ergonomically designed, the extra deep transparent vegetable compartments are easy-to-clean and provide ample storage for fruit and vegetables.



← 60 →

**TP 1764**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>146 / 0.400 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>135 l</b>
Volume:	Fridge: <b>118 l</b> / Freezer compartment: <b>18 l</b>
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 60.1 / 62.8<sup>1</sup></b>

#### Controls

- MagicEye on front, key electronic
- Digital temperature display for fridge compartment

#### Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 4.7 kg

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**TP 1760**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>93 / 0.254 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>155 l</b>
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 60.1 / 62.8<sup>1</sup></b>

Super  
Cool

#### Controls

- MagicEye on front, key electronic
- Digital temperature display for fridge compartment

#### Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**TP 1724**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>146 / 0.400 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>143 l</b>
Volume:	Fridge: <b>126 l</b> / Freezer compartment: <b>18 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 60.1 / 62.8<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.29 kg

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**TP 1720**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>92 / 0.252 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>145 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 60.1 / 62.8<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 60 →

**TPesf 1714**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	183 / 0.501 kWh <sup>1</sup>
Total volume <sup>2</sup> :	143 l
Volume:	Fridge: 126 l / Freezer compartment: 18 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Stainless steel / silver
Exterior dimensions in cm (h / w / d):	85 / 60.1 / 60.8 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.36 kg

#### Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**TPesf 1710**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	115 / 0.315 kWh <sup>1</sup>
Total volume <sup>2</sup> :	145 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Stainless steel / silver
Exterior dimensions in cm (h / w / d):	85 / 60.1 / 60.8 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**T 1714**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	183 / 0.501 kWh <sup>1</sup>
Total volume <sup>2</sup> :	143 l
Volume:	Fridge: 126 l / Freezer compartment: 18 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 60.1 / 62.8 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.36 kg

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**T 1810**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	118 / 0.323 kWh <sup>1</sup>
Total volume <sup>2</sup> :	161 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 60.1 / 62.8 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



### 4-star freezer compartment

You can freeze fresh food and store frozen food for long periods in appliances with the 4-star freezer compartment. Temperatures of  $-18^{\circ}\text{C}$  and lower ensure food is stored with all the vital vitamins and minerals preserved.



### Slimline door handle

The slimline door handle is discrete and ergonomically designed for ease of opening. Under counter fridges with manual controls can be further reduced in height by removing the tabletop of the fridge.



**TP 1414**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	176 / 0.482 kWh <sup>1</sup>
Total volume <sup>2</sup> :	120 l
Volume:	Fridge: 106.3 l / Freezer compartment: 15 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-ST (from $+10^{\circ}\text{C}$ to $+38^{\circ}\text{C}$ )
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 55.4 / 62.3 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Freezer compartment

- 4-star freezer compartment
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**T 1504**

Energy efficiency class:	
Energy consumption year / 24 hrs:	180 / 0.493 kWh <sup>1</sup>
Total volume <sup>2</sup> :	133 l
Volume:	Fridge: 116.9 l / Freezer compartment: 17 l
Noise output / noise class:	40 dB(A) / C
Climate rating:	SN-ST (from $+10^{\circ}\text{C}$ to $+38^{\circ}\text{C}$ )
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 55.4 / 62.3 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Plastic door shelves with bottle holder, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Freezer compartment

- 4-star freezer compartment
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 5.13 kg

#### Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



**T 1700**

Energy efficiency class:	
Energy consumption year / 24 hrs:	116 / 0.317 kWh <sup>1</sup>
Total volume <sup>2</sup> :	149 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (from $+10^{\circ}\text{C}$ to $+38^{\circ}\text{C}$ )
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 55.4 / 62.3 <sup>1</sup>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 50 →

**T 1414**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>176 / 0.482 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>120 l</b>
Volume:	Fridge: <b>106.3 l</b> / Freezer compartment: <b>15 l</b>
Noise output / noise class:	<b>40 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 50.1 / 62<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Freezer compartment

- 4-star freezer compartment
- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 5.35 kg

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 50 →

**T 1410**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>114 / 0.312 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>136 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 50.1 / 62<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 50 →

**T 1404**

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>176 / 0.482 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>120 l</b>
Volume:	Fridge: <b>106.3 l</b> / Freezer compartment: <b>15 l</b>
Noise output / noise class:	<b>40 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 50.1 / 62<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial
- CoolPlus function

#### Fridge compartment

- Plastic door shelves with bottle holder, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Freezer compartment

- 4-star freezer compartment
- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 5.35 kg

#### Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 50 →

**Tb 1400**

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>114 / 0.312 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>136 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>black / black</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 50.1 / 62<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging



← 50 →

**T 1400**

Energy efficiency class:	
Energy consumption year / 24 hrs:	<b>114 / 0.312 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>136 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>85 / 50.1 / 62<sup>1</sup></b>

#### Controls

- Mechanical control in interior, control dial

#### Fridge compartment

- Plastic door shelves with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

#### Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Freezers



FNsdd 5297 Δ Peak series

# Range overview by device height and series

- △ Peak series
- Prime series
- ◇ Plus series
- Pure series

**Freezers**

	← 70 → 185	← 70 → 165	← 70 → 145
NoFrost			
EasyTwist-Ice	FNc 7277	FNc 7076	FNc 6675
without EasyTwist-Ice	FNc 7227	FNc 7026	FNc 6625

**Freezers**

	← 60 → 185	← 60 → 165	← 60 → 145	← 60 → 125
NoFrost				
IceTower	FNsdd 5297			
	SFNsfe 5247			
EasyTwist-Ice	FNc 5277	FNb 5056 BluRoX	FNd 4655	FNd 4254
	FNsdd 5257	FNd 5056		
	FNd 525i			
without EasyTwist-Ice	FNe 5227	FNe 5026	FNd 4625	FNe 4224
				FNf 4204



**BluRoX**

FNb 5056 ○ Prime series

# Freezers



○ Pure series

◇ Plus series

◻ Prime series

△ Peak series

	○ Pure series	◇ Plus series	◻ Prime series	△ Peak series
<b>Freshness technology</b>	NoFrost	NoFrost	NoFrost	NoFrost
<b>Comfort and flexibility</b>	EasyOpen	EasyOpen	EasyOpen	EasyOpen
	FrostProtect	FrostProtect	FrostProtect	FrostProtect
	Tipping drawer	Tipping drawer	Tipping drawer	Tipping drawer
				SoftSystem soft closing mechanism for SBS-capable models
	SpaceBox	SpaceBox	SpaceBox	SpaceBox
	Integrated drawer guide	Integrated drawer guide	Integrated drawer guide	Drawers guided on telescopic rails
		Ice cube tray	Ice cube tray with lid for SBS-capable models	
		Freezer tray	Freezer tray	Freezer tray
			2 cold storage accumulators	2 cold storage accumulators
	VarioSpace	VarioSpace	VarioSpace	VarioSpace
<b>Design</b>			Status light	Status light
			Freezer compartment lighting	Freezer compartment lighting
				IceMaker lighting
	Touch display	Touch display	Touch & Swipe display	Touch & Swipe display
	Display behind the door	Display behind the door	Display behind the door	Display behind the door
	Recessed grip	Recessed grip	Slimline door handle with opening mechanism	Slimline door handle with opening mechanism
<b>Connectivity (SmartDeviceBox)</b>	can be retrofitted	can be retrofitted	can be retrofitted or is included with "i" models	can be retrofitted or is included with "i" models
<b>Ice</b>		EasyTwist-Ice or IceTower for SBS-capable models	EasyTwist-Ice or IceTower for SBS-capable models	EasyTwist-Ice or IceTower
		Ice cube tray for SBS-capable models	Ice cube tray for SBS-capable models	Ice cube tray for SBS-capable models

## Quality in every detail



### NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



### SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean offering additional capacity. Freezer drawers and glass shelves made of safety glass can be removed easily.



### Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your freezer intuitively and with ease. Simply select functions such as SuperFrost on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.



### FrostProtect

Not all freezers are fitted in heated rooms. Some are located in cold garages or sheds. It's good then that your Liebherr is ideally set up for such a cool environment because all components are designed to operate in ambient temperatures as low as -15 °C.



### Cold storage accumulator

The cold storage accumulators are doubly useful - both indoors and outdoors. Inside the freezer, they keep the frozen food cold for a period should there be a power failure. And they are on hand to chill your food and drinks when you're on outings.



### SpaceBox

Accommodate the "big stuff" in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.



### IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



### Status display

You want to check that everything is OK with your appliance? The status display on the appliance door lets you know very quickly, visually and audibly. A blue light indicates: everything is OK. If the status is anything but OK, the display lights up red and flashes. A warning tone also sounds.



### LED freezer compartment lighting

When you open the drawers in your Liebherr freezer, not only are you welcomed by the sight of your food, but also by the attractive lighting. This is provided by powerful, long-life, environmentally-friendly LEDs. The lighting makes it even easier to see all of the contents and is also a unique design element.



### EasyTwist-Ice

Whether it's a summer day or a party: Thanks to EasyTwist-Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist-Ice is easy to clean and ensures hygienic ice cube production at all times.



### Ice cube scoop

The Liebherr ice scoop makes portioning and transporting of ice easy. Thanks to the slanted tip and the ergonomic handle, ice cubes can make it from your IceTower into your drinks quickly and easily. The robust ice scoop made of sturdy plastic is also pleasing to the eye thanks to its satin surface in transparent glacier green.



### VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



**FNC 7277**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	178 / 0.487 kWh <sup>1</sup>
Total volume <sup>2</sup> :	363 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 69.7 / 76 <sup>1</sup>



Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 7 drawers, of which 5 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 19 h
- Freezing capacity in 24 hrs: 19 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**FNC 7227**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	178 / 0.487 kWh <sup>1</sup>
Total volume <sup>2</sup> :	363 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 69.7 / 76 <sup>1</sup>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 19 h
- Freezing capacity in 24 hrs: 19 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**FNC 7076**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	166 / 0.454 kWh <sup>1</sup>
Total volume <sup>2</sup> :	311 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 69.7 / 76 <sup>1</sup>



Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 6 drawers, of which 4 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



**FNC 7026**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	166 / 0.454 kWh <sup>1</sup>
Total volume <sup>2</sup> :	311 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 69.7 / 76 <sup>1</sup>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 6 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNC 6675**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	155 / 0.424 kWh <sup>1</sup>
Total volume <sup>2</sup> :	260 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	145.5 / 69.7 / 76 <sup>1</sup>



Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 5 drawers, of which 4 set on telescopic rails, VarioSpace
- LED lighting
- Status indicator
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNC 6625**  
Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	155 / 0.424 kWh <sup>1</sup>
Total volume <sup>2</sup> :	260 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	145.5 / 69.7 / 76 <sup>1</sup>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 5 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 16 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNsdd 5297**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	198 / 0.542 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as 0 °C
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



Ice Maker  
Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 7 drawers, of which 3 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNC 5277**  
Peak

Energy efficiency class:	
Energy consumption year / 24 hrs:	159 / 0.435 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



Frost Protect  
Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment**

- 7 drawers, of which 5 set on telescopic rails, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 60 →

### FNd 525i

Prime



Energy efficiency class:	
Energy consumption year / 24 hrs:	198 / 0.542 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators

#### Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



← 60 →

### FNsdd 5257

Prime



Energy efficiency class:	
Energy consumption year / 24 hrs:	198 / 0.542 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators

#### Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



BluRoX



← 60 →

### FNb 5056

Prime



Energy efficiency class:	
Energy consumption year / 24 hrs:	120 / 0.328 kWh <sup>1</sup>
Total volume <sup>2</sup> :	238 l
Noise output / noise class:	31 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 65.5 <sup>1</sup>



#### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\*\***

- 6 drawers, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 17 kg
- 2 Cold storage accumulators

#### Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Available from the 2nd quarter of 2023

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



### Unveiled in the Liebherr FNb 5056.

BluRoX can first be seen in the Liebherr FNb 5056. In the door of this freezer, the innovative vacuum insulation celebrates a very special world first: in accordance with the new EU energy label, the Liebherr FNb 5056 is the first freezer of its type to be awarded efficiency class "B". And to ensure this remains the case for many years, the high-quality insulation also boasts the durability that Liebherr is renowned for.



To learn more about this exciting technology and the many advantages of BluRoX, visit: [home.liebherr.com/blurox](http://home.liebherr.com/blurox)



## SFNsfe 5247

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as 0 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8.0 kg
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

### Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal



## FNe 5227

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	248 / 0.679 kWh <sup>1</sup>
Total volume <sup>2</sup> :	277 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 <sup>1</sup>



### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 7 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

### Key features

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



## FNd 5056

Prime

Energy efficiency class:	
Energy consumption year / 24 hrs:	187 / 0.512 kWh <sup>1</sup>
Total volume <sup>2</sup> :	238 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



Smart Device ready

### Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 6 drawers, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg
- 2 Cold storage accumulators

### Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



## FNe 5026

Plus

Energy efficiency class:	
Energy consumption year / 24 hrs:	234 / 0.641 kWh <sup>1</sup>
Total volume <sup>2</sup> :	238 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 <sup>1</sup>



### Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

### Freezer compartment **\*\*\*\***

- 6 drawers, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg

### Key features

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNd 4655**  
Prime

Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>176 / 0.482 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>199 l</b>
Noise output / noise class:	<b>34 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>145.5 / 59.7 / 67.5<sup>1</sup></b>



Smart Device ready

**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 5 drawers, VarioSpace
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNd 4625**  
Plus

Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>176 / 0.482 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>199 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>145.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 5 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 16 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNd 4254**  
Prime

Energy efficiency class:	<b>D</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>166 / 0.454 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>160 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>125.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 4 drawers, VarioSpace
- LED lighting
- Status indicator
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 15 kg
- 2 Cold storage accumulators

**Key features**

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNe 4224**  
Plus

Energy efficiency class:	<b>E</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>208 / 0.569 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>160 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>125.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 15 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



**FNf 4204**  
Pure

Energy efficiency class:	<b>F</b> <sup>A</sup> / <sub>G</sub> <sup>1</sup>
Energy consumption year / 24 hrs:	<b>260 / 0.712 kWh<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>160 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>125.5 / 59.7 / 67.5<sup>1</sup></b>



**Controls**

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

**Freezer compartment** **\*\*\*\***

- 4 drawers, VarioSpace
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 15 kg

**Key features**

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

**GNP 1066**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	186 / 0.509 kWh <sup>1</sup>
Total volume <sup>2</sup> :	99 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 60.2 / 62.8 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic

**Freezer compartment**

- 3 drawers, VarioSpace
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 60 →

**GN 1066**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	232 / 0.635 kWh <sup>1</sup>
Total volume <sup>2</sup> :	99 l
Noise output / noise class:	41 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 60.2 / 62.8 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic

**Freezer compartment**

- 3 drawers, VarioSpace
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



**SuperFrost**

The elegant and precise MagicEye control with its temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic SuperFrost function quickly reduces the temperature to freeze your food while preserving the vitamins.



**Tabletop**

The tabletop of the under counter freezers is extremely robust, with a scratch and heat resistant surface.



← 60 →

**GP 1486**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	137 / 0.375 kWh <sup>1</sup>
Total volume <sup>2</sup> :	102 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 60.2 / 62.8 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic

**Freezer compartment**

- 4 drawers, VarioSpace
- Temperature rise time: 14.6 h
- Freezing capacity in 24 hrs: 8.2 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



← 60 →

**GPesf 1476**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	171 / 0.468 kWh <sup>1</sup>
Total volume <sup>2</sup> :	102 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	85.1 / 60.2 / 61 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic

**Freezer compartment**

- 4 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- HardLine
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

**Colour / material options:**

GP 1476 in white



← 55 →

**GP 1376**  
Premium

Energy efficiency class:	
Energy consumption year / 24 hrs:	171 / 0.468 kWh <sup>1</sup>
Total volume <sup>2</sup> :	102 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 55.3 / 62.4 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic

**Freezer compartment**

- 4 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**GP 1213**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	170 / 0.465 kWh <sup>1</sup>
Total volume <sup>2</sup> :	97 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 55.3 / 62.4 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Alarm in case of malfunction: visual

**Freezer compartment**

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**G 1213**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	213 / 0.583 kWh <sup>1</sup>
Total volume <sup>2</sup> :	97 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85.1 / 55.3 / 62.4 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Alarm in case of malfunction: visual

**Freezer compartment**

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

**Key features**

- SwingDesign
- Recessed handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging



← 55 →

**GX 823**  
Comfort

Energy efficiency class:	
Energy consumption year / 24 hrs:	199 / 0.545 kWh <sup>1</sup>
Total volume <sup>2</sup> :	68 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures:	as low as -15 °C
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	63.1 / 55.3 / 62.4 <sup>1</sup>



**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Alarm in case of malfunction: visual

**Freezer compartment**

- 2 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

**Key features**

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Chest freezers



CFf 2080 ○ Pure series

## Quality in every detail



### StopFrost

StopFrost prevents a vacuum from building up, ensuring the lid opens easily. Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer.



### SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the chest freezers are smooth and easy-to-clean offering additional capacity.



### Condenser

The heat-exchange condenser is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the easy-to-clean outside walls.




### FrostProtect

Due to their shape and size, many chest freezers are kept outside of the normal household environment so Liebherr has developed FrostProtect to enable these models to work in low ambient temperatures. All chest freezer models will work in ambient temperatures as low as -15°C.



### LED interior light

The bright LED interior light allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



### SuperFrost function

The automatic SuperFrost function quickly reduces the temperature to freeze your food while preserving the vitamins. As soon as the food is completely frozen, the automated SuperFrost function switches back to normal mode.



←168→

### CFd 2505

Plus

Energy efficiency class:	<b>D</b>
Energy consumption year / 24 hrs:	<b>188 / 0.515 kWh</b>
Total volume <sup>1</sup> :	<b>359 l</b>
Noise output / noise class:	<b>32 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>82.5 / 167.5 / 70.9</b>



#### Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 15 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 5 Suspension baskets as standard, 1 retrofittable

#### Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock



←126→

### CFd 2085

Plus

Energy efficiency class:	<b>D</b>
Energy consumption year / 24 hrs:	<b>162 / 0.443 kWh</b>
Total volume <sup>1</sup> :	<b>248 l</b>
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>82.5 / 125.5 / 70.9</b>



#### Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 10 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 3 Suspension baskets as standard, 1 retrofittable

#### Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock



←168→

### CFe 2500

Pure

Energy efficiency class:	<b>E</b>
Energy consumption year / 24 hrs:	<b>294 / 0.805 kWh</b>
Total volume <sup>1</sup> :	<b>497 l</b>
Noise output / noise class:	<b>33 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>82.5 / 167.5 / 70.2</b>



#### Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 20 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 5 retrofittable

#### Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening



←126→

### CFF 2080

Pure

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>274 / 0.750 kWh</b>
Total volume <sup>1</sup> :	<b>353 l</b>
Noise output / noise class:	<b>32 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>82.5 / 125.5 / 70.2</b>



#### Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 15 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 3 retrofittable

#### Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening



←105→

### CFF 1870

Pure

Energy efficiency class:	<b>F</b>
Energy consumption year / 24 hrs:	<b>249 / 0.682 kWh</b>
Total volume <sup>1</sup> :	<b>281 l</b>
Noise output / noise class:	<b>32 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Designed to operate in ambient temperatures:	<b>as low as -15 °C</b>
Door / side walls:	<b>white / white</b>
Exterior dimensions in cm (h / w / d):	<b>82.5 / 104.5 / 70.2</b>



#### Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

#### Freezer compartment **\*\*\***

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 10 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 2 retrofittable

#### Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

## Wine fridges



WPbli 5231 GrandCru Selection

# Quality in every detail



## TempProtect Plus

Double protection. With TempProtect Plus, our wine storage fridges constantly measure the temperature with two sensors. This gives you double the assurance that your wines are protected from temperature fluctuations. This is because you are alerted as soon as one of the sensors detects a critical change in temperature, allowing you to take action quickly.



## Keeping corks in good condition

With HumiditySelect, the humidity in our wine storage fridges can be adjusted in two stages: Standard or High. Models in the GrandCru Selection series are equipped with HumidityControl. This function allows the humidity to be set within a range of 50 % to 80 % RH\* and constantly displays the actual value. If the value falls below 50 % RH\*, the appliance indicates this.



## UVProtect Plus

Triple protection. For long-term storage, the wine storage fridges with glass door offer unprecedented protection from UV radiation: three protective layers consisting of tinted glass and a double layer of vacuum-deposited metal. Known as Low-E coating, it provides highly efficient protection for your wine against harmful solar radiation.



## SelfClosing Door with EasyFill loading aid

Let it lighten the load for you. The EasyFill loading aid ensures that the door of your wine storage fridge remains open from an angle of 90° – for particularly easy filling. And thanks to the SelfClosing mechanism, the door closes all by itself when opened less than 90° – always as gently as your valuable wines require.



## VibrateSafe

Your wine needs peace and quiet. That's why our wine storage fridges guarantee gentle storage with particularly quiet compressors specially developed by Liebherr and stable wooden shelves made of solid beech wood. This allows your wine to mature quietly and undisturbed.



## Presentation light

Show off your wine to the best effect with your storage fridge's presentation light. On units with glass doors, the light can stay on even when the door is closed. This way, your wine collection is always something to catch the eye. The brightness of the lighting can be adjusted individually via the SmartDevice app and the display.



## Mechanical door lock

Keep your treasures to yourself. Wine collections are usually also valuable investments and ought to be protected as such. A mechanical door lock ensures that you always have control of who accesses the wines in your GrandCru Selection wine storage fridge. The lock is flush-mounted and blends unobtrusively into the overall design.



## Neck-to-neck storage for maximum bottle capacity

Maximum capacity. A Liebherr wine storage fridge also makes it easier to organise a growing wine collection. To take full advantage of its capacity, the interior has been designed so that your wine bottles can be stored neck-to-neck on the wooden shelves. This means there's plenty of room even for ever-increasing wine stocks. So feel free to keep collecting.



## Rear wall panel, stainless steel

Beautiful all around and even inside. The exterior of our wine storage fridges attracts attention, but it's also worth a look inside. The combination of wooden shelves and a SmartSteel stainless steel rear wall panel in the GrandCru Selection series is a delight even when empty. The technical benefits are as well thought-out as the design. For example, the surface of the rear wall panel ensures balanced air circulation.



## FreshAir activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine storage fridges have an activated charcoal filter that reliably binds odours of all kinds. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every 6 months to change the filter, which you can easily do yourself.



## Security

Protecting a valuable wine collection is a great responsibility. This is why our wine storage fridges are equipped with a comprehensive security package. Sophisticated alarm functions provide audible and optical alerts before the wine can come to harm.



## SmartDevice

Keep an eye on your wine wherever you are. All new wine storage fridges come network-ready or can be integrated into the smart home via the SmartDevice box accessory. This way, you benefit from the advantages of the SmartDevice app and have access to your appliance from anywhere. You can change settings on the go, view the temperature and get security information on your smartphone.

\* For temperatures in living environment. In the case of very dry/cold environments, e.g. cellars, we recommend the tailor-made water box from our range of accessories to support the system.

The features shown are model dependent; look for these features in your model choice.



**WTeS 5872**  
Vinidor

Energy efficiency class:	<b>G</b>
Energy consumption year / 24 hrs:	<b>206 / 0.564 kWh</b>
Max. Bordeaux bottles 0.75 l:	<b>178<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>503 l</b>
Noise output / noise class:	<b>35 dB(A) / B, SuperSilent</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Glass door with stainless steel frame / stainless steel</b>
Exterior dimensions in cm (h / w / d):	<b>192 / 70 / 74.2</b>



**Controls**

- LCD display in the interior, touch electronic
- Digital temperature display for 3 wine zones
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

**Wine compartment**

- 3 Temperature zones, which can set from +5 °C to +20 °C
- 3 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 13 Shelves, of which 10 set on telescopic rails, of which 1 is a presentation shelf

**Key features**

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock



**WTeS 5972**  
Vinidor

Energy efficiency class:	<b>G</b>
Energy consumption year / 24 hrs:	<b>191 / 0.523 kWh</b>
Max. Bordeaux bottles 0.75 l:	<b>211<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>521 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Glass door with stainless steel frame / stainless steel</b>
Exterior dimensions in cm (h / w / d):	<b>192 / 70 / 74.2</b>



**Controls**

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

**Wine compartment**

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

**Key features**

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock



**LED lighting**

The LED lighting in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



**Touch-electronic control system**

The electronic LCD display is an innovative design feature. Clear menu navigation and a Touch-electronic control system provides yet more information for tailored storage conditions. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



**WTeS 1672**  
Vinidor

Energy efficiency class:	<b>G</b>
Energy consumption year / 24 hrs:	<b>139 / 0.380 kWh</b>
Max. Bordeaux bottles 0.75 l:	<b>34<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>95 l</b>
Noise output / noise class:	<b>36 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Glass door with stainless steel frame / stainless steel</b>
Exterior dimensions in cm (h / w / d):	<b>82.2 / 59.8 / 57.5</b>



**Controls**

- MagicEye control in interior, touch electronic
- Digital temperature display for both wine zones
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

**Wine compartment**

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

**Key features**

- HardLine
- Aluminium handle
- Reversible door hinging
- Replaceable door seal
- Lock

Temperature ranges

+5 °C to +20 °C

+5 °C to +20 °C

+5 °C to +20 °C



2 Zones

3 Zones

With two to three temperature zones that can be set independently from each other to between +5 °C to +20 °C – accurate to the degree – our **multi-temperature wine fridges** offer the most flexibility for any use. That means that red wines, white wines and champagnes can all be stored at the same time and at an ideal temperature in one single appliance with three temperature zones. And these appliances also provide ideal climatic conditions for the long-term storage of wines. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each individual wine collection.

Temperature range

+5 °C to +20 °C



1 Zone

**Wine storage fridges** recreate the conditions of a wine cellar. A constant temperature is maintained within the entire interior of these appliances. They can be adjusted to between +5 °C and + 20 °C, depending on your requirements. Wine storage fridges are specially designed to hold a large number of bottles for storage and ageing, but they can also keep a larger stock of wine at drinking temperature.



**Compact fridges** – as specialists in all things cooling, storage and temperature control, Liebherr offers space-saving wonders for any occasion. Enter stage right: our efficient compact appliances for fresh ideas. Compact wine storage fridges provide just the right dimensions for the niche wine collection. Valuable cigars are kept under optimal storage conditions in the humidor.




**Bordeaux bottle size (0.75 l)**

All specifications regarding bottle capacity refer to these dimensions.


**Freestanding wine appliances**

**Compact appliances**

	← 75 →	← 70 →	← 60 →	← 43 →
Width in cm				
<b>Multi-temperature wine fridges</b>		WTes 5872 P. 160 WTes 5972 P. 160	WTes 1672 P. 161	
<b>Wine storage fridges</b>	WSbli 7731 P. 166		WPbli 5231 P. 166 WSbli 5231 P. 167 WPbli 5031 P. 168 WSbli 5031 P. 168 WPbli 5001 P. 169 WSbli 5001 P. 169 WPbli 4601 P. 170 WSbli 4601 P. 170 WPbli 4201 P. 171 WSbli 4201 P. 171 WKb 1812 P. 167	WKes 653 P. 173
<b>Humidor</b>				ZKes 453 P. 173



WSbl 5001 GrandCru



GrandCru



GrandCru Selection

	<b>GrandCru</b>	<b>GrandCru Selection</b>
<b>Quality</b>	Constant temperature maintenance Adjustable temperature range in one zone: +5°C to +20°C Permanent display of current temperature Triple UV and safety glazing / UVProtect Plus Low-vibration storage / VibrateSafe Neck-to-neck storage for maximum bottle capacity Replaceable door seal 2 height-adjustable feet	Constant temperature maintenance Adjustable temperature range in one zone: +5°C to +20°C Permanent display of current temperature Triple UV and safety glazing / UVProtect Plus Low-vibration storage / VibrateSafe Neck-to-neck storage for maximum bottle capacity Replaceable door seal 2 height-adjustable feet
<b>Feel good climate</b>	Adjustable humidity with HumiditySelect 1 FreshAir filter with replacement reminder Temperature setting in 1°C steps	<b>Controllable humidity with HumidityControl</b> <b>Current humidity display</b> 1 FreshAir filter with replacement reminder Temperature setting in 1°C steps
<b>Convenience and flexibility</b>	EasyFill loading aid SelfClosing Door Wooden pull-out shelf, height-adjustable Display: select from 9 languages (DE/EN/FR/ES/IT/NL/CS/PL/PT)	EasyFill loading aid SelfClosing Door Wooden pull-out shelf, height-adjustable Display: select from 9 languages (DE/EN/FR/ES/IT/NL/CS/PL/PT)
<b>Design and lifestyle</b>	LED ceiling lighting Rear wall panel: metal, graphite grey Touch display Presentation light (glass door) Handle: black Low noise	LED ceiling lighting (solid door), <b>LightColumn (glass door)</b> <b>Rear wall panel: stainless steel</b> Touch display Presentation light (glass door) <b>Handle: brushed aluminium</b> Low noise
<b>Safety</b>	TempProtect Plus Door, temperature and power failure alarm Alarm issued both audibly and visually on display, via illumination and push message thanks to SmartDevice* DisplayLock Mechanical lock, retrofittable	TempProtect Plus Door, temperature and power failure alarm Alarm issued both audibly and visually on display, via illumination and push message thanks to SmartDevice* DisplayLock <b>Mechanical lock, integrated</b>
<b>Connectivity*</b>	SmartDevice ready Presentation light* Temperature setting in 1°C steps* Display and control of relevant appliance functions*	<b>SmartDevice (SmartDeviceBox incl.)</b> Presentation light* Temperature setting in 1°C steps* Display and control of relevant appliance functions*

\* via SmartDevice app

## Wine storage fridges GrandCru Selection



**WSbli 7731**  
GrandCru Selection

Energy efficiency class:	<b>E</b> <sup>A</sup> / <sub>G</sub> <sup>2</sup>
Energy consumption year / 24 hrs:	<b>102 / 0.279 kWh <sup>2</sup></b>
Max. Bordeaux bottles 0.75 l:	<b>324 <sup>1</sup></b>
Total volume <sup>3</sup> :	<b>628 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Full door, black / black</b>
Exterior dimensions in cm (h / w / d):	<b>204.4 / 74.7 / 76.3 <sup>2</sup></b>

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							

### Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

### Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH \*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood shelves
- 7 Shelves

### Key features

- Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Lock



**WPbli 5231**  
GrandCru Selection

Energy efficiency class:	<b>F</b> <sup>A</sup> / <sub>G</sub> <sup>2</sup>
Energy consumption year / 24 hrs:	<b>115 / 0.315 kWh <sup>2</sup></b>
Max. Bordeaux bottles 0.75 l:	<b>229 <sup>1</sup></b>
Total volume <sup>3</sup> :	<b>442.6 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Glass door, frame black / black</b>
Exterior dimensions in cm (h / w / d):	<b>188.4 / 59.7 / 76.3 <sup>2</sup></b>

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
Light Column	Presentation Light	Steel Interior	Smart Device					

### Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

### Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH \*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED light one-sided permanently on, dimmable
- Adjustable beech wood shelves
- 6 Shelves

### Key features

- Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Lock



**WSbli 5231**  
GrandCru Selection

Energy efficiency class:	<b>E</b> <sup>A</sup> / <sub>G</sub> <sup>2</sup>
Energy consumption year / 24 hrs:	<b>96 / 0.263 kWh <sup>2</sup></b>
Max. Bordeaux bottles 0.75 l:	<b>229 <sup>1</sup></b>
Total volume <sup>3</sup> :	<b>433.9 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-T (from +10 °C to +43 °C)</b>
Door / side walls:	<b>Full door, black / black</b>
Exterior dimensions in cm (h / w / d):	<b>188.4 / 59.7 / 76.3 <sup>2</sup></b>

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							

### Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

### Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH \*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood shelves
- 6 Shelves

### Key features

- Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Lock

## Wine storage fridge Vinothek



**WKb 1812**  
Vinothek

Energy efficiency class:	<b>G</b> <sup>A</sup> / <sub>G</sub> <sup>2</sup>
Energy consumption year / 24 hrs:	<b>123 / 0.337 kWh <sup>2</sup></b>
Max. Bordeaux bottles 0.75 l:	<b>66 <sup>1</sup></b>
Total volume <sup>3</sup> :	<b>135 l</b>
Noise output / noise class:	<b>38 dB(A) / C</b>
Climate rating:	<b>SN-ST (from +10 °C to +38 °C)</b>
Door / side walls:	<b>Glass door, frame black / black</b>
Exterior dimensions in cm (h / w / d):	<b>89 / 60 / 61.3 <sup>2</sup></b>

1 Zone	Humidity Select	Fresh Air	UV Protect	Vibrate Safe

### Controls

- MagicEye on front, key electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

### Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Adjustable grid shelves
- 3 Shelves

### Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

\* For temperatures in living environment. In the case of very dry/cold environments, e.g. cellars, we recommend the tailor-made water box from our range of accessories to support the system.

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)  
<sup>2</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>3</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to [EU] 2017/1369 6a.



**WPbli 5031**  
GrandCru Selection

Energy efficiency class:	
Energy consumption year / 24 hrs:	111 / 0.304 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	196 <sup>1</sup>
Total volume <sup>3</sup> :	385.9 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
Light Column	Presentation Light	Steel Interior	Smart Device					

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH\*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED light one-sided permanently on, dimmable
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Lock

\* For temperatures in living environment. In the case of very dry/cold environments, e.g. cellars, we recommend the tailor-made water box from our range of accessories to support the system.



**WSbli 5031**  
GrandCru Selection

Energy efficiency class:	
Energy consumption year / 24 hrs:	97 / 0.265 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	196 <sup>1</sup>
Total volume <sup>3</sup> :	378.2 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Control	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Steel Interior	Smart Device							

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH\*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Lock

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)  
<sup>2</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



**WPbl 5001**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	113 / 0.309 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	196 <sup>1</sup>
Total volume <sup>3</sup> :	385 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED lighting permanently on, dimmable
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>3</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to [EU] 2017/1369 6a.



**WSbl 5001**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	97 / 0.265 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	196 <sup>1</sup>
Total volume <sup>3</sup> :	378.1 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	168.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED interior lighting
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

**WPbl 4601**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	111 / 0.304 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	166 <sup>1</sup>
Total volume <sup>3</sup> :	328.7 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	148.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED lighting permanently on, dimmable
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

**WSbl 4601**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	84 / 0.230 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	166 <sup>1</sup>
Total volume <sup>3</sup> :	322.8 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	148.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED interior lighting
- Adjustable beech wood shelves
- 5 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

**WPbl 4201**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	95 / 0.260 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	141 <sup>1</sup>
Total volume <sup>3</sup> :	272.2 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Glass door, frame black / black
Exterior dimensions in cm (h / w / d):	128.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	UV Protect Plus	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill
LED	Smart Device ready							

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED lighting permanently on, dimmable
- Adjustable beech wood shelves
- 4 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal



← 60 →

**WSbl 4201**  
GrandCru

Energy efficiency class:	
Energy consumption year / 24 hrs:	76 / 0.208 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l:	141 <sup>1</sup>
Total volume <sup>3</sup> :	267.2 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Full door, black / black
Exterior dimensions in cm (h / w / d):	128.4 / 59.7 / 76.3 <sup>2</sup>

1 Zone	Temp Protect Plus	Humidity Select	Fresh Air	Vibrate Safe	Touch-Display	Self Closing Door	Easy Fill	LED
Smart Device ready								

**Controls**

- LC monochrome display in the door, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED interior lighting
- Adjustable beech wood shelves
- 4 Shelves

**Key features**

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)  
<sup>2</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>3</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to [EU] 2017/1369 6a.



WKes 653 GrandCru



**WKes 653**  
GrandCru

Energy efficiency class:	<b>E</b>
Energy consumption year / 24 hrs:	<b>78 / 0.213 kWh</b>
Max. Bordeaux bottles 0.75 l:	<b>12<sup>1</sup></b>
Total volume <sup>2</sup> :	<b>48 l</b>
Noise output / noise class:	<b>37 dB(A) / C</b>
Climate rating:	<b>SN (from +10 °C to +32 °C)</b>
Door:	<b>Glass door with stainless steel frame and SmartSteel</b>
Side walls:	<b>stainless steel with SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>61.2 / 42.5 / 47.8</b>



**Controls**

- LCD display in the interior, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

**Wine compartment**

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves

**Key features**

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- Drawer for accessories
- Suitable for wall mounting
- Lock



**ZKes 453**  
Humidor

Energy efficiency class:	<b>E</b>
Energy consumption year / 24 hrs:	<b>162 / 0.443 kWh</b>
Total net capacity:	<b>39 l</b>
Noise output:	<b>40 dB(A)</b>
Climate rating:	<b>N (from +16 °C to +32 °C)</b>
Door:	<b>Glass door with stainless steel frame and SmartSteel</b>
Side walls:	<b>stainless steel with SmartSteel</b>
Exterior dimensions in cm (h / w / d):	<b>61.2 / 42.5 / 47.8</b>



**Controls**

- LCD display in the interior, touch electronic
- Digital display of temperature and humidity
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

**Humidor**

- 1 Temperature zone, which can set from +16 °C to +20 °C
- Humidity range, adjustable between 68% to 75%
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 Shelves

**Key features**

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- 2 presentation boxes
- Suitable for wall mounting
- Lock

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)  
<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.  
 You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



OKes 1750



### Outdoor

Outdoor kitchens with refrigerators – whether freestanding or built-in – also provide convenience and perfect storage outdoors. The Outdoor Cooler is ideally suited to outdoor use thanks to its rust- and weatherproof materials, robust construction and high-quality components as well as its automatic shut-down function and integrated lock.



### Flexible and ergonomic interior layout

With bottles stored at the bottom, the two storage racks are ideal for smaller packages. The glass shelf on telescopic rails provides an overview of foodstuffs stored at the back. Depending on the size, containers can also be stored on two height-adjustable glass shelves. And a separable glass shelf means that larger and open bottles can easily be stored upright.



### OKes 1750

Energy efficiency class:	<b>B</b>
Energy consumption year / 24 hrs:	177 / 0.484 kWh
Total volume <sup>1</sup> :	109 l
Door / side walls:	Stainless steel / stainless steel
Exterior dimensions in cm (h / w / d):	81.8 / 59.8 / 57.7



#### Controls

- LCD display in the interior
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

#### Outdoor Cooler

- LED lighting
- 1 Temperature zone, which can set from +2°C to +14°C
- Safety shut-down
- Ambient temperature range: +2°C to +35°C

#### Key features

- Can be installed underneath counters (ventilation via the base)
- Stainless steel slimline door handle
- Height-adjustable feet at front and back
- Reversible door hinging
- Concealed hinge with restricted opening
- Lock
- Splash-proof class: IPX-4

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

## Brief explanation of features

### Freshness technologies

<b>Bio Fresh Professional</b>	BioFresh-Professional offers even more flexibility for individual food storage.
<b>Hydro Breeze</b>	Cooling like a pro: Cold mist and a temperature in the safe of around 0 °C ensure a longer storage time and create a fabulous visual effect.
<b>Fish &amp; Seafood</b>	The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger.
<b>Bio Fresh</b>	The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance.
<b>Bio Fresh Plus</b>	Adjustable temperature range of 0 °C and -2 °C, BioFresh-Plus safe includes a versatile Fish & Seafood-Safe.
<b>Bio Cool</b>	Optimum humidity for fruit and vegetables via slider control and longer term food storage.
<b>Easy Fresh</b>	The air-tight safe allows humidity to rise keeping food fresher for longer.
<b>Duo Cooling</b>	Two separately controlled refrigeration circuits. The temperatures within the refrigerator and freezer compartments can be controlled independently.
<b>No Frost</b>	Defrosting is never needed as the freezer automatically defrosts itself.
<b>Smart Frost</b>	Defrosting is required much less often.
<b>Super Cool</b>	SuperCool boosts the cooling power until the food recently placed inside reaches the temperature of the rest of the contents.
<b>Super Frost</b>	SuperFrost increases the cooling power for a short time – this means the temperature remains constant when you place in unfrozen food.
<b>Vario Temp</b>	Freezer section becomes alternative additional cooling zone by setting an accurate temperature of between -2 °C and +14 °C.

### Wine

<b>1 Zone</b>	With constant temperature throughout the interior, adjustable from +5 °C to +20 °C.
<b>2 Zones</b>	With two temperature zones, independently and precisely adjustable from +5 °C to +20 °C.
<b>3 Zones</b>	With three temperature zones, independently and precisely adjustable from +5 °C to +20 °C.

### Wine

<b>Humidity Control</b>	The humidity can be actively regulated in 5% increments between 50% and 80% RH.
<b>Humidity Select</b>	The humidity can be adjusted between two levels: Standard or High.
<b>Temp Protect Plus</b>	Two sensors constantly measure the temperature in the wine fridge. A notification is sent in the event of a critical change.*
<b>Vibrate Safe</b>	The fully vibration-insulated cooling system allows the wine to mature undisturbed.
<b>Fresh Air</b>	For a pure bouquet, an activated charcoal filter reliably binds odours of any kind.
<b>UV Protect Plus</b>	Triple protection: a tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from solar radiation.
<b>UV Protect</b>	Double protection: a tinted glass door with one layer of vacuum-deposited metal provides efficient protection from solar radiation.

### Convenience and flexibility

<b>Soft System</b>	The door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.
<b>Soft-Telescopic Rails</b>	Fully extendible drawers run on telescopic rails and feature a convenient self-retraction mechanism with soft-closing.
<b>Telescopic Rails</b>	Drawers set on high-quality, smooth-running telescopic rails for reliable and secure opening and closing.
<b>Touch &amp; Swipe-Display</b>	Intuitive control – simply by touching and swiping on the colour display.
<b>Touch-Display</b>	A Liebherr is really simple to use with a gentle tap of a finger on the clear touch display.
<b>Space Box</b>	For flexible food storage: At a height of 250 mm, the space box offers lots of extra room even for really large frozen items.
<b>Vario Space</b>	For extra high storage space: Simply take out the individual freezer drawers and the glass horizontal dividers below and make space for extra tall frozen items.
<b>Easy Open</b>	EasyOpen means the freezer door can be opened multiple times one after another, conveniently and easily.
<b>Self Closing Door</b>	The door of the wine fridge closes smoothly by itself when opened less than 90°.

\*SmartDevice/Smart app required

## Brief explanation of features

### Convenience and flexibility

**Easy Fill** Loading aid for easy stocking of the wine fridge. From an angle of 90°, the door remains open.

**Easy Serve Basket** The bottle basket for clearly arranged storage and easy accessibility at the bar.

**Presentation Board** Shows off exquisite wines and presents bottles that have been opened.

### Design

**Glass & Steel Interior** The interior features elegant glass and stainless steel elements.

**Light Tower** The new LightTower lighting concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.

**Light Column** LED light column from top to bottom evenly illuminates the interior. One-sided or double-sided depending on the series.

**Presentation Light** Effectively showcases the wine collection even when the glass door is closed. The brightness can be dimmed using the display.\*

**LED** Minimal heat generation, energy-saving and maintenance-free for optimum lighting.

**Steel Interior** Not just an attractive design element, the SmartSteel stainless steel rear wall panel ensures balanced air circulation.

### Water and ice

**Infinity Spring** Ice-cold water on tap with no heavy lifting of bottles and is better for our environment.

**Ice Tower** Perfect for Parties: You will never run out of cold drinks. The 8 kg supply of ice cubes makes sure of that.

**Ice Maker** Automatic IceMaker with fixed water connection.

**Easy Twist Ice** Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the finished ice cubes with a twist.

**Ice Maker Water tank** If no fixed water connection is available, there is an IceMaker with a water tank in the fridge compartment.

### Connectivity

**Smart Device ready** The SmartDeviceBox allows the appliance to be controlled and used via mobile devices. The SmartDeviceBox can be ordered as an accessory.

**Smart Device** The SmartDeviceBox allows the appliance to be controlled and used via mobile devices. The SmartDeviceBox is already included.

### Product groups

**Wine** The perfect range for wine aficionados.

**Cigar** Quality storage for fine cigars.

**Outdoor** Outdoor kitchens with refrigerators also provide convenience and perfect storage outdoors.

\*SmartDevice/Smart app required

# Stay in touch

---

## Our catalogue programme

Ask your Liebherr dealer for our main catalogues for freestanding and fully integrated appliances and for our specials. All catalogues are also available for download at [home.liebherr.com](http://home.liebherr.com).



**SmartDevice app:** The smart companion for your Liebherr. Operate your appliances conveniently via app, receive important status messages and benefit from many other services relating to your fridge.



**HNGRY:** The smart every-day assistant for shopping, storage and supplies. The app helps you organise your shopping perfectly, keep an eye on your supplies at all times, and store them correctly.



You can download our apps here.



Subject to technical changes.  
Colour deviations depending on media type.  
For latest available data, see [home.liebherr.com](http://home.liebherr.com).  
Printed in Croatia by STEGA TISAK d.o.o. 7943 094-20/02.23