
Core Range 2024

LIEBHERR

Refrigeration and freezing



Tasty for longer.

You don't compromise when you're shopping. You look for natural ingredients, the best quality and maximum freshness. Of course, anyone who values good food wants to keep it fresh for as long as possible. That is precisely why we have developed innovative freshness technologies and improve them year after year, so your food still tastes fresh after some time in the refrigerator.



EasyFresh. Ideal for fruit and vegetables.
Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after 7 days.



BioFresh. Our all-rounder.
The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy safe.



BioFresh Professional with HydroBreeze. Refrigerate like the professionals.
A cold mist that covers fruit and vegetables like a protective balm. It ensures crisp freshness and improves structure - the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



BioFresh Professional with Fish & Seafood Safe. Like freshly caught fish from the market.
Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood Safe is therefore ideal to keep items tasting fresh for longer.



DuoCooling. No drying out.
Our basic technology in selected models. The two completely separate refrigeration circuits ensure that there is no air exchange between the fridge and freezer compartments. Groceries do not dry out nor spread odour.



NoFrost. No more defrosting.
The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during manual defrosting. The constant optimal freezing remains the same without interruptions.



Specifications made in days are comparisons to the normal fridge compartment.




Even the smallest detail deserves the utmost attention.

We prioritise uncompromising quality – down to the tiniest screw. And we have done so from the very start. We have been manufacturing high-quality refrigerators and freezers and selling them worldwide since 1954. However, at heart we are still a family business with deep roots in Germany. It is here that we continue to develop all our products just as before. German engineering – out of loyalty to our founder and with the knowledge built up by generations of engineers.

Convenience for everybody.

Our new freestanding units are available in different series: Pure, Plus, Prime and Peak. But whatever series you opt for, every single Liebherr comes with uncompromising Liebherr quality. This is because even in the Pure series, every appliance comes with a wide range of features. One example is NoFrost – the automatic defrosting function. Another is our EasyFresh technology for storing fruit and vegetables. Then there is our DuoCooling feature. With two separate refrigerant circuits, it ensures that no air is exchanged between the fridge and freezer compartments. The stored groceries do not dry out and no odours are transferred.



CNSda 5723 ◊ Plus series

Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. We also test all other functional parts to ensure that they can last just as long.

And if, contrary to expectations, a small detail no longer meets your requirements, you or our premium service partners can usually correct it quickly. Because all our appliances are extremely repair-friendly. We keep all essential spare parts in stock for well over 10 years. This practice is not just sustainable, it also saves you money on minor repairs or the purchase of a new appliance.

We don't just say it. We also guarantee it.

During manufacturing we inspect all components of our refrigerators with great care and test them far more rigorously than required by law – and we do this for the last time just before they are packaged. It is only then that our appliances can relax a little. All of our manufacturing sites are certified in accordance with the international standards for quality ISO 9001, energy management ISO 50001 and environmental management ISO 14001. Therefore, nothing could be easier for us than to guarantee for at least two years that our products are free of material and manufacturing faults and are particularly easy to install.

Selected fridge-freezers come with a 10-year guarantee (terms and conditions apply).

In short: one thing is certain – you will be able to enjoy your Liebherr for a long time.



EasyFresh for fruit and vegetables from the Pure series upwards.



Magnetic door gasket ensures safe closing.

Our path to the future

One thing unites all our product innovations: they all present a path towards greater sustainability. Taking responsibility is one of our core values. That's why we have a decades-long tradition of research and development into eco-friendly products, with the entire product lifecycle in mind.

Materials

We want to reduce the environmental impact of our business activities and are preparing recyclable products by increasing the use of renewable materials and recycled materials in our appliances and reducing the variety of materials we use. In doing so, we look at the entire product.

Recycling/disposal

We are aiming for a sustainable circular economy in the long term and actively design our products to maximise the re-use of the materials in them by making them easy to separate.



Use phase

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are extremely long-lasting and easy to repair – supported by forward-looking customer service. We also offer products and solutions that help to reduce food waste. More on this on the following pages.

Production

We want to produce in an environmentally conscious manner by reducing the energy requirements of our plants and increasingly utilising renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact above and beyond CO₂ emissions.*



* EcoVadis Gold

Our efforts have been awarded gold for 2023 by EcoVadis, the world's leading Corporate Social Responsibility ratings agency. We are proud to be among the top 3% of companies assessed by EcoVadis.

Efficient, more efficient, Liebherr.

This year's range once again has a great many appliances with the best energy efficiency classes on the market – and that is true for all our product groups: fridges, freezers and fridge-freezers from the new generation of freestanding units.

But of course there are plenty of other details, some very minor, that make a significant difference to a Liebherr in terms of efficiency. The four energy-saving modes, for example. Like EnergySaver, which increases the standard temperature to +7 °C. Or HolidayMode, which cools only the essentials while you are on holiday. Then there is CleaningMode, which saves energy while you clean your appliance.

Quality that has an impact on the climate.

We work exclusively with long-life vacuum panels and natural refrigerants, and we will use absolutely no HFO propellants until their environmental effects are fully understood. We also bear the environment in mind during production. Mostly we install materials that can be recycled after the appliance is scrapped. We also ensure that excess plastic is consistently reused.



For water without plastic.

Our InfinitySpring provides cold, perfectly filtered water in your kitchen. So you no longer need to buy bottled water, and carry bottles and crates around.

Perfectly thought out: a powerful, complete package.

Our fridges are real all-rounders. Along with their low power consumption, they also have impressively low noise levels, plenty of space for groceries, a long service life and reliable power reserves for when it really matters. We take account of a great many factors during the development stage and can offer a perfectly balanced appliance. Or to put it another way: all good things come in fours.



Energy consumption

Our new freestanding units occupy top positions in the efficiency rankings. In this way, they protect the precious resources of our environment and – thanks to low electricity costs – your wallet too.

Cooling volume

We have the perfect appliance for all family sizes, lifestyles and niche heights. We make sure that we do not waste a single litre of capacity in the extra-large drawers – right down to the smallest detail, for example with the lighting solutions that have been integrated in the housing to save space.

Noise level

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. Our new freestanding range therefore offers a wide selection of extremely quiet appliances. In some cases, it even reaches the ultra-quiet noise level of 32 db.



High efficiency: This is how economical a Liebherr can be

You can find out how efficient our appliances are using the online tool from the EU-financed projects LABEL2020 and BELT. At this site (tool.label2020.eu) you can view and compare the electricity consumption and lots of other product data for electrical appliances. The calculator also takes account of local electricity prices and shows the costs for the entire period of use. The comparison shows that a Liebherr is worth it!

Cooling performance


Intelligent sensor technology constantly adapts the cooling performance to current use, making our freestanding units very energy-efficient and economical in everyday use. At the same time they also have plenty of power in reserve, for example to cool down a large quantity of groceries after the weekly shop.



Performance in balance perfected: Our BluPerformance technology

What is innovative about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size have a considerably greater net capacity. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. Our appliances are now even quieter. We are certain that this technology will appeal not only to fans of new technology.

The current EU energy label for electronic appliances



1. The QR code for identifying the product in the EU's EPREL database (European Product Database for Energy Labelling).
2. The model identifier for manual identification of the product in the EU's EPREL database, e.g. using the article number.
3. The new A to G efficiency scale. Note: G is solely used for wine cabinets.
4. The total volume * of all freezer compartments.
5. The total volume * of all cold storage and refrigerator compartments.
6. The noise level is now classified in classes A to D.

* The term "volume" is defined in current Regulation (EU) 2019/2016.



Enough ice for even the largest party: the IceTower

The IceTower in our freezers sets new standards. It combines two large compartments: the automatic IceMaker for up to 8 kilograms of ice cubes, and another spacious compartment – large enough to store a few family pizzas upright, for example. And because this was not convenient enough for us, both of them glide in and out on a pull-out shelf with telescopic rails. We have even included an ice scoop, so your hands stay warm.



BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.



Black Steel Interior

As tasteful inside as outside: Black stainless steel inside and out makes our BlackSteel appliances a feast for the eyes through and through.

XRFbs 5295 Δ Peak series



XRFbs 5295

Peak

←121→



SFNbsd 529i

Energy efficiency class:	
Energy consumption year / 24 hrs:	199 / 0.545 kWh ¹
Total volume ² :	277 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- No Frost
- Super Frost
- LED
- Ice Tower
- Soft System
- Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Space Box
- Vario Space
- Easy Open
- Smart Device

SRBbsc 529i

Energy efficiency class:	
Energy consumption year / 24 hrs:	108 / 0.295 kWh ¹
Total volume ² :	386 l
Volume:	Fridge: 246.2 l / BioFresh compartment: 140.6 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	BlackSteel / BlackSteel
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- Bio Fresh Professional
- Hydro Breeze
- Super Cool
- Glass & Steel Interior
- Light Tower
- Infinity Spring
- Soft System
- Soft Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



LED freezer compartment lighting

When you open the drawers in your Liebherr freezer, not only are you welcomed by the sight of your food, but also by the attractive lighting. This is provided by powerful, long-life, environmentally-friendly LEDs. The lighting makes it even easier to see all of the contents and is also a unique design element.



Bottle shelf above the BioFresh safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



XRFsd 5265

Prime

←121→



SFNsdd 526i

Energy efficiency class:	
Energy consumption year / 24 hrs:	199 / 0.545 kWh ¹
Total volume ² :	277 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- No Frost
- Super Frost
- LED
- Ice Tower
- Soft System
- Super Silent
- Touch & Swipe Display
- Space Box
- Vario Space
- Easy Open
- Smart Device

SRBsdd 526i

Energy efficiency class:	
Energy consumption year / 24 hrs:	134 / 0.367 kWh ¹
Total volume ² :	384 l
Volume:	Fridge: 245.8 l / BioFresh compartment: 138.4 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- Bio Fresh Professional
- Fish & Seafood
- Super Cool
- Glass & Steel Interior
- Light Tower
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device



XRCsd 5255

Prime

←121→



SBNsdd 526i

Energy efficiency class:	
Energy consumption year / 24 hrs:	171 / 0.468 kWh ¹
Total volume ² :	313 l
Volume:	BioFresh compartment: 180.7 l / Freezer compartment: 133 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- Bio Fresh
- Duo Cooling
- No Frost
- Super Frost
- Vario Temp
- Glass & Steel Interior
- Ice Maker
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Vario Space
- Smart Device

SRsdc 525i

Energy efficiency class:	
Energy consumption year / 24 hrs:	79 / 0.216 kWh ¹
Total volume ² :	401 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- Easy Fresh
- Super Cool
- Glass & Steel Interior
- Light Tower
- Soft System
- Super Silent
- Touch & Swipe Display
- Smart Device

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezer



SpaceBox

Accommodate the "big stuff" in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



XRFsf 5220

Plus

← 123 →



SFNsfd 5227

Energy efficiency class:	D
Energy consumption year / 24 hrs:	199 / 0.545 kWh¹
Total volume ² :	277 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as low as	-15 °C
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5¹



SRsfd 5220

Energy efficiency class:	D
Energy consumption year / 24 hrs:	98 / 0.268 kWh¹
Total volume ² :	399 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5¹



Frenchdoor fridge-freezer



BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frostfree.




CBNste 8872

← 91 →

Energy efficiency class:	E
Energy consumption year / 24 hrs:	320 / 0.876 kWh
Total volume ² :	522 l
Volume:	Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 160 l
Noise output / noise class:	42 dB(A) / D
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Stainless steel / stainless steel
Exterior dimensions in cm (h / w / d):	202.7 / 91 / 61.5





VarioTemp

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C – and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties – or over the long term as a cellar compartment for storing potatoes.



EasyTwist-Ice

Whether it's a summer day or a party: Thanks to EasyTwist-Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist Ice is easy to clean and ensures hygienic ice cube production at all times.



CBNsdc 765i
Prime

Energy efficiency class:	C ¹
Energy consumption year / 24 hrs:	189 / 0.517 kWh¹
Total volume ² :	423 l
Volume:	Fridge: 216.3 l / BioFresh compartment: 68.7 l / Freezer compartment: 138 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 74.7 / 67.5¹

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Glass & Steel Interior	Light Tower	Easy Twist Ice
Soft System	Soft-Telescopic Rails	Super Silent	Touch & Swipe Display	Vario Space	Smart Device			

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



CNSda 5723
Plus

Energy efficiency class:	A ¹
Energy consumption year / 24 hrs:	104 / 0.284 kWh¹
Total volume ² :	371 l
Volume:	Fridge: 267.9 l / Freezer compartment: 103 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	201.5 / 59.7 / 67.5¹

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Easy Twist Ice	Super Silent	Touch Display	Vario Space
Smart Device Ready								

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



Replaceable door seal

Do you think the door seal on your Liebherr needs to be replaced after a few years? This is very easy to do yourself. The replaceable door seal can be removed in a few simple steps – and the new seal is just as easy to insert. As a result, this part of the refrigerator is always spotless and hygienically clean.



CNSfd 5203
Pure

Energy efficiency class:	D ¹
Energy consumption year / 24 hrs:	201 / 0.550 kWh¹
Total volume ² :	330 l
Volume:	Fridge: 227.1 l / Freezer compartment: 103 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SteelFinish / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5¹

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Super Silent	Touch Display	Vario Space	Smart Device Ready
------------	-------------	----------	------------	-------------	--------------	---------------	-------------	--------------------



Bottle shelf

The bottle shelf is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



LED light

The space-saving integrated LED light ensures that the whole interior of the refrigerator is evenly and harmoniously lit. With its low energy consumption, the long-lasting LED light is an environmentally friendly solution for a perfect overview of the food in the fridge.



CUele 2831



← 55 →

CUele 2831

Energy efficiency class:	
Energy consumption year / 24 hrs:	192 / 0.526 kWh ¹
Total volume ² :	265 l
Volume:	Fridge: 212.4 l / Freezer compartment: 54 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	Stainless steel look / silver
Exterior dimensions in cm (h / w / d):	161.2 / 55 / 63 ¹



← 55 →

CUe 2831

Energy efficiency class:	
Energy consumption year / 24 hrs:	192 / 0.526 kWh ¹
Total volume ² :	265 l
Volume:	Fridge: 212.4 l / Freezer compartment: 54 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	161.2 / 55 / 63 ¹



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.
² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.
 You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



SoftTelescopic

Look forward to opening your BioFresh safes. And this is not just because of the fresh food – but also because opening is so easy, and closing is automatic and cushioned. The telescopic rails slide the safe gently towards you. Because these extend fully, you have the best overview of the contents.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



3 bottle shelf

Now your bottles stay where they should. The 3 bottle shelf securely holds three bottles in your fridge ready to be used. The bottle shelf fits on every glass shelf and is therefore very flexible. And if you need the space for other reasons, simply take the bottle shelf out of the fridge.



TouchControl

A gentle finger tap and you set your Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple – and efficient, as the sleek button is integrated into the interior, creating more space for all your fresh goods.



← 60 →



RBsdc 525i
Prime

Energy efficiency class:	
Energy consumption year / 24 hrs:	108 / 0.295 kWh ¹
Total volume ² :	386 l
Volume:	Fridge: 245.8 l / BioFresh compartment: 140.9 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	SmartSteel / silver
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5 ¹

- Bio Fresh
- Super Cool
- Glass & Steel Interior
- Light Tower
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm (BLU Performance 1.5 cm). If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



← 60 →



Rd 5000
Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	93 / 0.254 kWh ¹
Total volume ² :	348 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5 ¹

- Easy Fresh
- Super Cool
- Touch Display
- Smart Device Ready

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



← 55 →

Re 1400
Pure

Energy efficiency class:	
Energy consumption year / 24 hrs:	90 / 0.246 kWh ¹
Total volume ² :	125 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 55 / 60.7 ¹

- Super Cool
- Super Silent
- Touch Display
- Touch Control
- Door Stop



NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.

EasyOpen

Thanks to the new EasyOpen technology, our freezers can be opened smoothly and easily at any time. Even without a handle. How do we do it? With the help of an innovative door gasket and the new BluPerformance technology module, we have managed to reduce the door-opening force by half. Space-saving, simple, convenient.

SpaceBox

Accommodate the “big stuff” in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.

SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



FNd 522i
Plus

Energy efficiency class:	D
Energy consumption year / 24 hrs:	199 / 0.545 kWh¹
Total volume ² :	277 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C	
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	185.5 / 59.7 / 67.5¹

- No Frost
- Super Frost
- Touch Display
- Space Box
- Vario Space
- Easy Open
- Frost Protect
- Smart Device



FNd 5026
Plus

Energy efficiency class:	D
Energy consumption year / 24 hrs:	188 / 0.515 kWh¹
Total volume ² :	238 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C	
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	165.5 / 59.7 / 67.5¹

- No Frost
- Super Frost
- Touch Display
- Space Box
- Vario Space
- Easy Open
- Frost Protect
- Smart Device Ready



FNd 4625
Plus

Energy efficiency class:	D
Energy consumption year / 24 hrs:	177 / 0.484 kWh¹
Total volume ² :	199 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C	
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	145.5 / 59.7 / 67.5¹

- No Frost
- Super Frost
- Touch Display
- Space Box
- Vario Space
- Easy Open
- Frost Protect
- Smart Device Ready



Fe 1404
Pure

Energy efficiency class:	E
Energy consumption year / 24 hrs:	172 / 0.471 kWh¹
Total volume ² :	107 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C	
Door / side walls:	white / white
Exterior dimensions in cm (h / w / d):	85 / 55 / 60.7¹

- Smart Frost
- Super Frost
- LED
- Touch Display
- Touch Control
- Vario Space
- Frost Protect

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm (BluPerformance 1.5 cm). If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



ECBNe 8872



LED side lighting on both sides

For a quick overview of everything in the refrigerator: thanks to the LED side lighting on both sides, your food is in view at all times. The LEDs are positioned so that your large refrigerator is also illuminated with food inside it. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.



BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



ECBNe 8872 ← 91 → 203

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	E A G
Energy consumption year / 24 hrs:	320 / 0.876 kWh
Total volume ¹ :	522 l
Volume: Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 160 l	
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	203.2-207.2 / 91.5 / min. 63.5

- Bio Fresh
- Duo Cooling
- No Frost
- Super Cool
- Super Frost
- Ice Maker
- Soft System



ECBNe 8870 ← 91 → 203

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	E A G
Energy consumption year / 24 hrs:	320 / 0.876 kWh
Total volume ¹ :	522 l
Volume: Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 160 l	
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	203.2-207.2 / 91.5 / min. 63.5

- Bio Fresh
- Duo Cooling
- No Frost
- Super Cool
- Super Frost
- Ice Maker
- Soft System

Choose from left (ECBNe 8871 - special order) or right (ECBNe 8870 - stocked) hand hinge, fixed.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



IceMaker

Are there any ice cubes left? An IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The ice cube separator helps to divide the drawer into any size you want – for example, ice cubes on the left, ice cream on the right – or just for ice cubes.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



Transparent FrostSafe drawers

All transparent FrostSafe drawers are extra deep. They are designed so that all frozen foods, from a duck to a boxed pizza, will fit conveniently and neatly, and are easy to remove. Every drawer can be used for both freezing and storage, so there's no need to repack the food once it has been frozen.



ICBNdi 5163
Prime

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	D
Energy consumption year / 24 hrs:	208 / 0.569 kWh
Total volume ¹ :	246 l
Volume:	Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 71 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Glass & Steel Interior	Light Tower	Ice Maker
Soft System	Soft-Telescopic Rails	Super Silent	Touch & Swipe Display	Vario Space	Smart Device			



ICBNci 5153
Prime

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	C
Energy consumption year / 24 hrs:	166 / 0.454 kWh
Total volume ¹ :	245 l
Volume:	Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 70 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

Bio Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Vario Temp	Glass & Steel Interior	Light Tower	Soft System
Soft-Telescopic Rails	Super Silent	Touch & Swipe Display	Vario Space	Smart Device				



ICNSe 5103
Pure

Sliding door / Built-in appliance for integrated use	
Energy efficiency class:	E
Energy consumption year / 24 hrs:	227 / 0.621 kWh
Total volume ¹ :	253 l
Volume:	Fridge: 183.3 l / Freezer compartment: 70 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

Easy Fresh	Duo Cooling	No Frost	Super Cool	Super Frost	Super Silent	Touch Display	Vario Space	Smart Device Ready
------------	-------------	----------	------------	-------------	--------------	---------------	-------------	--------------------



ICSe 5103
Pure

Sliding door / Built-in appliance for integrated use	
Energy efficiency class:	E
Energy consumption year / 24 hrs:	228 / 0.624 kWh
Total volume ¹ :	264 l
Volume:	Fridge: 183.3 l / Freezer compartment: 81 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

Easy Fresh	Duo Cooling	Smart Frost	Super Cool	Super Frost	Super Silent	Touch Display	Vario Space	Smart Device Ready
------------	-------------	-------------	------------	-------------	--------------	---------------	-------------	--------------------



Open Stage

OpenStage drawers

Now there's a clear view of everything. The different heights of the drawers make it easy to store food of different sizes. In the bottom drawer, practical dividers ensure bottles are held securely in place. And, thanks to the transparent GlassLine drawers, you have a clear view of everything from bottom to top.



IRBPci 5170
Peak



↑
178
↓

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	C
Energy consumption year / 24 hrs:	100 / 0.274 kWh
Total volume ¹ :	297 l
Volume:	Fridge: 199 l / BioFresh compartment: 98.4 l
Noise output / noise class:	31 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Bio Fresh
- Super Cool
- Open Stage
- Glass & Steel Interior
- Light Tower
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device



InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.



LED BioFresh lighting

Experience the pleasure of brightly lit fresh fruit and vegetables. The LED BioFresh lighting shows off the contents of your BioFresh safe in its best light. The lighting is positioned centrally above the BioFresh safes and supplemented by LED light columns on both sides. These extend into the topmost BioFresh safe ensuring bright illumination.



IRBci 5180
Peak



↑
178
↓

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	C
Energy consumption year / 24 hrs:	100 / 0.274 kWh
Total volume ¹ :	296 l
Volume:	Fridge: 198.1 l / BioFresh compartment: 97.9 l
Noise output / noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Bio Fresh Professional
- Hydro Breeze
- Super Cool
- Glass & Steel Interior
- Light Tower
- Infinity Spring
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device



IRBci 5151
Prime



↑
178
↓

Fixed door / Built-in appliance for integrated use

Energy efficiency class:	C
Energy consumption year / 24 hrs:	131 / 0.358 kWh
Total volume ¹ :	276 l
Volume:	Fridge: 151.3 l / BioFresh compartment: 98.4 l / Freezer compartment: 27 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Bio Fresh
- Super Cool
- Glass & Steel Interior
- Light Tower
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device



VarioBoxes

The two detachable, fridge-to-table VarioBoxes are perfect for storing ready-to-serve foods in the refrigerator. The Liebherr egg tray for 12 eggs fits perfectly in the large VarioBox. The accessories set comprises of two VarioBoxes and a robust stainless steel securing rail. VarioBoxes can be securely attached to the door interior at various levels.



SoftSystem

The stylish white SoftSystem mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



reddot winner 2021
best of the best



↑
178
↓

IRBci 5150
Prime

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	C <small>A+ G</small>
Energy consumption year / 24 hrs:	100 / 0.274 kWh
Total volume ¹ :	296 l
Volume:	Fridge: 197.7 l / BioFresh compartment: 98.4 l
Noise output / noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Bio Fresh
- Super Cool
- Glass & Steel Interior
- Light Tower
- Soft System
- Soft-Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Smart Device



↑
178
↓

IRBd 5120
Plus

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	D <small>A+ G</small>
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume ¹ :	294 l
Volume:	Fridge: 195.8 l / BioFresh compartment: 98.2 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Bio Fresh
- Super Cool
- Soft System
- Super Silent
- Touch Display
- Smart Device Ready



↑
178
↓

IRe 5100
Pure

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	E <small>A+ G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	308 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- Easy Fresh
- Super Cool
- Super Silent
- Touch Display
- Smart Device Ready



↑
140
↓

IRd 4520
Plus

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	D <small>A+ G</small>
Energy consumption year / 24 hrs:	84 / 0.230 kWh
Total volume ¹ :	235 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7-141.3 / 56-57 / min. 55

- Easy Fresh
- Super Cool
- Soft System
- Super Silent
- Touch Display
- Smart Device Ready

Freezer for integrated use



IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your freezer intuitively and with ease. Simply select functions such as SuperFrost on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? Well, it then shows you the actual temperature.

Freezers for integrated use



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



Freezer drawers

The top drawer in the freezer is often a bit of a mystery because you just can't see what's up there. A simple tilting function on the drawer allows it to be angled downwards when opened. This gives you a complete overview all the time. It also makes it easier to add and remove frozen goods. And the pull-out stop ensures the compartment does not fall out.



LED-lighting

The LED lighting is positioned above the drawers in order to save space. It ensures the best overview of your goods, saves energy and has a long life.



Side by Side
↑
178
↓

SIFNdi 5188
Peak

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	D <small>A+ G</small>
Energy consumption year / 24 hrs:	190 / 0.520 kWh
Total volume ¹ :	213 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- No Frost
- Super Frost
- LED
- Ice Tower
- Soft System
- Telescopic Rails
- Super Silent
- Touch & Swipe Display
- Vario Space
- Smart Device

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



Side by Side
↑
178
↓

SIFNe 5128
Plus

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	E <small>A+ G</small>
Energy consumption year / 24 hrs:	237 / 0.649 kWh
Total volume ¹ :	213 l
Noise output / noise class:	33 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2-178.8 / 56-57 / min. 55

- No Frost
- Super Frost
- Soft System
- Super Silent
- Touch Display
- Vario Space
- Smart Device Ready

You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



Side by Side
↑
140
↓

SIFNdi 4556
Prime

Fixed door / Built-in appliance for integrated use	
Energy efficiency class:	D <small>A+ G</small>
Energy consumption year / 24 hrs:	173 / 0.474 kWh
Total volume ¹ :	156 l
Noise output / noise class:	34 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7-141.3 / 56-57 / min. 55

- No Frost
- Super Frost
- LED
- Soft System
- Super Silent
- Touch & Swipe Display
- Vario Space
- Smart Device

Under-worktop freezer for integrated use



SoftSystem

The stylish white SoftSystem mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



NoFrost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



SUIGN 1554
Premium

Fixed door / Under-worktop appliance for integrated use

Energy efficiency class:	D
Energy consumption year / 24 hrs:	152 / 0.416 kWh
Total volume ¹ :	79 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-T (from +10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	82-88 / 60 / min. 55



Bottle baskets

If more space is needed for beverages, removable bottle baskets (optional accessory) can be inserted*. They provide plenty of space for bottles (up to 1.5 l) and drinks packages. The integrated handle makes them easy to carry and the adjustable holders ensure the bottles are held securely.


*In exchange for a removable storage shelf.



UIKo 1550
Premium

Fully extendible pull-out drawer / Under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	93 / 0.254 kWh
Total volume ¹ :	132 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82-88 / 60 / min. 55



LED ceiling light

The LED ceiling light creates a high-class ambience within the refrigerator. Its beautifully designed, space-efficient housing is centrally positioned to provide a delightfully even illumination.



UIK 1510
Comfort

Fixed door / Under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	94 / 0.257 kWh
Total volume ¹ :	136 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82-88 / 60 / min. 55



¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

Multi-temperature wine fridge



Electronic door lock

If there is one thing in life you can be sure of, it is your wines. The electronic door lock ensures this – it is unlocked by entering a PIN, preventing unauthorised use. And it is also more efficient, since the convenient unlocking method enables you to open the door more quickly.



Wall panel in BlackSteel

The ideal backdrop for your wine collection: a rear wall panel in BlackSteel. The striking black stainless steel adds a certain je ne sais quoi to the inside of your wine tempering fridge. However, appearance is just one of its advantages, the back wall also ensures balanced air circulation and perfectly controlled humidity.

Wine fridges for integrated use



LED lighting

All wine fridges feature dimmable LED lighting, which evenly illuminates the interior and can be left on permanently if desired. Because LEDs generate minimal heat, wines can be sympathetically illuminated and beautifully presented for an extended period of time.



Wooden shelves mounted on telescopic rails

The Vinidor appliances are equipped with solid wooden shelves mounted on telescopic rails. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. Storing bottles neck to neck facilitates maximum storage capacity.



WPgbi 5272
Vinidor Selection

Energy efficiency class:	F
Energy consumption year / 24 hrs:	127 / 0.347 kWh
Max. Bordeaux bottles 0.75 l:	106 ¹
Total volume ² :	367 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Door:	Black insulated glass door
Side walls:	BlackSteel
Exterior dimensions in cm (h / w / d):	185.4 / 59.7 / 67.8 ³

2 Zones	Temp Protect Plus	Storage Zone	Fresh Air	UV Protect Plus	Flex Fit	Vibrate Safe	Steel Interior	Light Tower
Soft System	Telescopic Rails	Super Silent	Touch & Swipe Display	eDoor Lock	Smart Device			

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm). You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



EWTdf 3553
Vinidor

Insulated glass door / Built-in appliance with decor panel	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	162 / 0.443 kWh
Max. Bordeaux bottles 0.75 l:	80 ¹
Total volume ² :	259 l
Noise output / noise class:	32 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Insulated glass door prepared for cabinet door or stainless steel front	
Aperture dimensions in cm (h / w / d):	177.2-178 / 56-57 / min. 55

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Steel Interior
LED	Soft System	Telescopic Rails	Super Silent	Presentation Board	

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.
³ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

Door requires furniture or s/steel frame & handle kit - Order no. 9901573

178



UWTgb 1682
Vinidor

Flush / Under-worktop appliance	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	138 / 0.378 kWh
Max. Bordeaux bottles 0.75 l:	34 ¹
Total volume ² :	94 l
Noise output / noise class:	35 dB(A) / B, SuperSilent
Climate rating:	SN-ST (from +10 °C to +38 °C)
Black insulated glass door, handle and frame free	
Aperture dimensions in cm (h / w / d):	82-87 / 60 / min. 58

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Steel Interior
LED	Soft System	Telescopic Rails	Tip Open	Super Silent	

82-87



UWTes 1672
Vinidor

Flush / Under-worktop appliance	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	142 / 0.389 kWh
Max. Bordeaux bottles 0.75 l:	34 ¹
Total volume ² :	94 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (from +10 °C to +38 °C)
Glass door with Stainless steel frame	
Aperture dimensions in cm (h / w / d):	82-87 / 60 / min. 58

2 Zones	Humidity Select	Fresh Air	UV Protect	Vibrate Safe	Steel Interior
LED	Telescopic Rails				

Liebherr After Sales & Customer Care



2 Year Warranty

All Liebherr appliances have a full 2 year warranty covering parts and labour. If any part of the machine fails or a fault develops through normal use, it will be repaired free of charge (in accordance with terms and conditions on our warranty card).



This guarantee is granted free of charge for selected freestanding fridge-freezers. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years.

For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee

Customer must install appliance as per manufacturer's instructions. Accidental damages to parts are not covered. For further information please go to: www.myliebherr.ie.



Customer Care

Our National Customer Care Centre can be contacted should you require instructions or service.

Please call 01 4600064 or you can email liebherr@naa.ie.

Spare Parts Direct

To order spare parts or accessories please call 01 4600064 or email liebherr@naa.ie with the model and 9 digit service number.

The parts or accessories can be quickly despatched direct to your home.

Liebherr's Killarney Hotels Ltd.



Ard na Sidhe Country House



Hotel Dunloe Castle



The Europe Hotel & Resort

Liebherr's Killarney Hotels Ltd. owns and operates two five-star luxury hotels in Killarney, including The Europe Hotel & Resort, situated on the famous Lakes of Killarney and Hotel Dunloe Castle overlooking the Gap of Dunloe. The company also owns and manages Ard na Sidhe Country House, a delightful Victorian style manor house, which is situated on the shores of Caragh Lake just outside Killarney. The Liebherr Group has been active in Ireland since 1958, when Liebherr (Ireland) Ltd. was founded in Killarney, Co. Kerry. Initially, this company manufactured large tower cranes. During the following decades, Liebherr's portfolio in Ireland has been significantly enlarged. Today, the Liebherr Group comprises three Irish companies operating in the sectors of maritime cranes, construction machinery and hotels, which are employing a total workforce of about 1200 people.

naa appliances ltd · wogan house · crosslands bus park · lwr ballymount road · Dublin 12
Tel.: 01 4600064
www.myliebherr.ie