



Optimal Freshness

When it comes to groceries, you care about top quality and an authentic culinary experience. You take detours to visit stalls selling regional cheeses, you appreciate freshly caught fish, and you like to grow your own radishes. Wouldn't it be great if you could still taste this quality, even after several days in the fridge? Almost as if time were standing still? We think it would.

That is what motivates us to constantly develop new and even better solutions that guarantee perfect storage conditions for all kinds of groceries. For long-lasting freshness, to protect valuable vitamins, and for food that tastes as if it had just been bought or harvested. But why not find out for yourself? Check out our 2024 freestanding units.



Contents

| Liebherr Group | |
|--|----|
| 10-year manufacturer's guarantee | |
| Quality | |
| Sustainability | |
| Performance in balance | |
| World first: BluRoX | |
| Freshness technologies | |
| EasyFresh | |
| BioFresh | |
| BioFresh Professional with HydroBreeze | |
| BioFresh Professional with Fish & Seafood Safe | |
| Design | |
| Convenience and flexibility | |
| Water and ice | |
| Connectivity | |
| User interface | , |
| Flexible accessories | |
| Series | 4 |
| Freshness centres | |
| Side-by-Side fridge-freezers | |
| Side a, Side mage messes | |
| XL-Fridge-freezers | |
| Frenchdoor fridge-freezer | |
| Fridge-freezers | |
| Fridge-freezers | |
| Fridge-freezers (with bottom freezer) | |
| Fridge-freezers (with top freezer) | (|
| | |
| Fridges | 10 |
| Fridges | 10 |
| Under counter fridges | 1 |
| Freezers | 1: |
| Freezers | 1 |
| Under counter freezers | 1 |
| Chest freezer | 1! |
| Wine Fridges | 1 |
| Design & LifeStyle | 1 |
| Outdoor Cooler | ľ |



Earthmoving



Mining



Concrete technology



Gear technology and automation systems



Components



Material handling



Mobile and crawler cranes



Maritime cranes



Refrigerators and freezers



Specialist civil engineering



Tower Cranes



Aerospace and transportation systems

A tradition of reliability admired the world over.

For 75 years Liebherr has offered high-quality products for pioneering industries. With our customers and partners all over the world, we constantly reach new heights.



One big family

The Liebherr Group was established in 1949 by Hans Liebherr. With a history spanning 75 years, the family-run company is characterised by stability and reliability. Liebherr is one of the biggest manufacturers of construction equipment and is also successful in many other industries. The Group has a decentralised organisation with more than 50,000 employees worldwide and is divided into independently operating business units.

The Group now encompasses 13 product segments – earthmoving machinery, material handling technology, deep foundation machines, mining, mobile and crawler cranes, tower cranes, concrete technology, maritime cranes, aerospace and transportation systems, gear technology and automation systems, refrigerators and freezers, components and hotels – and comprises more than 140 companies across all continents. The holding company of the Group is Liebherr-International AG in Bulle (Switzerland), all of whose shareholders are members of the Liebherr family.

Cutting edge combined with experience: Appliances

The Appliances division was established at the Ochsenhausen site in 1954 and for many years it has played an important part in the development of the Group. For 70 years, Liebherr has been a premium manufacturer of innovative refrigerators and freezers for domestic and commercial use. With an annual production of more than 2.2 million appliances, Liebherr is one of Europe's leading suppliers of cooling and freezing appliances. The five production sites in Ochsenhausen (Germany), Lienz (Austria), Radinovo (Bulgaria), Kluang (Malaysia) and Aurangabad (India) form a manufacturing network for refrigerators and freezers that meets all the most up-to-date standards.

Liebherr is active all over the world. With a dense network of sales subsidiaries and offices in Bulgaria, Germany, the UK, Austria, Canada, Malaysia, Russia, Switzerland, Singapore, South Africa and the USA, the refrigeration and freezing specialists ensure that customers receive expert advice and that service and maintenance work is provided professionally on site.



Freshness without compromise

Reliability and durability are not just buzzwords for us. Why? Because at Liebherr, every tiny detail must meet our demanding requirements. Every functional part is extensively and intensively tested. This continues until we are convinced that our refrigerators and freezers are of the highest quality.



*This guarantee is offered free of charge for selected freestanding fridge-freezers. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years. For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee

Please note that this guarantee is subject to registration and evidence of a qualifying purchase.

Secure a 10-year manufacturer's guarantee*:



Buy your new Liebherr appliance* from our webshop or a Liebherr specialist dealer by 31/12/2024.



Register

Register your appliance within 12 months using our web form (where available) or SmartDevice app.





Enjoy 10 years of Liebherr manufacturer's guarantee and long-lasting freshness.





Even the smallest detail deserves the utmost attention.

We prioritise uncompromising quality – down to the tiniest screw. And we have done so from the very start. We have been manufacturing high-quality refrigerators and freezers and selling them worldwide since 1954. However, at heart we are still a family business with deep roots in Germany. It is here that we continue to develop all our products just as before. German engineering – out of loyalty to our founder and with the knowledge built up by generations of engineers.

Convenience for everybody.

Our new freestanding units are available in different series: Pure, Plus, Prime and Peak. But whatever series you opt for, every single Liebherr comes with uncompromising Liebherr quality. This is because even in the Pure series, every appliance comes with a wide range of features. One example is NoFrost – the automatic defrosting function. Another is our EasyFresh technology for storing fruit and vegetables. Then there is our DuoCooling feature. With two separate refrigerant circuits, it ensures that no air is exchanged between the fridge and freezer compartments. The stored groceries do not dry out and no odours are transferred.









Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long.

And if, contrary to expectations, a small detail no longer meets your requirements, you or our premium service partners can usually correct it quickly. Because all our appliances are extremely repair-friendly. We keep all essential spare parts in stock for well over 10 years. This practice is not just sustainable, it also saves you money on minor repairs or the purchase of a new appliance.

We don't just say it. We also guarantee it.

During manufacturing we inspect all components of our refrigerators with great care and test them far more rigorously than required by law – and we do this for the last time just before they are packaged. It is only then that our appliances can relax a little. All of our manufacturing sites are certified in accordance with the international standards for quality ISO 9001, energy management ISO 50001 and environmental management ISO 14001. Therefore, nothing could be easier for us than to guarantee for at least two years that our products are free of material and manufacturing faults and are particularly easy to install.

Selected fridge-freezers come with a 10-year guarantee (terms and conditions apply). And with WarrantyPlus you can extend your guarantee to 5 or 10 years on any model.

In short: one thing is certain – you will be able to enjoy your Liebherr for a long time.



10 11

Our path to the future

One thing unites all our product innovations: they all present a path towards greater sustainability. Taking responsibility is one of our core values. That's why we have a decades-long tradition of research and development into eco-friendly products, with the entire product lifecycle in mind.

* EcoVadis Gold

Our efforts have been awarded gold for 2023 by EcoVadis, the world's leading Corporate Social Responsibility ratings agency. We are proud to be among the top 3% of companies assessed by EcoVadis.

Product responsibility

Use phase

Use phase

We reduce our environmental impact by continuing to offer first-class, energy-efficient products that are extremely long-lasting and easy to repair – supported by forward-looking customer service. We also offer products and solutions that help to reduce food waste. More on this on the following pages.

Production


We want to produce in an environmentally conscious manner by reducing the energy requirements of our plants and increasingly utilising renewable energy sources. By using water responsibly, minimising waste and avoiding pollution, we reduce our environmental impact above and beyond CO₂ emissions.*

ecovadis

Performance in balance
Performance in balance

Perfectly thought out: a powerful, complete package. Our fridges are real all-rounders. Along with their low power consumption, they also have impressively low noise levels, plenty of space for groceries, a long service life and reliable power reserves for when it really matters. We take account of a great many factors during the development stage and can offer a perfectly balanced appliance. Or to put it another way: all good things come in fours.





Our new freestanding units occupy top positions in the efficiency rankings. In this way, they protect the precious resources of our environment and – thanks to low electricity costs – your wallet too.


Cooling volume

We have the perfect appliance for all family sizes, lifestyles and niche heights. We make sure that we do not waste a single litre of capacity in the extra-large drawers – right down to the smallest detail, for example with the lighting solutions that have been integrated in the housing to save space.




Noise level

The boundaries between the kitchen and living areas are becoming ever more blurred in modern households. This underlines the importance of particularly quiet appliances. Our new freestanding range therefore offers a wide selection of extremely quiet appliances. In some cases, it even reaches the ultra-quiet noise level of 32 db.



Intelligent sensor technology constantly adapts the cooling performance to current use, making our freestanding units very energy-efficient and economical in everyday use. At the same time they also have plenty of power in reserve, for example to cool down a large quantity of groceries after the weekly shop.



*The term "volume" is defined in current Regulation (EU) 2019/2016. The label for Great Britain includes the Union Jack.



Performance in balance perfected: Our BluPerformance technology

What is innovative about our BluPerformance models? We have integrated all of the refrigeration technology in the appliance base. As a result, the appliances of the same size have a considerably greater net capacity. So you have noticeably more space for your food and drink. In addition, we were able to further improve energy efficiency thanks to improved ventilation and extraction in the base. And our appliances are now even quieter. We are certain that this technology will appeal not only to fans of new technology.



High efficiency: This is how economical a Liebherr can be

You can find out how efficient our appliances are using the online tool from the EU-financed projects LABEL2020 and BELT. At this site (tool.label2020.eu) you can view and compare the electricity consumption and lots of other product data for electrical appliances. The calculator also takes account of local electricity prices and shows the costs for the entire period of use. The comparison shows that a Liebherr is worth it!

The current energy label for electronic appliances

- The QR code for identifying the product in the EU's EPREL database (European Product Database for Energy Labelling)
- The model identifier for manual identification of the product in the EU's EPREL database, e.g. using the article number.
- The new A to G efficiency scale Note: G is solely used for wine fridges.
- 4. The total volume* of all freezer compartments.
- 5. The total volume* of all cold storage and refrigerator compartments
- 6. The noise level is classified in classes A to D.

14 15

BluRoX: Cold insulation with innovative vacuum perlite technology.

BluRoX represents a major step towards an energy-efficient and recyclable future. To transform cooling and freezing in a sustainable way, the pioneering BluRoX technology from Liebherr does not simply use conventional polyurethane foam but instead utilises a much more effective form of cold insulation: a vacuum. Finely ground lava stone, known as perlite, stabilises the vacuumed components – with numerous advantages for people and the environment.



The future is circular.

To learn more about this exciting technology and the many advantages of BluRoX, visit: home.liebherr.com/blurox

Maximum energy efficiency.

BluRoX provides cold insulation that is so effective that Liebherr models with this innovative vacuum insulation can deliver maximum energy efficiency. Currently the most efficient freezer of its type: the Liebherr FNb 505i with BluRoX technology in the door.





More volume.

With the same external dimensions, thanks to BluRoX there is around 25 percent more usable space inside. The particularly effective insulating effect of the vacuum enables walls and doors to be thinner compared to freezers made using polyurethane foam, creating valuable space for all the frozen goods you like to have at home.

Recyclable product design.

BluRoX is a new type of insulation which does not use conventional polyurethane foam. BluRoX delivers cold insulation using a vacuum that is stabilised with finely ground lava stone (perlite). This creates an incomparably energy-efficient and simultaneously recyclable solution: At the end of the lifespan of a BluRoX freezer, the perlite can be reused without significant processing.





Unveiled in the Liebherr FNb 505i.

BluRoX can first be seen in the Liebherr FNb 505i. In the door of this freezer, the innovative vacuum insulation celebrates a very special world first: in accordance with the new EU energy label, the Liebherr FNb 505i is the first freezer of its type to be awarded efficiency class "B". And to ensure this remains the case for many years, the high-quality insulation also boasts the durability that Liebherr is renowned for.

Tasty for longer.

You don't compromise when you're shopping. You look for natural ingredients, the best quality and maximum freshness. Of course, anyone who values good food wants to keep it fresh for as long as possible. That is precisely why we have developed innovative freshness technologies and improve them year after year, so your food still tastes fresh after some time in the refrigerator.



Full-space BioFresh.

Enough space for an entire field.

Especially at harvest time, you may need to store a lot of fruit and vegetables at the same time. Our full-space BioFresh refrigerator is idea for this. At just over 0 °C and with flexible humidity, everything stays crisp and fresh for a long time. And, if it's a smaller harvest this year, the drawers keep dairy, meat and sausages fresh for longer than in the regular fridge compartment. This appliance is rated in the highest Energy Efficiency Class A.





EasyFresh.

Ideal for fruit and vegetables.

Unpackaged fruit and vegetables feel right at home here. Stored at the same temperature as the fridge compartment and sealed airtight in the safe, lettuce, for example, is still crisp and fresh after 7 days.



BioFresh Professional with HydroBreeze. Refrigerate like the professionals.

A cold mist that covers fruit and vegetables like a protective balm. It ensures crisp freshness and improves structure - the special wow effect for fruit and vegetables in the BioFresh Professional Safe.



DuoCooling. No drying out.

The two completely separate refrigeration circuits ensure that there is no air exchange between the fridge and freezer compartments. Groceries do not dry out nor spread odour.



BioFresh.

Our all-rounder.

The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance. With the perfect humidity, fruit and vegetables stay fresh even longer in the airtight Fruit & Vegetable safe. Meat, fish and dairy products can enjoy ideal conditions in the Meat & Dairy safe.



BioFresh Professional with Fish & Seafood Safe. Like freshly caught fish from the market.

Particularly delicate foods like fish and seafood are best stored in icy temperatures and at low humidity. The constant temperature of -2 °C in the Fish & Seafood Safe is therefore ideal to keep these items tasting fresh for longer.



NoFrost.

No more defrosting.

The automatic defrosting function guarantees that frozen foods remain fresh. There is no longer a need to store frozen food temporarily during manual defrosting. The constant optimal freezing remains the same without interruptions.



Cool and misty. Perfect weather for your vegetables.

Our HydroBreeze feature exemplifies our highest standard of freshness. A cold mist covers fruit and vegetables like a protective balm in the BioFresh Professional Safe. The mist ensures crisp freshness, improves structure and keeps produce with fine leaves fresh for longer. It also creates an optical wow effect in the BioFresh Professional Safe.



Nature's freshness secret.

The Salinas valley in California is known as the salad bowl of the USA. And that is because of the particularly favourable climatic conditions. Its proximity to the cool waters of the Pacific means a fine, moist mist covers the valley and its fields in summer. This prevents the crops growing here from drying out. It is precisely this idea which inspired our BioFresh Professional with HydroBreeze.



Every time the door is opened, a fresh, cold mist is generated.



Like freshly caught fish from the market. Our Fish & Seafood Safe.

To keep fish and seafood tasting as fresh as at the market stall, even after a few days, you need a fridge compartment which maintains their freshness; such as our Fish & Seafood Safe. Fish and seafood can be stored here at -2 °C and low humidity. Perfect conditions to enjoy that freshly caught flavour for much longer.








Flexible us

The surface of the BioFresh Professional Safe can be adjusted to individual requirements. The -2 °C can be partially or even completely adjusted to a temperature zone at just above 0 °C. This is the optimal storage environment for meat and dairy products. We have illustrated these four options below:



Make a statement. In your kitchen.

Fridges stopped being uniform white kitchen appliances a long time ago. Now that dining and living areas are no longer clearly separated, design plays an increasingly important role. The new puristic design language of Liebherr appliances catches the eye with its exceptional lines, elegant surfaces and simple silhouette.

A classic, exclusive look that allows our appliances to blend seamlessly into any modern kitchen and yet still stand out. But there's no need to say any more: after all, the design already speaks for itself.

Our appliances are available with a display integrated in the door. Or, for purists, in the interior of the appliance.









InteriorFit. Fits perfectly.

Make elegant use of niches in the kitchen. With InteriorFit, our freestanding appliances fit into your kitchen without using much space – they don't need a ventilation gap between the appliance and the walls or adjacent furniture. Only the fridge door itself projects into your kitchen. Everything else is invisible.



Our options: Elegant, elegant or elegant.

Every kitchen is unique, so why should a fridge be off-the-shelf? We offer a selection of very different high-quality materials, subtle colours and ergonomic handle designs. But no matter what your customers choose: they really can't go wrong with these exclusive options.

This handle does not extend into the room. The elegant recess

harmonises with your kitchen's sleek, handle-free design.

Handle with opening mechanism

The door handle adapts gently to your hand movement and is thus even easier to open.




Door fronts

Surfaces

The following designs are available to choose from:

SmartSteel





Recessed grip

The exclusive BlackSteel elements in the interior of BlackSteel freestanding appliances and selected fully integrated appliances are an additional eye-catching feature.



Handle solutions





BlackSteel interior



For groceries with the highest requirements.

No matter how much you love the exterior of your Liebherr, at some stage you actually have to open it. So it's lucky that its interior is visually appealing as well.

Design meets functionality.

Traditional and timeless on the one hand, elegant and exclusive on the other. The new design language seamlessly blends into any interior. The interior features elegant glass and stainless steel elements. The precise machining, an eye for detail and the harmonious combination of materials, shapes and colours create an appealing overall appearance. This is subtly highlighted by the new lighting concept.









The LightTower lighting concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.

30 31

Convenience and flexibility

Convenience and flexibility





We have made simple even simpler.

Fridges and freezers are used every day. That is why we develop freestanding appliances that offer ease of use, clarity and flexibility – from the first opening of the door down to the tiniest feature.

Sometimes in life we can have everything we want.

The features of the new freestanding appliances give you more space. The divisible glass shelf, with its effortless one-handed operation, creates space for tall containers and carafes. Do you like things to be well organised? With the VarioBox and the VarioSafe you can store smaller objects neatly in the door or interior – always exactly at the height you like.

How about a cold drink? The glass shelf above the BioFresh safe can be converted into a bottle shelf in next to no time.

In our fridge-freezers with VarioTemp, the freezer compartments can be switched variably to another temperature. As a result, the freezer compartment can be used as a fridge or cellar compartment.

In turn, VarioSpace provides enough space in the freezer compartment for even the largest turkey or tallest ice-cream cake. Speaking of cake: For fans of baking, the fridge compartments in our fridges and fridge-freezers are even spacious enough for a full baking tray.

Full of food. And convenience.

The drawers in the fridge and freezer compartments of our appliances glide in and out smoothly on telescopic rails, so all your groceries are always in perfect reach. Rails also support the pull-out tray with two bottle baskets, which are easy to remove by their built-in handles. And even once you have found all the ingredients and drinks you need, things remain convenient. Thanks to the SoftSystem. This means that our doors always close gently and quietly, even if the force applied is a little too strong.



Convenience and flexibility



Drawers on telescopic rails

Pleasantly easy opening and closing – even when fully loaded – ensures that all of the groceries are perfectly accessible.



FlexSystem

Ensures clear order in the BioFresh safe. It is perfect for storing smaller portions of fruit and vegetables or sensitive groceries.



Variable temperature space as required

With VarioTemp, there is flexibility for every situation. The freezer compartment can be adjusted to a fridge or cellar compartment, with a variable temperature between -2 °C and +14 °C.

As a result, you are always perfectly prepared, even for big parties. If necessary, the freezer compartment can be used as an additional cooling zone for appetisers or drinks. Or as a cellar compartment for groceries that are sensitive to cold, such as potatoes, onions and other similar items.

Your family has grown and you are running out of space in your fridge-freezer? Not a problem. VarioTemp allows you to use the freezer compartments as a fridge in your kitchen. If combined with a separate freezer, this means you have enough space to supply even a large family with fresh groceries.



Use as fridge compartment (between -2 °C and +9 °C)



Use as freezer compartment (-18 °C)



Use as cellar compartment (+14 °C)





SpaceBoxIdeal for anything that requires a little more space.



SoftSystem soft stop mechanism

The particularly quiet and soft door closing mechanism is integrated into all models from our Prime series upwards.



Water and ice
Water and ice

This spring has its source in the fridge.

With the InfinitySpring, we bring a crystal clear, cold water source right into the heart of your kitchen. Because water is healthy. This makes lugging heavy crates and water in plastic bottles a thing of the past. This relieves the strain on your back and on our environment. Simple and sustainable.

Ice-cold water on tap with no heavy lifting.

The flush-mounted water dispenser is always there when it is needed and almost invisible when it's not. It is suitable for containers of almost any size, including carafes or bottles for soda makers. The integrated filter system ensures perfect water quality. By the way, unlike traditional table-top water filters, this one only needs to be replaced every six months.







BottleTimer.

Provides extra-fast cooling for drinks. And reminds you via the SmartDevice app not to forget bottles in the freezer compartment.

38 39

Water and ice Water and ice

Cocktails will run out before the ice does.

You like inviting people around and enjoy having as many guests as possible? Then you will love our ice features. One thing is certain: no drink will remain uncooled at your party.







Enough ice for even the largest party: the IceTower.

The IceTower in our freezers sets new standards. It combines two large compartments: the automatic IceMaker for up to 8 kilograms of ice cubes, and another spacious compartment – large enough to store a few family pizzas upright, for example. And because this was not convenient enough for us, both of them glide in and out on a pull-out shelf with telescopic rails. We have even included an ice scoop, so your hands stay warm.



Ice in a jiffy with EasyTwist Ice.


Make a supply of ice cubes quickly – without a fixed water connection. Simply fill the tank with water, let it freeze and then release the ice cubes with a twist. The EasyTwist Ice is simple to clean, and is installed in most of our freestanding appliances in the Pure series. Alternatively, it can be added easily as an accessory.



Rains ice cubes: the IceMaker.

The IceMaker produces up to 130 ice cubes a day, which automatically drop into two drawers. When MaxIce is activated, it is even possible to speed up the production of ice cubes if more guests arrive than expected. The IceMaker is connected to the fresh water pipe. If no fixed water connection is available, there is also a model with a water tank in the fridge compartment.

SmartDevice



home.liebherr.com/getsmart

Always well connected

All our appliances are either factory-equipped with a network connection module or can be retrofitted with the SmartDeviceBox.


This way, you will benefit from the many possibilities of our SmartDevice app and from connecting all fridges or freezers to your existing smart home environment. Important status and alarm notifications are sent directly to your smartphone, for example notification of an open fridge door via door alarm. Our SmartDevice app has much more to offer besides: As well as simple management and remote control of your appliances, the app also helps you with tips and tricks for your Liebherr appliance. The right accessories for each appliance, access to instruction manuals and much more can also be found here.

You can download the SmartDevice app here:

App Store







HNGRYnsite

No matter what else you have to remember every day, with HNGRYnsite and the HNGRY app, you'll always know what's in the fridge.

Every time the fridge door is closed, HNGRYnsite sends a picture to the HNGRY app. This means that you only buy what you really need and throw less away. And so that it stays that way in future, the camera has three differently sized brackets so that it can be easily fitted in any kind of fridge.









43

Refrigerators, that leave all your options open – and your doors closed.

We don't develop the refrigerators with the most functions. We develop refrigerators with exactly the right functions to store food safely and give our customers what they really need. To make their lives noticeably easier. And then we implement these features to technical perfection.

You can never be too safe.



Door alarm

Alarm when the door is open, visual as well with pulsating LED lighting.



Temperature alarm

Visual and audible warning as soon as the temperature in the freezer compartment reaches a critical level.



Power failure alarm

Visual and audible alarm in case of power failure for safe storage.



Appliance failure alarmOptical and acoustic warning

in case of appliance failure.



Reminder

Automatic reminder for maintenance and care.



Input lock

Prevents all changes to settings or activation of functions.



DemoMode

For optimal presentation of the appliance in showrooms: User interface and lighting on, cooling system off.

A touch more convenience.



CleaningMode

For a perfect view when cleaning, the lights stay on while the cooling system switches off.



PartyMode

PartyMode activates functions like SuperCool and maximum ice production.



HolidayMode

The fan, SuperCool and SuperFrost are switched off and the fridge temperature is increased to $\pm 15\,^{\circ}\mathrm{C}$ to save electricity. The freezer compartment stays switched on.



EnergySaver

Raises the standard temperature to maximum 7 °C to reduce power consumption.



abbathMode

All lighting and sounds are switched off, reactivating themselves after 80 hours.



Language settings'

Variable language setting for 12 languages on the display.



Status indicat

Be sure everything is OK at all times – thanks to the integrated status display in the appliance door. A blue light indicates everything is OK. If the status is anything but OK, the display flashes red and a warning tone also sounds.





Core competence cooling.



Temperature display

The display always shows the current temperature value. Flashing items in the menu indicate changes.



SuperFrost

Increased cooling in the freezer compartment for vitamin-preserving freezing.



uperCool

Increase the cooling performance until the fresh food is as cool as the rest of the contents.



VarioTem

Variable temperature setting between -2 °C and +14 °C means the entire freezer compartment can also be used for cooling or as a cellar compartment.

Simply smart with the app.

\bigcirc^{\diamondsuit}

NightMode

All sounds and noises are switched off – and the lighting is dimmed. For undisturbed quiet.



BottleTi

Extra fast cooling by activating SuperFrost.
The app sends an automatic reminder to take the bottles out of the ice compartment.



EasyTwist Ice

Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the finished ice cubes with a twist.



$IceCubeTimer {\tt **}$

Faster rate of ice cube production. As soon as the ice cubes are ready, the app sends a notification.

*Function only available with Touch & Swipe display.

**Available only in the Prime and Peak series.

45

Flexible accessories **Practical** LIEBHERR accessories for every need. Discover the versatility of the original Liebherr range of accessories for your fridge - and make your daily life a little easier. Our accessories Find them online with your dream model at the Liebherr Domestic Appliances store home.liebherr.com/shop or buy them from your Liebherr dealer. 46

Organisational systems

A fridge compartment design to suit your needs: If you want to sort your groceries clearly, you could use the VarioSafe, VarioBoxes, variable egg trays and the FlexSystem, for example. Additional bottle shelves and clip-on labelling systems provide a clear overview of wine stocks.







VarioBoxes

FlexSystem

Bottle shelf

Useful help of all kinds

From the practical butter dish to the easy-fill ice cube tray with a lid or the handy freezer tray, the range of accessories offers plenty of smart solutions for serving food and keeping it fresh.







Butter dish

Ice cube tray with lid

HNGRYnsite









EasyTwist Ice

Ice in a jiffy - without a fixed water connection. Quickly build up a stock of ice cubes with a water tank and a simple twist. Easy to retrofit as an accessory.

FreshAir activated charcoal filter Cleans the circulating air and quickly binds unpleasant odours. The filter is easy to replace and ensures optimum air quality.

SmartDeviceBox

You can retrofit your Liebherr with a SmartDeviceBox to connect it to the internet. The SmartDeviceBox can be installed in just a few steps and will open up the whole world of digital possibilities to you today.





FlexCube

Accessories and Consumables

Please contact our Customer Service Team who can provide you with further support: Tel: 03330 147 888 option 3, Email: lgb.refrigeration@liebherr.com

Please note that not all accessories fit all models. To find the accessory range for your appliance, please visit our webshop: home.liebherr.com/shop or buy them from your Liebherr dealer.

For a clear overview. Even before you open the fridge.

O Pure ♦ Plus ♦ Prime △ Peak

Which appliance is right for me?
A customer question that is not always easy to answer. That's why we have made it easier for you to navigate through our product range, by dividing it into four logically structured series.

O Pure series

The Pure series is our basic class. Simple, clear and perfectly equipped for all essential needs. Appliances in the Pure series are stripped down to the essentials. But are to the absolute highest level of Liebherr quality.









♦ Plus series

The Plus series builds on our Pure series and has many impressive additional details. Above all, Plus means a plus in comfort. The appliances not only provide first-class refrigeration and freezing, they are also just that little bit smarter. They help make operation a little easier.

O Prime series

With the Prime series things get much more classy. It makes an unmistakable mark in terms of design and material. Above all, genuine quality materials are used inside the appliances, such as stainless steel. But special lighting solutions also make the appliances in this series particularly appealing.









△ Peak series

The Peak series is our premium series. Here the best is combined with the best. There is no compromise. Innovative Liebherr technology meets exceptional high-end design and convenience all in a class of their own. Appliances in this series are for those who want to have it all.



Quality in every detail



BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.



DuoCooling

DuoCooling uses two completely separate refrigeration circuits to ensure no air is exchanged between the fridge and freezer compartments. The food neither dries out nor is odour transferred. This means throwing less away, shopping less often, but saving more and greater enjoyment.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



Fish & Seafood Safe

Love fish? Your Liebherr keeps fish fresh! The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger. Adjust the size of the -2 °C zone as much as you want – and store the remaining meat and dairy products at the optimum 0 °C. An LED display indicates that the -2 °C zone is currently active.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? It then shows you the actual temperature.



NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



LED freezer compartment lighting

When you open the drawers in your Liebherr freezer, not only are you welcomed by the sight of your food, but also by the attractive lighting. This is provided by powerful, long-life, environmentally-friendly LEDs. The lighting makes it even easier to see all of the contents and is also a unique design element.



Bottle shelf above the BioFresh safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this is a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



IceTower


You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.

The features shown are model dependent; look for these features in your model choice.





| 3FNUSU 3291 | |
|------------------------------------|------------------------------|
| Energy efficiency class: | D A T |
| Energy consumption year / 24 hrs: | 199 / 0.545 kWh ³ |
| Total volume ² : | 277 |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | BlackSteel / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 |
| | |



Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8 kg
- · LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

54

- Side wall heating right, suitable for combination with other refrigerators,
- freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinge, left
- Replaceable door seal

SRBbsc 529i

| *************************************** | |
|---|---|
| Energy efficiency class: | C A 1 |
| Energy consumption year / 24 hrs: | 108 / 0.295 kWh ¹ |
| Total volume 2: | 386 l |
| Volume: | Fridge: 246.2 l / BioFresh compartment: 140.6 l |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | BlackSteel / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |
| | |

| Bio Fresh Professional | Hydro Breeze | Super Cool | Glass & Steel Interior | Light Tower | Infinity Spring | Soft System | Soft Telescopic | Super Silent |
|------------------------------|-----------------|---------------|------------------------------|----------------|--------------------|----------------|--------------------|-----------------|
| Touch & Swipe | Smart | | | | | | | |

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- · SmartDeviceBox included
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- LED light panel, both sides
- LED BioFresh lighting
- 3 BioFresh safes with SoftTelescopic, 2 Fruit & Vegetable safes, of which 1 with HydroBreeze, 1 Meat & Dairy safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal
- Dry rear wall and door panel in BlackSteel





XRFst 5295

SFNetd 529i

| 0111314 3271 | |
|------------------------------------|------------------------------|
| Energy efficiency class: | D A 1 |
| Energy consumption year / 24 hrs: | 199 / 0.545 kWh ¹ |
| Total volume ² : | 277 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SmartSteel / SmartSteel |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |
| | |



Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- · Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection, LED lighting
- · Ice cube production in 24 hrs: 0.8 kg
- · Ice cube reservoir 8 kg
- LED lighting
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

• Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances

2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back

and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

- · Height-adjustable feet at front
- · Reversible door hinge, left
- · Replaceable door seal

SRBstc 529i

| Energy efficiency class: | C A 1 |
|------------------------------------|---|
| Energy consumption year / 24 hrs: | 108 / 0.295 kWh ¹ |
| Total volume ² : | 3861 |
| Volume: | Fridge: 246.2 l / BioFresh compartment: 140.6 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SmartSteel/SmartSteel |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |





Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Integrated bottle shelf
- · LED light panel, both sides
- LED BioFresh lighting
- 3 BioFresh safes with SoftTelescopic, 2 Fruit & Vegetable safes, of which 1 with
- HydroBreeze, 1 Meat & Dairy safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection

Key features


- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front - Reversible door hinging, right
- Replaceable door seal
- Dry rear wall and door panel in stainless steel with SmartSteel



←121→

XRCsd 5255

Prime





Controls

- 2.4" TFT-colour display behind-the-door. touch- & swipe
- · Digital temperature display for BioFresh and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and
- acoustic Door alarm: visual and acoustic
- Fridge and BioFresh compartments
- PowerCooling with FreshAir activated
- charcoal filter Premium GlassLine storage shelves with
- bottle holder, removable VarioBoxes
- 1 GlassLine storage shelf, of which 1 is
- divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- · LED BioFresh lighting

56

- 2 BioFresh safes with SoftTelescopic.
- 2 Fruit & Vegetable safes

Freezer compartment ****

- 4 drawers, VarioSpace
- · IceMaker with fixed 3/4" water
- · Ice cube production in 24 hrs: 1.2 kg
- · Ice cube reservoir 5.4 kg
- LED lighting
- · Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg • 2 cold storage accumulators
- · Safety glass fittings

Key features

- · Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Slimline handles with integrated opening
- · Transport handles, front and at back,
- transport castors at back · Height-adjustable feet at front
- · Reversible door hinge, left
- Replaceable door seal
- · Dry rear wall in stainless steel with SmartSteel

SRsdc 525i

| Energy efficiency class: | C A |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 79 / 0.216 kWh |
| Total volume ² : | 401 |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | SmartSteel/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 |
| | |



Controls

- 2.4" TFT-colour display behind-the-door. touch- & swipe
- · Digital temperature display
- SmartDeviceBox included
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED light panel, both sides
- 1 EasyFresh safe on telescopic rails
- 1 spacious fruit and vegetable drawer on telescopic rails

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

· Dry rear wall in stainless steel with

- PowerCooling with FreshAir activated charcoal filter
- · Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- is divided into two parts
- VarioSafe
- · Bottle shelf
- · LED light panel, both sides
- 1 EasyFresh safe on telescopic rails





touch- & swipe

SCNsdc 525i

Total volume 2:

Climate rating:

Volume:

Energy efficiency class:

Noise output / noise class:





















- Freezer compartment **** - 3 drawers, VarioSpace
- · Ice cube tray with lid Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators

- freezers and/or wine appliances
- Slimline handles with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinge, left
- SmartSteel

- 2.4" TFT-colour display behind-the-door. touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

- PowerCooling with FreshAir activated
- Premium GlassLine storage shelves with
- adjustable egg tray, butter dish

- LED light panel, both sides

Freezer compartment ****

- 3 drawers, VarioSpace
- · Ice cube tray with lid

Safety glass fittings

- Temperature rise time: 20 h

161 / 0.441 kWh

34 dB(A) / B, SuperSilent

SmartSteel / silver

185.5 / 59.7 / 67.5 1

SN-T (from +10 °C to +43 °C)


Fridge: 228.7 l / Freezer compartment: 103 l

• Freezing capacity in 24 hrs: 10 kg 2 cold storage accumulators

Key features

LED lighting

- · Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Slimline handles with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Replaceable door seal
- SmartSteel



2 in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

57

•



←121→

XCCsd 5250

SCNsdc 525i

Total volume 2:

Climate rating:

Door / side walls:

Volume:

Controls


Energy efficiency class:

Noise output/noise class:

Energy consumption year / 24 hrs:

Exterior dimensions in cm (h/w/d):

161 / 0.441 kWh ³ Energy consumption year / 24 hrs: 331 l Fridge: 228.7 l / Freezer compartment: 103 l 34 dB(A) / B, SuperSilent SN-T (from +10 °C to +43 °C)



- Controls • 2.4" TFT-colour display behind-the-door.
- Digital temperature display for fridge and LED lighting freezer compartments - SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic · Door alarm: visual and acoustic

- Fridge compartment
- 4 GlassLine storage shelves, of which 1

· Safety glass fittings

- **Key features** - Side wall heating right, suitable for combination with other refrigerators.

- · Replaceable door seal · Dry rear wall in stainless steel with

- Fridge compartment charcoal filter
- bottle holder, removable VarioBoxes,
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Bottle shelf
- 1 EasyFresh safe on telescopic rails
- · Reversible door hinging, right
- Dry rear wall in stainless steel with






←123→

XRFsf 5245







- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ****

- 7 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8 kg
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

Key features

58

- Side wall heating right, suitable for combination with other refrigerators,
- freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinge, left
- · Replaceable door seal

SRBsfc 5220

| Energy efficiency class: | C A T |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 101 / 0.276 kWh ¹ |
| Total volume 2: | 382 l |
| Volume: | Fridge: 288.7 l/BioFresh compartment: 93.7 l |
| Noise output/noise class: | 34 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- · SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←123→

SFNsfd 5247

| D A d |
|------------------------------|
| 199 / 0.545 kWh ¹ |
| 277 (|
| 36 dB(A)/C |
| SN-T (from +10 °C to +43 °C) |
| SteelFinish/silver |
| 185.5 / 59.7 / 67.5 1 |
| |















Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- IceTower
- IceMaker with fixed 3/4" water connection
- · Ice cube production in 24 hrs: 0.8 kg
- · Ice cube reservoir 8 kg
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 18 kg

Key features

- Side wall heating right, suitable for combination with other refrigerators,
- freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinge, left
- · Replaceable door seal

SRsfd 5220

| Energy efficiency class: | D A 1 |
|------------------------------------|----------------------------------|
| Energy consumption year / 24 hrs: | 98 / 0.268 kWh ¹ |
| Total volume ² : | 399 l |
| Noise output/noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |









- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Bottle shelf
- · LED ceiling lighting • 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal





←123→

XRFsf 5225



Energy efficiency class: Energy consumption year / 24 hrs: 199 / 0.545 kWh 1 Total volume 2: 277 l 36 dB(A)/C Noise output / noise class: Climate rating: SN-T (from +10 °C to +43 °C) Door/side walls: SteelFinish / silver 185.5 / 59.7 / 67.5 1 Exterior dimensions in cm (h/w/d):



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- · Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

Key features

60

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinge, left
- Replaceable door seal

SRBsfc 5220

| Energy efficiency class: | C A † |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 101 / 0.276 kWh ¹ |
| Total volume 2: | 382 l |
| Volume: | Fridge: 288.7 l / BioFresh compartment: 93.7 l |
| Noise output/noise class: | 34 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- · SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←123→

SRbdd 5220

Total volume 2:

Climate rating:

Door/side walls:

Energy efficiency class:

Noise output/noise class:

Energy consumption year / 24 hrs:

SFNbdd 5227

| *************************************** | |
|---|------------------------------|
| Energy efficiency class: | D A T |
| Energy consumption year / 24 hrs: | 199 / 0.545 kWh ¹ |
| Total volume ² : | 277 (|
| Noise output / noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | BlackSteel/black |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 1 |
| | |





- Digital temperature display

· SmartDeviceBox: optional accessory

- Door alarm: visual and acoustic

Freezer compartment ** * * *

• Temperature rise time: 16 h

· Freezing capacity in 24 hrs: 18 kg

freezers and/or wine appliances

· Height-adjustable feet at front

· Reversible door hinge, left

· Replaceable door seal

· Vertical recessed handle

· Ice cube tray

Key features



· LC monochrome display behind-the-door, touch electronic

- Alarm in case of malfunction: visual and acoustic

• 7 drawers on integrated drawer guide, VarioSpace

· Side wall heating right, suitable for combination with other refrigerators,

• Transport handles, front and at back, transport castors at back

- Top drawer with convenient tilting function











Exterior dimensions in cm (h/w/d):







- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

98 / 0.268 kWh

BlackSteel / black

185.5 / 59.7 / 67.5 1

35 dB(A) / B, SuperSilent

SN-T (from +10 °C to +43 °C)



←123→



| SFNstd 5227 | |
|------------------------------------|-----------------------------|
| Energy efficiency class: | D A |
| Energy consumption year / 24 hrs: | 199 / 0.545 kWh |
| Total volume ² : | 277 |
| Noise output / noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C |
| Door/side walls: | SteelFinish/silve |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 |





• LC monochrome display behind-the-door, touch electronic















- Digital temperature display
- · SmartDeviceBox: optional accessory

- Door alarm: visual and acoustic Freezer compartment *****

· SmartDeviceBox: optional accessory

- Digital temperature display

• 7 drawers on integrated drawer guide, VarioSpace

- Alarm in case of malfunction: visual and acoustic

- Top drawer with convenient tilting function
- · Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg

Key features

- Side wall heating right, suitable for combination with other refrigerators,
- freezers and/or wine appliances
- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinge, left
- Replaceable door seal

SRsfd 5220

| Energy efficiency class: | D a |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 98 / 0.268 kWh ³ |
| Total volume ² : | 399 1 |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 |
| | |



- LC monochrome display behind-the-door, touch electronic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←123→

XRF 5220

SRd 5220

Total volume 2:

Climate rating:

Door/side walls:

Energy efficiency class: Energy consumption year / 24 hrs:

Noise output/noise class:

SFNd 5227

| ······································ | |
|--|----------------------------------|
| Energy efficiency class: | D A 1 |
| Energy consumption year / 24 hrs: | 199 / 0.545 kWh ¹ |
| Total volume ² : | 277 l |
| Noise output/noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |
| | |





· SmartDeviceBox: optional accessory

- Door alarm: visual and acoustic

Freezer compartment ** * * *

• Temperature rise time: 16 h

· Freezing capacity in 24 hrs: 18 kg

freezers and/or wine appliances

· Height-adjustable feet at front

· Reversible door hinge, left

Replaceable door seal

· Vertical recessed handle

· Ice cube tray

Key features

Digital temperature display



- Alarm in case of malfunction: visual and acoustic

• 7 drawers on integrated drawer guide, VarioSpace

- Top drawer with convenient tilting function

· LC monochrome display behind-the-door, touch electronic



· Side wall heating right, suitable for combination with other refrigerators,

• Transport handles, front and at back, transport castors at back







- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory

Exterior dimensions in cm (h/w/d):

- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube - 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

98 / 0.268 kWh

white/white

185.5 / 59.7 / 67.5 1

35 dB(A) / B, SuperSilent

SN-T (from +10 °C to +43 °C)

62





BioFresh drawers

Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frostfree.



CBNste 8872

| Energy ef | ficiency class: | E |
|------------|---|--|
| Energy co | nsumption year / 24 hrs: | 320 / 0.876 kW |
| Total volu | me¹: | 522 |
| Volume: | Fridge: 292.2 l / BioFresh compart | tment: 70.6 l / Freezer compartment: 160 |
| Noise out | put/noise class: | 42 dB(A)/ |
| Climate ra | ating: | SN-T (from +10 °C to +43 °C |
| Door/sid | e walls: | Stainless steel / stainless stee |
| Exterior d | imensions in cm (h /w /d). | 202.7/91/61. |



- MagicEye behind-the-door, touch
- Digital temperature display for fridge and freezer compartments
- FrostControl
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelves with bottle holder
- 3 GlassLine storage shelves
- · Integrated bottle shelf
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment *****

- 2 drawers on telescopic rails
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.4 kg
- · Ice cube reservoir 2.7 kg
- LED lighting
- Temperature rise time: 16.9 hFreezing capacity in 24 hrs: 9.5 kg

Key features

- Aluminium handles
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- neight-aujustable leet at ho
- Door hinge left fixed/right fixed
- Replaceable door sealDry rear wall in stainless steel
- Dry rear wall in staintess steet



CBNbsc 778i

←75 →

| reak reak | |
|--|--|
| Energy efficiency class: | C A 1 |
| Energy consumption year / 24 hrs: | 203 / 0.556 kWh ¹ |
| Total volume ² : | 473 l |
| Volume: Fridge: 208.7 l / BioFresh compartme | nt: 126.2 l / Freezer compartment: 138 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | BlackSteel / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 201.5 / 74.7 / 67.5 1 |
| - | |

| Bio Fresh Professional | Hydro Breeze | Fish & Seafood | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior |
|------------------------------|-----------------|--------------------|-----------------|-----------------------------|----------------|-----------------|---------------|------------------------------|
| Light Tower | Soft System | Soft Telescopic | Super Silent | Touch & Swipe Display | Vario Space | Smart Device | | |

Freezer compartment *****

pull-out, VarioSpace

· Ice cube tray with lid

· LED lighting

Key features

Vertical recessed handles

transport castors at back

· Height-adjustable feet at front

· Reversible door hinging, right

• Dry rear wall and door panel in

· Replaceable door seal

BlackSteel

· Transport handles, front and at back,

- 3 drawers with telescopic partial

Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- · SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- LED BioFresh lighting
- 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe with HydroBreeze, 1 Fish & Seafood safe, 1 FlexSystem



←75 →

CBNsdb 775i

| Energy efficiency class: | B A | | | |
|---|---|--|--|--|
| Energy consumption year / 24 hrs: | 162 / 0.443 kWh ¹ | | | |
| Total volume ² : | 473 l | | | |
| Volume: Fridge: 208.7 l / BioFresh compartm | ent: 126.9 l / Freezer compartment: 138 l | | | |
| Noise output/noise class: 34 dB(A)/B, Supe | | | | |
| Climate rating: | SN-T (from +10 °C to +43 °C) | | | |
| Door/side walls: | SmartSteel/silver | | | |
| Exterior dimensions in cm (h/w/d): | 201.5 / 74.7 / 67.5 1 | | | |

| Exterior | dimension | | 201.5 / 74 | 1.7 / 67. | | | | |
|----------------|--------------------|-----------------|-----------------------------|----------------|-----------------|------------------------------|----------------|----------------------|
| Bio Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior | Light Tower | Easy Twist Ice |
| Soft System | Soft Telescopic | Super Silent | Touch & Swipe Display | Vario Space | Smart Device | | | |

- 2.4" TFT-colour display in-the-door, touch- & swipe
 - · Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox included
- Temperature rise time: 20 h · Freezing capacity in 24 hrs: 10 kg · Alarm in case of malfunction: visual and • 2 cold storage accumulators acoustic
 - Door alarm: visual and acoustic

Fridge and BioFresh compartments


- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- · LED BioFresh lighting
- · 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe, 1 Meat & Dairy

Freezer compartment *****

- 3 drawers, VarioSpace
- LED lighting
- · Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Slimline handles with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal
- · Dry rear wall in stainless steel with SmartSteel





PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan as powerful as it is quiet - distributes the cold air efficiently throughout the entire refrigeration compartment.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? It then shows you the actual temperature.



←75→

CBNsdc 765i

Energy efficiency class: 189 / 0.517 kWh 1 Energy consumption year / 24 hrs: Total volume 2: Volume: Fridge: 216.3 l/BioFresh compartment: 68.7 l/Freezer compartment: 138 l Noise output/noise class: 34 dB(A) / B, SuperSilent SN-T (from +10 °C to +43 °C) Climate rating: SmartSteel / silver Door/side walls: Exterior dimensions in cm (h/w/d): 185.5 / 74.7 / 67.5 1

| Bio Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior | Light Tower | Ea Tv Ice |
|----------------|--------------------|-----------------|-----------------------------|----------------|-----------------|------------------------------|----------------|-----------------|
| Soft System | Soft Telescopic | Super Silent | Touch & Swipe Display | Vario Space | Smart Device | | | |

Freezer compartment *****

- Temperature rise time: 20 h

- 2 cold storage accumulators

- Freezing capacity in 24 hrs: 10 kg

· Transport handles, front and at back,

transport castors at back

· Height-adjustable feet at front

· Reversible door hinging, right

· Dry rear wall in stainless steel with

· Replaceable door seal

- 3 drawers, VarioSpace

- Safety glass fittings

- LED lighting

Key features

mechanism

SmartSteel

Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

- Slimline handles with integrated opening

- Fridge and BioFresh compartments • PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- · LED BioFresh lighting
- 1 BioFresh safe with SoftTelescopic, 1 Fruit & Vegetable safe
- 2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.
 You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost fridge-freezers



←75 →

CNsdd 776i

Energy efficiency class: 232 / 0.635 kWh 1 Energy consumption year / 24 hrs: Total volume 2: Volume: Fridge: 349.1 l / Freezer compartment: 139 l 34 dB(A) / B, SuperSilent Noise output / noise class: SN-T (from +10 °C to +43 °C) Climate rating: SmartSteel/silver Door/side walls: Exterior dimensions in cm (h/w/d): 201.5 / 74.7 / 67.5 1

| Easy Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior | Light Tower | Ice Ma |
|----------------|-----------------|-----------------------------|----------------|-----------------|---------------|------------------------------|----------------|-----------|
| Soft System | Super Silent | Touch & Swipe Display | Vario Space | Smart Device | | | | |

Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Bottle shelf

68

- · LED light panel, both sides
- 1 EasyFresh safe on telescopic rails

Freezer compartment *****

- 3 drawers, VarioSpace
- IceMaker with fixed 3/4" water
- Ice cube production in 24 hrs: 1.2 kg
- · Ice cube reservoir 5.4 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- · Slimline handles with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal
- · Dry rear wall in stainless steel with
- SmartSteel



←75→

CNsfd 7723

| D A T |
|--|
| 231/0.632 kWh |
| 485 |
| Fridge: 347.7 l / Freezer compartment: 138 |
| 35 dB(A) / B, SuperSilent |
| SN-T (from +10 °C to +43 °C) |
| SteelFinish / silver |
| 201.5 / 74.7 / 67.5 |
| |

Duo No Super Super Easy Super Touch Vario Cooling Frost Cool Frost Coe Silent Display Space



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and Freezing capacity in 24 hrs: 10 kg freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and
- acoustic · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, egg tray, FlexCube
- · 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarinSafe
- · Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment *****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Safety glass fittings

Kev features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

EasyTwist Ice

NoFrost

- and saving money.

When you open your freezer, you want to see frozen food - and certainly not ice and frost.

NoFrost protects the freezer compartment from

unwanted icing, which consumes a lot of energy

and can be expensive. NoFrost means no more

tedious and time-consuming defrosting of the

freezer compartment, more time for other things

Whether it's a summer day or a party: Thanks to EasyTwist Ice, you can prepare a supply of ice cubes quickly and easily - without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist - and you're ready to serve cool drinks. The EasyTwist Ice is easy to clean and ensures hygienic ice cube production at all times.

NoFrost fridge-freezers



←75→

CNd 7723

| Energy efficiency class: | D A 1 |
|--------------------------------------|--|
| Energy consumption year / 24 hrs: | 231 / 0.632 kWh ¹ |
| Total volume 2: | 485 l |
| Volume: | Fridge: 347.7 l / Freezer compartment: 138 l |
| Noise output/noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h /w /d): | 201 5 / 74 7 / 47 5 1 |

















Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and Freezing capacity in 24 hrs: 10 kg freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, egg tray, FlexCube
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment ****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h

Safety glass fittings


Kev features

- Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal





Range overview by device height and series



△ Peak series

Prime series

♦ Plus series

O Pure series

Fridge-freezers - BioFresh Professional

| HydroBreeze/IceMaker/VarioTemp CBNstb 579i HydroBreeze/Fish & Seafood/VarioTemp CBNbsc 778i CBNbsd 578i |
|---|
| HydroBreeze/Fish & Seafood/VarioTemp CBNbsc 778i CBNbsd 578i |
| |

Fridge-freezers – BioFresh

| Frost | | | |
|-------------------------|-------------|---------------|-------------|
| EasyTwist-Ice/VarioTemp | CBNsdb 775i | CBNsda 575i | |
| | CBNsdc 765i | CBNbsa10 575i | |
| VarioTemp | | CBNsdb 575i | |
| EasyTwist-Ice | | CBNbda 572i | CBNsda 5223 |
| | | CBNa 572i | CBNsfc 5223 |
| | | CBNsfc 57vi | CBNc 5223 |
| | | CBNsda 572i | CBNsdc 522i |
| | | CBNc 5723 | CBNbda 5223 |
| | | CBNbdc 573i | |
| | | CBNsdc 573i | |

Fridge-freezers - EasyFresh

| Frost | | | | |
|--------------------|------------|------------|------------|------------|
| with IceMaker | CNsdd 776i | CNsfc 574i | | |
| with EasyTwist-Ice | CNsfd 7723 | CNbdc 573i | CNbdb 5223 | |
| | CNd 7723 | CNc 5724 | CNsdb 5223 | |
| | | CNbda 5723 | | |
| | | CNsda 5723 | | |
| | | CNsdb 5723 | | |
| | | CNsfd 5704 | CNsfd 5204 | CNsfc 5023 |
| | | CNd 5704 | CNd 5204 | |
| | | CNsfd 5703 | CNsfd 5203 | |
| | | CNd 5703 | CNd 5203 | |

Series

Fridge-freezers







♦ Plus series



O Prime series



△ Peak series

| | O Pure series | \Diamond Plus series | ○ Prime series | riangle Peak series |
|----------------------------------|--------------------------------------|---|---|---|
| Freshness technology | EasyFresh on integrated drawer guide | EasyFresh on integrated drawer guide | EasyFresh on telescopic rails | EasyFresh on telescopic rails |
| | | BioFresh on telescopic rails | BioFresh with SoftTelescopic | BioFresh Professional with SoftTelescopic |
| | | | | HydroBreeze |
| | | | | Fish & Seafood safe |
| | DuoCooling | DuoCooling | DuoCooling | DuoCooling |
| | FreshAir filter | FreshAir filter | FreshAir filter | FreshAir filter |
| | | | VarioTemp | VarioTemp |
| | NoFrost | NoFrost | NoFrost | NoFrost on telescopic rails |
| Comfort and flexibility | | Divisible glass shelf | Divisible glass shelf | Divisible glass shelf |
| | | | SoftSystem soft closing mechanism | SoftSystem soft closing mechanism |
| | | VarioSafe | VarioSafe | VarioSafe |
| | | | VarioBoxes | VarioBoxes |
| | | | Butter dish | Butter dish |
| | Egg tray | Egg tray | Adjustable egg tray | Adjustable egg tray |
| | Bottle shelf | Bottle shelf | Bottle shelf | Bottle shelf |
| | | Ice cube tray | Ice cube tray with lid | Ice cube tray with lid |
| | | | | FlexSystem |
| Design | Ceiling lighting fridge compartment | Ceiling lighting fridge compartment | LightTower | LightTower |
| | | | Lighting BioFresh safe | Lighting BioFresh safe |
| | | | Freezer compartment lighting | Freezer compartment lighting |
| | | | | IceMaker lighting |
| | | | | Fan lighting |
| | | | SmartSteel rear wall | SmartSteel rear wall |
| | | | | SmartSteel door interior |
| | Transparent glass | Transparent glass | Satin finish glass | Satin finish glass |
| | Stainless steel look shelves | Stainless steel look shelves | Glass & stainless steel rack | Glass & stainless steel rack |
| | Touch display | Touch display | Touch & Swipe display | Touch & Swipe display |
| | | Display behind the door | Display behind the door | Display behind the door |
| | Display behind the door | or Display in the door | or Display in the door | or Display in the door |
| | Recessed handles | Recessed handles | Slimline door handles with opening mechanism | Recessed handles |
| Connectivity (SmartDeviceBox) | Can be retrofitted | Can be retrofitted or is included with "i" models | Can be retrofitted or is included with "i" models | Can be retrofitted or is included with "i" models |
| Water and ice | - | IceMaker or EasyTwist-Ice | IceMaker or EasyTwist-Ice | IceMaker |
| | | | | |

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

Quality in every detail



BioFresh with HydroBreeze

Do you want to cool fruit and vegetables like professionals? You'll be inspired by HydroBreeze. The cold mist combined with a temperature in the safe of around 0 °C gives food that extra boost for longer shelf life. And it creates a genuine visual wow effect. HydroBreeze is activated every 90 min. for 4 seconds and for 8 seconds when the door is opened.



InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables drip-free water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



Fish & Seafood Safe

Love fish? Your Liebherr keeps fish fresh! The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger. Adjust the size of the -2 °C zone as much as you want – and store the remaining meat and dairy products at the optimum 0 °C. An LED display indicates that the -2 °C zone is currently active.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your refrigerator intuitively and with ease. Simply select functions such as SuperCool on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? It then shows you the actual temperature.



SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this is a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



LED ceiling lighting

The LED ceiling lighting illuminates the interior from above – providing a good overview of your food. Another highlight: the LEDs are positioned in front of the glass shelves so that even a full refrigerator is well lit.



Recessed grip

Special and functional: You can open the appliance very easily using the vertically integrated and ergonomically fitted handle. Additionally, the modern and puristic design fits perfectly into your hands-free kitchen.




VarioTemp

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C - and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties - or over the long term as a cellar compartment for storing potatoes.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



IceMaker with fixed water connection

Are there any ice cubes left? The IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The versatile ice compartment divider lets you choose the amount of ice cubes you want to store; easy and just as you like it.

BioFresh NoFrost fridge-freezers



←60→



| Energy efficiency class: | $\begin{bmatrix} B & A \\ f & G \end{bmatrix}$ | |
|--|--|--|
| Energy consumption year / 24 hrs: | 144 / 0.394 kWh ¹ | |
| Total volume ² : | 362 l | |
| Volume: Fridge: 160.3 l / BioFresh compartment | : 98.7 l / Freezer compartment: 104 l | |
| Noise output/noise class: | 33 dB(A) / B, SuperSilent | |
| Climate rating: | SN-T (from +10 °C to +43 °C) | |
| Door/side walls: | SmartSteel/SmartSteel | |
| Exterior dimensions in cm (h/w/d): 201.5/ | | |

| Bio Fresh Professional | Hydro Breeze | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior | Light Tower |
|------------------------------|-----------------|----------------|--------------------|-----------------|-----------------------------|----------------|------------------------------|----------------|
| Infinity Spring | Ice Maker | Soft System | Soft Telescopic | Super Silent | Touch & Swipe Display | Vario Space | Smart Device | |

Freezer compartment *****

partial pull-out, VarioSpace

connection, LED lighting

· Ice cube reservoir 5.4 kg

• Temperature rise time: 20 h

- 2 cold storage accumulators

Vertical recessed handles

transport castors at back

· Height-adjustable feet at front

· Reversible door hinging, right

· Replaceable door seal

steel with SmartSteel

• Transport handles, front and at back,

• Dry rear wall and door panel in stainless

Safety glass fittings

· Freezing capacity in 24 hrs: 10 kg

LED lighting

· IceMaker with fixed 3/4" water

- 3 drawers, of which 2 with telescopic

· Ice cube production in 24 hrs: 1.2 kg

Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight and FreshAir activated charcoal filter
- Premium GlassLine storage shelves with Key features bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- LED BioFresh lighting
- 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe with HydroBreeze, 1 Meat & Dairy safe,
- 1 FlexSystem
- · InfinitySpring with fixed 3/4" water connection



| Energy ef | ficiency class: | D A T |
|------------|--|---|
| Energy co | nsumption year / 24 hrs: | 225 / 0.616 kWh ¹ |
| Total volu | me²: | 359 l |
| Volume: | Fridge: 160.3 l/BioFresh compartn | nent: 96.1 l / Freezer compartment: 103 l |
| Noise out | put/noise class: | 34 dB(A) / B, SuperSilent |
| Climate ra | ating: | SN-T (from +10 °C to +43 °C) |
| Door/sid | e walls: | BlackSteel/BlackSteel |
| Exterior d | imensions in cm (h/w/d): | 201.5 / 59.7 / 67.5 1 |



Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
 - · Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox included
 - · Alarm in case of malfunction: visual and
 - Door alarm: visual and acoustic

Fridge and BioFresh compartments • PowerCooling with Ambilight and

- FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf · LED light panel, both sides
- · LED BioFresh lighting
- 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe with HydroBreeze, 1 Fish & Seafood safe, 1 FlexSystem

Freezer compartment ****

- 3 drawers, of which 2 with telescopic

reddot winner 2022

←60→

- partial pull-out, VarioSpace · Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front · Reversible door hinging, right
- · Replaceable door seal
- Dry rear wall and door panel in
- BlackSteel

1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm.





Our energy saving fridge-freezers in class A

That feeling of getting fresh fruit and crisp vegetables out of the fridge just got better. With our class A fridge-freezers, you have the best energy efficiency available and sophisticated freshness technology to keep your food fresher for longer - saving resources twice over.



VarioTemp

VarioTemp means you have plenty of scope when storing food in your fridge freezer. This is because you can also set the accurate temperature in the freezer compartment in a range between -2 °C and +14 °C - and therefore also use this compartment as a further cooling zone. For example, it can be used over the short term for drinks and snacks at parties - or over the long term as a cellar compartment for storing potatoes.



←60→

CBNsda 575i

| 100.00 | | |
|-------------|--|---|
| Energy eff | iciency class: | A A |
| Energy co | nsumption year / 24 hrs: | 116 / 0.317 kWh ³ |
| Total volu | me²: | 362 |
| Volume: | Fridge: 159.9 l / BioFresh compartn | nent: 99.2 l / Freezer compartment: 103 |
| Noise out | out/noise class: | 33 dB(A) / B, SuperSilent |
| Climate ra | ting: | SN-T (from +10 °C to +43 °C) |
| Door/side | e walls: | SmartSteel/silver |
| Exterior di | mensions in cm (h/w/d): | 201.5 / 59.7 / 67.5 |



Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

- Fridge and BioFresh compartments • PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- · LED BioFresh lighting
- 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe, 1 Meat & Dairy

Freezer compartment *****

- 3 drawers, VarioSpace
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings


- Slimline handles with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right · Replaceable door seal
- · Dry rear wall in stainless steel with SmartSteel

- 2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the
- nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.
 You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

BioFresh NoFrost fridge-freezers BioFresh NoFrost fridge-freezers







| Ultra Efficient A -10% | Bio Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass & Steel Interior | Light Tower |
|------------------------------|----------------|--------------------|-----------------|-----------------------------|----------------|-----------------|------------------------------|----------------|
| Easy Twist Ice | Soft System | Soft Telescopic | Ultra Silent | Touch & Swipe Display | Vario Space | Smart Device | | |

Freezer compartment ****

- Temperature rise time: 20 h

2 cold storage accumulators

• Freezing capacity in 24 hrs: 10 kg

· Slimline handles with integrated opening

3 drawers, VarioSpace

· Safety glass fittings

• Replaceable door seal

BlackSteel

LED lighting

Key features

Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish, FlexCube
- 2 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- LED light panel, both sides
- LED BioFresh lighting

80

· 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe



←60→

CBNsdb 575i

Energy efficiency class: 144 / 0.394 kWh Energy consumption year / 24 hrs: Total volume² Volume: Fridge: 159.9 l/BioFresh compartment: 99.2 l/Freezer compartment: 103 l 29 dB(A) / A, UltraSilent Noise output / noise class: SN-T (from +10 °C to +43 °C) Climate rating: Door/side walls: SmartSteel / silver Exterior dimensions in cm (h/w/d): 201.5 / 59.7 / 67.5 1

| Bio Fresh | Duo Cooling | No Frost | Super Cool | Super Frost | Vario Temp | Glass Steel Interi |
|--------------------|-----------------|-----------------------------|----------------|-----------------|---------------|--------------------------|
| Soft Telescopic | Ultra Silent | Touch & Swipe Display | Vario Space | Smart Device | | |

Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
 - Door alarm: visual and acoustic

- Fridge and BioFresh compartments mechanism · Transport handles, front and at back, · PowerCooling with FreshAir activated
- transport castors at back charcoal filter · Height-adjustable feet at front • Premium GlassLine storage shelves with · Reversible door hinging, right bottle holder, removable VarioBoxes,
- adjustable egg tray, butter dish · Dry rear wall and door panel in - 2 GlassLine storage shelves, of which 1 is divided into two parts
 - VarioSafe
 - · Integrated bottle shelf
 - · LED light panel, both sides
 - · LED BioFresh lighting
 - · 2 BioFresh safes with SoftTelescopic, 1 Fruit & Vegetable safe, 1 Meat & Dairy

Freezer compartment ****

- 3 drawers, VarioSpace
- · Ice cube tray with lid
- LED lighting
- Temperature rise time: 20 h
 - Freezing capacity in 24 hrs: 10 kg
 - · 2 cold storage accumulators
 - · Safety glass fittings

Key features

- · Slimline handles with integrated opening
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal
- · Dry rear wall in stainless steel with SmartSteel





CBNbda 572i

A d d Energy efficiency class: 116 / 0.317 kWh ¹ Energy consumption year / 24 hrs: Total volume 2: 360 l Volume: Fridge: 158.8 l/BioFresh compartment: 98.9 l/Freezer compartment: 103 l 34 dB(A) / B, SuperSilent Noise output / noise class: SN-T (from +10 °C to +43 °C) Climate rating: Door/side walls: BlackSteel / black 201.5 / 59.7 / 67.5 1 Exterior dimensions in cm (h/w/d):



Controls

acquistic

charcoal filter

egg tray, FlexCube

· Integrated bottle shelf

· LED ceiling lighting

1 Meat & Dairy safe

3 drawers, VarioSpace

· Safety glass fittings

- 3 GlassLine storage shelves,

touch electronic

freezer compartments SmartDeviceBox included





· LC monochrome display behind-the-door,

Digital temperature display for fridge and

Alarm in case of malfunction: visual and

· Door alarm: visual and acoustic

Fridge and BioFresh compartments

PowerCooling with FreshAir activated

· Plastic door shelves with bottle holder,

of which 1 is divided into two parts

• 2 BioFresh safes with telescopic partial

pull-out, 1 Fruit & Vegetable safe,

Freezer compartment ****

- Temperature rise time: 20 h

· Freezing capacity in 24 hrs: 10 kg









Key features



Vertical recessed handles

transport castors at back

· Replaceable door seal

Colour/material options:

CBNa 572i in white

· Height-adjustable feet at front

· Reversible door hinging, right

· Transport handles, front and at back,



←60→





Energy efficiency class:

Noise output/noise class:

Total volume 2:

Climate rating:

Door/side walls

Energy consumption year / 24 hrs:



Exterior dimensions in cm (h/w/d):



CBNbdc 573i

Volume: Fridge: 158.8 l/BioFresh compartment: 98.9 l/Freezer compartment: 103 l







35 dB(A) / B, SuperSilent

SN-T (from +10 °C to +43 °C)

←60→



181 / 0.495 kWh 1

BlackSteel / black

201.5 / 59.7 / 67.5 1



Key features

- touch- & swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included

Controls

- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments


- PowerCooling with FreshAir activated
- charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves,
- of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe

Freezer compartment ****

- 3 drawers, VarioSpace
- · Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

• 2.4" TFT-colour display in-the-door, Vertical recessed handles

- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal




BioFresh NoFrost fridge-freezers BioFresh NoFrost fridge-freezer













- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- LED ceiling lighting
- · 2 BioFresh safes with telescopic partial pull-out, 2 Fruit & Vegetable safes,
- 2 FlexSystem

Freezer compartment *****

- 3 drawers. VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features


82

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front · Reversible door hinging, right
- Replaceable door seal



←60→

CBNsda 572i





- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe,
- 1 Meat & Dairy safe

Freezer compartment *****

- 3 drawers. VarioSpace
- · Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg Safety glass fittings

Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front · Reversible door hinging, right
- · Replaceable door seal







CBNsdc 573i

| Energy efficiency class: | C A 1 |
|--|--|
| Energy consumption year / 24 hrs: | 181 / 0.495 kWh ¹ |
| Total volume 2: | 360 l |
| Volume: Fridge: 158.8 l / BioFresh con | npartment: 98.9 l / Freezer compartment: 103 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SmartSteel/silver |
| Exterior dimensions in cm (h/w/d): | 201.5 / 59.7 / 67.5 1 |



Controls



SmartDeviceBox included

· Integrated bottle shelf

· LED ceiling lighting

1 Meat & Dairy safe

3 drawers, VarioSpace

Safety glass fittings

· Ice cube tray

Key features

Freezer compartment ****

- Temperature rise time: 20 h

Vertical recessed handles

· Height-adjustable feet at front

· Reversible door hinging, right

Replaceable door seal

Freezing capacity in 24 hrs: 10 kg

• Door alarm: visual and acoustic

Fridge and BioFresh compartments





• 2.4" TFT-colour display in-the-door, touch- & swipe

· Alarm in case of malfunction: visual and acoustic

· PowerCooling with FreshAir activated charcoal filter

· Plastic door shelves with bottle holder, egg tray, FlexCube

• 3 GlassLine storage shelves, of which 1 is divided into two parts

- Transport handles, front and at back, transport castors at back

• 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe,





- Digital temperature display for fridge, BioFresh and freezer compartments















Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Energy efficiency class:

Noise output/noise class:

Total volume 2:

Climate rating:

Door/side walls:

Energy consumption year / 24 hrs:

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe,
- 1 Meat & Dairy safe

Freezer compartment ****

- 3 drawers. VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- · Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front · Reversible door hinging, right
- Replaceable door seal

2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.








181 / 0.495 kWh 1

white/white





Volume: Fridge: 158.8 l/BioFresh compartment: 98.9 l/Freezer compartment: 103 l






















BioFresh NoFrost fridge-freezers BioFresh NoFrost fridge-freezer





←60→







- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- 1 BioFresh safe with telescopic partial pull-out, 1 Fruit & Vegetable safe

Freezer compartment *****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings


Kev features

84

- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal







←60→



- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- LED ceiling lighting
- 1 BioFresh safe with telescopic partial pull-out, 1 Fruit & Vegetable safe

Freezer compartment ****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

Colour/material options:

CBNc 5223 in white





CBNsdc 522i

| Energy efficiency class: | C A C |
|--|---|
| Energy consumption year / 24 hrs: | 170 / 0.465 kWh ¹ |
| Total volume ²: | 320 l |
| Volume: Fridge: 164.7 l/BioFresh compartr | nent: 52.9 l / Freezer compartment: 103 l |
| Noise output / noise class: | 31 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SmartSteel/silver |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |

Duo No Super Super Easy Super Touch Vario Cooling Frost Cool Frost Co Silent Display Space



Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED ceiling lighting
- 1 BioFresh safe with telescopic partial pull-out, 1 Fruit & Vegetable safe


Freezer compartment ****

- 3 drawers, VarioSpace
- · Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

Key features

- Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front · Reversible door hinging, right
- Replaceable door seal





Energy efficiency class: 109 / 0.298 kWh 1 Energy consumption year / 24 hrs: Total volume 2: Volume: Fridge: 164.7 l / BioFresh compartment: 52.9 l / Freezer compartment: 103 l Noise output/noise class: 34 dB(A) / B, SuperSilent SN-T (from +10 °C to +43 °C) Climate rating: BlackSteel / black Door/side walls: Exterior dimensions in cm (h/w/d): 185.5 / 59.7 / 67.5 1





Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf · LED ceiling lighting
- 1 BioFresh safe with telescopic partial pull-out, 1 Fruit & Vegetable safe

Freezer compartment ** * * *

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal





←60→

Freezer compartment *****

- IceMaker with fixed 3/4" water

- Ice cube production in 24 hrs: 1.2 kg

· Freezing capacity in 24 hrs: 10 kg

· Transport handles, front and at back,

3 drawers, VarioSpace

· Ice cube reservoir 5.4 kg

· Safety glass fittings


Key features

• Temperature rise time: 20 h

transport castors at back · Height-adjustable feet at front

· Replaceable door seal

· Reversible door hinging, right





Controls

• 2.4" TFT-colour display in-the-door, touch- & swipe

- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Alarm in case of malfunction; visual and acoustic
- Door alarm: visual and acoustic


Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- · 4 GlassLine storage shelves,
- of which 1 is divided into two parts
- VarioSafe


86

- Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails





←60→



Key features

· Vertical recessed handles


transport castors at back

· Replaceable door seal

· Height-adjustable feet at front

· Reversible door hinging, right

• Transport handles, front and at back,





Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- · Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
 - · Door alarm: visual and acoustic

Fridge compartment · Vertical recessed handles

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 5 GlassLine storage shelves, of which 1 is divided into two parts
- VarinSafe
- · Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment ****

- 3 drawers, VarioSpace
- · Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings





CNc 5724

←60→

| Energy efficiency class: | $\begin{pmatrix} C & A \\ f & G \end{pmatrix}^1$ |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 168 / 0.460 kWh ¹ |
| Total volume 2: | 359 l |
| Volume: | Fridge: 227.1 l / Freezer compartment: 132 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 201.5 / 59.7 / 67.5 1 |





Controls · LC monochrome display behind-the-door,

- touch electronic Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and
- acoustic · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- · 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarinSafe
- · Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment *****

- Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- 4 drawers, VarioSpace
- Safety glass fittings

Key features

- · Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

- LC monochrome display behind-the-door,

- touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 5 GlassLine storage shelves,
- of which 1 is divided into two parts
- VarioSafe
- · Bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment ****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Safety glass fittings







Controls



Key features


- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal


Colour/material options: CNsda 5723 with Stainless steel front

• Freezing capacity in 24 hrs: 10 kg



←60→





Key features

Vertical recessed handles

• Transport handles, front and at back,

· Height-adjustable feet at front

· Reversible door hinging, right



Controls

- · LC monochrome display behind-the-door, touch electronic
- freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and Replaceable door seal
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 5 GlassLine storage shelves,
- of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment *****


- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings



←60→

CNsfd 5704

| Energy efficiency class: | |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 210 / 0.575 kWh ¹ |
| Total volume ² : | 359 l |
| Volume: | Fridge: 227.1 l / Freezer compartment: 132 l |
| Noise output / noise class: | 35 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 201.5/59.7/67.5 1 |



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- 3-bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment ****

- · 4 drawers, VarioSpace
- · Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings


Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal





CNd 5704





















←60→



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments

CNsfd 5703

- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

Controls

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray
- 5 GlassLine storage shelves
- 3-bottle shelf
- LED ceiling lighting
- · 1 EasyFresh safe on running rails


Freezer compartment ****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

Colour / material options: CNd 5703 in white





- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- 3-bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment *****

- 4 drawers, VarioSpace
- · Temperature rise time: 20 h • Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- · Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

←60→

Fridge: 267.9 l / Freezer compartment: 103 l

203 / 0.556 kWh 1

35 dB(A) / B, SuperSilent

SteelFinish / silver

201.5 / 59.7 / 67.5 1


SN-T (from +10 °C to +43 °C)

371 l





←60→







Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment *****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

Kev features

90

- · Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal





| 128 / 0.350 kWh ¹ 330 l |
|---------------------------------------|
| 330 l |
| |
| er compartment: 103 l |
| IB(A) / B, SuperSilent |
| rom +10 °C to +43 °C) |
| SmartSteel / silver |
| 185.5 / 59.7 / 67.5 1 |
| - |



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment *****

- 3 drawers, VarioSpace
- · Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

Kev features

- Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←60→

CNsfd 5204

Energy efficiency class: 202 / 0.553 kWh ³ Energy consumption year / 24 hrs: Total volume 2: 319 l Volume: Fridge: 187.1 l / Freezer compartment: 132 l 35 dB(A) / B, SuperSilent Noise output / noise class: SN-T (from +10 °C to +43 °C) Climate rating: Door/side walls: SteelFinish/silver Exterior dimensions in cm (h/w/d): 185.5 / 59.7 / 67.5 1



Controls



· SmartDeviceBox: optional accessory

• Door alarm: visual and acoustic

- 3 GlassLine storage shelves

• 1 EasyFresh safe on running rails

Freezer compartment ****

· Temperature rise time: 20 h

Vertical recessed handles

Replaceable door seal

· Height-adjustable feet at front • Reversible door hinging, right

· Freezing capacity in 24 hrs: 10 kg

Fridge compartment

• 3-bottle shelf

LED ceiling lighting

4 drawers, VarioSpace

· Safety glass fittings

Key features





- LC monochrome display behind-the-door, touch electronic

- Alarm in case of malfunction: visual and acoustic

· PowerCooling with FreshAir activated charcoal filter

· Transport handles, front and at back, transport castors at back

- Plastic door shelves with bottle holder, egg tray

- Digital temperature display for fridge and freezer compartments















Energy efficiency class:

Noise output/noise class:

Total volume 2:

Climate rating:

Door/side walls:

Volume:

Energy consumption year / 24 hrs:





CNd 5204



Fridge: 187.1 l / Freezer compartment: 132 l



35 dB(A) / B, SuperSilent

SN-T (from +10 °C to +43 °C)



185.5 / 59.7 / 67.5 1

white/white



- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- 3-bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment *****

- 4 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- · Safety glass fittings

Key features

- Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal


←60→

202 / 0.553 kWh 1

319 l

←60→

























←60→







Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- 3-bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails

Freezer compartment *****

- 3 drawers, VarioSpace
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

92

- · Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←60→

CNd 5203

| Energy efficiency class: | |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 201/0.550 kWh ¹ |
| Total volume 2: | 330 l |
| Volume: | Fridge: 227.1 l / Freezer compartment: 103 l |
| Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 185.5/59.7/67.5 ¹ |

| side wall: | 8: | | | | | wh | ite/white |
|---------------|-------------|---------------|----------------|-----------------|------------------|----------------|--------------------------|
| r dimens | ons in cm (| h/w/d): | | | | 185.5/ | 59.7 / 67.5 ¹ |
| Duo Coolin | No Frost | Super Cool | Super Frost | Super Silent | Touch Display | Vario Space | Smart Device Ready |

- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- 3-bottle shelf
- LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment *****

- 3 drawers, VarioSpace
- · Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- · Vertical recessed handles
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



Replaceable door seal

Do you think the door seal on your Liebherr needs to be replaced after a few years? This is very easy to do yourself. The replaceable door seal can be removed in a few simple steps - and the new seal is just as easy to insert. As a result, this part of the refrigerator is always spotless and hygienically clean.



Recessed grip

Special and functional: You can open the appliance very easily using the vertically integrated and ergonomically fitted handle. Additionally, the modern and puristic design fits perfectly into your hands-free kitchen.



CNsfc 5023

| Energy efficiency class: | $\left(\begin{array}{c} A \\ C \end{array}\right)^{1}$ |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 153 / 0.419 kWh ¹ |
| Total volume 2: | 280 l |
| Volume: | Fridge: 177 l / Freezer compartment: 103 l |
| Noise output/noise class: | 35 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 165.5 / 59.7 / 67.5 ¹ |













←60→





- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- Bottle shelf
- LED ceiling lighting
- · 1 EasyFresh safe on running rails

Freezer compartment ****

- 3 drawers, VarioSpace
- · Ice cube tray
- · Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

- Vertical recessed handles
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.
You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.












←55→

| Energy effici | ency class: | Ę į |
|-------------------------|--------------------------------|------------------------------|
| Energy cons | umption year / 24 hrs: | 224 / 0.613 kWh ¹ |
| Total volume | 22: | 296 l |
| Volume: | Fridge: 212.4 l / Freez | er compartment: 84 l |
| Noise output | t/noise class: | 38 dB(A)/C |
| Climate ratir | ng: SN-ST (fi | rom +10 °C to +38 °C) |
| Door/side walls: Stain! | | ss steel look/silver |
| Exterior dim | ensions in cm (h/w/d): | 181.2/55/63 ¹ |

CUele 3331



Energy efficiency class: 192 / 0.526 kWh 1 Energy consumption year / 24 hrs: 192 / 0.526 kWh 1 Total volume 2: Volume: Fridge: 212.4 l / Freezer compartment: 54 l Noise output/noise class: 38 dB(A)/C Climate rating: SN-ST (from +10 °C to +38 °C) Door/side walls: FrozenBlue / FrozenBlue Exterior dimensions in cm (h/w/d): 161.2 / 55 / 63 1



Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- · Bottle shelf · LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- · Recessed handles
- Versatile installation due to front ventilation
- · Transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right



Energy efficiency class:

Energy consumption year / 24 hrs:

Controls

- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- · LED lighting
- 2 fruit and vegetable drawers

Freezer compartment *****

- 2 drawers, VarioSpace
- · Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg - Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- Transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right



Controls

- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- · LED lighting
- 2 fruit and vegetable drawers

Freezer compartment *****

- 2 drawers, VarioSpace
- · Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Transport castors at back
- · Height-adjustable feet at front - Reversible door hinging, right

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. 2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and









CUele 2331

←55→

CUe 2331

←55→

| Energy cons | umption year / 24 hrs: | 192 / 0.526 kWh ¹ |
|--------------|--------------------------|------------------------------|
| Total volume | . , . | 265 l |
| Volume: | Fridge: 212.4 l / Freeze | r compartment: 54 l |
| Noise outpu | t/noise class: | 38 dB(A)/C |
| Climate rati | ng: SN-ST (fro | om +10 °C to +38 °C) |
| Door/side v | valls: | white/white |
| Evtorior dim | ensions in cm (h/w/d): | 161.2 / 55 / 63 1 |



Space

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment


- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelfLED lighting
- 2 fruit and vegetable drawers

Freezer compartment *****

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- · SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right





Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment


- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment *****

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- · Recessed handles
- Versatile installation due to front ventilation
- Transport castors at back
- Height-adjustable feet at front
- · Reversible door hinging, right







Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and

SmartFrost Top Mount fridge-freezers SmartFrost Top Mount fridge-freezers







- 55 →



←55→

CTele 2931

| Energy effici | ency class: | E |
|----------------------------------|------------------------------|-------------------------------|
| Energy consu | umption year / 24 hrs: | 190 / 0.520 kWh ¹ |
| Total volume | 2: | 270 l |
| Volume: | Fridge: 218.6 l / Fre | ezer compartment: 52 l |
| Noise output | /noise class: | 37 dB(A)/C |
| Climate ratin | g: SN-T | (from +10 °C to +43 °C) |
| Door/side w | alls: Stai | nless steel look/silver |
| Exterior dimensions in cm (h/w/d | |): 157.1/55/63 ¹ |



- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- · LED lighting
- 1 spacious fruit and vegetable drawer


Freezer compartment *****


- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 2.5 kg
- · Safety glass fittings

Key features

98

- SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- · Height-adjustable feet at front
- · Reversible door hinging, right





Controls

- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment


- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer


Freezer compartment *****

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 20 h
- · Freezing capacity in 24 hrs: 2.5 kg
- · Safety glass fittings

Key features

- · SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- · Height-adjustable feet at front
- · Reversible door hinging, right







Controls

- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment *****

- · 4-star freezer compartment
- · Ice cube tray
- · Temperature rise time: 17 h
- · Freezing capacity in 24 hrs: 2.5 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- · Height-adjustable feet at front
- · Reversible door hinging, right











← 55 →

CTe 2531

| Energy efficiency class: | E A G |
|------------------------------------|---------------------|
| Energy consumption year / 24 hrs: | 181/0.495 kWh |
| Total volume 2: | 233 |
| Volume: Fridge: 189.5 l / Freez | er compartment: 44 |
| Noise output/noise class: | 37 dB(A)/(|
| Climate rating: SN-T (fr | om +10 °C to +43 °C |
| Door/side walls: | white / white |
| Exterior dimensions in cm (h/w/d): | 140.1/55/63 |

| E A T | En |
|--------------------------|-----|
| / 0.495 kWh ¹ | En |
| 233 l | Tot |
| oartment: 44 l | Vo |
| 37 dB(A)/C | No |
| °C to +43°C) | Cli |
| white/white | Do |
| 0.1/55/631 | Ex |
| | |

ergy efficiency class: 181 / 0.495 kWh 1 nergy consumption year / 24 hrs: tal volume 2: 196 l lume: Fridge: 152.2 l / Freezer compartment: 44 l 37 dB(A)/C oise output/noise class: SN-T (from +10 °C to +43 °C) imate rating: oor/side walls: Stainless steel look / silver terior dimensions in cm (h/w/d): 124.1/55/631

| Energy effici | ency class: | EA |
|---------------|--------------------------------|------------------------------|
| Energy cons | umption year/24 hrs: | 181/0.495 kWh ³ |
| Total volume | 22: | 196 (|
| Volume: | Fridge: 152.2 l / Freez | zer compartment: 44 l |
| Noise output | t/noise class: | 37 dB(A)/C |
| Climate ratir | ng: SN-T (f | rom +10 °C to +43 °C) |
| Door/side w | valls: | white/white |
| Exterior dim | ensions in cm (h/w/d): | 124.1/55/63 |
| | | |

CTe 2131



- · Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- · LED lighting

Controls

• 1 spacious fruit and vegetable drawer

Freezer compartment *****

- 4-star freezer compartment
- · Ice cube tray
- Temperature rise time: 17 h
- · Freezing capacity in 24 hrs: 2.5 kg
- · Safety glass fittings

Key features

- · SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging, right



Controls

- · Mechanical control in interior, control dial
- · Individually regulated cooling circuits: 1


Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- · 1 spacious fruit and vegetable drawer

Freezer compartment *****

- · 4-star freezer compartment
- · Ice cube tray
- Temperature rise time: 17 h • Freezing capacity in 24 hrs: 2.5 kg
- · Safety glass fittings

- **Key features** - SwingLine design
- Recessed handles
- · Versatile installation due to front ventilation
- · Height-adjustable feet at front
- · Reversible door hinging, right





Controls


- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves LED lighting
- 1 spacious fruit and vegetable drawer
- Freezer compartment **** · 4-star freezer compartment
- · Ice cube tray
- Temperature rise time: 17 h • Freezing capacity in 24 hrs: 2.5 kg
- · Safety glass fittings

Key features

- SwingLine design
- Recessed handles - Versatile installation due to front ventilation
- · Height-adjustable feet at front
- Reversible door hinging, right



2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



Range overview by device height and series

| Prime seriesPlus seriesPure series | | -60→ 185 | ←60→ 165 | ←60→ 145 145 | ←60 → 125 ↓ |
|--|-------------------|--|--------------|----------------|--------------|
| Fridges | | | | | |
| BioFresh Full-space BioFresh | | RBsdc 525i RBc 525i RBsfd 5221 RBc 5220 | | | Rba30 425i |
| EasyFresh | | Rsfd 5220 | | | 113400 4231 |
| | | Rd 5220 | | | |
| | | | Rsfd 5000 | | |
| | | | Rd 5000 | | |
| | | | | Rsfd 4600 | |
| | | | | Rd 4600 | D.I. (200 |
| | | | | | Rd 4200 |
| | | | ←60 → | ←55 → | ←50 → |
| | | | 85 ↓ | 85 ↓ | 85 ↓ |
| | Under counter fri | dges | | | |
| | EasyFresh | | Rsdci 1621 | | |
| | | | Rci 1621 | | |
| | | | Rsdci 1620 | | |
| | | | Rdi 1621 | | |
| | | | Rci 1620 | | |
| | | | Rdi 1620 | Rc 1400 | Rd 1200 |
| | | | | Rc 1400 | Nu 1200 |
| | | | | Rd 1400 | Rd 1201 |
| | | | | | |
| | | | | Rd 1401 | Re 1200 |
| | | | | | |



Series

104

Fridges







♦ Plus series



O Prime series

| | Pure series | \Diamond Plus series | Prime series | |
|----------------------------------|---|---|---|--|
| Freshness technology | EasyFresh on integrated drawer guide | EasyFresh on integrated drawer guide | EasyFresh on telescopic rails | |
| | | BioFresh on telescopic rails | BioFresh with SoftTelescopic | |
| | FreshAir filter | FreshAir filter | FreshAir filter | |
| Comfort and flexibility | | Divisible glass shelf | Divisible glass shelf | |
| | | | SoftSystem soft closing mechanism | |
| | | VarioSafe | VarioSafe | |
| | | | VarioBoxes | |
| | | | Butter dish | |
| | Egg tray | Egg tray | Adjustable egg tray | |
| | Bottle shelf | Bottle shelf | Bottle shelf | |
| Design | Ceiling lighting | Ceiling or side lighting | LightTower | |
| | | | Lighting BioFresh safe | |
| | | | SmartSteel rear wall | |
| | Transparent glass | Transparent glass | Satin finish glass | |
| | Stainless steel look shelves | Stainless steel look shelves | Glass & stainless steel rack | |
| | Touch display | Touch display | Touch & Swipe display | |
| | Display behind the door | Display behind the door | Display behind the door | |
| | Recessed grip | Recessed grip | Slimline door handle with opening mechanism | |
| Connectivity (SmartDeviceBox) | Can be retrofitted | Can be retrofitted | Can be retrofitted | |

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

Quality in every detail



Fruit & Vegetable safe

Crunchy salad and strawberries: the most delicate foods deserve a special place so they stay fresh longer – in BioFresh safes. In the Fruit & Vegetable safe the temperature is close to 0°C. Combined here with the constant humidity, thanks to the air-tight closure, unpackaged fruit and vegetables feel particularly at home. You do not have to adjust anything.



3 bottle shelf

Now your bottles stay where they should. The 3 bottle shelf securely holds three bottles in your fridge ready to be used. The bottle shelf fits on every glass shelf and is therefore very flexible. And if you need the space for other reasons, simply take the bottle shelf out of the fridge.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresher for longer.



LED side lighting, single sided

For a quick overview of everything in the refrigerator: the LED side lighting helps you to keep your food in view. The LEDs are positioned so that the light beams go up and down. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.



LightTower

Enjoy an optimally illuminated interior: the LightTower shows off the food in its best light and is positioned so that all of your filled fridge is illuminated at all times. The flush mounting of the LightTower in the side walls means there is also more space for your food.



Door hinge exchange, integrated freezer compartment

Switch the opening direction on your 4* freezer compartment door quickly and easily: The clever slide control means this can be done in seconds and without any manual skills. Simply slide the control on the 4*freezer compartment right or left – that's it, done.



Slimline door handle with integrated opening mechanism

Opening made easy: The practical and elegant slimline door handle with an integrated opening mechanism allows you to open the appliance door effortlessly, even when it's opened multiple times in quick succession. The classy, minimalistic handles are also an eye-catcher on your appliance.



Door shelf

Do you want a safe storage area for your drinks or food? And do you still want to reach them easily? Our height-adjustable door shelves offer you both – thanks to the safety glass shelves and stainless steel rails. The sliding and removable bottle holder also ensures that your bottles are held securely.



Bottle shelf above the BioFresh safe

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



SoftTelescopic

Look forward to opening your BioFresh safes. And this is not just because of the fresh food – but also because opening is so easy, and closing is cushioned. The telescopic rails slide the safe gently towards you. And because these extend fully, you have the best overview of the contents.



FlexSystem

Small and delicate fruit in the refrigerator can easily roll out of sight or become crushed. That's why your Liebherr comes with the FlexSystem. Two flexibly positionable boxes in the BioFresh safe ensure everything is clearly arranged and organised. And they also safely protect even the smallest raspberry from bruising or from being mixed up with other foods.



Space for baking tray

Do you want to keep that home-baked fruit pie fresh? Or maybe a prepared pizza to be baked later on? If so, simply slide your baking tray into your Liebherr – it has plenty of space. Really convenient – you can slide the baking tray in and out when the door is opened at 90°.

107

The features shown are model dependent; look for these features in your model choice.

BioFresh fridges BioFresh fridges







RBsdc 525i

Energy efficiency class: 108 / 0.295 kWh 1 Energy consumption year / 24 hrs: Total volume 2: Volume: Fridge: 245.8 l / BioFresh compartment: 140.9 l Noise output / noise class: 33 dB(A) / B, SuperSilent SN-T (from +10 °C to +43 °C) Climate rating: SmartSteel/silver Door/side walls: 185.5 / 59.7 / 67.5 1 Exterior dimensions in cm (h/w/d):





- · 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceRox included
- · Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- LED BioFresh lighting
- 3 BioFresh safes with SoftTelescopic, 2 Fruit & Vegetable safes, 1 Meat & Dairy safe

108


- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel



←60→



RBc 525i































- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- · Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- · Premium GlassLine storage shelves with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- · Integrated bottle shelf
- · LED light panel, both sides
- · LED BioFresh lighting
- 3 BioFresh safes with SoftTelescopic, 2 Fruit & Vegetable safes, 1 Meat & Dairy safe

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal
- Dry rear wall in stainless steel with SmartSteel







RBsfd 5221

| Energy effi | ciency class: | D A T |
|--------------|----------------------------------|--|
| Energy con | sumption year / 24 hrs: | 164 / 0.449 kWh ¹ |
| Total volum | ne²: | 351 l |
| Volume: | Fridge: 223 l / BioFresh compart | ment: 93.9 l / Freezer compartment: 34 l |
| Noise outp | ut/noise class: | 35 dB(A) / B, SuperSilent |
| Climate rat | ing: | SN-T (from +10 °C to +43 °C) |
| Door/side | walls: | SteelFinish/silver |
| Exterior din | nensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 ¹ |













- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- · SmartDeviceBox: optional accessory
- · Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- · Integrated bottle shelf
- · LED light one-sided
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe

Freezer compartment ****

- · 4-star freezer compartment, reversible door hinging
- · Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 5 kg

Key features

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→



RBc 5220

| Energy efficiency class: | C A 1 |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 101 / 0.276 kWh ¹ |
| Total volume ² : | 382 l |
| Volume: | Fridge: 288.7 l / BioFresh compartment: 93.7 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 185.5 / 59.7 / 67.5 1 |











- LC monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts VarioSafe
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh safes with telescopic partial pull-out, 1 Fruit & Vegetable safe, 1 Meat & Dairy safe

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal





BioFresh

BioFresh guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.



LED lighting

The LED lighting ensures your BioFresh safes are pleasantly lit. This makes it even easier for you to find the food you want. The energy-efficient LED unit is elegantly positioned above the safes to save space.



←60→



RBa30 425i

| Energy efficiency class: | A G |
|------------------------------------|----------------------------------|
| Energy consumption year / 24 hrs: | 65 / 0.178 kWh ¹ |
| Total volume ² : | 160 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 125.5 / 59.7 / 67.5 ¹ |









- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- · LED BioFresh lighting
- 4 BioFresh safes on integrated drawer guide

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.


You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

EasyFresh fridges EasyFresh fridges



←60→







Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features


112

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



←60→

Rd 5220















Controls

- LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 6 GlassLine storage shelves, of which 1 is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting
- 1 EasyFresh safe on running rails
- 1 spacious fruit and vegetable drawer

Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal





Rsfd 5000

| Energy efficiency class: | |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 93 / 0.254 kWh ¹ |
| Total volume ² : | 348 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SteelFinish/silver |
| Exterior dimensions in cm (h/w/d): | 165.5 / 59.7 / 67.5 ¹ |







Controls

- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray
- 7 GlassLine storage shelves
- 3-bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails

Key features

- · Vertical recessed handle
- $\boldsymbol{\cdot}$ Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→



Rd 5000

Energy efficiency class: 93 / 0.254 kWh ¹ Energy consumption year / 24 hrs: Total volume 2: 348 l 37 dB(A)/C Noise output/noise class: Climate rating: SN-T (from +10 °C to +43 °C) Door/side walls: white / white Exterior dimensions in cm (h/w/d): 165.5 / 59.7 / 67.5 1







Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray
- 7 GlassLine storage shelves
- 3-bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails


- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

EasyFresh fridges EasyFresh fridge and fridge



←60→







Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray
- 6 GlassLine storage shelves
- 3-bottle shelf
- · LED ceiling lighting
- 1 EasyFresh safe on running rails

Key features

114


- · Vertical recessed handle
- $\boldsymbol{\cdot}$ Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→



Rd 4600







- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder, egg tray
- 6 GlassLine storage shelves
- 3-bottle shelf
- · LED ceiling lighting
- · 1 EasyFresh safe on running rails

Key features

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal






Rd 4200

84 / 0.230 kWh ³ 247 l 37 dB(A)/C Volume: SN-T (from +10 °C to +43 °C) white/white Exterior dimensions in cm (h/w/d): 125.5/59.7/67.51





←55→





K 2340

←55→

Energy efficiency class: 101 / 0.276 kWh 1 Energy consumption year / 24 hrs: Total volume 2: 213 l Noise output / noise class: 38 dB(A)/C SN-ST (from +10 °C to +38 °C) Climate rating: Door/side walls: white / white 114/55/631 Exterior dimensions in cm (h/w/d):

Comfort

Controls

- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display

Energy efficiency class:

Noise output / noise class:

Total volume 2:

Climate rating:

Door / side walls:

Energy consumption year / 24 hrs:

- · SmartDeviceBox: optional accessory
- · Door alarm: visual and acoustic

Fridge compartment

- · PowerCooling with FreshAir activated charcoal filter
- · Plastic door shelves with bottle holder, egg tray
- 5 GlassLine storage shelves
- 3-bottle shelf · LED ceiling lighting
- 1 EasyFresh safe on running rails

Key features

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

Controls

- · Mechanical control in interior, control dial
- · CoolPlus function

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves - Bottle shelf
- LED lighting
- · 2 fruit and vegetable drawers

Freezer compartment *****

- 4-star freezer compartment, reversible door hinging
- · Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 4.5 kg

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- · Versatile installation due to front ventilation
- · Transport handles at back, transport castors at back
- · Height-adjustable feet at front · Reversible door hinging, right
- Colour/material options:

Ke 2834 in white

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 5 GlassLine storage shelves

- 2 fruit and vegetable drawers

- · Bottle shelf LED lighting
- Key features

- SwingLine design

- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right

Under counter fridges Rsdci 1621 ♦ Plus series

Quality in every detail



DoorStop

Keep your Liebherr fresh and odor-free with our retractable DoorStop.
Prevents odors by keeping the door open when not in use. Save time and energy.



LED side lighting

The LED side lighting illuminates the interior from the side – providing a good overview of your food. Another highlight: the LEDs are positioned in front of the glass shelves so that even a full refrigerator is well lit.



EasyFresh safe

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



Slimline door handle with integrated opening mechanism

The sturdy, secure handles have an elegant, premium quality appearance and feature an integrated opening mechanism, which allows convenient and effortless door opening.



Height-adjustable inner door shelves

Use all of the space in your Liebherr – and entirely to suit your requirements. The height adjustable inner door shelves will help with this: These allow you to change the height at which the shelves are mounted quickly and easily at any time – which means they can be used entirely flexibly and securely for storing a wide range of containers and foodstuffs.




TouchControl

A gentle finger tap and you set your Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple – and efficient, as the sleek button is integrated into the interior, creating more space for all your fresh goods.



←60→

Rsdci 1621





Controls

- · TouchControl in the interior, touch electronic
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf
- LED lighting
- 1 EasyFresh safe

Freezer compartment *****

- Hinged 4-star freezer compartment door
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

118

- Slimline handle with integrated opening mechanism
- Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→

Rci 1621

| Energy efficiency class: | $\begin{pmatrix} C & A \\ f & G \end{pmatrix}^1$ |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 95 / 0.260 kWh ¹ |
| Total volume ² : | 125 l |
| Volume: | Fridge: 109.2 l / Freezer compartment: 17 l |
| Noise output/noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/60/60.7 ¹ |















Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf
- LED lighting
- 1 EasyFresh safe

Freezer compartment *****


- · Hinged 4-star freezer compartment door
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal





















Controls

- · TouchControl in the interior, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 3 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf
- LED lighting
- 1 EasyFresh safe

Freezer compartment ****

- · Hinged 4-star freezer compartment door
- Temperature rise time: 10 h
- · Freezing capacity in 24 hrs: 2 kg

Key features

- · Slimline handle with integrated opening mechanism
- Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



-60→

Rsdci 1620

| Energy efficiency class: | C A 1 |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 59 / 0.161 kWh ¹ |
| Total volume ² : | 141 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | SmartSteel/silver |
| Exterior dimensions in cm (h/w/d): | 85/60/60.71 |
| | |















- TouchControl in the interior, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder, egg tray, FlexCube
- · 4 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf
- LED lighting
- 1 EasyFresh safe

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



Rci 1620

Energy efficiency class: 59 / 0.161 kWh 1 Energy consumption year / 24 hrs: Total volume 2: 141 l 34 dB(A) / B, SuperSilent Noise output / noise class: Climate rating: SN-T (from +10 °C to +43 °C) Door/side walls: white/white Exterior dimensions in cm (h/w/d): 85/60/60.71



Controls

- · TouchControl in the interior, touch electronic
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder, egg tray, FlexCube
- · 4 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf LED lighting
- 1 EasyFresh safe

Key features

120

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



Rdi 1620

| Energy efficiency class: | D A t |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 73 / 0.200 kWh |
| Total volume ² : | 141 |
| Noise output / noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/60/60.7 |
| | |



- · TouchControl in the interior, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment


- · Plastic door shelves with bottle holder, egg tray, FlexCube
- 4 GlassLine storage shelves, of which 1 is divided into two parts
- 3-bottle shelf
- LED lighting
- 1 EasyFresh safe

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



Rc 1401















Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- · 1 fruit and vegetable drawer

Freezer compartment ****

- · Hinged 4-star freezer compartment door
- Temperature rise time: 10 h
- · Freezing capacity in 24 hrs: 2 kg

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



Rd 1400

| Energy efficiency class: | |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 72 / 0.197 kWh ¹ |
| Total volume ² : | 125 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/55/60.71 |









Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment


- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED lighting
- · 1 fruit and vegetable drawer

Key features

- · Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal

Colour/material options:

Rc 1400 in white



Energy consumption year/24 hrs: 58/0.158 kWh



TouchControl

A gentle finger tap and you set your Liebherr to 3, 5, 7 or 9°C with TouchControl. So simple – and efficient, as the sleek button is integrated into the interior, creating more space for all your fresh goods.



Slimline door handle with integrated opening mechanism

122

The sturdy, secure handles have an elegant, premium quality appearance and feature an integrated opening mechanism, which allows convenient and effortless door opening.



←55→

Rd 1401

| Energy efficiency class: | |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 114 / 0.312 kWh ¹ |
| Total volume 2: | 111 (|
| Volume: | Fridge: 96.9 l / Freezer compartment: 15 l |
| Noise output / noise class: | 35 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/55/60.71 |
| | |















- · TouchControl in the interior, touch electronic
- Digital temperature display
- · Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- 1 fruit and vegetable drawer

Freezer compartment *****

- · Hinged 4-star freezer compartment door
- · Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



Re 1401

Energy efficiency class: 142 / 0.389 kWh ¹ Energy consumption year / 24 hrs: Total volume 2: Fridge: 96.9 l / Freezer compartment: 15 l Volume: 37 dB(A)/C Noise output / noise class: SN-T (from +10 °C to +43 °C) Climate rating: white/white Door/side walls: 85/55/60.7¹ Exterior dimensions in cm (h/w/d):









Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment


- · Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- · 1 fruit and vegetable drawer

Freezer compartment ****

- · Hinged 4-star freezer compartment door
- Temperature rise time: 10 h
- · Freezing capacity in 24 hrs: 2 kg

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Replaceable door seal





Re 1400

Energy efficiency class: 90 / 0.246 kWh 1 Energy consumption year / 24 hrs: Total volume 2: Noise output/noise class: 35 dB(A) / B, SuperSilent Climate rating: SN-T (from +10 °C to +43 °C) Door/side walls: white/white Exterior dimensions in cm (h/w/d): 85/55/60.71











- TouchControl in the interior, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment


- · Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED lighting
- · 1 fruit and vegetable drawer

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



←50→

Rd 1201







- · TouchControl in the interior, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- · 1 fruit and vegetable drawer

Freezer compartment *****

- Hinged 4-star freezer compartment door
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 2 kg

Key features

124

- Recessed handle
- · Height-adjustable feet at front · Reversible door hinging, right
- · Replaceable door seal



←50→

Rsve 1201

| Energy efficiency class: | E A 1 |
|------------------------------------|--|
| Energy consumption year / 24 hrs: | 138 / 0.378 kWh ¹ |
| Total volume ² : | 98 l |
| Volume: | Fridge: 85.2 l / Freezer compartment: 13 l |
| Noise output/noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door / side walls: | silver/silver |
| Exterior dimensions in cm (h/w/d): | 85/50/60.7 ¹ |









Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- 1 fruit and vegetable drawer

Freezer compartment *****

- · Hinged 4-star freezer compartment door
- · Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Recessed handle
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←50→

138 / 0.378 kWh ¹

SN-T (from +10 °C to +43 °C)

37 dB(A)/C

white/white

85/50/60.71

Controls

• TouchControl in the interior, touch electronic

- Alarm in case of malfunction: visual and acoustic

- Plastic door shelves with bottle holder, egg tray

· Digital temperature display

• 4 GlassLine storage shelves

• 1 fruit and vegetable drawer

Fridge compartment

· LED lighting

Key features

- Door alarm: visual and acoustic



Rd 1200

←50→



←50→

Re 1200

| Energy efficiency class: | D A 1 | Energy efficiency class: | E A 1 |
|--------------------------------|---------------------------------------|------------------------------|---------------------------------------|
| Energy consumption year / 24 h | nrs: 71/0.194 kWh ¹ | Energy consumption year / 2 | 4 hrs: 88/0.241 kWh ¹ |
| Total volume 2: | 110 l | Total volume 2: | 110 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent | Noise output / noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) | Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | white/white | Door/side walls: | white/white |
| Exterior dimensions in cm (h/v | w/d): 85/50/60.7 1 | Exterior dimensions in cm (h | /w/d): 85/50/60.7 ¹ |



Fridge: 85.2 l / Freezer compartment: 13 l







Controls

- TouchControl in the interior, touch electronic
- · Digital temperature display

Energy efficiency class:

Noise output / noise class:

Total volume 2:

Climate rating:

Door/side walls:

Volume:

Energy consumption year / 24 hrs:

Exterior dimensions in cm (h/w/d):

- Alarm in case of malfunction: visual and acoustic
- · Door alarm: visual and acoustic

Fridge compartment

- · Plastic door shelves with bottle holder, egg tray
- 2 GlassLine storage shelves
- · LED lighting
- · 1 fruit and vegetable drawer

Freezer compartment ****

- · Hinged 4-star freezer compartment door
- · Temperature rise time: 8 h
- · Freezing capacity in 24 hrs: 2 kg

- Recessed handle
- · Height-adjustable feet at front
- · Reversible door hinging, right · Replaceable door seal
- Key features

· Recessed handle · Height-adjustable feet at front

- · Reversible door hinging, right
- Replaceable door seal





Controls

- TouchControl in the interior, touch electronic
- Digital temperature display
 - Alarm in case of malfunction: visual and acoustic
 - Door alarm: visual and acoustic


Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- · LED lighting
- 1 fruit and vegetable drawer

- · Recessed handle
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



Range overview by device height and series



Fsve 1404



Series

Freezers







 \Diamond Plus series



○ Prime series



 \triangle Peak series

| | O Pure series | \Diamond Plus series | Prime series | riangle Peak series |
|----------------------------------|----------------------------|--|--|--|
| Freshness technology | NoFrost | NoFrost | NoFrost | NoFrost |
| Comfort and flexibility | EasyOpen | EasyOpen | EasyOpen EasyOpen | EasyOpen |
| | FrostProtect | FrostProtect | FrostProtect | FrostProtect |
| | Tipping drawer | Tipping drawer | Tipping drawer | Tipping drawer |
| | | | | SoftSystem soft closing mechanism for SBS-capable models |
| | SpaceBox | SpaceBox | SpaceBox | SpaceBox |
| | Integrated drawer guide | Integrated drawer guide | Integrated drawer guide | Drawers guided on telescopic rails |
| | | Ice cube tray | Ice cube tray with lid for SBS-capable models | |
| | | Freezer tray | Freezer tray | Freezer tray |
| | | | 2 cold storage accumulators | 2 cold storage accumulators |
| | VarioSpace | VarioSpace | VarioSpace | VarioSpace |
| Design | | | Status light | Status light |
| | | | Freezer compartment lighting | Freezer compartment lighting |
| | | _ | | IceMaker lighting |
| | Touch display | Touch display | Touch & Swipe display | Touch & Swipe display |
| | Display behind the door | Display behind the door | Display behind the door | Display behind the door |
| | Recessed grip | Recessed grip | Slimline door handle with opening mechanism | Slimline door handle with opening mechanism |
| Connectivity (SmartDeviceBox) | Can be retrofitted | Can be retrofitted | Can be retrofitted or is included with "i" models | Can be retrofitted or is included with "i" models |
| Ice | | EasyTwist-Ice or IceTower for SBS-capable models | EasyTwist-Ice or IceTower for SBS-capable models | EasyTwist-Ice or IceTower |
| | | Ice cube tray for SBS-capable models | Ice cube tray for SBS-capable models | Ice cube tray for SBS-capable models |

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

Quality in every detail



NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



IceTower

You will never run out of cold drinks at your party. The IceTower, which holds 8 kg of ice cubes, makes sure of that. The ice cube scoop and the pull-out tray on telescopic rails allow easy access to the ice cubes. An extra insert tray means you can also store less ice and make room for frozen food underneath. The adjacent drawer provides storage space for frozen goods.



SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean offering additional capacity. Freezer drawers and glass shelves made of safety glass can be removed easily.



Touch & Swipe display

Control of your Liebherr at your fingertips: thanks to the Touch & Swipe display, you can operate your freezer intuitively and with ease. Simply select functions such as SuperFrost on the colour display by tapping and swiping. The temperature is controlled just as easily. And, what if you are not actively using the display? It then shows you the actual temperature.



Status display

You want to check that everything is OK with your appliance? The status display on the appliance door lets you know very quickly, visually and audibly. A blue light indicates: everything is OK. If the status is anything but OK, the display lights up red and flashes. A warning tone also sounds.



LED freezer compartment lighting

When you open the drawers in your Liebherr freezer, not only are you welcomed by the sight of your food, but also by the attractive lighting. This is provided by powerful, long-life, environmentally-friendly LEDs. The lighting makes it even easier to see all of the contents and is also a unique design element.



FrostProtect

Not all freezers are fitted in heated rooms. Some are located in cold garages or sheds. It's good then that your Liebherr is ideally set up for such a cool environment because all components are designed to operate in ambient temperatures as low as -15 °C.



Cold storage accumulator

The cold storage accumulators are doubly useful - both indoors and outdoors. Inside the freezer, they keep the frozen food cold for a period should there be a power failure. And they are on hand to chill your food and drinks when you're on outings.



SpaceBox

Accommodate the "big stuff" in your Liebherr: An XL turkey or a multi-layered ice cream cake simply needs more space. Your Liebherr has the SpaceBox for exactly that purpose: At a generous height of 250 mm, it offers lots of extra space, even for large frozen goods. Helpful for you when storing food flexibly.



EasyTwist-Ice

Whether it's a summer day or a party: Thanks to EasyTwist-Ice, you can prepare a supply of ice cubes quickly and easily – without the need for a fixed water connection. Simply fill the tank with water, let it freeze and then release the finished ice cubes with a simple twist – and you're ready to serve cool drinks. The EasyTwist-Ice is easy to clean and ensures hygienic ice cube production at all times.



Ice cube scoop

The Liebherr ice scoop makes portioning and transporting of ice easy. Thanks to the slanted tip and the ergonomic handle, ice cubes can make it from your IceTower into your drinks quickly and easily. The robust ice scoop made of sturdy plastic is also pleasing to the eye thanks to its satin surface in transparent glacier green.



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party?

No problem for your Liebherr freezer:

Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.

The features shown are model dependent; look for these features in your model choice.



NoFrost

When you open your freezer, you want to see frozen food - and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things - and saving money.



VarioSpace

134

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



←70 →



FNc 7227

| Energy efficiency class: | $\left(\begin{array}{c} A \\ f \\ G \end{array}\right)^1$ |
|--|---|
| Energy consumption year / 24 hrs: | 178 / 0.487 kWh ¹ |
| Total volume 2: | 363 l |
| Noise output / noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 185.5 / 69.7 / 76 1 |

















- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers on integrated drawer guide, VarioSpace
- · Top drawer with convenient tilting function
- · Ice cube tray
- · Temperature rise time: 19 h
- · Freezing capacity in 24 hrs: 19 kg


Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal





FNc 707i





Controls



























←70 →


- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ****

- 6 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- · Top drawer with convenient tilting function
- LED lighting
- Status indicator
- · Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg
- 2 cold storage accumulators
- · Safety glass fittings

Key features

- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



Controls

- · LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ****

- 6 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg


- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←70→



FNd 7026



















Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 6 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg

Key features

136

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←70→

FNc 667i

| Energy efficiency class: | C A 1 |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 155 / 0.424 kWh ¹ |
| Total volume ² : | 260 l |
| Noise output/noise class: | 34 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 145.5 / 69.7 / 76 1 |



- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 5 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- · LED lighting
- · Status indicator
- · Temperature rise time: 18 h
- · Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- · Safety glass fittings

Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



The FNa 6625: the first in its class.

Our 146-cm-tall freezer is rated as energy efficiency class A, the best that is currently available on the market. High-quality vacuum insulation panels with silica (silicic acid), sophisticated electronics and a powerful compressor make it more energy-efficient than any other appliance with conventional insulation. Its NoFrost technology and five drawers ensure long-term freshness and plenty of freezer space.



VarioSpace

Want to store a multi-layer ice cream cake safely until the summer party? No problem for your Liebherr freezer: Sometimes you just need more space and it's prepared for just that. With VarioSpace you can remove individual freezer drawers and the horizontal glass dividers below them, and hey presto, you have an extra large storage space.



←70 →



FNa 6625

| Energy efficiency class: | A A T |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 99 / 0.271 kWh ¹ |
| Total volume ² : | 260 l |
| Noise output/noise class: | 33 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 145.5 / 69.7 / 76 1 |

















Controls

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 5 drawers on integrated drawer guide, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 17 kg


- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→



FNsdd 529i







· 2.4" TFT-colour display behind-the-door, touch- & swipe

- Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers, of which 3 with telescopic partial pull-out, VarioSpace
- Top drawer with convenient tilting function
- IceTower

Controls

- · IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 8 kg
- LED lighting
- · Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- · Safety glass fittings

Kev features


138

- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



←60→

FNc 527i





- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers, of which 5 with telescopic partial pull-out, VarioSpace
- · Top drawer with convenient tilting function
- LED lighting
- · Status indicator
- · Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- · Safety glass fittings


Key features

- · Slimline handle with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal





FNd 525i





Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 7 drawers on integrated drawer guide, VarioSpace
- · Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators

Key features

- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal





FNd 522i

Designed to operate in ambient temperatures: as low as -15°C

Exterior dimensions in cm (h/w/d): 185.5/59.7/67.5 ¹

199 / 0.545 kWh 1

SN-T (from +10 °C to +43 °C)

277 l

36 dB(A)/C

white/white

Energy efficiency class:

Noise output / noise class:

Total volume 2:

Climate rating:

Door / side walls:

Controls

· Digital temperature display

- SmartDeviceBox included

• Door alarm: visual and acoustic

Freezer compartment ****

• Temperature rise time: 16 h

· Vertical recessed handle

· Height-adjustable feet at front

· Reversible door hinging, right

· Replaceable door seal

• Freezing capacity in 24 hrs: 18 kg

Ice cube tray

Key features

at hack

· Alarm in case of malfunction: visual and acoustic

- 7 drawers on integrated drawer guide, VarioSpace

- Transport handles, front and at back, transport castors

• Top drawer with convenient tilting function

Energy consumption year / 24 hrs:







FNe 5207

←60→

Energy efficiency class: Energy consumption year / 24 hrs: 249 / 0.682 kWh 1 Total volume 2: 277 l Noise output / noise class: 36 dB(A)/C SN-T (from +10 °C to +43 °C) Climate rating: Designed to operate in ambient temperatures: as low as -15°C Door/side walls: white / white Exterior dimensions in cm (h/w/d): $185.5/59.7/67.5^{-1}$









Controls

- LC monochrome display behind-the-door, touch electronic • LC monochrome display behind-the-door, touch electronic
 - Digital temperature display

 - · SmartDeviceBox: optional accessory - Alarm in case of malfunction: visual and acoustic
 - Door alarm: visual and acoustic

Freezer compartment *****

- 7 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 18 kg

- Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



Unveiled in the Liebherr FNb 505i

BluRoX can first be seen in the Liebherr FNb 505i. In the door of this freezer, the innovative vacuum insulation celebrates a very special world first: in accordance with the new EU energy label, the Liebherr FNb 505i is the first freezer of its type to be awarded efficiency class "B". And to ensure this remains the case for many years, the high-quality insulation also boasts the durability that Liebherr is renowned for.





To learn more about this exciting technology and the many advantages of BluRoX, visit: home.liebherr.com/blurox



BluRoX

←60→



FNb 505i

| Performance | | | Prime | | | | |
|--|--------|----------------------|-----------------|-----------------------------|--------------|----------------|--|
| Energy efficiency | class: | | | | | | $\begin{bmatrix} B & A \\ f & G \end{bmatrix}^1$ |
| Energy consumption year / 24 hrs: | | | | | 120/0. | 328 kWh 1 | |
| Total volume ² : | | | | | | 238 l | |
| Noise output / noise class: | | | | 33 dE | B(A) / B, S | uperSilent | |
| Climate rating: | | | | SN-T (fr | om +10°C | to +43°C) | |
| Designed to operate in ambient temperatures: | | | | | as lov | / as -15°C | |
| Door/side walls: | | | | | | wh | ite/white |
| Exterior dimensions in cm (h/w/d): | | | | | 165.5/5 | 9.7 / 65.5 1 | |
| | | | | | | | |
| No Super Frost Frost | LED | Easy Twist Ice | Super Silent | Touch & Swipe Display | Space Box | Vario Space | Easy Open |

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 6 drawers on integrated drawer guide, VarioSpace
- · Top drawer with convenient tilting function
- · LED lighting
- · Status indicator
- · Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg
- · 2 cold storage accumulators


- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal







FNc 507i







- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 6 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- · Top drawer with convenient tilting function
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg
- 2 cold storage accumulators
- · Safety glass fittings

Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→



FNd 505i

| Energy efficiency class: | D A |
|--|-----------------------------|
| Energy consumption year / 24 hrs: | 188 / 0.515 kWh |
| Total volume 2: | 238 |
| Noise output/noise class: | 34 dB(A) / B, SuperSilen |
| Climate rating: | SN-T (from +10 °C to +43 °C |
| Designed to operate in ambient temperatures: | as low as -15°0 |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 165.5 / 59.7 / 67.5 |
| | |

Easy Super Touch & Space Vario Space Ice Display



Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 6 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- LED lighting
- · Status indicator
- · Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg
- 2 cold storage accumulators

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→



FNd 5026

| Energy efficiency class: | D A 1 G |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 188 / 0.515 kWh ¹ |
| Total volume ² : | 238 l |
| Noise output/noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 165.5 / 59.7 / 67.5 |























- LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 6 drawers on integrated drawer guide, VarioSpace
- Top drawer with convenient tilting function
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 17 kg

Key features

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal



←60→

FNe 5006

| 70.010.00 | |
|--|------------------------------|
| Energy efficiency class: | E A D |
| Energy consumption year / 24 hrs: | 235 / 0.643 kWh ³ |
| Total volume ² : | 238 [|
| Noise output/noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 165.5 / 59.7 / 67.5 |
| | |



Controls

- LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 6 drawers on integrated drawer guide, VarioSpace
- · Top drawer with convenient tilting function
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 17 kg

Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm.


If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.





←60→

FNc 467i





Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 5 drawers, of which 4 with telescopic partial pull-out, VarioSpace
- LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 16 kg
- · 2 cold storage accumulators
- · Safety glass fittings

Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→

FNd 465i

Energy efficiency class: 177 / 0.484 kWh ¹ Energy consumption year / 24 hrs: Total volume 2: Noise output/noise class: 35 dB(A) / B, SuperSilent Climate rating: SN-T (from +10 °C to +43 °C) Designed to operate in ambient temperatures: as low as -15°C Door/side walls: white/white 145.5 / 59.7 / 67.5 1 Exterior dimensions in cm (h/w/d):

Easy Super Touch & Space Silent Display Space Box



Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 5 drawers on integrated drawer guide, VarioSpace
- LED lighting
- Status indicator
- · Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 16 kg • 2 cold storage accumulators


- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal


NoFrost freezers NoFrost freezers





FNb 465i







Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 5 drawers on integrated drawer guide, VarioSpace
- · LED lighting
- Status indicator
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators

Key features

144

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→

FNd 4625

| Energy efficiency class: | D A 1 |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 177 / 0.484 kWh ¹ |
| Total volume ² : | 199 l |
| Noise output/noise class: | 37 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 145.5 / 59.7 / 67.5 1 |



Controls

- · LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 5 drawers on integrated drawer guide, VarioSpace
- Ice cube trav
- · Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 16 kg


Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal





FNe 4605







Controls

- LC monochrome display behind-the-door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 5 drawers on integrated drawer guide, VarioSpace
- Temperature rise time: 16 h
- · Freezing capacity in 24 hrs: 16 kg

Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal








←60→

FNb 425i

| Energy efficiency class: | B A 1 |
|-----------------------------------|------------------------------|
| Energy consumption year / 24 | hrs: 106 / 0.290 kWh 1 |
| Total volume 2: | 160 l |
| Noise output/noise class: | 33 dB(A) / B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient to | emperatures: as low as -15°C |
| Door / side walls: | white/white |
| Exterior dimensions in cm (h/ | w/d): 125.5/59.7/67.5 1 |



FNe 4204





Controls

- 2.4" TFT-colour display behind-the-door, touch- & swipe
- Digital temperature display
- · SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers on integrated drawer guide, VarioSpace
- · LED lighting

Controls

- · Status indicator
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 15 kg
- 2 cold storage accumulators

Key features

- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

- LC monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers on integrated drawer guide, VarioSpace
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 15 kg

- Vertical recessed handle
- Transport handles, front and at back, transport castors
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

Under counter NoFrost freezers Under counter SmartFrost freezers











FNe 1404

Pure

←55→

FNsddi 1624

| Energy efficiency class: | | D A 1 |
|-----------------------------------|------------------|----------------------------|
| Energy consumption year / 24 | hrs: 14 8 | 8 / 0.405 kWh ¹ |
| Fotal volume ²: | | 92 l |
| Noise output/noise class: | | 37 dB(A)/C |
| Climate rating: | SN-T (from + | L0 °C to +43 °C) |
| Designed to operate in ambient to | emperatures: | as low as -15°C |
| Door/side walls: | | white/white |
| Exterior dimensions in cm (h / | w/dJ. | 85 / 60 / 60.7 1 |





Controls

- TouchControl in the worktop, touch electronic
- Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****


- 4 drawers, VarioSpace
- Ice cube trav
- LED lighting
- Temperature rise time: 9.5 h - Freezing capacity in 24 hrs: 8.5 kg
- Safety glass fittings

Key features

- · Slimline handle with integrated opening mechanism
- Height-adjustable feet at front
- Reversible door hinging, right
- · Replaceable door seal

FNdi 1624

| Energy efficiency class: | D A T |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 148 / 0.405 kWh ¹ |
| Total volume 2: | 92 l |
| Noise output/noise class: | 37 dB(A)/C |
| Climate rating: SN-T | (from +10 °C to +43 °C) |
| Designed to operate in ambient tempera | atures: as low as -15 °C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d |): 85/60/60.7 ¹ |



Controls

- · TouchControl in the worktop, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- · 4 drawers, VarioSpace
- · Ice cube tray
- LED lighting
- Temperature rise time: 9.5 h
- Freezing capacity in 24 hrs: 8.5 kg
- Safety glass fittings

Key features

· Slimline handle with integrated opening mechanism

1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm.

If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

| ₹ d | Energy efficiency class: |
|-----------------------------|--|
| 85 / 0.506 kWh ¹ | Energy consumption year / 24 hrs: 18 |
| 92 l | Total volume ² : |
| 37 dB(A)/C | Noise output / noise class: |
| +10 °C to +43 °C) | Climate rating: SN-T (from |
| as low as -15°C | Designed to operate in ambient temperatures: |
| white/white | Door/side walls: |
| 85/55/60.71 | Exterior dimensions in cm (h/w/d): |























Controls

- TouchControl in the worktop, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers, VarioSpace
- LED lighting
- · Temperature rise time: 9 h
- · Freezing capacity in 24 hrs: 7.5 kg
- · Safety glass fittings

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



Fci 1624

| Energy efficiency class: | C A 1 |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 110 / 0.301 kWh ¹ |
| Total volume ² : | 107 l |
| Noise output/noise class: | 36 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/60/60.7 ¹ |



































Controls


- TouchControl in the worktop, touch electronic
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 4 drawers, VarioSpace
- · Ice cube tray
- · LED lighting
- Temperature rise time: 15 h
- · Freezing capacity in 24 hrs: 7.5 kg Safety glass fittings

Key features

- · Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal







Exterior dimensions in cm (h/w/d):











85/60/60.71

←60→



Controls

- TouchControl in the worktop, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers, VarioSpace
- Ice cube tray - LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 7.5 kg

Key features


Safety glass fittings

- · Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front - Reversible door hinging, right
- · Replaceable door seal

Under counter SmartFrost freezers Under counter SmartFrost freezers



Fc 1404





Controls

- TouchControl in the worktop, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers, VarioSpace
- · LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 7.5 kg
- Safety glass fittings

Key features

148

- · Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←55→

Fd 1404

Pure

| Energy efficiency class: | D A 1 |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 137 / 0.375 kWh ¹ |
| Total volume ² : | 107 l |
| Noise output/noise class: | 37 dB(A) / C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 85/55/60.7 ¹ |



Controls

- · TouchControl in the worktop, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ****

- 4 drawers, VarioSpace
- · LED lighting
- Temperature rise time: 13.5 h
- Freezing capacity in 24 hrs: 7 kg
- Safety glass fittings

Key features

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



Fe 1414

Designed to operate in ambient temperatures: as low as -15 °C



172 / 0.471 kWh ¹

SN-T (from +10 °C to +43 °C)

107 l

37 dB(A)/C

white/white

85/55/60.7

← 55 →



Fsve 1404

| Energy efficiency class: | E A 1 |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 172 / 0.471 kWh ¹ |
| Total volume 2: | 107 l |
| Noise output / noise class: | 39 dB(A)/C |
| Climate rating: SN-T (from | +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door/side walls: | silver/silver |
| Exterior dimensions in cm (h/w/d): | 85/55/60.7 ¹ |

Pure Energy efficiency class: Energy consumption year / 24 hrs: 172 / 0.471 kWh 1 Total volume 2:

Noise output / noise class: 37 dB(A)/C SN-T (from +10 °C to +43 °C) Climate rating: Designed to operate in ambient temperatures: as low as -15°C Door/side walls: white/white Exterior dimensions in cm (h/w/d): 85/55/60.71

107 l















- TouchControl in the worktop, touch electronic
- · Digital temperature display

Controls

Energy efficiency class:

Noise output / noise class:

Total volume 2:

Climate rating:

Door/side walls:

Energy consumption year / 24 hrs:

Exterior dimensions in cm (h/w/d):

- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ** * * * *

- 4 drawers, VarioSpace
- · LED lighting
- Temperature rise time: 12.5 h
- · Freezing capacity in 24 hrs: 5.5 kg
- · Safety glass fittings

Key features

- · Recessed handle
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal

Controls

- TouchControl in the worktop, touch electronic
- · Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment *****

- 4 drawers, VarioSpace
- · LED lighting
- Temperature rise time: 12.5 h
- Freezing capacity in 24 hrs: 5.5 kg
- · Safety glass fittings

Key features

- · Recessed handle
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

Controls

- TouchControl in the worktop, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic


Freezer compartment *****

- 4 drawers, VarioSpace
- LED lighting - Temperature rise time: 12.5 h
- Freezing capacity in 24 hrs: 5.5 kg
- · Safety glass fittings

- Slimline handle with integrated opening mechanism
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal

Chest freezer Chest freezer

Quality in every detail



StopFrost

StopFrost prevents a vacuum from building up, ensuring the lid opens easily. Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer.



SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the chest freezers are smooth and easy-to-clean offering additional capacity.



Condenser

The heat-exchange condenser is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the easy-to-clean outside walls.



FrostProtect

Due to their shape and size, many chest freezers are kept outside of the normal household environment so Liebherr has developed FrostProtect to enable these models to work in low ambient temperatures. All chest freezer models will work in ambient temperatures as low as -15°C.



LED interior light

The bright LED interior light allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



SuperFrost function

The automatic SuperFrost function quickly reduces the temperature to freeze your food while preserving the vitamins. As soon as the food is completely frozen, the automated SuperFrost function switches back to normal mode.



←168→

CFe 2500

| Energy efficiency class: | E Î |
|--|------------------------------|
| Energy consumption year / 24 hrs: | 295 / 0.808 kWh |
| Total volume 1: | 497 (|
| Noise output/noise class: | 33 dB(A)/B, SuperSilent |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Designed to operate in ambient temperatures: | as low as -15°C |
| Door / side walls: | white/white |
| Exterior dimensions in cm (h/w/d): | 82.5 / 167.5 / 70.2 |











- · Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- FrostControl
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ****

- · Low vibration, low noise, easy-to-clean foam-embedded condenser
- · LED lighting
- Temperature rise time: 40 h
- · Freezing capacity in 24 hrs: 20 kg
- · Removable freezer tray as partition wall can be used as a drip tray
- 2 suspension baskets as standard, 5 retrofittable

- · Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening



Quality in every detail



LightTower

One of the most important – and most neglected – design elements is light. Cleverly used, it can do wonders for setting the right mood, just like it does in our glass door appliances. Two vertical light columns illuminate your wine bottles like the pieces of art they are, every time you open the door, or all the time. The choice is yours – just like the light intensity.



Recessed handle

Functionality meets elegance: the recessed handles of the Vinidor Selection models offer a smooth and comfortable grip - and an unobstructed view of the wine tempering fridge's refined design, which fits even the most sophisticated surroundings.



Wall panel in BlackSteel

The ideal backdrop for your wine collection: a rear wall panel in BlackSteel. The striking black stainless steel adds a certain je ne sais quoi to the inside of you wine tempering fridge. However, appearance it just one of its advantages, the back wall also ensures balanced air circulation and perfectly controlled humidity.



Water tray

Ideal humidity, even in dry conditions, thanks to the easily retrofittable water tray. It helps maintain optimal humidity in the appliance by collecting water from inside the appliance or from you filling it as required. This way, your wine collection is kept in the ideal conditions in any environment.



Integrated door opening mechanism

All doors are meant to be opened, but only some are designed to feel effortless. Whether you need to access your appliance regularly or with minimal effort, the integrated door opening mechanism has your back – while keeping the strain on it to a minimum. As a bonus, the elegant handle adds an eye-catching element to your appliance as well.



FlexFit wooden bars

Even more flexibility for storing wine bottles. The Vinidor Selection models are equipped with FlexFit wooden bars. These can be fitted as accessories for Vinidor models with plastic shelves.



Touch & Swipe display

Maintain the perfect tempering conditions inside your wine appliance, without ever opening the door. The Glass Touch & Swipe display enables you to easily navigate the sleek interface and manage temperature and humidity on the vivid colour display. Even when not in use, the display provides you with real-time temperature updates for each zone.



Electronic door lock

If there is one thing in life you can be sure of, it is your wines. The electronic door lock ensures this – it is unlocked by entering a PIN, preventing unauthorised use. And it is also more efficient, since the convenient unlocking method enables you to open the door more quickly.



Soft telescopic rails

Exploring your wine collection, made even more enjoyable. The thoughtfully designed soft telescopic rails of Vinidor selection fridges ensure a smooth retrieving and retracting of your wine racks, disrupting your wine as little as possible, and bringing it to you with convenience – which leaves you with the simple pleasure of deciding which one suits your taste.

155



Activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine tempering fridges have an activated charcoal filter that reliably binds odours of all kinds. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every 6 months to change the filter, which you can easily do yourself.



SommeliereBoard

Bring elegance to your room, with the SommeliereBoard. This refined set presents all of your wine, glasses, decanter, and utensils in a sophisticated manner.

Not only does it look amazing, but it also offers practicality with the integrated storage box and dedicated working surface for wine opening and serving.

154 The features shown are model dependent; look for these features in your model choice.

Model groups

Overview of the product range

Temperature ranges

+5 °C to +20 °C

+5 °C to +20 °C

+5 °C to +20 °C



With two to three temperature zones that can be set independently from each other to between +5 °C to +20 °C – accurate to the degree – our **multi-temperature wine fridges** offer the most flexibility for any use. That means that red wines, white wines and champagnes can all be stored at the same time and at an ideal temperature in one single appliance with three temperature zones. And these appliances also provide ideal climatic conditions for the long-term storage of wines. With their temperature zones of different sizes and temperature settings that offer complete flexibility, these appliances are perfect for each individual wine collection.



+5 °C to +20 °C



Wine storage fridges recreate the conditions of a wine cellar. A constant temperature is maintained within the entire interior of these appliances. They can be adjusted to between +5 °C and + 20 °C, depending on your requirements. Wine storage fridges are specially designed to hold a large number of bottles for storage and ageing, but they can also keep a larger stock of wine at drinking temperature.



Compact fridges – as specialists in all things cooling, storage and temperature control, Liebherr offers space-saving wonders for any occasion. Enter stage right: our efficient compact appliances for fresh ideas. Compact wine storage fridges provide just the right dimensions for the niche wine collection. Valuable cigars are kept under optimal storage conditions in the humidor.



Bordeaux bottle size (0.75 l)

All specifications regarding bottle capacity refer to these dimensions.

Freestanding wine appliances

Multi-temperature

Wine storage fridges

WSbli 7731

wine fridges

←75 → ←70 → ←60 →

Width in cm

WPgbi 7483

WPgbi 7473 WPgbi 7472

| | ←43→ |
|------------|----------|
| WPgbi 5283 | |
| WPgbi 5273 | |
| WPgbi 5272 | |
| WPbsi 5252 | - |
| WSbsi 5252 | |
| WPsd 5252 | |
| WPbsi 5052 | |
| WPsd 4652 | |
| WTes 1672 | |
| WPbli 5231 | WKes 653 |
| WSbli 5231 | |
| WPbli 5031 | |

WSbli 5031
WPbl 5001
WSbl 5001
WPbl 4601
WSbl 4601
WPbl 4201
WSbl 4201

WKb 1812

Compact appliances

ZKes 453



156

Series Series


Vinidor **Vinidor Selection** Vinidor **Vinidor Selection** Quality Constant temperature maintenance Constant temperature maintenance StainlessSteel 60 cm GlassBlack 60 cm Adjustable temperature range in 2 zones: +5 °C to +20 °C Adjustable temperature range in 2 or 3 zones: +5 °C to +20 °C Constant display of the current temperature in each zone Permanent display of current temperature Triple UV and safety glazing (UVProtect Plus) Triple UV and safety glazing (UVProtect Plus) Vibration-damped bearing (VibrateSafe) Vibration-damped bearing (VibrateSafe) 185 185 185 185 Replaceable door seal Replaceable door seal 2 height-adjustable feet 2 height-adjustable feet Optimum Adjustable humidity with HumiditySelect Regulated humidity with climate HumidityControl in the StorageZone Actual display of the humidity in the StorageZone Water tray FreshAir filter in zone separator with replacement reminder FreshAir filter in each zone separator with replacement reminder Temperature setting in 1 °C increments Temperature setting in 1 °C increments **WPgbi 5272 WPgbi 5273** WPgbi 5283 WPsd 4652 WPsd 5252 Comfort and Zone separator with plastic bottle shelf, can be upgraded Zone separator with FlexFit wooden bars flexibility with FlexFit wooden bars (accessory) Д **Max** Д **М**ах ¹ Max ¹ Max **155 ∐107 ∐106 」85 ∐104** Presentation shelf Stainless steel bottle presenter SoftSystem soft stop mechanism SoftSystem soft stop mechanism All appliances available from Summer 2024 All appliances available from Summer 2024 Height-adjustable wooden racks FlexFit wooden racks (additional racks available as accessories) with SoftTelescopic self-closing mechanism Display: choice of 9 or 12 languages * Display: choice of 12 languages BlackSteel 60 cm GlassBlack 70 cm (DE/EN/FR/ES/IT/NL/CS/PL/PT/BG/RU/ZH-CN) (DE/EN/FR/ES/IT/NL/CS/PL/PT/BG/RU/ZH-CN) SommelierBoard* Design and LED ceiling lighting for each zone LightTower lifestyle Rear wall panel: BlackSteel Rear wall panel: SmartSteel 200 200 185 185 Touch display (SmartSteel models) 165 Touch & Swipe display (BlackSteel models) Touch & Swipe display in the glass door Presentation light (glass door) Presentation light Slimline aluminium door handle with opening mechanism Recessed vertical grip Zones Low noise Low noise InteriorFit InteriorFit Security TempProtect Plus TempProtect Plus Door, temperature and power failure alarm Door, temperature and power failure alarm WPgbi 7472 WPbsi 5052 WPbsi 5252 WSbsi 5252 **WPgbi 7473 WPgbi 7483** Humidity notification Alarm issued both audibly and visually on display, Alarm issued both audibly and visually on display, ∄ Max ∄ Max ¹∖ Max \ Max ∄ Max Max via illumination and push message thanks to SmartDevice ** via illumination and push message thanks to SmartDevice ** **∐155 ∐155 ∐204 ∐182 ∐145** Display lock Display lock eDoorLock, electronic door lock All appliances available from Summer 2024 All appliances available from Summer 2024 Connectivity* SmartDevice (SmartDeviceBox included) * SmartDevice (SmartDeviceBox included) Presentation light ** Presentation light ** Temperature setting in 1-°C increments ** Temperature setting in 1-°C increments ** Display and control of relevant appliance functions ** Display and control of relevant appliance functions ** * depending on the model ** via SmartDevice app 60-cm-wide models: appliance depth 67.5 cm 70-cm-wide models: appliance depth 76.4 cm

158



SommeliereBoard

Bring elegance to your room, with the Sommeliere-Board. This refined set presents all of your wine, glasses, decanter, and utensils in a sophisticated manner. Not only does it look amazing, but it also offers practicality with the integrated storage box and dedicated working surface for wine opening and serving.



LightTower

160

One of the most important - and most neglected design elements is light. Cleverly used, it can do wonders for setting the right mood, just like it does in our glass door appliances. Two vertical light columns illuminate your wine bottles like the pieces of art they are, every time you open the door, or all the time. The choice is yours – just like the light intensity.



←70 →

WPgbi 7483 Vinidor Selection

| Energy efficiency class: | F A t |
|------------------------------------|---|
| Energy consumption year / 24 hrs: | 144 / 0.394 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 145 ' |
| Total volume 3: | 561 l |
| Noise output / noise class: | 35 dB(A)/B, SuperSilent |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Black insulated glass door / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 201.3 / 69.7 / 76.4 ² |
| 3 Temp Storage Fresh | UV . Flex Sommelier Vibrate Steel |

| 3 Zones | Temp Protect Plus | Storage Zone | Fresh Air | UV Protect Plus | Flex Fit | Sommelier Board |
|----------------|-------------------------|---------------------|-----------------|-----------------------------|---------------|--------------------|
| Light Tower | Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | eDoor Lock | Smart Device |

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for 3 wine zones
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- · Child lock

Wine compartment

- 3 temperature zones, which can set from +5°C to +20°C
- · StorageZone with HumidityControl
- 3 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- LED light panel, both sides permanently on, dimmable
- · Beech wood fittings
- 11 shelves, of which 8 set on telescopic rails

Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



Electronic door lock

If there is one thing in life you can be sure of, it is your wines. The electronic door lock ensures this - it is unlocked by entering a PIN, preventing unauthorised use. And it is also more efficient, since the convenient unlocking method enables you to open the door more quickly.



Activated charcoal filter

To ensure that your wine can mature in optimum air quality, all Liebherr wine tempering fridges have an activated charcoal filter that reliably binds odours of all kinds. This means your wine will keep its pure bouquet. To make sure that it stays that way, your Liebherr reminds you every 6 months to change the filter, which you can easily do yourself.





←70→

WPgbi 7473

Vinidor Selection

| Energy efficiency class: | F A 2 |
|------------------------------------|---|
| Energy consumption year / 24 hrs: | 144 / 0.394 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 182 ¹ |
| Total volume ³ : | 561 l |
| Noise output/noise class: | 35 dB(A) / B, SuperSilent |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Black insulated glass door / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 201.3 / 69.7 / 76.4 ² |

| Exterior dimensions in our (ii) wy dy. | | | | | | | | ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,, |
|--|-------------------------|-----------------|-----------------------------|-----------------------|-----------------|-----------------|-------------------|---|
| 3 Zones | Temp Protect Plus | Storage Zone | Fresh Air | UV Protect Plus | Flex Fit | Vibrate Safe | Steel Interior | Light Tower |
| Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | eDoor Lock | Smart Device | | | |

Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for 3 wine zones
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 3 temperature zones, which can set from +5 °C to +20 °C
- StorageZone with HumidityControl
- 3 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- LED light panel, both sides permanently on, dimmable
- · Beech wood fittings
- 12 shelves, of which 9 set on telescopic rails

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal


¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: $300.5\,$ mm, Ø 76.1 mm) 2 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be

used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



←70→

WPgbi 7472 Vinidor Selection





Controls

- · 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for both wine zones
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5 °C to +20 °C
- StorageZone with HumidityControl
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · LED light panel, both sides permanently on, dimmable
- · Beech wood fittings
- 10 shelves, of which 8 set on telescopic rails

Key features

162

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WPgbi 5283 Vinidor Selection

| F d |
|---------------------------------------|
| 126 / 0.345 kWh ² |
| 85¹ |
| 357 l |
| 35 dB(A)/B, SuperSilent |
| SN-ST (from +10 °C to +38 °C) |
| Black insulated glass door/BlackSteel |
| 185.4/59.7/67.8 ² |
| |

| 3 Zones | Temp Protect Plus | Storage Zone | Fresh Air | UV Protect Plus | Flex Fit | Sommelier Board | Vibrate Safe | Steel Interior |
|----------------|-------------------------|---------------------|-----------------|-----------------------------|---------------|--------------------|-----------------|-------------------|
| Light Tower | Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | eDoor Lock | Smart Device | | |

Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for 3 wine zones
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 3 temperature zones, which can set from +5 °C to +20 °C
- · StorageZone with HumidityControl
- 3 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · LED light panel, both sides permanently on, dimmable
- · Beech wood fittings
- 10 shelves, of which 7 set on telescopic rails

Key features

- · Vertical recessed handle
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal



←60→

WPgbi 5273 Vinidor Selection

Energy efficiency class: 126 / 0.345 kWh ² Energy consumption year / 24 hrs: Max. Bordeaux bottles 0.75 l: 104 1 357 l Total volume 3: 35 dB(A) / B, SuperSilent Noise output / noise class: SN-ST (from +10 °C to +38 °C) Climate rating: Black insulated glass door / BlackSteel Door/side walls:



Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for 3 wine zones
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 3 temperature zones, which can set from +5 °C to +20 °C
- · StorageZone with HumidityControl
- 3 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · LED light panel, both sides permanently on, dimmable
- Beech wood fittings
- 11 shelves, of which 8 set on telescopic rails

Key features

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WPgbi 5272

Energy efficiency class: 127 / 0.347 kWh ² Energy consumption year / 24 hrs: Max. Bordeaux bottles 0.75 l: 106 1 367 l Total volume 3: Noise output/noise class: 35 dB(A) / B, SuperSilent SN-ST (from +10 °C to +38 °C) Climate rating:

| Door/sid | le walls: | | | В | Black insulated glass door / BlackSteel | | | | |
|----------------|-------------------------|-----------------|-----------------------------|-----------------------|---|-----------------|-------------------|-------------------------|--|
| Exterior d | limensions | s in cm (h | /w/d): | | | | 185.4 / 59 | 9.7 / 67.8 ² | |
| 2 Zones | Temp Protect Plus | Storage Zone | Fresh Air | UV Protect Plus | Flex Fit | Vibrate Safe | Steel Interior | Light Tower | |
| Soft System | Telescopic Rails | Super Silent | Touch & Swipe Display | eDoor Lock | Smart Device | | | | |

Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for both wine zones
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5 $^{\circ}\text{C}$ to +20 $^{\circ}\text{C}$
- StorageZone with HumidityControl
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- LED light panel, both sides permanently on, dimmable
- · Beech wood fittings
- 10 shelves, of which 8 set on telescopic rails

- · Vertical recessed handle
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

Multi-temperature wine fridges Multi-temperature wine fridges



Touch & Swipe display

Maintain the perfect tempering conditions inside your wine appliance, without ever opening the door. The Glass Touch & Swipe display enables you to easily navigate the sleek interface and manage temperature and humidity on the vivid colour display. Even when not in use, the display provides you with real-time temperature updates for each zone.



Integrated door opening mechanism

All doors are meant to be opened, but only some are designed to feel effortless. Whether you need to access your appliance regularly or with minimal effort, the integrated door opening mechanism has your back - while keeping the strain on it to a minimum. As a bonus, the elegant handle adds an eye-catching element to your appliance as well.

164



←60→

WPbsi 5252

| Energy efficiency class: | F A c |
|--|--------------------------------------|
| Energy consumption year / 24 hrs: | 127 / 0.347 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 155 ¹ |
| Total volume 3: | 367 l |
| Noise output / noise class: | 37 dB(A) / C |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: Insulating glass door w | ith frame in BlackSteel / BlackSteel |
| Exterior dimensions in cm (h/w/d): | 185.4 / 59.7 / 67.5 ² |
| | Flex Vibrate Steel Interior LED |

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for both wine zones
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5°C to +20°C
- 2 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED zone lighting permanently on, dimmable
- · Adjustable beech wood shelves
- 8 shelves, of which 1 is a presentation shelf

Key features

- · Slimline handle with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WSbsi 5252

| • |
|------------------------------------|
| E A 2 |
| 100 / 0.274 kWh ² |
| 155 ¹ |
| 349 l |
| 37 dB(A) / C |
| SN-T (from +10 °C to +43 °C) |
| Full door, BlackSteel / BlackSteel |
| 185.4/59.7/67.5 ² |
| Vibrate Steel Soft |
| |







Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for both wine zones
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5°C to +20°C
- 2 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity range adjusted between two levels
- · LED zone lighting
- · Adjustable beech wood shelves
- 8 shelves, of which 1 is a presentation shelf

Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



←60→

WPsd 5252

| Energy efficiency cla | SS: | F A T |
|-----------------------|-----------------------|--|
| Energy consumption | year / 24 hrs: | 127 / 0.347 kWh |
| Max. Bordeaux bottle | es 0.75 l: | 155 |
| Total volume 3: | | 367 |
| Noise output/noise | class: | 37 dB(A) / C |
| Climate rating: | | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Glass door with stain | less steel frame and SmartSteel/silver |
| Exterior dimensions | n cm (h/w/d): | 185.4 / 59.7 / 67.5 |





Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display for both wine zones
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- · LED zone lighting permanently on, dimmable
- Adjustable beech wood shelves
- 8 shelves

- · Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm. Ø 76.1 mm)

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

³ in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



←60→

WPbsi 5052

| Energy efficiency class | s: | F |
|-------------------------|---------------------|--|
| Energy consumption y | ear / 24 hrs: | 123 / 0.337 kWh |
| Max. Bordeaux bottles | 0.75 l: | 131 |
| Total volume 3: | | 319 |
| Noise output/noise c | ass: | 37 dB(A) / C |
| Climate rating: | | SN-ST (from +10 °C to +38 °C |
| Door/side walls: | Insulating glass do | oor with frame in BlackSteel / BlackStee |
| Exterior dimensions in | cm (h \ M \ q). | 165.4 / 59.7 / 67.5 |



Controls

- 2.4" TFT-colour display in-the-door, touch- & swipe
- Digital temperature display for both wine zones
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED zone lighting permanently on, dimmable
- Adjustable beech wood shelves
- 7 shelves, of which 1 is a presentation shelf

Key features

- Slimline handle with integrated opening mechanism
- Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WPsd 4652

| Door/side walls: Glass door with stainless steel frame and SmartSteel/silve Exterior dimensions in cm (h/w/d): 145.4/59.7/67.5 | | | | | | | | |
|---|--------------|--------------|--------|--|--|--|---------|----------------------|
| Noise output / noise class: 38 dB(A Climate rating: SN-ST (from +10 °C to +3 | | | | | | | | |
| | | | | | | | 272 l | |
| Max. Bor | deaux bot | tles 0.75 l: | | | | | | 107 1 |
| Energy o | onsumptio | n year / 24 | 4 hrs: | | | | 118/0.3 | 323 kWh ² |
| Energy e | efficiency c | lass: | | | | | | F f g 2 |

- · LC monochrome display in the door, touch electronic
- Digital temperature display for both wine zones
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5°C to +20°C
- 2 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- · LED zone lighting permanently on, dimmable
- Adjustable beech wood shelves
- 6 shelves

Key features

- Slimline handle with integrated opening mechanism
- · Transport handles, front and at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



LED lighting

The LED lighting in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



Touch-electronic control system

The electronic LCD display is an innovative design feature. Clear menu navigation and a Touch-electronic control system provides yet more information for tailored storage conditions.

The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



←60→

WTes 1672

| Energy efficiency class: | G 🖁 |
|-------------------------------|---|
| Energy consumption year / 24 | 4 hrs: 138/0.378 kWh |
| Max. Bordeaux bottles 0.75 l: | 341 |
| Total volume 3: | 94 l |
| Noise output/noise class: | 36 dB(A)/C |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Glass door with stainless steel frame / stainless steel |
| Exterior dimensions in cm (h | /w/d): 82.2/59.8/57.5 |



















- · MagicEye control in interior, touch electronic
- Digital temperature display for both wine zones
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 temperature zones, which can set from +5°C to +20°C
- 2 independently controllable zones
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 5 shelves, of which 3 set on telescopic rails

- HardLine
- Aluminium handle
- · Reversible door hinging, right
- · Replaceable door seal

³ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Wine







GrandCru Selection

| | GrandCru | GrandCru Selection | | |
|-----------------------------|---|---|--|--|
| Quality | Constant temperature maintenance | Constant temperature maintenance | | |
| | Adjustable temperature range in one zone: +5°C to +20°C | Adjustable temperature range in one zone: +5 °C to +20 °C | | |
| | Permanent display of current temperature | Permanent display of current temperature | | |
| | Triple UV and safety glazing / UVProtect Plus | Triple UV and safety glazing / UVProtect Plus | | |
| | Low-vibration storage / VibrateSafe | Low-vibration storage / VibrateSafe | | |
| | Neck-to-neck storage for maximum bottle capacity | Neck-to-neck storage for maximum bottle capacity | | |
| | Replaceable door seal | Replaceable door seal | | |
| | 2 height-adjustable feet | 2 height-adjustable feet | | |
| Feel good climate | Adjustable humidity with HumiditySelect | Controllable humidity with HumidityControl | | |
| | | Current humidity display | | |
| | 1 FreshAir filter with replacement reminder | 1 FreshAir filter with replacement reminder | | |
| | Temperature setting in 1°C steps | Temperature setting in 1°C steps | | |
| Convenience and flexibility | EasyFill loading aid | EasyFill loading aid | | |
| | SelfClosing Door | SelfClosing Door | | |
| | Wooden pull-out shelf, height-adjustable | Wooden pull-out shelf, height-adjustable | | |
| | Display: select from 9 languages (DE/EN/FR/ES/IT/NL/CS/PL/PT) | Display: select from 9 languages (DE/EN/FR/ES/IT/NL/CS/PL/PT) | | |
| Design and lifestyle | LED ceiling lighting | LED ceiling lighting (solid door), LightColumn (glass door) | | |
| | Rear wall panel: metal, graphite grey | Rear wall panel: stainless steel | | |
| | Touch display | Touch display | | |
| | Presentation light (glass door) | Presentation light (glass door) | | |
| | Handle: black | Handle: brushed aluminium | | |
| | Low noise | Low noise | | |
| Safety | TempProtect Plus | TempProtect Plus | | |
| | Door, temperature and power failure alarm | Door, temperature and power failure alarm | | |
| | Alarm issued both audibly and visually on display, via illumination and push message thanks to SmartDevice* | Alarm issued both audibly and visually on display, via illumination and push message thanks to SmartDevice* | | |
| | DisplayLock | DisplayLock | | |
| | Mechanical lock, retrofittable | Mechanical lock, integrated | | |
| Connectivity* | SmartDevice ready | SmartDevice (SmartDeviceBox incl.) | | |
| | Presentation light* | Presentation light* | | |
| | Temperature setting in 1°C steps* | Temperature setting in 1°C steps* | | |
| | Display and control of relevant appliance functions* | Display and control of relevant appliance functions* | | |


^{*} via SmartDevice app

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

168



WSbli 7731 GrandCru Selection





Controls

- · LC monochrome display in the door, touch electronic
- Digital temperature display
- SmartDeviceBox included
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 $^{\circ}\text{C}$ to +20 $^{\circ}\text{C}$
- Humidity regulation adjustable between 50% to 80% RH*
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED ceiling lighting
- Adjustable beech wood shelves
- 7 shelves

Key features

- Aluminium handle
- · Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WPbli 5231

GrandCru Selection

| Energy | efficiency (| class: | FA | | | | | | |
|----------|-----------------|---------------|--------|---------------|-------------------------------|---------|-----------------------|-------------------------|--|
| Energy | consumpti | on year/2 | 4 hrs: | | | 115/0 | .315 kWh ² | | |
| Max. Bo | rdeaux bot | ttles 0.75 l: | | | | | 229 ¹ | | |
| Total vo | olume³: | | | | 44 | | | | |
| Noise o | utput/nois | se class: | | | 38 dB(A)/0 | | | | |
| Climate | rating: | | | | SN-ST (from +10 °C to +38 °C | | | | |
| Door/s | ide walls: | | | | Glass door, frame black/black | | | | |
| Exterio | r dimensior | ns in cm (h | /w/d): | | | | 188.4/5 | 9.7 / 76.3 ² | |
| | | | | | | | | | |
| 1 | Temp Protect | Humidity | Fresh | UV Protect | Flex | Vibrate | Steel | Light | |

| 1 Zone | Temp Protect Plus | Humidity Control | Fresh Air | UV Protect Plus | Flex Fit | Vibrate Safe | Steel Interior | Li |
|-----------------------|-------------------------|---------------------|-------------------------|-----------------------|-----------------|-----------------|-------------------|----|
| Presentation Light | Touch Display | Door Lock | Self Closing Door | Easy Fill | Smart Device | | | |

Controls

- LC monochrome display in the door, touch electronic
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH*
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- · LED light one-sided permanently on, dimmable
- · Adjustable beech wood shelves
- 6 shelves

Key features

- Aluminium handle
- · Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal





WSbli 5231

GrandCru Selection

| Energy efficiency class: | E |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 96 / 0.263 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 229 1 |
| Total volume 3: | 433 l |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | Full door, black/black |
| Exterior dimensions in cm (h/w/d): | 188.4/59.7/76.3° |

Controls

- · LC monochrome display in the door, touch electronic
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH*
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity regulation via adjustable fan
- LED ceiling lighting
- Adjustable beech wood shelves
- 6 shelves

Key features

- Aluminium handle
- · Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



WKb 1812

| Energy efficiency class: | G |
|------------------------------------|-------------------------------|
| Energy consumption year / 24 hrs: | 123 / 0.337 kWh |
| Max. Bordeaux bottles 0.75 l: | 66 ¹ |
| Total volume 3: | 135 l |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Glass door, frame black/black |
| Exterior dimensions in cm (h/w/d): | 89/60/61.3 |











Controls

- MagicEye on front, key electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- · Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity regulation via adjustable fan
- · Interior lighting permanently on
- Adjustable grid shelves
- 3 shelves

- HardLine
- Ergonomically designed slimline handle, black
- · Reversible door hinging, right
- · Replaceable door seal

^{*} At temperatures in home environments. In very dry or cold environments such as home cellars, we recommend supporting the system with the tailor-made water box from our range of accessories.


³ in accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Wine storage fridges
Wine storage fridges



WPbli 5031 GrandCru Selection





Controls

- $\boldsymbol{\cdot}$ LC monochrome display in the door, touch electronic
- · Digital temperature display
- SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 $^{\circ}\text{C}$ to +20 $^{\circ}\text{C}$
- Humidity regulation adjustable between 50% to 80% $\rm RH^*$
- Convection cooling, fresh air supply via Fresh Air activated charcoal filter
- Humidity regulation via adjustable fan
- LED light one-sided permanently on, dimmable
- Adjustable beech wood shelves
- 5 shelves

Key features

- · Aluminium handle
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



WSbli 5031

←60→

| Energy efficiency class: | E A C |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 97 / 0.265 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 196¹ |
| Total volume 3: | 378 l |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | Full door, black/black |
| Exterior dimensions in cm (h/w/d): | 168.4/59.7/76.3° |

GrandCru Selection

| Exterior dimensions in cm (n/w/d): | | | | | | | 168.4 / 59 | 7.7 / /6.5 |
|------------------------------------|-------------------------|---------------------|-----------------|-------------|-----------------|-------------------|------------|------------------|
| 1 Zone | Temp Protect Plus | Humidity Control | Fresh Air | Flex Fit | Vibrate Safe | Steel Interior | LED | Touch Display |
| Door Lock | Self Closing Door | Easy Fill | Smart Device | | | | | |

Controls

- LC monochrome display in the door, touch electronic
- · Digital temperature display
- · SmartDeviceBox included
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Humidity regulation adjustable between 50% to 80% RH*
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED ceiling lighting
- Adjustable beech wood shelves
- 5 shelves

Key features

- Aluminium handle
- Transport handles at back, transport castors at back

If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level

- · Height-adjustable feet at front
- Reversible door hinging, right
- Replaceable door seal





WPbl 5001

GrandCru

| Energy consumption year / 24 hrs: | 113 / 0.309 kWh ² |
|------------------------------------|-------------------------------|
| Max. Bordeaux bottles 0.75 l: | 196¹ |
| Total volume ³ : | 385 l |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door / side walls: | Glass door, frame black/black |
| Exterior dimensions in cm (h/w/d): | 168.4/59.7/76.3 ² |

Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- · LED ceiling lighting permanently on, dimmable
- Adjustable beech wood shelves
- 5 shelves

Key features

- Slimline handle, black
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



WSbl 5001

GrandCru

| Energy efficiency class: | E A |
|------------------------------------|------------------------------|
| Energy consumption year / 24 hrs: | 97 / 0.265 kWh |
| Max. Bordeaux bottles 0.75 l: | 196 |
| Total volume ³ : | 378 |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C) |
| Door/side walls: | Full door, black/black |
| Exterior dimensions in cm (h/w/d): | 168.4/59.7/76.3 |



Controls

- LC monochrome display in the door, touch electronic
- · Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- · 1 temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED ceiling lighting
- Adjustable beech wood shelves
- 5 shelves

- Slimline handle, black
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)


2 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm.

3 In accordance with Regulation EU 2019/2016 we indicate the total volume to the and refrigeration compartments to one place after the decimal point.

Wine storage fridges Wine storage fridges



WPbl 4601 GrandCru





Controls

- LC monochrome display in the door, touch electronic
- · Digital temperature display
- SmartDeviceBox: optional accessory
- · Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity range adjusted between two levels
- LED ceiling lighting permanently on, dimmable
- Adjustable beech wood shelves
- 5 shelves

Key features

174

- Slimline handle, black
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



←60→

WSbl 4601

GrandCru

| Energy 6 | efficiency class: | | | | | | E A C | | |
|------------------------------------|-------------------------|--------------------|--------------|-------------|-----------------------------|-----|------------------|----------------------|--|
| Energy o | consumptio | on year / 24 | 4 hrs: | | | | 84/0.2 | 230 kWh ² | |
| Max. Bordeaux bottles 0.75 l: | | | | | | | | 166 ¹ | |
| Total vol | Total volume 3: | | | | | 32 | | | |
| Noise ou | utput/nois | e class: | | | 38 dB(A)/(| | | | |
| Climate | rating: | | | | SN-T (from +10 °C to +43 °C | | | | |
| Door/si | ide walls: | | | | Full door, black / black | | | | |
| Exterior dimensions in cm (h/w/d): | | | | | 148.4/59.7/76.3 | | | | |
| | | | | | | | | | |
| 1 Zone | Temp Protect Plus | Humidity Select | Fresh Air | Flex Fit | Vibrate Safe | LED | Touch Display | Door Lock | |

Controls

- LC monochrome display in the door, touch electronic
- · Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- · Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity range adjusted between two levels
- LED ceiling lighting
- Adjustable beech wood shelves
- 5 shelves

Key features

- Slimline handle, black
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal



WPbl 4201

GrandCru

| Energy efficiency class: | E A 2 |
|------------------------------------|-------------------------------|
| Energy consumption year / 24 hrs: | 95 / 0.260 kWh ² |
| Max. Bordeaux bottles 0.75 l: | 141 1 |
| Total volume ³ : | 272 l |
| Noise output/noise class: | 38 dB(A) / C |
| Climate rating: | SN-ST (from +10 °C to +38 °C) |
| Door/side walls: | Glass door, frame black/black |
| Exterior dimensions in cm (h/w/d): | 128.4/59.7/76.3 ² |

| 1 Zone | Temp Protect Plus | Humidity Select | Fresh Air | UV Protect Plus | Flex Fit | Vibrate Safe | LED | Touch Display |
|--------------|-------------------------|--------------------|--------------------------|-----------------------|-------------|-----------------|-----|------------------|
| Door Lock | Self Closing Door | Easy Fill | Smart Device Ready | | | | | |

Controls

- · LC monochrome display in the door, touch electronic
- Digital temperature display
- · SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity range adjusted between two levels
- · LED ceiling lighting permanently on, dimmable
- Adjustable beech wood shelves
- 4 shelves

Key features

- Slimline handle, black
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- · Replaceable door seal



WSbl 4201

GrandCru

| Energy efficiency class: | D A T |
|------------------------------------|-----------------------------|
| Energy consumption year / 24 hrs: | 76 / 0.208 kWh |
| Max. Bordeaux bottles 0.75 l: | 141 |
| Total volume ³ : | 267 |
| Noise output/noise class: | 38 dB(A)/C |
| Climate rating: | SN-T (from +10 °C to +43 °C |
| Door/side walls: | Full door, black / black |
| Exterior dimensions in cm (h/w/d): | 128.4 / 59.7 / 76.3 |
| | |





Controls

- LC monochrome display in the door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- · Humidity range adjusted between two levels
- LED ceiling lighting
- · Adjustable beech wood shelves
- 4 shelves

- Slimline handle, black
- Transport handles at back, transport castors at back
- · Height-adjustable feet at front
- · Reversible door hinging, right
- Replaceable door seal





←43→

WKes 653 GrandCru

Energy efficiency class: 78 / 0.213 kWh Energy consumption year / 24 hrs: Max. Bordeaux bottles 0.75 l: 12 ¹ Total volume 2: 48 l Noise output/noise class: 37 dB(A) / C Climate rating: SN (from +10 °C to +32 °C) Door: Glass door with stainless steel frame and SmartSteel stainless steel with SmartSteel Side walls: Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

















- LCD display in the interior, touch electronic
- Digital temperature display
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings 3 shelves

Key features

- HardLine
- · Fixed door hinge, right
- · Replaceable door seal
- Drawer for accessories
- · Suitable for wall mounting



←43→

ZKes 453

| Energy efficiency class: | | |
|--------------------------|--|--|
| Energy consumption year | /24 hrs: 162/0.443 kWh | |
| Total net capacity: | 39 [| |
| Noise output: | 40 dB(A) | |
| Climate rating: | N (from +16 °C to +32 °C) | |
| Door: | Glass door with stainless steel frame and SmartSteel | |

stainless steel with SmartSteel Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

Side walls:

- LCD display in the interior, touch electronic
- · Digital display of temperature and humidity
- Alarm in case of malfunction: visual and acoustic
- Door alarm: acoustic
- Child lock

Humidor

- 1 temperature zone, which can set from +16 °C to +20 °C
- Humidity range, adjustable between 68% to 75%
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 shelves

- HardLine
- · Fixed door hinge, right
- Replaceable door seal
- 2 presentation boxes
- Suitable for wall mounting

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)
2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.





Outdoor

Outdoor kitchens with refrigerators – whether freestanding or built-in – also provide convenience and perfect storage outdoors. The Outdoor Cooler is ideally suited to outdoor use thanks to its rust- and weatherproof materials, robust construction and high-quality components as well as its automatic shut-down function and integrated lock.



Flexible and ergonomic interior layout

With bottles stored at the bottom, the two storage racks are ideal for smaller packages. The glass shelf on telescopic rails provides an overview of foodstuffs stored at the back. Depending on the size, containers can also be stored on two height-adjustable glass shelves. And a separable glass shelf means that larger and open bottles can easily be stored upright.



←60→

OKes 1750

| Energy efficiency class: | В |
|------------------------------------|-------------------------------|
| Energy consumption year / 24 hrs: | 177 / 0.484 kW |
| Total volume 1: | 109 |
| Noise output: | 39 dB(/ |
| Door/side walls: | Stainless steel/stainless ste |
| Exterior dimensions in cm (h/w/d): | 81.8 / 59.8 / 57 |







Controls

- LCD display in the interior
- Alarm in case of malfunction: visual and acoustic
- Door alarm: visual and acoustic
- Child lock

Outdoor Cooler

- LED lighting
- 1 temperature zone, which can set from +2°C to +14°C
- Safety shut-down
- Ambient temperature range: +2°C to +35°C

- Can be installed underneath counters (ventilation via the base)
- Stainless steel slimline door handle
- Height-adjustable feet at front and back
- Reversible door hinging, right
- Concealed hinge with restricted opening
- Lock
- Splash-proof class: IPX-4

Brief explanation of features

Freshness technologies



BioFresh-Professional offers even more flexibility for individual food storage.



Cooling like a pro: Cold mist and a temperature in the safe of around 0 °C ensure a longer storage time and create a fabulous visual effect.



The Fish & Seafood Safe stores fish and seafood at the optimum temperature of -2 °C; as professionally as your fishmonger.

Bio Fresh The reliable BioFresh technology stores groceries at a temperature just above 0 °C, much cooler than in the rest of the appliance.

Bio Fresh Plus Adjustable temperature range of 0 °C and -2 °C, BioFresh-Plus safe includes a versatile Fish & Seafood-Safe.

Bio Cool Optimum humidity for fruit and vegetables via slider control and longer term food storage.



The air-tight safe allows humidity to rise keeping food fresher for longer.



Two separately controlled refrigeration circuits.

The temperatures within the refrigerator and freezer compartments can be controlled independently.



Defrosting is never needed as the freezer automatically defrosts itself.

Smart Frost

Defrosting is required much less often.



SuperCool boosts the cooling power until the food recently placed inside reaches the temperature of the rest of the contents.



SuperFrost increases the cooling power for a short time – this means the temperature remains constant when you place in unfrozen food.



Freezer section becomes alternative additional cooling zone by setting an accurate temperature of between -2 °C and +14 °C.

Wine



With constant temperature throughout the interior, adjustable from +5 °C to +20 °C.



With two temperature zones, independently and precisely adjustable from +5 °C to +20 °C.



With three temperature zones, independently and precisely adjustable from +5 °C to +20 °C.

Wine

Humidity Control The humidity can be actively regulated in 5% increments between 50% and 80% RH.

Humidity Select The humidity can be adjusted between two levels: Standard or High.

Temp Protect Plus Two sensors constantly measure the temperature in the wine fridge. A notification is sent in the event of a critical change.*

Vibrate Safe The fully vibration-insulated cooling system allows the wine to mature undisturbed.

Fresh Air For a pure bouquet, an activated charcoal filter reliably binds odours of any kind.

UV Protect Plus Triple protection: a tinted glass door with two layers of vacuum-deposited metal provides highly efficient protection from solar radiation.



Double protection: a tinted glass door with one layer of vacuum-deposited metal provides efficient protection from solar radiation

Convenience and flexibility

Soft System The door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.

Soft Telescopic Fully extendible drawers run on telescopic rails and feature a convenient self-retraction mechanism with soft-closing.

Telescopio Rails Drawers set on high-quality, smooth-running telescopic rails for reliable and secure opening and closing.

Touch & Swipe Display

Intuitive control – simply by touching and swiping on the colour display.

Touch Display A Liebherr is really simple to use with a gentle tap of a finger on the clear touch display.

Space Box For flexible food storage: At a height of 250 mm, the space box offers lots of extra room even for really large frozen items

Vario Space For extra high storage space: Simply take out the individual freezer drawers and the glass horizontal dividers below and make space for extra tall frozen items.

Easy Open EasyOpen means the freezer door can be opened multiple times one after another, conveniently and easily.

Self Closing

The door of the wine fridge closes smoothly by itself when opened less than 90°.

*SmartDevice/Smart app required

Brief explanation of features

Convenience and flexibility



Loading aid for easy stocking of the wine fridge. From an angle of 90°, the door remains open.



The bottle basket for clearly arranged storage and easy accessibility at the bar.



Shows off exquisite wines and presents bottles that have been opened.

Design



The interior features elegant glass and stainless steel elements.



The new LightTower lighting concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.



LED light column from top to bottom evenly illuminates the interior. One-sided or double-sided depending on the series



Effectively showcases the wine collection even when the glass door is closed. The brightness can be dimmed using the display.*



Minimal heat generation, energy-saving and maintenance-free for optimum lighting.



Not just an attractive design element, the SmartSteel stainless steel rear wall panel ensures balanced air circulation.

Water and ice



Ice-cold water on tap with no heavy lifting of bottles and is better for our environment.



Perfect for Parties: You will never run out of cold drinks. The 8 kg supply of ice cubes makes sure of that.



Automatic IceMaker with fixed water connection.



Conjure up ice cubes quickly: Fill the tank with water, let it freeze and then release the finished ice cubes with a twist.



If no fixed water connection is available, there is an IceMaker with a water tank in the fridge compartment.

Connectivity



The SmartDeviceBox allows the appliance to be controlled and used via mobile devices.
The SmartDeviceBox can be ordered as an accessory.



The SmartDeviceBox allows the appliance to be controlled and used via mobile devices.
The SmartDeviceBox is already included.

Product groups



The perfect range for wine aficionados.



Quality storage for fine cigars.



Outdoor kitchens with refrigerators also provide convenience and perfect storage outdoors.

*SmartDevice/Smart app required

Stay in touch

Our catalogue programme

Ask your Liebherr dealer for our main catalogues for freestanding and fully integrated appliances and for our specials. All catalogues are also available for download at home.liebherr.com.



SmartDevice app: The smart companion for your Liebherr. Operate your appliances conveniently via app, receive important status messages and benefit from many other services relating to your fridge.



HNGRY: The smart every-day assistant for shopping, storage and supplies. The app helps you organise your shopping perfectly, keep an eye on your supplies at all times, and store them correctly.



You can download our apps here.



This guarantee is granted free of charge for selected freestanding fridge-freezers. With our manufacturer's guarantee, you will not incur any costs for repair and service for 10 years. For more information, registration and guarantee conditions, go to: home.liebherr.com/guarantee









Liebherr-Great Britain Ltd.

Normandy Lane, Stratton Business Park, Biggleswade, SG18 8QB

Tel.: +44 (0) 3330 147 888

Email Sales: LGB.RefrigerationSales@liebherr.com Customer Service: LGB.Refrigeration@liebherr.com