

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

Product Information Sheet

Supplier's name or trade mark	Liebherr
Supplier's address	Liebherr-Hausgeräte GmbH Memminger Straße 77-79 D-88416 Ochsenhausen
Model identifier	IKB 3560_992963951

Electrical data

Voltage	220-240 V ~
Frequency	50 Hz
Rated current	1.2 A

Type of refrigerating appliance

Low-noise appliance	no	Design type	built-in
Wine storage appliance	no	Other refrigerating appliance	yes

General product parameters

Parameter		Value	Parameter	Value
Overall dimensions (millimeter)	Height	1770	Total volume (dm ³ or l)	309
	Width	559		
	Depth	544		
EEL	100	Energy efficiency class	E	
Airborne acoustical noise emissions (dB(A) re 1pW)	37	Airborne acoustical noise emissions class	C	
Annual energy consumption (kWh/a)	155.86	Climate class	extended temperate, temperate, subtropical, tropical	
Minimum ambient temperature (°C) for which the refrigerating appliance is suitable	10	Maximum ambient temperature (°C) for which the refrigerating appliance is suitable	43	
Winter setting	no			

Compartment Parameters

Compartment type		Compartment parameters and values			
		Compartment Volume (dm ² or l)	Recommended temperature setting (°C)	Freezing capacity (kg/24h)	Defrost type (auto-defrost=A, manual defrost=M)
Pantry	no	-	-	-	-
Wine storage	no	-	-	-	-
Cellar	no	-	-	-	-
Fresh food	yes	215.2	5	-	A
Chill	yes	94.1	0	-	A
0-star or ice-making	no	-	-	-	-
1-star	no	-	-	-	-
2-star	no	-	-	-	-
3-star	no	-	-	-	-
4-star	no	-	-	-	-
2-star section	no	-	-	-	-
Variable temperature compartment	no	-	-	-	-

For 4-star compartments

Fast freeze facility	-
----------------------	---

Light source parameters

Type of light source 1	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 2	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 3	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 4	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 5	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G

Type of light source 6	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 7	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 8	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G
Type of light source 9	Technology	LED
	Directionality	DLS
	Mains	NMLS
	Connected	no
	Colour tuneable	no
	Envelope	no
	High luminance	no
	Anti glare shield	no
	Dimmable	only with specific dimmers
	Energy efficiency class	G

Minimum duration of the guarantee offered by the manufacturer: 24 months

Additional Information: -

Weblink: <https://home.liebherr.com/>

The energy consumption was confirmed by measurements according to EN 62552:2020.