

BLU
Performance

An Optical Highlight in BlackSteel

Quality, Design and Innovation



SBSbs 8673 (SGNPbs 4365 & SKBbs 4350)



SKBbs 4350

LIEBHERR



BlackSteel surface: An absolutely stunning black stainless steel paired with Liebherr's premium SmartSteel finish. On BlackSteel models, our patented door handle is designed in complementary aluminium.



BioFresh: When stored at Biofresh's precisely maintained temperature of 0°C and correct humidity level, nutrients in your food are retained. Our BioFresh drawers fully extend on telescopic rails and feature a self-closing mechanism.



PowerCooling: A high-performance system that allows freshly stored items to be chilled rapidly while maintaining an even temperature throughout the interior. In this energy-efficient BluPerformance range, the fan switches off when the appliance door is opened, saving valuable energy.

Introducing the **SBSbs 8673** freestanding Side-by-Side fridge-freezer, an optical highlight in BlackSteel! The BluPerformance range is characterised by premium-quality materials, craftsmanship in every single detail, and precision touchscreen electronic controls. The integration of all the refrigeration components in the base of the appliance, coupled with optimised electronic controls, ensures maximum energy efficiency, greater net capacity, and enhanced freezer compartment ergonomics. BioFresh technology keeps your stored food much fresher for longer. To maintain the air quality in your appliance, it is recommended to change the activated charcoal filter² every 12 months.


SBSbs 8673

Premium




Refrigerator capacity litre	367
BioFresh comp. litre	133
Freezer capacity litre	262
Number of shelves	6
Number of door racks	5
Number of freezer drawers	9 with LED
Number of BioFresh drawers	3 with LED
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	Stainless steel with BlackSteel / Stainless steel with BlackSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	Visual and audible
Defrost type	Automatic
Interior light	LED lighting fridge & freezer
Door alarm	Visual and audible
IceMaker	Fixed water connection 20mm (3/4")
Ice cube output kg/24h	0.8
SoftSystem	Yes
Door hinges	Left, right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Gross / Net weight kg	176.6 / 164.5
Voltage V/Hz	220-240 / 50 / 60

Installation Diagram



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. This increases the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Water Connection



a = 1100 mm
b = 700 mm
c = 110 mm

M = Solenoid valve

Plumbing must be installed adjacent to the side of the appliance which contains the IceMaker.

Water pressure must be between 0.15 MPa and 0.6 MPa (1.5 bar - 6 bar)

² Available accessory: Activated Charcoal Filter (Part no. 98811600)

Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.