# **HCB 2090**

Fully Integrated Appliances

# LIEBHERR

### **Refrigeration and Freezing**







home.liebherr.com

Energy consumption (kWh / y) 580  Estimated Yearly Energy Cost* in US \$ 81  Sound rating** dB(A) 43  Total refrigerator capacity cu.ft. (I) 12.9(365)  BioFresh compartment cu.ft. (I) 2.4(6.9)  Freezer capacity cu.ft. (I) 6.0(170)  Electronic control MagicEye with digital temp. display, touch electronic  Defrost type Automatic  Interior light LED Light column both sides  Number of shelves 4  Number of BioFresh drawers 2  Number of BioFresh drawers 2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)  Door hinges		HCB 2090
Sound rating** dB(A) 43  Total refrigerator capacity cu.ft. (I) 12.9(365)  BioFresh compartment cu.ft. (I) 2.4(6.9)  Freezer capacity cu.ft. (I) 6.0(170)  Electronic control MagicEye with digital temp. display, touch electronic  Defrost type Automatic  Interior light LED Light column both sides  Number of shelves 4  Number of door racks 6  Number of BioFresh drawers 2  Number of freezer drawers 2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	Energy consumption (kWh/y)	580
Total refrigerator capacity cu.ft. (I)  BioFresh compartment cu.ft. (I)  Freezer capacity cu.ft. (I)  Electronic control  MagicEye with digital temp. display, touch electronic  Defrost type  Automatic  Interior light  LED Light column both sides  Number of shelves  4  Number of BioFresh drawers  2  Number of freezer drawers  2  Refrigerator Temperature range °F (°C)  Freezer Temperature range °F (°C)  Water filter  Ice maker  Ice cube output lbs. (kg.)  12.9(365)  2.4(6.9)  4.00  Automatic  LED Light column both sides  4  Number of heected unders  2  **Total column both sides  4  **Total column both sides  *	Estimated Yearly Energy Cost* in US \$	81
BioFresh compartment cu.ft. (I)  Freezer capacity cu.ft. (I)  Electronic control  Defrost type  Automatic  Interior light  Number of shelves  Number of BioFresh drawers  Refrigerator Temperature range °F (°C)  Water filter  Ice maker  Lec 2.4(6.9)  MagicEye with digital temp.  display, touch electronic  Automatic  LED Light column both sides  4  Number of door racks  6  Number of BioFresh drawers  2  Refrigerator Temperature range °F (°C)  Water filter  Ice maker  Fixed water connection  Ice cube output lbs. (kg.)  6.0(170)	Sound rating** dB(A)	43
Freezer capacity cu.ft. (I)  Electronic control  MagicEye with digital temp. display, touch electronic  Defrost type  Automatic  Interior light  LED Light column both sides  Number of shelves  4  Number of BioFresh drawers  2  Number of freezer drawers  2  Refrigerator Temperature range °F (°C)  Freezer Temperature range °F (°C)  Water filter  Ice maker  Ice cube output lbs. (kg.)  Ice cube stock lbs. (kg.)  Automatic  LED Light column both sides  4  Number of heet column both sides  4  Number of shelves  4  Number of BioFresh drawers  2  Refrigerator Temperature range °F (°C)  +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C)  3.1 (1.4)  Ice cube stock lbs. (kg.)  6(2.7)	Total refrigerator capacity cu.ft. (l)	12.9(365)
Electronic control display, touch electronic  Defrost type Automatic  Interior light LED Light column both sides  Number of shelves 4  Number of door racks 6  Number of BioFresh drawers 2  Number of freezer drawers 2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	BioFresh compartment cu.ft. (I)	2.4(6.9)
display, touch electronic  Defrost type Automatic  Interior light LED Light column both sides  Number of shelves 4 Number of door racks 6 Number of BioFresh drawers 2 Refrigerator Temperature range °F (°C) Freezer Temperature range °F (°C) Water filter Lee maker Fixed water connection  Ice cube output lbs. (kg.)  Jet 2 Automatic  Automatic	Freezer capacity cu.ft. (l)	6.0(170)
Defrost type Automatic Interior light LED Light column both sides Number of shelves 4 Number of door racks 6 Number of BioFresh drawers 2 Number of freezer drawers 2 Refrigerator Temperature range °F (°C) Freezer Temperature range °F (°C) Water filter  Ice maker Fixed water connection Ice cube output lbs. (kg.) Ice cube stock lbs. (kg.)  Automatic  LED Light column both sides  4  Number of shelves 4  Number of BioFresh drawers 2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C) +7°F to -17°F (-14°C to -27°C)  Water filter  yes Ice cube output lbs. (kg.) 3.1 (1.4) Ice cube stock lbs. (kg.)	Electronic control	MagicEye with digital temp.
Interior light  LED Light column both sides  Number of shelves  4  Number of door racks  6  Number of BioFresh drawers  2  Number of freezer drawers  2  Refrigerator Temperature range °F (°C)  Freezer Temperature range °F (°C)  Water filter  lce maker  Ice cube output lbs. (kg.)  Ice cube stock lbs. (kg.)  LED Light column both sides  4   LED Light column both sides  4   1  1  1  1  1  1  1  1  1  1  1  1		display, touch electronic
Number of shelves 4  Number of door racks 6  Number of BioFresh drawers 2  Number of freezer drawers 2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	Defrost type	Automatic
Number of door racks 6 Number of BioFresh drawers 2 Number of freezer drawers 2 Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C) Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C) Water filter yes Ice maker Fixed water connection Ice cube output lbs. (kg.) Ice cube stock lbs. (kg.) 6(2.7)	Interior light	LED Light column both sides
Number of BioFresh drawers  2 Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C) Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C) Water filter  Ice maker  Ice maker  Fixed water connection Ice cube output lbs. (kg.)  Ice cube stock lbs. (kg.)  6(2.7)	Number of shelves	4
Number of freezer drawers  2  Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C)  Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter  yes  Ice maker  Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	Number of door racks	6
Refrigerator Temperature range °F (°C) +37°F to +45°F (+3°C to +7°C) Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C) Water filter yes Ice maker Fixed water connection Ice cube output lbs. (kg.) 3.1 (1.4) Ice cube stock lbs. (kg.) 6(2.7)	Number of BioFresh drawers	2
Freezer Temperature range °F (°C) +7°F to -17°F (-14°C to -27°C)  Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	Number of freezer drawers	2
Water filter yes  Ice maker Fixed water connection  Ice cube output lbs. (kg.) 3.1 (1.4)  Ice cube stock lbs. (kg.) 6(2.7)	Refrigerator Temperature range °F (°C)	+37°F to +45°F (+3°C to +7°C)
lce maker Fixed water connection lce cube output lbs. (kg.) 3.1 (1.4) lce cube stock lbs. (kg.) 6(2.7)	Freezer Temperature range °F (°C)	+7°F to -17°F (-14°C to -27°C)
Ice cube output lbs. (kg.)  3.1 (1.4)  Ice cube stock lbs. (kg.)  6(2.7)	Water filter	yes
Ice cube stock lbs. (kg.) 6(2.7)	Ice maker	Fixed water connection
	Ice cube output lbs. (kg.)	3.1 (1.4)
Door hinges right	Ice cube stock lbs. (kg.)	6(2.7)
	Door hinges	right
Product dimensions	Product dimensions	
in inch (H / W / D) 79 13/16" / 35 7/8" / 24 1/16	in inch (H/W/D)	79 13/16" / 35 7/8" / 24 1/16"
in cm (H/W/D) 202.7/91/61.5	in cm (H/W/D)	202.7/91/61.5
Cut out dimensions	Cut out dimensions	
in inch (H / W / D) 80"-815/8" / 361/16" / 25"	in inch (H/W/D)	80"-815/8" / 361/16" / 25"
in cm (H / W / D) 203.2-207.2/91.5/63.5	in cm (H/W/D)	203.2-207.2/91.5/63.5
Net weight lbs. (kg) 363.8(165.0)	Net weight lbs. (kg)	363.8(165.0)
Voltage V / Hz 115/60	Voltage V / Hz	115/60

<sup>\*</sup> Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.



Accessories	
Water Filter	9880980/7440002
Stainless Steel Round Handles	9900327
Brushed Aluminimum Square Handle	s 9900329
Door Stopper 90*	9096699
Stainless Steel Panels Refrigerator 8	9900333
Stainless Steel Panels Refrigerator 8	9900331
Stainless Steel Panels Freezer Draw	ers 9900323

#### **Features**



Preserve just-bought groceries for optimum food freshness, while sealing in flavors and maintaining essential vitamins and minerals.



Lengthen the shelf life and preserve the flavor of your foods with a dual refrigeration system that creates ideal conditions in both the refrigerator and freezer.




Liebherr's automatic IceMaker produces perfect ice cubes and keeps a constant supply on hand for every occasion.



Store food securely within reach thanks to fully extendable pull-out drawers. The SoftTelescopic system provides convenient and reliable self-retraction with soft closing.

<sup>\*\*</sup> Noise output - according to EN 60704-3

## **Diagrams**



## **Panel Dimensions** Inset Installation Style Frameless Installation Style – 1/8" minimum Ш m (915 mm) 1/8" 13 - 7/16' 13 - 7/16" (341 mm) (341 mm) **¥** 1/8" 16 - 11/16" 4" (102 mm) 4" (102 mm) The height of this panel cannot be reduced for higher toe kicks as it will reveal structural elements of the

appliance. Instead, install appliance on a platform and adjust the opening height to accommodate.

Cabinet opening A	Refrigerator door panel B
80"	45-1/2" (1156 mm)
84"	49-1/4" (1251 mm)

Cabinet opening A	Refrigerator door panel B
80"	45-5/8" (1159 mm)
84"	49-3/4" (1264 mm)


Minimum panel thickness is 5/8" (16 mm).

Maximum panel thickness is 3/4" (20 mm).

Maximum weight of the refrigerator panel is 60 lbs (27 kg).

Maximum weight of each freezer panel is 26.5 lbs (12 kg).

## **Cutout Dimensions**



Factory available stainless steel panels are designed for an insetinstallation only and require a cabinet / gable depth of 24 - 3/4".

#### Inset cabinet Depth D

24" + panel thickness

#### Frameless cabinet Depth D

#### **Ventilation Requirements**



The appliance do not require ventilation considerations in the cabinetry. The required airflow is directed through the toe kick base. It is important to use the provided cover grille for the ventilation opening. This opening must not be covered.

Subject to modification. For up-to-date information, visit home.liebherr.com.

Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.