

to the

Quality, Design and Innovation

S YEARS

ENERG) RATINO

158

nodels at www.energyrating.gov.au









Door-on-door technology: Allows custom panels to be affixed directly onto the appliance door so that the hinges are concealed, plus the cabinet and the fridge door open as one, ensuring a wide range of design options and easy installation.



SoftTelescopic: A highly practical self-retracting, selfclosing feature. Our SoftTelescopic technology guarantees elimination of slamming even when the shelf is fully loaded.




MagicEye control system: Our LED control panel ensures all functions are easy and convenient to use as well as guaranteeing that the settings selected remain accurate and constant.

The precision control system of the **SUIKo 1550** creates a stunning visual impact and enhances the ease and convenience of use. The SuperCool function quickly reduces the temperature of the fridge compartment; ideal for rapidly cooling down freshly stored food. The innovative LED light and the special satin finish of the light cover produces a pleasant lighting atmosphere.

The pull-out fridge compartment is mounted on soft telescopic rails. It has a practical bottle shelf and a removable fruit and vegetable drawer. The large drawer can also be divided into two equal-sized compartments, with more storage space underneath.

Additionally you can opt for our high-quality, easy-to-fit stainless steel panel and handle¹ which enable the model's seamless integration into any kitchen!

SUIKo 1550 Premium	Soft Telescopic	
Energy consumption (kWh/yr) I Star rating		158 I 3.5
Compressors		1
Total Usable Litres		124
Refrigerator Usable Litres		124
MagicEye control system I Display		 I Digital
Child proof setting for display & temperature		•
Standard lighting		•
Door open warning signal		•
Optional extra stainless steel panel & handle		•
Fruit & vegetable drawer on telescopic rails		1
SuperCool		•
GlassLine shelves		•
Egg tray		
Automatic refrigerator defrosting		



Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.

Door hinges

Made in

Voltage (V) | Rated Current (A)

Pull-out trollev

220-240 / 1.2

Germany