

BLU
Performance

The Big, Cool Combination

Quality, Design and Innovation



SBSes 8484 (SBNes 4265 & SKBes 4360)



SBNes 4265



SKBes 4360

LIEBHERR



2.4" Touchscreen Display: Located behind the appliance door, this high-resolution and high-contrast 2.4" touchscreen display can be read from any angle. Stored menu options are intuitive and easy-to-operate.



BioFresh-Plus: With the adjustable temperature range of 0°C and -2°C, BioFresh-Plus technology offers even more flexibility for your produce. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe.





PowerCooling: A high-performance system that allows freshly stored items to be chilled rapidly while maintaining an even temperature throughout the interior. In this energy-efficient BluPerformance range, the fan switches off when the appliance door is opened, saving valuable energy.

The BluPerformance **SBSes 8484** Side-by-Side fridge-freezer combines plenty of storage space with perfect cooling performance for long-lasting freshness. BioFresh-Plus allows added storage flexibility and a longer shelf life for fruits, vegetables, fish, meat, and dairy products. With elegant and timeless design in combination with high-quality materials, components, and workmanship, this model will continue to catch the eye for many years to come. To maintain the air quality in your appliance, it is recommended to change the activated charcoal filter² every 12 months.

SBSes 8484
PremiumPlus

- Bio Fresh-Plus
- No Frost
- Ice Maker
- Soft System
- Soft Telescopic
- Smart Steel

Refrigerator capacity litre	366
BioFresh comp. litre	304
Freezer capacity litre	126
Number of shelves	8
Number of door racks	5
Number of freezer drawers	5 with LED
Number of BioFresh drawers	5 with LED
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	Stainless steel with SmartSteel / Stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	Visual and audible
Defrost type	Automatic
Interior light	LED ceiling lighting with dimmer function
Door alarm	Visual and audible
IceMaker	Fixed water connection 20mm (3/4")
Ice cube output kg/24h	1.2
SoftSystem	Yes
Door hinges	Left, right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Gross / Net weight kg	186.3 / 166
Voltage V/Hz	220-240 / 50 / 60



² Available accessory: Activated Charcoal Filter (Part no. 98811600)

Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.