

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

## Product Information Sheet

|                               |  |
|-------------------------------|--|
| Supplier's name or trade mark | Liebherr   |
| Supplier's address            | Liebherr-Hausgeräte GmbH<br>Memminger Straße 77-79<br>D-88416 Ochsenhausen |
| Model identifier              | CFd 2085_993860451   |

### Electrical data

|               |             |
|---------------|-------------|
| Voltage       | 220-240 V ~ |
| Frequency     | 50 Hz       |
| Rated current | 1.5 A       |

### Type of refrigerating appliance

|                        |    |                               |              |
|------------------------|----|-------------------------------|--------------|
| Low-noise appliance    | no | Design type                   | freestanding |
| Wine storage appliance | no | Other refrigerating appliance | yes          |

### General product parameters

| Parameter  |        | Value  | Parameter  | Value |
|--|--------|--|--|-------|
| Overall dimensions (millimeter)  | Height | 825  | Total volume (dm <sup>3</sup> or l)                  | 248   |
|  | Width  | 1255   |  |       |
|  | Depth  | 722  |  |       |
| EEL  | 75     | Energy efficiency class  | D  |       |
| Airborne acoustical noise emissions (dB(A) re 1pW)                                 | 38     | Airborne acoustical noise emissions class  | C  |       |
| Annual energy consumption (kWh/a)  | 162.00 | Climate class  | extended temperate, temperate, subtropical, tropical |       |
| Minimum ambient temperature (°C) for which the refrigerating appliance is suitable | 10     | Maximum ambient temperature (°C) for which the refrigerating appliance is suitable | 43   |       |
| Winter setting   | no     |  |  |       |

## Compartment Parameters

| Compartment type                 |     | Compartment parameters and values         |                                      |                            |   |
|----------------------------------|-----|---|--------------------------------------|----------------------------|---|
|                                  |     | Compartment Volume (dm <sup>2</sup> or l) | Recommended temperature setting (°C) | Freezing capacity (kg/24h) | Defrost type (auto-defrost=A, manual defrost=M) |
| Pantry                           | no  | -   | -                                    | -                          | -   |
| Wine storage                     | no  | -   | -                                    | -                          | -   |
| Cellar                           | no  | -   | -                                    | -                          | -   |
| Fresh food                       | no  | -   | -                                    | -                          | -   |
| Chill                            | no  | -   | -                                    | -                          | -   |
| 0-star or ice-making             | no  | -   | -                                    | -                          | -   |
| 1-star                           | no  | -   | -                                    | -                          | -   |
| 2-star                           | no  | -   | -                                    | -                          | -   |
| 3-star                           | no  | -   | -                                    | -                          | -   |
| 4-star                           | yes | 248.0                                     | -18                                  | 10.00                      | M   |
| 2-star section                   | no  | -   | -                                    | -                          | -   |
| Variable temperature compartment | no  | -   | -                                    | -                          | -   |

### For 4-star compartments

|                      |     |
|----------------------|-----|
| Fast freeze facility | yes |
|----------------------|-----|

**Light source parameters**

|                      |                         |    |
|----------------------|-------------------------|----|
| Type of light source | Technology              |    |
|                      | Directionality          |    |
|                      | Mains                   |    |
|                      | Connected               |    |
|                      | Colour tuneable         |    |
|                      | Envelope                |    |
|                      | High luminance          |    |
|                      | Anti glare shield       |    |
|                      | Dimmable                | no |
|                      | Energy efficiency class |    |

**Minimum duration of the guarantee offered by the manufacturer:** 24 months

**Additional Information:** -

**Weblink:** <https://home.liebherr.com/>

**The energy consumption was confirmed by measurements according to EN 62552:2020.**