

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

## Product information sheet

|                               |   |
|-------------------------------|---|
| Supplier's name or trade mark | Liebherr  |
| Supplier's address            | Liebherr-Hausgeräte GmbH<br>Memminger Straße 77-79<br>88416 Ochsenhausen<br>Germany |
| Model identifier              | CBNbe 5778_993332051  |

### Electrical data

|                   |             |
|-------------------|-------------|
| Voltage           | 220-240 V ~ |
| Frequency         | 50/60 Hz    |
| Connection rating | 1.4 A       |

### Type of refrigerating appliance

|                        |    |                               |              |
|------------------------|----|-------------------------------|--------------|
| Low-noise appliance    | no | Design type                   | freestanding |
| Wine storage appliance | no | Other refrigerating appliance | yes          |

### General product parameters

| Parameter   |        | Value                                    | Parameter  | Value |
|---|--------|--|--|-------|
| Overall dimensions (millimetre)   | Height | 2010                                     | Total volume (dm <sup>3</sup> or l)                  | 392   |
|   | Width  | 700                                      |  |       |
|   | Depth  | 665                                      |  |       |
| EEL   | 64     | Energy efficiency class                  | C  |       |
| Airborne acoustical noise emissions (dB(A) re 1 pW)                                 | 35     | Airborne acoustical noise emission class | B  |       |
| Annual energy consumption (kWh/a)   | 187    | Climate class                            | extended temperate, temperate, subtropical, tropical |       |
| Minimum ambient temperature (°C), for which the refrigerating appliance is suitable | 10     |  |  |       |
| Maximum ambient temperature (°C), for which the refrigerating appliance is suitable | 43     | Winter setting                           | no   |       |

## Compartment Parameters

| Compartment type                 |     | Compartment parameters and values         |   |                             |   |
|----------------------------------|-----|---|---|-----------------------------|---|
|                                  |     | Compartment Volume (dm <sup>3</sup> or l) | Recommended temperature setting for optimised food storage (°C) | Freezing capacity (kg/24 h) | Defrosting type<br>(auto-defrost = A, manual defrost = M) |
| Pantry                           | no  | -   | -   | -                           | -   |
| Wine storage                     | no  | -   | -   | -                           | -   |
| Cellar                           | no  | -   | -   | -                           | -   |
| Fresh food                       | yes | 168.5                                     | 5   | -                           | A   |
| Chill                            | yes | 112.6                                     | 0   | -                           | A   |
| 0-star or ice-making             | no  | -   | -   | -                           | -   |
| 1-star                           | no  | -   | -   | -                           | -   |
| 2-star                           | no  | -   | -   | -                           | -   |
| 3-star                           | no  | -   | -   | -                           | -   |
| 4-star                           | yes | 111.6                                     | -18   | 9.0                         | A   |
| 2-star section                   | no  | -   | -   | -                           | -   |
| Variable temperature compartment | no  | -   | -   | -                           | -   |

### For 4-star compartments

|                      |     |
|----------------------|-----|
| Fast freeze facility | yes |
|----------------------|-----|

### For wine storage appliances

|                                 |   |
|---------------------------------|---|
| Number of standard wine bottles | - |
|---------------------------------|---|

**Light source parameters**

|                |                          |     |
|----------------|--------------------------|-----|
| Light Source 4 | Lighting technology used | LED |
|                | Energy efficiency class  | G   |
| Light Source 3 | Lighting technology used | LED |
|                | Energy efficiency class  | G   |
| Light Source 2 | Lighting technology used | LED |
|                | Energy efficiency class  | G   |
| Light Source 1 | Lighting technology used | LED |
|                | Energy efficiency class  | G   |

**Minimum duration of the guarantee offered by the manufacturer:** 24 month

---

**Additional information:** -

---

**Weblink to the manufacturer's website, where the information in point 4(a) Annex of Commission Regulation (EU) 2019/2019 (4) (2) is found:** <https://home.liebherr.com/>

---

The energy consumption was confirmed by measurements according to EN 62552:2020.