

# A Spacious Refrigerator & Freezer All In One

Quality, Design and Innovation



SBSef 7242 (SGNef 3036 & Skef 4260)

# LIEBHERR



**VarioSpace:** Nearly all freezers include drawers and glass shelves that can be conveniently removed to create extra storage space. It's Liebherr's very practical solution to quickly accommodate even bulky items.



**SmartSteel:** With SmartSteel used on the appliance door the visibility of fingerprints is reduced, making it very easy to clean. Maintain this beautiful door exterior simply with a wipe of a clean, dry or damp cloth.



**NoFrost:** The food is frozen with chilled recirculating air, and any humidity is expelled. As a result, the freezer is always free of ice, and food no longer frosts over. NoFrost convenience makes defrosting a thing of the past.

A spacious refrigerator and freezer all in one! The Liebherr **SBSef 7242** fridge-freezer brings together high quality components, meticulous workmanship, as well as easy-to-use precision electronics. This side-by-side, freestanding model guarantees freshness, user friendliness and energy efficiency.

The freezer compartment offers up to eight drawers to provide an extra-large capacity for freezing your food. Transparent vegetable bins in the refrigerator compartment provide a clear view of the stored food and slide out effortlessly on the roller system.


**SBSef 7242**

Comfort



Sound rating dB(A) *	42
Refrigerator capacity litre	391
Freezer capacity litre	261
Number of shelves	7
Number of door racks	5
Number of freezer drawers	8
Electronic control	LCD display, touch electronic
Door / side walls	Stainless Steel with SmartSteel / Silver
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -28°C
Temperature alarm	Visible and audible
Defrost type	Automatic
Interior light	LED
Door alarm	Audible
Door hinges	Left, right
Product dimensions (H/W/D) cm	185.2 / 121 / 63
Gross / Net weight kg	160.6 / 151.7
Voltage V/Hz	220-240 / 50

**Installation Diagram**



1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. This increases the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

\* Noise output - according to EN 60704-3

*Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.*