

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

## Product Information Sheet

|                               |   |
|-------------------------------|---|
| Supplier's name or trade mark | LIEBHERR  |
| Supplier's address            | Liebherr-Hausgeräte GmbH<br>Memminger Straße 77-79<br>88416 Ochsenhausen<br>Germany |
| Model identifier              | EWTgb 3583_992823351  |

### Electrical data

| Parameter     | Value   | Parameter      | Value |
|---------------|---------|----------------|-------|
| Voltage (V ~) | 220-240 | Frequency (Hz) | 50    |

### Type of refrigerating appliance

|                        |     |                               |          |
|------------------------|-----|-------------------------------|----------|
| Low-noise appliance    | no  | Design type                   | built-in |
| Wine storage appliance | yes | Other refrigerating appliance | no       |

### General product parameters

|   |        |   |                                     |     |
|---|--------|---|-------------------------------------|-----|
| Overall dimensions (millimetre)   | Height | 1816  | Total volume (dm <sup>3</sup> or l) | 271 |
|   | Width  | 595   |                                     |     |
|   | Depth  | 572   |                                     |     |
| EEl   | 185    | Energy efficiency class   | G                                   |     |
| Airborne acoustical noise emissions (dB(A) re 1 pW)                                 | 32     | Airborne acoustical noise emission class  | B                                   |     |
| Annual energy consumption (kWh/a)   | 178    | Climate class   | extended temperate                  |     |
| Minimum ambient temperature (°C), for which the refrigerating appliance is suitable | 10     | Maximum ambient temperature (°C), for which the refrigerating appliance is suitable | 32                                  |     |
| Winter setting  | no     |   |                                     |     |

**Compartment Parameters**

| Compartment type                 |     | Compartment Volume (dm <sup>3</sup> or l) | Recommended temperature setting for optimised food storage (°C) | Freezing capacity (kg/24 h) | Defrosting type (auto-defrost = A, manual defrost = M) |
|----------------------------------|-----|---|---|-----------------------------|--|
| Pantry                           | no  | -   | -   | -                           | -  |
| Wine storage                     | yes | 271                                       | 12  | -                           | A  |
| Cellar                           | no  | -   | -   | -                           | -  |
| Fresh food                       | no  | -   | -   | -                           | -  |
| Chill                            | no  | -   | -   | -                           | -  |
| 0-star or ice- making            | no  | -   | -   | -                           | -  |
| 1-star                           | no  | -   | -   | -                           | -  |
| 2-star                           | no  | -   | -   | -                           | -  |
| 3-star                           | no  | -   | -   | -                           | -  |
| 4-star                           | no  | -   | -   | -                           | -  |
| 2-star section                   | no  | -   | -   | -                           | -  |
| Variable temperature compartment | no  | -   | -   | -                           | -  |

**For 4-star compartments**

|                      |    |
|----------------------|----|
| Fast freeze facility | no |
|----------------------|----|

**For wine storage appliances**

|                                 |   |
|---------------------------------|---|
| Number of standard wine bottles | - |
|---------------------------------|---|

**Light source parameters**

| Light Source | Lighting technology used | Energy efficiency class |
|--------------|--------------------------|-------------------------|
| 1            | LED                      | G                       |
| 2            | LED                      | G                       |

**Additional information**

Minimum duration of the guarantee offered by the manufacturer: 24 month

Additional information: -

Weblink to the manufacturer's website, where the information in point 4(a) Annex of Commission Regulation (EU) 2019/2019 is found: <https://home.liebherr.com/>

The energy consumption was confirmed by measurements according to EN 62552:2020.