

Convenience at  
Your Fingertips

Quality, Design and Innovation



SUIG 1514

**LIEBHERR**



**Door-on-door technology:** Allows custom panels to be affixed directly onto the appliance door so that the hinges are concealed, plus the cabinet and the fridge door open as one, ensuring a wide range of design options and easy installation.



**SoftSystem:** In built-in appliances, SoftSystem technology allows doors to close automatically and gently from 30° to eliminate slamming even when fully loaded.



The **SUIG 1514** undercounter freezer is suitable for Side-by-Side installation together with Liebherr's **SUIK 1510** undercounter fridge for integrated use.

*Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.*

Introducing the **SUIG 1514** undercounter freezer by Liebherr. For frozen goods, this model will be perfect. SmartFrost technology allows food to freeze faster and reduces ice build-up, making defrosting simpler and quicker. No ventilation grill is needed in the worktop as airflow enters and exits from the front of this appliance. Additionally, for convenience and safety, SoftSystem ensures that the freezer door closes automatically and gently from an opening angle of approximately 30°.

The compact SUIG 1514 undercounter freezer is the perfect companion for the SUIK 1510 undercounter fridge. Best suited for studio apartments and small families – bid farewell to space or food wastage!

**SUIG 1514**


Comfort

Smart Frost


Soft System

Sound rating dB(A) *	36
Freezer capacity litre	95
Number of door racks	0
Number of freezer drawers	3
Electronic control	MagicEye on front, buttons
Freezer temperature range °C	-14°C to -26°C
Defrost type	Manual
Interior light	No
Door alarm	Visual and audible
Door type	Door-on-door
Integrated lock	No
SoftSystem	Yes
Door hinges	Left, reversible
Product dimensions (H/W/D) cm	82 - 88 / 59.7 / 55
Cut out dimensions (H/W/D) cm	88.2 - 88 / 60 / min. 55
Gross / Net weight kg	44 / 38.2
Voltage V/Hz	220-240 / 50

**Installation Diagram**



**Ventilation Diagram**



- The airflow cavity must be at least 200 cm<sup>2</sup>  
 - The unit's energy consumption will increase if there is insufficient air flow.

\* Noise output - according to EN 60704-3