

For All Who Appreciate
Good Taste

Quality, Design and Innovation



LIEBHERR



Electronic LCD Display: Intuitive navigation of touch electronic control system enables tailored storage options. The digital temperature display can be viewed via the UV tinted glass door.



Tinted glazed door: The tinted glass door provides not only a perfect UV protection, but also an optimum glance at wine.



LED lighting: The light in the cooling compartments can be dimmed to give a pleasing ambient light inside the appliance.

For wine collectors, temperature, humidity, vibration, and light are the most important elements of wine storage. As a dual-temperature zone wine cabinet, the **UWTes 1672** clearly addresses all four areas and is perfect for all reds, whites, and champagne.

This appliance ventilates through the toe kick, hence no counterslot is necessary, and can be integrated easily and elegantly into your customised kitchen. It also boasts a digital temperature display with visibility through elegant glass doors.

UWTes 1672

Vinidor


LED

Wine

Telescopic Rails

Energy consumption (kWh/y)	190
Sound rating dB(A) *	38
Total capacity litre	94
Max No. of Bordeaux bottles (0.75l) **	34
Number of shelves	5
Shelves on telescopic rails	3
Shelf material	Beech wood shelves
Presentation shelf	0
Electronic control	LCD display, touch electronic
Temperature range °C	+5°C to +20°C
Temperature zones	2
Temperature alarm	Visual and audible
Interior light	LED
Door alarm	Audible
Safety thermostat	Yes
Activated charcoal filter	Yes
Door type	Glazed door with stainless steel frame
Integrated lock	Yes
SoftSystem	No
Door hinges	Right, reversible
Product dimensions (H/W/D) cm	81.8 / 59.7 / 57
Cut out dimensions (H/W/D) cm	82 - 87 / 60 / min. 58
Gross / Net weight kg	57 / 49
Voltage V/Hz	220-240 / 50

Installation Diagram



Activated charcoal filter
Part No.: 988128900

* Noise output - according to EN 60704-3

** These models are only bound for storing wine. Max. DIN norm bordeaux bottle capacity (0.75 l) as per norm NF H 35-124 (H:300.5 mm, Ø 76.1mm)