

BLU
Performance

Freshness With
Style And Elegance

Quality, Design and Innovation

SBSes 8673 (SGNPes 4365 & SKBes 4350)

LIEBHERR



2.4" Touchscreen Display: Located behind the appliance door, this high-resolution and high-contrast 2.4" touchscreen display can be read from any angle. Stored menu options are intuitive and easy-to-operate.



BioFresh: When stored at Biofresh's precisely maintained temperature of 0°C and correct humidity level, nutrients in your food are retained. Our BioFresh drawers fully extend on telescopic rails and feature a self-closing mechanism.



PowerCooling: A high-performance system that allows freshly stored items to be chilled rapidly while maintaining an even temperature throughout the interior. In this energy-efficient BluPerformance range, the fan switches off when the appliance door is opened, saving valuable energy.



Volume, efficiency, economy, ease of use, and outstanding design are the key features of the **SBSes 8673** side-by-side fridge-freezer from Liebherr's BluPerformance series. BioFresh technology allows your fruits, vegetables, meat, fish, and dairy products to stay fresher for longer. Meanwhile NoFrost technology ensures that this appliance never has to be defrosted. And thanks to its premium SmartSteel surface, this timelessly elegant model is easy to clean and will definitely be a visual highlight in your home!

To maintain the air quality in your appliance, it is recommended to change the activated charcoal filter² every 12 months.

SBSes 8673
Premium

- Bio Fresh
- No Frost
- Ice Maker
- Soft System
- Soft Telescopic
- Smart Steel

Refrigerator capacity litre	367
BioFresh comp. litre	133
Freezer capacity litre	262
Number of shelves	6
Number of door racks	5
Number of freezer drawers	9 with LED
Number of BioFresh drawers	3 with LED
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	Stainless steel with SmartSteel / Stainless steel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	Visual and audible
Defrost type	Automatic
Interior light	LED lighting fridge & freezer
Door alarm	Visual and audible
IceMaker	Fixed water connection 20mm (3/4")
Ice cube output kg/24h	0.8
SoftSystem	Yes
Door hinges	Left, right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Gross / Net weight kg	180.4 / 161.3
Voltage V/Hz	220-240 / 50 / 60



² Available accessory: Activated Charcoal Filter (Part no. 98811600)

Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.