

GFT21S1HC

ProfiLine



 GERMAN
ENGINEERING


LIEBHERR

Food Service Freezer with Top Mount Compressor and Stainless Steel Inner Liner



Single Door Freezer with Top Mount Compressor		GFT21S1HC Profiline			
Total gross/net capacity cu.ft. (l)	21.1/20.5 (597/580)				
Exterior dimensions in inches (w/d/h) in mm (w/d/h)	27 9/16"/32 11/16"/85 1/8" 700/830/2162				
Interior dimensions in inches (w/d/h) in mm (w/d/h)	20 1/8"/25 5/8"/61 1/16" 510/650/1550				
Energy consumption in 365 days *	1533 kWh				
Ambient temperature in °F (°C)	61°F to 109°F (16°C to 43°C)				
Refrigerant	R290				
Sound rating **	65 dB(A)				
Connection rating	10.0 A/700 W				
Frequency/voltage	60 Hz/115V~				
Cooling system	forced-air				
Defrost	automatic				
Temperature range in °F (°C)	14°F to -13°F (-10°C to -25°C)				
External cabinet finish	stainless steel				
Door/lid material	stainless steel				
Internal liner material	stainless steel				
Type of control	electronic control				
Temperature display	external digital				
Alarm	visual and audible				
Alarm forwarding	yes				
Interior light	LED ceiling light				
Adjustable shelves	4				
Shelf material	304-grade stainless steel wire shelves				
Shelf load weight in lbs (kg)	132.3 (60)				
Usable shelf area in inches (mm)	20 1/8"/25 5/8" (510/650)				
Casters	casters with brake at the front, fixed casters at the rear				
Handle	full-length integrated handle				
Lock	recessed				
Self-closing door	yes				
Door hinges	right, reversible on site				
Insulation in inches (mm)	3 5/16" – 2 3/8" (83 – 60)				
Gross/net weight in lbs (kg)	346.1/288.8 (157/131)				
Accessories					
Wire shelf	7112904				
Foot pedal opener	9590659				
Side-by-Side kit	9901969				
Adjustable feet	9593397				

Unit Dimensions



* Measured unloaded at 80°F (26.6°C) ambient temperature with set point of 0°F (-17.7°C).
 ** Noise level – sound power re 1pW – according to IEC 60704-2-14.

Subject to modification. For up-to-date information, visit home.liebherr.com.