

HW 8000

Fully Integrated Appliances

LIEBHERR

Refrigeration and Freezing



home.liebherr.com



HW 8000

Energy consumption (kWh/y)	155
Estimated Yearly Energy Cost in US \$	19
Sound rating dB(A)	36
Total capacity cu.ft. (l)	9.0 (254)
Max. No. of Bordeaux bottles (0.75 l)	80
Number of shelves	10
Shelves on telescopic rails	8
Shelf material	Beech wood shelves
Presentation shelf	1
Electronic control	LCD temp. display both wine zones, touch electronic
Temperature range °F (°C)	+41 to +68 (+5 to +20)
Temperature zones	2
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	panel ready or stainless steel panel as accessory
SoftSystem	yes
Door hinges	right, reversible
Product dimensions	
in inch (H/W/D)	69 11/16"/21 15/16"/21 13.16"
in cm (H/W/D)	177/55.7/55.3
Cut out dimensions	
in inch (H/W/D)	69 13/16"-70 1/8"/22 1/16"-22 1/2"/21 11/16"
in cm (H/W/D)	177.2-178/56-57/55
Net weight lbs. (kg)	200.6 (91)
Voltage V/Hz	115/60

* Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 12 cents per kWh.

** Noise output – according to EN 60704-3

Accessories


Door opening limitation (hinge pin)	9096212
Stainless-steel door panel with handle	9901573
Air filter	9193906
Toe kick ventilation grill	9097348

Features

- Super Silent** Noise levels are kept to a minimum thanks to virtually silent, speed-controlled, and sound absorbing compressors.
- Soft System** Ensure the door closes gently to reduce any unnecessary sounds.
- Electronic Control** The electronic touch system allows temperatures to be set to the exact desired degree, from 41°F to 68°F and are clearly displayed on the LCD display for accurate readings of your desired settings
- FreshAir** The activated charcoal filter prevents odors from forming and cleans the incoming air.
- ADA Compliant** Liebherr's appliances are ADA complaint, with control panels designed to be accessible within 55" from the floor.

Diagrams


Product Dimensions



Important:

Stated product height dimensions consider leveled feet are fully inserted.

Frameless Dedicated Cabinet Box Dimensions




This is a fully integrated wine appliance designed to be completely enclosed in a dedicated kitchen cabinet. This dedicated cabinet box must be constructed in accordance with the specified dimensions and must allow for sufficient air circulation to ensure proper operation. For more details about ventilation requirements, please refer to the Design Guide.

A ventilation grill (included with the appliance) must be installed in the base of the dedicated box, for dimensions of the toe kick ventilation grill, please refer to the Design Guide. The toe kick area of the Dedicated Cabinet Box can be recessed like the rest of the kitchen cabinets.

We recommend that the power outlet be located outside the dedicated cabinet box for easy access. Free length of the power cord is 7.9 ft. (2.4m).

3" of the cabinet needs to be surface finished as it is visible when the door is open.

Door Panel Dimensions



Custom panels should be at least 5/8" (16mm) and a maximum of 3/4" (19mm) thick and they should cover the front of the dedicated cabinet box.

Maximum weight of the custom panel door is 44 lbs. (20 kg) including handle.

If using a "shaker style" panel that undershoots the minimum panel thickness, please be aware that you will need to use shorter screws than those supplied in the accessory pack.