

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

Product Information Sheet

| | |
|-------------------------------|--|
| Supplier's name or trade mark | Liebherr |
| Supplier's address | Liebherr-Hausgeräte GmbH Memminger Straße 77-79 D-88416 Ochsenhausen |
| Model identifier | ICBd 5122_999210351 |

Electrical data

| | |
|---------------|-------------|
| Voltage | 220-240 V ~ |
| Frequency | 50-60 Hz |
| Rated current | 1.4 A |

Type of refrigerating appliance

| | | | |
|------------------------|----|-------------------------------|----------|
| Low-noise appliance | no | Design type | built-in |
| Wine storage appliance | no | Other refrigerating appliance | yes |

General product parameters

| Parameter | | Value | Parameter | Value |
|--|--------|--|--|-------|
| Overall dimensions (millimeter) | Height | 1770 | Total volume (dm ³ or l) | 255 |
| | Width | 559 | | |
| | Depth | 546 | | |
| EEL | 80 | Energy efficiency class | D | |
| Airborne acoustical noise emissions (dB(A) re 1pW) | 34 | Airborne acoustical noise emissions class | B | |
| Annual energy consumption (kWh/a) | 181.80 | Climate class | extended temperate, temperate, subtropical, tropical | |
| Minimum ambient temperature (°C) for which the refrigerating appliance is suitable | 10 | Maximum ambient temperature (°C) for which the refrigerating appliance is suitable | 43 | |
| Winter setting | no | | | |

Compartment Parameters

| Compartment type | | Compartment parameters and values | | | |
|----------------------------------|-----|---|--------------------------------------|----------------------------|---|
| | | Compartment Volume (dm ³ or l) | Recommended temperature setting (°C) | Freezing capacity (kg/24h) | Defrost type (auto-defrost=A, manual defrost=M) |
| Pantry | no | - | - | - | - |
| Wine storage | no | - | - | - | - |
| Cellar | no | - | - | - | - |
| Fresh food | yes | 130.0 | 5 | - | A |
| Chill | yes | 70.9 | 0 | - | A |
| 0-star or ice-making | no | - | - | - | - |
| 1-star | no | - | - | - | - |
| 2-star | no | - | - | - | - |
| 3-star | no | - | - | - | - |
| 4-star | yes | 54.4 | -18 | 4.00 | M |
| 2-star section | no | - | - | - | - |
| Variable temperature compartment | no | - | - | - | - |

For 4-star compartments

| | |
|----------------------|----|
| Fast freeze facility | no |
|----------------------|----|

Light source parameters

| | | |
|------------------------|-------------------------|----------------------------|
| Type of light source 1 | Technology | LED |
| | Directionality | DLS |
| | Mains | NMLS |
| | Connected | no |
| | Colour tuneable | no |
| | Envelope | no |
| | High luminance | no |
| | Anti glare shield | no |
| | Dimmable | only with specific dimmers |
| | Energy efficiency class | F |

Minimum duration of the guarantee offered by the manufacturer: 24 months

Additional Information: -

Weblink: <https://home.liebherr.com/>

The energy consumption was confirmed by measurements according to EN 62552:2020.