

Legendary German Engineering

Quality, Design and Innovation

5 YEARS

194

nergyrating.gov.au

211



SWTNes 4265 & SKBes 4360

LIEBHERR





2.4" Touchscreen Display: Located behind the appliance door, this high-resolution and high-contrast 2.4" touchscreen display can be read from any angle. Stored menu options are Intuitive and easy-to-operate.




BioFresh-Plus: With the adjustable temperature range of 0°C and -2°C, BioFresh-Plus technology offers even more flexibility for your produce. The BioFresh-Plus drawer includes a versatile Fish & Seafood-Safe.



PowerCooling: A high-performance system that allows freshly stored items to be chilled rapidly while maintaining an even temperature throughout the interior. In this energy-efficient BluPerformance range, the fan switches off when the appliance door is opened, saving valuable energy.


Introducing Liebherr's award-winning Side-by-Side model from the BluPerformance range – the **SBSes 8486**. This eye-catching unit boasts an array of innovative solutions with six different climate zones, but its multi-temperature wine compartment is what makes it most unique! Enjoy added flexibility with BioFresh-Plus safe which offers an adjustable temperature range of 0°C and -2°C. Comes with a versatile Fish & Seafood-Safe.

SBSes 8486 PremiumPlus	Bio Fresh- Plus	No Frost	lce Maker	Wine	Soft System	Soft Telescopic	Smart Steel	
*Side-by-Sides comprised of two models					SI	NTNes 4	SKBes 4360	
Energy consumption (kWh/yr) I Star rating							4.0	
Compressors							1	
Total Usable Litres							366	
Refrigerator Usable Litres							234	
Freezer Usable Litres							-	
BioFresh Usable Litres							132	
Wine Usable Litres					153	3 (48 bot	-	
Control system and display Child proof				2.	2.4"Touch display Yes			2.4"Touch display Yes
PremiumPlus lighting							Yes	Yes
Sabbath mode							Yes	
SoftSystem hinge - assists closure							Yes	
Door open I Temperature : alarms						Yes I	Yes	Yes I -
BioFreshPlus drawers on telescopic rails							1	
BioFresh drawers on telescopic rails							2	
SuperCool VarioSafe							Yes Yes	
SuperFrost VarioSpace						Yes I	- -	
Integrated bottle shelf							Yes	
Freezer drawers I Ice cube drawer						2	- -	
IceMaker Ice cube capacity (kg/24h)						Yes I	- -	
Stainless steel hose supplied (m)							-	
Stainless steel with SmartSteel Doors Walls				6		Yes I	Yes Yes	
Default hinge							Right	
Voltage (V) Rated Current (A)					22	0 - 240	220 - 240 1.2	
Made in						Germ	any	Germany



1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. This increases the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Water Connection



Plumbing must be installed adjacent to the side of the appliance which contains the IceMaker.

Water pressure must be between 0.15 MPa and 0.6 MPa (1.5 bar - 6 bar)

* These models are only bound for storing wine. Max. DIN norm bordeaus bottle capacity (0.75 l) as per norm NF H 35-124 (H:300.5 mm, Ø 76.1mm)

Important information: For Side-by-Side installation the freezer or the appliance with freezer compartment must be installed on the left as viewed from the front to prevent possible formation of condensation.

Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.

home.liebherr.com.au