

BLU  
Performance

# NoFrost With Style And Elegance

Quality, Design and Innovation



SGNPes 4365



# LIEBHERR



**2.4" Touchscreen Display:** Located behind the appliance door, this high-resolution and high-contrast 2.4" touchscreen display can be read from any angle. Stored menu options are intuitive and easy-to-operate.



**IceMaker:** Liebherr's automatic IceMaker produces flawless crescent ice and keeps a constant supply on hand for every occasion.



**VarioSpace:** The freezer includes include drawers and glass shelves that can be conveniently removed to create extra storage space. It's Liebherr's very practical solution to quickly accommodate even bulky items.

*Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.*



Volume, efficiency, economy, ease of use, and outstanding design are the key features of the **SGNPes 4365** freezer from Liebherr's BluPerformance series. High-quality components and materials, and perfect workmanship combined with precise touch electronics system are what made this appliance so efficient.

VarioSpace allows you to remove the freezers drawers and use the glass shelves to store irregular shaped or large items. Meanwhile NoFrost technology ensures that this appliance never has to be defrosted. And thanks to its premium SmartSteel surface, this timelessly elegant model is easy to clean and will definitely be a visual highlight in your home!

**SGNPes 4365**  
Premium

No Frost	Ice Maker	Soft System	Smart Steel
----------	-----------	-------------	-------------

Energy consumption (kWh/yr)   Star rating	211   5.0
Compressors	1
Total Usable Litres	262
Freezer Usable Litres	262
Control system and display   Child proof	2.4" Touch display   Yes
LED lighting	Yes
Sabbath mode	Yes
SoftSystem hinge - assists closure	Yes
Door open   Temperature : alarms	Yes   Yes
SuperFrost   VarioSpace	Yes   Yes
Freezer drawers   Ice cube drawer	8   1
IceMaker   Ice cube capacity (kg/24h)	Yes   0.8
Stainless steel hose supplied (m)	1.5
Stainless steel door with SmartSteel	Yes
Stainless steel walls with SmartSteel	Yes
Default hinge	Left
Voltage (V)   Rated Current (A)	220 - 240   1.3
Made in	Germany



Important information: For Side-by-Side installation the freezer or the appliance with freezer compartment must be installed on the left as viewed from the front to prevent possible formation of condensation.