

BLU
Performance

Freshness For
Healthy Living

Quality, Design and Innovation

SBSes 8474 (SBNes 4265 & SKBes 4350)

LIEBHERR



2.4" Touchscreen Display: Located behind the appliance door, this high-resolution and high-contrast 2.4" touchscreen display can be read from any angle. Stored menu options are intuitive and easy-to-operate.



BioFresh: When stored at Biofresh's precisely maintained temperature of 0°C and correct humidity level, nutrients in your food are retained. Our BioFresh drawers fully extend on telescopic rails and feature a self-closing mechanism.



PowerCooling: A high-performance system that allows freshly stored items to be chilled rapidly while maintaining an even temperature throughout the interior. In this energy-efficient BluPerformance range, the fan switches off when the appliance door is opened, saving valuable energy.


The BluPerformance **SBSes 8474** Side-by-Side fridge-freezer combines perfect cooling performance for long-lasting freshness, ample storage space, and timeless design. All its five BioFresh safes run on telescopic rails and provide optimal storage conditions for your groceries at a temperature of just above 0°C in combination with ideal humidity. Our IceMaker has a fixed water connection and provides ice cubes for every occasion. The SuperCool and SuperFrost functions allow food to be cooled or frozen quickly.

To maintain the air quality in your appliance, it is recommended to change the activated charcoal filter² every 12 months.


SBSes 8474
Premium

Bio Fresh	No Frost	Ice Maker	Soft System	Soft Telescopic	Smart Steel
-----------	----------	-----------	-------------	-----------------	-------------

Refrigerator capacity litre	539
BioFresh comp. litre	305
Freezer capacity litre	126
Number of shelves	8
Number of door racks	5
Number of freezer drawers	5 with LED
Number of BioFresh drawers	5 with LED
Electronic control	2.4" TFT-colour temp. display, touch electronic
Door / side walls	Stainless steel with SmartSteel / Stainless steel with SmartSteel
Refrigerator temperature range °C	+2°C to +9°C
Freezer temperature range °C	-14°C to -26°C
Temperature alarm	Visual and audible
Defrost type	Automatic
Interior light	LED ceiling lighting with dimmer function
Door alarm	Visual and audible
IceMaker	Fixed water connection 20mm (3/4")
Ice cube output kg/24h	1.2
SoftSystem	Yes
Door hinges	Left, right
Product dimensions (H/W/D) cm	185 / 121 / 66.5
Gross / Net weight kg	183.2 / 163
Voltage V/Hz	220-240 / 50 / 60



² Available accessory: Activated Charcoal Filter (Part no. 988111600)



Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.