

HWgb 1803

Wine Cabinets

LIEBHERR

Refrigeration and Freezing



home.liebherr.com



HWgb 1803

| | |
|--------------------------------------|--|
| Energy consumption (kWh / y) | 106 |
| Sound rating dB(A) | 34 |
| Total capacity cu.ft. (l) | 1.6 (46) |
| Max. No. of Bordeaux bottles (0.75l) | 18 |
| Number of shelves | 3 |
| Shelves on telescopic rails | 2 |
| Self material | Beech wood |
| Presentation shelf | No |
| Electronic control | Touch electronic |
| Temperature range °F (°C) | 41 to 68°F (5 to 20°C) |
| Temperature zones | 1 |
| Temperature alarm | Yes |
| Interior light | LED interior lighting |
| Door alarm | Acoustic |
| Safety thermostat | Yes |
| Activated charcoal filter | Yes |
| Door type | Elegant black glass drop-down door with TipOpen Technology |
| Door hinges | Drop down |
| SoftSystem | Yes |
| Door lock | No |
| Product dimensions | |
| in inch (H / W / D) | 17 11/16 / 21 7/8 / 22 1/6 |
| in cm (H / W / D) | 44.8 / 55.5 / 55.9 |
| Cut out dimensions | |
| in inch (H / W / D) | 17 3/4 - 17 13/16 / 22 1/16 - 22 1/2 / 21 11/16 |
| in cm (H / W / D) | 45 - 45.2 / 56-57 / 55 |
| Net weight lbs. (kg) | 75 (34) |
| Voltage V / Hz | 115/60 |

Accessories

| | |
|--------------------------|--------------------|
| FreshAir charcoal filter | 7434557 |
| Ventilation grill | 7420465 9097348 |

Features


- LED** LED lighting is energy efficient, long-lasting, and maintenance-free.
- Tip Open** For integration into handleless kitchen furniture, the handleless, full-surface insulated glass door with innovative TipOpen technology is the perfect solution. The glass door opens a few centimetres when tapped. If the door is not opened further after 3 seconds, the SoftSystem closes it again.
- Soft System** SoftSystem integrated into the appliance door, cushions the door closure, thus eliminating slamming, even when the shelves are fully loaded.
- Telescopic Rails** Telescopic rails a self-closing system for drawers and shelves, ensures easy and convenient handling.
- ADA Compliant** ADA compliant, with control panel designed to be accessible within 55" from the floor.

** Noise output – according to EN 60704-3


Not recommended for installation or use at altitude greater than 5000 feet above sea level.

Diagrams

Appliance Dimensions



Cabinet Dimensions




Ventilation



IMPORTANT
The area of ventilation above the unit should be at least 31 square inches (200 cm²). The air supply passes below the appliance door.

- ① Directly above the appliance
- ② Above the top unit
- ③ From the front of the top unit with decor grill



IMPORTANT
When using decor grills, the sum of the individual openings must total a minimum of 31 square inches. A cut-out section of 31 square inches (200 cm²) for installing the ventilation grill is thus not sufficient.