

EU declaration of conformity regarding energy consumption according to (EU) 2019/2019

Energy Label (EU) 2019/2016

Applied standard EN 62552:2020

## Product Information Sheet

|                               |  |
|-------------------------------|--|
| Supplier's name or trade mark | Liebherr   |
| Supplier's address            | Liebherr-Hausgeräte GmbH<br>Memminger Straße 77-79<br>D-88416 Ochsenhausen |
| Model identifier              | IRDe 5121_991603551  |

### Electrical data

|               |             |
|---------------|-------------|
| Voltage       | 220-240 V ~ |
| Frequency     | 50-60 Hz    |
| Rated current | 1.2 A       |

### Type of refrigerating appliance

|                        |    |                               |          |
|------------------------|----|-------------------------------|----------|
| Low-noise appliance    | no | Design type                   | built-in |
| Wine storage appliance | no | Other refrigerating appliance | yes      |

### General product parameters

| Parameter  |        | Value  | Parameter  | Value |
|--|--------|--|--|-------|
| Overall dimensions (millimeter)  | Height | 1770   | Total volume (dm <sup>3</sup> or l)                  | 286   |
|  | Width  | 559  |  |       |
|  | Depth  | 546  |  |       |
| EEL  | 100    | Energy efficiency class  | E  |       |
| Airborne acoustical noise emissions (dB(A) re 1pW)                                 | 35     | Airborne acoustical noise emissions class  | B  |       |
| Annual energy consumption (kWh/a)  | 170.80 | Climate class  | extended temperate, temperate, subtropical, tropical |       |
| Minimum ambient temperature (°C) for which the refrigerating appliance is suitable | 10     | Maximum ambient temperature (°C) for which the refrigerating appliance is suitable | 43   |       |
| Winter setting   | no     |  |  |       |

## Compartment Parameters

| Compartment type                 |     | Compartment parameters and values         |                                      |                            |   |
|----------------------------------|-----|---|--------------------------------------|----------------------------|---|
|                                  |     | Compartment Volume (dm <sup>2</sup> or l) | Recommended temperature setting (°C) | Freezing capacity (kg/24h) | Defrost type (auto-defrost=A, manual defrost=M) |
| Pantry                           | no  | -   | -                                    | -                          | -   |
| Wine storage                     | no  | -   | -                                    | -                          | -   |
| Cellar                           | no  | -   | -                                    | -                          | -   |
| Fresh food                       | yes | 259.2                                     | 5                                    | -                          | A   |
| Chill                            | no  | -   | -                                    | -                          | -   |
| 0-star or ice-making             | no  | -   | -                                    | -                          | -   |
| 1-star                           | no  | -   | -                                    | -                          | -   |
| 2-star                           | no  | -   | -                                    | -                          | -   |
| 3-star                           | no  | -   | -                                    | -                          | -   |
| 4-star                           | yes | 27.1                                      | -18                                  | 2.00                       | M   |
| 2-star section                   | no  | -   | -                                    | -                          | -   |
| Variable temperature compartment | no  | -   | -                                    | -                          | -   |

### For 4-star compartments

|                      |    |
|----------------------|----|
| Fast freeze facility | no |
|----------------------|----|

**Light source parameters**

|                        |                         |                            |
|------------------------|-------------------------|----------------------------|
| Type of light source 1 | Technology              | LED                        |
|                        | Directionality          | DLS                        |
|                        | Mains                   | NMLS                       |
|                        | Connected               | no                         |
|                        | Colour tuneable         | no                         |
|                        | Envelope                | no                         |
|                        | High luminance          | no                         |
|                        | Anti glare shield       | no                         |
|                        | Dimmable                | only with specific dimmers |
|                        | Energy efficiency class | F                          |
| Type of light source 2 | Technology              | LED                        |
|                        | Directionality          | DLS                        |
|                        | Mains                   | NMLS                       |
|                        | Connected               | no                         |
|                        | Colour tuneable         | no                         |
|                        | Envelope                | no                         |
|                        | High luminance          | no                         |
|                        | Anti glare shield       | no                         |
|                        | Dimmable                | only with specific dimmers |
|                        | Energy efficiency class | F                          |

**Minimum duration of the guarantee offered by the manufacturer:** 24 months

**Additional Information:** -

**Weblink:** <https://home.liebherr.com/>

**The energy consumption was confirmed by measurements according to EN 62552:2020.**