



The Storage Choice for Wine Aficionados

Quality, Design and Innovation

WKgb 4113


LIEBHERR



Recessed door handle & heated glass door: With its elegantly designed recessed door handle, the **WKgb 4113** looks perfect in any home or restaurant. This model comes with an insulated full-glass, black door to protect wines against UV radiation and is anti-condensation. Perfect for tropical climates.



LED lighting: The integrated LED lighting in the wine cabinet interior ensures pleasant illumination and an optimum glance at your wine collection.



Optimum humidity: Optimum humidity in our wine cabinets ensures that the bottle corks are supple in place whilst still allowing the wine to breathe in its maturing process.

Note: Whilst every effort is made to ensure all specifications and information in this flyer are accurate, Liebherr reserves the right to make changes without notification. Where actual appliance measurements, specifications, and ratings are crucial, we recommend that the actual appliance installation instructions that accompany each appliance be checked. Liebherr will not be liable for any loss.

The Liebherr Barrique **WKgb 4113** wine cabinet provides climatic conditions similar to that of a wine cellar and is perfect for the long-term storage or maturing of fine wines. Interior temperature can be adjusted between +5°C to + 20°C. Our integrated activated carbon filter absorbs odours from the ambient air and protects the taste of your fine wines. An insulated full-glass, black door provides protection from UV radiation and preserves the quality of wine. Anti-condensation technology also means that this unit is perfect for tropical climates! With its elegantly designed recessed handle, this wine cabinet looks perfect in any home or restaurant. For added flexibility, optional accessories¹ are available.

WKgb 4113


Barrique

LED

Wine

Total capacity litre	293
Max No. of Bordeaux bottles (0.75l) *	168
Number of shelves	6
Presentation shelf	1
Shelf material	Beech wood
Electronic control	LCD display, buttons
Temperature range °C	+5°C to +20°C
Temperature zones	1
Temperature alarm	Optical and audible
Interior light	LED
Door alarm	Audible
Safety thermostat	Yes
Activated charcoal filter	Yes
Door type	Insulated glazed door, black frame
Integrated lock	Yes
SoftSystem	No
Door hinges	Right fix
Product dimensions (H/W/D) cm	164.5 / 65.7 / 66.3
Gross / Net weight kg	86 / 78
Voltage V/Hz	220-240 / 50

Installation Diagram



Activated Charcoal Filter
Part no.: 988129100

* Noise output - according to EN 60704-3

** These models are only bound for storing wine. Max. DIN norm bordeaux bottle capacity (0.75 l) as per norm NF H 35-124 (H:300.5 mm, Ø 76.1mm)

¹ Available accessories: Activated Charcoal Filter (Part no. 988129100), Regular Shelf (Part no. 711173400), Presentation Shelf (Part no. 711173600)