HC 2092

Fully Integrated Appliances



Refrigeration and Freezing





home.liebherr.com

	HC 2092		
Energy consumption (kWh / y)	580		
Estimated Yearly Energy Cost* in US \$	81		
Sound rating** dB(A)	44		
Total refrigerator capacity cu.ft. (l)	13.5(382)		
BioFresh compartment cu.ft. (l)	-		
Freezer capacity cu.ft. (l)	6.0(170)		
Electronic control	MagicEye with digital temp.		
	display, touch electronic		
Defrost type	Automatic		
Interior light	LED Light column/ LED ceiling		
Number of shelves	3		
Number of door racks	6		
Number of BioFresh drawers	-		
Number of freezer drawers	3		
Refrigerator Temperature range °F (°C)	+36°F to +43°F (+2°C to +6°C)		
Freezer Temperature range °F (°C)	+7°F to -17°F (-14°C to -27°C)		
Water filter	yes		
Ice maker	Fixed with water connection		
Ice cube output lbs. (kg.)	3.1(1.4)		
Ice cube stock lbs. (kg.)	6(2.7)		
Door hinges	left/right		
Product dimensions			
in inch (H / W / D)	79 13/16" / 35 7/8" / 24 1/16"		
in cm (H / W / D)	202.7/91/61.5		
Cut out dimensions			
in inch (H / W / D)	80"-815/8" / 361/16" / 25"		
in cm (H / W / D)	203.2-207.2/91.5/63.5		
Net weight lbs. (kg)	368.2(167)		
Voltage V / Hz	115/60		

* Energy Cost will depend on utility rates and use. Estimated energy cost based on a national average electricity cost of 14 cents per KWh.



Accessories	
Water Filter	9880980/7440002
Stainless Steel Round Handles	9900339
Brushed Aluminimum Square Handles	9900513
Stainless Steel Panels Refrigerator 8	0" 9900337
Stainless Steel Panels Refrigerator 84	4" 9900335
Stainless Steel Panels Freezer Drawe	rs 9900323

Features



Lengthen the shelf life and preserve the flavor of your foods with a dual refrigeration system that creates ideal conditions in both the refrigerator and freezer.



Liebherr's automatic IceMaker produces perfect ice cubes and keeps a constant supply on hand for every occasion.



Ensure the door closes gently to reduce any unnecessary sounds.





Store food securely within reach thanks to fully extendable pull-out drawers. The SoftTelescopic system provides convenient and reliable self-retraction with soft closing.

** Noise output - according to EN 60704-3

Diagrams


Product Dimensions







Panel Dimensions



Cabinet opening A	Refrigerator door panel B	Cabinet opening A	Refrigerator door panel B
80"	45-1/2" (1156 mm)	80"	45-5/8" (11659 mm)
84"	49-1/4" (1251 mm)	84"	49-3/4" (1264 mm)


Minimum panel thickness is 5/8" (16 mm).

Maximum panel thickness is 3/4" (20 mm).

Maximum weight of the refrigerator panel is 26.5 lbs (12 kg).

IMPORTANT

Risk of interference with the adjacent panels! Do not use wider panels as given in the illustration above!



1-7/8"

<u>1-7</u>/16

<u>1-</u>11/16

-

3-3/4" (95 n

Ventilation Requirements

72" SI



The appliance do not require ventilation considerations in the cabinetry. The required airflow is directed through the toe kick base. It is important to use the provided cover grille for the ventilation opening. This opening must not be covered.

Subject to modification. For up-to-date information, visit home.liebherr.com.

Specifications are for planning purposes only. For more detailed information, refer to installation instructions or Design Guide.