

New dimensions  
in freshness

Quality, Design and Innovation



**LIEBHERR**

# Global Success: The Liebherr Group

Liebherr is a third-generation, family-owned company founded by Hans Liebherr in 1949 with the creation of the first ever tower crane.

With over 65 years of success, Liebherr has become synonymous with the equipment needed to build homes and businesses, as well as the appliances within them. One of the world's largest manufacturers of construction machinery, Liebherr has expanded to eleven divisions with a wide array of product ranges, including earthmoving, mining, mobile cranes, tower cranes, concrete technology, maritime cranes, aerospace and transportation systems, machine tools and automation systems, components, hotels and domestic appliances.

The company currently employs over 44,000 persons in more than 130 companies in over 50 countries worldwide. Liebherr Appliances is Europe's largest privately owned manufacturer of fridges and freezers for residential and commercial use, with an annual production of more than 2.1 million units.



Earthmoving



Mining



Mobile Cranes



Tower Cranes



Concrete Technology



Maritime Cranes



Aerospace and Transportation Systems





Machine Tools and Automation Systems



Domestic Appliances




Components



Hotels







# Quality

## Quality standards

Liebherr domestic appliances are produced under the highest international quality standard – ISO 9001 and are compliant with the international environmental management standard – ISO 14001.

## Tested quality

So that you can rely on your refrigeration appliance 24 hours a day, 365 days a year, we test every component for its long-term reliability, right from the design stage. For example, before a component such as a door hinge finds its way into production, it will first have to undergo 100,000 opening/closing cycles, which corresponds to more than 15 years of use.

## Proven quality

Before packaging, every single appliance goes through a comprehensive quality inspection. This procedure tests all refrigeration technology, and all mechanical and electronic components. In addition, a visual inspection to confirm quality of workmanship also takes place.

## VCC compressor

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.







# Design

## Practical design for daily use

At Liebherr, design and functionality go hand-in-hand. For example: to prevent finger marks on our stainless steel doors, we finish them with a SmartSteel surface; and, to make door opening easy and convenient, our ergonomically designed handles house an integrated opening mechanism; not to mention that all GlassLine shelves are dishwasher safe.

## Lighting design

Liebherr's fridges and freezers are fitted with modern LED lighting. Upon opening the appliance door, the interior becomes evenly illuminated. LEDs are long-life, energy efficient and generate hardly any heat. We take meticulous care to install specially selected LEDs in order to achieve a harmonious, slightly bluish tinted lighting effect.

## Award-winning design

The superb design-quality of our appliances has seen them honoured with many prestigious, international design awards from the likes of Plus X Award, reddot, iF product design and Good Design.







# Innovation

## **Innovative ideas**

Liebherr integrates style, function and technology: BioFresh, SuperCool and SuperFrost are just a few examples of performance features that contribute to better food preservation. Accurate and independent temperature control of the fridge and freezer compartments is facilitated by DuoCooling: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.

## **ActiveGreen initiative**

A concept that best represents Liebherr's commitment to finding greener ways to produce quality, sustainable products. Liebherr was the first refrigeration manufacturer to be RoHS compliant worldwide by restricting the use of hazardous substances. Energy efficiency is at the core of our ActiveGreen commitment, which is reflected in every aspect of our design and manufacturing process.

## **Energy efficiency**

Liebherr refrigerators and freezers help to produce less energy waste and greenhouse gas emissions with the aim to have the least damaging effect on the environment and offering solutions that help consumers conserve energy.



BioFresh



# Experience Super Freshness with BioFresh

Keeping your food fresh in a Liebherr is easy. BioFresh guarantees the perfect climate for super-long-term freshness. Through its advanced technology the temperature is kept at just above freezing.

Each drawer can be used individually and provides ideal humidity. The **DrySafe** drawer with low humidity is ideal for storing meat, fish and dairy products, while fruits and vegetables are best kept in the high humidity **HydroSafe** or **Fruit & Vegetable-Safe** (optional). The natural loss of moisture in fruit and vegetables is significantly reduced. It's simple: fresh is better.

# Freshness Perfected with BioFresh

Liebherr's BioFresh technology contributes to a healthy diet and wellbeing in addition to offering convenience that fits with your busy lifestyle. Nature offers a whole range of essential nutrients vitamins, minerals and carbohydrates to give us energy. However, the right temperature and ideal humidity conditions are essential if food is to retain its healthy properties and delicate flavours as long as possible.

Liebherr's BioFresh technology provides perfect freshness for all types of food and delivers impressive long lasting preservation as well as day-to-day convenience.

The Liebherr BioFresh App



[biofresh.liebherr.com](https://biofresh.liebherr.com)

It provides the ultimate tool for all health conscious food lovers to easily access valuable information regarding food storage, vitamins, minerals and shelf life.

The information relates to storage in a BioFresh drawer compared to a conventional fridge.





Carrots + 30 days



Asparagus + 8 days



Grapes + 17 days



Meat + 6 days



Raspberries + 2 days



Fish + 1 day



ECBN 6156

# Freestanding

# Built-in



## Side-by-Side

**SBSes 8486** page 18  
**SBSes 8484** page 20  
**SBSes 8474** page 20  
**SBSes 8683** page 22  
**SBSbs 8673** page 24  
**SBSes 8673** page 24  
**SBSes 7253** page 26  
**SBSef 7242** page 28



## Side-by-Side

**SIGN 3576**  
**SIKB 3550** page 40  
**SICN 3356**  
**SICBN 3366** page 42



## Fridge-Freezer

**CNef 4315** page 30  
**CNPef 4516** page 85




## Frenchdoor

**ECBN 6256** page 34



## Wine Cabinets

**WTes 5872** page 56  
**WTes 5972** page 56  
**Wkt 6451** page 58



## Fridge-Freezer

**ECBN 6156** page 36  
**ECBN 5066** page 38  
**SICBN 3356** page 44  
**SICN 3366** page 46  
**SICN 3314** page 48



## Wine Cabinets Barrique

**Wkb 4612** page 68  
**Wkb 4611** page 70  
**WkGb 4113** page 72  
**Wkb 4112** page 68  
**Wkb 1712** page 74



## Undercounter

**SUIKo 1550** page 50  
**SUIK 1510** page 52  
**SUIG 1514** page 52



## Design & Lifestyle

**WKes 653** page 78  
**ZKes 453** page 78



## Wine Cabinets

**EWtdf 3553** page 60  
**UWTes 1672** page 62  
**UWKes 1752** page 62  
**WKEes 553** page 64



CNPef 4516

# Features of Liebherr Freestanding Appliances



**Smart Steel**

**SmartSteel:** Available on select freestanding models significantly reduces the visibility of fingerprints and is very easy to clean and scratch resistant. All that is required to maintain this beautiful exterior is the wipe of a clean dry or damp cloth.



**Bio Fresh**

**BioFresh:** BioFresh drawers provide customizable interplay of temperature and humidity controls. The DrySafe drawer with low humidity is ideal for storing meat, fish and dairy products, while fruits and vegetables are best kept in the high humidity HydroSafe.



**Soft System**

**SoftSystem:** Automatic self-closing doors from 45 degrees eliminates slamming even when fully loaded.



**Water filtration:** The activated charcoal filter ensures pure water to produce perfectly fresh ice crescents. The precise electronic control will indicate when the filter needs to be replaced.



**VarioSpace:** Nearly all freezers include drawers and glass shelves that can be conveniently removed to create extra storage space. It's Liebherr's very practical solution to quickly accommodate even bulky items.



**Bottle shelf:** The versatile glass/bottle shelf can be interchanged depending on your personal preference. Utilize the glass layer for additional shelf storage or simply move glass plate beneath to access bottle rack to chill and store beverages instead.

The features shown are model dependent; the description applies to the relevant model.



# Legendary German engineering

Six climate zones in one appliance! The Side-by-Side fridge-freezer **SBSes 8486** with six different climate zones boasts an array of innovative solutions. The multi-temperature wine compartment has two independently adjustable zones for storing wine at the exact temperature required, ranging from +5 °C to +20 °C. The NoFrost freezer compartment with automatic IceMaker provides professional freezing technology for long-term freshness, while a spacious fridge compartment keeps food fresh on a day-to-day basis.

In the BioFresh compartment, fruits, vegetables, fish, meat and dairy products stay fresh for significantly longer at around 0 °C. With the adjustable temperature range of 0 °C and -2 °C, BioFresh-Plus offers even more flexibility. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe. In short, the SBSes 8486 guarantees optimal storage temperature for an array of produce.

- Bio Fresh-Plus
- No Frost
- Ice Maker
- Wine
- Soft System
- Soft Telescopic
- Smart Steel



## The big, cool combination

The **SBSes 8484** Side-by-Side fridge-freezer from the BluPerformance series combines plenty of storage space with perfect cooling performance for long-lasting freshness. The Side-by-Side appliance can be precisely controlled via the touch electronics system with digital temperature display. BioFresh technology ensures a longer shelf life for fruit, vegetables, fish, meat and dairy products at around 0 °C. With the adjustable temperature range of 0 °C and -2 °C, BioFresh-Plus offers even more flexibility. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe. Thanks to the innovative NoFrost technology, the appliance never has to be defrosted. The elegant and timeless design in combination with high-quality materials, components and workmanship mean this Side-by-Side appliance will catch the eye for many years to come.

Also available in regular BioFresh technology as **SBSes 8474**.

- Bio Fresh-Plus
- No Frost
- Ice Maker
- Soft System
- Soft Telescopic
- Smart Steel



## It doesn't get any fresher

Premium quality characterises the **SBSes 8683** Side-by-Side fridge-freezer from the BluPerformance series. High-quality components and materials, and perfect workmanship combined with precise touch electronics and digital temperature display, make the Side-by-Side a very efficient household appliance. Fruit, vegetables, fish, meat and dairy products keep for much longer thanks to BioFresh technology. With the adjustable temperature range of 0 °C and -2 °C, BioFresh-Plus offers even more flexibility. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe. The NoFrost technology means that the appliance never has to be defrosted. Its elegant and classic design with a SmartSteel surface ensures that the Side-by-Side appliance will remain a household highlight for years to come.

Bio  
Fresh-  
Plus

No  
Frost

Ice  
Maker

Soft  
System

Soft  
Telescopic

Smart  
Steel



## An optical highlight in BlackSteel

Meet the **SBSbs 8673** from our BluPerformance range, which is characterised by premium-quality materials, craftsmanship in every detail, and precision touchscreen electronic controls. The integration of all the refrigeration components into the base of the appliance, together with optimised electronic controls, ensures maximum energy efficiency, a greater net capacity, and enhanced freezer compartment ergonomics. Our BioFresh keeps stored food fresher for longer. The elegant and timeless design of the BluPerformance range ensures that these appliances are a guaranteed highlight in any home.

Also available in stainless steel as **SBSes 8673**.

Bio  
Fresh

No  
Frost

Ice  
Maker

Soft  
System

Soft  
Telescopic

Black  
Steel



## One size fits all

The spacious **SBSes 7253** Side-by-Side fridge-freezer has BioFresh technology to ensure a longer shelf life for fruit, vegetables, fish, meat and dairy products. High-quality materials and components combined with the precise workmanship ensure perfect cooling performance and efficiency. The Side-by-Side appliance's settings can be made very precisely via the easy-to-use touch electronics system with digital temperature display. And thanks to NoFrost technology, the appliance never has to be defrosted. The classically elegant and timeless design with SmartSteel surface also makes the Side-by-Side appliance visually very appealing.

Bio  
Fresh

No  
Frost

Smart  
Steel





## A spacious refrigerator and freezer all in one

The **SBSef 7242** brings together high-quality components, meticulous workmanship and easy-to-use precision electronics. We guarantee freshness, user friendliness and energy efficiency.

The freezer offers up to eight drawers, thus providing an extra-large capacity for freezing your food. The transparent fruit and vegetable drawers provide a clear view of the stored food and slide out effortlessly on the roller system.

No  
Frost

Smart  
Steel

# Energy efficiency at its best

The new BluPerformance **CNef 4315** is characterised by premium-quality materials, craftsmanship in every detail, and precision touchscreen electronic controls.

The integration of all the refrigeration components into the base of the appliance, together with optimised electronic controls, ensures maximum energy efficiency, a greater net capacity, and enhanced freezer compartment ergonomics. BioCool technology keeps stored food fresher for longer.

The elegant and timeless design of the BluPerformance CNef 4315 ensures that these appliances are a guaranteed highlight in any home and that they will satisfy for many years to come.

Bio  
Cool

No  
Frost

Duo  
Cooling

Smart  
Steel





LIEBHERR



SIGN 3576 & SIKB 3550

# Features of Liebherr Built-in Appliances



**Door-on-door technology:** Allows custom panels to be affixed directly onto the appliance door so that the hinges are concealed, plus the cabinet and the fridge open as one, ensuring a wide range of design options and easy installation.



**Ice Maker**

**IceMaker:** Liebherr's automatic IceMaker produces flawless crescent ice and keeps a constant supply on hand for every occasion. An activated charcoal filter ensures pure water for production of clear ice crescents.



**Touch control system:** Our intuitive electronic touch control panel (found on most models) ensures all functions are easy and convenient to use as well as guarantees that the settings selected remain accurate and constant.



**Soft Telescopic**

**SoftTelescopic:** BioFresh with SoftTelescopic – a highly practical self-retracting, self-closing feature – makes daily use convenient and secure. The drawers are fully extendable and removable from a door opening angle of 90°.



**LED**

**Light columns:** For Liebherr's PremiumPlus appliances as well as for Premium appliances with BioFresh, unique LED light columns are integrated into both sides of the compartment liner. Inside the columns are numerous LED lights that ensure uniform lighting throughout the interior.

The features shown are model dependent; the description applies to the relevant model.



**Bio Fresh**

**BioFresh:** BioFresh guarantees the perfect temperature and ideal humidity for much longer freshness. While the DrySafe is perfect for meat, fish, and dairy products, the high humidity in the Fruit & Vegetable-Safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.



## Your kitchen's best kept secret

Whichever appliance finish fits the kitchen, the **ECBN 6256** is highlighted by BioFresh technology, Liebherr's popular DuoCooling system and double freezer drawers with self-close mechanisms and NoFrost system.

An automatic IceMaker featuring the most technically advanced water filter provides an ample supply of perfect ice cubes. Sharing the ultimate performance features, the ECBN 6256 is the stylish answer to freshness. Stainless steel panels/handles are available as accessories.

Bio  
Fresh

No  
Frost

Duo  
Cooling

Ice  
Maker

Soft  
System

## The spacious freshness centre

The 91-cm-wide, built-in BioFresh fridge-freezer **ECBN 6156** is a real eyecatcher! Available with door-on-door installation that gives customised integration into existing kitchen units, and two freezer drawers that easily extend on premium-quality telescopic rails, this built-in masterpiece is a design highlight for any kitchen.

The large refrigerator compartment and adjacently arranged BioFresh drawers, together with the NoFrost freezer compartment offer optimum storage for all types of food. The integral IceMaker supplies ice cubes for every occasion, whilst the integrated water filter ensures optimum ice quality. Stainless steel panels/handles are available as accessories.

Bio  
Fresh

No  
Frost

Duo  
Cooling

Ice  
Maker





## More space for fresh ideas

The 76-cm-wide, built-in BioFresh fridge-freezer **ECBN 5066**. Available with door-on-door installation that gives customised integration into existing kitchen units, and two freezer drawers that easily extend on premium-quality telescopic rails, this built-in masterpiece is a design highlight for any kitchen. Featuring two integrated lighting columns on the left and right, each of which incorporates multiple LEDs to evenly illuminate the interior. A special satin-finished on the light cover creates an appealing and sophisticated lighting ambience. Stainless steel panels/handles are available as accessories.

Bio  
Fresh

No  
Frost

Duo  
Cooling

Ice  
Maker



## Fresh on the inside, sleek on the outside

Hidden away behind custom cabinetry, Liebherr's fully integrated **SIKB 3550** is the perfect refrigerator for any kitchen. BioFresh technology keeps meat, fish and dairy products fresh in the DrySafe compartment, while high humidity in the Fruit & Vegetable-Safe efficiently retains natural moisture in unpackaged fruits and vegetables. The practical FlexSystem ensures neat separation and clear sorting. The SIKB 3550 includes efficient LED lighting throughout, flexible bottle racks to maximise interior space, and SoftSystem technology for the gentle closing of doors, even when shelves are fully loaded.

Bio Fresh   Soft System   Soft Telescopic

The **SIGN 3576** includes transparent, extra-deep, and fully removable FrostSafe drawers on telescopic rails to efficiently organize frozen food. This unit also comes with the SoftSystem technology. Liebherr's automatic IceMaker with fixed water connection produces crystal clear ice cubes, keeping a constant supply on hand for every occasion.

No Frost   LED   Ice Maker   Soft System   Telescopic Rails

Stainless steel panels/handles are available as accessories.



SICN 3356 & SICBN 3366



## Ultimate food preservation

The sophisticated **SICBN 3366** fridge-freezer is the perfect built-in appliance for small spaces, galley kitchens, or apartment living. Our door-on-door technology allows custom paneling to be affixed directly onto the appliance door, ensuring that the cabinet and refrigerator door open as one. Liebherr's automatic IceMaker with fixed water connection produces a constant supply of ice cubes. Though slim in stature, this appliance is full of innovative features such as BioFresh technology. While the DrySafe is perfect for meat, fish, and dairy products, the Fruit & Vegetable-Safe is great at retaining moisture in fruits and vegetables. Our FlexSystem helps to ensure neat separation and clear sorting.

Bio  
Fresh

No  
Frost

Duo  
Cooling

Ice  
Maker

Soft  
System

Soft  
Telescopic

Liebherr's **SICN 3356** fridge-freezer adds elegance to your home, with our door-on-door technology allowing for easy and seamless installation. The panel-ready doors close automatically and gently thanks to our SoftSystem technology, which eliminates slamming even when shelves are fully loaded. The SICN 3356 also includes a BioCool drawer which regulates humidity via a slider control to keep fruits and vegetables fresher for longer.

Bio  
Cool

No  
Frost

Duo  
Cooling

Soft  
System





## Sleek, Precise, Perfect

The fully integrated **SICBN 3356** fulfills the highest criteria for custom-designed kitchens. Bringing together first-class components, meticulous workmanship, easy-to-use precision electronics, and leading-edge manufacturing processes which we guarantee to provide professional-standard performance.

BioFresh guarantees the perfect temperature for much longer freshness. At a temperature of just over 0 °C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is perfect for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable-Safe can prevent fruits and vegetables from drying out and helps preserve stored goods for an even longer period. By adjusting to low humidity, the Fruit & Vegetable-Safe can also be used as an additional DrySafe.

The interior GlassLine fittings are stylishly designed and are of excellent quality. The door shelves come furnished with a satin-finished safety glass base, elegant plastic surround, stainless steel rails, and a variable bottle shelf. In addition the doors of this appliance is fitted with two different-sized, removable, transparent VarioBoxes with lids.

Bio  
Fresh

No  
Frost

Duo  
Cooling

Soft  
System

Soft  
Telescopic

## Great design – integrated seamlessly

The **SICN 3366** fully integrated fridge-freezer provides diverse design options for a perfect, seamless kitchen with the help of Liebherr's door-on-door technology. Thanks to our SoftSystem technology, slamming is eliminated even when shelves are fully loaded. A BioCool drawer regulates humidity via a slider control to keep fruits and vegetables fresher for longer. Advantageously, this model eliminates the need for a plumbed water connection as it includes a convenient 1.42 litre internal water tank for the IceMaker. Simply fill the tank with filtered water to produce crystal clear ice cubes!

Bio  
Cool

No  
Frost

Duo  
Cooling

Ice  
Maker

Soft  
System



# The perfect match for your kitchen

The **SICN 3314** blends in beautifully with any kitchen cabinetry, providing diverse design options to fit your dream kitchen. Liebherr's door-on-door technology allows for custom paneling to be affixed directly onto the appliance door, ensuring that the cabinet and the refrigerator door open as one, allowing for additional design options and easy installation.

The SICN 3314 includes a BioCool drawer which regulates humidity via a slider control to help keep fruits and vegetables fresher for longer.

Bio  
Cool

No  
Frost

Duo  
Cooling





## The smooth operator

The precision control system of the **SUIKo 1550** creates a stunning visual impact. This precision electronic control system enhances the ease and convenience of use. The SuperCool function quickly reduces the temperature of the fridge compartment; ideal for rapidly cooling down freshly stored food. Food can be stored safely with easy access on the pull-out glass shelves.

Practical rails can be used to divide the glass shelves according to package size. The innovative LED light creates first class interior illumination while the special satin finish of the light cover produces a pleasant lighting atmosphere. The pull-out fridge compartment is mounted on telescopic rails with soft stop. It has a practical bottle shelf and a large fruit and vegetable compartment. The large compartment can also be divided into two equal-sized compartments, with further storage space underneath. Stainless steel panels/handles are available as accessories.

Soft  
Telescopic



# Convenience at your fingertips

Liebherr's space-saving and efficient undercounter appliances are the practical choice for compact living spaces or couples. The **SUIK 1510** undercounter fridge is great for your fresh produce. Our innovative SoftSystem technology ensures that the appliance door closes gently even when it is fully loaded. What's more, the door closes automatically from an opening angle of approximately 30°. Airflow in this unit enters and exits from the front at plinth level, hence no ventilation grill is required in the worktop. Heights of the glass shelves are adjustable to accommodate large items for added flexibility.

Soft  
System

And for frozen goods, the **SUIG 1514** undercounter freezer will be perfect. SmartFrost technology allows food to freeze faster and reduces ice build-up, making defrosting simpler and quicker. Similarly, SoftSystem allows soft closing to provide convenience and safety. No ventilation grill is needed in the worktop as airflow enters and exits from the front of this appliance.

Smart  
Frost

Soft  
System

The SUIK 1510 undercounter fridge and SUIG 1514 undercounter freezer are perfect companions for each other! Best suited for small families who can now bid farewell to space wastage.







WTes 5972

# Features of Liebherr Wine Cabinets



LED

**LED lighting:** The light in the wine cooling compartments can be dimmed to give a pleasing ambient light inside the appliance.



**Presentation shelf:** The practical shelf of the Vinidor models fulfills both bottle storage and presentation functions. The bottles can be stored horizontally at the rear.



**Activated charcoal filter:** Liebherr Wine cabinets have a permanent supply of odorless, fresh air via an easily exchangeable activated charcoal filter.



**Integrated lock:** Nicely concealed into the side of the door, this sturdy lock protects your fine wine collection.



**Electronic LCD display:** Intuitive navigation of touch electronic control system enables tailored storage options. The digital temperature display can be viewed via the UV tinted glass door.



**Compressors:** Specially developed compressors installed in the wine cabinets from Liebherr ensure that the wines are stored in a particularly low vibration environment.

The features shown are model dependent; the description applies to the relevant model.





## Created for true wine connoisseurs

A Liebherr **WTes 5872** satisfies your thirst for the smartest, most elegant ways to store wine in addition to adding sophisticated flair to entertainment areas while providing ideal conditions for wine to mature successfully – constant air quality, temperature and humidity control as well as quiet, vibration free storage. With three temperature zones you can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature.

Specially developed quiet compressors ensure that the unit has the lowest vibration possible. Liebherr uses an insulated glass door with UV protection and an activated charcoal filter to protect the wine from busy kitchen influences, such as light and odour. An innovative LCD display makes temperature continuously adjustable from +5 °C to +20 °C depending on owner's preferences and the contents of the unit. The practical presentation shelf of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the rear.

Wine units are equipped with an alarm system to alert the homeowner if the door has been left open or the temperature has been compromised. The energy efficient LED ceiling light not only emits virtually no heat, but it is dimmable to cast a cool glow across the room. As a true wine storage unit (and not just a refrigerator) the units also have heating capabilities to maintain accurate temperature when the location of the unit is colder than the desired set temperature.

Also available in two temperature zones as **WTes 5972**.





## Quality wines deserve quality storage

The wine storage cabinet **WKt 6451** offers similar conditions to a wine cellar. This appliance can be set to exactly the temperature required within the range of +5 °C to +20 °C. This ensures that the selected temperature is maintained constantly and uniformly throughout the interior.

Liebherr wine storage cabinets are ideal for storing wines for long periods of time to allow them to mature to perfection. Depending on what temperature the appliances are set to, they can also be used for keeping white wine or red wine at exactly the right temperature for serving.

The jumbo WKt 6451 boasts one of the largest capacity in the market, with the space to hold up to 312 Bordeaux bottles (standard size 0.75 l).

LED

Wine

# One solution for all your favourites

The advanced dual-zone **EWtdf 3553** offers a number of innovative solutions for wine storage. Controls are integrated into the insulation layer between the temperature zones, making it possible to set two different temperatures within the unit. Store red and white wines according to your preference – use the entire cabinet for one or store both, each at its optimum drinking temperature.

High-quality, easy-to-fit optional stainless steel accessory frame kit enables the model's integration into any kitchen. The robust stainless steel handle is easy to attach and makes opening of the door effortless.

This wine cabinet is compatible with furniture overlay panels (supplied by your kitchen retailer) or Liebherr's stainless steel overlay which is available as an accessory.





# For all who appreciate good taste

For wine collectors, temperature, humidity, vibration, and light are the most important elements of wine storage. The **UWTes 1672**, a dual temperature zone unit, clearly addresses all four areas – perfect for all reds, whites and champagne.

LED Wine Telescopic Rails

Meanwhile Liebherr's **UWKes 1752** wine storage cabinet is ideal for storing wines for long periods of time, allowing them to mature to perfection.

LED Wine Telescopic Rails

Both wine cabinets ventilate through the Toe Kick, hence no counter slot is necessary, and can be integrated easily and elegantly into your customised kitchen. Each appliance boasts a digital temperature display with visibility through elegant glass doors.



UWTes 1672 & UWKes 1752

## Classic and sleek, fits anywhere

**WKEes 553**, the fully integrated wine unit that holds 18 Bordeaux bottles in an ideal storage environment.

Innovative styling allows the unit to sit flushed in with cabinetry. Its recessed handle maintains crisp, simple lines that incorporates beautifully into your custom kitchen design. Take advantage of the appliance's design flexibility - place this sleek, modular wine cabinet anywhere in your home and proudly display your fine wine collection at eye level.

The temperature is adjustable from +5 °C to +20 °C and the LED ceiling light is dimmable to cast a cool glow across the room. Insulated glass door with UV protection and activated charcoal filter protect your wine from light and odour.







WKb 4112

# Features of Liebherr Barrique Wine Storage Cabinets



LED

**LED lighting:** The tinted glass door provides not only a perfect UV protection, but also an optimum glance at wine. The integrated LED lighting ensures a pleasant illumination of the complete interior.



**Precision electronics:** The precise electronic control system is equipped with a digital temperature display. The door and temperature alarm alerts of any irregularities, e.g. when the door is left open. The integrated lock on the front panel prevents unwanted access to the stored bottles.



**Wooden shelves:** The untreated wooden shelves are ideal for storing wine bottles. They can be stored in opposite directions to make full use of the capacity.



**Presentation shelf:** The presentation shelf, equipped with wooden angles, is ideal for presenting wine and storing open bottles safely. Up to 6 bottles can be set upright on the flexible shelf. In addition further bottles can be stored lying down either behind or at the side.



**Optimum humidity:** Liebherr wine cabinets guarantee an optimum humidity and this ensures the corks are kept in place whilst still allowing the wine to breathe in its maturing process.



**Activated charcoal filter:** The easy replaceable active charcoal filter purifies the incoming air to obtain an optimum odour-free interior.

The features shown are model dependent; the description applies to the relevant model.



## Perfect display for all your favourites

Stores wines like a professional wine cellar: the interior of the **WKb 4612** wine storage cabinet from the Barrique series has a constant temperature that can be set as needed from +5 °C to +20 °C using the control system with digital temperature display. With the capacity to hold 195 Bordeaux bottles, the spacious WKb 4612 is ideal for the long-term storage and maturation of wines. It also stores wines perfectly at the right serving temperature. The activated charcoal filter is easy to replace and provides optimal air quality. Wines are stored safely at all times on untreated wooden shelves. And thanks to the coated glass door, high-quality wines are well protected from UV radiation. The efficient LED lighting also ensures that the interior is illuminated evenly and pleasantly.

Also available in a shorter height as **WKb 4112**.

LED

Wine

# Wine storage sophistication for your home

Stores wine professionally like a wine cellar: The **WKb 4611** Barrique wine cabinet ensures a constant interior temperature, which can be adjusted between +5 °C and +20 °C. This makes the appliance great for the long-term storage and maturation of wines. The activated charcoal filter provides optimal air quality. Wines are always stored safely on untreated wooden shelves. The ergonomic slimline handle in black compliments the innovative design.

Wine









## The storage choice for wine aficionados

The high-quality **WKgb 4113** wine storage cabinet provides climatic conditions similar to those in a wine cellar. The appliance is ideal for the long-term storage of fine wines - be it for maturing or storage. The temperature can be adjusted from +5 °C to +20 °C. Our integrated activated carbon filter absorbs odours from the ambient air and prevents the taste of fine wines from being impaired.

The insulated full-black glass door also provides protection from UV radiation and preserves the quality of wine. And with its elegantly designed recessed handle, this wine cabinet looks perfect in any home or restaurant.

LED

Wine

## Superb conditions for fine wines

The **WKb 1712** wine cabinet, our most compact model from the Barrique series, can store up to 60 Bordeaux bottles. This unit ensures a constant temperature that can be set between +5 °C to +20 °C. Wines are stored optimally on two untreated height-adjustable wooden shelves. The activated charcoal filter is easy to replace and provides optimal air quality. Thanks to a tinted insulated glass door, high-quality wines are well protected from UV radiation. The LED lighting ensures that the interior is illuminated evenly and pleasantly – so wines can be presented with illumination even over a longer period. The ergonomic slimline handle in black compliments the innovative design.

LED


Wine





Wkes 653

# Features of the Liebherr Design & Lifestyle Appliances



LED

**LED lighting:** Liebherr's humidor has LED lighting with dimmer function incorporated in the glass door. As the LEDs emit virtually no heat, the cigars can be exposed to the light for long periods of time without damage.



LED

**LED lighting:** For ideal presentation of your best wine, the WKes 653 features LED lighting with dimmer function and separate switch. As the LEDs emit minimal heat and no UV radiation, wine can be showcased bathed in light for lengthy periods without compromising its quality.



**Fine cedar wood:** Our ZKes 453 humidor features two presentation boxes and two wooden shelves crafted from Spanish cedar wood. The presentation boxes are perfect for storing loose cigars.



**Wall mount option:** Both the WKes 653 wine cabinet and ZKes 453 humidor can be wall-mounted as an attractive eye-catcher with convenient access for serving.



**Ideal humidity:** The integrated water tray can accommodate one liter of distilled water for ideal humidity. Sensors regulate precise humidity level selected. The display informs when water needs to be replenished.



**Touch electronic control system:** The perfect wine storage temperature is +8 °C to +12 °C. White wine should ideally be stored below +10 °C and red wine at up to +18 °C. Our electronic control system allows temperature to be set to the exact degree required between +5 °C to +20 °C.

The features shown are model dependent; the description applies to the relevant model.



WKes 653 & ZKes 453



## The perfect climate for enjoying cigars and wine

Liebherr's approach in our entire product line is to provide ideal storage conditions – the humidor **ZKes 453** is no exception. Its innovative LCD display allows precise control to establish the proper balance of temperature and humidity so important to the optimal storage for fine cigars. The storage cabinet can be set from +16 °C to +20 °C and the humidity, controlled by a removable container for distilled water, can range from 68% to 75% humidity depending on your preferences.

LED Wine Smart Steel

And when it comes to savouring wine, the key is serving it at the ideal temperature. Storing wine at temperatures that are too high or too low impairs its flavour. The **WKes 653** wine storage cabinet in elegant stainless steel with glazed door has a compact footprint, measuring just 61 cm in height by 42 cm in width. Yet it can store a selection of up to 12 Bordeaux bottles (standard size 0.75 l) at perfect drinking temperature. With LED lighting with dimmer function and separate switch, your wine is always presented in the best light.

LED Cigar Smart Steel



With the option to wall mount or position on furniture, both the humidor ZKes 453 and WKes 653 wine cabinet provide a focal point in any environment. The most coveted cigars and wines in your collection will always be in sight and ready for your enjoyment.

# Freestanding



	SBSes 8486 PremiumPlus	SBSes 8484 PremiumPlus
	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>Bio Fresh-Plus</span> <span>No Frost</span> <span>Ice Maker</span> <span>Wine</span> <span>Soft System</span> <span>Soft Telescopic</span> <span>Smart Steel</span> </div>	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>Bio Fresh-Plus</span> <span>No Frost</span> <span>Ice Maker</span> <span>Soft System</span> <span>Soft Telescopic</span> <span>Smart Steel</span> </div>
Energy consumption (kWh/y) <sup>1</sup>	405	406
Refrigerator capacity litre	519	538
BioFresh comp. litre	132	304
Freezer capacity litre	126	126
Number of shelves	6	8
Number of door racks	5	5
Number of freezer drawers	5 with LED lighting	5 with LED lighting
Number of BioFresh drawers	3 with LED lighting	5 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic	2.4" TFT-colour temp. display, touch electronic
Door/side walls	stainless steel with SmartSteel / stainless steel with SmartSteel	stainless steel with SmartSteel / stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C	+2 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED ceiling lighting with dimmer function	LED ceiling lighting with dimmer function
Door alarm	visual and acoustic	visual and acoustic
IceMaker	fixed water connection 3/4"	fixed water connection 3/4"
Ice cube output kg/24h	1.2	1.2
SoftSystem	yes	yes
Door hinges	left/right	left/right
Product dimensions (H/W/D) cm <sup>1</sup>	185 / 121 / 66.5	185 / 121 / 66.5
Net weight kg	178.7	166
Voltage V/Hz	220-240/50/60	220-240/50/60

## Installation Diagram



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


## Freestanding



### SBSes 8683 PremiumPlus





### SBSes 8474 Premium



Energy consumption (kWh/y) <sup>1</sup>	405	406
Refrigerator capacity litre	366	539
BioFresh comp. litre	132	305
Freezer capacity litre	262	126
Number of shelves	6	8
Number of door racks	5	5
Number of freezer drawers	9 with LED lighting	5 with LED lighting
Number of BioFresh drawers	3 with LED lighting	5 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic	2.4" TFT-colour temp. display, touch electronic
Door /side walls	stainless steel with SmartSteel /stainless steel with SmartSteel	stainless steel with SmartSteel /stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C	+2 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED ceiling lighting with dimmer function	LED ceiling lighting with dimmer function
Door alarm	visual and acoustic	visual and acoustic
IceMaker	fixed water connection 3/4"	fixed water connection 3/4"
Ice cube output kg/24h	0.8	1.2
SoftSystem	yes	yes
Door hinges	left /right	left /right
Product dimensions (H/W/D) cm <sup>1</sup>	185 /121 /66.5	185 /121 /66.5
Net weight kg	164.3	163
Voltage V/Hz	220-240/50/60	220-240/50/60

### Installation Diagram





# Freestanding



	SBSbs 8673 Premium	SBSes 8673 Premium
	<div style="display: flex; justify-content: space-between; font-size: 8px;"> <span>Bio Fresh</span> <span>No Frost</span> <span>Ice Maker</span> <span>Soft System</span> <span>Soft Telescopic</span> <span>Black Steel</span> </div>	<div style="display: flex; justify-content: space-between; font-size: 8px;"> <span>Bio Fresh</span> <span>No Frost</span> <span>Ice Maker</span> <span>Soft System</span> <span>Soft Telescopic</span> <span>Smart Steel</span> </div>
Energy consumption (kWh/y) <sup>1</sup>	405	405
Refrigerator capacity litre	367	367
BioFresh comp. litre	133	133
Freezer capacity litre	262	262
Number of shelves	6	6
Number of door racks	5	5
Number of freezer drawers	9 with LED lighting	9 with LED lighting
Number of BioFresh drawers	3 with LED lighting	3 with LED lighting
Electronic control	2.4" TFT-colour temp. display, touch electronic	2.4" TFT-colour temp. display, touch electronic
Door/side walls	BlackSteel with SmartSteel/BlackSteel with SmartSteel	stainless steel with SmartSteel/stainless steel with SmartSteel
Refrigerator temperature range °C	+2 °C to +9 °C	+2 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED interior lighting	LED interior lighting
Door alarm	visual and acoustic	visual and acoustic
IceMaker	fixed water connection 3/4"	fixed water connection 3/4"
Ice cube output kg/24h	0.8	0.8
SoftSystem	yes	yes
Door hinges	left/right	left/right
Product dimensions (H/W/D) cm <sup>1</sup>	185/121/66.5	185/121/66.5
Net weight kg	161.3	161.3
Voltage V/Hz	220-240/50/60	220-240/50/60

### Installation Diagram



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

## Freestanding



1210



1210

### SBSes 7253 Premium





### SBSef 7242 Comfort




Energy consumption (kWh/y) <sup>1</sup>	562	589
Refrigerator capacity litre	364	391
BioFresh comp. litre	117	
Freezer capacity litre	261	261
Number of shelves	6	7
Number of door racks	4	5
Number of freezer drawers	8 with LED lighting	8
Number of BioFresh drawers	3	
Number of fruit and vegetable drawers		2
Electronic control	MagicEye with digital temp. display, touch electronic	MagicEye with digital temp. display, touch electronic
Door/side walls	stainless steel with SmartSteel/stainless steel	stainless steel with SmartSteel/silver
Refrigerator temperature range °C	+3 °C to +9 °C	+1 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED ceiling lighting	LED ceiling lighting
Door alarm	acoustic	acoustic
Door hinges	left/right	left/right
Product dimensions (H/W/D) cm <sup>1</sup>	185.2/121/63	185/121/63
Net weight kg	158.6	148.1
Voltage V/Hz	220-240/50	220-240/50

### Installation Diagram



## Freestanding




### CNef 4315 Comfort



Energy consumption (kWh/y) <sup>1</sup>	202
Refrigerator capacity litre	220
Freezer capacity litre	101
Number of shelves	4
Number of door racks	3
Number of freezer drawers	3
Number of BioCool drawers	1
Electronic control	2.4" TFT-monochrome temp. display, touch electronic
Door /side walls	stainless steel with SmartSteel / silver
Refrigerator temperature range °C	+1 °C to +9 °C
Freezer temperature range °C	-15 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	visual and acoustic
Door hinges	right, reversible
Product dimensions (H/W/D) cm <sup>1</sup>	185 / 60 / 66.5
Net weight kg	74.8
Voltage V/Hz	220-240/50/60

#### Installation Diagram



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

## Freestanding




### CNPef 4516 Comfort



Energy consumption (kWh/y) <sup>1</sup>	360
Refrigerator capacity litre	331
Freezer capacity litre	82
Number of shelves	5
Number of door racks	4
Number of freezer drawers	2
Number of fruit and vegetable drawers	2 with LED lighting
Electronic control	MagicEye with LCD temp. display, touch electronic
Door / side walls	stainless steel with SmartSteel / silver
Refrigerator temperature range °C	+2 °C to +7 °C
Freezer temperature range °C	-14 °C to -27 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED ceiling lighting
Door alarm	acoustic
Door hinges	right, reversible
Product dimensions (H/W/D) cm <sup>1</sup>	186 / 75 / 63
Net weight kg	95
Voltage V/Hz	220-240/50

### Installation Diagram





# Built-in



	ECBN 6256 PremiumPlus	ECBN 6156 PremiumPlus
	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>Bio Fresh</span> <span>No Frost</span> <span>Duo Cooling</span> <span>Ice Maker</span> <span>Soft System</span> </div>	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>Bio Fresh</span> <span>No Frost</span> <span>Duo Cooling</span> <span>Ice Maker</span> </div>
Energy consumption (kWh/y)	517	496
Refrigerator capacity litre	364	364
BioFresh comp. litre	69	69
Freezer capacity litre	116	116
Number of shelves	4	4
Number of door racks	6	6
Number of freezer drawers	2 with LED lighting	2 with LED lighting
Number of BioFresh drawers	2 with LED lighting	2 with LED lighting
Electronic control	MagicEye with digital temp. display, touch electronic	MagicEye with digital temp. display, touch electronic
Refrigerator temperature range °C	+3°C to +9°C	+3°C to +9°C
Freezer temperature range °C	-14°C to -28°C	-14°C to -28°C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED light column on both sides and LED ceiling lighting	LED light column on both sides and LED ceiling lighting
Door alarm	acoustic	acoustic
Water filter	yes	yes
IceMaker	fixed water connection 3/4"	fixed water connection 3/4"
Ice cube output kg/24h	1.3	1.3
SoftSystem	yes	
Door hinges	left/right	right
Product dimensions (H/W/D) cm	202.7/91/61	202.7/91/61
Cut out dimensions (H/W/D) cm	203.2-207.2/91.5/62.5	203.2-207.2/91.5/62.5
Net weight kg	160	164
Voltage V/Hz	220-240/50	220-240/50

## Installation Diagram






**ECBN 5066** PremiumPlus



Energy consumption (kWh/y)	489
Refrigerator capacity litre	284
BioFresh comp. litre	61
Freezer capacity litre	103
Number of shelves	4
Number of door racks	3
Number of freezer drawers	2 with LED lighting
Number of BioFresh drawers	2 with LED lighting
Electronic control	MagicEye with digital temp. display, touch electronic
Refrigerator temperature range °C	+3 °C to +9 °C
Freezer temperature range °C	-15 °C to -28 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED light column on both sides
Door alarm	acoustic
Water filter	yes
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	1.0
Door hinges	right
Product dimensions (H/W/D) cm	202.4/75.7/61
Cut out dimensions (H/W/D) cm	203.2-207.2/76.2/61
Net weight kg	148
Voltage V/Hz	220-240/50

**Installation Diagram**




# Built-in




	SICBN 3366 Premium	SICBN 3356 Premium
	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span style="background-color: #d9ead3; padding: 2px;">Bio Fresh</span> <span style="background-color: #d9ead3; padding: 2px;">No Frost</span> <span style="background-color: #d9ead3; padding: 2px;">Duo Cooling</span> <span style="background-color: #d9ead3; padding: 2px;">Ice Maker</span> <span style="background-color: #d9ead3; padding: 2px;">Soft System</span> <span style="background-color: #d9ead3; padding: 2px;">Soft Telescopic</span> </div>	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span style="background-color: #d9ead3; padding: 2px;">Bio Fresh</span> <span style="background-color: #d9ead3; padding: 2px;">No Frost</span> <span style="background-color: #d9ead3; padding: 2px;">Duo Cooling</span> <span style="background-color: #d9ead3; padding: 2px;">Soft System</span> <span style="background-color: #d9ead3; padding: 2px;">Soft Telescopic</span> </div>
Energy consumption (kWh/y)	340	335
Refrigerator capacity litre	179	179
BioFresh comp. litre	68	68
Freezer capacity litre	59	63
Number of shelves	4	4
Number of door racks	2	2
Number of freezer drawers	4 with LED lighting	3 with LED lighting
Number of BioFresh drawers	2 with LED lighting	2 with LED lighting
Electronic control	MagicEye with LCD temp. display, touch electronic	MagicEye with LCD temp. display, touch electronic
Refrigerator temperature range °C	+3°C to +9°C	+3°C to +9°C
Freezer temperature range °C	-14°C to -26°C	-14°C to -26°C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED light column on both sides	LED light column on both sides
Door alarm	acoustic	acoustic
IceMaker	fixed water connection 3/4"	
Ice cube output kg/24h	0.8	
SoftSystem	yes	yes
Door hinges	left, reversible	right, reversible
Product dimensions (H/W/D) cm	177+1.6/55.9/54.4	177+1.6/55.9/54.4
Cut out dimensions (H/W/D) cm	177.2-178.8/56-57/55	177.2-178.8/56-57/55
Net weight kg	79	76.6
Voltage V/Hz	220-240/50	220-240/50

## Installation Diagram



\* Recommended: 560 mm



\* Recommended: 560 mm

# Built-in



## SICN 3366 Premium




## SICN 3356 Premium




Energy consumption (kWh/y)	336	329
Refrigerator capacity litre	196	198
Freezer capacity litre	59	63
Number of shelves	5	5
Number of door racks	3	3
Number of freezer drawers	4 with LED lighting	3 with LED lighting
Number of BioCool drawers	1 with LED lighting	1
Electronic control	MagicEye with LCD temp. display, touch electronic	MagicEye with LCD temp. display, touch electronic
Refrigerator temperature range °C	+1 °C to +9 °C	+1 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic	visual and acoustic
Defrost type	automatic	automatic
Interior light	LED light column left	LED light column left
Door alarm	acoustic	acoustic
IceMaker	watertank	
Ice cube output kg/24h	0.8	
SoftSystem	yes	yes
Door hinges	left, reversible	right, reversible
Product dimensions (H/W/D) cm	177+1.6/55.9/54.4	177+1.6/55.9/54.4
Cut out dimensions (H/W/D) cm	177.2-178.8/56-57/55	177.2-178.8/56-57/55
Net weight kg	73.6	67.6
Voltage V/Hz	220-240/50	220-240/50

### Installation Diagram



\* Recommended: 560 mm




\* Recommended: 560 mm

# Built-in




	SICN 3314 Comfort	SIKB 3550 Premium
	<div style="display: flex; justify-content: space-around;"> <div style="background-color: #d9ead3; padding: 2px;">Bio Cool</div> <div style="background-color: #d9ead3; padding: 2px;">No Frost</div> <div style="background-color: #d9ead3; padding: 2px;">Duo Cooling</div> </div>	<div style="display: flex; justify-content: space-around;"> <div style="background-color: #d9ead3; padding: 2px;">Bio Fresh</div> <div style="background-color: #d9ead3; padding: 2px;">Soft System</div> <div style="background-color: #d9ead3; padding: 2px;">Soft Telescopic</div> </div>
Energy consumption (kWh/y)	300	328
Refrigerator capacity litre	198	308
BioFresh comp. litre		92
Freezer capacity litre	63	
Number of shelves	5	8
Number of door racks	3	5
Number of freezer drawers	3	
Number of BioFresh drawers		3 with LED lighting
Number of BioCool drawers	1	
Electronic control	MagicEye with LCD temp. display, key electronic	MagicEye with LCD temp. display, touch electronic
Refrigerator temperature range °C	+1 °C to +9 °C	+3 °C to +9 °C
Freezer temperature range °C	-14 °C to -26 °C	
Temperature alarm	visual and acoustic	
Defrost type	automatic	automatic
Interior light	LED interior lighting	LED light column on both sides
Door alarm	acoustic	acoustic
SoftSystem		yes
Door hinges	right, reversible	right, reversible
Product dimensions (H/W/D) cm	177+1.6/55.9/54.4	177+1.6/55.9/54.4
Cut out dimensions (H/W/D) cm	177.2-178.8/56-57/55	177.2-178.8/56-57/55
Net weight kg	64.3	75
Voltage V/Hz	220-240/50	220-240/50

## Installation Diagram



\* Recommended: 560 mm



\* Recommended: 560 mm

## Built-in




### SIGN 3576 Premium

No Frost	LED	Ice Maker	Soft System	Telescopic Rails
----------	-----	-----------	-------------	------------------

Energy consumption (kWh/y)	331
Freezer capacity litre	207
Number of freezer drawers	9
Electronic control	MagicEye with LCD temp. display, touch electronic
Freezer temperature range °C	-14 °C to -26 °C
Temperature alarm	visual and acoustic
Defrost type	automatic
Interior light	LED interior lighting
Door alarm	acoustic
IceMaker	fixed water connection 3/4"
Ice cube output kg/24h	0.8
SoftSystem	yes
Door hinges	left, reversible
Product dimensions (H/W/D) cm	177+1.6/55.9/54.4
Cut out dimensions (H/W/D) cm	177.2-178.8/56-57/55
Net weight kg	73.9
Voltage V/Hz	220-240/50

### Installation Diagram



\* Recommended: 560 mm

# Undercounter



82-88



82-88

	<b>SUIKO 1550</b> Premium <small>Soft Telescopic</small>	<b>SUIKO 1510</b> Comfort <small>Soft System</small>
Energy consumption (kWh/y)	158	147
Refrigerator capacity litre	124	136
Number of shelves	2	4
Number of door racks		2
Number of fruit and vegetable drawers	1	1
Electronic control	MagicEye with LCD temp. display, key electronic	MagicEye with LCD temp. display, key electronic
Refrigerator temperature range °C	+2°C to +9°C	+2°C to +9°C
Defrost type	automatic	automatic
Interior light	LED ceiling lighting	LED interior lighting
Door alarm	visual and acoustic	visual and acoustic
Door type	steel	steel
SoftSystem		yes
Door hinges	pullout	right, reversible
Product dimensions (H/W/D) cm	82-88/59.7/55	82-88/59.7/55
Cut out dimensions (H/W/D) cm	82-88/60/55	82-88/60/55
Net weight kg	41.5	34.5
Voltage V/Hz	220-240/50	220-240/50/60
<b>Installation Diagram</b>		

# Undercounter




82-88

## SUIG 1514 Comfort

Smart Frost Soft System

Energy consumption (kWh/y)	168
Freezer capacity litre	95
Number of freezer drawers	3
Electronic control	MagicEye with LCD temp. display, key electronic
Freezer temperature range °C	-14 °C to -26 °C
Defrost type	manual
Door alarm	visual and acoustic
Door type	steel
SoftSystem	yes
Door hinges	left, reversible
Product dimensions (H/W/D) cm	82-88/59.7/55
Cut out dimensions (H/W/D) cm	82-88/60/55
Net weight kg	38.2
Voltage V/Hz	200-240/50

### Installation Diagram



## Wine Cabinets



	WTes 5872 Vinidor	WTes 5972 Vinidor
	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>LED</span> <span style="background-color: #f08080; padding: 2px;">Wine</span> <span>Soft System</span> <span>Telescopic Rails</span> </div>	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>LED</span> <span style="background-color: #f08080; padding: 2px;">Wine</span> <span>Telescopic Rails</span> </div>
Energy consumption (kWh/y) <sup>1</sup>	245	248
Total capacity litre	511	526
Max. No. of Bordeaux bottles (0.75l) <sup>2</sup>	178	211
Number of shelves	13	10
Shelves on telescopic rails	10	8
Shelf material	beech wood shelves	beech wood shelves
Presentation shelf	1	1
Electronic control	LCD temp. display for 3 wine zones, touch electronic	LCD temp. display for both wine zones, touch electronic
Temperature range °C	+5 °C to +20 °C	+5 °C to +20 °C
Temperature zones	3	2
Temperature alarm	visual and acoustic	visual and acoustic
Interior light	LED lighting permanently on, dimmable	LED lighting permanently on, dimmable
Door alarm	acoustic	acoustic
Safety thermostat	yes	yes
Activated Charcoal filter	yes	yes
Door type	glass door with stainless steel frame	glass door with stainless steel frame
Integrated lock	yes	yes
SoftSystem	yes	
Door hinges	right, reversible	right, reversible
Product dimensions (H/W/D) cm <sup>1</sup>	192/70/74.2	192/70/74.2
Net weight kg	135	124
Voltage V/Hz	220–240/50	220–240/50
<b>Installation Diagram</b>		


<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

## Wine Cabinets




### WKt 6451 GrandCru




Energy consumption (kWh/y)	143
Total capacity litre	625
Max. No. of Bordeaux bottles (0.75l) <sup>2</sup>	312
Number of shelves	7
Shelf material	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic
Temperature range °C	+5 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED interior lighting
Door alarm	acoustic
Safety thermostat	yes
Activated Charcoal filter	yes
Door type	full door, terra
Integrated lock	yes
Door hinges	right, reversible
Product dimensions (H/W/D) cm	193/74.7/75.9
Net weight kg	86
Voltage V/Hz	220–240/50

### Installation Diagram



# Wine Cabinets



178



82-87

	<b>EWTdf 3553</b> Vinidor	<b>UWTes 1672</b> Vinidor
	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>LED</span> <span style="background-color: #f08080; padding: 2px;">Wine</span> <span>Soft System</span> <span>Telescopic Rails</span> </div>	<div style="display: flex; justify-content: space-around; font-size: 8px;"> <span>LED</span> <span style="background-color: #f08080; padding: 2px;">Wine</span> <span>Telescopic Rails</span> </div>
Energy consumption (kWh/y)	162	190
Total capacity litre	256	94
Max. No. of Bordeaux bottles (0.75l) <sup>1</sup>	80	34
Number of shelves	10	5
Shelves on telescopic rails	8	3
Shelf material	beech wood shelves	beech wood shelves
Presentation shelf	1	
Electronic control	LCD temp. display for both wine zones, touch electronic	MagicEye with digital temp. display for both wine zones, key electronic
Temperature range °C	+5 °C to +20 °C	+5 °C to +20 °C
Temperature zones	2	2
Temperature alarm	visual and acoustic	visual and acoustic
Interior light	LED lighting permanently on, dimmable	LED lighting permanently on, dimmable
Door alarm	acoustic	acoustic
Safety thermostat	yes	yes
Activated Charcoal filter	yes	yes
Door type	panel ready or stainless steel panel as accessory	glass door with stainless steel frame
Integrated lock		yes
SoftSystem	yes	
Door hinges	right, reversible	right, reversible
Product dimensions (H/W/D) cm	177 / 55.7 / 55.3	81.8 / 59.7 / 57.5
Cut out dimensions (H/W/D) cm	178 / 56 / 55	82-87 / 60 / 58
Net weight kg	88	49
Voltage V/Hz	220 – 240/50	220 – 240/50
<b>Installation Diagram</b>		

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

# Wine Cabinets



82-87



45

## UWKes 1752 GrandCru



LED Wine Telescopic Rails

## WKees 553 GrandCru


LED Wine Telescopic Rails

Energy consumption (kWh/y)	145	130
Total capacity litre	112	47
Max. No. of Bordeaux bottles (0.75l) <sup>1</sup>	46	18
Number of shelves	4	3
Shelves on telescopic rails	3	2
Shelf material	beech wood shelves	beech wood shelves
Electronic control	MagicEye with digital temp. display, key electronic	LCD temp. display, touch electronic
Temperature range °C	+5 °C to +20 °C	+5 °C to +20 °C
Temperature zones	1	1
Temperature alarm	visual and acoustic	visual and acoustic
Interior light	LED lighting permanently on	LED lighting permanently on, dimmable
Door alarm	acoustic	acoustic
Safety thermostat	yes	
Activated Charcoal filter	yes	yes
Door type	glass door with stainless steel frame	glass door with stainless steel frame
Integrated lock	yes	
Door hinges	right, reversible	right, reversible
Product dimensions (H/W/D) cm	81.8/59.7/57.5	44.1/55.7/52.2
Cut out dimensions (H/W/D) cm	82-87/60/58	45/56/55
Net weight kg	44	31
Voltage V/Hz	220-240/50	220-240/50

### Installation Diagram



## Wine Cabinets Barrique



◀66▶



◀66▶


	<b>WKb 4612</b> Barrique <span style="background-color: #ADD8E6; padding: 2px;">LED</span> <span style="background-color: #F08080; padding: 2px;">Wine</span>	<b>WKb 4611</b> Barrique <span style="background-color: #F08080; padding: 2px;">Wine</span>
Energy consumption (kWh/y)	204	175
Total capacity litre	336	336
Max. No. of Bordeaux bottles (0.75l) <sup>1</sup>	195	195
Number of shelves	7	7
Shelf material	beech wood shelves	beech wood shelves
Presentation shelf	1	
Electronic control	MagicEye with digital temp. display, key electronic	MagicEye with digital temp. display, key electronic
Temperature range °C	+5 °C to +20 °C	+5 °C to +20 °C
Temperature zones	1	1
Temperature alarm	visual and acoustic	visual and acoustic
Interior light	LED interior lighting	light bulb
Door alarm	acoustic	acoustic
Safety thermostat	yes	yes
Activated Charcoal filter	yes	yes
Door type	glass door with handle, frame black	full door with handle, black
Integrated lock	yes	yes
Door hinges	right, reversible	right, reversible
Product dimensions (H/W/D) cm	184/66/67	184/66/67
Net weight kg	86	68.5
Voltage V/Hz	220–240/50	220–240/50
<b>Installation Diagram</b>		

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

## Wine Cabinets Barrique



◀66▶



◀66▶



◀66▶

	<b>WKgb 4113</b> Barrique <span>LED</span> <span>Wine</span>	<b>WKb 4112</b> Barrique <span>LED</span> <span>Wine</span>	<b>WKb 1712</b> Barrique <span>LED</span> <span>Wine</span>
Energy consumption (kWh/y)	1570	178	149
Total capacity litre	293	293	121
Max. No. of Bordeaux bottles (0.75l) <sup>1</sup>	168	168	60
Number of shelves	6	6	3
Shelf material	beech wood shelves	beech wood shelves	beech wood shelves
Presentation shelf	1	1	
Electronic control	MagicEye with digital temp. display, key electronic	MagicEye with digital temp. display, key electronic	MagicEye with digital temp. display, key electronic
Temperature range °C	+5 °C to +20 °C	+5 °C to +20 °C	+5 °C to +20 °C
Temperature zones	1	1	1
Temperature alarm	visual and acoustic	visual and acoustic	visual and acoustic
Interior light	LED interior lighting	LED interior lighting	LED interior lighting
Door alarm	acoustic	acoustic	acoustic
Safety thermostat	yes	yes	yes
Activated Charcoal filter	yes	yes	yes
Door type	glass door with recessed handle, frame black	glass door with handle, frame black	glass door with handle, frame black
Integrated lock	yes	yes	yes
Door hinges	right	right, reversible	right, reversible
Product dimensions (H/W/D) cm	167 / 66 / 67	167 / 66 / 67	85 / 66 / 67
Net weight kg	78	78	45
Voltage V/Hz	220–240/50	220–240/50	220–240/50
<b>Installation Diagram</b>			




**WKes 653** GrandCru

LED Wine Smart Steel

Energy consumption (kWh/y)	75
Total capacity litre	38
Max. No. of Bordeaux bottles (0.75l) <sup>1</sup>	12
Number of shelves	3
Shelf material	beech wood shelves
Electronic control	LCD temp. display, touch electronic
Temperature range °C	+5 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame and SmartSteel
Integrated lock	yes
Door hinges	right
Product dimensions (H/W/D) cm	61.2 / 42.5 / 47.8
Net weight kg	29
Voltage V/Hz	220 – 240/50

**Installation Diagram**



<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).




**ZKes 453** Humidor



Energy consumption (kWh/y)	162
Total capacity litre	39
Number of shelves	2
Shelf material	Spanish cedar wood shelves
Electronic control	LCD temp. display, touch electronic
Temperature range °C	+16 °C to +20 °C
Temperature zones	1
Temperature alarm	visual and acoustic
Interior light	LED lighting permanently on, dimmable
Door alarm	acoustic
Activated Charcoal filter	yes
Door type	glass door with stainless steel frame and SmartSteel
Integrated lock	yes
Door hinges	right
Product dimensions (H/W/D) cm	61.2/42.5/47.8
Net weight kg	30
Voltage V/Hz	220–240/50

**Installation Diagram**





Click the link to directly access  
our social media channels:  
[socialmedia.home.liebherr.com](https://socialmedia.home.liebherr.com)

Liebherr Sales Kluang Sdn Bhd  
No. 1 & 3, Jalan Serendah 26/40, Seksyen 26,  
Pekan Hicom, 40400 Shah Alam, Selangor  
e-mail: [info.lkl@liebherr.com](mailto:info.lkl@liebherr.com)