

Refrigerators and freezers
CounterTop

Quality, Design and Innovation



LIEBHERR

For chilled and frozen display without compromise

Liebherr's compact yet spacious CounterTop appliances enhance your sales where space is limited. In bars, restaurants or on sales counters – the Liebherr CounterTop appliances attract impulse purchases of beverages and ice creams. They combine the flexible use of storage space, bright and efficient LED lighting and maximum product visibility. Customised

colour schemes and unique branding possibilities ensure the focus is on what's most important - the products for sale. Low energy consumption, compact design, flexible use and robust build-quality are also good reasons to choose Liebherr CounterTop appliances.



Vertical LED interior light.

Ideal for the attractive product presentation. The LED light column is integrated in the side wall and ensures attractive illumination. The focus is therefore always on the products.



Wire shelves.

The plastic-coated grid shelves are height-adjustable in 15 mm increments and the interior can be arranged and used in a variable manner depending on the size of the products. This means the customers always have easy access to the contents. The shelves are close-meshed for even small items and extremely resilient so that products are always stored securely. There is also a bar across the front of the shelf to prevent items falling out.



Temperature display.

The LED temperature display is integrated in the front panel of the CounterTop Fv 913. The temperature can be precisely set and clearly displayed.




Fan-assisted cooling.

On the CounterTop appliances BCv 1103 and Fv 913, highly efficient fans ensure that contents are frozen or cooled rapidly, guaranteeing uniform temperature distribution throughout the entire interior. Liebherr's dynamic cooling system is a huge advantage during events when appliances are frequently restocked.



Door profiles, recessed grip, replaceable gaskets.

Aluminium door profiles with a continuous recessed grip are not only elegant, they also make the door easier to open. The replaceable door gasket adds to the efficient operation. It can easily be inserted, cleaned or replaced, thus enabling perfect hygiene.



Replaceable door hinge.

The CounterTop appliances are right hand hinged as standard and can be changed to the left if necessary. They can be adapted on site to suit each location.



Facings.

The appliances are designed for maximum product visibility. Facing examples, 30 x 0.33 litre cans, 28 x 0.33 litre slimline cans, 12 x 0.5 litre PET bottles.

CounterTop appliances



Accessories

Connecting frame

To make best use of the available space, with the connecting frame the CounterTop appliances BCv 1103 (refrigeration) and Fv 913 or F 913 (both freezing) can be combined on top of, or next to one another.




CounterTop appliances

	BCv 1103 Fridge	Fv 913 Freezer	F 913 Freezer
Total gross/net capacity	110/90 l	88/74 l	88/88 l
Exterior dimensions in mm (w/d/h)	497/558/816	497/558/816	497/558/816
Interior dimensions in mm (w/d/h)	417/391/651	377/371/611	377/430/611
Ambient temperature range	+10°C to +32°C	+10°C to +32°C	+10°C to +32°C
Refrigerant	R 600a	R 290	R 290
Sound power level	49 dB(A)	62 dB(A)	
Connection rating	1.0 A	1.5 A	1.5 A
Frequency/voltage	50 Hz/220–240V~	50 Hz/220–240V~	50 Hz/220–240V~
Cooling system	fridge/freezer comp.	–/dynamic	–/static
Defrost	fridge/freezer comp.	–/automatic	–/manual
Temperature range	fridge/freezer comp.	–/–10°C to –25°C	–/–10°C to –25°C
External cabinet finish	steel/silver	steel/silver	steel/silver
Door/lid material	glass door	glass door	glass door
Internal liner material	steel	steel	steel
Type of control	analogue control	electronic controller	analogue control
Temperature display	internal analogue	external digital	internal analogue
Interior light	LED light column on right	LED light column on right	LED light column on right
Fault: warning signal		visual and audible	
Adjustable shelves	2	2	2
Shelf material	wire shelves plastic-coated	wire shelves plastic-coated	wire shelves plastic-coated
Loading capacity 0.5L PET/facings 0.5L PET	51/6		
Loading capacity 0.33L can/facings 0.33L can	147/6		
Shelf loading	30 kg	30 kg	30 kg
Handle	recessed grip	recessed grip	recessed grip
Lock	fitted	fitted	fitted
Self-closing door	yes	yes	yes
Door hinges	right, reversible on site	right, reversible on site	right, reversible on site
Insulation	40 mm	60 mm	60 mm
Gross/net weight	43,2/41 kg	51,5/49 kg	49,5/47 kg
Accessories			
Connecting frame	on request	on request	on request

Liebherr commercial appliances can be found at specialist retailers where providing first-class service and expert advice is their top priority.

You can find an overview of all Liebherr appliances in our catalogues. Available in stores or on home.liebherr.com.



Smart communication on all fronts



Discover the world of Liebherr-Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!



Click the link to directly access our social media channels:
socialmedia.home.liebherr.com



The Liebherr-Hausgeräte YouTube channel provides interesting and helpful films showing you the functions of Liebherr refrigerators and freezers.



Learn all about our current social media channels.
socialmedia.home.liebherr.com



Find out which app is available for which operating system (Apple, Android etc.), and which device type.
apps.home.liebherr.com

Subject to modification. Current data see home.liebherr.com.
Printed in Germany by Typodruck GmbH. 7900813-007/103.2019

