




# Customised branding – optimised merchandising

Discover the stylish design options available for our refrigerators and freezers



# LIEBHERR

Quality, Design and Innovation



# Increase awareness of your brand

Liebherr refrigerators and freezers tick all the boxes by offering you a stunning custom-designed brand look as well as a host of special features. We offer an extensive range of appliances with customer-specific fittings and features, so it's easy to find the right one to meet your particular requirements.

## Contents

- Good reasons to choose Liebherr \_\_\_\_\_ 04
- Leading brands use customised branding \_\_\_\_\_ 06
- How to put your brand in the limelight \_\_\_\_\_ 07
- Your branding in the right light \_\_\_\_\_ 08
- An overview of the customised display options \_\_\_\_\_ 10
- Choose your own customised features \_\_\_\_\_ 12
- Choose your own customised accessories \_\_\_\_\_ 14
- Upright bottle coolers \_\_\_\_\_ 18
- Chest-type bottle coolers \_\_\_\_\_ 30
- Ice cream chest freezers \_\_\_\_\_ 32
- Glass door display freezers \_\_\_\_\_ 36

# Good reasons to choose Liebherr



## Product presentation

Attractive product presentation is the best way to promote sales. Liebherr appliances are designed to present all products captivatingly to their very best advantage at all times, enticing customers to reach for them. Incorporating company logos and brand-specific images, our appliances are truly eye-catching.



## Design and look

High-performance technology at its very best: Liebherr attaches great importance to the overall design concept of its appliances to ensure that they radiate both elegance and design quality. And, thanks to this meticulous design, Liebherr appliances always combine extremely well and look sensational.



## Optimum performance

Liebherr drinks coolers and freezers offer perfect refrigeration performance, even under extreme ambient conditions. Using state-of-the-art components, high-performance and environmentally-friendly refrigerants, and precise controls these appliances guarantee top product quality and freshness.




## Efficiency

The combination of powerful compressors, precise electronic controls, highly effective insulation, and high-performance CFC-free refrigerants results in low energy consumption and correspondingly low operating costs. The high quality of our virtually maintenance-free, service-friendly appliances guarantees their long service life and functional reliability.



## Robust quality

Liebherr appliances are specially designed for intensive professional use and are therefore exceptionally robust. Only the highest quality materials are used and careful attention is paid to the very finest of details. Meticulous testing ensures the outstanding quality of Liebherr appliances. All electronic and refrigeration-related components are optimally balanced to ensure the highest levels of functionality and efficiency.



## Easy to clean

Hygiene is critically important in the commercial sector and therefore the interiors of Liebherr appliances feature large corner radii, which allow very easy cleaning. The grid shelves are easily removed for cleaning and are also height-adjustable and can accommodate all sorts of different sized items.

# Leading brands use customised branding

# How to put your brand in the limelight



The brands shown above are a just a few of our clients: Liebherr currently customises refrigerators and freezers for over 200 different brands.

Liebherr appliances can be individually styled using the current branding options described below. These differ from both a technical and cost perspective, depending on the specific requirements and on the quantities involved.



PVC stickers (vinyls)

This popular and by far the most commonly used technique involves the supplier printing the required design onto a suitable sticker material (usually PVC) using either silk-screen or digital printing, depending on the quantity and the image. Liebherr then manually applies the vinyl to the outer housing of the appliance.



Dye sublimation – inkjet printer paper

As with the printing of PVC stickers, this decorative process involves two steps and is carried out by our supplier. In the first step a sublimation paper of the design is created using inkjet digital printing. This is then used to transfer the design onto the specially-coated, flat and unformed base material. Under controlled heat and pressure, the inks then penetrate the material's surface to create a permanent full-colour image.

# Your branding in the right light



Customised colour schemes

A customised colour scheme presents your brand in a visually strong, attention-demanding manner and promotes the appeal of your products. Several materials and effects can be used to add customer-specific designs to side walls, door frames, handles, plinths, display frames and compartment interiors.



Glass door vinyls

Vinyls with individually designed brand images can be adhered to the glass door. These are also available as 'non-permanent' stickers. If necessary, these can be easily removed at any time without leaving any visible trace.



LED lighting integrated into the glass door

An individual motif can be engraved on the inside of the glass door and illuminated with LEDs. Only the motif is illuminated so that it stands out very impressively. The engraving is set between the two panes of glass and is suitable for FKv 50 and FKv 30 appliances.



BlackSteel

BlackSteel is a visually stunning and exceptionally appealing black stainless steel. Paired with a high-quality SmartSteel finish, BlackSteel lends an appliance both high-tech appeal and timeless elegance. The transverse-polished finish gives BlackSteel appliances a compelling and exclusive appearance, and significantly reduces the visibility of fingerprints on the doors and side walls. The finish is also easy to clean and much less sensitive to scratches.



3D branding

3D branding gives an appliance extraordinary visual appeal and opens up new opportunities for creatively using images in advertising graphics. An innovative technique is employed to create high-quality stickers using 3D lenticular printing. In addition, we can apply different printing levels and layers to glass door surfaces to create a 3D effect when combined with the right backlighting. 3D branding transforms any appliance into a stunning, unique, head-turning feature that is sure to encourage impulse buying.



3D effect



Lenticular technique

# An overview of the display options

Liebherr offers great-looking display options that draw more attention to your appliances, products and brand. The display panel can be styled according to the customer's specific preferences.

## Interior LightGuide display

The transparent LightGuide display, which is installed on the inside of the door, is partially illuminated. It combines clear product visibility and at the same time attracts great attention to your logo.



FKDv 4523

## Exterior LightGuide display

The fully illuminated exterior LightGuide display, which is attached to the outside of the door, places your brand in the limelight and is guaranteed to attract people's attention. No separate power supply is required for the lighting.



FKDv 4513

## Interior door sticker

The sticker on the inside at the top of the glass door and is effectively illuminated by the ceiling lighting.



FKDv 4503

## LED backlit display

The LED backlit display attracts a high amount of attention to the brand.



FKDv 42..

# Choose your own individual features

Design your appliance exactly how you want it! The exceptional branding opportunities offered by Liebherr enable appliances to be factory fitted with a variety of features and extras upon request.

## Dimmable LED lighting

FKDv models can be fitted with a rotary control dial for dimming the lighting. The appliance's interior brightness level can then be adjusted to optimally illuminate the interior and to provide ideal product presentation.



FKDv 42../4503/4513

## Labels for scanner rails

The scanner rails can be attached to the grid shelves to provide customers with information about products and their prices. Labels with individual customer branding can also easily be inserted into the scanner rails.



FKDv, BCDv 10., FKv(sl) 26../36../41..

## EMS controller

EMS controller – fitted as standard on the FKDv 4523 and available as a special feature for other display refrigerators – is a convenient technology designed to improve energy efficiency. It detects, for example, door opening cycles: the refrigeration system then provides only the required cooling capacity and, in combination with the 'lights out' function, significant energy savings can be made.



FKDv 42../4503/4513

## Connection cable with appliance coupler

Thanks to the design of the appliance coupler, the connection cable is easy to replace and the appliance can be disconnected from the mains without any trouble. Appliances with the same mains voltage can also be interchanged more quickly. The coupler is standardised and suitable for use in all countries.



FKDv

## Castors with a brake

Castors are particularly practical for chest-type appliances that require frequent repositioning. Four 75 mm swivel castors are available as accessories – two with and two without brake.



GTI, GTE, FT

## Rear wall cover


When fitted with the additional rear wall cover appliances look great from every angle and are ideal for freestanding use. They blend better into the installation environment and the rear wall surface can be used for branding.



FKDv in climate class 5

## Self-closing door

The door closes automatically after being opened to ensure that the appliance is never left open for too long and thereby maintain the appliance's efficiency.



FKDv 42..

## Additional LED side lighting

For optimised illumination and presentation of products, our various display refrigerators come with LED lighting on either one or both sides, as standard. Upon request, models with single side lighting can be fitted with additional lighting on the other side.



FKDv 42../4503/4513

# Choose your own appliance accessories

## Grid shelf

The highly resilient wire shelves have an abrasion-resistant coating and are designed for heavy shelf loads. They are height-adjustable to facilitate versatile use of the interior.

FKDv 4523	7113339		
FKDv 4513/03, FKDv 4213/11/03	7113337	FKv(sl) 54..	7113409
FDv, Fv	7438722	FKv(sl) 41../36../26..	7113413



## Additional display attachment

The 60-cm-wide illuminated display can be retrofitted to FKvsl models and is sure to draw a high degree of attention to the appliance and to its contents. The design of the display panel can be adapted to meet individual requirements.

FKv(sl) 26-41	9600457
---------------	---------



## Display protection guard

The safety guard provides added protection for the illuminated advertising display. Once the appliance has been positioned, the display protection can be folded backwards and out of the way so that it does not need to be detached and then reattached for subsequent relocations.

FKDv 42..	7790669
-----------	---------



## Wire basket for scoop ice cream containers

The robust wire baskets for holding scoop ice-cream containers have been designed specifically for the GTE chest freezers. Standard containers fit exactly in the wire baskets so that the ice cream is both perfectly presented and can be easily scooped out.


GTE	7113395
-----	---------



## Baskets for ice-cream cabinets

The baskets are designed for an orderly presentation of loose products.


FT	250 mm basket: 7113393
	210 mm basket: 7113319
GTE	250 mm basket: 7113399
	210 mm basket: 7113397



## Gravity feed shelf (bottle slide)

With the practical gravity feed shelf, bottles are always positioned to the front where they are easy to access. The gravity feed shelf is available with or without telescopic rails.

FKDv	Fixed gravity feed shelf	9007045
FKDv, FKv(sl) 26../36../41..	Pull-out gravity feed shelf	9007659



## Baskets for display freezers

The sturdy basket offers a capacity of 30 or 42 litres.

FDv, Fv	42-litre basket: 7111754
	30-litre basket: 7111758



## Castors with a brake

Castors are particularly practical if chest freezers need to be frequently moved around. Two high-quality, rubber-coated 50 mm castors with brakes are available as accessories. The brake ensures that the appliance is securely fixed in position at its installation site.

GTI, GTE, FT	7044750
--------------	---------



## Perforated metal shelf cover

The additional perforated metal cover together with the sturdy shelves provide a solid base and maximum stability for all types of bottles and containers. The perforated metal shelf covers are extremely tough and optimally suited for storing drinks.

FKDv	7746179
------	---------



## Castors for protection guard

To make it easier to transport appliances, two sturdy castors can be directly attached to the protection guard at the back. This enables the appliance to be easily moved around, similar to pushing a hand truck.

FKDv, FKv(sl) 36../41../54..	7790761
------------------------------	---------



# Choose your individual accessories

## Castor base

The robust castor base makes transportation far easier, especially if refrigerators are regularly moved around. Thanks to their superb workmanship and quality these castor bases are extremely durable.

FKvsl 54..	9086381		
FKv 54..	9086365		
FKvsl 36../26..	9086321	FKv 36../26..	9086323



## Scanner rails

Price labels and scan codes can be optimally read from the practical scanner rail, which attaches to the front of the grid shelves to give customers an instant, clear view of the prices or product information.

FDv, Fv	7443779
BCDv 10..	7440727



## Flexible scanner rails

The flexible scanner rails, made from premium-quality plastic, give customers product information at a glance and still allow drinks to be removed easily. Their flexibility means they are exceptionally easy to use and that it's quicker than ever to replenish appliance stocks. The scanner rails attach to the grid shelves and are available as accessories.

FKDv, FKv(sl) 26../36../41..	7435063
------------------------------	---------



## Lock

The FKDv 4513, which does not include a lock as standard, can be fitted with a lock.

FKDv 4513	9590067
-----------	---------



## Protection guard

When transporting larger FKv(sl) models and FKDv 45 models, the robust protection guard protects the condenser at the back of the appliance and the appliance underside from impacts. It is ideal for transporting unpacked appliances by lorry.

FKDv 45..	7790671	FKv(sl) 54..	7790739
FKv(sl) 41..	7790747	FKv(sl) 36..	7790773



## Alternative lock barrels

Certain appliances are fitted with identical locks as standard, so that a single key can be used to lock and unlock several appliances. Customised lock solutions with up to ten different locks and keys are available for FKDv 42.. and FKv 43.. models.

FKDv 42.., FKv..43	on request
--------------------	------------



## Key lock for solid lid

All chest freezers with a solid lid can be fitted with a key lock to protect their contents.

GTE ..00, FT ..00	7042835
-------------------	---------



## Key lock for sliding glass lid

All chest freezers with a sliding glass lid can be fitted with a key lock to protect their contents.

GTI, GTE ..52../02, FT ..02	7042845
-----------------------------	---------



## Height-adjustable feet

The height-adjustable feet are robust and provide sufficient ground clearance to allow easy and convenient cleaning underneath the appliance.

FKv(sl) 54..	9590229
FKv(sl) 36../26..	9590231



## Partition grid

Partition grids for the baskets contribute to optimal product presentation and enable flexible interior arrangements.

GTI	250 mm partition grid: 7113345	FDv, Fv	Partition grid for 42-litre basket: 7111755
	210 mm partition grid: 7113343		Partition grid for 30-litre basket: 7111759
GTE	250 mm partition grid: 7113349		
	210 mm partition grid: 7113347		



# Upright bottle coolers



FKDv 42

**ADDITIONAL INFORMATION:**

- Maximum of four gravity feed shelves per appliance
- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

## Upright bottle coolers

FKDv 42

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White powder-coated exterior	• Signal grey or black powder-coated exterior	•	•	•	•
		• Powder-coated exterior in a non-standard colour	•	•	•	•
		• Side wall vinyls (left-right)	•	•	•	•
Inner liner	White inner liner	• Silver inner liner; signal grey powder-coated rear-wall evaporator and fan housing	•	•	•	•
Door	Standard glass door	• Glass door vinyls	•	•	•	•
		• Glass door frame painted in a non-standard colour	•	•	•	•
	White plastic frame	• Glass door frame extruded in a non-standard colour	•	•	•	•
		• Black plastic handle	•	•	•	•
	White plastic handle	• Anodised aluminium handle	•	•	•	•
		• Powder-coated aluminium handle in a non-standard colour	•	•	•	•
		• White, grey or black recessed plastic handle	•	•	•	•
	White door gasket	• Grey or black door gasket	•	•	•	•
White powder-coated solid door	• Signal grey or black powder-coated solid door	•	•	•	•	
	• Powder-coated solid door in a non-standard colour	•	•	•	•	
	• Solid door with vinyls	•	•	•	•	
Display and display frame	Display with Liebherr logo	• Customised printed display	•	•	•	•
	White display frame	• Grey or black display frame	•	•	•	•
			• Display frame in non-standard colour	•	•	•
Accessories and special features		• Plastic-coated grid shelf	•	•	•	•
		• Metallic grid shelf	•	•	•	•
		• Dimmable LED lighting	•	•	•	•
		• Display protection guard without castors	•	•	•	•
		• Labels for scanner rails	•	•	•	•
		• EMS controller	•	•	•	•
		• Metallic, pull-out gravity feed shelf with base	•	•	•	•
		• Metallic, fixed gravity feed shelf with base	•	•	•	•
		• Cable with appliance coupler (plug and play)	•	•	•	•
		• Climate class 5	•	•	•	•
		• Perforated metal shelf cover	•	•	•	•
		• Castors for protection guard	•	•	•	•
		• Rear wall cover with vinyl as on side wall (climate class 5)	•	•	•	•
		• Rear wall cover (incl. unit compartment cover) in housing colour, powder coated (climate class 5)	•	•	•	•
		• Flexible scanner rails	•	•	•	•
		• Custom lock barrels	•	•	•	•
	• Self-closing door	•	•	•	•	
	• Additional LED side lighting	•	•	•	•	

# Upright bottle coolers



FKDv 4503  
FKDv 4513

## Upright bottle coolers

FKDv 4503, FKDv 4513

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	Signal grey powder-coated exterior	· White or black powder-coated exterior	•	•	•	•
		· Powder-coated exterior in a non-standard colour	•	•	•	•
		· Side wall vinyls (left-right)	•	•	•	•
Inner container	White inner container	· Silver inner container; signal grey powder-coated rear wall evaporator and fan housing	•	•	•	•
Door	Standard glass door	· Glass door vinyls	•	•	•	•
	Anodised aluminium profiles	· Powder-coated aluminium profiles in a non-standard colour	•	•	•	•
	Signal-grey door end pieces	· Painted door end piece in a non-standard colour	•	•	•	•
	Anodised aluminium handle	· Powder-coated aluminium handle in a non-standard colour · White, grey or black plastic recessed handle	•	•	•	•
	Grey door gasket	· White or black seal	•	•	•	•
Display and display frame	Interior door sticker with Liebherr logo	· Interior door sticker with customised printed display	•	•	•	•
	Grey LightGuide frame	· White or black LightGuide frame · Painted LightGuide frame in a non-standard colour	•	•	•	•
Accessories and special features		· Plastic-coated grid shelf	•	•	•	•
		· Metallic grid shelf	•	•	•	•
		· Dimmable LED lighting	•	•	•	•
		· Labels for scanner rails	•	•	•	•
		· EMS controller	•	•	•	•
		· Metallic, pull-out gravity feed shelf with base	•	•	•	•
		· Metallic, fixed gravity feed shelf with base	•	•	•	•
		· Cable with appliance coupler (plug and play)	•	•	•	•
		· Climate class 5	•	•	•	•
		· Perforated metal shelf cover	•	•	•	•
		· Castors for protection guard	•	•	•	•
		· Rear wall cover with vinyl as on side wall (climate class 5)	•	•	•	•
		· Rear wall cover (incl. motor compartment cover) in housing colour, powder coated (climate class 5)	•	•	•	•
		· Flexible scanner rails	•	•	•	•
		· Lock (FKDv 4513)	•	•	•	•
		· Protection guard without castors	•	•	•	•
	· Additional LED side lighting	•	•	•	•	

### ADDITIONAL INFORMATION:

- Maximum of five gravity feed shelves per appliance
- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Upright bottle coolers



FKDv 4523

## Upright bottle coolers

### FKDv 4523

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	Black powder-coated exterior	· White or signal grey powder-coated exterior	•	•	•	•
		· Powder-coated exterior in a non-standard colour	•	•	•	•
		· Side wall vinyls (left-right)	•	•	•	•
Inner liner	Silver inner liner	· White inner liner; signal grey powder-coated rear wall evaporator and fan housing	•	•	•	•
Door	Neutral glass door, backprinted black	· Glass door backprinted in a non-standard colour	•	•	•	•
		· Glass door backprinted with image (multi-coloured)	•	•	•	•
		· Glass door contour-printed in a non-standard colour	•	•	•	•
		· Glass door vinyls	•	•	•	•
	Anodised aluminium profiles	· Powder-coated aluminium profiles in a non-standard colour	•	•	•	•
	Anodised aluminium handle	· Powder-coated aluminium handle in a non-standard colour	•	•	•	•
· White, grey or black recessed plastic handle		•	•	•	•	
Black door gasket	· White or grey door gasket	•	•	•	•	
Display	Interior LightGuide display with Liebherr logo, blue LED	· Interior LightGuide with customer logo, contoured or printed		•	•	•
		· Red or white LED	•	•	•	•
		· Without LightGuide	•	•	•	•
Accessories and special features		· Plastic-coated grid shelf	•	•	•	•
		· Metallic grid shelf	•	•	•	•
		· Labels for scanner rails	•	•	•	•
		· Metallic, pull-out gravity feed shelf with base	•	•	•	•
		· Metallic, fixed gravity feed shelf with base	•	•	•	•
		· Cable with appliance coupler (plug and play)	•	•	•	•
		· Climate class 5	•	•	•	•
		· Perforated metal shelf cover	•	•	•	•
		· Castors for protection guard	•	•	•	•
		· Rear wall cover with vinyl as on side wall (climate class 5)	•	•	•	•
		· Rear wall cover (incl. motor compartment cover) in housing colour, powder coated (climate class 5)	•	•	•	•
		· Flexible scanner rails	•	•	•	•
		· Protection guard without castors	•	•	•	•

#### ADDITIONAL INFORMATION:

- Maximum of five gravity feed shelves per appliance
- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Upright bottle coolers



BCDv 10

## Upright bottle coolers

### BCDv 10

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White-aluminium powder-coated exterior	· Powder-coated exterior in a non-standard colour	•	•	•	•
		· White-aluminium or white powder-coated exterior	•	•	•	•
		· Full vinyl exterior branding	•	•	•	•
Door	Standard glass door	· Glass door with transparent, full-surface vinyl	•	•	•	•
Glass door frame	Anodised, colourless frame	· Powder-coated frame in a non-standard colour	•	•	•	•
	Grey recessed handle	· Grey or black recessed handle	•	•	•	•
Display and display frame	Display with Liebherr logo	· Printed display	•	•	•	•
	Grey plastic frame	· Plastic frame in a non-standard colour	•	•	•	•
			· Grey or white plastic frame	•	•	•
Accessories and special features		· Labels for scanner rails	•	•	•	•
		· Scanner rails	•	•	•	•

#### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Upright bottle coolers



FKv 50  
FKv 30

## Upright bottle coolers

FKv 50, FKv 30

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	Stainless steel exterior	· Powder-coated exterior in non-standard colour (incl. glass door frame)	•	•	•	•
		· Full vinyl exterior branding	•	•	•	•
		· Exterior with monochrome vinyls, contour-cut	•	•	•	•
		· Four-colour exterior vinyls, contour-cut	•	•	•	•
Door	Standard glass door	· Four-colour vinyls to glass door, contour-cut	•	•	•	•
		· Glass door with monochrome vinyls, contour-cut	•	•	•	•
		· Glass door with LED lighting	•	•	•	•
		· Silk-screen printed logo on glass door		•	•	•

### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Upright bottle coolers



FKv(s) 26  
FKv(s) 36  
FKv(s) 41  
FKv(s) 54

## Upright bottle coolers

### FKv(s) 26-54

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White (silver) powder-coated exterior and glass door frame	· Exterior and glass door frame in a non-standard colour, powder-coated	•	•	•	•
		· Dye-sublimated exterior	•	•	•	•
		· Side-wall vinyls	•	•	•	•
Door	Glass door/solid door	· Glass door with transparent, full-surface vinyl	•	•	•	•
		· Four-colour vinyls to glass door, contour-cut	•	•	•	•
		· Glass door with monochrome vinyls, contour-cut	•	•	•	•
		· Dye-sublimated solid door	•	•	•	•
Accessories and special features		· Plastic-coated grid shelf	•	•	•	•
		· Powder-coated display attachment in non-standard colour, printed (FKv(s) 26-41)	•	•	•	•
		· Neutral, signal grey display attachment (FKv(s) 26-41)	•	•	•	•
		· Labels for scanner rails (FKv(s) 26-41)	•	•	•	•
		· Metallic, pull-out gravity feed shelf with base (FKv(s) 26-41)	•	•	•	•
		· Castors for protection guard (FKv(s) 36-54)	•	•	•	•
		· Castor base (FKv(s) 54../36../26..)	•	•	•	•
		· Flexible scanner rails (FKv(s) 26-41)	•	•	•	•
		· Protection guard (FKv(s) 36-54)	•	•	•	•
		· Custom lock barrels (FKv ..43)	•	•	•	•
	· Height-adjustable feet (FKv(s) 54../36../26..)	•	•	•	•	

#### ADDITIONAL INFORMATION:

- The display attachment is not factory fitted
- Handle and appliance top only available in black, white or grey
- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Chest-type bottle coolers



## Chest-type bottle coolers

FT 33

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White coated exterior	- Side wall vinyls on three sides	•	•	•	•
		- Side wall vinyls on four sides	•	•	•	•
Plastic components	Grey plastic components	- "Process blue", blue or red plastic components	•	•	•	•
	Side unit cover Handle left and right Cover profile left and right	- Plastic components in a non-standard colour on request	•	•	•	•
Accessories and special features		- Attachment options on request	•	•	•	•
		- Basket 210 mm	•	•	•	•
		- Basket 250 mm	•	•	•	•
		- Castors with brake (50 mm)	•	•	•	•
		- Castors with brake (75 mm)	•	•	•	•
		- Key lock for foamed lid	•	•	•	•
		- Key lock for sliding glass lid	•	•	•	•

FT 33

### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Ice cream chest freezers



GTE 17  
GTE 33  
GTE 41  
GTE 49  
GTE 58

## Ice cream chest freezers

### GTE 17-58

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White coated exterior	· Side wall vinyls on three sides	•	•	•	•
		· Side wall vinyls on four sides	•	•	•	•
Plastic components	Grey plastic components	· "Process blue", blue or red plastic components	•	•	•	•
	Side unit cover Handle left and right Cover profile left and right	· Plastic components in a non-standard colour on request	•	•	•	•
Accessories and special features		· Attachment options on request	•	•	•	•
		· Wire basket for scoop ice cream containers	•	•	•	•
		· Basket 210 mm	•	•	•	•
		· Basket 250 mm	•	•	•	•
		· Castors with brake (50 mm)	•	•	•	•
		· Castors with brake (75 mm)	•	•	•	•
		· Key lock for foamed lid	•	•	•	•
		· Key lock for sliding glass lid	•	•	•	•
		· Partition grid 210 mm	•	•	•	•
	· Partition grid 250 mm	•	•	•	•	

#### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Ice cream chest freezers



GTI 17  
GTI 33  
GTI 41  
GTI 49  
GTI 58

## Ice cream chest freezers

GTI 17-58

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White coated exterior	- Side wall vinyls on three sides	•	•	•	•
		- Side wall vinyls on four sides	•	•	•	•
Plastic components	Grey plastic components	- "Process blue", blue or red plastic components	•	•	•	•
	Side unit cover Handle left and right Cover profile left and right	- Plastic components in a non-standard colour on request	•	•	•	•
Accessories and special features		- Attachment options on request	•	•	•	•
		- Castors with brake (50 mm)	•	•	•	•
		- Castors with brake (75 mm)	•	•	•	•
		- Key lock for sliding glass lid	•	•	•	•
		- Partition grid 210 mm	•	•	•	•
		- Partition grid 250 mm	•	•	•	•

### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Glass door display freezers



FDv 46

## Glass door display freezers

### FDv 46

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White powder-coated exterior	· Powder-coated exterior in black	•	•	•	•
		· Powder-coated exterior in a non-standard colour on request	•	•	•	•
		· Side wall vinyls (left-right)	•	•	•	•
	Anthracite unit compartment cover	· Unit compartment cover in a non-standard colour on request	•	•	•	•
	Castors (FDv 4643)	· Height-adjustable feet	•	•	•	•
	Height-adjustable feet (FDv 4613)	· Castors	•	•	•	•
Door	Standard glass door	· Glass door vinyls (FDv 4613)	•	•	•	•
	Silver aluminium profiles	· Aluminium profiles powder-coated in black	•	•	•	•
	Silver handle	· Handle in a non-standard colour on request	•	•	•	•
· Handle in black		•	•	•	•	
Display and display frame	Display with Liebherr logo	· Display sticker	•	•	•	•
		· Display frame in a non-standard colour on request	•	•	•	•
		· Display frame in a black	•	•	•	•
Accessories and special features		· Plastic-coated grid shelf	•	•	•	•
		· Climate class 7 (FDv 4613)	•	•	•	•
		· 30-litre basket	•	•	•	•
		· 42-litre basket	•	•	•	•
		· Scanner rails	•	•	•	•
		· Partition grid for 30-litre basket	•	•	•	•
		· Partition grid for 42-litre basket	•	•	•	•

#### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request

# Glass door display freezers



Fv 36

## Glass door display freezers

### Fv 36

	Basic appliance	Customised appliance	Purchase quantity per order			
			50 or more	100 or more	200 or more	500 or more
Exterior finish	White powder-coated exterior finish	· Powder-coated exterior in black	•	•	•	•
		· Powder-coated exterior in a non-standard colour on request	•	•	•	•
		· Side wall vinyls (left-right)	•	•	•	•
	Anthracite unit compartment cover	· Unit compartment cover in a non-standard colour on request	•	•	•	•
	Castors (Fv 3643)	· Height-adjustable feet	•	•	•	•
	Height-adjustable feet (Fv 3613)	· Castors	•	•	•	•
Door	Unbranded glass door	· Glass door with vinyls (Fv 3613)	•	•	•	•
	Silver aluminium profiles	· Aluminium profiles powder-coated in black	•	•	•	•
	Silver handle	· Handle in a non-standard colour, on request	•	•	•	•
· Handle in black		•	•	•	•	
Accessories and special features		· Plastic-coated grid shelf	•	•	•	•
		· Climate class 7 (Fv 3613)	•	•	•	•
		· 30-litre basket	•	•	•	•
		· 42-litre basket	•	•	•	•
		· Scanner rails	•	•	•	•
		· Partition grid for 30-litre basket	•	•	•	•
	· Partition grid for 42-litre basket	•	•	•	•	

#### ADDITIONAL INFORMATION:

- Some non-standard colours are already approved and available in quantities of 50 or more. Other colours are available on request