



BioFresh
Special 2017

LIEBHERR

Quality, Design and Innovation



Contents

BioFresh	4
Side-by-Side fridge-freezers	12
Frenchdoor fridge-freezers	22
Fridge-freezers	24
Fridges	40
Full BioFresh fridge	48
Integrated Side-by-Side fridge-freezers	50
Integrated fridge-freezers and fridges	56



BioFresh – the technology for really long-lasting freshness

Vegetables stay crisp, the vitamins in fruit are preserved, and fish keeps its freshly caught taste for longer: with BioFresh, Liebherr has created additional climate zones within the fridge so that food can be optimally stored at temperatures just over 0°C and at a tailored humidity level. BioFresh keeps food fresher for much longer than a normal fridge compartment, and it also ensures that valuable nutrients are preserved. Not only does BioFresh technology offer you amazingly long-lasting freshness, it's also extremely energy efficient as it utilises highly efficient compressors and is operated by precision electronic controls.




A comprehensive list of foods with precise details of their shelf life and their vitamin and mineral content can be found in the BioFresh App or at biofresh.liebherr.com.

Proof of lasting freshness: food stays healthier with BioFresh

Two renowned research institutions* – the Lake Constance Centre of Expertise for Fruit Growing (Kompetenzzentrum Obstbau-Bodensee) and the German Federal Research Institute for Nutrition (Bundesforschungsanstalt für Ernährung) – concluded that BioFresh technology vastly improves food quality: both independently determined that vitamin C content can be as much as 92% higher with BioFresh storage compared to normal vegetable compartment storage. Some foods even showed an increase in the vitamin C content. Weight retention during storage was increased by 68.3% on average and wastage in preparation was also significantly reduced.

	Apples	Asparagus	Peppers	Broccoli	Carrots	Grapes	Lettuce	Average
Vitamin C (after 15 days)								
HydroSafe	100.3%	78.2%	161.6%	88.3%	82.9%	134.4%	26.6%	104.4%
Vegetable drawer	92.9%	65%	154.2%	21.5%	32.4%	116.7%	21.9%	72.8%
Difference	8%	20%	5%	310%	156%	15%	21%	92%
Weight (after 15 days)								
HydroSafe	-0.6%	-4.8%	-1.7%	-3.8%	-9%	-0.6%	-3.1%	-3.1%
Vegetable drawer	-1.1%	-4.5%	-2.8%	-5.6%	-12.8%	-1.7%	-5.9%	-4.6%
Difference	105%	6%	63%	49%	43%	170%	91%	68.3%
Storage life (in days)								
HydroSafe	80	18	30	13	80	29	13	
Vegetable drawer	50	10	17	5	50	12	5	
Difference	30	8	13	8	30	17	8	

*Sources: Lake Constance Research Centre for Fruit Growing (KOB): »Influence of different climate zones in refrigerators on the quality of fruit and vegetables«; German Federal Research Institute for Nutrition (BFE): »Investigation into retaining the quality of fresh fruit and vegetables«, 2003.



Bio Fresh

Low humidity and a temperature just above freezing point are the ideal storage conditions for **meat, fish and dairy products**. BioFresh with the DrySafe setting provides just this type of climate and keeps it constant at all times.



Bio Fresh

Fruit and vegetables are best kept in the HydroSafe with high humidity. A precision electronic control system ensures that the temperature is maintained at just above 0 °C, preventing damaging frostbite.



Bio Fresh Plus

The ideal storage temperature for **fish and seafood** is at freezing point. The BioFresh drawers enable fish to be kept fresher for longer at this temperature. For true fish enthusiasts, the BioFresh-Plus technology provides greater flexibility and control for ideal food storage conditions. With its independent electronic control system the temperature in the top compartment can be adjusted to -2 °C, this together with the DrySafe setting makes the ideal environment for keeping fish and seafood fresher for longer.



Bio Fresh Plus

BioFresh-Plus allows temperature-sensitive **tropical fruits** to be kept fresh for an exceptionally long period of time. They are stored in perfect conditions at +6 °C with high humidity in the upper, adjustable drawer.

Vitamins at their very tastiest

All foods have their own unique qualities (texture, taste etc.) and nutritional benefits; to preserve these, they need to be stored in the right environment, i.e. at just above 0°C in a BioFresh-Safe.

Vitamin	Function	Source	Storage life
Vitamin A	strengthens the immune system, promotes good vision, promotes children's growth and strengthens teeth	carrots, kale, fennel, spinach, lamb's lettuce, broccoli, apricots, melon	e.g. carrots Vegetable bin: 50 days HydroSafe: 80 days
Vitamin B2	for clear and healthy skin, protects the nerve cells, is important for vision, boosts energy supply to cells	yellow peppers, kale, broccoli, avocados, mushrooms, porcini mushrooms	e.g. mushrooms Vegetable bin: 3 days HydroSafe: 7 days
Vitamin B5	promotes the growth of hair and hair pigmentation, helps to restore equanimity, wards off infection	strawberries, blackcurrants, apricots, cauliflower, broccoli	e.g. strawberries Vegetable bin: 3 days HydroSafe: 7 days
Vitamin B6	activates the immune system, supports nerve function, increases stamina, keeps muscles and connective tissue elastic and helps reduce stress	beans, spinach, potatoes, broccoli	e.g. broccoli Vegetable bin: 5 days HydroSafe: 13 days
Vitamin C	strengthens the body's defences, increases the production of collagen so maintains healthy skin, assists cell regeneration and promotes a sense of general well-being	peas, kohlrabi, artichokes, asparagus, peppers, onions, cabbage, raspberries	e.g. raspberries Vegetable bin: 1 day HydroSafe: 3 days
Vitamin E	is regarded as an anti-aging vitamin, counteracts aging processes, strengthens the immune system, hinders the formation of deposits in blood vessels	fennel, peppers, brussel sprouts, tomatoes, white beans, asparagus, lettuce	e.g. lettuce Vegetable bin: 5 days HydroSafe: 13 days
Vitamin K	promotes vitality, supports healthy bone structure, assists the optimal utilisation of carbohydrates	chicory, carrots, brussel sprouts, lettuce, cauliflower, peas, broccoli	e.g. peas Vegetable bin: 7 days HydroSafe: 14 days



Freshness: an overview

	Main constituents		Storage life (days)		
Vegetables / HydroSafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Artichoke	iron, fluoride	A, B1, B2, C	7	14	14 (0 °C)
Asparagus	copper, magnesium	B1, C, K	10	18	18 (0 °C)
Bean sprouts	sodium, potassium, phosphorus	B1, B2, B3, B5, B6, C, E	2	7	7 (0 °C)
Beans	magnesium, manganese	A, B2, folic acid	6	11	11 (0 °C)
Beetroot	iron, manganese	Prov. A, folic acid	6	18	18 (0 °C)
Broccoli	iron, iodine	C, folic acid, K	5	13	13 (0 °C)
Carrot	potassium, calcium	A, C, D, E	50	80	80 (0 °C)
Cauliflower	potassium, magnesium	C, E, folic acid, K	12	21	21 (0 °C)
Chard	magnesium, manganese	A, B1, B2, C	6	10	10 (0 °C)
Chicory	potassium, manganese	B1, B2	18	27	27 (0 °C)
Fennel	magnesium, manganese	Prov. A, B1	13	28	28 (0 °C)
Garlic	potassium, manganese	B6, C, ajoen	80	160	160 (0 °C)
Herbs	potassium, calcium	A, B1, B2, B3, B5, C, E	6	13	13 (0 °C)
Lamb's lettuce	iron, fluoride	A, C, E, folic acid	7	19	19 (0 °C)
Leek	calcium, magnesium	B1, E, folic acid	15	29	29 (0 °C)
Lettuce	iron, potassium, manganese	A, E, folic acid	5	13	13 (0 °C)
Mushrooms	iodine, potassium, copper	B1, B2, D, K	3	7	7 (0 °C)
Onion	potassium, zinc	A, B1, B2, C, E	15	28	28 (0 °C)
Pepper	iron, potassium	B6, C, E, K	17	30	30 (0 °C)
Radish	potassium, manganese	Prov. A, C	18	27	27 (0 °C)
Spinach	iodine, magnesium	A, E, folic acid, K	5	13	13 (0 °C)
Sweet corn	potassium, phosphorus, magnesium	A, B1, B2, B3, B5, B6, B7	2	5	5 (0 °C)
Tomatoes	magnesium, zinc	A, B1, C, E	9	20	20 (0 °C)
Fruit / HydroSafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Apple	iron, potassium	A, B1, biotin	50	80	80 (0 °C)
Blackberries	iron, potassium, calcium	C, folic acid	1	3	3 (0 °C)
Blueberries	manganese, zinc	B1, B2, B6, C, E	4	9	9 (0 °C)
Cherries (sweet)	iron, potassium	B1, B2, B6, C	7	14	14 (0 °C)
Currants	iron, zinc	B1, B2, B6, C, E	3	7	7 (0 °C)
Grapes	iron, potassium	C, E, folic acid	12	29	29 (0 °C)
Honeydew melon	potassium, sodium, zinc	A, C, folic acid	17	•	19 (+6 °C)
Kiwi	calcium, magnesium	A, C, K	40	80	80 (0 °C)
Lime	potassium, calcium, magnesium	A, C, E, folic acid	50	•	55 (+6 °C)
Pear	calcium, magnesium	B1, B2, B6, E	26	55	55 (0 °C)
Pineapple	iron, manganese	B1, B2, B6, C	23	•	27 (+6 °C)
Raspberries	calcium, magnesium	A, B6, C, folic acid	1	3	3 (0 °C)
Strawberries	manganese, zinc	C, K, folic acid	3	7	7 (0 °C)

	Main constituents		Storage life (days)		
Cheese / DrySafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Alpine cheese	iodine, phosphorus, zinc	A, B2, D	10	110	110 (0 °C)
Emmental	copper, sodium	A, B2, B12, D	10	110	110 (0 °C)
Gorgonzola	chloride, sodium, potassium	B1, B2, B6, beta-carotene	7	70	70 (0 °C)
Parmesan	iron, iodine, calcium	A, B2, B12, D	10	110	110 (0 °C)
Dairy products / DrySafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Butter	phosphorus, zinc	A, D, E, K	30	90	90 (0 °C)
Cream	phosphorus, zinc	A, D, E	4	7	7 (0 °C)
Egg, raw	iron, selen, calcium	B12, biotin, D, K	15	45	45 (0 °C)
Milk	potassium, calcium	A, B2, D, K	3	12	12 (0 °C)
Yoghurt	phosphorus, zinc	A, B2, K	3	12	12 (0 °C)
Fish / DrySafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Cod	iron, fluoride	A, B12, D, E	1	2	4 (-2 °C)
Sea bream	potassium, magnesium	B2, D, E	1	2	4 (-2 °C)
Oysters	iron, fluoride	A, B2, B12, D	1	3	6 (-2 °C)
Pollock	iron, potassium, zinc	A, B2, B12, D	1	2	4 (-2 °C)
Trout	copper, phosphorus, zinc	A, B2, B12, D, E	1	2	4 (-2 °C)
Zander	fluorine, iodine, zinc	A, B2, D, E	1	2	4 (-2 °C)
Meat / DrySafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Beef	potassium, phosphorus, zinc	B6, B12, niacin	1	7	7 (0 °C)
Minced meat	potassium, sulfur, phosphorus	B2, B3, B5, B6, E	•	2	2 (0 °C)
Pork	iron, zinc	B1, B12, niacin	1	7	7 (0 °C)
Poultry	sulphur, potassium, phosphorus	A, B3, B5, B6, E	1	6	6 (0 °C)
Veal	pan. acid, potassium, phosphorus	B1, B2, B6, E-active	1	7	7 (0 °C)
Sausage / DrySafe	Minerals	Vitamins	Fridge	BioFresh	BioFresh-Plus
Bratwurst	phosphorus, calcium, magnesium	A, B1, B2, B6, C, E	1	9	9 (0 °C)
Ham	phosphorus, zinc	B1, B2, B6, B12	1	9	9 (0 °C)
Liver sausage	sodium, chlorine, potassium	A, B3, C, E	1	9	9 (0 °C)
Mortadella	chlorine, sodium, potassium	A, B1, B2, B3, B5, B6, C, E	1	9	9 (0 °C)
Salami	sodium, chlorine, potassium	B1, B2, B3, B5, B6, E	80	180	180 (0 °C)

All values are standard and vary on an individual basis depending on the variety and proper storage with an uninterrupted cooling chain from harvesting/producer to the Liebherr BioFresh refrigerator! For all foodstuffs with an expiry date, the date on the package applies. The foods marked by • are not suitable for storage in the refrigerator or BioFresh compartment as marked.

Sources: Vitamins & Mineral Nutrients, aid – Käsesteckbrief – 56 Sorten Käse in Wort und Bild (Cheese Characteristics – 56 Cheese Types, Text and Images), aid – Steckbrief – Fische, Krebs- und Weichtiere (Fish, Crustacean and Mollusc Characteristics), Dipl. oec. Troph. Petra Hopfenitz "Mineralstoffe" (Mineral Nutrients), GU, Dipl. oec. Troph. Ulla Unger-Göbel "Vitamine" (Vitamins), GU

Impressive food storage centres with BioFresh



Quality in every detail



Wine

In the **multi-temperature wine compartment**, wines can be stored in two individually controllable climate areas at a precisely regulated temperature between +5 °C and +20 °C. The wooden shelves extend on telescopic rails and are partially foldable.




Bio Fresh Plus

The **BioFresh-Plus** technology provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the top drawer to be lowered to -2 °C for storing fish. Together with the DrySafe setting, fish is kept fresh even longer. Exotic fruits find ideal storage conditions in the top adjustable safe at +6 °C and a high level of humidity.



SBSes 7165 PremiumPlus



Energy efficiency class: A++
Energy consumption year / 24 hrs: 431 / 1.178 kWh
Max. Bordeaux bottles 0.75 l: 41
Total net capacity: 591 litre (Fridge: 476 litre including BioFresh compartment: 110 litre including wine compartment: 126 litre / Freezer compartment: 115 litre)
Noise output: 42 dB(A)
Climate rating: SN-ST
Door / side walls: Stainless steel with SmartSteel / stainless steel
Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63



Ice Maker

No Frost

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The **NoFrost** technology keeps the freezer constantly frostfree.



LED

LED light columns on either side beautifully illuminate the interior. The **GlassLine** fittings in the generously sized fridge can be adjustably positioned and therefore configured in line with your requirements. The satin-finish shelves are made of safety glass and the door racks are height adjustable.

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh, wine and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- BioFresh-Plus
- 3 BioFresh-Safes on telescopic rails, of which 3 can be set variably to HydroSafe or DrySafe

Freezer compartment ********

- 5 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Wine compartment

- 2 separately controllable temperature zones, which can be regulated between +5 °C to +20 °C
- Tinted insulated glass door with UV protection
- Convection cooling fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 4 Shelves, of which 2 set on telescopic rails and 2 foldable

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front and back, transport castors at back
- Door hinge left fixed/right fixed

Quality in every detail



Black Steel

BlackSteel is a visually stunning and highly attractive black stainless steel. The addition of a scratch-resistant **SmartSteel finish** on the doors and side walls significantly reduces the visibility of finger marks and ensures easy cleaning.



Bio Fresh

The **BioFresh-Safe** drawers extend on telescopic rails and are effortless to open. **LED lighting** ensures that these drawers are perfectly illuminated. Depending on requirements, the **versatile bottle shelf** can be positioned above the glass shelf to store bottles or beneath it so that dishes or bowls can be accommodated.



Ice Maker


No Frost

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The **NoFrost** technology keeps the freezer constantly frostfree.



The practical **VarioSafe** makes it easy to view and organise all sorts of items. It is the ideal space for smaller food packets, tubes and jars. An additional insertion height is available for filling to a greater capacity if necessary.

SBSbs 8673
Premium



Energy efficiency class: $\langle A^{+++}/A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 255 / 0.696 kWh¹
 Total net capacity: 629 litre (Fridge: 367 litre including BioFresh compartment: 133 litre / Freezer compartment: 262 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185 / 121 / 66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Freezer compartment ****

- 9 drawers, of which 6 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 0.8 kg
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



Bio Fresh

The **BioFresh-Safe** drawers extend on telescopic rails and are effortless to open. **LED lighting** provides perfect illumination for the drawers. Depending on requirements, the **versatile bottle shelf** can be positioned above the glass shelf to store bottles or beneath it so that dishes or bowls can be accommodated.



The premium-quality **GlassLine** interior door shelves are made from safety glass and can easily hold 1.5-litre bottles. The removable **VarioBoxes** and the storage shelves can be flexibly positioned at different heights.



SBSes 8663
Premium



Energy efficiency class: $\langle A^{+++}/A^{+++} \rangle^1$

Energy consumption year / 24 hrs: 258 / 0.702 kWh ¹

Total net capacity: 635 litre (Fridge: 367 litre including BioFresh compartment: 133 litre / Freezer compartment: 268 litre)

Noise output: 38 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185 / 121 / 66.5 ¹



No Frost

Powerful, long-life **LEDs** provide pristine illumination for the open freezer drawers. The drawers extend on smooth-running **roller tracks** and can be completely removed with ease using the highly convenient integrated carrying handles. **NoFrost** technology keeps the freezer frost-free at all times.



Power Cooling

The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours. A reminder function in the control panel indicates when a filter change is required.

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Freezer compartment *******

- 8 drawers, of which 7 set on roller tracks, VarioSpace
- LED lighting
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



Bio Fresh

The **BioFresh-Safe drawers** extend on telescopic rails and are effortless to open. **LED lighting** provides perfect illumination for the drawers. Depending on requirements, the **versatile bottle shelf** can be positioned above the glass shelf to store bottles or beneath it so that dishes or bowls can be accommodated.




Black Steel

BlackSteel is a visually stunning and highly attractive black stainless steel. The addition of a scratch-resistant **SmartSteel finish** on the doors and side walls significantly reduces the visibility of finger marks and ensures easy cleaning.



121

SBSbs 7353
Premium



Energy efficiency class: **A++**¹
 Energy consumption year/24 hrs: 383/1.048 kWh¹
 Total net capacity: 654 litre (Fridge: 539 litre including BioFresh compartment: 155 litre/Freezer compartment: 115 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185.2/121/63¹



Ice Maker

No Frost

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The **NoFrost** technology keeps the freezer constantly frostfree.



Power Cooling

The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours. A reminder function in the control panel indicates when a filter change is required.

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- 2 GlassLine shelves in the BioFresh compartment
- Bottle shelf, Champagne rack
- LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe
- 2 fruit and vegetable drawers on telescopic rails

Freezer compartment ********

- 5 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front and back, transport castors at back
- Door hinge left fixed/right fixed

Colour/material options:

SBSes 7353 in Stainless steel

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



The elegant **MagicEye control system** with the innovative, user-friendly **Touch-electronic** feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



Bio Fresh

Both **BioFresh drawers** are mounted on **telescopic rails** which extend effortlessly providing a full view of your food, which is easily accessible. The lateral **LED lights** ensure perfect illumination of the drawers. The versatile glass/bottle shelves can be used depending on your personal preference.



CBNes 6256
PremiumPlus

Bio Fresh **No Frost** **A++** **Duo Cooling** **Ice Maker**

Energy efficiency class: $\lt; A^{+}$
 Energy consumption year / 24 hrs: 322 / 0.881 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel / stainless steel
 Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5

CBNbe 6256
PremiumPlus

Bio Fresh **No Frost** **A++** **Duo Cooling** **Ice Maker**

Energy efficiency class: $\lt; A^{+}$
 Energy consumption year / 24 hrs: 322 / 0.881 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Tür / Seitenwände: beige / beige
 Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5



No Frost

Ice Maker

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated **water filter** ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The **NoFrost** technology keeps the freezer constantly frost-free.



LED

The interior is beautifully illuminated by premium quality **LED light columns** on either side and a flush-installed **LED ceiling light**. Within the generously sized interior, the **GlassLine** fittings can be flexibly configured in line with your requirements. The height adjustable satin-finished shelves and door shelves are made from extra-strong safety glass and feature solid aluminium trims.

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.3 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 45 h
- Freezing capacity in 24 hrs: 11 kg

Key features

- HardLine
- Aluminium handles
- Front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Concealed hinge with restricted opening

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.3 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 45 h
- Freezing capacity in 24 hrs: 11 kg

Key features

- HardLine
- Aluminium handles
- Front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Concealed hinge with restricted opening

Fridge-freezers



CBNes 5758



Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, longterm storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



For more about NoFrost, please visit: nofrost.liebherr.com



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean.



Bio Fresh

BioFresh provides the perfect storage climate for long-lasting food storage freshness. When stored at just over 0 °C and at the ideal humidity level, fruit, vegetables, meat and fish all retain their nutritious vitamins for longer.



For more about BioFresh, please visit: biofresh.liebherr.com



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of toughened glass. The satin-finished glass shelves with premium-quality stainless steel trim are scratch-resistant and easy to clean. The sectioned, slide-under glass shelf can be located to suite individual requirements.



Ready to serve food can be stored in the fridge in the two removable **VarioBoxes**. Their lids are detachable and so these stylish VarioBoxes can be taken from the fridge straight to the dining table. The VarioBoxes can be securely positioned at different heights within the door interior.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored.

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail




The sturdy **handle with** its refined, premium-quality appearance and **an integrated opening mechanism** ensures easy and effortless opening of the door.



Duo Cooling

Accurate and independent temperature control of the fridge and freezer compartments is facilitated by **DuoCooling**: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug 2. Functional wall spacer to maintain wall clearance and allow connection 3. Variable speed compressor 4. Plinth fan with noise-damping 5. Condenser 6. Defrost water drain



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system. Appliances can be adapted to specific customer requirements using preset programmes, thereby ensuring optimal food storage.

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail



Soft Telescopic

The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



Power Cooling

The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours. A reminder function in the control panel indicates when a filter change is required.



LED

The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a homogeneous, high-quality lighting concept.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables accurate temperature settings.



The **versatile bottle shelf** is an innovative and practical feature. It can be positioned above the glass shelf to store bottles or beneath it so that dishes or bowls can be accommodated.



Super Cool

Super Frost

SuperCool and/or **SuperFrost** quickly generate greater cooling reserves to rapidly chill or freeze freshly stored food so that vitamins are optimally preserved. Reversion from the quick-chill and quick-freeze temperatures (+2 °C in the fridge and -32 °C in the freezer) to the normal operating temperatures is time or quantity-controlled, which helps to save energy.

The features shown are model dependent; the description applies to the relevant model.



The **BioFresh-Plus** technology provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the top drawer to be lowered to -2 °C for storing fish. Together with the **DrySafe** setting, fish is kept fresh even longer. Exotic fruits find ideal storage conditions in the top adjustable safe at +6 °C and a high level of humidity.



The PremiumPlus interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. At the same time the light columns provide freedom for rearranging the toughened glass shelves to suit your storage needs.



◀75▶

CBNPes 5167 PremiumPlus	Bio Fresh Plus	No Frost	A++	Duo Cooling	Ice Maker	Soft System	Smart Steel
Energy efficiency class: $\langle A^{++} \rangle^1$							
Energy consumption year / 24 hrs: 304 / 0.832 kWh ¹							
Total net capacity: 411 litre (Fridge: 299 litre including BioFresh compartment: 99 litre / Freezer compartment: 112 litre)							
Noise output: 41 dB(A)							
Climate rating: SN-T							
Door / side walls: Stainless steel with SmartSteel / stainless steel							
Exterior dimensions in cm (h/w/d): 202/75/63 ¹							

Controls	Freezer compartment ★★★★★
<ul style="list-style-type: none"> Cursor controlled LCD display in-the-door, touch electronic Digital temperature display for fridge, BioFresh and freezer compartments Automatic SuperCool Automatic SuperFrost, quantity-controlled Warning signal in case of fault: visual and acoustic Door alarm: acoustic 	<ul style="list-style-type: none"> 4 drawers, VarioSpace IceMaker with fixed 3/4" water connection Ice cube production in 24 hrs: 1.0 kg Ice cube reservoir: 1.5 kg LED lighting Temperature rise time: 34 h Freezing capacity in 24 hrs: 14 kg 2 cold storage accumulators Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray 3 GlassLine storage shelves, of which one is divided into two parts Variable bottle shelf LED light column on both sides LED BioFresh lighting BioFresh-Plus 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe 	<ul style="list-style-type: none"> SwingLine design Stainless steel slimline handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles at back Height-adjustable feet at front, transport castors at back Reversible door hinging



◀75▶

CBNPes 5156 Premium	Bio Fresh	No Frost	A++	Duo Cooling	Smart Steel
Energy efficiency class: $\langle A^{++} \rangle^1$					
Energy consumption year / 24 hrs: 305 / 0.835 kWh ¹					
Total net capacity: 421 litre (Fridge: 306 litre including BioFresh compartment: 107 litre / Freezer compartment: 115 litre)					
Noise output: 40 dB(A)					
Climate rating: SN-T					
Door / side walls: Stainless steel with SmartSteel / stainless steel					
Exterior dimensions in cm (h/w/d): 202/75/63 ¹					

Controls	Freezer compartment ★★★★★
<ul style="list-style-type: none"> LCD display in-the-door, touch electronic Digital temperature display for fridge and freezer compartments Automatic SuperCool Automatic SuperFrost, quantity-controlled Warning signal in case of fault: visual and acoustic Door alarm: acoustic 	<ul style="list-style-type: none"> 3 drawers, VarioSpace Ice cube tray Temperature rise time: 30 h Freezing capacity in 24 hrs: 14 kg 2 cold storage accumulators Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray 3 GlassLine storage shelves, of which one is divided into two parts Variable bottle shelf LED ceiling lighting 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe 	<ul style="list-style-type: none"> SwingLine design Stainless steel slimline handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles at back Height-adjustable feet at front, transport castors at back Reversible door hinging



◀75▶

CBNesf 5133 Comfort	Bio Fresh	No Frost	A++	Duo Cooling	Smart Steel
Energy efficiency class: $\langle A^{++} \rangle^1$					
Energy consumption year / 24 hrs: 305 / 0.835 kWh ¹					
Total net capacity: 421 litre (Fridge: 306 litre including BioFresh compartment: 107 litre / Freezer compartment: 115 litre)					
Noise output: 41 dB(A)					
Climate rating: SN-T					
Door / side walls: Stainless steel with SmartSteel / silver					
Exterior dimensions in cm (h/w/d): 202/75/63 ¹					

Controls	Freezer compartment ★★★★★
<ul style="list-style-type: none"> MagicEye behind-the-door, key electronic LED temperature display for fridge and freezer compartments Automatic SuperFrost, time-controlled Warning signal in case of fault: visual and acoustic Door alarm: acoustic 	<ul style="list-style-type: none"> 3 drawers, VarioSpace Ice cube tray Temperature rise time: 30 h Freezing capacity in 24 hrs: 14 kg Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling Comfort GlassLine storage shelf with bottle holder, egg tray 3 GlassLine storage shelves, of which one is divided into two parts LED ceiling lighting 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe 	<ul style="list-style-type: none"> SwingLine design Stainless steel slimline handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles at back Height-adjustable feet at front, transport castors at back Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0 °C.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system. Appliances can be adapted to specific customer requirements using preset programmes, thereby ensuring optimal food storage.



The **LED ceiling light** creates a high-class ambience within the refrigerator. Its beautifully designed, space-efficient housing is centrally positioned to provide a delightfully even illumination.



The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



CBNPes 5758
Premium

Bio Fresh No Frost A+++ -20% Duo Cooling Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\lt; A^{+++}$ ¹
 Energy consumption year / 24 hrs: 157 / 0.430 kWh ¹
 Total net capacity: 381 litre (Fridge: 275 litre including BioFresh compartment: 108 litre / Freezer compartment: 106 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

Controls

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe

Freezer compartment ❄️❄️❄️

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CBNef 5715
Comfort

Bio Fresh No Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\lt; A^{+++}$ ¹
 Energy consumption year / 24 hrs: 195 / 0.534 kWh ¹
 Total net capacity: 381 litre (Fridge: 275 litre including BioFresh compartment: 108 litre / Freezer compartment: 106 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment ❄️❄️❄️

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

The features shown are model dependent; the description applies to the relevant model.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



CBNPes 3967
PremiumPlus

Bio Fresh Plus No Frost A++ Duo Cooling Ice Maker Soft System Smart Steel

Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year / 24 hrs: 262 / 0.716 kWh¹
 Total net capacity: 321 litre (Fridge: 238 litre including BioFresh compartment: 80 litre / Freezer compartment: 83 litre)
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / stainless steel
 Exterior dimensions in cm (h/w/d): 201.1 / 60 / 63¹

CBNPbs 4858
Premium

Bio Fresh No Frost A+++20% Duo Cooling Soft System Soft Telescopic Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 149 / 0.408 kWh¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5¹

CBNPes 4858
Premium

Bio Fresh No Frost A+++20% Duo Cooling Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 149 / 0.408 kWh¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5¹

CBNbs 4815
Comfort

Bio Fresh No Frost A+++ Duo Cooling Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 186 / 0.507 kWh¹
 Total net capacity: 343 litre (Fridge: 242 litre including BioFresh compartment: 94 litre / Freezer compartment: 101 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5¹

Controls

- Cursor controlled LCD display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ★★★★★

- 4 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- BioFresh-Plus
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Controls

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ★★★★★

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe

Controls

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ★★★★★

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe

Colour / material options:
CBNP 4858 in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ★★★★★

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Colour / material options:
CBNef 4815 with Stainless steel front
CBN 4815 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



GlassEdition appliances have a **recessed handle with integrated opening mechanism** to the side of the door casing, which provides convenient and easy door opening. Being flush integrated, as opposed to protruding forwards, this handle concept is perfect for contemporary, hand-free kitchens.



Premium GlassLine door shelves with stainless steel trim. Elegant s/steel bars help retain taller bottles and jars.



CBNPgb 4855
Premium

Bio Fresh No Frost A+++ 20% Duo Cooling Soft System Soft Telescopic Glass Edition

Energy efficiency class: $\lt; A^{+++}$ ¹
 Energy consumption year / 24 hrs: 149 / 0.408 kWh ¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Glass front black / silver
 Exterior dimensions in cm (h / w / d): 201 / 60 / 68.5 ¹

CBNPgw 4855
Premium

Bio Fresh No Frost A+++ 20% Duo Cooling Soft System Soft Telescopic Glass Edition

Energy efficiency class: $\lt; A^{+++}$ ¹
 Energy consumption year / 24 hrs: 149 / 0.408 kWh ¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Glass front white / white
 Exterior dimensions in cm (h / w / d): 201 / 60 / 68.5 ¹



The high-performance **PowerCooling system** ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, quantity-controlled
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Variable bottle shelf
 - LED ceiling lighting with dimmer function
 - LED BioFresh lighting
 - LED rear wall lighting
 - 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe
- Freezer compartment** ********
- 3 drawers, of which 2 set on roller tracks, VarioSpace
 - Ice cube tray
 - LED lighting
 - Temperature rise time: 24 h
 - Freezing capacity in 24 hrs: 16 kg
 - 2 cold storage accumulators
 - Safety glass fittings
- Key features**
- GlassEdition
 - Recessed handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, quantity-controlled
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Variable bottle shelf
 - LED ceiling lighting with dimmer function
 - LED BioFresh lighting
 - LED rear wall lighting
 - 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe
- Freezer compartment** ********
- 3 drawers, of which 2 set on roller tracks, VarioSpace
 - Ice cube tray
 - LED lighting
 - Temperature rise time: 24 h
 - Freezing capacity in 24 hrs: 16 kg
 - 2 cold storage accumulators
 - Safety glass fittings
- Key features**
- GlassEdition
 - Recessed handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Fridges



KBPgw 4354

Quality in every detail




LED

The **LED rear wall lighting** is integrated into the rear section of the horizontal dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the fridge compartment, from top to bottom and provide high-quality illumination.



The practical **VarioSafe** makes it easy to view and organise all sorts of stored items. It is the ideal space for smaller food packets, tubes and jars. An additional insertion height is available for filling to a greater capacity if necessary.



BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug 2. Functional wall spacer to maintain wall clearance and allow connection 3. Variable speed compressor 4. Plinth fan with noise-damping 5. Condenser 6. Defrost water drain



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.



Soft
System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of toughened glass. The sectioned, slide-under glass shelf can be located to suite individual requirements.

The features shown are model dependent; the description applies to the relevant model.



Quality in every detail



GlassEdition appliances have a **recessed handle with integrated opening mechanism** to the side of the door casing, which provides convenient and easy door opening. Being flush integrated, as opposed to protruding forwards, this handle concept is perfect for contemporary, hand-free kitchens.



The **4-star freezer** compartment is designed to freeze fresh food and store it for long periods. Temperatures of -18 °C and lower ensure that nutritional content is preserved during storage.

KBPes 4354
Premium

Bio Fresh A+++ -20% Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\lt;A^{+++}$¹
 Energy consumption year / 24 hrs: 128/0.350 kWh¹
 Total net capacity: 338 litre (Fridge: 314 litre including BioFresh compartment: 133 litre/Freezer compartment: 24 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBPgb 4354
Premium

Bio Fresh A+++ -20% Soft System Soft Telescopic Glass Edition

Energy efficiency class: $\lt;A^{+++}$¹
 Energy consumption year / 24 hrs: 128/0.350 kWh¹
 Total net capacity: 338 litre (Fridge: 314 litre including BioFresh compartment: 133 litre/Freezer compartment: 24 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Glass front black/silver
 Exterior dimensions in cm (h/w/d): 185/60/68.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ★★★★★

- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ★★★★★

- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- HardLine
- Recessed handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Colour / material options:
KBPgw 4354 with Glass front white




LED light columns are integrated on **either side** to uniformly illuminate the fridge interior. A special satinfinish on the light cover creates an appealing and sophisticated lighting ambience.



The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure. The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



KBbs 4350
Premium

Bio Fresh A+++ Soft System Soft Telescopic Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 90 / 0.244 kWh¹
 Total net capacity: 367 litre (Fridge: 367 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5¹

KBes 4350
Premium

Bio Fresh A+++ Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 90 / 0.244 kWh¹
 Total net capacity: 367 litre (Fridge: 367 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
 Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5¹

KBes 3750
Premium

Bio Fresh A+++ Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 87 / 0.236 kWh¹
 Total net capacity: 318 litre (Fridge: 318 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
 Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5¹

KB 4310
Comfort

Bio Fresh A+++

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 90 / 0.244 kWh¹
 Total net capacity: 366 litre (Fridge: 366 litre including BioFresh compartment: 133 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Colour / material options:
KB 4350 in white

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Colour / material options:
KB 3750 in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to HydroSafe or DrySafe

Colour / material options:
KBef 4310 with Stainless steel front

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



BP 2850

Full BioFresh fridge



By gently touching the precision **touchscreen control panel**, all BioFresh-Safes can be set to either 'Dry' for drier storage conditions that suit meat, fish and dairy products or 'Hydro' for moister storage conditions that favour fruit and vegetables.



The sturdy **handle with** its refined, premium-quality appearance and **an integrated opening mechanism** ensures easy and effortless opening of the door.



BLU
Performance

◀60▶

BP 2850
Premium

Bio
Fresh

A+++
A-20%

Energy efficiency class: $\lt; A^{+++}$¹

Energy consumption year/24 hrs: 62/0.169 kWh¹

Total net capacity: 157 litre

Noise output: 37 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 125/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

BioFresh compartment

- Ventilator
- LED lighting
- 5 BioFresh-Safes on telescopic rails, adjustable from HydroSafe to DrySafe

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Integrated Side-by-Side
food storage centres



Quality in every detail



LED light columns are integrated on one or both sides of the fridge compartment to uniformly illuminate the interior. The light gradually gets brighter when the door is opened. The satin finish on the light unit creates elegant lighting. The LED light columns also enable you to position the glass shelves at your convenience.



Made from safety glass, the stylish **GlassLine** fittings add the finishing touches to the high quality interior design. These satin-finished glass shelves, with premium quality stainless steel edging, are scratch-resistant and easy to clean. The split glass shelf offers outstanding flexibility.



BioFresh provides the perfect storage climate for long-lasting food storage freshness. When stored at just over 0 °C and at the ideal humidity level, fruit, vegetables, meat and fish all retain their nutritious vitamins for longer.



For more about BioFresh, please visit: biofresh.liebherr.com



Soft Telescopic

Premium BioFresh appliances have fully extendable BioFresh-Safes featuring **SoftTelescopic**, a self-retraction mechanism with soft closing, for practical, reliable and convenient everyday use. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.



Certain Premium models with BioFresh feature the new **VarioSafe** drawer, which enables organisation whilst providing a clear view. It is the perfect place to keep smaller items. The drawer can be positioned at various levels elevations on the lighting columns.



No Frost

With **NoFrost**, chilled circulating air freezes the food and any moisture is expelled, which keeps the freezer compartment ice-free at all times and prevents food frosting over.



For more about NoFrost, please visit: nofrost.liebherr.com



Ice Maker

The plumbed-in automatic **IceMaker** keeps you topped up with high-quality ice cubes for every occasion. Whether you need ice for a refreshing drink or a party with friends, with two drawers, the IceMaker holds all the ice cubes you'll need. Furthermore, it automatically keeps your supplies topped up and you can switch it off at any time.

The features shown are model specific; the description applies to the relevant model.



178

SBS 7014
Premium



178

SBS 6613
Premium

SIGN 3576
Premium

No Frost A++ LED Ice Maker Soft System Telescopic Rails

Fixed door / built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year/24 hrs: 241/0.660 kWh
 Total net capacity: 209 litre
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

IKBP 3560
Premium

Bio Fresh A+++ Soft System Soft Telescopic

Fixed door / built-in appliance for integrated use
 Energy efficiency class: <A+++>
 Energy consumption year/24 hrs: 89/0.242 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 35 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

SIGN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Soft System

Fixed door / built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year/24 hrs: 230/0.628 kWh
 Total net capacity: 255 litre (Fridge: 193 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

ICBN 3386
Premium

Bio Fresh No Frost A++ Duo Cooling Ice Maker Soft System Soft Telescopic

Fixed door / built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year/24 hrs: 232/0.633 kWh
 Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ★★★★★

- 9 drawers, of which 5 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.5 kg
- LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinge, left

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ★★★★★

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinge, left

Fridge compartment

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- LED light column left
- 1 BioCool-Box on telescopic rails with LED lighting

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ★★★★★

- 4 drawers, of which 1 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.0 kg
- LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Integrated fridge-freezers and fridges



Both the extra-strong, satin-finished **GlassLine shelves** and the door shelves with solid aluminium railings are height adjustable. The door shelving can easily accommodate large bottles as well as wider containers.



Available as optional accessories: easy-to-install **stainless steel fronts** and handles in elegant **stainless steel** or sturdy **aluminium** that ensure that the door is particularly effortless to open.

Integrated fridge-freezers



◀ 91 ▶
203



◀ 91 ▶
203

ECBN 6256 PremiumPlus



Fixed door/built-in appliance for integrated use

Energy efficiency class: <A>

Energy consumption year/24 hrs: 322/0.881 kWh

Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)

Noise output: 43 dB(A)

Climate rating: SN-T

Aperture dimensions in cm (h/w/d): 203.2-203.3/91.5/at least 62.5

Special fitting depth see installation diagram

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ****

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.3 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 11 kg

Key features

- Height-adjustable feet at front and back
- Door hinge left fixed / right fixed

ECBN 6156 PremiumPlus



Fixed door/built-in appliance for integrated use

Energy efficiency class: <A>

Energy consumption year/24 hrs: 410/1.121 kWh

Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)

Noise output: 42 dB(A)

Climate rating: SN-T

Aperture dimensions in cm (h/w/d): 203.2/91.5/at least 62.5

Special fitting depth see installation diagram

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ****

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.3 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 11 kg

Key features

- Height-adjustable feet at front and back
- **Choose from left (617) or right (001) hand hinge, fixed**



LED light columns are integrated on either side of the fridge to uniformly illuminate the interior. A special satin finish on the light cover creates an appealing and sophisticated lighting ambience, and the lights softly brighten when the appliance is opened creating an extremely pleasant effect.




Available as optional accessories: easy-to-install **stainless steel fronts** and handles in elegant **stainless steel** or sturdy **aluminium** that ensure that the door is particularly effortless to open.

Integrated fridge-freezers



ECBN 5066 PremiumPlus



Fixed door/built-in appliance for integrated use

Energy efficiency class: $\leq A^{++}$

Energy consumption year/24 hrs: 287/0.785 kWh

Total net capacity: 379 litre (Fridge: 276 litre including BioFresh compartment: 57 litre / Freezer compartment: 103 litre)

Noise output: 42 dB(A)

Climate rating: SN-T

Aperture dimensions in cm (h/w/d): 203.2/76.2/at least 61

Special fitting depth see installation diagram

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.0 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 30 h
- Freezing capacity in 24 hrs: 12 kg

Key features

- Height-adjustable feet at front and back
- **Choose from left (617) or right (001) hand hinge, fixed**

Quality in every detail



Ice Maker

The **plumbed-in IceMaker** provides high-quality ice cubes. The two drawers hold all the ice you need for any occasion. The IceMaker - which can be switched off any time - automatically keeps your ice supplies topped up.



Soft System

The stylish white **SoftSystem** mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



Liebherr's practical **FlexSystem** for BioFresh drawers provides flexible, organised and clear food storage. For example, fruit and vegetables can be kept clearly separated or foods can be stored according to their use-by date. All components of the sturdy FlexSystem are easy to clean and dishwasher safe.



The extendible design of the **versatile egg shelf** makes it suitable for securely storing up to 20 chicken eggs or 28 quail eggs. To extend their shelf life, we recommend storing the eggs pointy-end down or placing the egg shelf in the FlexSystem of a BioFresh drawer (low humidity).



The large **ice cube tray** is easy to fill with water thanks to its convenient fill opening. The lid seals on tightly so that the tray can be safely moved and placed in the appliance without spills.



The **versatile bottle shelf**, which sits above the BioFresh drawers - Safes in Premium-range appliances, is an innovative feature. It can be used in two ways: to store bottles or the integrated glass panel beneath it can be inserted and the shelf used for general storage.



Soft Telescopic

BioFresh drawers on smooth-running, full-extension rails are equipped with **SoftTelescopic**. The self-retracting function with a soft closing mechanism makes them practical, reliable and convenient for daily use. The drawers can even be fully pulled out and removed when the door is open at a 90° angle.

The features shown are model specific; the description applies to the relevant model.

Quality in every detail



The two **removable VarioBoxes** make it easier to sort and store small food items so that they can be clearly seen. A drawer stop ensures that the VarioBoxes are secure and do not fall out when items are removed.



The elegant **Premium-electronics** system ensures that the selected temperature is precisely maintained. All functions can be easily and conveniently managed by gently tapping the touchscreen interface. The temperature is numerically displayed and can be read from the MagicEye's LCD display.



The practical **VarioSafe** makes it easy to view and organise all sorts of stored items. It is the ideal space for smaller food packets, tubes and jars. An additional insertion height is available for filling to a greater capacity if necessary.



The stylish **butter dish** can be conveniently accessed and removed with just one hand, and is easily opened. It is shatterproof, dishwasher safe and fits on all Liebherr shelves.



**Side
by
Side**

The **Side-by-Side** concept makes it possible to position fridges, freezers and wine cabinets for your personal choice. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. Further information can be found on pages 74/75 and in the Liebherr built-in appliances catalogue.



**Power
Cooling**

The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly chilled and that an even temperature is maintained throughout the interior. A door contact switch turns the fan off when the door is opened, to help save valuable energy.



**Duo
Cooling**

With two independently controlled circuits, **DuoCooling** can be used to separately control the temperature in the fridge and freezer compartments of fridge-freezers. Furthermore, there is no air exchange between the fridge and freezer compartments. This prevents odour transfer and stops food from drying out.

The features shown are model specific; the description applies to the relevant model.



ICBN 3386
Premium

- Bio Fresh
- No Frost
- A++
- Duo Cooling
- Ice Maker
- Soft System
- Soft Telescopic

Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 232/0.633 kWh
 Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Freezer compartment ★★★★★

- 4 drawers, of which 1 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 1.0 kg
- LED lighting
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

ICBN 3376
Premium

- Bio Fresh
- No Frost
- A++
- Duo Cooling
- Soft System
- Soft Telescopic

Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 236/0.644 kWh
 Total net capacity: 238 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Freezer compartment ★★★★★

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

ICBP 3266
Premium

- Bio Fresh
- Smart Frost
- A+++
- Duo Cooling
- Soft System
- Soft Telescopic

Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 162/0.442 kWh
 Total net capacity: 261 litre (Fridge: 204 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 34 dB(A)
 Climate rating: SN
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Freezer compartment ★★★★★

- 2 drawers, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 27 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

ICBN 3324
Comfort

- Bio Fresh
- No Frost
- A++
- Duo Cooling

Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 235/0.643 kWh
 Total net capacity: 237 litre (Fridge: 175 litre including BioFresh compartment: 67 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment ★★★★★

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Quality in every detail



The elegant **Premium-electronics** system ensures that the selected temperature is precisely maintained. All functions can be easily and conveniently managed by gently tapping the touchscreen interface. The temperature is numerically displayed and can be read from the MagicEye's LCD display.



Soft Telescopic

BioFresh drawers on smooth-running, full-extension rails are equipped with **SoftTelescopic**. The self-retracting function with a soft closing mechanism makes them practical, reliable and convenient for daily use. The drawers can even be fully pulled out and removed when the door is open at a 90° angle.



178



178

IKBP 3560
Premium

Bio Fresh A+++ Soft System Soft Telescopic

Fixed door/built-in appliance for integrated use
 Energy efficiency class: <A+++>
 Energy consumption year/24 hrs: 89/0.242 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 35 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging

IKBP 3564
Premium

Bio Fresh A+++ Soft System Soft Telescopic

Fixed door/built-in appliance for integrated use
 Energy efficiency class: <A+++>
 Energy consumption year/24 hrs: 160/0.438 kWh
 Total net capacity: 284 litre (Fridge: 257 litre including BioFresh compartment: 90 litre / Freezer compartment: 27 litre)
 Noise output: 35 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57/at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Freezer compartment ****

- Ice cube tray with lid
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



Soft System

The stylish white **SoftSystem** mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.



Fresh food can be carefully frozen and kept in long-term storage in the **4-star freezer compartment**. For clearer visibility and easy access, the removable shelf can be used to conveniently divide the freezer compartment into two sections.

The features shown are model specific; the description applies to the relevant model.



178



178




140



122

IKB 3560
Premium



Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 133/0.363 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging

IKB 3520
Comfort



Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 133/0.363 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 3 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Key features

- Height-adjustable feet at front
- Reversible door hinging

IKBP 2760
Premium



Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 83/0.226 kWh
 Total net capacity: 230 litre (Fridge: 230 litre including BioFresh compartment: 59 litre)
 Noise output: 35 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 139.7 - 141.3/56 - 57 / at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging

IKB 2360
Premium



Fixed door/built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 121/0.329 kWh
 Total net capacity: 196 litre (Fridge: 196 litre including BioFresh compartment: 59 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 122 - 123.6/56 - 57 / at least 55

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to HydroSafe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging



Side by Side

Our Side-by-Side concept enables the creation of customised food and wine storage centres. For example, the full space BioFresh fridge IB 1650 can be combined with a conventional fridge positioned above it.

Further information about our Side-by-Side concept can be found on pages 74/75 and in the built-in appliances catalogue.

Integrated full BioFresh fridge



By gently touching the precision **touchscreen control panel**, all BioFresh-Safes can be set to either 'Dry' for drier storage conditions that suit meat, fish and dairy products or 'Hydro' for moister storage conditions that favour fruit and vegetables.



The chic white **SoftSystem** mechanism that is integrated into the door of the IB 1650 conveniently cushions door movement and ensures particularly soft closure. Further, the door closes automatically from an angle of about 30°.



Side by Side

88

IB 1650
Premium

Bio Fresh

A⁺⁺

Soft System

Fixed door / built-in appliance for integrated use

Energy efficiency class: $\lt; A^+$

Energy consumption year / 24 hrs: 109 / 0.298 kWh

Total net capacity: 84 litre

Noise output: 38 dB(A)

Climate rating: SN-T

Aperture dimensions in cm (h/w/d): 87.4 - 89 / 56 - 57 / at least 55

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

BioFresh compartment

- Ventilator
- 4 BioFresh-Safes, of which 3 on roller tracks, adjustable from HydroSafe to DrySafe, 1 FlexSystem

Key features

- Side wall and ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging

Your individually styled food and wine storage centre

Built-in appliances with BioFresh can be combined with other built-in models by being installed next to or on top of one another. This enables you to create your very own storage centre consisting of fridge-freezers, fridges, freezers and wine cabinets. All appliances labelled 'Side-by-Side' are able to be used as the starting point for possible combinations that will integrate perfectly into your kitchen and meet your own personal storage and freshness requirements. Our food and wine storage centres allow you to enjoy all the benefits of Liebherr appliances at once: BioFresh for food that stays fresher for longer, wine at the perfect drinking temperature, a large fridge, and the frost-free convenience of a NoFrost freezer.

Further information about our Side-by-Side concept can be found in the built-in appliances catalogue.



Our catalogues

Find out everything you need to know about Liebherr Freestanding & Built-In refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as hard copy or PDF downloads from home.liebherr.com.



View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



biofresh.liebherr.com



nofrost.liebherr.com



wine.liebherr.com

Smart communication on all fronts



BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



Kitchen Photo Designer App

Be your own interior designer: take a photo of your kitchen, select the Liebherr model of your choice and position it into your photo by swiping the screen.



IceCrusher App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.

apps.home.liebherr.com




Discover the world of Liebherr-Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!



Click the link to directly access our social media channels:

socialmedia.home.liebherr.com

Please contact Liebherr-Great Britain Ltd. to locate your nearest Liebherr displaying dealer:



Liebherr-Great Britain Ltd.

Normandy Lane, Stratton Business Park, Biggleswade, SG18 8QB

Tel.: +44 (0) 3330 147 888, Fax: +44 (0) 1767-602 152,

Email Sales: sales.ukrefrigeration@liebherr.com, Customer Service: customerservice.ukrefrigeration@liebherr.com
home.liebherr.com