



Built-in Core Range
Refrigeration 2017

LIEBHERR
Quality, Design and Innovation



Quality

For more than 60 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

Discernible quality: BioFresh

BioFresh technology offers tangible, long-lasting freshness. Many foods will retain their healthy nutrients, such as vitamins and minerals, significantly longer in a BioFresh compartment (with a temperature close to 0°C and controlled humidity conditions) than in a traditional fridge compartment.

Professional quality

As a refrigeration appliance specialist, Liebherr offers a wide range of professional appliances for commercial use. In the professional sector, the most stringent demands must be met in terms of food safety and freshness. The expertise that we have built up through decades of experience in the commercial sector can be enjoyed on a daily basis as you use your contemporary Liebherr appliance.

Tested quality

So that you can rely on your refrigeration appliance 24 hours a day, 365 days a year, we test every component for its long-term reliability, right from the design stage. For example, before a component such as a door hinge finds its way into production, it will first have to undergo 100.000 opening/closing cycles, which corresponds to more than 15 years of use.

Proven quality

Before packaging, every single appliance goes through a comprehensive quality inspection. This procedure tests all refrigeration technology, and all mechanical and electronic components. In addition, a visual inspection to confirm quality of workmanship also takes place.

Guaranteed quality

We provide a two-year warranty that covers all parts and labour costs to repair or replace any part of the appliance that proves to be defective in materials or workmanship and also a ten year parts availability.

VCC compressor

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.



Detailed quality



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost: nofrost.liebherr.com



Duo Cooling

Accurate and independent temperature control of the fridge and freezer compartments is facilitated by **DuoCooling**: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards allowing taller bottles to be stored. **BioFresh drawers** in the Premium models come with central **LED lighting** for an optimum view of the food stored. The LEDs are integrated into the partition plate to evenly and brightly illuminate the extended BioFresh drawers from directly above.



The **versatile egg storage tray** is fully removable and its capacity can be adjusted to securely accommodate between 10 and 20 hens' eggs, or up to 28 quails' eggs if it is inverted. It allows eggs to be stored with their pointed side facing downwards, which increases their storage life.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running roller tracks; it is convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slide control.

The features shown are model dependent; the description applies to the relevant model.



178

178

SBS 6613 Premium
(SICN 3386/ICBN 3386)

Bio Cool No Frost A++ Duo Cooling Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
Energy efficiency class: **A++**
Energy consumption year/24 hrs: 230/0.628 kWh
Total net capacity: 255 litre (Fridge: 193 litre/Freezer compartment: 62 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

Fixed door/Built-in appliance for integrated use
Energy efficiency class: **A++**
Energy consumption year/24 hrs: 232/0.633 kWh
Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre/Freezer compartment: 57 litre)
Noise output: 38 dB(A)
Climate rating: SN-ST
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



178

178

SBS 6612 Premium
(ICN 3386/SICN 3386)

Bio Cool No Frost A++ Duo Cooling Ice Maker Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
Energy efficiency class: **A++**
Energy consumption year/24 hrs: 225/0.615 kWh
Total net capacity: 248 litre (Fridge: 191 litre/Freezer compartment: 57 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

Fixed door/Built-in appliance for integrated use
Energy efficiency class: **A++**
Energy consumption year/24 hrs: 230/0.628 kWh
Total net capacity: 255 litre (Fridge: 193 litre/Freezer compartment: 62 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



ICBN 3386

Fridge-freezers



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** - the practical storage solution for larger items. The built-in fridge-freezers in the Premium range also have **LED** lighting in the freezer compartment.



Premium BioFresh appliances feature **two integrated lighting columns** with multiple LEDs to evenly illuminate the interior. The lighting columns also facilitate the variable positioning of the glass shelves.



178



178

ICBN 3386
Premium

Bio Fresh	No Frost	A++	Duo Cooling	Ice Maker	Soft System	Soft Telescopic
-----------	----------	-----	-------------	-----------	-------------	-----------------

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: $\lt; A^+$
 Energy consumption year / 24 hrs: 232 / 0.633 kWh
 Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICBN 3376
Premium

Bio Fresh	No Frost	A++	Duo Cooling	Soft System	Soft Telescopic
-----------	----------	-----	-------------	-------------	-----------------

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: $\lt; A^+$
 Energy consumption year / 24 hrs: 236 / 0.644 kWh
 Total net capacity: 238 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



Bio Fresh

In the **BioFresh compartments** food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C.



The **VarioSafe** in Premium BioFresh models provides a clear view whilst creating order. It is the ideal space for smaller food packets, tubes and jars. The safe can be positioned at various levels on the lighting column. An additional insertion height is available for filling to a greater capacity if necessary.



Ice Maker

The automatic **IceMaker** from Liebherr provides perfect ice cubes for every occasion. An integrated water filter ensures perfect water quality at all times. The electronic display indicates when the water filter needs replacing.



Soft System

The **SoftSystem** feature provides added safety and convenience. Integrated on the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.



178



178



178



Side by Side

178

ICBN 3324
Comfort

Bio Fresh No Frost A++ Duo Cooling

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 235/0.643 kWh
 Total net capacity: 237 litre (Fridge: 175 litre including BioFresh compartment: 67 litre/Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICBP 3266
Premium

Bio Fresh Smart Frost A+++ Duo Cooling Soft System Soft Telescopic

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\langle A^{+++} \rangle$
 Energy consumption year/24 hrs: 162/0.442 kWh
 Total net capacity: 261 litre (Fridge: 204 litre including BioFresh compartment: 67 litre/Freezer compartment: 57 litre)
 Noise output: 34 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Ice Maker Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 225/0.615 kWh
 Total net capacity: 248 litre (Fridge: 191 litre/Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

SICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 230/0.628 kWh
 Total net capacity: 255 litre (Fridge: 193 litre/Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.



No Frost

The **NoFrost system** provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost: nofrost.liebherr.com



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. A door contact switch turns off the fan when the door is opened, saving energy.



Smart Frost

With the **SmartFrost technology**, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



178



178



178



178

ICNS 3324
Comfort



Sliding door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 230/0.630 kWh
 Total net capacity: 256 litre (Fridge: 194 litre/Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICUN 3324
Comfort



Fixed door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 230/0.630 kWh
 Total net capacity: 256 litre (Fridge: 194 litre/Freezer compartment: 62 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICUNS 3324
Comfort



Sliding door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 230/0.630 kWh
 Total net capacity: 256 litre (Fridge: 194 litre/Freezer compartment: 62 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICP 3324
Comfort



Fixed door/Built-in appliance for integrated use
 Energy efficiency class: **A+++**
 Energy consumption year/24 hrs: 156/0.427 kWh
 Total net capacity: 274 litre (Fridge: 194 litre/Freezer compartment: 80 litre)
 Noise output: 34 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



Comfort models come with **Comfort GlassLine** - superior glass fittings for the door interior. The shelves for storing preserves and bottles are fitted with a satin-finished safety glass base and an attractive plastic surround with an adjustable bottle holder.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** - the practical storage solution for larger items.



The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.



All **transparent FrostSafe drawers** are extra deep. They are designed so that all frozen foods, from a duck to a boxed pizza, will fit conveniently and neatly, and are easy to remove. Every drawer can be used for both freezing and storage, so there's no need to repack the food once it has been frozen.



178



178



178



158

ICU 3324
Comfort Bio Cool Smart Frost A⁺⁺

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: A⁺⁺
 Energy consumption year/24 hrs: 235/0.642 kWh
 Total net capacity: 274 litre (Fridge: 194 litre/Freezer compartment: 80 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICUS 3324
Comfort Bio Cool Smart Frost A⁺⁺

Sliding door/Built-in appliance for integrated use
 Energy efficiency class: A⁺⁺
 Energy consumption year/24 hrs: 224/0.611 kWh
 Total net capacity: 274 litre (Fridge: 194 litre/Freezer compartment: 80 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICUS 3224
Comfort Bio Cool Smart Frost A⁺⁺

Sliding door/Built-in appliance for integrated use
 Energy efficiency class: A⁺⁺
 Energy consumption year/24 hrs: 217/0.593 kWh
 Total net capacity: 281 litre (Fridge: 224 litre/Freezer compartment: 57 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

ICUS 2924
Comfort Bio Cool Smart Frost A⁺⁺

Sliding door/Built-in appliance for integrated use
 Energy efficiency class: A⁺⁺
 Energy consumption year/24 hrs: 203/0.556 kWh
 Total net capacity: 241 litre (Fridge: 184 litre/Freezer compartment: 57 litre)
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 157.4-159/56-57/min. 55



IKB 3560

**Side
by
Side**

Refrigerators can be perfectly combined with other fridges, freezers and wine cabinets to create an individualised food storage centre to fit a variety of niche sizes, such as here: a BioFresh refrigerator (IKB 3560) with a freezer (SIGN 3556).

Fridges



**Soft
Telescopic**

The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



The **versatile egg storage tray** is fully removable and its capacity can be adjusted to securely accommodate between 10 and 20 hens' eggs, or up to 28 quails' eggs if it is inverted. It allows eggs to be stored with their more pointed side facing downwards, which increases their storage life.



178



178

IKB 3560
Premium

Bio Fresh A++ Soft System Soft Telescopic

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 133 / 0.363 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

IKB 3520
Comfort

Bio Fresh A++

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 133 / 0.363 kWh
 Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



The **4-star freezer** compartment is designed to freeze fresh food and store it for long periods. Temperatures of -18°C and lower ensure that nutritional content is preserved during storage.



The **bottle shelf** is a practical and elegant solution for storing drinks. As many as five bottles can be chilled and stored neatly.




Two **removable bottle baskets** on the pull-out shelf provide plenty of space for bottles (up to 1.5 l) and drinks cartons. The integrated handles make carrying the baskets easy while the adjustable bottle carriers stop things from sliding around.



With the bottle baskets removed, the **pull-out shelf** offers enough space for a conventional drinks crate. Smooth-running telescopic rails make it easy to access the large stock of chilled drinks.



178



178



178

IK 3524
Comfort

Bio Cool A++ Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 214/0.584 kWh
 Total net capacity: 306 litre (Fridge: 279 litre/Freezer compartment: 27 litre)
 Noise output: 37 dB(A)
 Climate rating: ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

IK 3520
Comfort

Bio Cool A++ Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 117/0.319 kWh
 Total net capacity: 325 litre
 Noise output: 34 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55

IKF 3510
Comfort

A++ Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 117/0.319 kWh
 Total net capacity: 325 litre
 Noise output: 36 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55



Fridges



Premium BioFresh appliances feature **two integrated lighting columns** with multiple LEDs to evenly illuminate the interior. The lighting columns also facilitate the variable positioning of the glass shelves.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. A door contact switch turns off the fan when the door is opened, saving energy.



140



140



140

IKBP 2760 Premium

Bio Fresh A+++ Soft System Soft Telescopic

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\lt; A^{+++}$
 Energy consumption year/24 hrs: 83/0.226 kWh
 Total net capacity: 230 litre (Fridge: 230 litre including BioFresh compartment: 59 litre)
 Noise output: 35 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 139.7-141.3/56-57/min. 55

IK 2764 Premium

Bio Cool A++ Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\lt; A^{++}$
 Energy consumption year/24 hrs: 187/0.512 kWh
 Total net capacity: 235 litre (Fridge: 215 litre/Freezer compartment: 20 litre)
 Noise output: 38 dB(A)
 Climate rating: ST
 Aperture dimensions in cm (h/w/d): 139.7-141.3/56-57/min. 55

IK 2760 Premium

Bio Cool A++ Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
 Energy efficiency class: $\lt; A^{++}$
 Energy consumption year/24 hrs: 109/0.296 kWh
 Total net capacity: 251 litre
 Noise output: 36 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 139.7-141.3/56-57/min. 55



In the **BioFresh compartments** food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C. BioFresh drawers in the Premium models come with central **LED** lighting for an optimum view of the food stored.



The **SoftSystem** feature provides added safety and convenience. Integrated on the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.



The large, **lidded ice cube tray** is easy to refill with water thanks to its convenient filling hole and, because the lid seals thoroughly, the newly refilled tray can be transported safely back to the freezer without spillage.



The **removable VarioBoxes** provide excellent organisation and storage for smaller food items and, at the same time, they allow a clear view of the contents. They are easy to open, fill and close with one hand, as well as to completely remove and subsequently reinsert.



122



122



122



122



102

IKB 2360
Premium

Bio Fresh A++ Soft System Soft Telescopic

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 121/0.329 kWh
Total net capacity: 196 litre (Fridge: 196 litre including BioFresh compartment: 59 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 122-123.6/56-57/min. 55

IK 2360
Premium

Bio Cool A++ Soft System Telescopic Rails

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 105/0.286 kWh
Total net capacity: 216 litre
Noise output: 35 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 122-123.6/56-57/min. 55

IK 2320
Comfort

Bio Cool A++

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 105/0.286 kWh
Total net capacity: 217 litre
Noise output: 35 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 122-123.6/56-57/min. 55

IK 2324
Comfort

Bio Cool A++

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 174/0.476 kWh
Total net capacity: 201 litre (Fridge: 185 litre/
Freezer compartment: 16 litre)
Noise output: 37 dB(A)
Climate rating: ST
Aperture dimensions in cm (h/w/d): 122-123.6/56-57/min. 55

IK 1960
Premium

Bio Cool A++ Soft System

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 101/0.275 kWh
Total net capacity: 181 litre
Noise output: 33 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 102.4-104/56-57/min. 55



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.



You can freeze fresh food and store frozen food for long periods in appliances with the **4-star freezer compartment**. Temperatures of -18°C and lower ensure food is stored with all the vital vitamins and minerals preserved.



Models in the Comfort range feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort Glassline comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



Ergonomically designed, the extra deep transparent **vegetable compartments** are easy-to-clean and provide ample storage for fruit and vegetables.



88



88



88



88



88

IK 1624
Comfort

Bio Cool A⁺⁺

Fixed door/Built-in appliance for integrated use
Energy efficiency class: <A>
Energy consumption year/24 hrs: 151/0.413 kWh
Total net capacity: 134 litre (Fridge: 118 litre/Freezer compartment: 16 litre)
Noise output: 36 dB(A)
Climate rating: ST
Aperture dimensions in cm (h/w/d): 87.4-89/56-57/min. 55

IKS 1624
Comfort

Bio Cool A⁺⁺

Sliding door/Built-in appliance for integrated use
Energy efficiency class: <A>
Energy consumption year/24 hrs: 147/0.401 kWh
Total net capacity: 134 litre (Fridge: 118 litre/Freezer compartment: 16 litre)
Noise output: 35 dB(A)
Climate rating: N
Aperture dimensions in cm (h/w/d): 87.4-89/56-57/min. 55

IK 1620
Comfort

Bio Cool A⁺⁺

Fixed door/Built-in appliance for integrated use
Energy efficiency class: <A>
Energy consumption year/24 hrs: 98/0.266 kWh
Total net capacity: 151 litre
Noise output: 33 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 87.4-89/56-57/min. 55

IKS 1620
Comfort

Bio Cool A⁺⁺

Sliding door/Built-in appliance for integrated use
Energy efficiency class: <A>
Energy consumption year/24 hrs: 98/0.266 kWh
Total net capacity: 151 litre
Noise output: 34 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 87.4-89/56-57/min. 55

EK 1620
Comfort

Bio Cool A⁺⁺

flush/Built-in appliance with decor panel
Energy efficiency class: <A>
Energy consumption year/24 hrs: 98/0.266 kWh
Total net capacity: 151 litre
Noise output: 34 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 87.4-88/56-57/min. 55



SIGN 2756

Freezers



No Frost

The **NoFrost system** from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.



LED

Energy-efficient, powerful, long-life and environmentally friendly **LEDs** are integrated into the underside of the freezer interior to illuminate the contents of the drawers when they are opened. As soon as the door is opened, the LED lighting brightens, conveniently displaying the contents of the drawers.



Side by Side

178



Side by Side

140

SIGN 3556 Premium	No Frost	A ⁺⁺	LED	Soft System	Telescopic Rails
Fixed door / Built-in appliance for integrated use					
Energy efficiency class: <A>					
Energy consumption year / 24 hrs: 244 / 0.668 kWh					
Total net capacity: 213 litre					
Noise output: 38 dB(A)					
Climate rating: SN-T					
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/min. 55					

SIGN 2756 Premium	No Frost	A ⁺⁺	LED	Soft System	Telescopic Rails
Fixed door / Built-in appliance for integrated use					
Energy efficiency class: <A>					
Energy consumption year / 24 hrs: 207 / 0.567 kWh					
Total net capacity: 157 litre					
Noise output: 37 dB(A)					
Climate rating: SN-T					
Aperture dimensions in cm (h/w/d): 139.7-141.3/56-57/min. 55					

Side by Side

All freezers with recess heights of 140 and 178 cm can be perfectly combined side by side with refrigerators and wine cabinets with various recess sizes to form a customised Food Storage Centre.

Freezers



All drawers and glass shelves can be easily removed from the freezer compartments in all fridge freezers with SmartFrost – this concept is known as **VarioSpace**, a practical system that quickly creates extra storage space.



Smart Frost

With the **SmartFrost technology**, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



Liebherr have now redefined energy saving with the innovative **A++ freezers**. Use of the latest electronics combined with a highly efficient refrigerating system enables the energy consumption to be significantly reduced. This super energy-saving solution actively contributes to environmental conservation.



Side by Side

88



Side by Side

88



Side by Side

72

IG 1624 Comfort

Smart Frost A++

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 159/0.434 kWh
Total net capacity: 100 litre
Noise output: 35 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d):
87.4-89/56-57/min. 55

IGS 1624 Comfort

Smart Frost A++

Sliding door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 159/0.434 kWh
Total net capacity: 100 litre
Noise output: 36 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d):
87.4-89/56-57/min. 55

IG 1024 Comfort

Smart Frost A++

Fixed door/Built-in appliance for integrated use
Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 144/0.393 kWh
Total net capacity: 73 litre
Noise output: 36 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d):
71.4-73/56-57/min. 55



UJK 1550

Under counter pull-out refrigerator



The fully extendible **pull-out fridge compartment** with **SoftTelescopic** is mounted on telescopic rails with soft stop and self-closing. It has a practical bottle shelf and a removable fruit and vegetable drawer. The large drawer can also be divided into two equal-sized compartments, with further storage space underneath.



Food can be stored securely and accessed easily on the two **fully extendable glass shelves**. Rails can be used to variably partition the glass shelves according to storage requirements.



82-87

UJK 1550
Premium

A++ Soft Telescopic

Fully extendible pull-out drawer / Under-worktop appliance for integrated use

Energy efficiency class: **A++**

Energy consumption year / 24 hrs: 92 / 0.250 kWh

Total net capacity: 118 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Aperture dimensions in cm (h/w/d): 82-87 / 60 / min. 55

Under counter fridges and freezer



The **extra-deep bottle rack** allows storing items in two rows. For instance, tall bottles in the back row and preserves or small yoghurt tubs at the front. Both rows are safely separated by an end-to-end rail. A relocatable bottle holder keeps the bottles securely in position.



UIK 1610 is suitable for **Side-by-Side installation** in conjunction with the UIG 1313 under-worktop fridge for integrated use (fridge must be on the left).



You can freeze fresh food and store frozen food for long periods in appliances with the **4-star freezer compartment**. Temperatures of -18°C and lower ensure food is stored with all the vital vitamins and minerals preserved.



All **transparent drawers** with the UIG 1313 are extra deep. They are designed so that all frozen foods, from a duck to a boxed pizza, will fit conveniently and neatly, and are easy to remove. **VarioSpace** - removable drawers sit on removable tempered glass shelves to enable the storage of large items.



82-87



82-87



82



82



Side by Side

82-87

UIK 1424
Comfort

A++ Soft System Super Cool

Fixed door/Under-worktop appliance for integrated use
 Energy efficiency class: **A++**
 Energy consumption year/24 hrs: 137/0.374 kWh
 Total net capacity: 113 litre (Fridge: 97 litre/Freezer compartment: 16 litre)
 Noise output: 39 dB(A)
 Climate rating: N-ST
 Aperture dimensions in cm (h/w/d): 82-87/60/min. 55

UIK 1610
Comfort

A+ Super Cool

Fixed door/Under-worktop appliance for integrated use
 Energy efficiency class: **A+**
 Energy consumption year/24 hrs: 119/0.324 kWh
 Total net capacity: 135 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 82-87/60/min. 55

UK 1524
Comfort

A+ Super Cool

flush/Under-worktop appliance with decor panel
 Energy efficiency class: **A+**
 Energy consumption year/24 hrs: 176/0.481 kWh
 Total net capacity: 132 litre (Fridge: 116 litre/Freezer compartment: 16 litre)
 Noise output: 39 dB(A)
 Climate rating: N
 Aperture dimensions in cm (h/w/d): 82/60/min. 57

UK 1720
Comfort

A+

flush/Under-worktop appliance with decor panel
 Energy efficiency class: **A+**
 Energy consumption year/24 hrs: 118/0.321 kWh
 Total net capacity: 150 litre
 Noise output: 34 dB(A)
 Climate rating: SN
 Aperture dimensions in cm (h/w/d): 82/60/min. 57

UIG 1313
Comfort

Smart Frost **A+** Super Frost

Fixed door/Under-worktop appliance for integrated use
 Energy efficiency class: **A+**
 Energy consumption year/24 hrs: 188/0.515 kWh
 Total net capacity: 96 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 82-87/60/min. 55




EWTgw 3583

Wine

Wine

Detailed quality



LED

All wine cabinets feature dimmable **LED lighting**, which evenly illuminates the interior and can be left on permanently if desired or activated by the door opening. Because LEDs generate minimal heat, wines can be sympathetically illuminated and beautifully presented for an extended period of time.




The electronic LC-Display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The controlled environment facilitates enhanced flavour and longevity of the stored wine.



Tip
Open

The handle-less glazed door guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines. The **TipOpen technology** opens the glazed door 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will shut it again.



Soft
System

The **SoftSystem** feature provides added safety and convenience. Integrated on the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.

The features shown are model dependent; the description applies to the relevant model.



EWTgw 3583


Multi-temperature wine cabinets



Appliances in the Vinidor range feature two separately-controllable, independent wine compartments, each of which can be set to between +5°C and +20°C. The **precise electronic controls** have a digital temperature display and are easy to use, via either a touch screen interface or electronic keys depending on the model.



The fresh air supplied through the **FreshAir activated charcoal filter** and recirculating air cooling system ensures optimal air quality. This is crucially important for the maturing process and preservation of the wine. FreshAir charcoal filters are easily accessible from the front and are replaceable.



Available from July 2017



Available from July 2017



Side by Side

Wine cabinets can be perfectly combined with other wine cabinets or refrigerators and freezers with various recess sizes.

EWTgb 3583
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open


Flush-mounted insulated glass door / Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year / 24 hrs: 165 / 0.450 kWh
 Max. Bordeaux bottles 0.75 l: 83 ¹
 Gross / net capacity: 307 / 271 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: black insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 178 / 56 / min. 55

EWTgw 3583
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open

Flush-mounted insulated glass door / Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year / 24 hrs: 165 / 0.450 kWh
 Max. Bordeaux bottles 0.75 l: 83 ¹
 Gross / net capacity: 307 / 271 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: white insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 178 / 56 / min. 55

¹ These models are designed to store DIN norm bordeaux bottles (0.75) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm) Please check cabinet weight limits with your Kitchen Retailer.



LED

All wine cabinets feature dimmable **LED lighting**, which evenly illuminates the interior and can be left on permanently if desired or activated by the door opening. Because LEDs generate minimal heat, wines can be sympathetically illuminated and beautifully presented for an extended period of time.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.




Soft System

The **SoftSystem** gentle-closing mechanism cushions movement as the door is shut to ensure extremely gentle closing, preventing vibration, which affects the quality of the wine. The door will close automatically from an opening angle of approx. 45°.



Available from July 2017

122



Available from July 2017

122



Available from July 2017

88



Available from July 2017

88

EWTgb 2383
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open

Flush-mounted insulated glass door/Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year/24 hrs: 153/0.419 kWh
 Max. Bordeaux bottles 0.75 l: 51¹
 Gross/net capacity: 195/169 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: black insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 122/56/min. 55

EWTgw 2383
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open

Flush-mounted insulated glass door/Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year/24 hrs: 153/0.419 kWh
 Max. Bordeaux bottles 0.75 l: 51¹
 Gross/net capacity: 195/169 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: white insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 122/56/min. 55

EWTgb 1683
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open

Flush-mounted insulated glass door/Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year/24 hrs: 146/0.400 kWh
 Max. Bordeaux bottles 0.75 l: 33¹
 Gross/net capacity: 125/104 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: black insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 88/56/min. 55


EWTgw 1683
Vinidor

- Wine
- LED
- Soft System
- Telescopic Rails
- Tip Open

Flush-mounted insulated glass door/Built-in appliance
 Energy efficiency class: <A>
 Energy consumption year/24 hrs: 146/0.400 kWh
 Max. Bordeaux bottles 0.75 l: 33¹
 Gross/net capacity: 125/104 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door: white insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 88/56/min. 55


¹ These models are designed to store DIN norm bordeaux bottles (0.75) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

Multi-temperature wine cabinets



Tip Open

The handle-less glazed door guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines. The **TipOpen technology** opens the glazed door 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will shut it again.



Telescopic Rails

The Vinidor appliances are equipped with solid wooden shelves mounted on **telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. Storing the bottles in opposite directions permits full use of the capacity.

Wine storage cabinet



The **hand-crafted wooden shelves** on telescopic rails are specially designed for safely storing Bordeaux bottles. The flexible clip-on labelling system provides a quick, clear overview of your wine store.



82-87



82-87



82-87

UWT 1682 Vinidor

Wine LED Soft System Telescopic Rails Tip Open

flush / Under-worktop appliance

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 144 / 0.392 kWh

Max. Bordeaux bottles 0.75 l: 34¹

Gross / net capacity: 123 / 94 litre

Noise output: 36 dB(A)

Climate rating: SN-ST

Door: black insulated glass door, handle and frame free

Aperture dimensions in cm (h/w/d): 82-87 / 60 / min. 58

UWTes 1672 Vinidor

Wine LED Telescopic Rails

flush / Under-worktop appliance

Energy efficiency class:

Energy consumption year / 24 hrs: 196 / 0.535 kWh

Max. Bordeaux bottles 0.75 l: 34¹

Gross / net capacity: 123 / 94 litre

Noise output: 38 dB(A)

Climate rating: SN-ST

Door: Glass door with stainless steel frame

Aperture dimensions in cm (h/w/d): 82-87 / 60 / min. 58

UWKes 1752 GrandCru

Wine LED Telescopic Rails

flush / Under-worktop appliance

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 145 / 0.396 kWh

Max. Bordeaux bottles 0.75 l: 46¹

Gross / net capacity: 135 / 110 litre

Noise output: 38 dB(A)

Climate rating: SN-ST

Door: Glass door with stainless steel frame

Aperture dimensions in cm (h/w/d): 82-87 / 60 / min. 57.5

¹ These models are designed to store DIN norm bordeaux bottles (0.75) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

Wine storage cabinets



The smooth-running **accessories drawer** can be used to store accessories directly below wine storage cabinets in the WKE 5 model range. This increases the 45 cm recess to a 60 cm one.

Available in white glass (9792 449), black glass (9792 451) and stainless steel (9792 453).



LED

The **dimnable LED lighting**, which evenly illuminates the interior and can be left on permanently if desired or activated by the door. Because LEDs generate minimal heat, wines can be sympathetically illuminated and beautifully presented for long term storage.



The electronic LC-Display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



45



45



45



WKEgb 582

WKEgb 582
GrandCru

Wine A+ LED Soft System Telescopic Rails Tip Open

Flush-mounted insulated glass door / Built-in appliance
 Energy efficiency class: $\lt; A$
 Energy consumption year / 24 hrs: 106 / 0.290 kWh
 Max. Bordeaux bottles 0.75 l: 18¹
 Gross / net capacity: 48 / 46 litre
 Noise output: 34 dB(A)
 Climate rating: SN-ST
 Door: black insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 45 / 56 / min. 55

WKEgw 582
GrandCru

Wine A+ LED Soft System Telescopic Rails Tip Open

Flush-mounted insulated glass door / Built-in appliance
 Energy efficiency class: $\lt; A$
 Energy consumption year / 24 hrs: 106 / 0.290 kWh
 Max. Bordeaux bottles 0.75 l: 18¹
 Gross / net capacity: 48 / 46 litre
 Noise output: 34 dB(A)
 Climate rating: SN-ST
 Door: white insulated glass door, handle and frame free
 Aperture dimensions in cm (h/w/d): 45 / 56 / min. 55

WKEes 553
GrandCru

Wine LED Telescopic Rails

flush / Built-in appliance
 Energy efficiency class: $\lt; A$
 Energy consumption year / 24 hrs: 130 / 0.356 kWh
 Max. Bordeaux bottles 0.75 l: 18¹
 Gross / net capacity: 48 / 46 litre
 Noise output: 32 dB(A)
 Climate rating: SN
 Door: Glass door with stainless steel frame
 Aperture dimensions in cm (h/w/d): 45 / 56 / min. 55

¹ These models are designed to store DIN norm bordeaux bottles (0.75) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)
 Max. 18 Bordeaux bottles for front to back storage. Taller bottles can be stored side on using the brackets provided (max. 12 Bordeaux bottles).

Global Success: Liebherr Corporate Group

Liebherr is a third-generation, family-owned company founded by Dr. Hans Liebherr in 1949 with the creation of the first ever mobile crane. With over 60 years of success, Liebherr has become synonymous with the equipment needed to build homes and businesses, as well as the appliances within them.

One of the world's largest manufacturers of construction machinery, Liebherr has expanded to eleven divisions with a wide array of product ranges, including earth moving equipment, mining, tower and maritime cranes, aerospace and transportation systems, and hotels. The company currently employs over 41,000 people in more than 130 companies in over 50 countries worldwide.

Liebherr Appliances is Europe's largest privately owned manufacturer of fridges and freezers for residential and commercial use, with an annual production of more than 2.1 million units.



Construction



Aerospace and Transportation Systems



Refrigeration & freezing



Liebherr Appliances facility in Lienz, Austria



Mining



Cranes



Tower, mobile construction & maritime cranes



Liebherr Appliances facility in Ochsenhausen, Germany