

CENTRAL  
PowerCooling

New  
TopFreezer  
Models



**LIEBHERR**

Quality, Design and Innovation



Liebherr is a leading manufacturer of fridges and freezers, known for developing products that offer outstanding energy efficiency, quality food storage and ease of use. And, because Liebherr prioritises investment in continuous research and development, its appliances are consistently innovative and always characterised by both exceptional quality and timeless design.



## Quality

For more than 60 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

## Design

Characterised by elegant and timeless design, Liebherr's fridges and freezers fulfil and surpass the highest aesthetic demands. Extensive detailing – as seen in the superb stainless steel craftsmanship, the choice of high quality materials, the stylish interior fittings, and the practical GlassLine door interior – is typical in our appliances and reveals their design quality.

## Innovation

Liebherr was first to implement lots of ideas that are now standard features in today's fridges and freezers. For example: fully enclosed FrostSafe freezer drawers that prevent loss of chilled air when the appliance is opened; patented BioFresh technology; and convenient, SoftSystem cushioned door closure.

<p>1954</p> <p>Liebherr home appliances founded in Germany</p> 	<p>1966</p> <p>Introduction of FrostSafe system</p> <p><b>Frost Safe System</b></p>	<p>1971</p> <p>First electronic control</p> 	<p>1987</p> <p>NoFrost Technology eliminating the need to defrost</p> 	<p>1993</p> <p>Conversion to CFC/HFC-free equipment program</p> 	<p>1996</p> <p>Patented BioFresh technology – system for extended storage-life</p> <p><b>Bio Fresh</b></p>	<p>2004</p> <p>Innovative LED lighting for energy efficient illumination</p> 	<p>2006</p> <p>Vinidor with adjustable temperature zones</p> 	<p>2009</p> <p>SmartSteel finish reduces the visibility of finger prints</p> 	<p>2011</p> <p>SoftSystem for gentle door closure</p> 	<p>2013</p> <p>Super thrifty built-in appliances</p> <p><b>A+++</b></p>	<p>2015</p> <p>Under-worktop TipOpen appliance for seamless integration</p> 	<p>2016</p> <p>BluPerformance: A new dimension in freshness</p> <p><b>BLU Performance</b></p>	<p>2016</p> <p>Central-PowerCooling: New TopFreezer-Models</p> <p><b>CENTRAL PowerCooling</b></p>
--	---	---	---	---	--	--	--	--	---	---	---	---	---

# Precision control and timeless design

CENTRAL  
PowerCooling

With our ingenious Central-PowerCooling technology, the refrigeration process is faster and more controlled. Cold air produced in the freezer compartment passes through air ducts into the fridge compartment. Two temperature sensors regulate the process and ensure that the required temperature is precisely maintained throughout the entire fridge compartment.

CTNef 5215  
Comfort

Bio  
Cool

No  
Frost

A++

Central  
Power  
Cooling

Smart  
Steel

Energy efficiency class:  $\leq A^{++}$  <sup>1</sup>

Energy consumption year/24 hrs: 270/0.739 kWh <sup>1</sup>

Total net capacity: 418 litre (fridge: 332 litre/freezer compartment: 86 litre)

Noise output: 40 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185.2/69.7/76 <sup>1</sup>

#### Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

#### Fridge compartment

- Central-PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

#### Freezer compartment **\*\*\*\***

- Ice cube tray
- Temperature rise time: 24 hrs
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings
- Door rack

#### Key features

- HardLine-Design
- Recessed handles
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

#### Colour / material options:

CTN 5215 in white

Central  
Power  
Cooling



<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

# Quality in every detail



Our **refrigeration technology** is integrated into the appliance plinth, instead of being located within the rear wall, which means that a significantly larger net capacity is available. Our appliances are also ultra energy efficient thanks to a highly efficient compressor and our new precision control system.



**Touch Electronic**

The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables individual temperature setting.



**Bio Cool**

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running roller tracks; it is convenient-to-use and it ensures that stored food is clearly visible. The humidity level in the BioCool-Box is regulated using a slide control.



**LED**

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored.



**Glass Line**

Stylish **GlassLine safety glass shelves** add the finishing touch to the high-quality interior design. These elegant satin-finished glass shelves, with high-quality stainless steel trims, are scratch-resistant and easy-to-clean. Their generous capacity offers plenty of space to store a wide range of food items.




**Glass Line**

The interior of the refrigerator door is furnished with **Comfort GlassLine shelves**, for yet another aesthetic accent to the overall design. These safety glass shelves are shatterproof, scratch-resistant and easy-to-clean.



Sited immediately above the refrigerator compartment, the generously sized **4-star freezer compartment** provides plenty of space for gentle, nutrient-preserving freezing of fresh foods and for long-term food storage. The safety glass shelf and door storage provide a clear overview of the contents and easy access.



Subject to modification.  
Printed in Germany by Typodruck.  
7945 529-00/07.16