



Freestanding
Refrigeration
2016/2017

LIEBHERR
Quality, Design and Innovation



Contents

Quality, Design and Innovation	04
BluPerformance	10
Food storage centres	16
Side-by-Side fridge-freezers	20
Frenchdoor fridge-freezer	26
Fridge-freezers	28
Fridges	62
Freezers	86
Wine Cabinets	118
Accessories	136

Quality

For more than 60 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

Discernible quality: BioFresh

BioFresh technology offers tangible, long-lasting freshness. Many foods will retain their healthy nutrients, such as vitamins and minerals, significantly longer in a BioFresh compartment (with an exact temperature of 0°C and controlled humidity conditions) than in a traditional fridge compartment.

Professional quality

As a refrigeration appliance specialist, Liebherr offers a wide range of professional appliances for commercial use. In the professional sector, the most stringent demands must be met in terms of food safety and freshness. The expertise that we have built up through decades of experience in the commercial sector can be enjoyed on a daily basis as you use your contemporary Liebherr appliance.

Tested quality

So that you can rely on your refrigeration appliance 24 hours a day, 365 days a year, we test every component for its long-term reliability, right from the design stage. For example, before a component such as a door hinge finds its way into production, it will first have to undergo 100.000 opening/closing cycles, which corresponds to more than 15 years of use.

Proven quality

Before packaging, every single appliance goes through a comprehensive quality inspection. This procedure tests all refrigeration technology, and all mechanical and electronic components. In addition, a visual inspection to confirm quality of workmanship also takes place.

Guaranteed quality

We provide a two-year warranty that covers all parts and labour costs to repair or replace any part of the appliance that proves to be defective in materials or workmanship.

VCC compressor

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.





Design

Characterised by elegant and timeless design, Liebherr's fridges and freezers fulfil and surpass the highest aesthetic demands. Extensive detailing – as seen in the superb stainless steel craftsmanship, the choice of high quality materials, the stylish interior fittings, and the practical Glassline door interior – is typical in our appliances and reveals their design quality.

Design for every kitchen space

So you can enjoy a lifetime of pleasure owning your Liebherr appliance, and find the perfect appliance for you, we offer a wide range of designs e.g. models in classic stainless steel, elegant BlackSteel or with stylish glass fronts, all of which blend harmoniously into modern kitchens and living spaces.

Practical design for daily use

At Liebherr, design and functionality go hand-in-hand. For example: to prevent finger marks on our stainless steel doors, we finish them with a SmartSteel surface; and, to make door opening easy and convenient, our ergonomically designed handles house an integrated opening mechanism; not to mention that, all Glassline shelves are dishwasher safe.

Lighting design

Liebherr's fridges and freezers are fitted with modern LED lighting. Upon opening the appliance door, the interior becomes evenly illuminated. LEDs are long-life, energy efficient and generate hardly any heat. We take meticulous care to install specially selected LEDs in order to achieve a harmonious, slightly bluish tinted lighting effect.

Award-winning design

The superb design-quality of our appliances has seen them honoured with many prestigious, international design awards from the likes of Plus X Award, reddot, iF product design and Good Design.



Innovation

Liebherr was first to implement lots of ideas that are now standard features in today's fridges and freezers. For example: fully enclosed FrostSafe freezer drawers that prevent loss of chilled air when the appliance is opened; patented BioFresh technology; and convenient, SoftSystem cushioned door closure.

Innovative ideas

We place great importance on the continual ongoing development of our products. Therefore, at all of our production sites, we have state-of-the-art design centres with highly skilled employees. Our goal is to be 'Best in Class' in every respect. For example, Liebherr's current appliances are super-economical in terms of energy consumption thanks to the incorporation of advanced electronics and optimised refrigeration design.

Efficiency in our range

A large proportion of our appliances fall into the highest efficiency classes. We aim to produce energy-saving appliances that do not compromise on convenience. Many of our current appliances are as much as 20% more economical than the threshold value required for the A+++ class.

Innovation for even greater freshness

The latest fridges and freezers offer the ideal climate zone for almost every type of food. So, in addition to the classic refrigerator compartment, Liebherr offers: the BioCool box: a fruit and vegetable compartment in which humidity can be regulated; BioFresh drawers, in which meat, fish, dairy products, and fruit/vegetables all find their ideal storage climate; and a NoFrost freezer compartment that offers professional quality freezing.

Innovative in every detail

It couldn't be easier to set and adjust appliances with touch screen operation. The GlassLine storage shelves can be adjustably positioned for tailored use of the interior space. Drinks storage is provided in the door interior and, depending on the model, a bottle rack or versatile bottle shelf offer additional practical storage solutions.



Frost Safe System

1966
Introduction of FrostSafe system



1987
NoFrost Technology eliminating the need to defrost

Bio Fresh

1996
Patented BioFresh technology - system for extended storage-life



2006
Vinidor with adjustable temperature zones

Duo Cooling

2010
DuoCooling for superior performance and efficiency

A+++ -20%

2013
Super thrifty Built-in appliances



2016
BLUPerformance: A new dimension in freshness

1954

Liebherr home appliances founded in Germany



1971

First electronic control



1993

Conversion to CFC / HFC-free equipment program



2004

Innovative LED lighting for energy efficient illumination



2009

SmartSteel finish reduces the visibility of finger prints



2011

SoftSystem for gentle door closure



2015

Under-worktop TipOpen appliance for seamless integration



BLU
Performance

BluPerformance – A new dimension in refrigeration design

High quality materials, meticulous workmanship in every detail, and easy-to-use/precise touch-electronics define the new BluPerformance range. The compact integration of refrigeration technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics. BioFresh and BioCool ensure lasting freshness quality for stored foods.

With elegant and timeless design, these appliances are a highlight in any kitchen and are guaranteed to be a daily pleasure to use and enjoy for many years to come.



A+++

**A+++
-20%**



Multifunction touch control

In the touch-electronic BluPerformance appliances all functions can be easily and conveniently set by gently touching the screen. The high-resolution 7" colour display enables individual settings. Preset programs such as: 'EnergySaver', 'MaxPerformance', 'Party' or 'Holiday' assist in achieving optimum food storage.

Day-to-Day

The Day-to-Day program is aimed at meeting everyday requirements. It offers optimum refrigeration performance and efficiency using standard temperature settings in the fridge and freezer compartments.

EnergySaver

The EnergySaver program lowers energy consumption further, beyond standard settings. To save energy, the temperature in the fridge and freezer compartments is slightly raised. The touch-electronic displays useful energy saving tips to help you further reduce electricity costs.

Party

The Party program is ideal when preparing for celebrations: SuperCool and SuperFrost are activated for the short-term storage and chilling of larger quantities of food. The BottleTimer allows rapid chilling of drinks. Appliances with an IceMaker can increase ice cube production.

MaxPerformance

The MaxPerformance program allows the appliance to deliver its highest refrigeration performance. It selects lower temperature settings for the fridge and freezer compartments.

Holiday

The Holiday program minimises energy consumption during extended absences from the home. The fridge compartment is set to +15°C, and the freezer compartment to -18°C.





Freshness has a name: BioFresh

With BioFresh technology food keeps fresh for much longer. When stored at a temperature close to 0°C and at the correct humidity level, many foods retain their nutrients, such as vitamins and minerals, for far longer than in a conventional fridge compartment.

Vitamins for a healthy diet

It goes without saying that it is extremely important for newly purchased and freshly harvested foods to be stored properly so that their nutrients are preserved for longer. The shelf life and freshness of most fruit and vegetables can be significantly extended by storing them in a fridge, particularly in a BioFresh compartment. Surprisingly, the vitamin content of fruit and vegetables has been found to increase during storage in a BioFresh compartment.

The perfect climate

With high humidity, the HydroSafe offers a perfect storage climate for fruit and vegetables. The drier conditions in the DrySafe are ideal for storing of meat, fish and dairy products. The moist HydroSafe climate can be changed to a dry DrySafe climate using the humidity slide control.



Find out more about BioFresh:
biofresh.liebherr.com

Food storage centres



Quality in every detail



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the appliance's net capacity).



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door.



Bio Fresh

BioFresh guarantees the perfect climate for extra long freshness. A temperature slightly above 0°C and ideal air humidity maintain the delicate aroma and appetising appearance of fruit and vegetables, meat, fish and milk products significantly longer than in a standard fridge. The **BioFresh-Plus** technology provides greater flexibility and control for ideal food storage conditions. With its independent electronic control system the temperature in the top compartment can be adjusted from -2°C (fish), to + 6°C (exotic fruits).



Find out more about BioFresh:
biofresh.liebherr.com



No Frost

The **NoFrost** system provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frostfree.



Find out more about NoFrost:
nofrost.liebherr.com



Ice Maker

The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

The features shown are model dependent; the description applies to the relevant model.

Side-by-Side fridge-freezers



121

SBSes 7165 PremiumPlus



Energy efficiency class: **A++**

Energy consumption year/24 hrs: 430/1.178 kWh

Max. Bordeaux bottles 0.75 l: 41

Total net capacity: 591 litre (Fridge: 476 litre including BioFresh compartment: 110 litre including wine compartment: 128 litre/Freezer compartment: 115 litre)

Noise output: 42 dB(A)

Climate rating: SN-ST

Door/side walls: Stainless steel with SmartSteel/stainless steel

Exterior dimensions in cm (h/w/d): 185.2/121/63

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh, wine and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- BioFresh-Plus
- 3 BioFresh-Safes on telescopic rails, of which 3 can be set variably to HydroSafe or DrySafe

Freezer compartment ********

- 5 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

Wine compartment

- 2 separately controllable temperature zones, which can be regulated between +5°C to +20°C
- Tinted insulated glass door with UV protection
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 4 shelves, of which 2 on telescopic rails and 2 foldable
- Partially-foldable wooden shelf on telescopic rails
- LED lighting permanently on, dimmable

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed

Special accessories (from page 136)

- 04, 06, 07, 10, 14, 17, 18



121

SBSes 7353 Premium



Energy efficiency class: **A++**¹

Energy consumption year/24 hrs: 383/1.048 kWh¹

Total net capacity: 661 litre (Fridge: 546 litre including BioFresh compartment: 155 litre/Freezer compartment: 115 litre)

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: Stainless steel with SmartSteel/stainless steel

Exterior dimensions in cm (h/w/d): 185.2/121/63¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- 2 GlassLine shelves in the BioFresh compartment, of which one is divided into two parts
- Bottle shelf, Champagne rack
- LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe
- 2 fruit and vegetable drawers on telescopic rails

Freezer compartment ********

- 5 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed

Special accessories (from page 136)

- 02, 04, 06, 07, 17, 18

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Side-by-Side fridge-freezers



SBSbs 7263 Premium



Energy efficiency class: $\langle A^{+}/A^{+} \rangle^1$

Energy consumption year / 24 hrs: 344 / 0.941 kWh¹

Total net capacity: 610 litre (Fridge: 358 litre including BioFresh compartment: 116 litre / Freezer compartment: 252 litre)

Noise output: 42 dB(A)

Climate rating: SN-T

Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to HydroSafe or DrySafe

Freezer compartment ********

- 9 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 1.5 kg
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed

Special accessories (from page 136)

- 02, 04, 05, 06, 07

SBSes 7263 Premium



Energy efficiency class: $\langle A^{+}/A^{+} \rangle^1$

Energy consumption year / 24 hrs: 441 / 1.207 kWh¹

Total net capacity: 610 litre (Fridge: 358 litre including BioFresh compartment: 116 litre / Freezer compartment: 252 litre)

Noise output: 42 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel / stainless steel

Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to HydroSafe or DrySafe

Freezer compartment ********

- 9 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 1.5 kg
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed

Special accessories (from page 136)

- 02, 04, 05, 06, 07, 17, 18

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Side-by-Side fridge-freezers



◀121▶

SBSes 7253 Premium



Energy efficiency class: $\langle A^{++}/A^{+}>$¹

Energy consumption year / 24 hrs: 378 / 1.033 kWh¹

Total net capacity: 615 litre (Fridge: 358 litre including BioFresh compartment: 116 litre / Freezer compartment: 257 litre)

Noise output: 42 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel / stainless steel

Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to HydroSafe or DrySafe

Freezer compartment E^{***}

- 8 drawers, VarioSpace
- LED lighting
- Temperature rise time: 43 h
- Freezing capacity in 24 hrs: 20 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed

Special accessories (from page 136)

- 02, 05, 06, 07, 17, 18



◀121▶

SBSef 7242 Comfort



Energy efficiency class: $\langle A^{++}/A^{+}>$¹

Energy consumption year / 24 hrs: 359 / 0.982 kWh¹

Total net capacity: 634 litre (Fridge: 381 litre / Freezer compartment: 253 litre)

Noise output: 43 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on telescopic rails

Freezer compartment E^{***}

- 8 drawers, VarioSpace
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 20 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal

Special accessories (from page 136)

- 02, 05, 06, 07

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail




The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



Bio Fresh

Both **BioFresh drawers** are mounted on **telescopic rails** which extend effortlessly providing a full view of your food, which is easily accessible. The lateral **LED lights** ensure perfect illumination of the drawers. The versatile glass/bottle shelves can be used depending on your personal preference.



No Frost

Ice Maker

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated **water filter** ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The **NoFrost** technology keeps the freezer constantly frostfree.



The interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. The elegant, high quality **GlassLine** interior is adaptable to suit individual requirements.

CBNes 6256
PremiumPlus



Energy efficiency class: **A++**
 Energy consumption year / 24 hrs: 322 / 0.881 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel / stainless steel
 Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment **E4*****

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.3 kg
- Ice cube reservoir 2.7 kg
- LED lighting
- Temperature rise time: 45 h
- Freezing capacity in 24 hrs: 11 kg

Key features

- HardLine
- Aluminium handles
- Front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 03, 06, 17, 18



Fridge-freezers



CBNPes 4858

Our fridge-freezers: an overview

Liebherr's extensive range of fridge-freezers offers the ideal solution for almost everyone - whatever your demands and needs are. Our fridge-freezers offer innovative features such as BioFresh or BioCool and NoFrost or SmartFrost. Once you have made your preferred choice, all of our appliances are available with a variety of fittings and come in various sizes and colours.



Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.

No Frost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean.

Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost: nofrost.liebherr.com



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



Bio Fresh

In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C. The **BioFresh-Plus technology** provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the top drawer to be lowered to -2°C for storing fish. Together with the DrySafe setting, fish is kept fresh even longer.



Find out more about BioFresh: biofresh.liebherr.com



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of toughened glass. The sectioned, slide-under glass shelf can be located to suite individual requirements.



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running roller tracks; its convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slide control.

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail




Ice Maker

The automatic **IceMaker** from Liebherr provides ice cubes for every occasion. Whether you fancy a quick drink or you're having a large party, the extra-large drawer holds an ample supply of ice cubes.



Duo Cooling

Accurate and independent temperature control of the fridge and freezer compartments is facilitated by **DuoCooling**: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug
2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor
4. Plinth fan with noise-damping
5. Condenser
6. Defrost water drain



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system. Appliances can be adapted to specific customer requirements using preset programmes, thereby ensuring optimal food storage.

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail



Soft Telescopic

The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



The high-performance **PowerCooling system** ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a homogeneous, high-quality lighting concept.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables accurate temperature settings.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles.



The automatic **SuperFrost function** makes freezing food simple and energy efficient. It rapidly lowers the temperature to -32°C to create the coldness levels required to preserve vitamins during freezing. The automatic **SuperCool function** lowers the refrigerator temperature to +2°C for a defined period of 3, 6, 9 or 12 hours, offering flexibility according to the amount of food stored.

The features shown are model dependent; the description applies to the relevant model.



The **BioFresh-Plus** technology provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the top drawer to be lowered to -2°C for storing fish. Together with the **DrySafe** setting, fish is kept fresh even longer. Exotic fruits find ideal storage conditions in the top adjustable safe at $+6^{\circ}\text{C}$ and a high level of humidity.



The PremiumPlus interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. At the same time the light columns provide freedom for rearranging the toughened glass shelves to suit your storage needs.



75

CBNPes 5167 PremiumPlus	Bio Fresh Plus	No Frost	A++	Duo Cooling	Ice Maker	Soft System	Smart Steel
Energy efficiency class: $\langle A^{++} \rangle^1$							
Energy consumption year/24 hrs: 304/0.832 kWh ¹							
Total net capacity: 411 litre (Fridge: 299 litre including BioFresh compartment: 99 litre/ Freezer compartment: 112 litre)							
Noise output: 41 dB(A)							
Climate rating: SN-T							
Door /side walls: Stainless steel with SmartSteel / stainless steel							
Exterior dimensions in cm (h/w/d): 202/75/63 ¹							

Controls

- Cursor controlled LCD display in-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- BioFresh-Plus
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ★★★★★

- 4 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.0 kg
- Ice cube reservoir 1.5 kg
- LED lighting
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 14 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 04, 06, 17, 18



The **LED ceiling light** creates a high-class ambience within the refrigerator. Its beautifully designed, space-efficient housing is centrally positioned to provide a delightfully even illumination.



75

CBNesf 5133 Comfort	Bio Fresh	No Frost	A++	Duo Cooling	Smart Steel
Energy efficiency class: $\langle A^{++} \rangle^1$					
Energy consumption year/24 hrs: 305/0.835 kWh ¹					
Total net capacity: 421 litre (Fridge: 306 litre including BioFresh compartment: 107 litre/ Freezer compartment: 115 litre)					
Noise output: 41 dB(A)					
Climate rating: SN-T					
Door /side walls: Stainless steel with SmartSteel / silver					
Exterior dimensions in cm (h/w/d): 202/75/63 ¹					

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment ★★★★★

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 30 h
- Freezing capacity in 24 hrs: 14 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06



The **NoFrost system** from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀60▶



◀60▶



◀60▶

CBNPes 3967
PremiumPlus

Bio Fresh Plus No Frost A++ Duo Cooling Ice Maker Soft System Smart Steel

Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 262 / 0.716 kWh¹
 Total net capacity: 321 litre (Fridge: 238 litre including BioFresh compartment: 80 litre / Freezer compartment: 83 litre)
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / stainless steel
 Exterior dimensions in cm (h/w/d): 201.1 / 60 / 63¹

CBNPbs 4858
Premium

Bio Fresh No Frost A+++ A-20% Duo Cooling Soft System Soft Telescopic Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 149 / 0.408 kWh¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5¹

CBNPgb 4855
Premium

Bio Fresh No Frost A+++ A-20% Duo Cooling Soft System Soft Telescopic Glass Edition

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 149 / 0.408 kWh¹
 Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment: 97 litre / Freezer compartment: 101 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Glass front black / silver
 Exterior dimensions in cm (h/w/d): 201 / 60 / 68.5¹

CBNef 4815
Comfort

Bio Fresh No Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year / 24 hrs: 186 / 0.507 kWh¹
 Total net capacity: 343 litre (Fridge: 242 litre including BioFresh compartment: 94 litre / Freezer compartment: 101 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5¹

Controls

- Cursor controlled LCD display in-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- BioFresh-Plus
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment **★★★★**

- 4 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 1.5 kg
- Temperature rise time: 25 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 04, 06, 07, 17, 18

Controls

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour / material options:
CBNPes 4858 in SmartSteel
CBNP 4858 in white

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray
- LED lighting
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- GlassEdition
- Recessed handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour / material options:
CBNPgw 4855 in Glass front white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour / material options:
CBNbs 4815 in BlackSteel
CBN 4815 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



CBPef 4815
Comfort

Bio Fresh Smart Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 147/0.401 kWh¹
 Total net capacity: 357 litre (Fridge: 242 litre including BioFresh compartment: 94 litre/Freezer compartment: 115 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 201/60/66.5¹

CBef 4815
Comfort

Bio Fresh Smart Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 183/0.499 kWh¹
 Total net capacity: 357 litre (Fridge: 242 litre including BioFresh compartment: 94 litre/Freezer compartment: 115 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 201/60/66.5¹

CBef 4315
Comfort

Bio Fresh Smart Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 175/0.478 kWh¹
 Total net capacity: 319 litre (Fridge: 204 litre including BioFresh compartment: 94 litre/Freezer compartment: 115 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

CNef 4815
Comfort

Bio Cool No Frost A+++ Duo Cooling Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 174/0.474 kWh¹
 Total net capacity: 361 litre (Fridge: 260 litre/Freezer compartment: 101 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 201/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 33 h
- Freezing capacity in 24 hrs: 13 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back transport castors at back
- Height-adjustable feet at front, reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 33 h
- Freezing capacity in 24 hrs: 13 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back transport castors at back
- Height-adjustable feet at front, reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour/material options:
CB 4815 in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 33 h
- Freezing capacity in 24 hrs: 13 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back transport castors at back
- Height-adjustable feet at front, reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour/material options:
CB 4315 in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features


- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back transport castors at back
- Height-adjustable feet at front, reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 01, 02, 06, 07, 10, 19, 20, 21

Colour/material options:
CN 4815 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀60▶



◀60▶



◀75▶

CNbs 4315
Comfort



Energy efficiency class: $\langle A^{+++}$¹
 Energy consumption year/24 hrs: 165/0.451 kWh¹
 Total net capacity: 321 litre (Fridge: 220 litre/Freezer compartment: 101 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

- | | |
|--|---|
| <p>Controls</p> <ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperCool (time restricted) · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic <p>Fridge compartment</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, Egg tray · 4 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 1 BioCool-Box on roller tracks <p>Freezer compartment ****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 24 h · Freezing capacity in 24 hrs: 16 kg · Safety glass fittings | <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening <p>Special accessories (from page 136)</p> <ul style="list-style-type: none"> · 01, 02, 06, 07, 10, 19, 20, 21 <p>Colour / material options:</p> <ul style="list-style-type: none"> · CNef 4315 with Stainless steel front · CN 4315 in white |
|--|---|


CPef 4815
Comfort



Energy efficiency class: $\langle A^{+++}$¹
 Energy consumption year/24 hrs: 137/0.375 kWh¹
 Total net capacity: 375 litre (Fridge: 260 litre/Freezer compartment: 115 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 201/60/66.5¹

- | | |
|--|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperCool (time restricted) · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic <p>Fridge compartment</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, Egg tray · 5 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 1 BioCool-Box on roller tracks <p>Freezer compartment ****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 33 h · Freezing capacity in 24 hrs: 13 kg · Safety glass fittings | <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening <p>Special accessories (from page 136)</p> <ul style="list-style-type: none"> · 01, 02, 06, 07, 10, 19, 20, 21 <p>Colour / material options:</p> <ul style="list-style-type: none"> · CP 4815 in white |
|--|--|

CP 4315
Comfort



Energy efficiency class: $\langle A^{+++}$¹
 Energy consumption year/24 hrs: 131/0.357 kWh¹
 Total net capacity: 335 litre (Fridge: 220 litre/Freezer compartment: 115 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

- | | |
|--|---|
| <p>Controls</p> <ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperCool (time restricted) · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic <p>Fridge compartment</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, Egg tray · 4 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 1 BioCool-Box on roller tracks <p>Freezer compartment ****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 33 h · Freezing capacity in 24 hrs: 13 kg · Safety glass fittings | <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Slimline handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening <p>Special accessories (from page 136)</p> <ul style="list-style-type: none"> · 01, 02, 06, 07, 10, 19, 20, 21 <p>Colour / material options:</p> <ul style="list-style-type: none"> · CPef 4315 with Stainless steel front |
|--|---|

CNesf 5113
Comfort



Energy efficiency class: $\langle A$¹
 Energy consumption year/24 hrs: 371/1.016 kWh
 Total net capacity: 453 litre (Fridge: 338 litre/Freezer compartment: 115 litre)
 Noise output: 42 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 202/75/63

- | | |
|---|--|
| <p>Controls</p> <ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · LED temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic <p>Fridge compartment</p> <ul style="list-style-type: none"> · PowerCooling · Comfort GlassLine storage shelf with bottle holder, Egg tray · 5 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 2 fruit and vegetable drawers on roller tracks <p>Freezer compartment ****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 30 h · Freezing capacity in 24 hrs: 14 kg · Safety glass fittings | <p>Key features</p> <ul style="list-style-type: none"> · SwingLine design · Stainless steel slimline handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging <p>Special accessories (from page 136)</p> <ul style="list-style-type: none"> · 02, 06 <p>Colour / material options:</p> <ul style="list-style-type: none"> · CN 5113 in white |
|---|--|

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀60▶



◀60▶



◀60▶

CNbs 4015
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 252 / 0.688 kWh¹
 Total net capacity: 356 litre (Fridge: 269 litre / Freezer compartment: 87 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h / w / d): 201.1 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **CNef 4015** with Stainless steel front
- **CN 4015** in white

CNef 3915
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 263 / 0.718 kWh¹
 Total net capacity: 340 litre (Fridge: 221 litre / Freezer compartment: 119 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 201.1 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **CNbs 3915** in BlackSteel

CN 3915
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 263 / 0.718 kWh¹
 Total net capacity: 340 litre (Fridge: 221 litre / Freezer compartment: 119 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 201.1 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

CNef 3515
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 237 / 0.648 kWh¹
 Total net capacity: 308 litre (Fridge: 221 litre / Freezer compartment: 87 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 181.7 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **CN 3515** in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀55▶



◀55▶



◀60▶

CNeF 3115
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 222 / 0.608 kWh¹
 Total net capacity: 260 litre (Fridge: 173 litre / Freezer compartment: 87 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 162.3 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:
CN 3115 in white

CNsI 3033
Comfort



Energy efficiency class: $\langle A \rangle$
 Energy consumption year / 24 hrs: 269 / 0.736 kWh
 Total net capacity: 272 litre (Fridge: 194 litre / Freezer compartment: 78 litre)
 Noise output: 42 dB(A)
 Climate rating: SN-ST
 Door / side walls: silver / silver
 Exterior dimensions in cm (h / w / d): 180 / 55 / 62.9

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

CUN 3033
Comfort



Energy efficiency class: $\langle A \rangle$
 Energy consumption year / 24 hrs: 270 / 0.738 kWh
 Total net capacity: 274 litre (Fridge: 196 litre / Freezer compartment: 78 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-ST
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 180 / 55 / 62.9

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge compartment
- Individually regulated cooling circuits: 1
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- SwingLine design
- Ergonomically designed bar handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Cef 4025
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 241 / 0.659 kWh¹
 Total net capacity: 357 litre (Fridge: 269 litre / Freezer compartment: 88 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 201.1 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 28 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:
C 4025 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Fridge-freezers



◀60▶



◀60▶



◀60▶

Cef 3825

Comfort

Smart Frost

A+++

Duo Cooling

Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year/24 hrs: 151/0.413 kWh¹

Total net capacity: 312 litre (Fridge: 224 litre/Freezer compartment: 88 litre)

Noise output: 38 dB(A)

Climate rating: SN-T

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 201.1/60/62.5¹

Cef 3525

Comfort

Smart Frost

A++

Duo Cooling

Smart Steel

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year/24 hrs: 226/0.618 kWh¹

Total net capacity: 309 litre (Fridge: 221 litre/Freezer compartment: 88 litre)

Noise output: 39 dB(A)

Climate rating: SN-T

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 181.7/60/62.5¹

Cbs 3425

Comfort

Smart Frost

A+++

Duo Cooling

Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year/24 hrs: 143/0.391 kWh¹

Total net capacity: 272 litre (Fridge: 184 litre/Freezer compartment: 88 litre)

Noise output: 38 dB(A)

Climate rating: SN-T

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 181.7/60/62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers

Freezer compartment **★ ★ ★ ★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 29 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **C 3825** in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers

Freezer compartment **★ ★ ★ ★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 28 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **C 3525** in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers

Freezer compartment **★ ★ ★ ★**

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 29 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 02, 06, 07

Colour / material options:

- **Cef 3425** with Stainless steel front
- **C 3425** in white



Liebherr's **BlackSteel** combines modern design with timeless elegance. The premium SmartSteel finish not only significantly reduces the visibility of fingerprints and is extremely easy to clean, but also offers a new level of scratch resistance.



Models in the Comfort range now feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort Glassline comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

The features shown are model dependent; the description applies to the relevant model.



Fridge-freezers



◀55▶



◀55▶



◀55▶

CUfr 3311



Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 210/0.575 kWh ¹
Total net capacity: 294 litre (Fridge: 210 litre/ Freezer compartment: 84 litre)
Noise output: 39 dB(A)
Climate rating: SN-ST
Door/side walls: FireRed/FireRed
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 27 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

CUwb 3311



Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 210/0.575 kWh ¹
Total net capacity: 294 litre (Fridge: 210 litre/ Freezer compartment: 84 litre)
Noise output: 39 dB(A)
Climate rating: SN-ST
Door/side walls: WaterBlue/WaterBlue
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 27 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

CUag 3311



Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 210/0.575 kWh ¹
Total net capacity: 294 litre (Fridge: 210 litre/ Freezer compartment: 84 litre)
Noise output: 39 dB(A)
Climate rating: SN-ST
Door/side walls: AvacadoGreen/AvacadoGreen
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 27 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀55▶



◀60▶



◀55▶



◀55▶

CUef 3311	Smart Frost	A ⁺⁺	Smart Steel
Energy efficiency class: $\langle A^+ \rangle^1$			
Energy consumption year/24 hrs: 210/0.575 kWh ¹			
Total net capacity: 294 litre (Fridge: 210 litre/Freezer compartment: 84 litre)			
Noise output: 39 dB(A)			
Climate rating: SN-ST			
Door/side walls: Stainless steel with SmartSteel/silver			
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹			

Controls
<ul style="list-style-type: none"> Mechanical control in interior, control dial Individually regulated cooling circuits: 1 CoolPlus function
Fridge compartment
<ul style="list-style-type: none"> Comfort GlassLine storage shelf with bottle holder, Egg tray 4 GlassLine storage shelves, of which one is divided into two parts Bottle shelf LED lighting 2 fruit and vegetable drawers
Freezer compartment ★★★★
<ul style="list-style-type: none"> 3 drawers, VarioSpace Ice cube tray Temperature rise time: 27 h Freezing capacity in 24 hrs: 4 kg Safety glass fittings
Key features
<ul style="list-style-type: none"> SwingLine design Stainless steel slimline handles with integrated opening mechanism Versatile installation due to front ventilation Height-adjustable feet at front Reversible door hinging
Special accessories (from page 136)
<ul style="list-style-type: none"> 02, 06

CU 2915	Smart Frost	A ⁺⁺
Comfort		
Energy efficiency class: $\langle A^+ \rangle^1$		
Energy consumption year/24 hrs: 196/0.535 kWh ¹		
Total net capacity: 277 litre (Fridge: 222 litre/Freezer compartment: 55 litre)		
Noise output: 39 dB(A)		
Climate rating: SN-ST		
Door/side walls: white/white		
Exterior dimensions in cm (h/w/d): 162.3/60/62.5 ¹		

Controls
<ul style="list-style-type: none"> 2.4" TFT-monochrome display behind-the-door, touch electronic Digital temperature display for fridge compartment Individually regulated cooling circuits: 1 Automatic SuperCool (time restricted) Automatic SuperFrost, time-controlled Door alarm: visual and acoustic
Fridge compartment
<ul style="list-style-type: none"> Comfort GlassLine storage shelf with bottle holder, Egg tray 3 GlassLine storage shelves, of which one is divided into two parts Bottle shelf LED ceiling lighting 2 fruit and vegetable drawers
Freezer compartment ★★★★
<ul style="list-style-type: none"> 2 drawers, VarioSpace Ice cube tray Temperature rise time: 23 h Freezing capacity in 24 hrs: 6 kg Safety glass fittings
Key features
<ul style="list-style-type: none"> HardLine Slimline handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles, front and at back Height-adjustable feet at front, transport castors at back Reversible door hinging Replaceable door seal
Special accessories (from page 136)
<ul style="list-style-type: none"> 02, 06, 07

CUef 2811	Smart Frost	A ⁺⁺	Smart Steel
Energy efficiency class: $\langle A^+ \rangle^1$			
Energy consumption year/24 hrs: 191/0.523 kWh ¹			
Total net capacity: 263 litre (Fridge: 210 litre/Freezer compartment: 53 litre)			
Noise output: 39 dB(A)			
Climate rating: SN-ST			
Door/side walls: Stainless steel with SmartSteel/silver			
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹			

Controls
<ul style="list-style-type: none"> Mechanical control in interior, control dial Individually regulated cooling circuits: 1 CoolPlus function
Fridge compartment
<ul style="list-style-type: none"> Comfort GlassLine storage shelf with bottle holder, Egg tray 4 GlassLine storage shelves, of which one is divided into two parts Bottle shelf LED lighting 2 fruit and vegetable drawers
Freezer compartment ★★★★
<ul style="list-style-type: none"> 2 drawers, VarioSpace Ice cube tray Temperature rise time: 25 h Freezing capacity in 24 hrs: 4 kg Safety glass fittings
Key features
<ul style="list-style-type: none"> SwingLine design Stainless steel slimline handles with integrated opening mechanism Versatile installation due to front ventilation Height-adjustable feet at front Reversible door hinging
Special accessories (from page 136)
<ul style="list-style-type: none"> 02, 06
Colour/material options:
<ul style="list-style-type: none"> CUsl 2811 in silver CU 2811 in white

CU 2311	Smart Frost	A ⁺⁺
Energy efficiency class: $\langle A^+ \rangle^1$		
Energy consumption year/24 hrs: 176/0.481 kWh ¹		
Total net capacity: 208 litre (Fridge: 155 litre/Freezer compartment: 53 litre)		
Noise output: 39 dB(A)		
Climate rating: SN-ST		
Door/side walls: white/white		
Exterior dimensions in cm (h/w/d): 137.2/55/63 ¹		

Controls
<ul style="list-style-type: none"> Mechanical control in interior, control dial Individually regulated cooling circuits: 1 CoolPlus function
Fridge compartment
<ul style="list-style-type: none"> Comfort GlassLine storage shelf with bottle holder, Egg tray 3 GlassLine storage shelves, of which one is divided into two parts LED lighting 2 fruit and vegetable drawers
Freezer compartment ★★★★
<ul style="list-style-type: none"> 2 drawers, VarioSpace Ice cube tray Temperature rise time: 25 h Freezing capacity in 24 hrs: 4 kg Safety glass fittings
Key features
<ul style="list-style-type: none"> SwingLine design Ergonomically designed bar handles Versatile installation due to front ventilation Height-adjustable feet at front Reversible door hinging
Special accessories (from page 136)
<ul style="list-style-type: none"> 02, 06
Colour/material options:
<ul style="list-style-type: none"> CUsl 2311 in silver

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



CTNef 5215

Central Power Cooling



With our ingenious **Central-PowerCooling** technology, the refrigeration process is faster and more controlled. Cold air produced in the freezer compartment passes through air valves into the refrigerator compartment. Two temperature sensors regulate the procedure and ensure that the required refrigeration temperature is precisely maintained throughout the entire refrigerator compartment.

Bio Cool



The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running roller tracks; it's convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slide control.



Stylish **GlassLine safety glass fittings** add the finishing touch to the high-quality interior design. These elegant satin-finished glass shelves, with high-quality stainless steel trims, are scratch resistant and easy to clean. Their generous capacity offers plenty of space to store a wide range of food items. The interior of the refrigerator door is furnished with Glassline shelves, for yet another aesthetic accent to the overall design.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables accurate temperature settings.



◀70▶



◀75▶



◀60▶



◀60▶

CTNef 5215
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year/24 hrs: 270/0.739 kWh¹
 Total net capacity: 418 litre (Fridge: 332 litre/Freezer compartment: 86 litre)
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185.2/69.7/76¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Individually regulated cooling circuits: 1
- Automatic SuperCool
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Central-PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment **★★★★**

- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings
- Door rack

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Special accessories (from page 136)

- 06

Colour / material options:
CTN 5215 in white

CTNes 4753
Premium



Energy efficiency class: $\langle A^+ \rangle$
 Energy consumption year/24 hrs: 339/0.928 kWh
 Total net capacity: 413 litre (Fridge: 329 litre/Freezer compartment: 84 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/stainless steel
 Exterior dimensions in cm (h/w/d): 186/75/63

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Individually regulated cooling circuits: 2
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment **★★★★**

- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 17, 18

CTNesf 3663
Premium



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year/24 hrs: 223/0.610 kWh¹
 Total net capacity: 306 litre (Fridge: 246 litre/Freezer compartment: 60 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 191.1/60/63¹

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Individually regulated cooling circuits: 2
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 1 spacious fruit and vegetable drawer on roller tracks

Freezer compartment **★★★★**

- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour / material options:
CTN 3663 in white

CTN 3223
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year/24 hrs: 213/0.582 kWh¹
 Total net capacity: 273 litre (Fridge: 213 litre/Freezer compartment: 60 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 176.1/60/63¹

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Individually regulated cooling circuits: 2
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment **★★★★**

- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour / material options:
CTNesf 3223 with Stainless steel front

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀60▶



◀55▶



◀55▶



◀55▶

CTPesf 3316
Comfort



Energy efficiency class: $\langle A^{++} \rangle$ ¹
 Energy consumption year/24 hrs: 211/0.577 kWh ¹
 Total net capacity: 307 litre (Fridge: 232 litre/Freezer compartment: 75 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-ST
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 176.1/60/63 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge compartment
- Individually regulated cooling circuits: 1
- Automatic SuperFrost, time-controlled

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment $\langle **** \rangle$

- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour/material options:

CTP 3316 in white

CTPesf 3016
Comfort



Energy efficiency class: $\langle A^{++} \rangle$ ¹
 Energy consumption year/24 hrs: 198/0.541 kWh ¹
 Total net capacity: 275 litre (Fridge: 212 litre/Freezer compartment: 63 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-ST
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 161.1/60/63 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge compartment
- Individually regulated cooling circuits: 1
- Automatic SuperFrost, time-controlled

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment $\langle **** \rangle$

- Ice cube tray
- Temperature rise time: 22 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging


Special accessories (from page 136)

- 02, 06

Colour/material options:

CTP 3016 in white

CTP 2921
Comfort



Energy efficiency class: $\langle A^{++} \rangle$ ¹
 Energy consumption year/24 hrs: 201/0.549 kWh ¹
 Total net capacity: 268 litre (Fridge: 216 litre/
 Freezer compartment: 52 litre)
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 157.1/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment $\langle **** \rangle$

- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour/material options:

CTPsl 2921 in silver

CTPsl 2521
Comfort



Energy efficiency class: $\langle A^{++} \rangle$ ¹
 Energy consumption year/24 hrs: 187/0.510 kWh ¹
 Total net capacity: 231 litre (Fridge: 187 litre/
 Freezer compartment: 44 litre)
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: silver/silver
 Exterior dimensions in cm (h/w/d): 140.1/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment $\langle **** \rangle$

- Ice cube tray
- Temperature rise time: 22 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour/material options:

CTPsl 2521 in white

CTP 2121
Comfort



Energy efficiency class: $\langle A^{++} \rangle$ ¹
 Energy consumption year/24 hrs: 176/0.480 kWh ¹
 Total net capacity: 195 litre (Fridge: 151 litre/
 Freezer compartment: 44 litre)
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 124.1/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment $\langle **** \rangle$

- Ice cube tray
- Temperature rise time: 22 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 02, 06

Colour/material options:

CTPsl 2121 in silver

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Fridges



KBPgw 4354

Our fridges: an overview

Liebherr fridges excel with their impressive freshness technology. The range on offer extends from models featuring a classic vegetable compartment, to BioCool models with an adjustable humidity compartment, all the way to BioFresh appliances, which deliver the longest-lasting freshness. Whatever you're looking for, you're sure to find just the right fridge to meet your needs and requirements within Liebherr's comprehensive range – be it an upright, under counter or counter top appliance.

Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately maintained at around 0°C.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.

Fridges



**Bio
Fresh**

from page 70



**Bio
Cool**

from page 76



from page 78

Under counter fridges



from page 82

Quality in every detail



Bio Fresh

The fresher your food, the better it is for a healthy diet. **BioFresh safes**, sited on telescopic rails, guarantee the perfect environment for greater freshness. When stored at a temperature of just over 0°C and at just the right humidity level, fruit and vegetables, fish, meat and dairy products all retain their vitamins, delicate flavours and appetising appearance for far longer than in a conventional fridge compartment.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. A door contact switch turns off the fan when the door is opened, saving energy.



Soft System

The **SoftSystem** integrated in the door cushions the movement when the door is closed and ensures gentle closing even when the inside of the door is fully loaded.



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail



The **LED rear wall lighting** is integrated into the rear section of the horizontal dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the Fridge compartment, from top to bottom and provide high-quality illumination.



The **replaceable door seal** optimally supports safe food storage. It is designed to match the appliance door or housing colour and can be easily inserted, cleaned or replaced, ensuring that spotless hygiene standards can be consistently met.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The sectioned, slide-under glass shelf can be located at different heights as required.



SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



The **versatile bottle shelf** is an innovative feature in all BioFresh Premium models. It can be positioned above or below the glass shelf to suite individual requirements.

The features shown are model dependent; the description applies to the relevant model.



Quality in every detail



GlassEdition appliances have a **recessed handle with integrated opening mechanism** to the side of the door casing, which provides convenient and easy door opening. Being flush integrated, as opposed to protruding forwards, this handle concept is perfect for contemporary, hand-free kitchens.



The **4-star freezer** compartment is designed to freeze fresh food and store it for long periods. Temperatures of -18°C and lower ensure that nutritional content is preserved during storage.

KBPeS 4354
Premium

Bio Fresh A+++ A-20% Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 128/0.350 kWh¹
 Total net capacity: 338 litre (Fridge: 314 litre including BioFresh compartment: 133 litre/
 Freezer compartment: 24 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBPgb 4354
Premium

Bio Fresh A+++ A-20% Soft System Soft Telescopic Glass Edition

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 128/0.350 kWh¹
 Total net capacity: 338 litre (Fridge: 314 litre including BioFresh compartment: 133 litre/
 Freezer compartment: 24 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door/side walls: Glass front black/silver
 Exterior dimensions in cm (h/w/d): 185/60/68.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 06, 10, 19, 20, 21

Colour / material options: KBP 4354 in white

Freezer compartment ****

- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 2 kg

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Recessed handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 06, 10, 19, 20, 21

Colour / material options: KBPgw 4354 in Glass front white

Freezer compartment ****

- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 2 kg



The interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance.



Soft Telescopic

BioFresh safes with **SoftTelescopic** feature a convenient self-retracting, soft closing mechanism to guarantee practical and reliable everyday use. The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide optimal illumination in the BioFresh drawers and guarantee that the stored food is clearly visible.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

The features shown are model dependent; the description applies to the relevant model.



KBes 4350
Premium

Bio Fresh A+++ Soft System Soft Telescopic Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 90/0.244 kWh¹
 Total net capacity: 367 litre (Fridge: 367 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBbs 4350
Premium

Bio Fresh A+++ Soft System Soft Telescopic Black Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 90/0.244 kWh¹
 Total net capacity: 367 litre (Fridge: 367 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBef 4310
Comfort

Bio Fresh A+++ Smart Steel

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 90/0.244 kWh¹
 Total net capacity: 366 litre (Fridge: 366 litre including BioFresh compartment: 133 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KB 3750
Premium

Bio Fresh A+++ Soft System Soft Telescopic

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 87/0.236 kWh¹
 Total net capacity: 318 litre (Fridge: 318 litre including BioFresh compartment: 133 litre)
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 165/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 10, 19, 20, 21

Colour / material options:

KB 4350 in white

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 10, 19, 20, 21

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 10, 19, 20, 21

Colour / material options:

KB 4310 in white

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe

Special accessories (from page 136)

- 01, 02, 10, 19, 20, 21

Colour / material options:

KBes 3750 in SmartSteel

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



B 2850


BioFresh fridge



BioFresh drawers located on roller tracks, guarantee the perfect environment for greater freshness. When stored at a temperature of just over 0°C and when the correct humidity level is set, fruit and vegetables, fish, meat and dairy products all retain their vitamins, delicate flavours and appetising appearance for far longer than in a conventional fridge compartment.



The **SoftSystem** integrated in the door cushions the movement when the door is closed and ensures gentle closing.



B 2850
Premium

Bio Fresh A+++ Soft System

Energy efficiency class: **A+++**¹
 Energy consumption year /24 hrs: 77 /0.210 kWh¹
 Total net capacity: 157 litre
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door /side walls: white /white
 Exterior dimensions in cm (h/w/d): 125/60/66.5¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic

- Fridge and BioFresh compartments**
- Ventilator
 - LED lighting
 - 5 BioFresh-Safes on roller tracks, adjustable from HydroSafe to DrySafe

- Key features**
- HardLine
 - Slimline handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening

- Special accessories (from page 136)**
- 21

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



KPef 4350
Premium

Bio Cool A+++ Soft System Telescopic Rails Smart Steel

Energy efficiency class: $\lt; A^{+++}$¹
 Energy consumption year / 24 hrs: 63 / 0.171 kWh¹
 Total net capacity: 390 litre
 Noise output: 37 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display
 - Automatic SuperCool (time restricted)
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
 - 6 GlassLine storage shelves, of which one is divided into two parts
 - VarioSafe
 - Bottle shelf
 - LED ceiling lighting with dimmer function
 - 2 BioCool-Boxes on telescopic rails
- Key features**
- HardLine
 - Aluminium handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Special accessories (from page 136)**
- 01, 02, 10, 19, 20, 21
- Colour / material options:**
K 4310 with Stainless steel front

K 4310
Comfort

Bio Cool A+++ Telescopic Rails

Energy efficiency class: $\lt; A^{+++}$¹
 Energy consumption year / 24 hrs: 78 / 0.212 kWh¹
 Total net capacity: 390 litre
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5¹

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
 - Digital temperature display
 - Automatic SuperCool (time restricted)
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
 - Comfort GlassLine storage shelf with bottle holder, Egg tray
 - 6 GlassLine storage shelves, of which one is divided into two parts
 - Bottle shelf
 - LED ceiling lighting
 - 2 BioCool-Boxes on telescopic rails
- Key features**
- HardLine
 - Slimline handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Special accessories (from page 136)**
- 01, 02, 10, 19, 20, 21
- Colour / material options:**
K 4310 with Stainless steel front

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it's convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slide control.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated charcoal filter that is integrated into the fan purifies circulating air and quickly traps odours.

Kef 3710
Comfort

Bio Cool A+++ Telescopic Rails Smart Steel

Energy efficiency class: $\lt; A^{+++}$¹
 Energy consumption year / 24 hrs: 75 / 0.204 kWh¹
 Total net capacity: 342 litre
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5¹

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
 - Digital temperature display
 - Automatic SuperCool (time restricted)
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
 - Comfort GlassLine storage shelf with bottle holder, Egg tray
 - 6 GlassLine storage shelves, of which one is divided into two parts
 - Bottle shelf
 - LED ceiling lighting
 - 1 BioCool-Box on telescopic rails
- Key features**
- HardLine
 - Aluminium handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Special accessories (from page 136)**
- 01, 02, 10, 19, 20, 21
- Colour / material options:**
K 3710 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀55▶



◀60▶



◀55▶

Ksl 3130
Comfort



Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year / 24 hrs: 109/0.296 kWh¹
 Total net capacity: 297 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door / side walls: silver / silver
 Exterior dimensions in cm (h/w/d): 144.7/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02

Colour / material options:

K 3130 in white

K 2814
Comfort



Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year / 24 hrs: 178/0.485 kWh¹
 Total net capacity: 250 litre (Fridge: 229 litre / Freezer compartment: 21 litre)
 Noise output: 40 dB(A)
 Climate rating: SN-ST
 Door / side walls: white / white
 Exterior dimensions in cm (h/w/d): 140.2/55/63¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02

Colour / material options:

Ksl 2814 in silver

Ksl 2630
Comfort



Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year / 24 hrs: 104/0.283 kWh¹
 Total net capacity: 248 litre
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door / side walls: silver / silver
 Exterior dimensions in cm (h/w/d): 125/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02

Colour / material options:

K 2630 in white

K 2330
Comfort



Energy efficiency class: $\langle A \rangle$
 Energy consumption year / 24 hrs: 126/0.344 kWh
 Total net capacity: 213 litre
 Noise output: 40 dB(A)
 Climate rating: SN-ST
 Door / side walls: white / white
 Exterior dimensions in cm (h/w/d): 117.5/55/63

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 02

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



The elegant and precise **MagicEye** control with its digital temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperCool** function lowers the refrigerator temperature to +2°C. It is perfect for quickly cooling freshly stored food.



You can freeze fresh food and store frozen food for long periods in appliances with the **4-star freezer compartment**. Temperatures of -18°C and lower ensure food is stored with all the vital vitamins and minerals preserved.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The sectioned, slide-under glass shelf lends itself to versatile use as it can be inserted at different heights, as required.



The **slimline door handle** is aesthetically pleasing and ergonomically designed for ease of opening. Under counter fridges with manual controls can be further reduced in height by **removing the top** of the fridge.



Ergonomically designed, the extra deep transparent **vegetable compartments** are easy-to-clean and provide ample storage for fruit and vegetables.



Premium GlassLine door shelves with stainless steel trim. Elegant s/steel bars help retain taller bottles and jars.

The features shown are model dependent; the description applies to the relevant model.

Under counter fridges



◀60▶



◀60▶



◀60▶



◀60▶



◀55▶

TP 1764

Premium

A+++

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year / 24 hrs: 99 / 0.270 kWh¹

Total net capacity: 136 litre (Fridge: 118 litre /

Freezer compartment: 18 litre)

Noise output: 38 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 85 / 60.1 / 62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment *********

- Ice cube tray
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

TPesf 1714

Comfort

A++

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year / 24 hrs: 146 / 0.399 kWh¹

Total net capacity: 143 litre (Fridge: 125 litre /

Freezer compartment: 18 litre)

Noise output: 41 dB(A)

Climate rating: SN-ST

Door / side walls: Stainless steel / silver

Exterior dimensions in cm (h/w/d): 85 / 60.1 / 61¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- Interior lighting
- 2 fruit and vegetable drawers

Freezer compartment *********

- Ice cube tray
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 17, 18

TP 1760

Premium

A+++

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year / 24 hrs: 64 / 0.173 kWh¹

Total net capacity: 154 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 85 / 60.1 / 62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperCool

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

TPesf 1710

Comfort

A++

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year / 24 hrs: 93 / 0.254 kWh¹

Total net capacity: 145 litre

Noise output: 39 dB(A)

Climate rating: SN-ST

Door / side walls: Stainless steel / silver

Exterior dimensions in cm (h/w/d): 85 / 60.1 / 60.8¹

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Interior lighting
- 2 fruit and vegetable drawers

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 17, 18

TP 1434

Comfort

A+++

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year / 24 hrs: 93 / 0.253 kWh¹

Total net capacity: 122 litre (Fridge: 107 litre / Freezer compartment: 15 litre)

Noise output: 38 dB(A)

Climate rating: SN-ST

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 85 / 55.4 / 62.3¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment *********

- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀55▶



◀50▶



◀55▶



◀55▶



◀50▶



◀50▶

TP 1414
Comfort **A⁺⁺**

Energy efficiency class: **A⁺⁺** ¹
 Energy consumption year/24 hrs: 139/0.380 kWh ¹
 Total net capacity: 122 litre (Fridge: 107 litre/
 Freezer compartment: 15 litre)
 Noise output: 41 dB(A)
 Climate rating: SN-ST
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 85/55.4/62.3 ¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Tsl 1414
Comfort **A⁺** **Silver**

Energy efficiency class: **A⁺**
 Energy consumption year/24 hrs: 177/0.484 kWh
 Total net capacity: 122 litre (Fridge: 107 litre/
 Freezer compartment: 15 litre)
 Noise output: 41 dB(A)
 Climate rating: SN-ST
 Door/side walls: silver/silver
 Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- SwingDesign
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:

T 1414 in white

TP 1410
Comfort **A⁺⁺**

Energy efficiency class: **A⁺⁺** ¹
 Energy consumption year/24 hrs: 92/0.252 kWh ¹
 Total net capacity: 136 litre
 Noise output: 39 dB(A)
 Climate rating: SN-ST
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 85/55.4/62.3 ¹

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

TX 1021
Comfort **A⁺**

Energy efficiency class: **A⁺**
 Energy consumption year/24 hrs: 113/0.309 kWh
 Total net capacity: 86 litre (Fridge: 86 litre of which
 0-star freezer: 6 litre)
 Noise output: 39 dB(A)
 Climate rating: SN-ST
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 63/55.4/62.4

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 1 GlassLine storage shelf
- Interior lighting
- 2 fruit and vegetable drawers
- 0-star compartment (0°C to -6°C)

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Height-adjustable feet at front
- Reversible door hinging

T 1410
Comfort **A⁺**

Energy efficiency class: **A⁺**
 Energy consumption year/24 hrs: 118/0.321 kWh
 Total net capacity: 136 litre
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Tb 1400
Comfort **A⁺**

Energy efficiency class: **A⁺**
 Energy consumption year/24 hrs: 118/0.321 kWh
 Total net capacity: 136 litre
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Door/side walls: black/black
 Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Plastics, Egg tray
- 4 GlassLine storage shelves
- Interior lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Freezers



GNP 4355



Our freezers: an overview

Featuring a choice of NoFrost, SmartFrost or StopFrost – Liebherr freezers offer maximum convenience. With tall, under counter and chest freezers available – Liebherr has just the right appliance whatever your requirements. Choose from a variety of sizes and select your preferred fittings.

No Frost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean.

Stop Frost

Frosting over of the freezer and frozen food is reduced, reducing the number of times you need to defrost the freezer. **StopFrost** prevents a vacuum from building up, ensuring the lid opens easily.

Tall freezers



No Frost

from page 94



Smart Frost

from page 102

Under counter freezers



No Frost

from page 106



Smart Frost

from page 108

Chest freezers



Stop Frost

from page 110

Quality in every detail



No Frost

The **NoFrost system** from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.



Smart Frost

With the **SmartFrost technology**, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



The **status indicator** is discretely integrated into the appliance door, allowing for quick and easy assessment of the appliance status, even if the door is closed. A blue light indicates that the appliance is working properly. In the case of any other status, a red light and an audible tone are emitted.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables individual temperature setting.



LED

Energy-efficient, powerful, long-life and environmentally friendly **LEDs** are integrated into the underside of the freezer interior to illuminate the contents of the drawers when they are opened. As soon as the door is opened, the LED lighting brightens, conveniently displaying the contents of the drawers.



So that food can be conveniently accessed with minimal effort, even if the drawers are fully stocked, all BluPerformance freezer **drawers** are sited on smooth-running **roller tracks**. For convenient removal and storage of food, the top drawer tilts slightly downwards when opened – an especially helpful feature in taller appliances. The position and size of the bottom drawer make it ideal for storing ice cream, herbs or other small items.

The features shown are model dependent; the description applies to the relevant model.

Quality in every detail



The automatic **SuperFrost** function makes freezing food simple and energy efficient. It rapidly lowers the temperature to -32°C to create the temperature levels required to preserve vitamins and enhance the flavour and texture of the food when consumed.




The elegant, high precision **MagicEye control** unit featuring the innovative Touch-electronic control concept ensures that the selected temperatures are kept to the exact temperature required. The Touch-electronic panel makes the control of all the functions easy and convenient to use.



**Telescopic
Rails**

The transparent freezer drawers on **telescopic rails** are easy to access and use even when filled with heavy contents. They ensure both great visibility and optimum storage. The **FrostSafe** fully enclosed drawers prevent cold air from escaping, thereby contributing to energy-efficient operation.



BLU
Performance

BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug
2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor
4. Plinth fan with noise-damping
5. Condenser
6. Defrost water drain



The freezer drawers in the BluPerformance appliances can be easily opened on **roller tracks**. The drawers and intervening glass shelves can be removed to create **VarioSpace** - a no-fuss system for quickly creating extra storage space.



If you are not using the entire freezer space, unused drawers can be switched off with the optional **Vario Energy-Saving Panel**. Energy consumption can then be reduced again by up to 50%.

The features shown are model dependent; the description applies to the relevant model.

Freezers



◀70▶



◀70▶



◀70▶



◀70▶

GNP 4113

Comfort

No Frost

A+++

LED

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year/24 hrs: 195/0.534 kWh¹

Total net capacity: 345 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 194.7/69.7/75¹

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 8 drawers, VarioSpace
- LED lighting
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 26 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

GN 4113

Comfort

No Frost

A++

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year/24 hrs: 293/0.802 kWh¹

Total net capacity: 345 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 194.7/69.7/75¹

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 8 drawers, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 26 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

GNP 3613

Comfort

No Frost

A+++

LED

Energy efficiency class: $\langle A^{+++} \rangle^1$

Energy consumption year/24 hrs: 179/0.488 kWh¹

Total net capacity: 299 litre

Noise output: 38 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 175.1/69.7/75¹

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 7 drawers, VarioSpace
- LED lighting
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 24 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

GN 3613

Comfort

No Frost

A++

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year/24 hrs: 268/0.733 kWh¹

Total net capacity: 299 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 175.1/69.7/75¹

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 7 drawers, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 24 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



GNP 3113
Comfort

No Frost A+++ LED

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 162/0.442 kWh¹
 Total net capacity: 253 litre
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 155.5/69.7/75¹

GN 3113
Comfort

No Frost A++

Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year/24 hrs: 243/0.664 kWh¹
 Total net capacity: 253 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 155.5/69.7/75¹

GNP 2613
Comfort

No Frost A+++ LED

Energy efficiency class: $\langle A^{+++} \rangle^1$
 Energy consumption year/24 hrs: 145/0.395 kWh¹
 Total net capacity: 206 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 135.9/69.7/75¹

GN 2613
Comfort

No Frost A++

Energy efficiency class: $\langle A^{++} \rangle^1$
 Energy consumption year/24 hrs: 217/0.593 kWh¹
 Total net capacity: 206 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 135.9/69.7/75¹

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 6 drawers, VarioSpace
- LED lighting
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 22 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 6 drawers, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 22 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 5 drawers, VarioSpace
- LED lighting
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 20 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

Controls

- MagicEye on front, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 5 drawers, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 20 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Freezers



◀60▶



◀60▶



◀60▶



◀60▶

SGNes 3011 Premium	No Frost	A ⁺	LED	Ice Maker	Smart Steel
Energy efficiency class: $\langle A \rangle^1$					
Energy consumption year/24 hrs: 309/0.844 kWh					
Total net capacity: 252 litre					
Noise output: 42 dB(A)					
Climate rating: SN-T					
Door/side walls: Stainless steel with SmartSteel/stainless steel					
Exterior dimensions in cm (h/w/d): 185.2/60/63					

Controls
<ul style="list-style-type: none"> · MagicEye behind-the-door, touch electronic · Digital temperature display · Automatic SuperFrost, quantity-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic
Freezer compartment ★★★★
<ul style="list-style-type: none"> · 9 drawers, of which 1 herb and berry tray, VarioSpace · IceMaker with fixed 3/4" water connection · Ice cube production in 24 hrs: 0.8 kg · Ice cube reservoir 1.5 kg · LED lighting · Temperature rise time: 24 h · Freezing capacity in 24 hrs: 18 kg · 2 Cold storage accumulators · Safety glass fittings
Key features
<ul style="list-style-type: none"> · SwingLine design · Stainless steel slimline handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front, transport castors at back · Reversible door hinge, left
Special accessories (from page 136)
· 05, 06, 07, 17, 18

GNPes 4355 Premium	No Frost	A ⁺⁺⁺	LED	Smart Steel
Energy efficiency class: $\langle A^{+++} \rangle^1$				
Energy consumption year/24 hrs: 168/0.460 kWh ¹				
Total net capacity: 270 litre				
Noise output: 38 dB(A)				
Climate rating: SN-T				
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel				
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹				

Controls
<ul style="list-style-type: none"> · 2.4" TFT-colour display behind-the-door, touch electronic · Digital temperature display · Automatic SuperFrost, quantity-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic
Freezer compartment ★★★★
<ul style="list-style-type: none"> · 8 drawers, of which 7 set on roller tracks, VarioSpace · Ice cube tray · LED lighting · Status indicator · Temperature rise time: 20 h · Freezing capacity in 24 hrs: 18 kg · 2 Cold storage accumulators · Safety glass fittings
Key features
<ul style="list-style-type: none"> · HardLine · Aluminium handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening
Special accessories (from page 136)
· 05, 06, 07, 21
Colour/material options:
GNP 4355 in white

GNP 3013 Comfort	No Frost	A ⁺⁺
Energy efficiency class: $\langle A^{++} \rangle^1$		
Energy consumption year/24 hrs: 245/0.670 kWh ¹		
Total net capacity: 257 litre		
Noise output: 42 dB(A)		
Climate rating: SN-T		
Door/side walls: white/white		
Exterior dimensions in cm (h/w/d): 184.1/60/63 ¹		

Controls
<ul style="list-style-type: none"> · MagicEye on front, key electronic · Graphic temperature display · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic
Freezer compartment ★★★★
<ul style="list-style-type: none"> · 8 drawers, VarioSpace · Temperature rise time: 24 h · Freezing capacity in 24 hrs: 20 kg · Safety glass fittings
Key features
<ul style="list-style-type: none"> · SwingLine design · Slimline handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging
Special accessories (from page 136)
· 05, 06, 07

GNP 2713 Comfort	No Frost	A ⁺⁺
Energy efficiency class: $\langle A^{++} \rangle^1$		
Energy consumption year/24 hrs: 225/0.616 kWh ¹		
Total net capacity: 221 litre		
Noise output: 42 dB(A)		
Climate rating: SN-T		
Door/side walls: white/white		
Exterior dimensions in cm (h/w/d): 164.4/60/63 ¹		

Controls
<ul style="list-style-type: none"> · MagicEye on front, key electronic · Graphic temperature display · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic
Freezer compartment ★★★★
<ul style="list-style-type: none"> · 7 drawers, of which 1 herb and berry tray, VarioSpace · Temperature rise time: 24 h · Freezing capacity in 24 hrs: 18 kg · Safety glass fittings
Key features
<ul style="list-style-type: none"> · SwingLine design · Slimline handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging
Special accessories (from page 136)
· 05, 06, 07

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



GNPef 2313
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 206 / 0.563 kWh¹
 Total net capacity: 185 litre
 Noise output: 42 dB(A)
 Climate rating: SN-T
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 6 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06, 07

Colour / material options:

GNP 2313 in white

GNP 1913
Comfort



Energy efficiency class: $\langle A^+ \rangle^1$
 Energy consumption year / 24 hrs: 186 / 0.508 kWh¹
 Total net capacity: 149 litre
 Noise output: 42 dB(A)
 Climate rating: SN-T
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 125 / 60 / 63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 5 drawers, of which 1 herb and berry tray, VarioSpace
- Ice cube tray
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 15 kg
- Safety glass fittings

Key features

- SwingDesign
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06, 07

GN 1923
Comfort



Energy efficiency class: $\langle A \rangle$
 Energy consumption year / 24 hrs: 237 / 0.647 kWh
 Total net capacity: 149 litre
 Noise output: 42 dB(A)
 Climate rating: SN-T
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 125 / 60 / 63

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 5 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 15 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 05, 06, 07

FrostSafe. The removable, extra-deep drawers with transparent front are fully enclosed all the way round. They provide a perfect view of the contents and the best storage conditions for the frozen food. Freezer drawers and toughened glass shelves can be removed.

VarioSpace - the practical storage solution for larger produce.



The elegant and precise **MagicEye control** with its graphic temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function keys makes for easy and convenient use. The automatic **SuperFrost function** quickly reduces the temperature to freeze your food while preserving the vitamins.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Freezers




◀70▶



◀70▶



◀70▶



◀60▶

G 4013

Comfort

Smart Frost

A⁺⁺

Energy efficiency class: $\langle A^+ \rangle^1$

Energy consumption year/24 hrs: 286/0.783 kWh¹

Total net capacity: 399 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 194.7/69.7/75¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 9 drawers, of which 1 herb and berry tray, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 26 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06

G 3513

Comfort

Smart Frost

A⁺⁺

Energy efficiency class: $\langle A^+ \rangle^1$

Energy consumption year/24 hrs: 264/0.722 kWh¹

Total net capacity: 350 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 175.1/69.7/75¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 25 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06

G 3013

Comfort

Smart Frost

A⁺⁺

Energy efficiency class: $\langle A^+ \rangle^1$

Energy consumption year/24 hrs: 241/0.660 kWh¹

Total net capacity: 300 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 155.5/69.7/75¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *********

- 7 drawers, of which 1 herb and berry tray, VarioSpace
- Lighting in the front housing
- Temperature rise time: 34 h
- Freezing capacity in 24 hrs: 24 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06

GP 2733

Comfort

Smart Frost

A⁺⁺

Energy efficiency class: $\langle A^+ \rangle^1$

Energy consumption year/24 hrs: 206/0.562 kWh¹

Total net capacity: 224 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 164.4/60/63.2¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment *********

- 7 drawers, VarioSpace
- Temperature rise time: 28 h
- Freezing capacity in 24 hrs: 22 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06, 07

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



The elegant and precise **MagicEye control** with its graphic temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function keys makes for easy and convenient use. The automatic **SuperFrost function** quickly reduces the temperature to freeze your food while preserving the vitamins.



Liebherr have now redefined energy saving with the innovative **A++** freezers. Use of the latest electronics combined with a highly efficient refrigerating system enables the energy consumption to be significantly reduced. This super energy-saving solution actively contributes to environmental conservation.



◀60▶



◀60▶

GP 2433 Comfort

Smart Frost A++

Energy efficiency class: $\lt; A^{++}$¹
 Energy consumption year/24 hrs: 191/0.522 kWh¹
 Total net capacity: 190 litre
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 144.7/60/63.2¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment **★★★★**

- 6 drawers, VarioSpace
- Temperature rise time: 26 h
- Freezing capacity in 24 hrs: 22 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06, 07

GP 2033 Comfort

Smart Frost A++

Energy efficiency class: $\lt; A^{++}$¹
 Energy consumption year/24 hrs: 175/0.479 kWh¹
 Total net capacity: 156 litre
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 125/60/63.2¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment **★★★★**

- 5 drawers, VarioSpace
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 19 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Special accessories (from page 136)

- 06, 07



Attractively designed, the robust **removable transparent drawers** with an easy-to-clean interior provide ample storage and the best possible storage solution for frozen food. Freezer drawers and toughened glass shelves removed to create additional space.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger produce.

The features shown are model dependent; the description applies to the relevant model.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Under counter freezer



The elegant and precise **MagicEye control** with its visual temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperFrost** function quickly reduces the temperature to freeze your food while preserving the vitamins.



The **top** of the under counter freezers is extremely robust, with a scratch and heat resistant surface.



◀60▶

GNP 1066
Premium

No Frost
A++

Energy efficiency class: $\langle A^{++} \rangle^1$

Energy consumption year/24 hrs: 150/0.409 kWh¹

Total net capacity: 91 litre

Noise output: 41 dB(A)

Climate rating: SN-ST

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/60.2/62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Temperature rise time: 22 h
- Freezing capacity in 24 hrs: 14 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06, 07

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



◀60▶



◀60▶



◀55▶



◀55▶



◀55▶



◀55▶

GP 1486
Premium

Smart Frost A+++

Energy efficiency class: $\langle A^{+++} \rangle^1$
Energy consumption year/24 hrs: 100/0.273 kWh¹
Total net capacity: 103 litre
Noise output: 38 dB(A)
Climate rating: SN-T
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85.1/60.2/62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment **★★★★**

- 4 drawers, VarioSpace
- Temperature rise time: 23 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06

GPesf 1476
Premium

Smart Frost A++

Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 151/0.413 kWh¹
Total net capacity: 103 litre
Noise output: 40 dB(A)
Climate rating: SN-T
Door/side walls: Stainless steel/silver
Exterior dimensions in cm (h/w/d): 85.1/60.2/61¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment **★★★★**

- 4 drawers, VarioSpace
- Temperature rise time: 24 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06, 17, 18

Colour / material options:

GP 1476 in white

GP 1376
Premium

Smart Frost A++

Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 151/0.413 kWh¹
Total net capacity: 103 litre
Noise output: 40 dB(A)
Climate rating: SN-T
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment **★★★★**

- 4 drawers, VarioSpace
- Temperature rise time: 23 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06

Gsl 1223
Comfort

Smart Frost A+ Silver

Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 190/0.518 kWh
Total net capacity: 98 litre
Noise output: 43 dB(A)
Climate rating: SN-T
Door/side walls: silver/silver
Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Temperature rise time: 26 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- SwingDesign
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06

GP 1213
Comfort

Smart Frost A++

Energy efficiency class: $\langle A^{++} \rangle^1$
Energy consumption year/24 hrs: 149/0.407 kWh¹
Total net capacity: 98 litre
Noise output: 40 dB(A)
Climate rating: SN-T
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment **★★★★**

- 3 drawers, VarioSpace
- Temperature rise time: 26 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06

GX 823
Comfort

Smart Frost A+

Energy efficiency class: $\langle A^+ \rangle$
Energy consumption year/24 hrs: 172/0.470 kWh
Total net capacity: 68 litre
Noise output: 43 dB(A)
Climate rating: SN-T
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 63.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment **★★★★**

- 2 drawers, VarioSpace
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Height-adjustable feet at front
- Reversible door hinging

Special accessories (from page 136)

- 06


¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

Quality in every detail



Soft System

Chest freezers in the premium range benefit from the **SoftSystem** closing mechanism, a convenient and highly desirable feature for everyday use. Integrated into the hinges on the freezer lid, SoftSystem allows the lid to close gently and prevents slamming.




Stop Frost

Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer. **StopFrost** prevents a vacuum from building up, ensuring the lid opens easily.



The heat-exchange **condenser** is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the outside and the smooth outside walls are easy-to-clean.



Innovative freezers from Liebherr in a new energysaving dimension: In the best **A+++ energy efficiency class**, the appliances are approximately 48% more energy efficient than the top limit of class A+.



The bright **interior light** allows a clear view of all your stored products even in low ambient lighting conditions.



All operating and control functions are clearly and practically integrated into the ergonomically designed **chest freezer handle**. As soon as the food is completely frozen, the automated **SuperFrost function** switches back to normal mode.

The features shown are model dependent; the description applies to the relevant model.

Chest freezers



164



164



137



137

GTP 4656 Premium



Energy efficiency class: $\langle A^{+++}$
 Energy consumption year/24 hrs: 175/0.478 kWh
 Total net capacity: 419 litre
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 91.7/164.4/80.7

Controls

- MagicEye in door handle, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 90 h
- Freezing capacity in 24 hrs: 38 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 6 Suspension baskets as standard, 10 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle
- Lock

Special accessories (from page 136)

- 06, 07, 08

GT 6122 Comfort



Energy efficiency class: $\langle A^+$
 Energy consumption year/24 hrs: 412/1.128 kWh
 Total net capacity: 572 litre
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 91.7/164.4/80.7

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 76 h
- Freezing capacity in 24 hrs: 33 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 3 Suspension baskets as standard, 13 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

GTP 3656 Premium



Energy efficiency class: $\langle A^{+++}$
 Energy consumption year/24 hrs: 152/0.414 kWh
 Total net capacity: 331 litre
 Noise output: 39 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 91.7/136.9/80.7

Controls

- MagicEye in door handle, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 77 h
- Freezing capacity in 24 hrs: 35 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 5 Suspension baskets as standard, 8 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle
- Lock

Special accessories (from page 136)

- 06, 07, 08

GT 4932 Comfort



Energy efficiency class: $\langle A^{++}$
 Energy consumption year/24 hrs: 275/0.751 kWh
 Total net capacity: 449 litre
 Noise output: 40 dB(A)
 Climate rating: SN-T
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 91.7/136.9/80.7

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 74 h
- Freezing capacity in 24 hrs: 31 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 2 Suspension baskets as standard, 11 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09



129



129



129



113

GTP 3156
Premium

Stop Frost A+++ Soft System

Energy efficiency class: <A+++>
Energy consumption year / 24 hrs: 137 / 0.373 kWh
Total net capacity: 276 litre
Noise output: 38 dB(A)
Climate rating: SN-T
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 91.7 / 128.5 / 75.8

GTP 2756
Premium

Stop Frost A+++ Soft System

Energy efficiency class: <A+++>
Energy consumption year / 24 hrs: 127 / 0.347 kWh
Total net capacity: 240 litre
Noise output: 39 dB(A)
Climate rating: SN-T
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 91.7 / 128.5 / 75.8

GT 4232
Comfort

Stop Frost A++

Energy efficiency class: <A+>
Energy consumption year / 24 hrs: 247 / 0.675 kWh
Total net capacity: 380 litre
Noise output: 40 dB(A)
Climate rating: SN-T
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 91.7 / 128.5 / 75.8

GTP 2356
Premium

Stop Frost A+++ Soft System

Energy efficiency class: <A+++>
Energy consumption year / 24 hrs: 117 / 0.318 kWh
Total net capacity: 200 litre
Noise output: 38 dB(A)
Climate rating: SN-T
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 91.7 / 112.9 / 75.8

Controls

- MagicEye in door handle, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment [****]

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 70 h
- Freezing capacity in 24 hrs: 31 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 3 Suspension baskets as standard, 7 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle
- Lock

Special accessories (from page 136)

- 06, 07, 08

Controls

- MagicEye in door handle, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment [****]

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 124 h
- Freezing capacity in 24 hrs: 25 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 3 Suspension baskets as standard, 7 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle
- Lock

Special accessories (from page 136)

- 06, 07, 08

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment [****]

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 72 h
- Freezing capacity in 24 hrs: 29 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 2 Suspension baskets as standard, 8 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

Controls

- MagicEye in door handle, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment [****]

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 110 h
- Freezing capacity in 24 hrs: 23 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 3 Suspension baskets as standard, 7 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle
- Lock

Special accessories (from page 136)

- 06, 07, 08

Chest freezers



113



100



87



75



57

GT 3632

Comfort

Stop Frost

A⁺⁺

Energy efficiency class: <A⁺>

Energy consumption year / 24 hrs: 225 / 0.614 kWh

Total net capacity: 324 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 91.7 / 112.9 / 75.8

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ****

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 70 h
- Freezing capacity in 24 hrs: 28 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 2 Suspension baskets as standard, 8 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

GT 3032

Comfort

Stop Frost

A⁺⁺

Energy efficiency class: <A⁺>

Energy consumption year / 24 hrs: 209 / 0.570 kWh

Total net capacity: 284 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 91.7 / 99.5 / 75.8

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ****

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 65 h
- Freezing capacity in 24 hrs: 27 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 2 Suspension baskets as standard, 5 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

GT 2632

Comfort

Stop Frost

A⁺⁺

Energy efficiency class: <A⁺>

Energy consumption year / 24 hrs: 190 / 0.518 kWh

Total net capacity: 237 litre

Noise output: 40 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 91.7 / 86.9 / 75.8

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ****

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Interior lighting
- Temperature rise time: 60 h
- Freezing capacity in 24 hrs: 24 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 2 Suspension baskets as standard, 5 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

GT 2132

Comfort

Stop Frost

A⁺⁺

Energy efficiency class: <A⁺>

Energy consumption year / 24 hrs: 172 / 0.470 kWh

Total net capacity: 193 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 91.7 / 75 / 75.8

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ****

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Temperature rise time: 51 h
- Freezing capacity in 24 hrs: 20 kg
- Defrost drain
- Removable freezer tray as partition wall - can be used as a drip tray
- 1 Suspension basket as standard, 3 retrofittable

Key features

- SwingDesign
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

GT 1432

Comfort

Stop Frost

A⁺⁺

Energy efficiency class: <A⁺>

Energy consumption year / 24 hrs: 149 / 0.408 kWh

Total net capacity: 137 litre

Noise output: 38 dB(A)

Climate rating: SN-T

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 91.7 / 56.5 / 75.8

Controls

- Electronic controls in chest handle, key electronic
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ****

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- Temperature rise time: 45 h
- Freezing capacity in 24 hrs: 13 kg
- 1 Suspension basket as standard, 3 retrofittable

Key features

- HardLine
- Ergonomically designed chest freezer handle

Special accessories (from page 136)

- 06, 07, 08, 09

Wine cabinets



WTes 5872



Find out more about
Wine cabinets:
wine.liebherr.com

Our wine cabinets: an overview

Wine lovers have the most stringent demands when it comes to storing their favourite wines. Many like to be able to enjoy their fine wines on the spur of the moment; others prefer to establish a collection of wines over the longer term; and some want the best of both worlds. Liebherr offers premium wine storage cabinets that guarantee perfect wine storage temperatures, whatever your requirements. With heating and cooling circuits and air filtration, our wine cabinets offer unsurpassed wine storage conditions.



Vinidor range

Offering either 2 or 3 individually controllable climate zones between +5°C and +20°C and accurate to within +/- 1°C. The Vinidor range offers great flexibility. This range facilitates the combined storage of red and white wines at the correct serving or long term storage temperatures.



GrandCru and Vinothek range

Wine storage cabinets offer similar conditions to a wine cellar. This range facilitates the storage of red and white wines at the correct long term storage temperatures or individual variety serving temperatures. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.




Vinothek range

Multi-temperature wine cabinets from the Vinothek range offer versatile storage for different types of wine, each at its perfect drinking temperature. The innovative climate technology that we use creates a graduated temperature zone from up to +18°C and down to +5°C. In this way a variety of wines can be stored at the various correct serving temperatures.



Vinidor - from page 124



GrandCru - from page 126



Vinothek - from page 129



Design & Lifestyle - from page 134

Quality in every detail



The electronic LCD display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions. The Vinidor 2 and 3 zone models feature an integrated door seal in the dividing shelf to maintain correct individual temperatures.



The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. Storing bottles neck to neck facilitates maximum storage capacity. The **clip-on labelling system** provides a quick and clear overview of your wine store.



LED

The **LED lighting** in the wine cooling compartments can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with this innovative, no-heat LED lighting concept. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical aluminium **door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.



Soft System

The **SoftSystem** feature provides added safety and convenience. Integrated on the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 45°.

The features shown are model dependent; the description applies to the relevant model.

Vinidor range



◀70▶



◀70▶




◀70▶



◀60▶

WTeS 5872 Vinidor



Energy efficiency class: $\langle A \rangle^2$
Energy consumption year/24 hrs: 180/0.493 kWh ²
Max. Bordeaux bottles 0.75 l: 178 ¹
Gross/net capacity: 578/496 litre
Noise output: 37 dB(A)
Climate rating: SN-ST
Door/side walls: Glass door with stainless steel frame/stainless steel
Exterior dimensions in cm (h/w/d): 192/70/74.2 ²

Controls

- LCD display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 3 Temperature zones, which can set from +5°C to +20°C
- 3 Individually regulated cooling circuits
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 13 Shelves, of which 10 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

Special accessories (from page 136)

- 10, 12, 14, 17, 18

WTeS 5972 Vinidor



Energy efficiency class: $\langle A \rangle^2$
Energy consumption year/24 hrs: 182/0.498 kWh ²
Max. Bordeaux bottles 0.75 l: 211 ¹
Gross/net capacity: 593/516 litre
Noise output: 38 dB(A)
Climate rating: SN-ST
Door/side walls: Glass door with stainless steel frame/stainless steel
Exterior dimensions in cm (h/w/d): 192/70/74.2 ²

Controls

- LCD display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5°C to +20°C
- 2 Individually regulated cooling circuits
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

Special accessories (from page 136)

- 10, 12, 14, 17, 18

WTpes 5972 Vinidor



Energy efficiency class: $\langle A \rangle^2$
Energy consumption year/24 hrs: 182/0.498 kWh ²
Max. Bordeaux bottles 0.75 l: 155 ¹
Gross/net capacity: 593/516 litre
Noise output: 38 dB(A)
Climate rating: SN-ST
Door/side walls: Glass door with stainless steel frame/stainless steel
Exterior dimensions in cm (h/w/d): 192/70/74.2 ²

Controls

- LCD display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5°C to +20°C
- 2 Individually regulated cooling circuits
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 6 Shelves, of which 5 set on telescopic rails, of which 2 are pull-out baskets

Key features

- HardLine
- Stainless steel slimline door handle
- Reversible door hinging
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 14, 17, 18

WTeS 1672 Vinidor



Energy efficiency class: $\langle A \rangle$
Energy consumption year/24 hrs: 137/0.375 kWh
Max. Bordeaux bottles 0.75 l: 34 ¹
Gross/net capacity: 123/95 litre
Noise output: 38 dB(A)
Climate rating: SN-ST
Door/side walls: Glass door with stainless steel frame/stainless steel
Exterior dimensions in cm (h/w/d): 82.2/60/57.5

Controls

- LCD display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5°C to +20°C
- 2 Individually regulated cooling circuits
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

Key features

- HardLine
- Stainless steel slimline door handle
- Reversible door hinging
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 14, 17, 18

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


Wine storage cabinets GrandCru



◀75▶



◀70▶



◀70▶



◀70▶

WKt 6451 GrandCru

Wine A++ LED

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 118 / 0.323 kWh

Max. Bordeaux bottles 0.75 l: 312¹

Gross / net capacity: 666 / 625 litre

Noise output: 41 dB(A)

Climate rating: SN-T

Door / side walls: Full door, terra / terra

Exterior dimensions in cm (h/w/d): 193 / 74.7 / 75.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Beech wood fittings
- 7 Shelves

Key features

- SwingLine design
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Lock

Special accessories (from page 136)

- 10, 14

WKt 5552 GrandCru

Wine A+ LED

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 140 / 0.382 kWh

Max. Bordeaux bottles 0.75 l: 253¹

Gross / net capacity: 573 / 525 litre

Noise output: 41 dB(A)

Climate rating: SN-ST

Door / side walls: Glass door, frame terra / terra

Exterior dimensions in cm (h/w/d): 192 / 70 / 74.2

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on
- Beech wood fittings
- 7 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 12, 13, 14

WKt 5551 GrandCru

Wine A++ LED

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 111 / 0.302 kWh

Max. Bordeaux bottles 0.75 l: 253¹

Gross / net capacity: 547 / 499 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door / side walls: Full door, terra / terra

Exterior dimensions in cm (h/w/d): 192 / 70 / 74.2

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Beech wood fittings
- 7 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Lock

Special accessories (from page 136)

- 10, 12, 13, 14

WKes 4552 GrandCru

Wine A+ LED

Energy efficiency class: <A>

Energy consumption year / 24 hrs: 133 / 0.364 kWh

Max. Bordeaux bottles 0.75 l: 201¹

Gross / net capacity: 478 / 435 litre

Noise output: 41 dB(A)

Climate rating: SN-ST

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 165 / 70 / 74.2

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on
- Beech wood fittings
- 6 Shelves

Key features


- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 12, 13, 14, 17, 18

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

Wine storage cabinets GrandCru




◀70▶



◀70▶

Wine storage cabinets Vinothek



◀60▶



◀60▶

WKt 4552 GrandCru

Wine

A+

LED

Energy efficiency class: <A>

Energy consumption year/24 hrs: 133/0.364 kWh

Max. Bordeaux bottles 0.75 l: 201¹

Gross/net capacity: 478/435 litre

Noise output: 41 dB(A)

Climate rating: SN-ST

Door/side walls: Glass door, frame terra/terra

Exterior dimensions in cm (h/w/d): 165/70/74.2

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on
- Beech wood fittings
- 6 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 12, 13, 14

WKt 4551 GrandCru

Wine

A++

LED

Energy efficiency class: <A++>

Energy consumption year/24 hrs: 106/0.288 kWh

Max. Bordeaux bottles 0.75 l: 201¹

Gross/net capacity: 456/413 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door/side walls: Full door, terra/terra

Exterior dimensions in cm (h/w/d): 165/70/74.2

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Beech wood fittings
- 6 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Lock

Special accessories (from page 136)

- 10, 12, 13, 14

WKb 4212 Vinothek

Wine

Energy efficiency class: <A>

Energy consumption year/24 hrs: 168/0.458 kWh

Max. Bordeaux bottles 0.75 l: 200¹

Gross/net capacity: 427/395 litre

Noise output: 41 dB(A)

Climate rating: SN-ST

Door/side walls: Glass door, frame black/black

Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Beech wood fittings
- 6 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 09, 10, 13, 14

WKr 4211 Vinothek

Wine

A++

Energy efficiency class: <A++>

Energy consumption year/24 hrs: 103/0.282 kWh

Max. Bordeaux bottles 0.75 l: 200¹

Gross/net capacity: 409/377 litre

Noise output: 39 dB(A)

Climate rating: SN-T

Door/side walls: Full door, burgundy/black

Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 6 Shelves


Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging


Special accessories (from page 136)

- 09, 10, 13, 14

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)



◀60▶



◀60▶



◀60▶

WKb 3212
Vinothek

Wine

Energy efficiency class: <A>
Energy consumption year / 24 hrs: 161 / 0.441 kWh
Max. Bordeaux bottles 0.75 l: 164¹
Gross / net capacity: 336 / 309 litre
Noise output: 39 dB(A)
Climate rating: SN-ST
Door / side walls: Glass door, frame black / black
Exterior dimensions in cm (h / w / d): 135 / 60 / 73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Beech wood fittings
- 4 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 09, 10, 13, 14

WKr 3211
Vinothek

Wine

A⁺⁺

Energy efficiency class: <A⁺⁺>
Energy consumption year / 24 hrs: 99 / 0.269 kWh
Max. Bordeaux bottles 0.75 l: 164¹
Gross / net capacity: 322 / 295 litre
Noise output: 39 dB(A)
Climate rating: SN-T
Door / side walls: Full door, burgundy / black
Exterior dimensions in cm (h / w / d): 135 / 60 / 73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 4 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging

Special accessories (from page 136)

- 09, 10, 13, 14

WKb 1812
Vinothek

Wine

A⁺

Energy efficiency class: <A⁺>
Energy consumption year / 24 hrs: 113 / 0.307 kWh
Max. Bordeaux bottles 0.75 l: 66¹
Gross / net capacity: 145 / 134 litre
Noise output: 38 dB(A)
Climate rating: SN-ST
Door / side walls: Glass door, frame black / black
Exterior dimensions in cm (h / w / d): 89 / 60 / 61.3

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Galvanised grid shelves
- 3 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 09, 10, 14, 15



The precision **electronic control system** is clearly arranged in the insulation plate. The digital temperature display can be read from the outside of appliances with glass doors. The door and temperature alarm alerts the user to any irregularities, e.g. a door that has been left open. The child lock prevents any inadvertent changes to the control system.



For ideal presentation of your best wines, appliances with glazed doors feature an **interior light** with separate switch.

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)



WTb 4212

Multi-temperature wine cabinets Vinothek



WTb 4212

Vinothek

Wine

Energy efficiency class: <A>
 Energy consumption year/24 hrs: 168/0.460 kWh
 Max. Bordeaux bottles 0.75 l: 200¹
 Gross/net capacity: 427/395 litre
 Noise output: 41 dB(A)
 Climate rating: SN-ST
 Door/side walls: Glass door, frame black/black
 Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 6 Targeted temperature layers ranging from +5°C to +18°C
- Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via lava stones
- Interior lighting permanently on
- Beech wood fittings
- 6 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

Special accessories (from page 136)

- 09, 10, 11, 13, 14

WTr 4211

Vinothek

Wine

Energy efficiency class: <A>
 Energy consumption year/24 hrs: 167/0.457 kWh
 Max. Bordeaux bottles 0.75 l: 200¹
 Gross/net capacity: 409/377 litre
 Noise output: 40 dB(A)
 Climate rating: SN-ST
 Door/side walls: Full door, burgundy/black
 Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 6 Targeted temperature layers ranging from +5°C to +18°C
- Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via lava stones
- Beech wood fittings
- 6 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging

Special accessories (from page 136)

- 09, 10, 11, 13, 14

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)



WKes 653 and ZKes 453

Design & Lifestyle



WKes 653 GrandCru



Energy efficiency class: $\lt; A^+$
 Energy consumption year / 24 hrs: 75 / 0.205 kWh
 Max. Bordeaux bottles 0.75 l: 12¹
 Gross / net capacity: 56 / 38 litre
 Noise output: 40 dB(A)
 Climate rating: SN
 Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
 Exterior dimensions in cm (h / w / d): 61.2 / 42.5 / 47.8

Controls

- LCD display behind-the-door, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5°C to +20°C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves

Key features

- HardLine
- Fixed door hinge, right
- Utensil drawer
- Suitable for wall mounting
- Replaceable door seal
- Lock

Special accessories (from page 136)

- 10, 14, 16

ZKes 453 Humidor



Energy efficiency class:
 Energy consumption year / 24 hrs: 162 / 0.443 kWh
 Gross / net capacity: 43 / 39 litre
 Noise output: 40 dB(A)
 Climate rating: N
 Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
 Exterior dimensions in cm (h / w / d): 61.2 / 42.5 / 47.8

Controls

- LCD display behind-the-door, touch electronic
- Digital display of temperature and humidity
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Humidor

- 1 Temperature zone, which can set from +16°C to +20°C
- Humidity range, adjustable between 68% to 75%
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 Shelves

Key features

- HardLine
- Fixed door hinge, right
- 2 presentation boxes
- Suitable for wall mounting
- Lock

Special accessories (from page 136)

- 10, 16

CMes 502



Energy efficiency class: $\lt; A$
 Energy consumption year / 24 hrs: 107 / 0.293 kWh
 Gross / net capacity: 45 / 42 litre
 Noise output: 36 dB(A)
 Climate rating: SN-ST
 Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
 Exterior dimensions in cm (h / w / d): 61.2 / 42.5 / 45

Controls

- Mechanical controls, external control dial

Fridge compartment

- 1 Temperature zone, which can set from +2°C to +10°C
- LED lighting permanently on, dimmable
- Galvanised grid shelves
- 3 Shelves

Key features

- HardLine
- Height-adjustable feet at front
- Fixed door hinge, right
- Suitable for wall mounting
- Lock

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

01 VarioSafe

The VarioSafe provides a clear view whilst creating order. It is the ideal space for smaller food packets, tubes and jars. The safe can be positioned at various levels on the lighting column.



BluPerformance BioCool appliances; K- and KB appliances	7275 142
BluPerformance BioFresh fridge-freezers	7275 144

02 Bottle shelf

The bottle shelf provides elegant and practical storage for drinks.



BluPerformance BioCool appliances; K- and KB appliances	7112 508	CTNesf 3663, CTN 3223	7112828
BluPerformance BioFresh fridge-freezers	7112 510	K 2330, K(sI) 2814; CTP(sI) 2121, 2521, 2921; CN 30;	
C(bs, ef) 3425, C(ef) 3825	7112 442	CUN 30; CU 23, CU 28, CU(ef, ag, wb, fr) 33	7112 822
C(ef) 35, C(ef) 40; CN(ef) 31, CN(ef) 35, CN(ef) 39, CN(bs, ef) 40; CTP(ef) 33; CU 29	7112 446	CTP(ef) 3016; K(sI) 2630, K(sI) 3130	7112 826
75 cm: CBN(esf); CBNP(es) (except CBNPes 5167)	7112 325	SBS(es, bs, ef) 7353, 7263, 7253, 7242	7112 448
		75 cm: CN(esf) 51; CTNes 4753	7112 341

03 Water filter

Replacement for the integrated water filter. Provides perfect water quality every time in appliances with an IceMaker. The electronic control unit indicates when the water filter needs to be replaced.



CBNes 6256	7440 002
------------	----------

04 Three-metre hose for IceMaker

Reinforced flexible hose (1m long) for appliances with a 3/4" plumbed-in connection.



SBSes 7165, SBS(es, bs) 7263, SBSes 7353; CBNPes 5167, CBNPes 3967	6030 785
---	----------

05 Vario energy-saving panel

The Vario energy saving plate can shut off unused drawers in NoFrost upright freezers and the full space BioFresh refrigerator. Energy consumption can be reduced by up 50%.



SBS(es, bs, ef) 7242, 7253, 7263	9363 210	70 cm wide:	
60 cm wide:		GN(P) 26-41	9363 372
BluPerformance-Freezers	9368 032		

06 Cold storage accumulator

Freezers, and the freezer compartments of fridge-freezers are protected in the event of a power failure by the cold storage accumulator. This acts as an additional 'cold reserve' to prevent the temperature from rising in such circumstances, and thereby protects the frozen produce.



Chest freezers	7412 053	Fridge-freezers, freezers and SBS appliances	7422 838
----------------	----------	---	----------

07 Freezer tray

The innovative freezer tray is perfect for freezing fruits, berries and herbs individually. Not only does this prevent them from sticking together, but it also ensures they retain their shape, and makes them easier to vacuum pack, and to divide into portions later on.



SBS; CN(ef) 31, 35, CN(bs, ef) 39, 40; SGNes 3011; GNP 1913, 2313, 2713, 3013	7426 080	GT 6122, 4932	7431 387
C(bs, ef) 34, C(ef) 35, C(ef) 38, C(ef) 40; CU 29; GP 20, 24, 27; GN 1923	7426 356	GTP 2756, 2356	7431 419
BluPerformance fridge-freezers and freezers	7422 828	GTP 3656, 4656	7431 391
		GT 1432, 2132, 2632, 3032, 3632, 4232	7431 389
		GTP 3156	7431 393

08 Additional baskets for chest freezers


Versatility is increased by the use of additional baskets. These make it easier to sort small frozen food items, and facilitate easier access to stored produce.



GTP 2356	7112 317	GTP 3156	7113 555
GTP 2756	7112 251	GT 1432, 2132, 2632, 3032	7112 725
GTP 4656, GTP 3656	7113 627	GT 4932	7113 553
GT 3632, GT 4232	7113 557	GT 6122	7112 727

09 Lock

The lock prevents unwanted access. Simply assemble on the housing with Vinothek wine cabinets. If two wine cabinets are set up Side-by-Side, the operation of the sideways lock is limited. In this case an additional lock can be fitted below.



GT Comfort 21-61, GT 1432	9590 835	Vinothek wine appliances	9094 443
---------------------------	----------	--------------------------	----------

10 FreshAir active carbon filter

During prolonged storage, wines and cigars are sensitive to any odours that contaminate the storage environment. Liebherr appliances benefit from optimum air quality and freshness thanks to the easy-to-replace FreshAir active carbon filter which is integrated into the wine compartment of the SBSes 7165 Side-by-Side fridge-freezer, into all wine cabinets, and into the humidor. Annual replacement is recommended.



WTes 1672	7434 557	BluPerformance fridge-freezers and fridges	9096 342
WKes 653; ZKes 453	7440 699		
All other wine appliances; SBSes 7165	7433 243		

Optional Accessories

When ordering accessories, please ensure that you quote not only the order numbers shown below, but also the full appliance name/service number.

11

Lava stone

The humidity in the Vinothek multi-temperature wine cabinets can be increased as required using lava stones.

WTb 4212; WTr 4211 9590 785



12

Presentation shelf

The shelf can be used to present exquisite wines, or to safely store already-opened bottles.

WTes 5872, 5972 7112 043 GrandCru wine appliances 7113 619



13

Wooden shelf

The handcrafted shelf, made from natural wood, is the perfect accessory for safely storing Bordeaux bottles. Positioning the bottles in opposite directions enables full use of the shelf's capacity.

GrandCru wine appliances (except WKt 6451) 7112 159 Vinothek wine appliances 7112 113



14

Clip-on labelling system

The clip-on labelling system provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.

For wooden shelves (5 pieces) 9086 709 For grill shelves WKb 1812 (2 pieces) 9086 723



15

Galvanised grill shelf

Grill shelf for additional requirements.

WKb 1812 7112 035




16

Underside cover for wall mounting

Covers the underside, enabling compact appliances to be attractively wall mounted without their underside being visible.

WKes 653; ZKes 453 9590 519



17

Stainless steel cleaner

The stainless steel cleaner reliably and gently removes fingerprints, streaks, and stains from stainless steel surfaces. It cleans quickly, without streaking, and also prevents the subsequent accumulation of stubborn dirt. (Not suitable for use on SmartSteel fronts.)

250 ml es-models (stainless steel without SmartSteel) 8409 022



18

Stainless steel polish

For polishing stainless steel surfaces after they have been cleaned (do not use on SmartSteel).

250 ml es-models (stainless steel without SmartSteel) 8409 030



19

VarioBoxes

The two detachable, fridge-to-table VarioBoxes are perfect for storing ready-to-serve foods in the refrigerator. The Liebherr egg tray for 12 eggs fits perfectly in the large VarioBox. The accessories set comprises two VarioBoxes and a robust stainless steel securing rail. VarioBoxes can be securely attached to the door interior at various levels.

BluPerformance fridge-freezers and fridges 7438 202



20

FlexSystem

The FlexSystem, for BioFresh safes and BioCool boxes, provides flexible, organised and easily viewed storage for food. For example, fruit and vegetables can be kept clearly separated or foods can be stored according to use-by date. All components of the sturdy FlexSystem are easy-to-clean and dishwasher friendly.

BluPerformance BioFresh and BioCool models (except B 2850) 7413 532



21

3-metre appliance cable

In cases where the standard 2.1 metre cable length is insufficient, the 3-metre appliance cable allows greater installation flexibility. The cable plug can be removed from the appliance with minimal effort.

BluPerformance appliances (except Great Britain) 6009 158

BluPerformance appliances (Great Britain) 6009 186



Our catalogues

Find out everything you need to know about Liebherr built-in appliances in the latest catalogue. In addition our special brochures contain comprehensive information about our BioFresh, FoodCentres and wine cabinet ranges. Available in printed format from retailers or as a PDF download from home.liebherr.com.



Smart communication on all fronts



BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



Kitchen Photo Designer App

Be your own interior designer: take a photo of your kitchen, select the Liebherr model of your choice and position it into your photo by swiping the screen.



IceCrusher App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.
apps.home.liebherr.com

View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



biofresh.liebherr.com



nofrost.liebherr.com



wine.liebherr.com

Click the link to directly access our social media channels: socialmedia.home.liebherr.com



Please contact Liebherr-Great Britain Ltd. to locate your nearest LIEBHERR displaying dealer:



Subject to modification. Printed in Germany by raff mediagroup. 7 943 251-07/07.2016



Liebherr-Great Britain Ltd.

Normandy Lane, Stratton Business Park, Biggleswade, SG18 8QB

Tel.: +44 (0) 3330 147 888, Fax: +44 (0) 1767-602 152,

Email Sales: sales.ukrefrigeration@liebherr.com, Customer Service: customerservice.ukrefrigeration@liebherr.com

www.myliebherr.co.uk