

French Door and Single Door
Food Centres

LIEBHERR

Quality, Design and Innovation

New integrated Frenchdoor fridge-freezer with BioFresh: ECBN 6256

The new 91 cm wide, Frenchdoor fridge-freezer ECBN 6256 is definitely a design highlight in any kitchen and, with Liebherr's BioFresh technology, it's a healthy choice too! BioFresh technology guarantees the best possible environment for lasting freshness, which is really important because the freshness and quality of the food that we eat plays a key role in our health and well-being.

Integrated lighting columns on either side of the appliance interior provide perfectly even illumination, and high-quality GlassLine fittings lend elegance to the interior design. The two freezer drawers extend effortlessly on premium-quality telescopic rails, and the plumbed-in IceMaker provides sophisticated ice cubes for whatever the occasion.




The **versatile bottle shelf** above the BioFresh drawers can be used either as a bottle shelf or a glass storage shelf, both are stored in the recess. The interior features two **integrated lighting columns** with multiple LEDs to evenly illuminate the interior. The lighting columns also facilitate the variable positioning of the glass shelves.

The **SoftSystem**, in pristine white, is integrated into the door to cushion movement as the door is shut, ensuring that the door closes gently, even with fully-loaded door shelves. The door closes automatically from an opening angle of approx. 30°.

Integrated fridge-freezer with BioFresh

ECBN 6256 PremiumPlus



Door assembly

Net capacity Fridge compartment
including BioFresh compartment
Freezer compartment

Energy efficiency class

Energy consumption in 365 days/24 h

Climate rating

Aperture dimensions in cm (h/w/d)

Adjustable cooling circuits

Type of control

Position

Control

Accessories (see pages 10–11)

Door on Door

357 litre

68 litre

114 litre

A++

322/0.881 kWh

SN-T

203.2/91.5/at least 62.5

2 - DuoCooling

MagicEye with digital temperature display

behind the door

Touch-electronic

1, 2, 3, 4, 5, 6, 9



The two freezer compartment drawers extend on premium-quality **telescopic rails** and benefit from a self-closing mechanism, making them almost effortless to use. And Liebherr's professional **NoFrost technology** means there is no need to defrost the appliance and also ensures particularly low energy consumption.

Bio
FreshNo
Frost

Built-in

Extra-wide BioFresh food storage centre: ECBN 6156

The new 91-cm-wide, built-in BioFresh fridge-freezer ECBN 6156 PremiumPlus (net capacity 471 litres) is a real eyecatcher! Available with door-on-door installation that gives customised integration into kitchen design, and two freezer drawers that easily extend on premium-quality telescopic rails, this built-in masterpiece is a design highlight for any kitchen. The large

refrigerator compartment and adjacently arranged BioFresh drawers, together with the NoFrost freezer compartment offer optimum storage for all types of food. The integral IceMaker supplies ice cubes for every occasion, whilst the integrated water filter ensures optimum ice quality.




The innovative **electronic controls** ensure that the selected temperature is accurately maintained. Thanks to the ingenious touch interface, all functions can be set with ease. The temperature in the refrigeration and freezer compartments can be read from the MagicEye digital display on the LCD. The PremiumPlus interior features **LED light columns** integrated on either side of the compartment liner.

The professional **NoFrost technology** from Liebherr makes defrosting a thing of the past. The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.

Integrated fridge-freezer with BioFresh

ECBN 6156 PremiumPlus



Door assembly	Door on Door/for integrated use
Net capacity	Fridge compartment: 357 litre including BioFresh compartment: 68 litre Freezer compartment: 114 litre
Energy efficiency class	A+
Energy consumption in 365 days/24 h	410/1.121 kWh
Climate rating	SN-T
Aperture dimensions in cm (h/w/d)	203.2/91.5/at least 62.5
Adjustable cooling circuits	2 - DuoCooling
Type of control	MagicEye with digital temperature display
Position of control	behind the door
Control	Touch-electronic
Door hinges fixed	001: right door hinges / 617: left door hinges
Accessories (see pages 10–11)	1, 2, 3, 4, 5, 6, 7, 8, 9



BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0°C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator.

ECBN 6156 617 with left hand hinge

Stainless steel panels are not included. This appliance must be bracketed to the wall/floor.

Bio
FreshNo
Frost

Built-in

The new innovative food storage centre: ECBN 5066

The 76-cm-wide ECBN 5066 food centre creates a stunning visual impact in any kitchen environment. As the doors open, the interior also reveals a host of innovative ideas, LED lighting, BioFresh drawers mounted on telescopic rails, together with the NoFrost

freezer compartment offers optimum storage for all food types. The integral IceMaker supplies ice for every occasion, whilst the integrated water filter ensures optimum ice quality.



BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0 °C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator. The DrySafe, with a low humidity level, is ideal for storing meat, fish and milk products.

ECBN 5066 comes with an **LED lighting column** on each side of the inner door, which incorporates multiple LEDs to evenly illuminate the appliance interior. A special satin-finish on the light cover creates an appealing and sophisticated lighting effect. The lighting column also facilitates the variable positioning of the glass shelves.



ECBN 5066 001 with right hand hinge
This appliance must be bracketed to the wall/floor.

Integrated fridge-freezer with BioFresh

ECBN 5066 PremiumPlus



Door assembly	Door on Door/for integrated use
Net capacity	Fridge compartment: 276 litre including BioFresh compartment: 57 litre Freezer compartment: 103 litre
Energy efficiency class	A++
Energy consumption in 365 days/24 h	287/0.785 kWh
Climate rating	SN-T
Aperture dimensions in cm (h/w/d)	203.2/76.2/at least 61
Adjustable cooling circuits	2 - DuoCooling
Type of control	MagicEye with digital temperature display
Position of control	behind the door
Control	Touch-electronic
Door hinges fixed	001: right door hinges / 617: left door hinges
Accessories (see pages 10–11)	1, 2, 3, 4, 5, 6, 7, 8, 9



The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.

Frenchdoor fridge-freezers with BioFresh and NoFrost: CBN(es, be) 6256

The Food Storage Centres CBN(es, be) 6256 with their elegant Frenchdoor concept are a focal point in any kitchen, open or closed. The interior presents a host of innovative ideas. Take the LED interior light and the automatic IceMaker with fixed water connection in the freezer compartment, for example. Or the two BioFresh drawers, which keep food fresh for significantly longer. Accurate and independent temperature control of the fridge and freezer compartments is ensured by DuoCooling: two separately adjustable cooling circuits. There is no air exchange between the refrigerator and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



Both **BioFresh drawers** are mounted on **telescopic rails** which extend effortlessly providing a full view of your food, which is easily accessible. The lateral **LED light spots** ensure perfect illumination of the drawers. The versatile glass/bottle shelf can be used depending on your personal preference. The glass on top gives you shelf space, and the glass underneath gives you bottle space.



CBNes 6256 PremiumPlus



CBNbe 6256 PremiumPlus



357 litre
68 litre
114 litre



322/0.881 kWh

SN-T

203.9/91/61.5

2 - DuoCooling

Stainless steel

Stainless steel

MagicEye with digital temperature display

behind the door

Touch-electronic

3, 4, 5, 6

357 litre
68 litre
114 litre



322/0.881 kWh

SN-T

203.9/91/61.5

2 - DuoCooling

beige

beige

MagicEye with digital temperature display

behind the door

Touch-electronic

3, 4

Fridge-freezer with BioFresh

Net capacity Fridge compartment including BioFresh compartment
Freezer compartment

Energy efficiency class

Energy consumption in 365 days/24 h

Climate rating

Exterior dimensions in cm (h/w/d)

Adjustable cooling circuits

Door

Side walls

Type of control

Position of control

Control

Accessories (see pages 10–11)



Our professional **NoFrost technology** makes defrosting a thing of the past. The CBN(es, be) 6256 NoFrost food centres are a highly energy efficient A++ rated appliance. The **two pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



The elegant, high quality **GlassLine interior** is adaptable to suit individual requirements. The satin-finish shelves and door racks with solid aluminium trims are height adjustable. The door interior accommodates tall bottles and wide containers.

01

Stainless steel panels

The use of the stainless steel panels requires a 90° hinge limitation. The panels will interfere with the adjacent gable or panel at 105° opening angle. The "Door stop pins" are required.

ECBN 6256	fridge compartement 84"	9900 335-00	ECBN 6156	freezer compartement	9900 323-00
ECBN 6256	fridge compartement 80"	9900 337-00	ECBN 5066	fridge compartement 84"	9900 285-00
ECBN 6256	freezer compartement	9900 323-00	ECBN 5066	fridge compartement 80"	9900 287-00
ECBN 6156	fridge compartement 84"	9900 331-00	ECBN 5066	freezer compartement	9900 283-00
ECBN 6156	fridge compartement 80"	9900 333-00			



02

Handles

Either aluminium or stainless steel handles can be fitted in combination with stainless steel panels, according to preference.

ECBN 6256	Stainless steel handles	9900 339-00	ECBN 6256	Aluminium handles	9900 513-00
ECBN 6156	Stainless steel handles	9900 327-00	ECBN 6156	Aluminium handles	9900 329-00
ECBN 5066	Stainless steel handles	9900 279-00	ECBN 5066	Aluminium handles	9900 281-00



03

Water filter

Replacement for the integrated water filter. Provides perfect water quality every time in appliances with an IceMaker. The electronic control unit indicates when the water filter needs to be replaced.

Water filter	7440 002
--------------	----------



04

Cold storage accumulator

The freezer compartments of fridge-freezers are protected in the event of a power failure by the cold storage accumulator. This acts as an additional 'cold reserve' to prevent the temperature from rising in such circumstances, and thereby protects the frozen produce.

Cold storage accumulator	7422 838
--------------------------	----------



05

Stainless steel cleaner

The stainless steel cleaner reliably and gently removes fingerprints, streaks, and stains from stainless steel surfaces. It cleans quickly, without streaking, and also prevents the subsequent accumulation of stubborn dirt.

250 ml	8409 022
--------	----------



06

Stainless steel polish

For polishing stainless steel surfaces after they have been cleaned.

250 ml	8409 030
--------	----------




07

Side-by-Side kit

The Side-by-Side kit allows SBS appliances to be optimally aligned and fixed together – ensuring full functionality and an attractive appearance.

ECBN 6156	9900 155-00	ECBN 5066	9900 157-00
-----------	-------------	-----------	-------------




08

Door hinge replacement kit

Appliances are supplied from the factory with right-hinged door closure. Being able to swap over the side of door closure means that the appliance can always be positioned to its best advantage, wherever it is installed.

ECBN 6156	9900 165-00	ECBN 5066	9900 167-00
-----------	-------------	-----------	-------------




09

Door stop pins

It may be necessary to limit the opening of the door hinges to 90° and to achieve this a specially designed pin is inserted into the door hinge. Restricted door opening is necessary with stainless steel panels.

ECBN 6256	9096 214-00	ECBN 6156, ECBN 5066	9096 699-00
-----------	-------------	----------------------	-------------



10 good reasons to choose LIEBHERR

1 Know-how that matters!

LIEBHERR is a specialist refrigeration manufacturer in both the domestic and commercial markets and has been developing and innovating product solutions for over 60 years. No other refrigeration appliance manufacturer secures greater brand loyalty from its customers than LIEBHERR, and knowing this motivates us to keep on delivering appliances that merit their confidence and trust.

2 Optimal product quality

To guarantee consistent product quality, LIEBHERR always uses the very best materials and components in the manufacturing of its appliances. Every appliance is tested for quality and functionality during production. Continual product development, optimised components, and superb workmanship ensure that Liebherr's reputation for quality and long-lasting appliances is never in doubt.

3 Innovative ideas

With its range of over 300 models, whether freestanding, under-worktop or built-in, Liebherr provides the perfect solution for food storage and freshness for almost every customer with its refrigerators, freezers and combined fridge-freezers. LIEBHERR appliances boast a compelling array of innovative ideas. Take, for example, the appliances with user-friendly Touch-electronic navigation feature, or trend-setting LED lighting, convenient IceMaker with TwistTray, or GlassLine shelves for versatile use.

4 Classic design

LIEBHERR refrigeration and freezers meet outstanding design criteria by combining excellent materials (premium-quality stainless steel, precision electronics, and exquisite GlassLine fittings) with classic contours, to produce a timeless elegance. Stainless steel doors with SmartSteel reduce the visibility of finger marks and are very easy-to-clean and far more scratch-resistant. The slimline door handles with integrated opening mechanism in stainless steel or white are fitted at a convenient height for easy opening.

5 Environmentally friendly

LIEBHERR takes environmental responsibility seriously, and our ActiveGreen philosophy is applied right from the beginning of appliance development right down to the finished product. Not only does Liebherr use the highest-quality components to build appliances that are reliable, durable and energy efficient, but also Liebherr ensures all plastics are labelled for optimum recycling. Further, all manufacturing processes are designed to use resources efficiently, e.g. heat generated during production is recycled and reused as heating energy for office buildings on the production premise. All European manufacturing sites are certified in accordance with the international environmental management standard ISO 14001.

Active
Green

6 Outstanding energy efficiency

A⁺ A⁺⁺

With innovative precision electronics and unequalled refrigeration performance, LIEBHERR offers highly economical appliances across its product range. All product groups feature models that fall into the top energy efficiency classes, providing great savings all round.

7 BioFresh – definitely healthier

Bio
Fresh

BioFresh provides the perfect climate for long-lasting freshness. When stored at a temperature slightly above 0 °C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance significantly longer than in a standard refrigerator. The BioFresh-Plus technology provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the adjustable drawer at +6°C to be lowered to -2°C.

8 NoFrost – professional freezing quality

No
Frost

No more defrosting: LIEBHERR's NoFrost technology provides rapid, fan-assisted, frostfree freezing that gives professional standard, long term freshness. Food is frozen by chilled circulating air and humidity is expelled, ensuring that the freezer remains ice-free and preventing produce from frosting over.

9 Perfect climate for fine wines

Wine

LIEBHERR's wine cabinets and multi-temperature wine cabinets are designed specifically to store wine in its optimum environment. This range features state-of-the-art electronic control systems, heating and cooling circuits, special vibration free compressors and a host of features such as tinted glazed doors, activated charcoal filters and solid hand crafted wooden shelves on telescopic rails.

10 Awards given to the range

The outstanding product and design quality of LIEBHERR appliances is confirmed again and again by independent organisations. The integrated ECBN 5066 fridge-freezer won Plus X Seals of Approval for High Quality, Design, Ease of Use and Ecology. This model also received the Good Design Award. The CBNes 6256 French door fridge-freezer has also been recognised with several awards including the IF Product Design Award and the reddot title 'Best of the Best'.



Subject to modification. Printed in Germany by
raff mediagroup GmbH. 7945 261-00/02.2016

