

# Freestanding 2021/22

[home.liebherr.com](https://home.liebherr.com)

# LIEBHERR

Refrigeration and freezing





# Contents

Liebherr Corporate Group	04
Quality, Design and Innovation	06
New energy label	12
Flexible accessories	14
BluPerformance	16
BioFresh	20
Food storage centres	22
Side-by-Side fridge-freezers	26
Frenchdoor fridge-freezer	32
Fridge-freezers	34
with bottom freezer	44
with top freezer	60
Fridges	62
Freezers	88
Wine Cabinets	112

# Global Success: Liebherr Corporate Group

Liebherr is a third-generation, family-owned company founded by Dr. Hans Liebherr in 1949 with the creation of the first ever mobile crane. With more than 70 years of success, Liebherr has become synonymous with the equipment needed to build homes and businesses, as well as the appliances within them. One of the world's largest manufacturers of construction machinery, Liebherr has expanded to eleven divisions with a wide array of product ranges, including earth moving equipment, mining, tower and maritime cranes, aerospace and transportation systems, and hotels. The company currently employs over 48,049 people in more than 140 companies in over 50 countries worldwide. Liebherr Appliances is Europe's largest privately owned manufacturer of fridges and freezers for residential and commercial use, with an annual production of more than 2.2 million units.



Construction



Aerospace and Transportation Systems



Mining



Cranes



Liebherr Appliances facility in Ochsenhausen, Germany



Liebherr Appliances facility in Lienz, Austria

For 70 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

## **Quality fresh food storage: BioFresh**

Liebherr's BioFresh technology preserves fresh food for longer. Stored in the BioFresh compartment, at just over 0 °C and at the ideal humidity level, food will retain its nutritional value for far longer than it would in a normal fridge compartment.

## **Professional quality**

As a refrigeration specialist, Liebherr offers a wide range of professional appliances for commercial use. The demands of the professional sector are high; this sector wants reliable, top quality storage that guarantees safe food storage. As you use your Liebherr appliance in the home on a daily basis, you are benefiting from the expertise that Liebherr has accrued from decades in the commercial sector.

## **Quality assured**

So that you can trust your fridge or freezer to perform 24 hours a day, 365 days a year, we check all components at every stage of their development to ensure that they will function reliably for many years. For instance, before our door hinges find their way into production, they have to successfully pass through at least 100.000 opening cycles, which equates to more than 15 years use. All components undergo similar testing.

## **Approved quality**


Prior to packaging, every appliance is subject to a comprehensive quality inspection during which all components – refrigeration, mechanical and electronic systems – are tested. The quality of workmanship is also visually checked. All newly manufactured domestic appliances from Liebherr comply with the requirements of standard IEC 60335-2-24 A2 §30 in terms of heat and fire resistance.

## **Guaranteed quality**

We provide a two-year warranty that covers all parts and labour costs to repair or replace any part of the appliance that proves to be defective in materials or workmanship. We also offer a ten year parts availability. All Liebherr production sites are certified according to international standards for quality management (ISO 9001) and environmental management (ISO 1400).

## **VCC compressor**

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.



# Design

Characterised by elegant and timeless design, Liebherr's fridges and freezers fulfil and surpass the highest aesthetic demands. Extensive detailing – as seen in the superb stainless steel craftsmanship, the choice of high quality materials, the stylish interior fittings, and the practical GlassLine door interior – is typical in our appliances and reveals their design quality.

## Design for every kitchen space

So you can enjoy a lifetime of pleasure owning your Liebherr appliance, and find the perfect appliance for you, we offer a wide range of designs including models in classic stainless steel, elegant BlackSteel or vibrant ColourLine finishes, all of which complement modern kitchen and living spaces.

## Practical design for daily use

At Liebherr, design and functionality go hand-in-hand. To prevent finger marks on our stainless steel doors, we finish them with a SmartSteel surface. To make door opening easy and convenient, our ergonomically designed handles house an integrated opening mechanism. All GlassLine shelves are dishwasher safe.

## Lighting design


Liebherr's fridges and freezers are fitted with modern LED lighting. Upon opening the appliance door, the interior becomes evenly illuminated. LEDs are long-life, energy efficient and generate very little heat. We take meticulous care to install specially selected LEDs in order to achieve a harmonious, slightly bluish tinted lighting effect.

## Award-winning design

The superb design quality of our appliances has seen them honoured with many prestigious, international design awards from the likes of Plus X Award, reddot, iF product design and Good Design.



## Door Design



HardLine-Design offers a clear, linear and minimalist style creating a pristine overall appearance and a sense of elegance.



SwingLine-Design features elegantly contoured edges for a timeless appeal.



SwingDesign has gently rounded edges resulting in a balanced design.

# Innovation

Liebherr was first to implement features that are now standard in today's fridges and freezers. For example: fully enclosed FrostSafe freezer drawers that prevent loss of chilled air when the appliance is opened; patented BioFresh technology; and convenient, SoftSystem cushioned door closure.

## Innovative ideas

We place great importance on the continual development of our products. Therefore, at all of our production sites, we have state-of-the-art design centres with highly skilled employees. Our goal is to be 'Best in Class' in every respect. For example, Liebherr's current appliances are super-economical in terms of energy consumption thanks to the incorporation of advanced electronics and optimised refrigeration design.

## Innovation for even greater freshness

The latest fridges and freezers offer the ideal climate zone for almost every type of food. So, in addition to the classic refrigerator compartment, Liebherr offers a range of features including the BioCool box: a fruit and vegetable compartment in which humidity can be regulated; BioFresh drawers, in which meat, fish, dairy products, and fruit/vegetables all find their ideal storage climate; and a NoFrost freezer compartment that offers professional quality frost free freezing.

## Excellence in every detail

It couldn't be easier to set and adjust appliances with touch screen operation. The Glassline storage shelves can be easily positioned for tailored use of the interior space. Drinks storage is provided in the door interior and, depending on the model, a bottle rack or versatile bottle shelf offer additional practical storage solutions.

1954

Liebherr home appliances founded in Germany



1971

First electronic control



1987

NoFrost Technology eliminating the need to defrost



1993

Conversion to CFC / HFC-free equipment program



1996

Patented BioFresh technology - system for extended storage-life



2004

Innovative LED lighting for energy efficient illumination



2006

Vinidor with adjustable temperature zones



2008

SoftSystem for gentle door closure



2009

SmartSteel finish reduces the visibility of finger prints



2010

DuoCooling for superior performance and efficiency



2013

Super efficient Built-in appliances



2014

Under-worktop TipOpen appliance for seamless integration



2016

BLUPerformance: A new dimension in freshness



2019

SmartDevice - Smart food management



2020

The new dimension for built-in appliances




# The new energy label for electrical appliances.

It is now once again possible to distinguish more easily between efficient and inefficient appliances. With the reform of the energy label, appliances will once again be rated from A to G on the efficiency scale. This will make things much clearer for you in future.

## Technology is developing all the time. And we also never stand still.

We are constantly working on features that make everyday work easier, optimise storage and reduce consumption. We were one of the first manufacturers in Europe to develop fridges and freezers in the highest efficiency class. And that is also our aim for the future. Fridges and freezers work around the clock and are responsible for up to 15 percent of the electricity bill. As our appliances consume less energy, they make an important contribution to climate protection.



- 1 The QR code for identifying the product in the EPREL (European Product Database for Energy Labeling) EU database.
- 2 The model identifier for identifying the product manually in the EPREL EU database, e.g. via the article number.
- 3 The new A to G efficiency scale. However G is only intended for wine coolers.
- 4 The sum of the volumes of the frozen compartment(s).
- 5 The sum of the volumes of the chill compartment(s) and the unfrozen compartment(s).
- 6 The noise level is now also classified into classes A to D.

The label for Great Britain includes the Union Jack.





# Flexible accessories for your appliance

Discover the versatility of the Liebherr range of accessories for your fridge – and make your daily life a little bit easier. Get more from your Liebherr appliance with our range of accessories.



## Organisational systems

Set up your fridge how you want it: In addition to the VarioSafe and the VarioBoxes, to leave room on the shelves for larger items, we have solutions for loose produce such as the variable egg tray and the FlexSystem. Or personalise your wine cabinet with our bottle shelves, presentation shelves and clip on labelling.



## Lifestyle features

Our butter dish offers space for a wide variety of butter sizes and fits perfectly into all shelves. The easy-to-fill ice cube tray is non-spill. Saving energy made easy: With the Vario energy-saving panel, you can reduce the energy consumption of your NoFrost freezer by up to 30% when you are not using all drawers.



## Consumable accessories

Your fridge includes items that are to be replaced on a regular basis for optimal performance. Water and activated carbon filters can be conveniently purchased from your Liebherr retailer. If your Liebherr appliance has a FreshAir filter or water filter, you can find the right size for your model in our webshop.




<https://home.liebherr.com/shop/en/gbr/>

BLU  
Performance

# BluPerformance – A new dimension in refrigeration design

High quality materials, meticulous workmanship in every detail, and easy-to-use, precise touch-electronics define the BluPerformance range. The compact integration of cooling technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics. BioFresh and BioCool ensure lasting quality and freshness for stored foods. In addition, these models are quieter than ever, so will not disturb your living environment.

With elegant and timeless design, BluPerformance appliances are a highlight in any kitchen and are guaranteed to be a pleasure to use for many years to come.



# Multifunction touch control

In the touch-electronic BluPerformance appliances all functions can be easily and conveniently set by gently touching the screen. The high-resolution 7" colour display enables individual settings. Preset programs such as: 'EnergySaver', 'MaxPerformance', 'Party' or 'Holiday' assist in achieving optimum food storage and minimum energy use.

## Day-to-Day

The Day-to-Day program is aimed at meeting everyday requirements. It offers optimum refrigeration performance and efficiency using standard temperature settings in the fridge and freezer compartments.

## EnergySaver

The EnergySaver program lowers energy consumption further, beyond standard settings. To save energy, the temperature in the fridge and freezer compartments is slightly raised. The touch-electronics screen displays useful energy saving tips to help you further reduce electricity costs.

## Party

The Party program is ideal when preparing for celebrations: SuperCool and SuperFrost are activated for the short-term storage and chilling of larger quantities of food. The BottleTimer allows rapid chilling of drinks. Appliances with an IceMaker can increase ice cube production.

## MaxPerformance

The MaxPerformance program allows the appliance to deliver its highest refrigeration performance. It selects lower temperature settings for the fridge and freezer compartments.

## Holiday

The Holiday program minimises energy consumption during extended absences from the home. The fridge compartment is set to +15 °C, and the freezer compartment to -18 °C.





# BioFresh: enjoy lasting freshness

With BioFresh technology food keeps fresh for much longer. When stored at a temperature close to 0 °C and at the correct humidity level, many foods retain their nutrients, such as vitamins and minerals, for far longer than in a conventional fridge compartment.

## Considerably longer shelf life

It is important for newly purchased and freshly harvested foods to be stored properly so that their nutrients are preserved for longer.

The dry conditions in the DrySafe are ideal for storing meat, fish and dairy products.

The shelf life and freshness of most fruit and vegetables can be significantly extended by storing them in a fridge, particularly in the Fruit & Vegetable safe. The high humidity in this storage environment means less liquid is lost from food keeping fruit and vegetables fresh and crisp. By adjusting to low humidity, the Fruit & Vegetable safe can also be used as an additional DrySafe.

## Less packaging is better for the environment

More and more packaging waste is being produced which is harmful to our environment. This is one of the reasons why the Fruit & Vegetable safe was developed. Here fruit and vegetables are best stored unpackaged and they also maintain their freshness for longer. This means there's nothing to stop you shopping at the farmer's market or in the packaging-free supermarket. The practical FlexSystem (depending on model) helps to separate and sort products neatly and cleanly.



Find out more about  
BioFresh:  
[biofresh.liebherr.com/en](https://biofresh.liebherr.com/en)

## Food storage centres



SBSes 8496

# Quality in every detail



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Smart Steel

**SmartSteel** significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



Bio Fresh

**BioFresh** guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.

**BioFresh-Plus** offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps fish and seafood fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile **Fish & Seafood-Safe**.



Bio Fresh Plus



No Frost

The **NoFrost** system provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost free.



Find out more about NoFrost: [nofrost.liebherr.com/en](http://nofrost.liebherr.com/en)



Ice Maker

The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party – there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

The features shown are model dependent; look for these features in your model choice.



SBSes 8496

Side-by-Side fridge-freezer



←121→

SBSes 8496  
PremiumPlus

SWTNes 4285  
PremiumPlus

- Duo Cooling
- No Frost
- Soft System
- Ice Maker
- Smart Steel
- Smart Device ready
- Wine

Energy efficiency class:
Energy consumption year / 24 hrs: 187 / 0.512 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l: 48 <sup>1</sup>
Total volume <sup>3</sup> : 289 litre
Volume: Wine compartment: 156.4 litre / Freezer compartment: 132.8 litre
Noise output: 37 dB(A) / C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 60 / 68.5 <sup>1</sup>

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for wine and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm wine and freezer compartment: visual and acoustic

Freezer compartment

- 5 drawers, of which 2 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 1.8 kg capacity
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

Wine compartment

- 2 separately controllable temperature zones, which can be regulated between +5 °C to +20 °C
- Tinted insulated glass door with UV protection
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 4 shelves, of which 4 on telescopic rails and 2 foldable
- Partially-foldable wooden shelf on telescopic rails
- LED lighting permanently on, dimmable

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front and back, transport castors at back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

SKBes 4380  
PremiumPlus

- Bio Fresh Plus
- Soft System
- Smart Steel
- Smart Device ready
- Soft-Telescopic

Energy efficiency class:
Energy consumption year / 24 hrs: 133 / 0.364 kWh <sup>2</sup>
Total volume <sup>3</sup> : 371 litre
Volume: Fridge: 235.7 litre / BioFresh compartment: 135.8 litre
Noise output: 36 dB(A) / C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- BioFresh-Plus with Fish & Seafood-Safe
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>3</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBSbs 8683  
Premium

SBSes 8773  
Premium

<b>SGNbs 4385</b> Premium	No Frost	Soft System	LED	Ice Maker	Black Steel	Smart Device ready	Telescopic Rails
Energy efficiency class:							
Energy consumption year / 24 hrs: 198/0.542 kWh <sup>1</sup>							
Total volume <sup>2</sup> : 276 litre							
Noise output: 37 dB(A)/C							
Climate rating: SN-T (from +10 °C to +43 °C)							
Door /side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel							
Exterior dimensions in cm (h/w/d): 185/60/66.5 <sup>1</sup>							

<b>SKBbs 4370</b> Premium	Bio Fresh	Soft System	Black Steel	Smart Device ready	Soft-Telescopic
Energy efficiency class:					
Energy consumption year / 24 hrs: 133/0.364 kWh <sup>1</sup>					
Total volume <sup>2</sup> : 372 litre					
Volume: Fridge: 235.7 litre /BioFresh compartment: 137.2 litre					
Noise output: 36 dB(A)/C					
Climate rating: SN-T (from +10 °C to +43 °C)					
Door /side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel					
Exterior dimensions in cm (h/w/d): 185/60/66.5 <sup>1</sup>					

<b>SGNes 4375</b> Premium	No Frost	Soft System	LED	Smart Steel	Smart Device ready	Telescopic Rails
Energy efficiency class:						
Energy consumption year / 24 hrs: 198/0.542 kWh <sup>1</sup>						
Total volume <sup>2</sup> : 276 litre						
Noise output: 37 dB(A)/C						
Climate rating: SN-T (from +10 °C to +43 °C)						
Door /side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel						
Exterior dimensions in cm (h/w/d): 185/60/66.5 <sup>1</sup>						

<b>SKBes 4370</b> Premium	Bio Fresh	Soft System	Smart Steel	Smart Device ready	Soft-Telescopic
Energy efficiency class:					
Energy consumption year / 24 hrs: 133/0.364 kWh <sup>1</sup>					
Total volume <sup>2</sup> : 372 litre					
Volume: Fridge: 235.7 litre /BioFresh compartment: 137.2 litre					
Noise output: 36 dB(A)/C					
Climate rating: SN-T (from +10 °C to +43 °C)					
Door /side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel					
Exterior dimensions in cm (h/w/d): 185/60/66.5 <sup>1</sup>					

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinge, left</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 9 drawers, of which 5 set on telescopic rails, of which 1 set on roller tracks, VarioSpace</li><li>· IceMaker with fixed 3/4" water connection</li><li>· Ice cube production in 24 hrs: 0.8 kg</li><li>· Ice cube reservoir 0.8 kg capacity</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 18 kg</li><li>· 2 Cold storage accumulators</li><li>· Safety glass fittings</li></ul>	

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and BioFresh compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Variable bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· LED BioFresh lighting</li><li>· LED rear wall lighting</li><li>· 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>	

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinge, left</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 18 kg</li><li>· 2 Cold storage accumulators</li><li>· Safety glass fittings</li></ul>	

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and BioFresh compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Variable bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· LED BioFresh lighting</li><li>· LED rear wall lighting</li><li>· 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>	

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBNes 8483  
Premium

SGNef 7242  
Comfort

SBNes 4285  
Premium

SKes 4370  
Premium

SGNef 3036  
Comfort

SKef 4260  
Comfort

Energy efficiency class:
Energy consumption year / 24 hrs: 171 / 0.468 kWh <sup>1</sup>
Total volume <sup>2</sup> : 311 litre
Volume: BioFresh compartment: 179.1 litre / Freezer compartment: 132.8 litre
Noise output: 36 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>

Energy efficiency class:
Energy consumption year / 24 hrs: 78 / 0.213 kWh <sup>1</sup>
Total volume <sup>2</sup> : 395 litre
Noise output: 36 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>

Energy efficiency class:
Energy consumption year / 24 hrs: 306 / 0.838 kWh <sup>1</sup>
Total volume <sup>2</sup> : 268 litre
Noise output: 41 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel/ silver
Exterior dimensions in cm (h / w / d): 185.2 / 60 / 62.3 <sup>1</sup>

Energy efficiency class:
Energy consumption year / 24 hrs: 151 / 0.413 kWh <sup>1</sup>
Total volume <sup>2</sup> : 385 litre
Noise output: 33 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel/ silver
Exterior dimensions in cm (h / w / d): 185.2 / 60 / 62.3 <sup>1</sup>

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for BioFresh and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 5 drawers, of which 2 set on roller tracks, VarioSpace</li><li>· IceMaker with fixed 3/4" water connection</li><li>· Ice cube production in 24 hrs: 1.2 kg</li><li>· Ice cube reservoir 1.8 kg capacity</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Temperature rise time: 16 h</li><li>· Freezing capacity in 24 hrs: 9 kg</li><li>· 2 Cold storage accumulators</li><li>· Safety glass fittings</li></ul>
<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· 2 GlassLine shelves in the BioFresh compartment, of which one is divided into two parts</li><li>· LED ceiling lighting with dimmer function</li><li>· LED BioFresh lighting</li><li>· 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinge, left</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge compartment</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 6 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· 2 BioCool-Boxes on telescopic rails</li></ul>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, key electronic</li><li>· Digital temperature display</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 8 drawers, of which 1 herb and berry tray, VarioSpace</li><li>· Temperature rise time: 8.5 h</li><li>· Freezing capacity in 24 hrs: 15.9 kg</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Fixed door hinge, left</li><li>· Replaceable door seal</li></ul>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, touch electronic</li><li>· Digital temperature display for fridge compartment</li><li>· Automatic SuperCool</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: acoustic</li></ul>	<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 7 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on telescopic rails</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Fixed door hinge, right</li><li>· Replaceable door seal</li></ul>	

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Quality in every detail



The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



Bio  
Fresh

Both **BioFresh drawers** are mounted on **telescopic rails** which extend effortlessly providing easy access to and a full view of your food. The lateral **LED lights** ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



No  
Frost

Ice  
Maker

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated **water filter** ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The **NoFrost** technology keeps the freezer constantly frostfree.



LED

The interior features **LED light columns** integrated on either side of the refrigerator, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. The elegant, high quality **GlassLine** interior is adaptable to suit individual requirements.



← 91 →

**CBNes 6256**  
PremiumPlus

Bio  
Fresh

Duo  
Cooling

No  
Frost

Ice  
Maker

Energy efficiency class: **F** **A** **G**

Energy consumption year / 24 hrs: 341 / 0.934 kWh

Total volume <sup>1</sup>: 522 litre

Volume: Fridge: 292.2 litre / BioFresh compartment: 70.6 litre / Freezer compartment: 159.5 litre

Noise output: 42 dB(A)/D

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel / stainless steel

Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5

## Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

## Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, adjustable egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

## Freezer compartment **\*\*\*\***

- 2 drawers on telescopic, self-retracting rails
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir 2.7 kg capacity
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

## Key features

- HardLine
- Aluminium handles
- Versatile installation due to front ventilation
- Front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



# Fridge-freezers



CBNef 5735

# Our fridge-freezers: an overview

Liebherr's extensive range of fridge-freezers offers the ideal solution for almost everyone – whatever your demands and needs are. Our fridge-freezers offer innovative features such as BioFresh or BioCool and NoFrost or SmartFrost. Once you have made your preferred choice, all of our appliances are available with a variety of fittings and come in various sizes and colours.



**Bio Fresh**

When stored under BioFresh conditions, at just above 0 °C and at the ideal humidity level, fruit, vegetables, meat, fish and dairy products retain their nutrients, delicate flavour, and appetising appearance for much longer than they do under normal fridge conditions.

**Bio Cool**

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient to use and it ensures that stored food is clearly visible.

**No Frost**

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

**Smart Frost**

SmartFrost offers great convenience: the freezer compartment seldom requires defrosting, and the interior and frozen food frost over far less. In addition, the smooth interior walls are easy to clean.

# Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost:  
[nofrost.liebherr.com](http://nofrost.liebherr.com)



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves are made of safety glass and can be removed easily.



Bio Fresh

**BioFresh** guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.



Ice Maker

If the quality of the mains water is poor or there is no plumbed-in connection, the CNef 5745 offers the **IceMaker with a water tank** supply. With a 1.2 litre capacity and a practical handle, this can be easily removed and filled.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clearly visible. The humidity level in the BioCool-Box is regulated using a slide control.

The features shown are model dependent; look for these features in your model choice.

# Quality in every detail




The sturdy **handle with** its refined, premium-quality appearance and **an integrated opening mechanism** ensures easy and effortless opening of the door. The handle perfectly complements the Hardline door design, and is made from anodised aluminium or white plastic. It can be easily repositioned if the hinge side of the door is changed.



## Duo Cooling

With two independently controlled cooling circuits, **DuoCooling** controls the temperature in fridge-freezers with precision. There is no air exchange between the fridge and freezer compartments, odour transfer is prevented and stored food does not dry out. Also, the refrigeration compartment can be switched off while the freezer compartment continues operating. This can be useful, for example, when going on holiday.



**BluPerformance** models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug
2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor
4. Plinth fan with noise-damping
5. Condenser
6. Defrost water drain



## Smart Steel

**SmartSteel** significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.



The **replaceable door seal** optimally supports safe food storage. It is designed to match the appliance door or housing colour and can be easily inserted, cleaned or replaced, ensuring that spotless hygiene standards can be consistently met.



The clear, minimalist style of **HardLine-Design** lends a real sense of elegance to the appliances. Consistently applied throughout the appliance, internally and externally, this linear design creates a pristine overall appearance.

The features shown are model dependent; look for these features in your model choice.

# Quality in every detail



**Telescopic Rails**

The BioFresh safes on **telescopic rails** are easy to access and use even when filled with heavy contents. They ensure both great visibility and optimum storage.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Models in the Comfort range feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort Glassline comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables accurate temperature settings.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles.



The automatic **SuperFrost** function makes freezing food simple and energy efficient. It rapidly lowers the temperature to  $-32^{\circ}\text{C}$  to create the coldness levels required to preserve vitamins during freezing. The automatic **SuperCool** function lowers the refrigerator temperature to  $+2^{\circ}\text{C}$  for a defined period of 3, 6, 9 or 12 hours, offering flexibility according to the amount of food stored.

The features shown are model dependent; look for these features in your model choice.

BioFresh NoFrost fridge-freezers



CBNeS 5775  
Premium

Bio Fresh

Duo Cooling

No Frost

Super Silent

Soft System

Smart Steel

Smart Device ready

Soft-Telescopic

Energy efficiency class: <div>B A G 1</div>
Energy consumption year / 24 hrs: 149/0.408 kWh <sup>1</sup>
Total volume <sup>2</sup> : 392 litre
Volume: Fridge: 168.5 litre / BioFresh compartment: 112.6 litre / Freezer compartment: 111.6 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201/70/66.5 <sup>1</sup>

**Controls**

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

**Freezer compartment**

\*\*\*\*

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting

**2 BioFresh-Safes with SoftTelescopic**, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

CBNef 5735  
Comfort

Bio Fresh

Duo Cooling

No Frost

Smart Steel

Smart Device ready

Energy efficiency class: <div>D A G 1</div>
Energy consumption year / 24 hrs: 234/0.641 kWh <sup>1</sup>
Total volume <sup>2</sup> : 392 litre
Volume: Fridge: 168.5 litre / BioFresh compartment: 112.6 litre / Freezer compartment: 111.6 litre
Noise output: 36 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/ silver
Exterior dimensions in cm (h/w/d): 201/70/66.5 <sup>1</sup>

**Controls**

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

**Freezer compartment**

\*\*\*\*

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

CBNes 4898  
PremiumPlus

Bio Fresh Plus

Duo Cooling

No Frost

Super Silent

Soft System

Ice Maker

Smart Steel

Smart Device ready

Soft-Telescopic

Energy efficiency class: <div>C A G 1</div>
Energy consumption year / 24 hrs: 182/0.498 kWh <sup>1</sup>
Total volume <sup>2</sup> : 349 litre
Volume: Fridge: 147.5 litre / BioFresh compartment: 97.9 litre / Freezer compartment: 104.2 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201/60/66.5 <sup>1</sup>

**Controls**

- 7" TFT-colour display in-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

**Freezer compartment**

\*\*\*\*

- 4 drawers, of which 1 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 1.8 kg capacity
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- BioFresh-Plus

**2 BioFresh-Safes with SoftTelescopic**, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe, 1 FlexSystem

CBNes 4875  
Premium

Bio Fresh

Duo Cooling

No Frost

Super Silent

Soft System

Smart Steel

Smart Device ready

Soft-Telescopic

Energy efficiency class: <div>B A G 1</div>
Energy consumption year / 24 hrs: 145/0.397 kWh <sup>1</sup>
Total volume <sup>2</sup> : 351 litre
Volume: Fridge: 147.5 litre / BioFresh compartment: 100.9 litre / Freezer compartment: 103.5 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/ Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201/60/66.5 <sup>1</sup>

**Controls**

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

**Freezer compartment**

\*\*\*\*

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

**Key features**

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

**Fridge and BioFresh compartments**

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting

**2 BioFresh-Safes with SoftTelescopic**, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

BioCool NoFrost fridge-freezers



<b>CNef 5745</b> Comfort	Bio Cool	Duo Cooling	No Frost	Ice Maker Water tank	Smart Steel	Smart Device ready
Energy efficiency class:						
Energy consumption year / 24 hrs: 210/0.575 kWh <sup>1</sup>						
Total volume <sup>2</sup> : 411 litre						
Volume: Fridge: 299.2 litre / Freezer compartment: 112.2 litre						
Noise output: 36 dB(A)/C						
Climate rating: SN-T (from +10 °C to +43 °C)						
Door / side walls: Stainless steel with SmartSteel / silver						
Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 <sup>1</sup>						

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· IceMaker with water tank</li><li>· Ice cube production in 24 hrs: 1.2 kg</li><li>· Ice cube reservoir 2.2 kg capacity</li><li>· Ice cube tray</li><li>· Temperature rise time: 16 h</li><li>· Freezing capacity in 24 hrs: 9 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 BioCool-Box on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>CNef 5735</b> Comfort	Bio Cool	Duo Cooling	No Frost	Smart Steel	Smart Device ready
Energy efficiency class:					
Energy consumption year / 24 hrs: 210/0.575 kWh <sup>1</sup>					
Total volume <sup>2</sup> : 410 litre					
Volume: Fridge: 299.2 litre / Freezer compartment: 111.6 litre					
Noise output: 36 dB(A)/C					
Climate rating: SN-T (from +10 °C to +43 °C)					
Door / side walls: Stainless steel with SmartSteel / silver					
Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 <sup>1</sup>					

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· Temperature rise time: 16 h</li><li>· Freezing capacity in 24 hrs: 9 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Comfort GlassLine storage shelf with bottle holder, adjustable egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 BioCool-Box on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

NoFrost fridge-freezers



<b>CNef 4015</b> Comfort	Duo Cooling	No Frost	Smart Steel	Smart Device ready
Energy efficiency class:				
Energy consumption year / 24 hrs: 245/0.671 kWh <sup>1</sup>				
Total volume <sup>2</sup> : 365 litre				
Volume: Fridge: 270.5 litre / Freezer compartment: 95.3 litre				
Noise output: 38 dB(A)/C				
Climate rating: SN-T (from +10 °C to +43 °C)				
Door / side walls: Stainless steel with SmartSteel / silver				
Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 <sup>1</sup>				

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 10.8 h</li><li>· Freezing capacity in 24 hrs: 8.2 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

<b>CN 3915</b> Comfort	Duo Cooling	No Frost	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 260/0.712 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 350 litre			
Volume: Fridge: 222.4 litre / Freezer compartment: 128.3 litre			
Noise output: 38 dB(A)/C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· 4 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 12.1 h</li><li>· Freezing capacity in 24 hrs: 9 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

**Colour / material options:**  
**CNbs 3915** in BlackSteel  
**CNef 3915** with Stainless steel front

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

NoFrost fridge-freezers



<b>CNeF 3515</b> Comfort	Duo Cooling	No Frost	Smart Steel	Smart Device ready
Energy efficiency class:				
Energy consumption year / 24 hrs: 246 / 0.674 kWh <sup>1</sup>				
Total volume <sup>2</sup> : 317 litre				
Volume: Fridge: 222.4 litre / Freezer compartment: 95.3 litre				
Noise output: 38 dB(A) / C				
Climate rating: SN-T (from +10 °C to +43 °C)				
Door / side walls: Stainless steel with SmartSteel / silver				
Exterior dimensions in cm (h / w / d): 181.7 / 60 / 62.5 <sup>1</sup>				

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment </b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.32 h</li><li>· Freezing capacity in 24 hrs: 6.2 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

<b>CN 3515</b> Comfort	Duo Cooling	No Frost	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 246 / 0.674 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 317 litre			
Volume: Fridge: 222.4 litre / Freezer compartment: 95.3 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 181.7 / 60 / 62.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment </b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.32 h</li><li>· Freezing capacity in 24 hrs: 6.2 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

<b>CNef 3115</b> Comfort	Duo Cooling	No Frost	Smart Steel	Smart Device ready
Energy efficiency class:				
Energy consumption year / 24 hrs: 235 / 0.643 kWh <sup>1</sup>				
Total volume <sup>2</sup> : 269 litre				
Volume: Fridge: 174.4 litre / Freezer compartment: 95.3 litre				
Noise output: 38 dB(A) / C				
Climate rating: SN-T (from +10 °C to +43 °C)				
Door / side walls: Stainless steel with SmartSteel / silver				
Exterior dimensions in cm (h / w / d): 162.3 / 60 / 62.5 <sup>1</sup>				

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment </b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.3 h</li><li>· Freezing capacity in 24 hrs: 7.3 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 3 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

<b>CN 3115</b> Comfort	Duo Cooling	No Frost	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 235 / 0.643 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 269 litre			
Volume: Fridge: 174.4 litre / Freezer compartment: 95.3 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 162.3 / 60 / 62.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: visual and acoustic</li></ul>	<b>Freezer compartment </b> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.3 h</li><li>· Freezing capacity in 24 hrs: 7.3 kg</li><li>· Safety glass fittings</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 3 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED ceiling lighting</li><li>· 2 fruit and vegetable drawers on roller tracks</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handles with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



CNeI 4813

NoFrost fridge-freezers



← 60 →




← 60 →

CNeI 4813

Duo Cooling

No Frost

Stainless Steel Look

Energy efficiency class: 

Energy consumption year / 24 hrs: 251 / 0.687 kWh <sup>1</sup>

Total volume<sup>2</sup>: 344 litre

Volume: Fridge: 243.2 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel look / silver

Exterior dimensions in cm (h / w / d): 201.1 / 60 / 65.5 <sup>1</sup>

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment 

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg


Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CN 4813

Duo Cooling

No Frost

Energy efficiency class: 

Energy consumption year / 24 hrs: 251 / 0.687 kWh <sup>1</sup>

Total volume<sup>2</sup>: 344 litre

Volume: Fridge: 243.2 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 201.1 / 60 / 65.5 <sup>1</sup>

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment 

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal


<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.


You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.


NoFrost fridge-freezers





CN 4713	Duo Cooling	No Frost
Energy efficiency class:  <sup>1</sup>		
Energy consumption year / 24 hrs: 246 / 0.674 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 334 litre		
Volume: Fridge: 199.4 litre / Freezer compartment: 134.8 litre		
Noise output: 40 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 201.1 / 60 / 65.5 <sup>1</sup>		


<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, key electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b>  <sup>1</sup> <ul style="list-style-type: none"><li>· 4 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 12 h</li><li>· Freezing capacity in 24 hrs: 9.5 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Vertical recessed handles</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>


CNel 4213	Duo Cooling	No Frost	Stainless Steel Look
Energy efficiency class:  <sup>1</sup>			
Energy consumption year / 24 hrs: 248 / 0.679 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 300 litre			
Volume: Fridge: 165.6 litre / Freezer compartment: 134.8 litre			
Noise output: 40 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: Stainless steel look / silver			
Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, key electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Plastic door shelves, Egg tray</li><li>· 3 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b>  <sup>1</sup> <ul style="list-style-type: none"><li>· 4 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 12 h</li><li>· Freezing capacity in 24 hrs: 9.5 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Vertical recessed handles</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>
<b>Colour / material options:</b> <b>CN 4213</b> in white

CNP 4313	Duo Cooling	No Frost
Energy efficiency class:  <sup>1</sup>		
Energy consumption year / 24 hrs: 197 / 0.539 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 310 litre		
Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre		
Noise output: 39 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, key electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b>  <sup>1</sup> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.6 h</li><li>· Freezing capacity in 24 hrs: 8 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Vertical recessed handles</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>

CN 4313	Duo Cooling	No Frost
Energy efficiency class:  <sup>1</sup>		
Energy consumption year / 24 hrs: 246 / 0.674 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 310 litre		
Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre		
Noise output: 40 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye behind-the-door, key electronic</li><li>· Digital temperature display for fridge and freezer compartments</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm fridge and freezer compartment: acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b>  <sup>1</sup> <ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Ice cube tray</li><li>· Temperature rise time: 11.6 h</li><li>· Freezing capacity in 24 hrs: 8 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Vertical recessed handles</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li></ul>
<b>Colour / material options:</b> <b>CNel 4313</b> with Stainless steel look

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



CNNo 4313

NoFrost fridge-freezers



← 60 →



← 60 →



← 60 →

CNNo 4313

Duo Cooling	No Frost	Colour Line
-------------	----------	-------------

Energy efficiency class:

Energy consumption year/24 hrs: 246/0.674 kWh <sup>1</sup>

Total volume<sup>2</sup>: 310 litre

Volume: Fridge: 209.4 litre/  
Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: NeonOrange/NeonOrange

Exterior dimensions in cm (h/w/d): 186.1/60/65.5 <sup>1</sup>

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CNkw 4313

Duo Cooling	No Frost	Colour Line
-------------	----------	-------------

Energy efficiency class:

Energy consumption year/24 hrs: 246/0.674 kWh <sup>1</sup>

Total volume<sup>2</sup>: 310 litre

Volume: Fridge: 209.4 litre/  
Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: KiwiGreen/KiwiGreen

Exterior dimensions in cm (h/w/d): 186.1/60/65.5 <sup>1</sup>

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CNfb 4313

Duo Cooling	No Frost	Colour Line
-------------	----------	-------------

Energy efficiency class:

Energy consumption year/24 hrs: 246/0.674 kWh <sup>1</sup>

Total volume<sup>2</sup>: 310 litre

Volume: Fridge: 209.4 litre/  
Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: FrozenBlue/FrozenBlue

Exterior dimensions in cm (h/w/d): 186.1/60/65.5 <sup>1</sup>

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm.

If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



<b>CUel 3331</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 280 / 0.767 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 296 litre	
Volume: Fridge: 212.4 litre / Freezer compartment: 84.1 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: Stainless steel look / silver	
Exterior dimensions in cm (h / w / d): 181.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 4 GlassLine storage shelves</div><div>· Bottle shelf</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 3 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 20 h</div><div>· Freezing capacity in 24 hrs: 3.8 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<b>CU 3331</b>	<div>Smart Frost</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 280 / 0.767 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 296 litre	
Volume: Fridge: 212.4 litre / Freezer compartment: 84.1 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 181.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 4 GlassLine storage shelves</div><div>· Bottle shelf</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 3 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 20 h</div><div>· Freezing capacity in 24 hrs: 3.8 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<b>CUel 2831</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 240 / 0.657 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 265 litre	
Volume: Fridge: 212.4 litre / Freezer compartment: 53.5 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: Stainless steel look / silver	
Exterior dimensions in cm (h / w / d): 161.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 4 GlassLine storage shelves</div><div>· Bottle shelf</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 2 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 18 h</div><div>· Freezing capacity in 24 hrs: 3 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<b>CU 2831</b>	<div>Smart Frost</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 240 / 0.657 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 265 litre	
Volume: Fridge: 212.4 litre / Freezer compartment: 53.5 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 161.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 4 GlassLine storage shelves</div><div>· Bottle shelf</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 2 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 18 h</div><div>· Freezing capacity in 24 hrs: 3 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<b>CUel 2331</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 241 / 0.660 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 210 litre	
Volume: Fridge: 156.5 litre / Freezer compartment: 53.5 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: Stainless steel look / silver	
Exterior dimensions in cm (h / w / d): 137.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 3 GlassLine storage shelves</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 2 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 18 h</div><div>· Freezing capacity in 24 hrs: 3 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<b>CU 2331</b>	<div>Smart Frost</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 241 / 0.660 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 210 litre	
Volume: Fridge: 156.5 litre / Freezer compartment: 53.5 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 137.2 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
<div><div>· Mechanical control in interior, control dial</div><div>· Individually regulated cooling circuits: 1</div><div>· CoolPlus function</div></div>
<b>Fridge compartment</b>
<div><div>· Plastic door shelves, Egg tray</div><div>· 3 GlassLine storage shelves</div><div>· LED lighting</div><div>· 2 fruit and vegetable drawers</div></div>
<b>Freezer compartment</b> <div>***</div>
<div><div>· 2 drawers, VarioSpace</div><div>· Ice cube tray</div><div>· Temperature rise time: 18 h</div><div>· Freezing capacity in 24 hrs: 3 kg</div><div>· Safety glass fittings</div></div>
<b>Key features</b>
<div><div>· SwingLine design</div><div>· Recessed handles</div><div>· Versatile installation due to front ventilation</div><div>· Height-adjustable feet at front</div><div>· Reversible door hinging</div></div>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



CUno 2831

CUkw 2831

CUfb 2831

SmartFrost fridge-freezers



← 55 →




← 55 →



← 55 →

CUno 2831



Energy efficiency class:

Energy consumption year/24 hrs: 240/0.657 kWh <sup>1</sup>

Total volume<sup>2</sup>: 265 litre

Volume: Fridge: 212.4 litre/  
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: NeonOrange/NeonOrange

Exterior dimensions in cm (h/w/d): 161.2/55/63 <sup>1</sup>

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers


Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUkw 2831



Energy efficiency class:

Energy consumption year/24 hrs: 240/0.657 kWh <sup>1</sup>

Total volume<sup>2</sup>: 265 litre

Volume: Fridge: 212.4 litre/  
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: KiwiGreen/KiwiGreen

Exterior dimensions in cm (h/w/d): 161.2/55/63 <sup>1</sup>

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUfb 2831



Energy efficiency class:

Energy consumption year/24 hrs: 240/0.657 kWh <sup>1</sup>

Total volume<sup>2</sup>: 265 litre

Volume: Fridge: 212.4 litre/  
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: FrozenBlue/FrozenBlue

Exterior dimensions in cm (h/w/d): 161.2/55/63 <sup>1</sup>

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm.

If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.




<b>CTel 2931</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class:	<div>F</div> <div>A</div> <div>G</div> <sup>1</sup>
Energy consumption year / 24 hrs:	231 / 0.632 kWh <sup>1</sup>
Total volume <sup>2</sup> :	270 litre
Volume: Fridge:	218.6 litre/
Freezer compartment:	51.5 litre
Noise output:	37 dB(A)/C
Climate rating:	SN-T (from +10 °C to +43 °C)
Door / side walls:	Stainless steel look/silver
Exterior dimensions in cm (h/w/d):	157.1 / 55 / 63 <sup>1</sup>


<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 19.54 h
· Freezing capacity in 24 hrs: 3.32 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

CT 2931	<div>Smart Frost</div>
Energy efficiency class: <div>F A G<sup>1</sup></div>	
Energy consumption year / 24 hrs: 231 / 0.632 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 270 litre	
Volume: Fridge: 218.6 litre/ Freezer compartment: 51.5 litre	
Noise output: 37 dB(A)/C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door/side walls: white/white	
Exterior dimensions in cm (h/w/d): 157.1 / 55 / 63 <sup>1</sup>	


<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 19.54 h
· Freezing capacity in 24 hrs: 3.32 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

<b>CTel 2531</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class:  <sup>1</sup>	
Energy consumption year / 24 hrs: 212 / 0.580 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 233 litre	
Volume: Fridge: 189.5 litre /	
Freezer compartment: 43.8 litre	
Noise output: 37 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: Stainless steel look / silver	
Exterior dimensions in cm (h / w / d): 140.1 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 3 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 17.12 h
· Freezing capacity in 24 hrs: 3.56 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

<b>CT 2531</b>	<div>Smart Frost</div>
Energy efficiency class:  <sup>1</sup>	
Energy consumption year / 24 hrs: 212 / 0.580 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 233 litre	
Volume: Fridge: 189.5 litre /	
Freezer compartment: 43.8 litre	
Noise output: 37 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 140.1 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 3 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 17.12 h
· Freezing capacity in 24 hrs: 3.56 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

<b>CTel 2131</b>	<div>Smart Frost</div> <div>Stainless Steel Look</div>
Energy efficiency class:  <sup>1</sup>	
Energy consumption year / 24 hrs: 198 / 0.542 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 196 litre	
Volume: Fridge: 152.2 litre /	
Freezer compartment: 43.8 litre	
Noise output: 37 dB(A)/C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door/side walls: Stainless steel look/silver	
Exterior dimensions in cm (h/w/d): 124.1 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 3 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 17.3 h
· Freezing capacity in 24 hrs: 3.74 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

CT 2131	<div>Smart Frost</div>
Energy efficiency class: <div>F A G</div> <sup>1</sup>	
Energy consumption year / 24 hrs: 198 / 0.542 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 196 litre	
Volume: Fridge: 152.2 litre /	
Freezer compartment: 43.8 litre	
Noise output: 37 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door/side walls: white / white	
Exterior dimensions in cm (h / w / d): 124.1 / 55 / 63 <sup>1</sup>	

<b>Controls</b>
· Mechanical control in interior, control dial
· Individually regulated cooling circuits: 1
<b>Fridge compartment</b>
· Plastic door shelves, Egg tray
· 3 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
<b>Freezer compartment</b> <div>****</div>
· Ice cube tray
· Temperature rise time: 17.3 h
· Freezing capacity in 24 hrs: 3.74 kg
· Safety glass fittings
<b>Key features</b>
· SwingLine design
· Recessed handles
· Versatile installation due to front ventilation
· Height-adjustable feet at front
· Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Fridges



KBeF 4330

# Our fridges: an overview

Liebherr fridges excel with their impressive freshness technology. The range on offer extends from models featuring a classic vegetable compartment, to BioCool models with an adjustable humidity compartment, all the way to BioFresh appliances, which deliver the longest-lasting freshness. Whatever you're looking for, you're sure to find just the right fridge to meet your needs and requirements within Liebherr's comprehensive range – be it an upright or under counter appliance.

## Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately maintained at around 0 °C.

## Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.

## Fridges



## Under counter fridges



# Quality in every detail



Bio  
Fresh

The fresher your food, the better it is for a healthy diet. **BioFresh safes**, sited on telescopic rails, guarantee the perfect environment for greater freshness. When stored at a temperature of just over 0 °C and at just the right humidity level, fruit and vegetables, fish, meat and dairy products all retain their vitamins, delicate flavours and appetising appearance for far longer than in a conventional fridge compartment.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Models in the Comfort range feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort GlassLine comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



Bio  
Cool

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



The sturdy **handle** with its refined, premium-quality appearance and an **integrated opening mechanism** ensures easy and effortless opening of the door. The handle perfectly complements the HardLine door design, and is made from anodised aluminium or white plastic. It can be easily repositioned if the hinge side of the door is changed.

The features shown are model dependent; look for these features in your model choice.

# Quality in every detail



LED



The clear, minimalist style of **HardLine-Design** lends a real sense of elegance to the appliances. Consistently applied throughout the appliance, internally and externally, this linear design creates a pristine overall appearance.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



Smart Steel

**SmartSteel** significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



In BioFresh Comfort models, the **integrated bottle shelf** offers two options: With the glass shelf, it can be used as a storage shelf for cups, bowls and other containers or – if the glass shelf is removed – as a handy bottle shelf.

The features shown are model dependent; look for these features in your model choice.

BioFresh fridges



<b>KBies 4370</b> Premium	Bio Fresh	Soft System	Smart Steel	Smart Device	Soft-Telescopic
Energy efficiency class:					
Energy consumption year / 24 hrs: 107 / 0.293 kWh <sup>1</sup>					
Total volume <sup>2</sup> : 372 litre					
Volume: Fridge: 235.7 litre / BioFresh compartment: 137.2 litre					
Noise output: 36 dB(A) / C					
Climate rating: SN-T (from +10 °C to +43 °C)					
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel					
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>					

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and BioFresh compartments</li><li>· SmartDeviceBox included</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Integrated bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· LED BioFresh lighting</li><li>· LED rear wall lighting</li><li>· 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>	

<b>KBbs 4370</b> Premium	Bio Fresh	Soft System	Black Steel	Smart Device ready	Soft-Telescopic
Energy efficiency class:					
Energy consumption year / 24 hrs: 107 / 0.293 kWh <sup>1</sup>					
Total volume <sup>2</sup> : 372 litre					
Volume: Fridge: 235.7 litre / BioFresh compartment: 137.2 litre					
Noise output: 36 dB(A) / C					
Climate rating: SN-T (from +10 °C to +43 °C)					
Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel					
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>					

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and BioFresh compartments</li><li>· SmartDeviceBox included</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Integrated bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· LED BioFresh lighting</li><li>· LED rear wall lighting</li><li>· 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>	

<b>KB 4330</b> Comfort	Bio Fresh	Smart Device ready
Energy efficiency class:		
Energy consumption year / 24 hrs: 133 / 0.364 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 371 litre		
Volume: Fridge: 234.5 litre / BioFresh compartment: 137.2 litre		
Noise output: 37 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge and BioFresh compartments</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Comfort GlassLine storage shelf with bottle holder, adjustable egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Integrated bottle shelf</li><li>· LED ceiling lighting</li><li>· 3 BioFresh-Safes on telescopic rails, of which 2 variably adjustable from Fruit &amp; Vegetable-Safe to DrySafe</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>	
<b>Colour / material options:</b> <b>KBef 4330</b> with Stainless steel front	


<b>B 2830</b> Comfort	Bio Fresh	Smart Device ready
Energy efficiency class:		
Energy consumption year / 24 hrs: 65 / 0.178 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 161 litre		
Noise output: 38 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h / w / d): 125 / 60 / 66.5 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>	<b>Fridge and BioFresh compartments</b> <ul style="list-style-type: none"><li>· Ventilator</li><li>· LED lighting</li><li>· 5 BioFresh-Safes</li><li>· Cabinet can be adjusted from HydroSafe to DrySafe</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>	


<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.




<b>Kef 4370</b> Premium	Bio Cool	Soft System	Smart Steel	Smart Device ready
Energy efficiency class:  <sup>1</sup>				
Energy consumption year / 24 hrs: 78 / 0.213 kWh <sup>1</sup>				
Total volume <sup>2</sup> : 395 litre				
Noise output: 36 dB(A) / C				
Climate rating: SN-T (from +10 °C to +43 °C)				
Door / side walls: Stainless steel with SmartSteel / silver				
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>				


<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-colour display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge compartment</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish</li><li>· 6 GlassLine storage shelves, of which one is divided into two parts</li><li>· VarioSafe</li><li>· Bottle shelf</li><li>· LED ceiling lighting with dimmer function</li><li>· 2 BioCool-Boxes on telescopic rails</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>Kef 4330</b> Comfort	Bio Cool	Smart Steel	Smart Device ready
Energy efficiency class:  <sup>1</sup>			
Energy consumption year / 24 hrs: 98 / 0.268 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 395 litre			
Noise output: 37 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: Stainless steel with SmartSteel / silver			
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge compartment</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Comfort GlassLine storage shelf with bottle holder, adjustable egg tray</li><li>· 6 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 2 BioCool-Boxes on telescopic rails</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Aluminium handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Colour / material options:</b> <b>K 4330</b> in white

<b>K 3730</b> Comfort	Bio Cool	Smart Device ready
Energy efficiency class:  <sup>1</sup>		
Energy consumption year / 24 hrs: 93 / 0.254 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 346 litre		
Noise output: 37 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Door / side walls: white / white		
Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display for fridge compartment</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperCool (time restricted)</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling with FreshAir activated charcoal filter</li><li>· Comfort GlassLine storage shelf with bottle holder, adjustable egg tray</li><li>· 6 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED ceiling lighting</li><li>· 1 BioCool-Box on telescopic rails</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>
<b>Colour / material options:</b> <b>Kef 3730</b> with Stainless steel front

<b>Ksl 3130</b> Comfort	Silver
Energy efficiency class:  <sup>1</sup>	
Energy consumption year / 24 hrs: 139 / 0.380 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 297 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: silver / silver	
Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63.1 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display for fridge compartment</li><li>· Automatic SuperCool</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 6 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingLine design</li><li>· Stainless steel slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li></ul>
<b>Colour / material options:</b> <b>K 3130</b> in white

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



The **4-star freezer** compartment is designed to freeze fresh food and store it for long periods. Temperatures of -18 °C and lower ensure that nutritional content is preserved during storage.



The **bottle shelf** is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



← 55 →



← 60 →



← 60 →



← 55 →

<b>Ksl 2834</b> Comfort	Silver
Energy efficiency class:	
Energy consumption year / 24 hrs: 197 / 0.539 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 250 litre	
Volume: Fridge: 229.8 litre / Freezer compartment: 21.1 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: silver / silver	
Exterior dimensions in cm (h/w/d): 140.2/55/63 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· Ice cube tray</li><li>· Temperature rise time: 8 h</li><li>· Freezing capacity in 24 hrs: 3 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingLine design</li><li>· Stainless steel slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li></ul>
<b>Colour / material options:</b> <b>K 2834</b> in white

<b>Ksl 2630</b> Comfort	Silver
Energy efficiency class:	
Energy consumption year / 24 hrs: 131 / 0.358 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 248 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: silver / silver	
Exterior dimensions in cm (h/w/d): 125/60/63.1 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display for fridge compartment</li><li>· Automatic SuperCool</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingLine design</li><li>· Stainless steel slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li></ul>

<b>K 2630</b> Comfort	
Energy efficiency class:	
Energy consumption year / 24 hrs: 131 / 0.358 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 248 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h/w/d): 125/60/63.1 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display for fridge compartment</li><li>· Automatic SuperCool</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· PowerCooling</li><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 5 GlassLine storage shelves, of which one is divided into two parts</li><li>· Bottle shelf</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingLine design</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li></ul>

<b>K 2340</b> Comfort	
Energy efficiency class:	
Energy consumption year / 24 hrs: 126 / 0.345 kWh	
Total volume <sup>2</sup> : 214 litre	
Noise output: 38 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h/w/d): 114/55/63	

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Plastic door shelves, Egg tray</li><li>· 5 GlassLine storage shelves</li><li>· Bottle shelf</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingLine design</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

## Under counter fridges



TP 1760

# Quality in every detail



The elegant and precise **MagicEye** control with its digital temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperCool** function lowers the refrigerator temperature to +2 °C. It is perfect for quickly cooling freshly stored food.



You can freeze fresh food and store frozen food for long periods in appliances with the **4-star freezer compartment**. Temperatures of -18 °C and lower ensure food is stored with all the vital vitamins and minerals preserved.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



The **slimline door handle** is discrete and ergonomically designed for ease of opening. Under counter fridges with manual controls can be further reduced in height by **removing the tabletop** of the fridge.



Ergonomically designed, the extra deep transparent **vegetable compartments** are easy-to-clean and provide ample storage for fruit and vegetables.



**Premium GlassLine** door shelves with stainless steel trim. Elegant stainless steel bars help protect taller bottles and jars.

The features shown are model dependent; look for these features in your model choice.

Under counter fridges



<b>TP 1764</b> Premium	Super Silent
Energy efficiency class:	
Energy consumption year / 24 hrs: 146 / 0.400 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 135 litre	
Volume: Fridge: 118.0 litre / Freezer compartment: 17.7 litre	
Noise output: 34 dB(A) / B, SuperSilent	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Digital temperature display for fridge compartment</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Premium GlassLine storage shelf with bottle holder, Egg tray</li><li>· 3 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Ice cube tray</li><li>· Temperature rise time: 8.9 h</li><li>· Freezing capacity in 24 hrs: 4.7 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>TP 1760</b> Premium	Super Silent
Energy efficiency class:	
Energy consumption year / 24 hrs: 93 / 0.254 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 155 litre	
Noise output: 34 dB(A) / B, SuperSilent	
Climate rating: SN-T (from +10 °C to +43 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Digital temperature display for fridge compartment</li><li>· Automatic SuperCool</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Premium GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>TP 1724</b> Comfort	
Energy efficiency class:	
Energy consumption year / 24 hrs: 146 / 0.400 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 143 litre	
Volume: Fridge: 126.0 litre / Freezer compartment: 17.6 litre	
Noise output: 37 dB(A) / C	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 2 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Ice cube tray</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 4.29 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>TP 1720</b> Comfort	Super Silent
Energy efficiency class:	
Energy consumption year / 24 hrs: 92 / 0.252 kWh <sup>1</sup>	
Total volume <sup>2</sup> : 145 litre	
Noise output: 35 dB(A) / B, SuperSilent	
Climate rating: SN-ST (from +10 °C to +38 °C)	
Door / side walls: white / white	
Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8 <sup>1</sup>	

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Under counter fridges



<b>TPesf 1714</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 183/0.501 kWh <sup>1</sup>
Total volume <sup>2</sup> : 143 litre
Volume: Fridge: 126.0 litre/Freezer compartment: 17.6 litre
Noise output: 37 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door /side walls: Stainless steel/silver
Exterior dimensions in cm (h/w/d): 85/60.1/60.8 <sup>1</sup>

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 2 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Ice cube tray</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 4.36 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Stainless steel slimline door handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>TPesf 1710</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 115/0.315 kWh <sup>1</sup>
Total volume <sup>2</sup> : 145 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door /side walls: Stainless steel/silver
Exterior dimensions in cm (h/w/d): 85/60.1/60.8 <sup>1</sup>

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Stainless steel slimline door handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>T 1714</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 183/0.501 kWh
Total volume <sup>2</sup> : 143 litre
Volume: Fridge: 126.0 litre/Freezer compartment: 17.6 litre
Noise output: 37 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 85/60.1/62.8

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 2 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Ice cube tray</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 4.36 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>T 1810</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 118/0.323 kWh
Total volume <sup>2</sup> : 161 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 85/60.1/62.8

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves, of which one is divided into two parts</li><li>· LED lighting</li><li>· 2 fruit and vegetable drawers</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



The space-saving integrated **LED light** ensures that the whole interior of the refrigerator is evenly and harmoniously lit. With its low energy consumption, the long-lasting LED light is an environmentally friendly solution for a perfect overview of the food in the fridge.



Models in the Comfort range feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort GlassLine comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



<b>TP 1414</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 176 / 0.482 kWh <sup>1</sup>
Total volume <sup>2</sup> : 120 litre
Volume: Fridge: 106.3 litre / Freezer compartment: 14.5 litre
Noise output: 39 dB(A) / C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 55.4 / 62.3 <sup>1</sup>

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 2 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 2 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>TP 1410</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 114 / 0.312 kWh <sup>1</sup>
Total volume <sup>2</sup> : 136 litre
Noise output: 37 dB(A) / C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 55.4 / 62.3 <sup>1</sup>

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Under counter fridges



<b>T 1414</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 176/0.482 kWh
Total volume <sup>1</sup> : 120 litre
Volume: Fridge: 106.3 litre / Freezer compartment: 14.5 litre
Noise output: 40 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 50.1 / 62

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 2 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Temperature rise time: 8.9 h</li><li>· Freezing capacity in 24 hrs: 5.35 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>T 1410</b> Comfort
Energy efficiency class:
Energy consumption year / 24 hrs: 114/0.312 kWh
Total volume <sup>1</sup> : 136 litre
Noise output: 36 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 50.1 / 62

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Comfort GlassLine storage shelf with bottle holder, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>T 1404</b>
Energy efficiency class:
Energy consumption year / 24 hrs: 176/0.482 kWh
Total volume <sup>1</sup> : 120 litre
Volume: Fridge: 106.3 litre / Freezer compartment: 14.5 litre
Noise output: 40 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 50.1 / 62

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li><li>· CoolPlus function</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Plastic door shelves, Egg tray</li><li>· 2 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Freezer compartment</b> <ul style="list-style-type: none"><li>· Temperature rise time: 8.9 h</li><li>· Freezing capacity in 24 hrs: 5.35 kg</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Recessed handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>Tb 1400</b>
Energy efficiency class:
Energy consumption year / 24 hrs: 114/0.312 kWh
Total volume <sup>1</sup> : 136 litre
Noise output: 36 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: black / black
Exterior dimensions in cm (h / w / d): 85 / 50.1 / 62

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Recessed handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>T 1400</b>
Energy efficiency class:
Energy consumption year / 24 hrs: 114/0.312 kWh
Total volume <sup>1</sup> : 136 litre
Noise output: 36 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: white / white
Exterior dimensions in cm (h / w / d): 85 / 50.1 / 62

<b>Controls</b> <ul style="list-style-type: none"><li>· Mechanical control in interior, control dial</li></ul>
<b>Fridge compartment</b> <ul style="list-style-type: none"><li>· Plastic door shelves, Egg tray</li><li>· 4 GlassLine storage shelves</li><li>· LED lighting</li><li>· 1 spacious fruit and vegetable drawer</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Recessed handle</li><li>· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Freezers



GN 5275

# Our freezers: an overview

Featuring options such as NoFrost, SmartFrost, StopFrost and FrostProtect – Liebherr freezers offer maximum convenience. With tall, under counter and chest freezers available – Liebherr has just the right appliance whatever your requirements. Choose from a variety of sizes and select your preferred fittings.

## No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

## Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean offering additional capacity.

## Stop Frost

Frosting over of the freezer and frozen food is reduced, reducing the number of times you need to defrost the freezer. **StopFrost** prevents a vacuum from building up in our chest freezers, ensuring the lid opens easily.


## Frost Protect

FrostProtect models will work in ambient **temperatures as low as -15 °C** for example in an unheated garage or outbuilding.

### Tall freezers




### Under counter freezers



### Chest freezers



### Selected SmartFrost freezer models



# Quality in every detail



No Frost

The **NoFrost system** from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.



Smart Frost

With the **SmartFrost technology**, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean offering additional capacity. Freezer drawers and glass shelves made of safety glass can be removed easily.



The **status indicator** is discretely integrated into the appliance door, allowing for quick and easy assessment of the appliance status, even if the door is closed. A blue light indicates that the appliance is working properly. In the case of any other status, a red light and an audible tone are emitted.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables individual temperature setting.



LED

Energy-efficient, powerful, long-life and environmentally friendly **LEDs** are integrated into the underside of the freezer interior to illuminate the contents of the drawers when they are opened. As soon as the door is opened, the LED lighting brightens, conveniently displaying the contents of the drawers.



So that food can be conveniently accessed with minimal effort, even if the drawers are fully stocked, all BluPerformance freezer **drawers** are sited on smooth-running **roller tracks**. For convenient removal and storage of food, the top drawer tilts slightly downwards when opened – an especially helpful feature in taller appliances. The position and size of the bottom drawer make it ideal for storing ice cream, herbs or other small items.

The features shown are model dependent; look for these features in your model choice.

# Quality in every detail



Frost Protect

Many freezers are kept outside of the normal household environment, so Liebherr has developed FrostProtect on selected models to enable these models to function in low ambient temperatures. Models indicated as FrostProtect will work in **ambient temperatures as low as -15 °C**.



Telescopic Rails

The transparent freezer drawers on **telescopic rails** are easy to access and use even when filled with heavy contents. They ensure both great visibility and optimum storage. The **FrostSafe** fully enclosed drawers prevent cold air from escaping, thereby reducing energy consumption.



The automatic **SuperFrost** function makes freezing food simple and energy efficient. It rapidly lowers the temperature to -32 °C to create the temperature levels required to preserve vitamins and enhance the flavour and texture of the food when consumed.



BLU Performance

**BluPerformance** models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

- 1. Power connection for appliance plug
- 2. Functional wall spacer to maintain wall clearance and allow connection
- 3. Variable speed compressor
- 4. Plinth fan with noise-damping
- 5. Condenser
- 6. Defrost water drain



The freezer drawers in the BluPerformance appliances can be easily opened on **roller tracks**. The drawers and intervening glass shelves in all appliances can be removed to create **VarioSpace** – a no-fuss system for quickly creating extra storage space.




If you are not using the entire freezer space, unused drawers can be switched off with the optional **Vario Energy-Saving Panel**. Energy consumption can then be reduced again by up to 30%.

The features shown are model dependent; look for these features in your model choice.




GN 4375

NoFrost freezers



← 70 →



← 60 →

GN 5275  
Premium



Energy efficiency class:

Energy consumption year / 24 hrs: 179/0.490 kWh <sup>1</sup>

Total volume<sup>2</sup>: 369 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 195/70/75 <sup>1</sup>

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4375  
Premium



Energy efficiency class:

Energy consumption year / 24 hrs: 198/0.542 kWh <sup>1</sup>

Total volume<sup>2</sup>: 276 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 185/60/66.5 <sup>1</sup>

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

NoFrost freezers



<b>GNef 4335</b> Comfort	No Frost	LED	Smart Steel	Smart Device ready
Energy efficiency class:				
Energy consumption year / 24 hrs: 248 / 0.679 kWh <sup>1</sup>				
Total volume <sup>2</sup> : 276 litre				
Noise output: 38 dB(A) / C				
Climate rating: SN-T (from +10 °C to +43 °C)				
Door / side walls: Stainless steel with SmartSteel / silver				
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>				

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 8 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Status indicator</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 18 kg</li><li>· 1 Cold storage accumulator</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>GN 4335</b> Comfort	No Frost	LED	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 248 / 0.679 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 276 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 8 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Status indicator</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 18 kg</li><li>· 1 Cold storage accumulator</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>GN 3735</b> Comfort	No Frost	LED	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 235 / 0.643 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 238 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 7 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Status indicator</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 17 kg</li><li>· 1 Cold storage accumulator</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>GN 3235</b> Comfort	No Frost	LED	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 221 / 0.605 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 200 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 145 / 60 / 66.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 6 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Status indicator</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 16 kg</li><li>· 1 Cold storage accumulator</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<b>GN 2835</b> Comfort	No Frost	LED	Smart Device ready
Energy efficiency class:			
Energy consumption year / 24 hrs: 208 / 0.569 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 161 litre			
Noise output: 38 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Door / side walls: white / white			
Exterior dimensions in cm (h / w / d): 125 / 60 / 66.5 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li><li>· Digital temperature display</li><li>· SmartDeviceBox: optional accessory</li><li>· Automatic SuperFrost, time-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li><li>· Door alarm: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 5 drawers, VarioSpace</li><li>· Ice cube tray with lid</li><li>· LED lighting</li><li>· Status indicator</li><li>· Temperature rise time: 9 h</li><li>· Freezing capacity in 24 hrs: 15 kg</li><li>· 1 Cold storage accumulator</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Slimline handle with integrated opening mechanism</li><li>· Versatile installation due to front ventilation</li><li>· Transport handles, front and at back</li><li>· Height-adjustable feet at front, transport castors at back</li><li>· Reversible door hinging</li><li>· Replaceable door seal</li><li>· Concealed hinge with restricted opening</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.



GNP 3013

Comfort

No Frost

Energy efficiency class: <div>F A G 1</div>
Energy consumption year / 24 hrs: 307 / 0.841 kWh 1
Total volume <sup>2</sup> : 268 litre
Noise output: 41 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 184.1/60/63 1

GNP 2713

Comfort

No Frost

Energy efficiency class: <div>F A G 1</div>
Energy consumption year / 24 hrs: 291 / 0.797 kWh 1
Total volume <sup>2</sup> : 231 litre
Noise output: 41 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 164.4/60/63 1

GNP 2313

Comfort

No Frost

Energy efficiency class: <div>F A G 1</div>
Energy consumption year / 24 hrs: 275 / 0.753 kWh 1
Total volume <sup>2</sup> : 195 litre
Noise output: 41 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 144.7/60/63 1

GNP 1913

Comfort

No Frost

Energy efficiency class: <div>F A G 1</div>
Energy consumption year / 24 hrs: 258 / 0.706 kWh 1
Total volume <sup>2</sup> : 158 litre
Noise output: 40 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 125/60/63 1

GNP 1066

Premium

No Frost

Energy efficiency class: <div>E A G 1</div>
Energy consumption year / 24 hrs: 186 / 0.509 kWh 1
Total volume <sup>2</sup> : 99 litre
Noise output: 39 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door /side walls: white/white
Exterior dimensions in cm (h/w/d): 85.1/60.2/62.8 1

Controls

· MagicEye on front, key electronic

· Graphic temperature display

· Automatic SuperFrost, time-controlled

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

Freezer compartment 

\*\*\*\*

· 8 drawers, of which 1 herb and berry tray, VarioSpace

· Temperature rise time: 8.5 h

· Freezing capacity in 24 hrs: 13.5 kg

· Safety glass fittings

Key features

· SwingLine design

· Slimline handle with integrated opening mechanism

· Versatile installation due to front ventilation

· Transport handles at back

· Height-adjustable feet at front, transport castors at back

· Reversible door hinging

Controls

· MagicEye on front, key electronic

· Graphic temperature display

· Automatic SuperFrost, time-controlled

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

Freezer compartment 

\*\*\*\*

· 7 drawers, of which 1 herb and berry tray, VarioSpace

· Temperature rise time: 8.1 h

· Freezing capacity in 24 hrs: 13.1 kg

· Safety glass fittings

Key features

· SwingLine design

· Slimline handle with integrated opening mechanism

· Versatile installation due to front ventilation

· Transport handles at back

· Height-adjustable feet at front, transport castors at back

· Reversible door hinging

Controls

· MagicEye on front, key electronic

· Graphic temperature display

· Automatic SuperFrost, time-controlled

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

Freezer compartment 

\*\*\*\*

· 6 drawers, of which 1 herb and berry tray, VarioSpace

· Temperature rise time: 8.3 h

· Freezing capacity in 24 hrs: 13.2 kg

· Safety glass fittings

Key features

· SwingLine design

· Slimline handle with integrated opening mechanism

· Versatile installation due to front ventilation

· Transport handles at back

· Height-adjustable feet at front, transport castors at back

· Reversible door hinging

Controls

· MagicEye on front, key electronic

· Graphic temperature display

· Automatic SuperFrost, time-controlled

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

Freezer compartment 

\*\*\*\*

· 5 drawers, of which 1 herb and berry tray, VarioSpace

· Temperature rise time: 8.4 h

· Freezing capacity in 24 hrs: 11.8 kg

· Safety glass fittings

Key features

· SwingLine design

· Slimline handle with integrated opening mechanism

· Versatile installation due to front ventilation

· Transport handles at back

· Height-adjustable feet at front, transport castors at back

· Reversible door hinging

Controls

· MagicEye on front, key electronic

· Digital temperature display

· Automatic SuperFrost, quantity-controlled

· FrostControl

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

Freezer compartment 

\*\*\*\*

· 3 drawers, VarioSpace

· Temperature rise time: 10 h

· Freezing capacity in 24 hrs: 11 kg

· 2 Cold storage accumulators

· Safety glass fittings

Key features

· SwingDesign

· Ergonomically designed slimline handle

· Versatile installation due to front ventilation

· Height-adjustable feet at front

· Reversible door hinging

1 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

2 In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

SmartFrost freezers



GP 2733  
Comfort

Smart FrostFrost Protect

Energy efficiency class: 

F

A

G

<sup>1</sup>

Energy consumption year / 24 hrs: 262 / 0.717 kWh <sup>1</sup>

Total volume<sup>2</sup>: 224 litre

Noise output: 39 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as −15 °C

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 164.4 / 60 / 63 <sup>1</sup>

- Controls
- MagicEye on front, key electronic
  - Graphic temperature display
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
- Freezer compartment 

\*\*\*\*
- 7 drawers, VarioSpace
  - Temperature rise time: 19 h
  - Freezing capacity in 24 hrs: 11 kg
  - Safety glass fittings
- Key features
- SwingLine design
  - Slimline handle with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging

GP 2433  
Comfort

Smart FrostFrost Protect

Energy efficiency class: 

F

A

G

<sup>1</sup>

Energy consumption year / 24 hrs: 249 / 0.682 kWh <sup>1</sup>

Total volume<sup>2</sup>: 191 litre

Noise output: 39 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as −15 °C

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63 <sup>1</sup>

- Controls
- MagicEye on front, key electronic
  - Graphic temperature display
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
- Freezer compartment 

\*\*\*\*
- 6 drawers, VarioSpace
  - Temperature rise time: 19 h
  - Freezing capacity in 24 hrs: 10 kg
  - Safety glass fittings
- Key features
- SwingLine design
  - Slimline handle with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging

GP 2033  
Comfort

Smart FrostFrost Protect

Energy efficiency class: 

F

A

G

<sup>1</sup>

Energy consumption year / 24 hrs: 235 / 0.643 kWh <sup>1</sup>

Total volume<sup>2</sup>: 157 litre

Noise output: 39 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as −15 °C

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 125 / 60 / 63 <sup>1</sup>

- Controls
- MagicEye on front, key electronic
  - Graphic temperature display
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
- Freezer compartment 

\*\*\*\*
- 5 drawers, VarioSpace
  - Temperature rise time: 19 h
  - Freezing capacity in 24 hrs: 9 kg
  - Safety glass fittings
- Key features
- SwingLine design
  - Slimline handle with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging

Under counter SmartFrost freezer



The elegant and precise **MagicEye control** with its temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperFrost** function quickly reduces the temperature to freeze your food while preserving the vitamins.



The **tabletop** of the under counter freezers is extremely robust, with a scratch and heat resistant surface.



GP 1486  
Premium

Smart FrostFrost Protect

Energy efficiency class: 

D

A

G

<sup>1</sup>

Energy consumption year / 24 hrs: 137 / 0.375 kWh <sup>1</sup>

Total volume<sup>2</sup>: 102 litre

Noise output: 37 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as −15 °C

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 85.1 / 60.2 / 62.8 <sup>1</sup>

- Controls
- MagicEye on front, key electronic
  - Digital temperature display
  - Automatic SuperFrost, quantity-controlled
  - FrostControl
  - Warning signal in case of fault: visual and acoustic
- Freezer compartment 

\*\*\*\*
- 4 drawers, VarioSpace
  - Temperature rise time: 14.6 h
  - Freezing capacity in 24 hrs: 8.2 kg
  - Safety glass fittings
- Key features
- SwingDesign
  - Ergonomically designed slimline handle
  - Versatile installation due to front ventilation
  - Height-adjustable feet at front
  - Reversible door hinging

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Under counter SmartFrost freezers



<b>GPesf 1476</b> Premium	Smart Frost	Smart Steel	Frost Protect
Energy efficiency class:			
Energy consumption year / 24 hrs: 171 / 0.468 kWh <sup>1</sup>			
Total volume <sup>2</sup> : 102 litre			
Noise output: 39 dB(A) / C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Designed to operate in ambient temperatures as low as –15 °C			
Door / side walls: Stainless steel with SmartSteel / silver			
Exterior dimensions in cm (h/w/d): 85.1 / 60.2 / 61 <sup>1</sup>			

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Digital temperature display</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 4 drawers, VarioSpace</li><li>· Temperature rise time: 17 h</li><li>· Freezing capacity in 24 hrs: 6 kg</li><li>· 2 Cold storage accumulators</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· HardLine</li><li>· Stainless steel slimline door handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>
<b>Colour / material options:</b> <b>GP 1476</b> in white

<b>GP 1376</b> Premium	Smart Frost	Frost Protect
Energy efficiency class:		
Energy consumption year / 24 hrs: 171 / 0.468 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 102 litre		
Noise output: 39 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Designed to operate in ambient temperatures as low as –15 °C		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 85.1 / 55.3 / 62.4 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Digital temperature display</li><li>· Automatic SuperFrost, quantity-controlled</li><li>· FrostControl</li><li>· Warning signal in case of fault: visual and acoustic</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 4 drawers, VarioSpace</li><li>· Temperature rise time: 14 h</li><li>· Freezing capacity in 24 hrs: 6 kg</li><li>· 2 Cold storage accumulators</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>GP 1213</b> Comfort	Smart Frost	Frost Protect
Energy efficiency class:		
Energy consumption year / 24 hrs: 170 / 0.465 kWh <sup>1</sup>		
Total volume <sup>2</sup> : 97 litre		
Noise output: 39 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Designed to operate in ambient temperatures as low as –15 °C		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 85.1 / 55.3 / 62.4 <sup>1</sup>		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Temperature rise time: 17 h</li><li>· Freezing capacity in 24 hrs: 6 kg</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>G 1213</b>	Smart Frost	Frost Protect
Energy efficiency class:		
Energy consumption year / 24 hrs: 213 / 0.583 kWh		
Total volume <sup>2</sup> : 97 litre		
Noise output: 39 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Designed to operate in ambient temperatures as low as –15 °C		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 85.1 / 55.3 / 62.4		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 3 drawers, VarioSpace</li><li>· Temperature rise time: 17 h</li><li>· Freezing capacity in 24 hrs: 6 kg</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Recessed handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<b>GX 823</b> Comfort	Smart Frost	Frost Protect
Energy efficiency class:		
Energy consumption year / 24 hrs: 199 / 0.545 kWh		
Total volume <sup>2</sup> : 68 litre		
Noise output: 39 dB(A) / C		
Climate rating: SN-T (from +10 °C to +43 °C)		
Designed to operate in ambient temperatures as low as –15 °C		
Door / side walls: white / white		
Exterior dimensions in cm (h/w/d): 63.1 / 55.3 / 62.4		

<b>Controls</b> <ul style="list-style-type: none"><li>· MagicEye on front, key electronic</li><li>· Graphic temperature display</li><li>· Automatic SuperFrost, time-controlled</li><li>· Warning signal in case of fault: visual</li></ul>
<b>Freezer compartment</b>
<ul style="list-style-type: none"><li>· 2 drawers, VarioSpace</li><li>· Temperature rise time: 14 h</li><li>· Freezing capacity in 24 hrs: 6 kg</li><li>· Safety glass fittings</li></ul>
<b>Key features</b> <ul style="list-style-type: none"><li>· SwingDesign</li><li>· Ergonomically designed slimline handle</li><li>· Versatile installation due to front ventilation</li><li>· Height-adjustable feet at front</li><li>· Reversible door hinging</li></ul>

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

# Chest freezers



CFI 2080

# Quality in every detail



Stop Frost

**StopFrost** prevents a vacuum from building up, ensuring the lid opens easily. Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer.



The bright **LED interior light** allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



The heat-exchange **condenser** is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the easy-to-clean outside walls.



Frost Protect

Due to their shape and size, many chest freezers are kept outside of the normal household environment so Liebherr has developed FrostProtect to enable these models to work in low ambient temperatures. All chest freezer models will work in **ambient temperatures as low as -15 °C**.



The automatic **SuperFrost function** quickly reduces the temperature to freeze your food while preserving the vitamins. As soon as the food is completely frozen, the automated SuperFrost function switches back to normal mode.

The features shown are model dependent; look for these features in your model choice.



The bright **LED interior light** allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



The heat-exchange **condenser** is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the easy-to-clean outside walls.



←168→

<b>CFF 2500</b> Pure	Stop Frost	LED	Frost Protect
Energy efficiency class:			
Energy consumption year / 24 hrs: 324/0.887 kWh			
Total volume <sup>1</sup> : 497 litre			
Noise output: 39 dB(A)/C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Designed to operate in ambient temperatures as low as –15 °C			
Door / side walls: white / white			
Exterior dimensions in cm (h/w/d): 82.5/167.5/72.2			

<b>Controls</b>
· Electronic controls in front, key electronic
· Automatic SuperFrost, time-controlled
· FrostControl
· Warning signal in case of fault: visual and acoustic
· Door alarm: visual and acoustic
<b>Freezer compartment</b>
· Low vibration, low noise, easy-to-clean foam-embedded condenser
· LED lighting
· Temperature rise time: 40 h
· Freezing capacity in 24 hrs: 20 kg
· Defrost drain
· Removable freezer tray as partition wall – can be used as a drip tray
· 2 Suspension baskets as standard, 5 retrofittable
<b>Key features</b>
· Recessed handle
· Replaceable door seal
· Concealed hinge with restricted opening
<b>Available 3rd quarter 2021</b>



←126→

<b>CFF 2080</b> Pure	Stop Frost	LED	Frost Protect
Energy efficiency class:			
Energy consumption year / 24 hrs: 274/0.750 kWh			
Total volume <sup>1</sup> : 353 litre			
Noise output: 39 dB(A)/C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Designed to operate in ambient temperatures as low as –15 °C			
Door / side walls: white / white			
Exterior dimensions in cm (h/w/d): 82.5/125.5/72.2			

<b>Controls</b>
· Electronic controls in front, key electronic
· Automatic SuperFrost, time-controlled
· FrostControl
· Warning signal in case of fault: visual and acoustic
· Door alarm: visual and acoustic
<b>Freezer compartment</b>
· Low vibration, low noise, easy-to-clean foam-embedded condenser
· LED lighting
· Temperature rise time: 40 h
· Freezing capacity in 24 hrs: 15 kg
· Defrost drain
· Removable freezer tray as partition wall – can be used as a drip tray
· 2 Suspension baskets as standard, 3 retrofittable
<b>Key features</b>
· Recessed handle
· Replaceable door seal
· Concealed hinge with restricted opening
<b>Available 3rd quarter 2021</b>



←105→

<b>CFF 1870</b> Pure	Stop Frost	LED	Frost Protect
Energy efficiency class:			
Energy consumption year / 24 hrs: 249/0.682 kWh			
Total volume <sup>1</sup> : 281 litre			
Noise output: 39 dB(A)/C			
Climate rating: SN-T (from +10 °C to +43 °C)			
Designed to operate in ambient temperatures as low as –15 °C			
Door / side walls: white / white			
Exterior dimensions in cm (h/w/d): 82.5/104.5/72.2			

<b>Controls</b>
· Electronic controls in front, key electronic
· Automatic SuperFrost, time-controlled
· FrostControl
· Warning signal in case of fault: visual and acoustic
· Door alarm: visual and acoustic
<b>Freezer compartment</b>
· Low vibration, low noise, easy-to-clean foam-embedded condenser
· LED lighting
· Temperature rise time: 40 h
· Freezing capacity in 24 hrs: 10 kg
· Defrost drain
· Removable freezer tray as partition wall – can be used as a drip tray
· 2 Suspension baskets as standard, 2 retrofittable
<b>Key features</b>
· Recessed handle
· Replaceable door seal
· Concealed hinge with restricted opening
<b>Available 3rd quarter 2021</b>

<sup>1</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

## Wine cabinets



WTes 5872



Find out more about  
Wine cabinets:  
[wine.liebherr.com/en](http://wine.liebherr.com/en)

# Our wine cabinets: an overview



## Vinidor range

The Vinidor range offers maximum flexibility with two separately controlled temperature zones. The temperature of these can be set independently between +5 °C and +20 °C. This means that red and white wines can be stored at their ideal serving temperatures in the same cabinet. These cabinets not only provide the ideal climate conditions for long-term storage of wine, but with differently sized zones and fully adjustable temperature controls, they are suitable for every wine collection.



## GrandCru and Vinothek range

Wine storage cabinets offer similar conditions to a wine cellar. This range facilitates the storage of red and white wines at the correct long term storage temperatures or individual serving temperatures. The temperature can be adjusted from +5 °C to +20 °C as appropriate, and is both even and constant throughout the entire appliance interior.

Wine lovers have the most stringent demands when it comes to storing their favourite wines. Many like to be able to enjoy their fine wines on the spur of the moment; others prefer to establish a collection of wines over the longer term; and some want the best of both worlds. Liebherr offers premium wine storage cabinets that guarantee perfect long term wine storage and serving temperatures, whatever your requirements. With heating and cooling circuits and air filtration, our wine cabinets offer unsurpassed wine storage conditions.



Vinidor – from page 118



GrandCru – page 120



Vinothek – from page 121



Design & Lifestyle – page 123

# Quality in every detail



The electronic LCD display offers clear menu navigation and a **Touch-electronic control system** provides bespoke storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions. The Vinidor 2 and 3 zone models feature an integrated door seal in the dividing shelf to maintain correct individual temperatures.



The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The **clip-on labelling system** provides a quick and clear overview of your wine store.



## LED

The **LED lighting** in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with no-heat LED lighting. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The **tinted safety glass** in Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical aluminium **door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.



## Soft System

The **SoftSystem** feature provides added safety and convenience. Integrated within the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 45°.

The features shown are model dependent; look for these features in your model choice.

Wine storage cabinets Vinidor



← 70 →



← 70 →



The **LED lighting** in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



← 60 →

W**Tes 5872**  
Vinidor

Super Silent

Soft System

LED

Wine

Telescopic Rails

Energy efficiency class: <div><div>G</div><div>A</div><div>G</div></div> <sup>2</sup>
Energy consumption year / 24 hrs: 206 / 0.564 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l: 178 <sup>1</sup>
Total volume <sup>3</sup> : 503 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d): 192 / 70 / 74.2 <sup>2</sup>

**Controls**

· LCD display in the interior, touch electronic

· Digital temperature display for 3 wine zones

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

**Wine compartment**

· 3 Temperature zones, which can set from +5 °C to +20 °C

· 3 independently controllable zones

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· LED lighting permanently on, dimmable

· Beech wood fittings

· 13 Shelves, of which 10 set on telescopic rails, of which 1 is a presentation shelf

**Key features**

· HardLine

· Aluminium handle with integrated opening mechanism

· Reversible door hinging

· Replaceable door seal

· Concealed hinge with restricted opening

· Lock

W**Tes 5972**  
Vinidor

Soft System

LED

Wine

Telescopic Rails

Energy efficiency class: <div><div>G</div><div>A</div><div>G</div></div> <sup>2</sup>
Energy consumption year / 24 hrs: 191 / 0.523 kWh <sup>2</sup>
Max. Bordeaux bottles 0.75 l: 211 <sup>1</sup>
Total volume <sup>3</sup> : 521 litre
Noise output: 38 dB(A) / C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d): 192 / 70 / 74.2 <sup>2</sup>

**Controls**

· LCD display in the interior, touch electronic

· Digital temperature display for both wine zones

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

**Wine compartment**

· 2 Temperature zones, which can set from +5 °C to +20 °C

· 2 independently controllable zones

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· LED lighting permanently on, dimmable

· Beech wood fittings

· 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

**Key features**

· HardLine

· Aluminium handle with integrated opening mechanism

· Reversible door hinging

· Replaceable door seal

· Concealed hinge with restricted opening

· Lock



The electronic LCD display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.

W**Tes 1672**  
Vinidor

LED

Wine

Telescopic Rails

Energy efficiency class: <div><div>G</div><div>A</div><div>G</div></div>
Energy consumption year / 24 hrs: 147 / 0.402 kWh
Max. Bordeaux bottles 0.75 l: 34 <sup>1</sup>
Total volume <sup>3</sup> : 95 litre
Noise output: 36 dB(A) / C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d): 82.2 / 59.8 / 57.5

**Controls**

· MagicEye control in interior, touch electronic

· Digital temperature display for both wine zones

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

**Wine compartment**

· 2 Temperature zones, which can set from +5 °C to +20 °C

· 2 independently controllable zones

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· LED lighting permanently on, dimmable

· Beech wood fittings

· 5 Shelves, of which 3 set on telescopic rails

**Key features**

· HardLine

· Aluminium handle

· Reversible door hinging

· Replaceable door seal

· Lock

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

<sup>3</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

Wine storage cabinets GrandCru



WKt 6451

GrandCru

LED

Wine

Energy efficiency class: <div>FAG</div>
Energy consumption year / 24 hrs: 125/0.342 kWh
Max. Bordeaux bottles 0.75 l: 312 <sup>1</sup>
Total volume <sup>2</sup> : 614 litre
Noise output: 39 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Full door, terra / terra
Exterior dimensions in cm (h/w/d): 193/74.7/75.9

Controls

· MagicEye on front, key electronic

· Digital temperature display

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

Wine compartment

· 1 Temperature zone, which can set from +5 °C to +20 °C

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· LED interior lighting

· Adjustable beech wood shelves

· 7 Shelves

Key features

· SwingLine design

· Aluminium handle with integrated opening mechanism

· Reversible door hinging

· Lock

WKt 5552

GrandCru

LED

Wine

Energy efficiency class: <div>GAG</div>
Energy consumption year / 24 hrs: 147/0.402 kWh
Max. Bordeaux bottles 0.75 l: 253 <sup>1</sup>
Total volume <sup>2</sup> : 526 litre
Noise output: 39 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door, frame terra / terra
Exterior dimensions in cm (h/w/d): 192/70/74.2

Controls

· MagicEye in the interior, key electronic

· Digital temperature display

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

Wine compartment

· 1 Temperature zone, which can set from +5 °C to +20 °C

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· LED lighting permanently on

· Adjustable beech wood shelves

· 7 Shelves

Key features

· HardLine

· Aluminium handle with integrated opening mechanism

· Reversible door hinging

· Replaceable door seal

· Lock

Wine storage cabinets Vinothek



WKb 4212

Vinothek

Wine

Energy efficiency class: <div>GAG</div>
Energy consumption year / 24 hrs: 177/0.484 kWh
Max. Bordeaux bottles 0.75 l: 200 <sup>1</sup>
Total volume <sup>2</sup> : 402 litre
Noise output: 39 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door, frame black / black
Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

· MagicEye on front, key electronic

· Digital temperature display

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

Wine compartment

· 1 Temperature zone, which can set from +5 °C to +20 °C

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· Interior lighting permanently on

· Adjustable beech wood shelves

· 6 Shelves

Key features

· HardLine

· Ergonomically designed slimline handle, black

· Reversible door hinging

· Replaceable door seal

WKr 4211

Vinothek

Wine

Energy efficiency class: <div>FAG</div>
Energy consumption year / 24 hrs: 108/0.295 kWh
Max. Bordeaux bottles 0.75 l: 200 <sup>1</sup>
Total volume <sup>2</sup> : 383 litre
Noise output: 37 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Full door, burgundy / black
Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

· MagicEye on front, key electronic

· Digital temperature display

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

Wine compartment

· 1 Temperature zone, which can set from +5 °C to +20 °C

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· Adjustable beech wood shelves

· 6 Shelves

Key features

· HardLine

· Ergonomically designed slimline handle, black

· Reversible door hinging

WKb 1812

Vinothek

Wine

Energy efficiency class: <div>GAG</div>
Energy consumption year / 24 hrs: 123/0.337 kWh
Max. Bordeaux bottles 0.75 l: 66 <sup>1</sup>
Total volume <sup>2</sup> : 135 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door / side walls: Glass door, frame black / black
Exterior dimensions in cm (h/w/d): 89/60/61.3

Controls

· MagicEye on front, key electronic

· Digital temperature display

· Warning signal in case of fault: visual and acoustic

· Door alarm: acoustic

· Child lock

Wine compartment

· 1 Temperature zone, which can set from +5 °C to +20 °C

· Convection cooling, fresh air supply via FreshAir activated charcoal filter

· Humidity regulation via adjustable fan

· Interior lighting permanently on

· Adjustable grid shelves

· 3 Shelves

Key features

· HardLine

· Ergonomically designed slimline handle, black

· Reversible door hinging

· Replaceable door seal

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.




WKes 653

Design & Lifestyle



WKes 653  
GrandCru



Energy efficiency class: 

Energy consumption year / 24 hrs: 78 / 0.213 kWh

Max. Bordeaux bottles 0.75 l: 12 <sup>1</sup>

Total volume <sup>2</sup>: 48 litre

Noise output: 37 dB(A)/C

Climate rating: SN (from +10 °C to +32 °C)

Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

Controls

- LCD display in the interior, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves

Key features

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- Utensil drawer
- Suitable for wall mounting
- Lock

ZKes 453  
Humidor



Energy efficiency class:

Energy consumption year / 24 hrs: 162 / 0.443 kWh

Total volume: 43 litre

Noise output: 40 dB(A)

Climate rating: N (from +16 °C to +32 °C)

Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

Controls

- LCD display in the interior, touch electronic
- Digital display of temperature and humidity
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Humidor

- 1 Temperature zone, which can set from +16 °C to +20 °C
- Humidity range, adjustable between 68% to 75%
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 Shelves

Key features

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- 2 presentation boxes
- Suitable for wall mounting
- Lock

<sup>1</sup> These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)  
<sup>2</sup> In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 13. According to (EU) 2017/1369 6a.

## Our catalogues

Find out everything you need to know about Liebherr Freestanding & Fully Integrated refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as PDF downloads from [home.liebherr.com](http://home.liebherr.com).



## Our Accessories:

Make the most of your Fully Integrated, Freestanding, and Wine Cabinet with official Liebherr accessories. Sign-up to our mailing list to receive exclusive content, FreshMAG Recipes, and refrigeration tips for your everyday life.



Sign up for news and offers:



UK webshop:

<https://home.liebherr.com/shop/en/gbr/>

View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



[biofresh.liebherr.com](http://biofresh.liebherr.com)



[nofrost.liebherr.com](http://nofrost.liebherr.com)



[wine.liebherr.com](http://wine.liebherr.com)

## Smart communication on all fronts



### SmartDevice-App

Device app lets you control your appliance from anywhere: Change the temperature of your appliance quickly and easily from anywhere or monitor all alerts and notifications at a glance.



### BioFresh-App

Useful information about perfect food storage, as well as vitamin and mineral content.



### Smoothies & Ice-App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.

[apps.home.liebherr.com](http://apps.home.liebherr.com)



Find out more about [smartdevice.liebherr.com](http://smartdevice.liebherr.com)



The fresh world of **FreshMAG**: Find out more about our models, food storage, nutrition, recipes and much more.



Click the link to directly access our social media channels:

[socialmedia.home.liebherr.com](http://socialmedia.home.liebherr.com)

Please contact Liebherr-Great Britain Ltd. to locate your nearest Liebherr displaying dealer:



Liebherr-Great Britain Ltd.

Normandy Lane, Stratton Business Park, Biggleswade, SG18 8QB, Tel.: +44 (0) 3330 147 888

Email Sales: [LGB.RefrigerationSales@liebherr.com](mailto:LGB.RefrigerationSales@liebherr.com), Customer Service: [LGB.Refrigeration@liebherr.com](mailto:LGB.Refrigeration@liebherr.com)  
[home.liebherr.com](http://home.liebherr.com)