
Freestanding 2021/22

LIEBHERR

Refrigeration and freezing





Contents

- Liebherr Corporate Group _____ 04
- Quality, Design and Innovation _____ 06
- Smart Home _____ 12
- EU energy label _____ 14
- Flexible accessories _____ 16
- BluPerformance _____ 18
- BioFresh _____ 22
- Food storage centres _____ 24
 - Side-by-Side fridge-freezers _____ 28
 - Frenchdoor fridge-freezer _____ 34
- Fridge-freezers _____ 36
 - with bottom freezer _____ 46
 - with top freezer _____ 72
- Fridges _____ 76
- Freezers _____ 102
- Wine Cabinets _____ 128

Global Success: Liebherr Corporate Group

Liebherr is a third-generation, family-owned company founded by Dr. Hans Liebherr in 1949 with the creation of the first ever mobile crane. With more than 70 years of success, Liebherr has become synonymous with the equipment needed to build homes and businesses, as well as the appliances within them. One of the world's largest manufacturers of construction machinery, Liebherr has expanded to eleven divisions with a wide array of product ranges, including earth moving equipment, mining, tower and maritime cranes, aerospace and transportation systems, and hotels. The company currently employs over 48,049 people in more than 140 companies in over 50 countries worldwide. Liebherr Appliances is Europe's largest privately owned manufacturer of fridges and freezers for residential and commercial use, with an annual production of more than 2.2 million units.



Construction



Aerospace and Transportation Systems



Mining



Cranes



Liebherr Appliances facility in Ochsenhausen, Germany



Liebherr Appliances facility in Lienz, Austria

For 70 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

Quality fresh food storage: BioFresh

Liebherr's BioFresh technology preserves fresh food for longer. Stored in the BioFresh compartment, at just over 0 °C and at the ideal humidity level, food will retain its nutritional value for far longer than it would in a normal fridge compartment.

Professional quality

As a refrigeration specialist, Liebherr offers a wide range of professional appliances for commercial use. The demands of the professional sector are high; this sector wants reliable, top quality storage that guarantees safe food storage. As you use your Liebherr appliance in the home on a daily basis, you are benefiting from the expertise that Liebherr has accrued from decades in the commercial sector.

Quality assured

So that you can trust your fridge or freezer to perform 24 hours a day, 365 days a year, we check all components at every stage of their development to ensure that they will function reliably for many years. For instance, before our door hinges find their way into production, they have to successfully pass through at least 100.000 opening cycles, which equates to more than 15 years use. All components undergo similar testing.

Approved quality

Prior to packaging, every appliance is subject to a comprehensive quality inspection during which all components - refrigeration, mechanical and electronic systems - are tested. The quality of workmanship is also visually checked. All newly manufactured domestic appliances from Liebherr comply with the requirements of standard IEC 60335-2-24 A2 §30 in terms of heat and fire resistance.

Guaranteed quality

We provide a two-year warranty that covers all parts and labour costs to repair or replace any part of the appliance that proves to be defective in materials or workmanship. We also offer a ten year parts availability. All Liebherr production sites are certified according to international standards for quality management (ISO 9001) and environmental management (ISO 1400).

VCC compressor

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.



Design

Characterised by elegant and timeless design, Liebherr's fridges and freezers fulfil and surpass the highest aesthetic demands. Extensive detailing – as seen in the superb stainless steel craftsmanship, the choice of high quality materials, the stylish interior fittings, and the practical GlassLine door interior – is typical in our appliances and reveals their design quality.

Design for every kitchen space

So you can enjoy a lifetime of pleasure owning your Liebherr appliance, and find the perfect appliance for you, we offer a wide range of designs including models in classic stainless steel, elegant BlackSteel or vibrant ColourLine finishes, all of which complement modern kitchen and living spaces.

Practical design for daily use

At Liebherr, design and functionality go hand-in-hand. To prevent finger marks on our stainless steel doors, we finish them with a SmartSteel surface. To make door opening easy and convenient, our ergonomically designed handles house an integrated opening mechanism. All GlassLine shelves are dishwasher safe.

Lighting design

Liebherr's fridges and freezers are fitted with modern LED lighting. Upon opening the appliance door, the interior becomes evenly illuminated. LEDs are long-life, energy efficient and generate very little heat. We take meticulous care to install specially selected LEDs in order to achieve a harmonious, slightly bluish tinted lighting effect.

Award-winning design

The superb design quality of our appliances has seen them honoured with many prestigious, international design awards from the likes of Plus X Award, reddot, iF product design and Good Design.



Door Design



HardLine-Design offers a clear, linear and minimalist style creating a pristine overall appearance and a sense of elegance.



SwingLine-Design features elegantly contoured edges for a timeless appeal.



SwingDesign has gently rounded edges resulting in a balanced design.

Innovation

Liebherr was first to implement features that are now standard in today's fridges and freezers. For example: fully enclosed FrostSafe freezer drawers that prevent loss of chilled air when the appliance is opened; patented BioFresh technology; and convenient, SoftSystem cushioned door closure.

Innovative ideas

We place great importance on the continual development of our products. Therefore, at all of our production sites, we have state-of-the-art design centres with highly skilled employees. Our goal is to be 'Best in Class' in every respect. For example, Liebherr's current appliances are super-economical in terms of energy consumption thanks to the incorporation of advanced electronics and optimised refrigeration design.

Innovation for even greater freshness

The latest fridges and freezers offer the ideal climate zone for almost every type of food. So, in addition to the classic refrigerator compartment, Liebherr offers a range of features including the BioCool box: a fruit and vegetable compartment in which humidity can be regulated; BioFresh drawers, in which meat, fish, dairy products, and fruit/vegetables all find their ideal storage climate; and a NoFrost freezer compartment that offers professional quality frost free freezing.

Excellence in every detail

It couldn't be easier to set and adjust appliances with touch screen operation. The Glassline storage shelves can be easily positioned for tailored use of the interior space. Drinks storage is provided in the door interior and, depending on the model, a bottle rack or versatile bottle shelf offer additional practical storage solutions.



1954

Liebherr home appliances founded in Germany



1971

First electronic control



1987

NoFrost Technology eliminating the need to defrost



1993

Conversion to CFC / HFC-free equipment program



1996

Patented BioFresh technology - system for extended storage-life



2004

Innovative LED lighting for energy efficient illumination



2006

Vinidor with adjustable temperature zones



2008

SoftSystem for gentle door closure



2009

SmartSteel finish reduces the visibility of finger prints



2010

DuoCooling for superior performance and efficiency



2013

Super efficient Built-in appliances



2014

Under-worktop TipOpen appliance for seamless integration



2016

BluPerformance: A new dimension in freshness



2019

SmartDevice - Smart food management



2020

The new dimension for built-in appliances



The smart fridge for your Smart Home

Liebherr's digital solutions make everyday life a lot easier: Your fridge-freezer's integrated BottleTimer reminds you via your smart lighting system, for example, that there are still bottles in the freezer compartment. Burst bottles are now a thing of the past. Using the SmartDeviceBox, simply integrate your Liebherr appliance into existing Smart Home solutions, or control your appliance easily and conveniently while on the move via the SmartDevice app. SmartDevice from Liebherr - for greater everyday convenience.

Smart Home - technology making your everyday life easier

With the assistance of the SmartDeviceBox, fridge-freezers and wine cabinets can be voice-controlled via cloud-based voice services such as Amazon Alexa and now also via Google Assistant. Status messages, e.g. relating to power cuts or doors being left open, are sent directly to your smartphone as push notifications.

A service which makes everyday life noticeably easier. Your fridge's SuperCool function, for example, can be activated automatically when entering the supermarket. At home, you can then store the food you've purchased at maximum cooling capacity in a way that protects vitamins - it couldn't be more convenient.

This and other connections to various Smart Home systems make our appliances more compatible from day to day. The fridge, for example, can be seamlessly integrated into your Smart Home and controlled more intelligently thanks to IFTTT, with individually defined rules set according to your wishes.

More than 120 free-standing and built-in appliances capable of networking are already equipped with SmartDevice technology. You too can benefit from numerous functions making your everyday life noticeably easier.



Models with this label are already fitted with the SmartDeviceBox.



Find out more about SmartDevice: smartdevice.liebherr.com



The new EU energy label for electrical appliances.

It is now once again possible to distinguish more easily between efficient and inefficient appliances. With the reform of the energy label, appliances will once again be rated from A to G on the efficiency scale. This will make things much clearer for you in future.


Technology is developing all the time. And we also never stand still.

We are constantly working on features that make everyday work easier, optimise storage and reduce consumption.

We were one of the first manufacturers in Europe to develop fridges and freezers in the highest efficiency class. And that is also our aim for the future.

Fridges and freezers work around the clock and are responsible for up to 15 percent of the electricity bill.

As our appliances consume less energy, they make an important contribution to climate protection.



- 1 The QR code for identifying the product in the EPREL (European Product Database for Energy Labeling) EU database.
- 2 The model identifier for identifying the product manually in the EPREL EU database, e.g. via the article number.
- 3 The new A to G efficiency scale. However G is only intended for wine coolers.
- 4 The sum of the volumes of the frozen compartment(s).
- 5 The sum of the volumes of the chill compartment(s) and the unfrozen compartment(s).
- 6 The noise level is now also classified into classes A to D.





Flexible accessories for your appliance

Discover the versatility of the Liebherr range of accessories for your fridge - and make your daily life a little bit easier. Get more from your Liebherr appliance with our range of accessories.



Organisational systems

Set up your fridge how you want it: In addition to the VarioSafe and the VarioBoxes, we also offer optimal organisation to leave room on the shelves for larger items, we have solutions for loose produce such as the variable egg tray and the FlexSystem. Thanks to our bottle shelves and the clip labelling system for your wine inventory, you can also keep track of your beverages. Or personalise your wine cabinet with our bottle shelves, presentation shelves and clip on labelling.



Lifestyle features

Our butter dish offers space for a wide variety of butter sizes and fits perfectly into all shelves. The easy-to-fill ice cube tray is non-spill. Saving energy made easy: With the Vario energy-saving panel, you can reduce the energy consumption of your NoFrost freezer by up to 30% when you are not using all drawers.



Consumable accessories

Your fridge includes items that are to be replaced on a regular basis for optimal performance. Water and activated carbon filters can be conveniently purchased from your Liebherr retailer. If your Liebherr appliance has a FreshAir filter or water filter, you can find the right size for your model in our webshop.

BLU
Performance

BluPerformance – A new dimension in refrigeration design

High quality materials, meticulous workmanship in every detail, and easy-to-use, precise touch-electronics define the BluPerformance range. The compact integration of cooling technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics. BioFresh and BioCool ensure lasting quality and freshness for stored foods. In addition, these models are quieter than ever, so will not disturb your living environment.

With elegant and timeless design, BluPerformance appliances are a highlight in any kitchen and are guaranteed to be a pleasure to use for many years to come.



Multifunction touch control

In the touch-electronic BluPerformance appliances all functions can be easily and conveniently set by gently touching the screen. The high-resolution 7" colour display enables individual settings. Preset programs such as: 'EnergySaver', 'MaxPerformance', 'Party' or 'Holiday' assist in achieving optimum food storage and minimum energy use.

Day-to-Day

The Day-to-Day program is aimed at meeting everyday requirements. It offers optimum refrigeration performance and efficiency using standard temperature settings in the fridge and freezer compartments.

EnergySaver

The EnergySaver program lowers energy consumption further, beyond standard settings. To save energy, the temperature in the fridge and freezer compartments is slightly raised. The touch-electronics screen displays useful energy saving tips to help you further reduce electricity costs.

Party

The Party program is ideal when preparing for celebrations: SuperCool and SuperFrost are activated for the short-term storage and chilling of larger quantities of food. The BottleTimer allows rapid chilling of drinks. Appliances with an IceMaker can increase ice cube production.

MaxPerformance

The MaxPerformance program allows the appliance to deliver its highest refrigeration performance. It selects lower temperature settings for the fridge and freezer compartments.

Holiday

The Holiday program minimises energy consumption during extended absences from the home. The fridge compartment is set to +15 °C, and the freezer compartment to -18 °C.





BioFresh: enjoy lasting freshness

With BioFresh technology food keeps fresh for much longer. When stored at a temperature close to 0 °C and at the correct humidity level, many foods retain their nutrients, such as vitamins and minerals, for far longer than in a conventional fridge compartment.

Considerably longer shelf life

It is important for newly purchased and freshly harvested foods to be stored properly so that their nutrients are preserved for longer.

The dry conditions in the DrySafe are ideal for storing meat, fish and dairy products.

The shelf life and freshness of most fruit and vegetables can be significantly extended by storing them in a fridge, particularly in the Fruit & Vegetable safe. The high humidity in this storage environment means less liquid is lost from food keeping fruit and vegetables fresh and crisp. By adjusting to low humidity, the Fruit & Vegetable safe can also be used as an additional DrySafe.

Less packaging is better for the environment

More and more packaging waste is being produced which is harmful to our environment. This is one of the reasons why the Fruit & Vegetable safe was developed. Here fruit and vegetables are best stored unpackaged and they also maintain their freshness for longer. This means there's nothing to stop you shopping at the farmer's market or in the packaging-free supermarket. The practical FlexSystem (depending on model) helps to separate and sort products neatly and cleanly.



Find out more about BioFresh:
biofresh.liebherr.com/en

Food storage centres



SBSes 8496

Quality in every detail



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



Bio Fresh

BioFresh guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period.

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps fish and seafood fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile **Fish & Seafood-Safe**.



Bio Fresh Plus



No Frost

The **NoFrost** system provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost free.



Find out more about NoFrost: nofrost.liebherr.com/en



Ice Maker

The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

The features shown are model dependent; look for these features in your model choice.



SBSes 8496

Side-by-Side fridge-freezer



←121→

SBSes 8496
PremiumPlus

SWTNes 4285 PremiumPlus

- Duo Cooling
- No Frost
- Soft System
- Ice Maker
- Smart Steel
- Smart Device ready
- Wine

Energy efficiency class: **D** ^A/₂

Energy consumption year / 24 hrs: 187 / 0.512 kWh ²

Max. Bordeaux bottles 0.75 l: 48 ¹

Total volume³: 289 litre

Volume: Wine compartment: 156.4 litre / Freezer compartment: 132.8 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/68.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm wine and freezer compartment: visual and acoustic

Freezer compartment **4** ³ ⁴ ⁵ ⁶

- 5 drawers, of which 2 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 1.8 kg capacity
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

Wine compartment

- 2 separately controllable temperature zones, which can be regulated between +5 °C to +20 °C
- Tinted insulated glass door with UV protection
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Beech wood fittings
- 4 shelves, of which 4 on telescopic rails and 2 foldable
- Partially-foldable wooden shelf on telescopic rails
- LED lighting permanently on, dimmable

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front and back, transport castors at back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

SKBes 4380 PremiumPlus

- Bio Fresh Plus
- Soft System
- Smart Steel
- Smart Device ready
- Soft-Telescopic

Energy efficiency class: **D** ^A/₂

Energy consumption year / 24 hrs: 133 / 0.364 kWh ²

Total volume³: 371 litre

Volume: Fridge: 235.7 litre / BioFresh compartment: 135.8 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- BioFresh-Plus with Fish & Seafood-Safe
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

³ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBSbs 8683
Premium



←121→



SBSes 8773
Premium



←121→

SGNbs 4385
Premium



Energy efficiency class: **D** ¹

Energy consumption year / 24 hrs: 198/0.542 kWh ¹

Total volume²: 276 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 9 drawers, of which 5 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir 0.8 kg capacity
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

SKBbs 4370
Premium



Energy efficiency class: **D** ¹

Energy consumption year / 24 hrs: 133/0.364 kWh ¹

Total volume²: 372 litre

Volume: Fridge: 235.7 litre / BioFresh compartment: 137.2 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

SGNes 4375
Premium



Energy efficiency class: **D** ¹

Energy consumption year / 24 hrs: 198/0.542 kWh ¹

Total volume²: 276 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

SKBes 4370
Premium



Energy efficiency class: **D** ¹

Energy consumption year / 24 hrs: 133/0.364 kWh ¹

Total volume²: 372 litre

Volume: Fridge: 235.7 litre / BioFresh compartment: 137.2 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBSes 8483
Premium



SKes 4370
Premium



←121→



SGNef 3036
Comfort



SKef 4260
Comfort

←121→

SBNes 4285
Premium



Energy efficiency class: **D** ^A/_G ¹

Energy consumption year/24 hrs: 171/0.468 kWh ¹

Total volume²: 311 litre

Volume: BioFresh compartment: 179.1 litre/Freezer compartment: 132.8 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- 2 GlassLine shelves in the BioFresh compartment, of which one is divided into two parts
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- 5 drawers, of which 2 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 1.8 kg capacity
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

Energy efficiency class: **C** ^A/_B ¹

Energy consumption year/24 hrs: 78/0.213 kWh ¹

Total volume²: 395 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting with dimmer function
- 2 BioCool-Boxes on telescopic rails

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

SGNef 3036
Comfort



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 306/0.838 kWh ¹

Total volume²: 268 litre

Noise output: 41 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185.2/60/62.3 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8.5 h
- Freezing capacity in 24 hrs: 15.9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Fixed door hinge, left
- Replaceable door seal

Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 151/0.413 kWh ¹

Total volume²: 385 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185.2/60/62.3 ¹

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on telescopic rails

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Fixed door hinge, right
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Quality in every detail



The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



Both **BioFresh drawers** are mounted on **telescopic rails** which extend effortlessly providing easy access to and a full view of your food. The lateral **LED lights** ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



No Frost

Ice Maker

The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated **water filter** ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The **NoFrost** technology keeps the freezer constantly frostfree.



LED

The interior features **LED light columns** integrated on either side of the refrigerator, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. The elegant, high quality **GlassLine** interior is adaptable to suit individual requirements.



← 91 →

CBNes 6256
PremiumPlus

- Bio Fresh
- Duo Cooling
- No Frost
- Ice Maker

Energy efficiency class: **F A G**

Energy consumption year/24 hrs: 341/0.934 kWh

Total volume¹: 522 litre

Volume: Fridge: 292.2 litre/BioFresh compartment: 70.6 litre/Freezer compartment: 159.5 litre

Noise output: 42 dB(A)/D

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel/stainless steel

Exterior dimensions in cm (h/w/d): 203.9/91/61.5

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, adjustable egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic, self-retracting rails
- IceMaker with fixed 3/4" water connection
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir 2.7 kg capacity
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

Key features

- HardLine
- Aluminium handles
- Versatile installation due to front ventilation
- Front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Door hinge left fixed/right fixed
- Replaceable door seal

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Fridge-freezers



CBNes 5778

Our fridge-freezers: an overview

Liebherr's extensive range of fridge-freezers offers the ideal solution for almost everyone - whatever your demands and needs are. Our fridge-freezers offer innovative features such as BioFresh or BioCool and NoFrost or SmartFrost. Once you have made your preferred choice, all of our appliances are available with a variety of fittings and come in various sizes and colours.



Bio Fresh

No Frost

from page 46



Bio Fresh Plus

No Frost

page 48



Bio Cool

No Frost

from page 52



No Frost

from page 56



Smart Frost

from page 66



No Frost

Smart Frost

from page 72

Bio Fresh

When stored under BioFresh conditions, at just above 0 °C and at the ideal humidity level, fruit, vegetables, meat, fish and dairy products retain their nutrients, delicate flavour, and appetising appearance for much longer than they do under normal fridge conditions.

Bio Fresh Plus

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient to use and it ensures that stored food is clearly visible.

No Frost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

SmartFrost offers great convenience: the freezer compartment seldom requires defrosting, and the interior and frozen food frost over far less. In addition, the smooth interior walls are easy to clean.

Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost: nofrost.liebherr.com




Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves are made of safety glass and can be removed easily.



Bio Fresh

BioFresh guarantees the perfect temperature for much longer freshness. At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment. While the DrySafe is particularly suitable for storing meat, fish and dairy products, the high humidity in the Fruit & Vegetable safe can prevent fruit and vegetables from drying out and helps preserve stored goods for an even longer period. **BioFresh-Plus** offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile **Fish & Seafood-Safe**.



Bio Fresh Plus



Ice Maker

If the quality of the mains water is poor or there is no plumbed-in connection, the CNef 5745 offers the **IceMaker with a water tank** supply. With a 1.2 litre capacity and a practical handle, this can be easily removed and filled.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clearly visible. The humidity level in the BioCool-Box is regulated using a slide control.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail




The sturdy **handle with** its refined, premium-quality appearance and **an integrated opening mechanism** ensures easy and effortless opening of the door. The handle perfectly complements the HardLine door design, and is made from anodised aluminium or white plastic. It can be easily repositioned if the hinge side of the door is changed.



Duo Cooling

With two independently controlled cooling circuits, **DuoCooling** controls the temperature in fridge-freezers with precision. There is no air exchange between the fridge and freezer compartments, odour transfer is prevented and stored food does not dry out. Also, the refrigeration compartment can be switched off while the freezer compartment continues operating. This can be useful, for example, when going on holiday.



BLU Performance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug
2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor
4. Plinth fan with noise-damping
5. Condenser
6. Defrost water drain



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system. Appliances can be adapted to specific customer requirements using preset programmes, thereby ensuring optimal food storage.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail

LED



Soft-Telescopic

The BioFresh safes with **SoftTelescopic** provide a convenient, self-retracting system with soft closing, making their daily use both practical and secure. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated charcoal filter that is integrated into the fan purifies circulating air and quickly traps odours.



The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a constant, perfectly lit storage environment.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables accurate temperature settings.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles.



The automatic **SuperFrost function** makes freezing food simple and energy efficient. It rapidly lowers the temperature to -32 °C to create the coldness levels required to preserve vitamins during freezing. The automatic **SuperCool function** lowers the refrigerator temperature to +2 °C for a defined period of 3, 6, 9 or 12 hours, offering flexibility according to the amount of food stored.

The features shown are model dependent; look for these features in your model choice.



The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost:
nofrost.liebherr.com



← 70 →



← 70 →



← 70 →

CBNes 5778 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Smart Steel	Smart Device ready	Soft-Telescopic
------------------------------	-----------	-------------	----------	--------------	-------------	-------------	--------------------	-----------------

Energy efficiency class: C ^A / _B ¹
Energy consumption year / 24 hrs: 187 / 0.512 kWh ¹
Total volume ² : 392 litre
Volume: Fridge: 168.5 litre / BioFresh compartment: 112.6 litre / Freezer compartment: 111.6 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

- | | |
|---|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 7" TFT-colour display in-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox: optional accessory · Automatic SuperCool (time restricted) · Automatic SuperFrost, quantity-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 3 GlassLine storage shelves, of which one is divided into two parts · Variable bottle shelf · LED ceiling lighting with dimmer function · LED BioFresh lighting · LED rear wall lighting | <ul style="list-style-type: none"> · 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 3 drawers, of which 2 set on roller tracks, VarioSpace · Ice cube tray with lid · LED lighting · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · 2 Cold storage accumulators · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|---|--|

CBNes 5775 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Smart Steel	Smart Device ready	Soft-Telescopic
------------------------------	-----------	-------------	----------	--------------	-------------	-------------	--------------------	-----------------

Energy efficiency class: B ^A / _B ¹
Energy consumption year / 24 hrs: 149 / 0.408 kWh ¹
Total volume ² : 392 litre
Volume: Fridge: 168.5 litre / BioFresh compartment: 112.6 litre / Freezer compartment: 111.6 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

- | | |
|---|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 2.4" TFT-colour display behind-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox: optional accessory · Automatic SuperCool (time restricted) · Automatic SuperFrost, quantity-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 3 GlassLine storage shelves, of which one is divided into two parts · Variable bottle shelf · LED ceiling lighting with dimmer function · LED BioFresh lighting · LED rear wall lighting | <ul style="list-style-type: none"> · 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 3 drawers, of which 2 set on roller tracks, VarioSpace · Ice cube tray with lid · LED lighting · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · 2 Cold storage accumulators · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|---|--|

CBNef 5735 Comfort	Bio Fresh	Duo Cooling	No Frost	Smart Steel	Smart Device ready
------------------------------	-----------	-------------	----------	-------------	--------------------

Energy efficiency class: D ^A / _B ¹
Energy consumption year / 24 hrs: 234 / 0.641 kWh ¹
Total volume ² : 392 litre
Volume: Fridge: 168.5 litre / BioFresh compartment: 112.6 litre / Freezer compartment: 111.6 litre
Noise output: 36 dB(A)/C
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / silver
Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

- | | |
|---|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox: optional accessory · Automatic SuperCool (time restricted) · Automatic SuperFrost, time-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, Egg tray · 3 GlassLine storage shelves, of which one is divided into two parts · Integrated bottle shelf · LED ceiling lighting | <ul style="list-style-type: none"> · 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray with lid · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|---|--|



The BioFresh safes with **SoftTelescopic** provide a convenient, self-retracting system with soft closing, making their daily use both practical and secure. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment.



The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party – there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.



CBNes 4898 PremiumPlus	Bio Fresh Plus	Duo Cooling	No Frost	Super Silent	Soft System	Ice Maker	Smart Steel	Smart Device ready	Soft-Telescopic
----------------------------------	----------------	-------------	----------	--------------	-------------	-----------	-------------	--------------------	-----------------

Energy efficiency class: C ^A / _B ¹
Energy consumption year / 24 hrs: 182/0.498 kWh ¹
Total volume ² : 349 litre
Volume: Fridge: 147.5 litre / BioFresh compartment: 97.9 litre / Freezer compartment: 104.2 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5 ¹

- | | |
|--|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 7" TFT-colour display in-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox: optional accessory · Automatic SuperCool (time restricted) · Automatic SuperFrost, quantity-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 3 GlassLine storage shelves, of which one is divided into two parts · Variable bottle shelf · LED ceiling lighting with dimmer function · LED BioFresh lighting · LED rear wall lighting · BioFresh-Plus | <ul style="list-style-type: none"> · 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe, 1 FlexSystem <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 4 drawers, of which 1 set on roller tracks, VarioSpace · IceMaker with fixed 3/4" water connection · Ice cube production in 24 hrs: 1.2 kg · Ice cube reservoir 1.8 kg capacity · LED lighting · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · 2 Cold storage accumulators · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|--|--|



CBNies 4878 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Smart Steel	Smart Device ready	Soft-Telescopic
-------------------------------	-----------	-------------	----------	--------------	-------------	-------------	--------------------	-----------------

Energy efficiency class: C ^A / _B ¹
Energy consumption year / 24 hrs: 182/0.498 kWh ¹
Total volume ² : 351 litre
Volume: Fridge: 147.5 litre / BioFresh compartment: 100.9 litre / Freezer compartment: 103.5 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5 ¹

- | | |
|--|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 7" TFT-colour display in-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox included · Automatic SuperCool (time restricted) · Automatic SuperFrost, quantity-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 3 GlassLine storage shelves, of which one is divided into two parts · Variable bottle shelf · LED ceiling lighting with dimmer function · LED BioFresh lighting · LED rear wall lighting | <ul style="list-style-type: none"> · 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 3 drawers, of which 2 set on roller tracks, VarioSpace · Ice cube tray with lid · LED lighting · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · 2 Cold storage accumulators · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|--|--|



CBNbs 4878 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Black Steel	Smart Device ready	Soft-Telescopic
------------------------------	-----------	-------------	----------	--------------	-------------	-------------	--------------------	-----------------

Energy efficiency class: C ^A / _B ¹
Energy consumption year / 24 hrs: 182/0.498 kWh ¹
Total volume ² : 351 litre
Volume: Fridge: 147.5 litre / BioFresh compartment: 100.9 litre / Freezer compartment: 103.5 litre
Noise output: 35 dB(A)/B, SuperSilent
Climate rating: SN-T (from +10 °C to +43 °C)
Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5 ¹

- | | |
|---|--|
| <p>Controls</p> <ul style="list-style-type: none"> · 7" TFT-colour display in-the-door, touch electronic · Digital temperature display for fridge, BioFresh and freezer compartments · SmartDeviceBox: optional accessory · Automatic SuperCool (time restricted) · Automatic SuperFrost, quantity-controlled · FrostControl · Warning signal in case of fault: visual and acoustic · Door alarm fridge and freezer compartment: visual and acoustic <p>Fridge and BioFresh compartments</p> <ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 3 GlassLine storage shelves, of which one is divided into two parts · Variable bottle shelf · LED ceiling lighting with dimmer function · LED BioFresh lighting · LED rear wall lighting | <ul style="list-style-type: none"> · 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe <p>Freezer compartment *****</p> <ul style="list-style-type: none"> · 3 drawers, of which 2 set on roller tracks, VarioSpace · Ice cube tray with lid · LED lighting · Temperature rise time: 16 h · Freezing capacity in 24 hrs: 9 kg · 2 Cold storage accumulators · Safety glass fittings <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Aluminium handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back · Height-adjustable feet at front, transport castors at back · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening |
|---|--|

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

BioFresh NoFrost fridge-freezer



←60→



←60→



←60→



←60→

CBNes 4875 Premium



Energy efficiency class: **B** ¹

Energy consumption year/24 hrs: 145/0.397 kWh ¹

Total volume²: 351 litre

Volume: Fridge: 147.5 litre/BioFresh compartment: 100.9 litre/
Freezer compartment: 103.5 litre

Noise output: 35 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting

- 2 BioFresh-Safes with SoftTelescopic, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CBNbs 4835 Comfort



Energy efficiency class: **D** ¹

Energy consumption year/24 hrs: 227/0.621 kWh ¹

Total volume²: 351 litre

Volume: Fridge: 149.2 litre/BioFresh compartment: 99.1 litre/
Freezer compartment: 103.5 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CBNef 4835 Comfort



Energy efficiency class: **D** ¹

Energy consumption year/24 hrs: 227/0.621 kWh ¹

Total volume²: 351 litre

Volume: Fridge: 149.2 litre/BioFresh compartment: 99.1 litre/
Freezer compartment: 103.5 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CBN 4835 Comfort



Energy efficiency class: **D** ¹

Energy consumption year/24 hrs: 227/0.621 kWh ¹

Total volume²: 351 litre

Volume: Fridge: 149.2 litre/BioFresh compartment: 99.1 litre/
Freezer compartment: 103.5 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, of which 1 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

BioCool NoFrost fridge-freezers



← 70 →



← 70 →



← 60 →



← 60 →

CNeF 5745 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 210/0.575 kWh ¹

Total volume²: 411 litre

Volume: Fridge: 299.2 litre / Freezer compartment: 112.2 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

CNeF 5735 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 210/0.575 kWh ¹

Total volume²: 410 litre

Volume: Fridge: 299.2 litre / Freezer compartment: 111.6 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 201 / 70 / 66.5 ¹

CNeF 4845 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 204/0.558 kWh ¹

Total volume²: 366 litre

Volume: Fridge: 262.3 litre / Freezer compartment: 104.0 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5 ¹

CNBs 4835 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 203/0.556 kWh ¹

Total volume²: 365 litre

Volume: Fridge: 262.3 litre / Freezer compartment: 103.5 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 201 / 60 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 2.2 kg capacity
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment

- 4 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir 1.8 kg capacity
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features


- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:

- **CN 4835** in white
- **CNeF 4835** with Stainless steel front

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



CNief 4335
Comfort



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 200 / 0.547 kWh

Total volume²: 325 litre

Volume: Fridge: 222.3 litre / Freezer compartment: 103.5 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CNef 4335
Comfort



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 200 / 0.547 kWh¹

Total volume²: 325 litre

Volume: Fridge: 222.3 litre / Freezer compartment: 103.5 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:
CN 4335 in white

CNfr 4335
Comfort



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 200 / 0.547 kWh¹

Total volume²: 325 litre

Volume: Fridge: 222.3 litre / Freezer compartment: 103.5 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: FireRed / FireRed

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

CNef 3735
Comfort



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 191 / 0.523 kWh

Total volume²: 275 litre

Volume: Fridge: 172.3 litre / Freezer compartment: 103.5 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 165 / 60 / 66.5

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost fridge-freezers



← 60 →



← 60 →



← 60 →



← 60 →

CNeF 4015 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 245/0.671 kWh ¹

Total volume²: 365 litre

Volume: Fridge: 270.5 litre / Freezer compartment: 95.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 10.8 h
- Freezing capacity in 24 hrs: 8.2 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Colour / material options:

- **CN 4015** in white
- **CNbs 4015** in BlackSteel
- **CNbe 4015** in beige

CNbs 3915 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 260/0.712 kWh ¹

Total volume²: 350 litre

Volume: Fridge: 222.4 litre / Freezer compartment: 128.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12.1 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

CNeF 3915 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 260/0.712 kWh ¹

Total volume²: 350 litre

Volume: Fridge: 222.4 litre / Freezer compartment: 128.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12.1 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

CN 3915 Comfort



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 260/0.712 kWh ¹

Total volume²: 350 litre

Volume: Fridge: 222.4 litre / Freezer compartment: 128.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 62.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12.1 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.




← 60 →



← 60 →



← 60 →



← 60 →

CNeF 3515
Comfort



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh¹

Total volume²: 317 litre

Volume: Fridge: 222.4 litre / Freezer compartment: 95.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 181.7 / 60 / 62.5¹

CN 3515
Comfort



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh¹

Total volume²: 317 litre

Volume: Fridge: 222.4 litre / Freezer compartment: 95.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 181.7 / 60 / 62.5¹

CNeF 3115
Comfort



Energy efficiency class:

Energy consumption year / 24 hrs: 235 / 0.643 kWh¹

Total volume²: 269 litre

Volume: Fridge: 174.4 litre / Freezer compartment: 95.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 162.3 / 60 / 62.5¹

CN 3115
Comfort



Energy efficiency class:

Energy consumption year / 24 hrs: 235 / 0.643 kWh¹

Total volume²: 269 litre

Volume: Fridge: 174.4 litre / Freezer compartment: 95.3 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 162.3 / 60 / 62.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.32 h
- Freezing capacity in 24 hrs: 6.2 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.32 h
- Freezing capacity in 24 hrs: 6.2 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.3 h
- Freezing capacity in 24 hrs: 7.3 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.3 h
- Freezing capacity in 24 hrs: 7.3 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



CNPef 4813

NoFrost fridge-freezers



← 60 →



← 60 →

CNPef 4813



Energy efficiency class: **D** ^A₁¹

Energy consumption year/24 hrs: 201/0.550 kWh¹

Total volume²: 344 litre

Volume: Fridge: 243.2 litre/Freezer compartment: 100.9 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour/material options:

- **CN 4813** in white
- **CNPef 4813** with Stainless steel front

CN 4813



Energy efficiency class: **E** ^A₁¹

Energy consumption year/24 hrs: 251/0.687 kWh¹

Total volume²: 344 litre

Volume: Fridge: 243.2 litre/Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour/material options:

- **CNef 4813** with Stainless steel front
- **CNef 4813** with Stainless steel look

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost fridge-freezers



← 60 →



← 60 →



← 60 →



← 60 →

CN 4713



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 334 litre

Volume: Fridge: 199.4 litre / Freezer compartment: 134.8 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 9.5 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour / material options:

CNel 4713 in Stainless steel look

CNel 4213



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 248 / 0.679 kWh ¹

Total volume²: 300 litre

Volume: Fridge: 165.6 litre / Freezer compartment: 134.8 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel look / silver

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 3 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 9.5 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour / material options:

CN 4213 in white

CNel 4313



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel look / silver

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour / material options:

CNef 4313 with Stainless steel front

CN 4313



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost fridge-freezers



← 60 →



← 60 →



← 60 →



← 60 →

CNbe 4313



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: beige / beige

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CNno 4313



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: NeonOrange / NeonOrange

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CNkw 4313



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: KiwiGreen / KiwiGreen

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

CNfb 4313



Energy efficiency class:

Energy consumption year / 24 hrs: 246 / 0.674 kWh ¹

Total volume²: 310 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 100.9 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: FrozenBlue / FrozenBlue

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11.6 h
- Freezing capacity in 24 hrs: 8 kg

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

SmartFrost fridge-freezers



← 60 →



← 60 →

CPeL 4813



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 191 / 0.523 kWh ¹

Total volume²: 343 litre

Volume: Fridge: 243.2 litre / Freezer compartment: 99.9 litre

Noise output: 36 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel look / silver

Exterior dimensions in cm (h/w/d): 201.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour / material options:

CPeL 4813 in white

CP 4313



Energy efficiency class: ¹

Energy consumption year / 24 hrs: 187 / 0.512 kWh ¹

Total volume²: 309 litre

Volume: Fridge: 209.4 litre / Freezer compartment: 99.9 litre

Noise output: 36 dB(A) / C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 186.1 / 60 / 65.5 ¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge compartment

- PowerCooling
- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour / material options:

CPeL 4313 with Stainless steel look

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



CPeL 4313



← 55 →



← 55 →



← 55 →



← 55 →



← 55 →



← 55 →

CUel 3331

Energy efficiency class:
Energy consumption year/24 hrs: 280/0.767 kWh ¹
Total volume ² : 296 litre
Volume: Fridge: 212.4 litre/ Freezer compartment: 84.1 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: Stainless steel look/silver
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - Bottle shelf
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 3 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 20 h
 - Freezing capacity in 24 hrs: 3.8 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

Colour/material options:
CUel 3331 with Stainless steel front

CU 3331

Energy efficiency class:
Energy consumption year/24 hrs: 280/0.767 kWh ¹
Total volume ² : 296 litre
Volume: Fridge: 212.4 litre/ Freezer compartment: 84.1 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - Bottle shelf
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 3 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 20 h
 - Freezing capacity in 24 hrs: 3.8 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CUel 2831

Energy efficiency class:
Energy consumption year/24 hrs: 240/0.657 kWh ¹
Total volume ² : 265 litre
Volume: Fridge: 212.4 litre/ Freezer compartment: 53.5 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: Stainless steel look/silver
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - Bottle shelf
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 2 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 18 h
 - Freezing capacity in 24 hrs: 3 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CU 2831

Energy efficiency class:
Energy consumption year/24 hrs: 240/0.657 kWh ¹
Total volume ² : 265 litre
Volume: Fridge: 212.4 litre/ Freezer compartment: 53.5 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - Bottle shelf
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 2 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 18 h
 - Freezing capacity in 24 hrs: 3 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CUel 2331

Energy efficiency class:
Energy consumption year/24 hrs: 241/0.660 kWh ¹
Total volume ² : 210 litre
Volume: Fridge: 156.5 litre/ Freezer compartment: 53.5 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: Stainless steel look/silver
Exterior dimensions in cm (h/w/d): 137.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 2 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 18 h
 - Freezing capacity in 24 hrs: 3 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CU 2331

Energy efficiency class:
Energy consumption year/24 hrs: 241/0.660 kWh ¹
Total volume ² : 210 litre
Volume: Fridge: 156.5 litre/ Freezer compartment: 53.5 litre
Noise output: 38 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 137.2/55/63 ¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
 - CoolPlus function

- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 2 fruit and vegetable drawers

- Freezer compartment**
- 2 drawers, VarioSpace
 - Ice cube tray
 - Temperature rise time: 18 h
 - Freezing capacity in 24 hrs: 3 kg
 - Safety glass fittings

- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

SmartFrost fridge-freezers



CUNo 2831

CUkw 2831

CUfb 2831



← 55 →



← 55 →



← 55 →

CUNo 2831



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year / 24 hrs: 240/0.657 kWh ¹

Total volume²: 265 litre

Volume: Fridge: 212.4 litre/
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: NeonOrange/NeonOrange

Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUkw 2831



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year / 24 hrs: 240/0.657 kWh ¹

Total volume²: 265 litre

Volume: Fridge: 212.4 litre/
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: KiwiGreen/KiwiGreen

Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUfb 2831



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year / 24 hrs: 240/0.657 kWh ¹

Total volume²: 265 litre

Volume: Fridge: 212.4 litre/
Freezer compartment: 53.5 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: FrozenBlue/FrozenBlue

Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost Top Mount fridge-freezer



CTNesf 3663



Accurate and independent temperature control of the fridge and freezer compartments is facilitated by **DuoCooling**: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



← 60 →

CTNesf 3663
Premium

Duo
Cooling

No
Frost

Smart
Steel

Energy efficiency class: **F A** ¹

Energy consumption year / 24 hrs: 257 / 0.704 kWh ¹

Total volume²: 306 litre

Volume: Fridge: 247.5 litre / Freezer compartment: 59.1 litre

Noise output: 41 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h/w/d): 191.1 / 60 / 63 ¹

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Individually regulated cooling circuits: 2
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm fridge and freezer compartment: acoustic

Fridge compartment

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 1 spacious fruit and vegetable drawer on roller tracks

Freezer compartment ********

- Ice cube tray
- Temperature rise time: 12.95 h
- Freezing capacity in 24 hrs: 2.5 kg
- Safety glass fittings

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging



The **MagicEye control** keeps the temperature at exactly the level you select. It is simple and convenient to use. The **automatic SuperFrost function** quickly reduces the temperature to freeze your food while preserving the vitamins.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



← 55 →



← 55 →



← 55 →



← 55 →



← 55 →



← 55 →

CTel 2931  

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 231/0.632 kWh¹
 Total volume²: 270 litre
 Volume: Fridge: 218.6 litre/
 Freezer compartment: 51.5 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 157.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 19.54 h
 - Freezing capacity in 24 hrs: 3.32 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CT 2931 

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 231/0.632 kWh¹
 Total volume²: 270 litre
 Volume: Fridge: 218.6 litre/
 Freezer compartment: 51.5 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 157.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 4 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 19.54 h
 - Freezing capacity in 24 hrs: 3.32 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CTel 2531  

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 212/0.580 kWh¹
 Total volume²: 233 litre
 Volume: Fridge: 189.5 litre/
 Freezer compartment: 43.8 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 140.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 17.12 h
 - Freezing capacity in 24 hrs: 3.56 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CT 2531 

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 212/0.580 kWh¹
 Total volume²: 233 litre
 Volume: Fridge: 189.5 litre/
 Freezer compartment: 43.8 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 140.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 17.12 h
 - Freezing capacity in 24 hrs: 3.56 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CTel 2131  

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 198/0.542 kWh¹
 Total volume²: 196 litre
 Volume: Fridge: 152.2 litre/
 Freezer compartment: 43.8 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 124.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 17.3 h
 - Freezing capacity in 24 hrs: 3.74 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

CT 2131 

Energy efficiency class: ¹
 Energy consumption year/24 hrs: 198/0.542 kWh¹
 Total volume²: 196 litre
 Volume: Fridge: 152.2 litre/
 Freezer compartment: 43.8 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 124.1/55/63¹

- Controls**
- Mechanical control in interior, control dial
 - Individually regulated cooling circuits: 1
- Fridge compartment**
- Plastic door shelves, Egg tray
 - 3 GlassLine storage shelves
 - LED lighting
 - 1 spacious fruit and vegetable drawer
- Freezer compartment** 
- Ice cube tray
 - Temperature rise time: 17.3 h
 - Freezing capacity in 24 hrs: 3.74 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Recessed handles
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Fridges




KBef 4330

Our fridges: an overview

Liebherr fridges excel with their impressive freshness technology. The range on offer extends from models featuring a classic vegetable compartment, to BioCool models with an adjustable humidity compartment, all the way to BioFresh appliances, which deliver the longest-lasting freshness. Whatever you're looking for, you're sure to find just the right fridge to meet your needs and requirements within Liebherr's comprehensive range – be it an upright or under counter appliance.

Fridges



Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately maintained at around 0 °C.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.

Under counter fridges



Quality in every detail



Bio Fresh

The fresher your food, the better it is for a healthy diet. **BioFresh safes**, sited on telescopic rails, guarantee the perfect environment for greater freshness. When stored at a temperature of just over 0 °C and at just the right humidity level, fruit and vegetables, fish, meat and dairy products all retain their vitamins, delicate flavours and appetising appearance for far longer than in a conventional fridge compartment.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated **charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail



LED

The **LED rear wall lighting** is integrated into the rear section of the horizontal dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the fridge compartment, from top to bottom and provide high-quality illumination.

The **versatile bottle shelf** is an innovative feature in all BioFresh Premium models. It can be positioned above or below the glass shelf to suite individual requirements.



The clear, minimalist style of **HardLine-Design** lends a real sense of elegance to the appliances. Consistently applied throughout the appliance, internally and externally, this linear design creates a pristine overall appearance.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Soft-Telescopic

The BioFresh safes with **SoftTelescopic** provide a convenient, self-retracting system with soft closing, making their daily use both practical and secure.

The features shown are model dependent; look for these features in your model choice.



B 2830
Comfort



Energy efficiency class: **A** ¹

Energy consumption year / 24 hrs: 65/0.178 kWh ¹
 Total volume²: 161 litre
 Noise output: 38 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door / side walls: white / white
 Exterior dimensions in cm (h/w/d): 125/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- Ventilator
- LED lighting
- 5 BioFresh-Safes
- Cabinet can be adjusted from HydroSafe to DrySafe

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

KBbs 4374
Premium



Energy efficiency class: **C** ¹

Energy consumption year / 24 hrs: 133/0.364 kWh ¹
 Total volume²: 344 litre
 Volume: Fridge: 182.9 litre / BioFresh compartment: 137.2 litre /
 Freezer compartment: 24.1 litre
 Noise output: 36 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Freezer compartment ********

- Ice cube tray with lid
- Temperature rise time: 13 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:
KBes 4374 in SmartSteel

KBies 4370
Premium



Energy efficiency class: **C** ¹

Energy consumption year / 24 hrs: 107/0.293 kWh ¹
 Total volume²: 372 litre
 Volume: Fridge: 235.7 litre / BioFresh compartment: 137.2 litre
 Noise output: 36 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:
KBbs 4370 in BlackSteel

KB 4330
Comfort



Energy efficiency class: **D** ¹

Energy consumption year / 24 hrs: 133/0.364 kWh ¹
 Total volume²: 371 litre
 Volume: Fridge: 234.5 litre / BioFresh compartment: 137.2 litre
 Noise output: 37 dB(A)/C
 Climate rating: SN-T (from +10 °C to +43 °C)
 Door / side walls: white / white
 Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 variably adjustable from Fruit & Vegetable-Safe to DrySafe

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:
KBef 4330 with Stainless steel front

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



Kef 4370
Premium



Energy efficiency class: **C** ^A/₁

Energy consumption year / 24 hrs: 78 / 0.213 kWh ¹

Total volume²: 395 litre

Noise output: 36 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED ceiling lighting with dimmer function
- 2 BioCool-Boxes on telescopic rails

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Kef 4330
Comfort



Energy efficiency class: **D** ^A/₁

Energy consumption year / 24 hrs: 98 / 0.268 kWh ¹

Total volume²: 395 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h / w / d): 185 / 60 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioCool-Boxes on telescopic rails

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:

K 4330 in white

K 3730
Comfort



Energy efficiency class: **D** ^A/₁

Energy consumption year / 24 hrs: 93 / 0.254 kWh

Total volume²: 346 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- SmartDeviceBox: optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on telescopic rails

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Colour / material options:

Kef 3730 with Stainless steel front

Ksl 3130
Comfort



Energy efficiency class: **F** ^A/₁

Energy consumption year / 24 hrs: 139 / 0.380 kWh ¹

Total volume²: 297 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: silver / silver

Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63.1 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display for fridge compartment
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Colour / material options:

K 3130 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



The **4-star freezer** compartment is designed to freeze fresh food and store it for long periods. Temperatures of $-18\text{ }^{\circ}\text{C}$ and lower ensure that nutritional content is preserved during storage.



The **bottle shelf** is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



← 55 →



← 60 →



← 60 →



← 55 →

KSI 2834
Comfort Silver

Energy efficiency class: F A¹

Energy consumption year / 24 hrs: 197 / 0.539 kWh¹

Total volume²: 250 litre

Volume: Fridge: 229.8 litre / Freezer compartment: 21.1 litre

Noise output: 38 dB(A) / C

Climate rating: SN-ST (from $+10\text{ }^{\circ}\text{C}$ to $+38\text{ }^{\circ}\text{C}$)

Door / side walls: silver / silver

Exterior dimensions in cm (h/w/d): 140.2/55/63¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

Colour / material options:

K 2834 in white

KSI 2630
Comfort Silver

Energy efficiency class: F A¹

Energy consumption year / 24 hrs: 131 / 0.358 kWh¹

Total volume²: 248 litre

Noise output: 38 dB(A) / C

Climate rating: SN-T (from $+10\text{ }^{\circ}\text{C}$ to $+43\text{ }^{\circ}\text{C}$)

Door / side walls: silver / silver

Exterior dimensions in cm (h/w/d): 125/60/63.1¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display for fridge compartment
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

K 2630
Comfort

Energy efficiency class: F A¹

Energy consumption year / 24 hrs: 131 / 0.358 kWh¹

Total volume²: 248 litre

Noise output: 38 dB(A) / C

Climate rating: SN-T (from $+10\text{ }^{\circ}\text{C}$ to $+43\text{ }^{\circ}\text{C}$)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 125/60/63.1¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display for fridge compartment
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

K 2340
Comfort

Energy efficiency class: F A

Energy consumption year / 24 hrs: 126 / 0.345 kWh

Total volume²: 214 litre

Noise output: 38 dB(A) / C

Climate rating: SN-ST (from $+10\text{ }^{\circ}\text{C}$ to $+38\text{ }^{\circ}\text{C}$)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 114/55/63

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Plastic door shelves, Egg tray
- 5 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Under counter fridges



TP 1760

Quality in every detail



The elegant and precise **MagicEye** control with its digital temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperCool** function lowers the refrigerator temperature to +2 °C. It is perfect for quickly cooling freshly stored food.



You can freeze fresh food and store frozen food for long periods in appliances with the **4-star freezer compartment**. Temperatures of -18 °C and lower ensure food is stored with all the vital vitamins and minerals preserved.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



The **slimline door handle** is discrete and ergonomically designed for ease of opening. Under counter fridges with manual controls can be further reduced in height by **removing the tabletop** of the fridge.



Ergonomically designed, the extra deep transparent **vegetable compartments** are easy-to-clean and provide ample storage for fruit and vegetables.



Premium GlassLine door shelves with stainless steel trim. Elegant stainless steel bars help protect taller bottles and jars.

The features shown are model dependent; look for these features in your model choice.



←60→



←60→



←60→



←60→

TP 1764
Premium



Energy efficiency class:

Energy consumption year/24 hrs: 146/0.400 kWh¹

Total volume²: 135 litre

Volume: Fridge: 118.0 litre/Freezer compartment: 17.7 litre

Noise output: 34 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display for fridge compartment

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 4.7 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

TP 1760
Premium



Energy efficiency class:

Energy consumption year/24 hrs: 93/0.254 kWh¹

Total volume²: 155 litre

Noise output: 34 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8¹

Controls

- MagicEye on front, key electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

TP 1724
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 146/0.400 kWh¹

Total volume²: 143 litre

Volume: Fridge: 126.0 litre/Freezer compartment: 17.6 litre

Noise output: 37 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.29 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

TP 1720
Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 92/0.252 kWh¹

Total volume²: 145 litre

Noise output: 35 dB(A)/B, SuperSilent

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8¹

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

TPesf 1714
Comfort

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 183 / 0.501 kWh ¹

Total volume²: 143 litre

Volume: Fridge: 126.0 litre / Freezer compartment: 17.6 litre

Noise output: 37 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Stainless steel / silver

Exterior dimensions in cm (h / w / d): 85 / 60.1 / 60.8 ¹

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.36 kg

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

TPesf 1710
Comfort

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 115 / 0.315 kWh ¹

Total volume²: 145 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Stainless steel / silver

Exterior dimensions in cm (h / w / d): 85 / 60.1 / 60.8 ¹

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Colour / material options:

TP 1710 in white

T 1714
Comfort

Energy efficiency class:

Energy consumption year / 24 hrs: 183 / 0.501 kWh

Total volume²: 143 litre

Volume: Fridge: 126.0 litre / Freezer compartment: 17.6 litre

Noise output: 37 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4.36 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

T 1810
Comfort

Energy efficiency class:

Energy consumption year / 24 hrs: 118 / 0.323 kWh

Total volume²: 161 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 85 / 60.1 / 62.8

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



The space-saving integrated **LED light** ensures that the whole interior of the refrigerator is evenly and harmoniously lit. With its low energy consumption, the long-lasting LED light is an environmentally friendly solution for a perfect overview of the food in the fridge.



Models in the Comfort range feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort GlassLine comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



← 55 →



← 55 →



← 55 →



← 55 →

TP 1414 Comfort
Energy efficiency class: F A ¹
Energy consumption year/24 hrs: 176/0.482 kWh ¹
Total volume ² : 120 litre
Volume: Fridge: 106.3 litre/Freezer compartment: 14.5 litre
Noise output: 39 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/55.4/62.3 ¹

Controls
· Mechanical control in interior, control dial
· CoolPlus function
Fridge compartment
· Comfort GlassLine storage shelf with bottle holder, Egg tray
· 2 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Freezer compartment ****
· Temperature rise time: 9 h
· Freezing capacity in 24 hrs: 2 kg
Key features
· SwingDesign
· Ergonomically designed slimline handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

TP 1410 Comfort
Energy efficiency class: F A ¹
Energy consumption year/24 hrs: 114/0.312 kWh ¹
Total volume ² : 136 litre
Noise output: 37 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/55.4/62.3 ¹

Controls
· Mechanical control in interior, control dial
Fridge compartment
· Comfort GlassLine storage shelf with bottle holder, Egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Key features
· SwingDesign
· Ergonomically designed slimline handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

T 1504
Energy efficiency class: F A
Energy consumption year/24 hrs: 180/0.493 kWh
Total volume ² : 133 litre
Volume: Fridge: 116.9 litre/ Freezer compartment: 16.5 litre
Noise output: 40 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/55.4/62.3

Controls
· Mechanical control in interior, control dial
· CoolPlus function
Fridge compartment
· Plastic door shelves, Egg tray
· 2 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Freezer compartment ****
· Temperature rise time: 8 h
· Freezing capacity in 24 hrs: 5.13 kg
Key features
· SwingDesign
· Recessed handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

T 1700
Energy efficiency class: F A
Energy consumption year/24 hrs: 116/0.317 kWh
Total volume ² : 149 litre
Noise output: 37 dB(A)/C
Climate rating: SN-ST (from +10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/55.4/62.3

Controls
· Mechanical control in interior, control dial
Fridge compartment
· Plastic door shelves, Egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Key features
· SwingDesign
· Recessed handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



← 50 →



← 50 →



← 50 →



← 50 →



← 50 →

T 1414
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 176/0.482 kWh

Total volume¹: 120 litre

Volume: Fridge: 106.3 litre/Freezer compartment: 14.5 litre

Noise output: 40 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 5.35 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

T 1410
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 114/0.312 kWh

Total volume¹: 136 litre

Noise output: 36 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

T 1404

Energy efficiency class:

Energy consumption year/24 hrs: 176/0.482 kWh

Total volume¹: 120 litre

Volume: Fridge: 106.3 litre/
Freezer compartment: 14.5 litre

Noise output: 40 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial
- CoolPlus function

Fridge compartment

- Plastic door shelves, Egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- Temperature rise time: 8.9 h
- Freezing capacity in 24 hrs: 5.35 kg

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Tb 1400

Energy efficiency class:

Energy consumption year/24 hrs: 114/0.312 kWh

Total volume¹: 136 litre

Noise output: 36 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: black/black

Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

T 1400

Energy efficiency class:

Energy consumption year/24 hrs: 114/0.312 kWh

Total volume¹: 136 litre

Noise output: 36 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/50.1/62

Controls

- Mechanical control in interior, control dial

Fridge compartment

- Plastic door shelves, Egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Freezers



GN 5275

Our freezers: an overview

Featuring options such as NoFrost, SmartFrost, StopFrost and FrostProtect – Liebherr freezers offer maximum convenience. With tall, under counter and chest freezers available – Liebherr has just the right appliance whatever your requirements. Choose from a variety of sizes and select your preferred fittings.

Tall freezers



No Frost

from page 110



Smart Frost

page 118

Under counter freezers



No Frost

page 117



Smart Frost

from page 119

Chest freezers



Stop Frost

from page 126

Selected SmartFrost freezer models



Frost Protect

from page 118

No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean offering additional capacity.

Stop Frost

Frosting over of the freezer and frozen food is reduced, reducing the number of times you need to defrost the freezer. **StopFrost** prevents a vacuum from building up in our chest freezers, ensuring the lid opens easily.

Frost Protect

FrostProtect models will work in ambient **temperatures as low as -15 °C** for example in an unheated garage or outbuilding.

Quality in every detail



No Frost

The **NoFrost system** from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.



Smart Frost

With the **SmartFrost technology**, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean offering additional capacity. Freezer drawers and glass shelves made of safety glass can be removed easily.



The **status indicator** is discretely integrated into the appliance door, allowing for quick and easy assessment of the appliance status, even if the door is closed. A blue light indicates that the appliance is working properly. In the case of any other status, a red light and an audible tone are emitted.



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables individual temperature setting.



LED

Energy-efficient, powerful, long-life and environmentally friendly **LEDs** are integrated into the underside of the freezer interior to illuminate the contents of the drawers when they are opened. As soon as the door is opened, the LED lighting brightens, conveniently displaying the contents of the drawers.



So that food can be conveniently accessed with minimal effort, even if the drawers are fully stocked, all BluPerformance freezer **drawers** are sited on smooth-running **roller tracks**. For convenient removal and storage of food, the top drawer tilts slightly downwards when opened - an especially helpful feature in taller appliances. The position and size of the bottom drawer make it ideal for storing ice cream, herbs or other small items.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail



Frost Protect

Many freezers are kept outside of the normal household environment, so Liebherr has developed FrostProtect on selected models to enable these models to function in low ambient temperatures. Models indicated as FrostProtect will work in **ambient temperatures as low as -15 °C**.




Telescopic Rails

The transparent freezer drawers on **telescopic rails** are easy to access and use even when filled with heavy contents. They ensure both great visibility and optimum storage. The **FrostSafe** fully enclosed drawers prevent cold air from escaping, thereby reducing energy consumption.



The automatic **SuperFrost** function makes freezing food simple and energy efficient. It rapidly lowers the temperature to **-32 °C** to create the temperature levels required to preserve vitamins and enhance the flavour and texture of the food when consumed.



BLU Performance

BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug
2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor
4. Plinth fan with noise-damping
5. Condenser
6. Defrost water drain




The freezer drawers in the BluPerformance appliances can be easily opened on **roller tracks**. The drawers and intervening glass shelves in all appliances can be removed to create **VarioSpace** - a no-fuss system for quickly creating extra storage space.



If you are not using the entire freezer space, unused drawers can be switched off with the optional **Vario Energy-Saving Panel**. Energy consumption can then be reduced again by up to 30%.

The features shown are model dependent; look for these features in your model choice.

NoFrost freezers



← 70 →



← 70 →



← 70 →



← 70 →

GN 5275 Premium



Energy efficiency class: ¹

Energy consumption year/24 hrs: 179/0.490 kWh ¹

Total volume²: 369 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 195/70/75 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4635 Comfort



Energy efficiency class: ¹

Energy consumption year/24 hrs: 210/0.575 kWh ¹

Total volume²: 320 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 175/70/75 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 7 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 17 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4135 Comfort



Energy efficiency class: ¹

Energy consumption year/24 hrs: 197/0.539 kWh ¹

Total volume²: 270 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 155/70/75 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 6 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 3835 Comfort



Energy efficiency class: ¹

Energy consumption year/24 hrs: 183/0.501 kWh ¹

Total volume²: 221 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 135/70/75 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 5 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 15 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost freezers



GN 4375
Premium



Energy efficiency class: **D** ^A/_G ¹

Energy consumption year / 24 hrs: 198 / 0.542 kWh ¹

Total volume²: 276 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNef 4335
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year / 24 hrs: 248 / 0.679 kWh ¹

Total volume²: 276 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNi 4335
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year / 24 hrs: 248 / 0.679 kWh

Total volume²: 276 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 185 / 60 / 66.5

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox included
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 3735
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year / 24 hrs: 235 / 0.643 kWh ¹

Total volume²: 238 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 165 / 60 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 7 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 17 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 3235
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year / 24 hrs: 221 / 0.605 kWh ¹

Total volume²: 200 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 145 / 60 / 66.5 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 6 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 2835
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year / 24 hrs: 208 / 0.569 kWh

Total volume²: 161 litre

Noise output: 38 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 125 / 60 / 66.5

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 5 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 15 kg
- 1 Cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

NoFrost freezers



← 60 →



← 60 →



← 60 →



← 60 →

GNP 3013 Comfort



Energy efficiency class: **F A G** ¹

Energy consumption year / 24 hrs: 307 / 0.841 kWh ¹

Total volume²: 268 litre

Noise output: 41 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 184.1 / 60 / 63 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8.5 h
- Freezing capacity in 24 hrs: 13.5 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

GNP 2713 Comfort



Energy efficiency class: **F A G** ¹

Energy consumption year / 24 hrs: 291 / 0.797 kWh ¹

Total volume²: 231 litre

Noise output: 41 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 164.4 / 60 / 63 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 7 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8.1 h
- Freezing capacity in 24 hrs: 13.1 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

GNP 2313 Comfort



Energy efficiency class: **F A G** ¹

Energy consumption year / 24 hrs: 275 / 0.753 kWh ¹

Total volume²: 195 litre

Noise output: 41 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 144.7 / 60 / 63 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 6 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8.3 h
- Freezing capacity in 24 hrs: 13.2 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

GNP 1913 Comfort



Energy efficiency class: **F A G** ¹

Energy consumption year / 24 hrs: 258 / 0.706 kWh ¹

Total volume²: 158 litre

Noise output: 40 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 125 / 60 / 63 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 5 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8.4 h
- Freezing capacity in 24 hrs: 11.8 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front, transport castors at back
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



GNP 1066

Under counter NoFrost freezers



← 60 →



← 60 →

GNP 1066 Premium

No Frost

Energy efficiency class: **E** ¹

Energy consumption year / 24 hrs: 186 / 0.509 kWh ¹

Total volume²: 99 litre

Noise output: 39 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 85.1 / 60.2 / 62.8 ¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *******

- 3 drawers, VarioSpace
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GN 1066 Premium

No Frost

Energy efficiency class: **F** ¹

Energy consumption year / 24 hrs: 232 / 0.635 kWh

Total volume²: 99 litre

Noise output: 41 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 85.1 / 60.2 / 62.8

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment *******

- 3 drawers, VarioSpace
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 11 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



GP 2733
Comfort



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 262/0.717 kWh ¹

Total volume²: 224 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 164.4/60/63 ¹

- Controls**
- MagicEye on front, key electronic
 - Graphic temperature display
 - Automatic SuperFrost, time-controlled
 - Warning signal in case of fault: visual and acoustic
- Freezer compartment** ********
- 7 drawers, VarioSpace
 - Temperature rise time: 19 h
 - Freezing capacity in 24 hrs: 11 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Slimline handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging

GP 2433
Comfort



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 249/0.682 kWh ¹

Total volume²: 191 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 144.7/60/63 ¹

- Controls**
- MagicEye on front, key electronic
 - Graphic temperature display
 - Automatic SuperFrost, time-controlled
 - Warning signal in case of fault: visual and acoustic
- Freezer compartment** ********
- 6 drawers, VarioSpace
 - Temperature rise time: 19 h
 - Freezing capacity in 24 hrs: 10 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Slimline handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging

GP 2033
Comfort



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 235/0.643 kWh ¹

Total volume²: 157 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 125/60/63 ¹

- Controls**
- MagicEye on front, key electronic
 - Graphic temperature display
 - Automatic SuperFrost, time-controlled
 - Warning signal in case of fault: visual and acoustic
- Freezer compartment** ********
- 5 drawers, VarioSpace
 - Temperature rise time: 19 h
 - Freezing capacity in 24 hrs: 9 kg
 - Safety glass fittings
- Key features**
- SwingLine design
 - Slimline handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles at back
 - Height-adjustable feet at front, transport castors at back
 - Reversible door hinging

The elegant and precise **MagicEye control** with its temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use. The automatic **SuperFrost** function quickly reduces the temperature to freeze your food while preserving the vitamins.



The **tabletop** of the under counter freezers is extremely robust, with a scratch and heat resistant surface.

GP 1486
Premium



Energy efficiency class: **D** ^A/_G ¹

Energy consumption year/24 hrs: 137/0.375 kWh ¹

Total volume²: 102 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/60.2/62.8 ¹

- Controls**
- MagicEye on front, key electronic
 - Digital temperature display
 - Automatic SuperFrost, quantity-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
- Freezer compartment** ********
- 4 drawers, VarioSpace
 - Temperature rise time: 14.6 h
 - Freezing capacity in 24 hrs: 8.2 kg
 - Safety glass fittings
- Key features**
- SwingDesign
 - Ergonomically designed slimline handle
 - Versatile installation due to front ventilation
 - Height-adjustable feet at front
 - Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



← 60 →



← 55 →



← 55 →



← 55 →



← 55 →

GPesf 1476
Premium



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year/24 hrs: 171/0.468 kWh ¹

Total volume²: 102 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 85.1/60.2/61 ¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic

Freezer compartment ********

- 4 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:

GP 1476 in white

GP 1376
Premium



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year/24 hrs: 171/0.468 kWh ¹

Total volume²: 102 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4 ¹

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic

Freezer compartment ********

- 4 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- 2 Cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GP 1213
Comfort



Energy efficiency class: **E** ^A/_G ¹

Energy consumption year/24 hrs: 170/0.465 kWh ¹

Total volume²: 97 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4 ¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ********

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

G 1213



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 213/0.583 kWh

Total volume²: 97 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ********

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Recessed handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GX 823
Comfort



Energy efficiency class: **F** ^A/_G ¹

Energy consumption year/24 hrs: 199/0.545 kWh

Total volume²: 68 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 63.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment ********

- 2 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.


² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Chest freezers



CFd 2085

Quality in every detail



Stop Frost

StopFrost prevents a vacuum from building up, ensuring the lid opens easily. Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer.



Soft System

Chest freezers in the Plus range benefit from the **SoftSystem** closing mechanism, a convenient and desirable feature for everyday use. Integrated into the hinges on the freezer lid, SoftSystem allows the lid to close gently and prevents slamming.



The heat-exchange **condenser** is embedded in foam along the exterior wall, minimising vibration and promoting quieter operation. No condensation forms on the easy-to-clean outside walls.



Frost Protect

Due to their shape and size, many chest freezers are kept outside of the normal household environment so Liebherr has developed FrostProtect to enable these models to work in low ambient temperatures. All chest freezer models will work in **ambient temperatures as low as -15 °C**.



The bright **LED interior light** allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



The automatic **SuperFrost function** quickly reduces the temperature to freeze your food while preserving the vitamins. As soon as the food is completely frozen, the automated SuperFrost function switches back to normal mode.

The features shown are model dependent; look for these features in your model choice.



←168→



←126→



←168→



←126→



←105→

CFd 2505
Plus



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 188/0.515 kWh

Total volume¹: 359 litre

Noise output: 32 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 82.5/167.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 15 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 5 Suspension baskets as standard, 1 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

CFd 2085
Plus



Energy efficiency class: **D** ^A/_G

Energy consumption year / 24 hrs: 162/0.443 kWh

Total volume¹: 248 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 82.5/125.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 10 kg
- 1 Cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 3 Suspension baskets as standard, 1 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

CFF 2500
Pure



Energy efficiency class: **F** ^A/_G

Energy consumption year / 24 hrs: 324/0.887 kWh

Total volume¹: 497 litre

Noise output: 33 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 82.5/167.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 20 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 5 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

CFF 2080
Pure



Energy efficiency class: **F** ^A/_G

Energy consumption year / 24 hrs: 274/0.750 kWh

Total volume¹: 353 litre

Noise output: 32 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 82.5/125.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 15 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 3 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

CFF 1870
Pure



Energy efficiency class: **F** ^A/_G

Energy consumption year / 24 hrs: 249/0.682 kWh

Total volume¹: 281 litre

Noise output: 32 dB(A)/B, SuperSilent

Climate rating: SN-T (from +10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door / side walls: white / white

Exterior dimensions in cm (h/w/d): 82.5/104.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 10 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 2 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Wine cabinets



Find out more about
Wine cabinets:
wine.cabineer.com/en

WTes 5872

Our wine cabinets: an overview

+5 °C to +20 °C

+5 °C to +20 °C

+5 °C to +20 °C



Vinidor range



The Vinidor range offers maximum flexibility with two separately controlled temperature zones. The temperature of these can be set independently between +5 °C and +20 °C. This means that red and white wines can be stored at their ideal serving temperatures in the same cabinet. These cabinets not only provide the ideal climate conditions for long-term storage of wine, but with differently sized zones and fully adjustable temperature controls, they are suitable for every wine collection.

+5 °C to +20 °C



GrandCru and Vinothek range



Wine storage cabinets offer similar conditions to a wine cellar. This range facilitates the storage of red and white wines at the correct long term storage temperatures or individual serving temperatures. The temperature can be adjusted from +5 °C to +20 °C as appropriate, and is both even and constant throughout the entire appliance interior.

Wine lovers have the most stringent demands when it comes to storing their favourite wines. Many like to be able to enjoy their fine wines on the spur of the moment; others prefer to establish a collection of wines over the longer term; and some want the best of both worlds. Liebherr offers premium wine storage cabinets that guarantee perfect long term wine storage and serving temperatures, whatever your requirements. With heating and cooling circuits and air filtration, our wine cabinets offer unsurpassed wine storage conditions.



Vinidor – from page 134



GrandCru – page 136



Vinothek – page 137



Design & Lifestyle – page 139

Quality in every detail



The electronic LCD display offers clear menu navigation and a **Touch-electronic control system** provides bespoke storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions. The Vinidor 2 and 3 zone models feature an integrated door seal in the dividing shelf to maintain correct individual temperatures.



The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The **clip-on labelling system** provides a quick and clear overview of your wine store.



The **LED lighting** in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with no-heat LED lighting. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The **tinted safety glass** in Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical aluminium **door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.



The **SoftSystem** feature provides added safety and convenience. Integrated within the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 45°.

The features shown are model dependent; look for these features in your model choice.

Wine storage cabinets Vinidor



← 70 →



← 70 →



← 60 →

WTes 5872 Vinidor



Energy efficiency class: **G** ^A/_B ²

Energy consumption year / 24 hrs: 206 / 0.564 kWh ²

Max. Bordeaux bottles 0.75 l: 178 ¹

Total volume³: 503 litre

Noise output: 35 dB(A)/B, SuperSilent

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 192 / 70 / 74.2 ²

Controls

- LCD display in the interior, touch electronic
- Digital temperature display for 3 wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 3 Temperature zones, which can set from +5 °C to +20 °C
- 3 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 13 Shelves, of which 10 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

WTes 5972 Vinidor



Energy efficiency class: **G** ^A/_B ²

Energy consumption year / 24 hrs: 191 / 0.523 kWh ²

Max. Bordeaux bottles 0.75 l: 211 ¹

Total volume³: 521 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 192 / 70 / 74.2 ²

Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

The **LED lighting** in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The electronic LCD display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.

WTes 1672 Vinidor



Energy efficiency class: **G** ^A/_B

Energy consumption year / 24 hrs: 147 / 0.402 kWh

Max. Bordeaux bottles 0.75 l: 34 ¹

Total volume³: 95 litre

Noise output: 36 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 82.2 / 59.8 / 57.5

Controls

- MagicEye control in interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

Key features


- HardLine
- Aluminium handle
- Reversible door hinging
- Replaceable door seal
- Lock

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

³ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Wine storage cabinets GrandCru



← 75 →




← 70 →

Wine storage cabinets Vinothek



← 60 →



← 60 →



← 60 →

WKt 6451 GrandCru



Energy efficiency class: **F** **A** **G**

Energy consumption year / 24 hrs: 125/0.342 kWh

Max. Bordeaux bottles 0.75 l: 312 ¹

Total volume²: 614 litre

Noise output: 39 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Full door, terra / terra

Exterior dimensions in cm (h/w/d): 193/74.7/75.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood shelves
- 7 Shelves

Key features

- SwingLine design
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Lock

WKt 5552 GrandCru



Energy efficiency class: **G** **A** **G**

Energy consumption year / 24 hrs: 147/0.402 kWh

Max. Bordeaux bottles 0.75 l: 253 ¹

Total volume²: 526 litre

Noise output: 39 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door, frame terra / terra

Exterior dimensions in cm (h/w/d): 192/70/74.2

Controls

- MagicEye in the interior, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on
- Adjustable beech wood shelves
- 7 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

WKb 4212 Vinothek



Energy efficiency class: **G** **A** **G**

Energy consumption year / 24 hrs: 177/0.484 kWh

Max. Bordeaux bottles 0.75 l: 200 ¹

Total volume²: 402 litre

Noise output: 39 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door, frame black / black

Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Adjustable beech wood shelves
- 6 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

WKr 4211 Vinothek



Energy efficiency class: **F** **A** **G**

Energy consumption year / 24 hrs: 108/0.295 kWh

Max. Bordeaux bottles 0.75 l: 200 ¹

Total volume²: 383 litre

Noise output: 37 dB(A)/C

Climate rating: SN-T (from +10 °C to +43 °C)

Door / side walls: Full door, burgundy / black

Exterior dimensions in cm (h/w/d): 165/60/73.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Adjustable beech wood shelves
- 6 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging

WKb 1812 Vinothek



Energy efficiency class: **G** **A** **G**

Energy consumption year / 24 hrs: 123/0.337 kWh

Max. Bordeaux bottles 0.75 l: 66 ¹

Total volume²: 135 litre

Noise output: 38 dB(A)/C

Climate rating: SN-ST (from +10 °C to +38 °C)

Door / side walls: Glass door, frame black / black

Exterior dimensions in cm (h/w/d): 89/60/61.3

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- Interior lighting permanently on
- Adjustable grid shelves
- 3 Shelves

Key features

- HardLine
- Ergonomically designed slimline handle, black
- Reversible door hinging
- Replaceable door seal

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.



WKes 653

Design & Lifestyle



← 43 →



← 43 →

WKes 653 GrandCru



Energy efficiency class: **E** ^A/_B

Energy consumption year / 24 hrs: 78 / 0.213 kWh

Max. Bordeaux bottles 0.75 l: 12 ¹

Total volume²: 48 litre

Noise output: 37 dB(A)/C

Climate rating: SN (from +10 °C to +32 °C)

Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

Controls

- LCD display in the interior, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves

Key features

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- Utensil drawer
- Suitable for wall mounting
- Lock

ZKes 453 Humidor



Energy efficiency class:

Energy consumption year / 24 hrs: 162 / 0.443 kWh

Total volume: 43 litre

Noise output: 40 dB(A)

Climate rating: N (from +16 °C to +32 °C)

Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 61.2 / 42.5 / 47.8

Controls

- LCD display in the interior, touch electronic
- Digital display of temperature and humidity
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Humidor

- 1 Temperature zone, which can set from +16 °C to +20 °C
- Humidity range, adjustable between 68% to 75%
- Convection cooling, fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 Shelves

Key features

- HardLine
- Fixed door hinge, right
- Replaceable door seal
- 2 presentation boxes
- Suitable for wall mounting
- Lock

¹ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at page 15. According to (EU) 2017/1369 6a.

Our catalogues

Find out everything you need to know about Liebherr Freestanding & Built-In refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as PDF downloads from home.liebherr.com.



Smart communication on all fronts



SmartDevice-App

Discover the many advantages of being able to control your refrigerator or freezer from any place and at any time.



BioFresh-App

Useful information about perfect food storage, as well as vitamin and mineral content.



Smoothies & Ice-App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type. apps.home.liebherr.com



Find out more about smartdevice.liebherr.com

View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



biofresh.liebherr.com



nofrost.liebherr.com



wine.liebherr.com



The fresh world of **FreshMAG**: Find out more about our models, food storage, nutrition, recipes and much more.



Click the link to directly access our social media channels: socialmedia.home.liebherr.com

Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle.