



ColourLine
Special 2018

LIEBHERR

Quality, Design and Innovation

ColourLine -

as colourful as life!

The fridge is gaining importance as a designer object and head turner in modern kitchens. Colour also plays a very important role here.

With ColourLine, Liebherr is now offering six modern trend colours in different fridge-freezers, and therefore the right model for almost any freshness needs.

Whether you choose a small, compact TopFreezer (from page 10), fridge-freezers with the practical SmartFrost function (from page 6) or with no-more-defrosting convenience (here on the right) - with a ColourLine model from Liebherr you can combine your individual and unique lifestyle with perfect freshness and convenience.



CNno 4313
NeonOrange



CNkw 4313
KiwiGreen



CNfb 4313
FrozenBlue

Quality in every detail



Duo Cooling

Accurate and independent temperature control of the fridge and freezer compartments is facilitated by **DuoCooling**: two separately adjustable cooling circuits. There is no air exchange between the fridge and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out.



The laterally integrated grip handles allow **ergonomic door opening** from almost any angle and are perfect for a handle free kitchen-look.



The interior is fitted with high quality **safety glass storage shelves** that are easy to clean and have a high load-bearing capacity. The **bottle shelf** is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



CNno 4313	CNkw 4313	CNfb 4313
No Frost A++ Duo Cooling		
Energy efficiency class: $\langle A \rangle^1$		
Energy consumption year/24 hrs: 240/0.655 kWh ¹		
Total net capacity: 304 litre (Fridge: 209 litre/Freezer compartment: 95 litre)		
Noise output: 42 dB(A)		
Climate rating: SN-T (+10°C to +43°C)		
Exterior dimensions in cm (h/w/d): 186.1/60/65.5 ¹		



The precision **key electronics** with MagicEye-Display ensure easy, degree-accurate temperature adjustment.



The elegant, single-piece plastic **door shelving** has a shapely structure - with clear lines and contours - that harmoniously complements the overall angular design concept.



The space-saving **LED ceiling lighting** is elegantly integrated and provides uniform illumination throughout the entire refrigerator interior. The high-performance **PowerCooling system** ensures that freshly stored produce are rapidly cooled and that an even temperature is maintained throughout the appliance interior.

- | | |
|--|--|
| <p>Controls</p> <ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm fridge compartment: acoustic <p>Fridge compartment</p> <ul style="list-style-type: none"> · PowerCooling · Plastic door shelves, Egg tray · 4 GlassLine storage shelves · Bottle shelf · LED ceiling lighting · 1 spacious fruit and vegetable drawer | <p>Freezer compartment ****</p> <ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 26 h · Freezing capacity in 24 hrs: 9 kg <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Vertical recessed handles · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal <p>Colour / material options:</p> <ul style="list-style-type: none"> CNno 4313 in NeonOrange CNkw 4313 in KiwiGreen CNfb 4313 in FrozenBlue |
|--|--|

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



CUfr 3311
FireRed

CUwb 3311
WaterBlue

CUJag 3311
AvocadoGreen



CTPfr 2121
FireRed

CTPwb 2121
WaterBlue

CTPag 2121
AvocadoGreen

Quality in every detail



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



The sturdy **handle with** its refined, premium-quality appearance and **an integrated opening mechanism** ensures easy and effortless opening of the door. The handle perfectly compliments the HardLine door design, and is made from anodised aluminium or white plastic. It can be easily repositioned if the hinge side of the door is changed.



The **bottle shelf** is the practical and elegant answer for storing drinks. As many as five bottles can be chilled and stored neatly.



55

CUfr 3311	CUwb 3311	CUag 3311
Smart Frost A**		
Energy efficiency class: $\langle A^+ \rangle^1$		
Energy consumption year/24 hrs: 210/0.575 kWh ¹		
Total net capacity: 294 litre (Fridge: 210 litre/Freezer compartment: 84 litre)		
Noise output: 39 dB(A)		
Climate rating: SN-ST (+10°C to +38°C)		
Exterior dimensions in cm (h/w/d): 181.2/55/63 ¹		



The **LED ceiling light** creates a high-class lighting ambience within the refrigerator. The **CoolPlus function** reduces the temperature in the freezer compartment for several hours so that food can be frozen quickly and safely.



Models in the Comfort range now feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort Glassline comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.

Controls	Key features
<ul style="list-style-type: none"> Mechanical control in interior, control dial Individually regulated cooling circuits: 1 CoolPlus function 	<ul style="list-style-type: none"> SwingLine design Aluminium handles with integrated opening mechanism Versatile installation due to front ventilation Height-adjustable feet at front Reversible door hinging
Fridge compartment <ul style="list-style-type: none"> Comfort GlassLine storage shelf with bottle holder, Egg tray 4 GlassLine storage shelves, of which one is divided into two parts Bottle shelf LED lighting 2 fruit and vegetable drawers 	Colour / material options: CUfr 3311 in FireRed CUwb 3311 in WaterBlue CUag 3311 in AvacadoGreen
Freezer compartment **** <ul style="list-style-type: none"> 3 drawers, VarioSpace Ice cube tray Temperature rise time: 27 h Freezing capacity in 24 hrs: 4 kg Safety glass fittings 	

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.



CTPag 2121
AvocadoGreen

SmartFrost Fridge-Freezers

Colour
Line



The large **4* freezer above the fridge section** provides plenty of space to freeze fresh food in a way that conserves vitamins and minerals and store it for long periods. The safety glass shelf can be inserted flexibly and makes it easier to see and access the stored goods.



The elegant **recessed handle** in CTP models is ergonomically positioned and makes the appliance easy to open. Ideal for handle-free kitchens.



55

CTPfr 2121 Comfort CTPwb 2121 Comfort CTPag 2121 Comfort



Energy efficiency class: **A++**¹

Energy consumption year/24 hrs: 176/0.480 kWh¹

Total net capacity: 195 litre (Fridge: 151 litre/Freezer compartment: 44 litre)

Noise output: 39 dB(A)

Climate rating: SN-T (+10°C to +43°C)

Exterior dimensions in cm (h/w/d): 124.1/55/63¹

Controls

- Mechanical control in interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, Egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment


- Ice cube tray
- Temperature rise time: 22 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Colour / material options:

- CTPfr 2121** in FireRed
- CTPwb 2121** in WaterBlue
- CTPag 2121** in AvocadoGreen



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.

Overview ColourLine program



Type/model numbers	CNno/kw/fb 4313	CUfr/wb/ag 3311	CTPfr/wb/ag 2121
	No Frost Duo Cooling	Smart Frost	Smart Frost Comfort
Energy efficiency class	$\langle A^+ \rangle^1$	$\langle A^+ \rangle^1$	$\langle A^+ \rangle^1$
Energy consumption year/24 hrs ²	240/0.655 kWh ¹	210/0.575 kWh ¹	176/0.480 kWh ¹
Total net capacity	304 litre	294 litre	195 litre
Fridge compartment	209 litre	210 litre	151 litre
Freezer compartment	95 litre	84 litre	44 litre
Star coding ³	***	***	***
Temperature rise time	26 h	27 h	22 h
Freezing capacity in 24 hrs	9 kg	4 kg	4 kg
Climate rating ⁴	SN-T (+10°C to +43°C)	SN-ST (+10°C to +38°C)	SN-T (+10°C to +43°C)
Noise output	42 dB(A)	39 dB(A)	39 dB(A)
Voltage	220-240V~	220-240V~	220-240V~
Connection rating	1.4 A	1.4 A	1.0 A
Fridge compartment			
Defrosting	Automatic	Automatic	Automatic
PowerCooling	■		
Interior light	LED ceiling lighting	LED	LED
Fruit and vegetable bins	1 spacious fruit and vegetable drawer	2	1
Bottle shelf	Bottle shelf	Bottle shelf	
Door interior	Plastic	Comfort-GlassLine	Comfort-GlassLine
Freezer compartment			
Freezing Technology	NoFrost	SmartFrost	SmartFrost
Defrosting	Automatic	Manual	Manual
CoolPlus function		■	
Automatic SuperFrost	time-controlled		
VarioSpace	■	■	
Ice cube tray	■	■	■
Dimensions			
Exterior dimensions in cm (h/w/d)	186.1/60/65.5 ¹	181.2/55/63 ¹	124.1/55/63 ¹
Features			
Design	HardLine	SwingLine	SwingLine
Handle	Vertical recessed handles	Stainless steel slimline handles with integrated opening mechanism	Recessed handles
Controls	MagicEye behind-the-door, key electronic	Mechanical control in interior, control dial	Mechanical control in interior, control dial

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² According to (EU) 1060/2010

³ *** freezer compartment with -18°C or colder

⁴ Climate Ratings: SN +10°C to +32°C ST +16°C to +38°C
T +16°C to +43°C

You can find the full range of efficiency classes at page 11. According to (EU) 2017/1369 6a.