

Food Centres Special
2018/2019



LIEBHERR

Quality, Design and Innovation



Side-by-Side fridge-freezers Large capacity food centres

Healthy food is the current trend in a modern lifestyle. Our Side-by-Side appliances are the ideal solution for giving large capacity storage for your food. They offer ample space for large food stocks with various climate zones for perfect food storage. When refrigerating large amounts of food you have a choice of refrigerators, BioFresh, Freezer, Wine climate zone and IceMakers. The exclusive design makes our Side-by-Side fridge-freezers the healthy focal point of any kitchen.

Refrigeration

A spacious fridge compartment with an adjustable temperature range from +3 °C to +9 °C ensures constant freshness every day.

BioFresh

At a temperature of just over 0 °C, large quantities of food, such as meat, fish, fruit, vegetables and dairy products, can be stored in the spacious BioFresh drawers significantly longer than in a conventional fridge compartment.

BioFresh-Plus

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment.

Freezing

The NoFrost freezer compartment with automatic IceMaker offers a continuous supply of ice. Food is frozen with refrigerated recirculated air and the humidity is dissipated. This keeps the freezer compartment free of ice preventing the food from frosting over. Defrosting is no longer necessary.

Multi-temperature wine compartment

The multi-temperature wine compartment of the SBSes 8486 has two independently adjustable zones for storing wine at the exact temperature required, between +5 °C and +20 °C. Red wines, white wines and champagne can be stored together at their individual optimum drinking temperatures.



Extremely low energy consumption

Liebherr has always been committed to energy efficiency, which plays a key role from the design stage onward.

Precision electronic controllers combined with optimised refrigeration components, highly insulating materials and very efficient compressors ensure that our appliances provide excellent energy efficiency.

Once again, Liebherr is leading the way with its current range of refrigerators and freezers, offering an attractive selection of appliances in energy efficiency classes A+ to A+++/-20%.



No Frost

The **NoFrost** system provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door.



Bio Fresh

BioFresh guarantees the perfect climate for extra long freshness. A temperature slightly above 0 °C and ideal air humidity maintain the delicate aroma and appetising appearance of fruit and vegetables, meat, fish and milk products significantly longer than in a standard fridge.

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile **Fish & Seafood Box**.




Bio Fresh-Plus



Wine

The Side-by-Side fridge-freezer **SBSes 8486** with six different climate zones offers a range of innovative solutions. The wine compartment has two independently adjustable zones for storing wine at the exact temperature required, between +5 °C and +20 °C.



BLU Performance

High quality materials, meticulous workmanship in every detail, and easy-to-use/precise touch-electronics define the **BLUPerformance** range. The compact integration of refrigeration technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics.



Ice Maker

The **plumbed-in IceMaker** provides high-quality ice cubes. The two drawers hold all the ice you need for any occasion. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.

The features shown are model dependent; the description applies to the relevant model.



Six climate zones in one appliance: SBSes 8486



The Side-by-Side fridge-freezer SBSes 8486 with six different climate zones boasts an array of innovative solutions. The multi-temperature wine compartment has two independently adjustable zones for storing wine at the exact temperature required, ranging from +5 °C to +20 °C. The NoFrost freezer compartment with automatic IceMaker provides professional freezing technology for long-term freshness, while a spacious fridge compartment keeps food fresh on a day-to-day basis. In the BioFresh

compartment, fruit, vegetables, meat and dairy products stay fresh for significantly longer at around 0 °C. With the adjustable temperature range of 0 °C and -2 °C BioFresh-Plus offers even more flexibility. The BioFresh-Plus safe includes a versatile Fish & Seafood Box. In short, the climate zones, refrigeration, BioFresh, freezing and wine, guarantee the optimal storage temperature for an array of produce.



You can choose to store red or white wine and champagne together or separately at their optimal drinking temperature in one and the same appliance. The tinted glazed door with UV protection makes an attractive focal point of your wine stock. For presentation, the LED interior light can be individually adjusted and has a continuous dimmer function. Since any heat generated by the LEDs is minimal, wines can be presented bathed in light for a longer period. The wooden shelves are mounted on telescopic rails and are foldable in some cases.



The BioFresh-Plus drawers are illuminated by LED technology for an optimal overview of the stored contents. They are also mounted on smooth-running telescopic rails and can be pulled out and removed at a door opening angle of just 90°. BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile Fish & Seafood Box.



SBSes 8486
PremiumPlus

Bio Fresh-Plus
No Frost
A++
Ice Maker
Wine
Soft System
Soft Telescopic
Smart Steel

Energy efficiency class: **A++**¹
 Energy consumption year / 24 hrs: 320/0.874 kWh¹
 Max. Bordeaux bottles 0.75 l: 48²
 Total net capacity: 645 litre (Fridge: 519 litre including BioFresh compartment: 132 litre including wine compartment: 153 litre/Freezer compartment: 126 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185.2/121/66.5¹

Controls
 2.4" TFT-colour display behind-the-door, touch electronic
 Digital temperature display for fridge, BioFresh, wine and freezer compartments



The IceMaker provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.
² Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).
 You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



An optical highlight in BlackSteel: SBSbs 8673



The BluPerformance range is characterised by premium-quality materials, craftsmanship in every detail, and precision touchscreen electronic controls. The integration of all the refrigeration components into the base of the appliance, together with optimised electronic controls, ensures maximum energy efficiency, a greater

net capacity, and enhanced freezer compartment ergonomics. The BioFresh technology keeps stored food fresher for longer. The elegant and timeless design of the BluPerformance range ensures that these appliances are a guaranteed highlight in any home and that they will satisfy for many years to come.



The **BlackSteel** is a highly attractive and unusual black stainless steel finish which catches every eye. Paired with the high quality SmartSteel finish, this new material lends the Side-by-Side fridge-freezer a hi-tech appeal whilst retaining a timeless elegance. The transverse polished finish creates an exclusive, visually appealing look, making the BlackSteel models a true highlight of every kitchen. The practical **aluminium door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The distinctive **Premium GlassLine** equipment puts the finishing touches to the overall impression of high quality conveyed by the interior. The shelves are made of safety glass, as are the racks with stainless steel trims in the door interior. The sectioned, slide-under glass shelf lends itself to versatile use as it can be inserted at different heights, as required. The **VarioSafe** drawer is the perfect place to keep smaller items. The drawer can be positioned at various levels elevations on the lighting columns.



SBSbs 8673
Premium

Bio Fresh	No Frost	A+++	Ice Maker	Soft System	Soft Telescopic	Black Steel
-----------	----------	------	-----------	-------------	-----------------	-------------

Energy efficiency class: **A+++**¹
 Energy consumption year/24 hrs: 255/0.696 kWh¹
 Total net capacity: 629 litre (Fridge: 367 litre including BioFresh compartment: 133 litre/Freezer compartment: 262 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel
 Exterior dimensions in cm (h/w/d): 185/121/66.5¹

Controls
 2.4" TFT-colour display behind-the-door, touch electronic
 Digital temperature display for fridge, BioFresh and freezer compartments



In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0 °C.



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



The BluPerformance Side-by-Side fridge-freezer: SBSes 8663



With their elegant and timeless design, Liebherr Side-by-Side fridge-freezers meet the highest aesthetic demands. The design quality offered by our appliances is evident throughout: from the use of premium-quality materials to the detailed design. To consistently fulfil our high quality standards, we

evaluate every new design on the basis of its practicality and ease-of-use for our customers. The high-resolution, high-contrast 2.4" touchscreen display is located behind the door and can be read from any angle. The stored menu options are intuitive and easy-to-operate.



Maintenance-free and energy efficient: long-life LEDs provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity). The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir activated charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles. The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a homogeneous, high-quality lighting concept.



SBSes 8663 Premium



Energy efficiency class: **A+++**¹

Energy consumption year / 24 hrs: 258 / 0.702 kWh¹

Total net capacity: 635 litre (Fridge: 367 litre including BioFresh compartment: 133 litre / Freezer compartment: 268 litre)

Noise output: 38 dB(A)

Climate rating: SN-T (+10°C to +43°C)

Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel

Exterior dimensions in cm (h / w / d): 185 / 121 / 66.5¹

Controls

2.4" TFT-colour display behind-the-door, touch electronic

Digital temperature display for fridge, BioFresh and freezer compartments



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



The Side-by-Side fridge-freezer with extra large BioFresh compartment: SBSes 8473



Apart from a spacious refrigerator compartment, the Side-by-Side fridge-freezer SBSes 8473 also offers two large BioFresh drawers. Foods such as fruit, vegetables, meat, fish and dairy products stay fresher significantly longer in the BioFresh compartment

compared to the conventional refrigerator compartment. The NoFrost freezer technology provides frost free freezing for the safe long-term storage of food, making defrosting a thing of the past; with its automatic IceMaker providing a plentiful supply of ice for any occasion.



The **BioFresh** drawers provide the perfect climate for lasting food freshness. At a temperature of just over 0 °C and ideal humidity, fruit and vegetables, meat and fish retain their healthy vitamins, their delicate aroma and their appetising appearance significantly longer than in a conventional refrigerator compartment.



The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker with fixed water connection, which you can switch off at any time, automatically keeps your supplies topped up.



SBSes 8473 Premium	Bio Fresh	Bio Cool	No Frost	A+++	Ice Maker	Soft System	Soft Telescopic	Smart Steel
------------------------------	-----------	----------	----------	------	-----------	-------------	-----------------	-------------

Energy efficiency class: $\langle A^{+++}/A^{+++} \rangle^1$
Energy consumption year/24 hrs: 251/0.686 kWh ¹
Total net capacity: 688 litre (Fridge: 562 litre including BioFresh compartment: 172 litre/Freezer compartment: 126 litre)
Noise output: 37 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 185.2/121/66.5 ¹

Controls
2.4" TFT-colour display behind-the-door, touch electronic
Digital temperature display for fridge, BioFresh and freezer compartments



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the appliance's net capacity).

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



The Side-by-Side fridge-freezer with extra large BioFresh compartment: SBSef 7343

Bio Fresh No Frost

Apart from a spacious refrigerator compartment, the Side-by-Side fridge-freezer SBSef 7343 also offers two large BioFresh drawers. Foods such as fruit, vegetables, meat, fish and dairy products stay fresher significantly longer in the BioFresh compartment compared to

the conventional refrigerator compartment. The NoFrost freezer technology provides frost free freezing for the safe long-term storage of food, making defrosting a thing of the past; with its automatic IceMaker providing a plentiful supply of ice for any occasion.



The **BioFresh drawers** provide the perfect climate for lasting food freshness. At a temperature of just over 0 °C and ideal humidity, fruit and vegetables, meat and fish retain their healthy vitamins, their delicate aroma and their appetising appearance significantly longer than in a conventional refrigerator compartment.

The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker with fixed water connection, which you can switch off at any time, automatically keeps your supplies topped up.



SBSef 7343 Comfort	Bio Fresh	No Frost	A++	Ice Maker	Smart Steel
Energy efficiency class: A++ ¹					
Energy consumption year/24 hrs: 383/1.048 kWh ¹					
Total net capacity: 654 litre (Fridge: 539 litre including BioFresh compartment: 155 litre/Freezer compartment: 115 litre)					
Noise output: 40 dB(A)					
Climate rating: SN-T (+10°C to +43°C)					
Door/side walls: Stainless steel with SmartSteel/silver					
Exterior dimensions in cm (h/w/d): 185.2/121/63 ¹					
Controls					
MagicEye behind-the-door, touch electronic					
Digital temperature display for fridge, BioFresh and freezer compartments					



SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Side-by-Side fridge-freezer with two temperature zones: SBSef 7242

No Frost

With the eight drawer NoFrost freezer compartment, the Side-by-Side fridge-freezer SBSef 7242 gives you an extra-large capacity for freezing your food. In addition to improved freshness in the fridge compartment, the transparent vegetable bins provide a clear view of the stored food and slide

out effortlessly on the roller system. The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.



Models in the Comfort range now feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort GlassLine comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.

The removable, **extra-deep drawers with transparent front** are fully enclosed all the way round. They provide a perfect view of the contents and the best storage conditions for the frozen food. Freezer drawers and toughened glass shelves can be removed. **VarioSpace** - the practical storage solution for larger produce.



SBSef 7242 Comfort



Energy efficiency class: **A++**¹
 Energy consumption year/24 hrs: 359/0.982 kWh¹
 Total net capacity: 634 litre (Fridge: 381 litre/Freezer compartment: 253 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185.2/121/63¹

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

Colour/material options: SBS 7242 in white



The **LED ceiling light** creates a high-class ambience within the refrigerator. Its beautifully designed, space-efficient housing is centrally positioned to provide a delightfully even illumination.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezer with two temperature zones: SBSesf 7222



With the eight drawer NoFrost freezer compartment, the Side-by-Side fridge-freezer SBSesf 7222 gives you an extra-large capacity for freezing your food. In addition to improved freshness in the fridge compartment, the transparent vegetable bins provide a clear view of the stored food and slide

out effortlessly on the roller system. The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** - the practical storage solution for larger items.



For storage of drinks, the **bottle shelf** offers a practical and elegant solution. Up to five bottles can be stored in this space-saving way.



SBSesf 7222 Comfort	No Frost	A+	Smart Steel
Energy efficiency class: A++			
Energy consumption year / 24 hrs: 460 / 1.258 kWh			
Total net capacity: 640 litre (Fridge: 383 litre / Freezer compartment: 257 litre)			
Noise output: 42 dB(A)			
Climate rating: SN-T (+10°C to +43°C)			
Door / side walls: Stainless steel with SmartSteel / silver			
Exterior dimensions in cm (h/w/d): 185 / 121 / 63			
Controls			
MagicEye behind-the-door, key electronic			
Digital temperature display for fridge and freezer compartments			
Colour / material options: SBS 7222 in white			



SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezer with two temperature zones: SBSesf 7212

With the eight drawer NoFrost freezer compartment, the Side-by-Side fridge-freezer SBSesf 7212 gives you an extra-large capacity for freezing your food. In addition to improved freshness in the fridge compartment, the transparent vegetable bins provide a clear view of the stored food and slide

out effortlessly on the roller system. The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.



The **FrostSafe** fully enclosed drawers prevent cold air from escaping, thereby contributing to energy-efficient operation.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The sectioned, slide-under glass shelf can be located at different heights as required.



SBSesf 7212 Comfort	No Frost	A+	Smart Steel
Energy efficiency class: A++			
Energy consumption year/24 hrs: 460/1.258 kWh			
Total net capacity: 640 litre (Fridge: 383 litre/Freezer compartment: 257 litre)			
Noise output: 42 dB(A)			
Climate rating: SN-T (+10°C to +43°C)			
Door/side walls: Stainless steel with SmartSteel/silver			
Exterior dimensions in cm (h/w/d): 185.2/121/63			
Controls			
MagicEye behind-the-door, key electronic			
LED temperature display for fridge and freezer compartments			
Colour/material options: SBS 7212 in white			

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



The elegant and precise **MagicEye control** with its visual temperature display lets you keep the temperature at exactly the level you select. The clear arrangement of the function buttons makes for easy and convenient use.

Frenchdoor fridge-freezer with BioFresh and NoFrost: CBNes 6256

Bio
Fresh

No
Frost

The food storage centre CBNes 6256 with its elegant Frenchdoor design is not just an eye-catcher in every kitchen when closed. The appliance also has many innovations on the inside. For example, the LED lighting and automatic IceMaker with a mains water connection in the freezer compartment. Food stays fresh for longer in the two BioFresh safes. DuoCooling means that the temperature can be regulated independently in the cooling

compartment and in the freezer compartment – all completely without air exchange. Odour transfer is prevented and stored food does not dry out. The integrated stainless steel rearwall interior panel ensures a more even cooling effect and gives the interior an elegant finish. In addition this model can be flush-fitted as the doors open within the width of the cabinet.



Both **BioFresh** drawers are mounted on **telescopic rails** which extend effortlessly providing a full view of your food, which is easily accessible. The lateral **LED** light spots ensure perfect illumination of the drawers. The versatile glass/bottle shelf can be used depending on your personal preference. The glass on top gives you shelf space, and the glass underneath gives you bottle space.

Our professional **NoFrost** technology makes defrosting a thing of the past. The CBNes 6256 NoFrost food centre is a highly energy efficient A++ rated appliance. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



CBNes 6256 PremiumPlus

Bio Fresh No Frost A++ Duo Cooling Ice Maker

Energy efficiency class: $\leq A^{++}$
 Energy consumption year/24 hrs: 322/0.881 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre/
 Freezer compartment: 114 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Door/side walls: Stainless steel/stainless steel
 Exterior dimensions in cm (h/w/d): 203.9/91/61.5

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



The interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. The elegant, high quality **GlassLine** interior is adaptable to suit individual requirements.





Frenchdoor fridge-freezer with BioFresh and NoFrost: CBNbe 6256

Bio
Fresh

No
Frost

The Frenchdoor appliance CBNbe 6256 has a unique design in the popular retro beige colour. The stainless steel rear panel on the interior is especially easy to clean and therefore exceptionally hygienic. It also helps to ensure a more even cooling effect. LED light columns on both sides as well as the ceiling and BioFresh LED lighting mean that the Frenchdoor appliance shines brightly in the inside. The high-quality glass shelves round off the

interior of the CBNbe 6256 perfectly. The freezer compartment has two large, self-retracting drawers on telescopic rails. The IceMaker has a mains water connection and makes 1.3 kg of ice cubes in 24 hours. Automatic SuperCool and SuperFrost functions make the fast cooling of large quantities of foodstuffs in the cooling or freezer compartment possible without problems.



The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



The professional **NoFrost** technology from Liebherr makes defrosting a thing of the past. The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



CBNbe 6256 PremiumPlus

Bio
Fresh

No
Frost

A++

Duo
Cooling

Ice
Maker

Energy efficiency class: $\langle A^{++} \rangle$
Energy consumption year / 24 hrs: 322 / 0.881 kWh
Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
Noise output: 43 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Door / side walls: beige / beige
Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge and freezer compartments



The elegant, high quality **GlassLine interior** is adaptable to suit individual requirements. The satin-finish shelves and door racks with solid aluminium trims are height adjustable. The door interior accommodates tall bottles and wide containers.

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.

Built-in



**Side
by
Side**

Mix and Match food storage centre:
multi-temperature wine cabinet (EWTgw 3583),
NoFrost freezer (SIGN 3576) and fridge (IKBP 3560).





Bio Fresh

In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0 °C. Each drawer can be used individually and provides ideal humidity – **HydroSafes** with high humidity or **DrySafes** with low humidity – for a versatile storage solution.



The elegant **Premium-electronics system** ensures that the selected temperature is precisely maintained. All functions can be easily and conveniently managed by gently tapping the touchscreen interface. The temperature is numerically displayed and can be read from the MagicEye's LC display.



No Frost

With **NoFrost**, chilled circulating air freezes the food and any moisture is expelled, which keeps the freezer compartment ice-free at all times and prevents food frosting over.



Certain Premium models with BioFresh/BioCool feature the new **VarioSafe** drawer, which enables organisation whilst providing a clear view. It is the perfect place to keep smaller items. The drawer can be positioned at various levels elevations on the lighting columns.



LED

LED light columns are integrated on one or both sides of the fridge compartment to uniformly illuminate the interior. The light gradually gets brighter when the door is opened. The satin finish on the light unit creates elegant lighting. The LED light columns also enable you to position the glass shelves at your convenience.



Soft Telescopic

Premium appliances have fully extendable BioFresh-Safes featuring **SoftTelescopic**, a self-retraction mechanism with soft closing, for practical, reliable and convenient everyday use. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.



Ice Maker

The **plumbed-in IceMaker** provides high-quality ice cubes. The two drawers hold all the ice you need for any occasion. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up. If the quality of the mains water is poor or there is no plumbed-in connection, the ICN 3386 offers the **IceMaker with a water tank** supply. With a 1.2 l capacity and a practical handle, this can be easily removed and filled.



Side by Side

Many Liebherr built-in appliances can be positioned next to or on top of one another. The **Side-by-Side concept** makes it possible to position fridges, freezers and wine cabinets for your personal choice. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations.

The features shown are model dependent; the description applies to the relevant model.



Low energy integrated appliance: SBS 7014

Bio Fresh

No Frost

Built-in

Liebherr's SBS 7014 Side-by-Side unit comprise of a fully integrated refrigerator with BioFresh and a fully integrated freezer with IceMaker is the perfect combination for any kitchen. Hidden away behind custom cabinetry, enjoy features such as BioFresh safes, efficient LED lighting throughout, and flexible bottle

racks to maximize interior space. In the full freezer tower, transparent drawers on telescopic rails with safety glass shelf dividers efficiently organize the frozen foods kept FrostSafe with continual circulated air. Both sides incorporate SoftSystem technology for gentle closing of doors.



Maintenance-free and energy efficient: long-life LEDs provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards allowing taller bottles to be stored. **BioFresh drawers** in the Premium models come with central **LED lighting** for an optimum view of the food stored. The LEDs are integrated into the partition plate to evenly and brightly illuminate the extended BioFresh drawers from directly above.

SBS 7014
Premium

Side by Side
178

178

SIGN 3576
Premium

No Frost A++ LED Ice Maker Soft System Telescopic Rails

Door-on-door/built-in appliance for integrated use
Energy efficiency class: <A++>
Energy consumption year/24 hrs: 241/0.660 kWh
Total net capacity: 209 litre
Noise output: 37 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/at least 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for freezer compartment

IKBP 3560
Premium

Bio Fresh A+++ Soft System Soft Telescopic

Door-on-door/built-in appliance for integrated use
Energy efficiency class: <A+++>
Energy consumption year/24 hrs: 89/0.242 kWh
Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
Noise output: 34 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57/at least 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge compartment

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Double luxury for the kitchen: SBS 6613

Bio Fresh No Frost Built-in

This Side-by-Side provides the most sophisticated solution for cooling and freezing. It has a plenty space for all fresh produce and fits the needs of a modern family perfectly. Also if you want to store the shopping for the weekend or the frozen supply, in this Side-by-Side all can be stored comfortably and easily. The generosity in the SBS 6613 comes with a host of premium features.

The interior GlassLine fittings are stylishly designed and are of excellent quality. The door shelves come furnished with a satin-finished safety glass base, elegant plastic surround, stainless steel rails, bottle shelf with an adjustable bottle holder and BioCool. In addition the doors of this appliance is fitted with two different-sized, removable, transparent VarioBoxes with lids.



Premium BioFresh appliances have fully extendable BioFresh-Safes featuring **SoftTelescopic**, a self-retraction mechanism with soft closing, for practical, reliable and convenient everyday use. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°. **BioFresh** provides the perfect storage climate for long-lasting food storage freshness. When stored at just over 0 °C and at the ideal humidity level, fruit, vegetables, meat and fish all retain their nutritious vitamins for longer.

The plumbed-in automatic **IceMaker** keeps you topped up with high-quality ice cubes for every occasion. Whether you need ice for a refreshing drink or a party with friends, with two drawers, the IceMaker holds all the ice cubes you'll need. Furthermore, it automatically keeps your supplies topped up and you can switch it off at any time.

SBS 6613
Premium



SICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Soft System

Door-on-door/built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 230/0.628 kWh
 Total net capacity: 255 litre (Fridge: 193 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls
 MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

ICBN 3386
Premium

Bio Fresh No Frost A++ Duo Cooling Ice Maker Soft System Soft Telescopic

Door-on-door/built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 232/0.633 kWh
 Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 34 dB(A)
 Climate rating: SN-ST (+10°C to +38°C)
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls
 MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Reliable, long-lasting freshness with BioCool: SBS 6612

Bio Cool No Frost Built-in

Liebherr's NoFrost technology provides professional-standard performance that guarantees long-lasting freshness. Chilled circulating air freezes the food and humidity is expelled so that the freezer is always ice-free and produce never frosts over. NoFrost means no more defrosting. If the quality of the mains water is poor or there

is no plumbed-in connection, the SBS 6612 offers the IceMaker with a water tank supply. With a 1.2 l capacity and a practical handle, this can be easily removed and filled. The BioCool-Box enables regulation of the humidity level in the fridge compartment to keep fruit and vegetables fresher for longer.



The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The stylish white **SoftSystem** mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.

SBS 6612
Premium

Side by Side 178

178

SICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Soft System

Door-on-door/built-in appliance for integrated use
 Energy efficiency class: $\lt; A^+$
 Energy consumption year / 24 hrs: 230/0.628 kWh
 Total net capacity: 255 litre (Fridge: 193 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

ICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Ice Maker Soft System

Door-on-door/built-in appliance for integrated use
 Energy efficiency class: $\lt; A^+$
 Energy consumption year / 24 hrs: 225/0.615 kWh
 Total net capacity: 248 litre (Fridge: 191 litre / Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T (+10°C to +43°C)
 Aperture dimensions in cm (h/w/d): 177.2 - 178.8/56 - 57 / at least 55

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Reliable, long-lasting freshness with BioCool: SBS 7012

Bio Cool

No Frost

Built-in

Liebherr's NoFrost technology provides professional standard performance that guarantees long-lasting freshness. Chilled circulating air freezes the food and humidity is expelled so that the freezer is always ice-free

and produce never frosts over. NoFrost means no more defrosting. The BioCool-Box enables regulation of the humidity level in the fridge compartment to keep fruit and vegetables fresher for longer.



The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



Comfort models are fitted with **Comfort GlassLine**, high-quality glass fittings in door interior. The shelves for preserves and bottles have a satin-finished safety glass base and an attractive plastic surround, and come with an adjustable, secure bottle holder. Comfort GlassLine door shelves are height adjustable.

SBS 7012
Comfort

Side
by
Side

178

178

SIGN 3524
Comfort

No Frost

A++

Door-on-door/built-in appliance for integrated use
Energy efficiency class: $\lt; A^+$
Energy consumption year / 24 hrs: 244 / 0.668 kWh
Total net capacity: 213 litre
Noise output: 40 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Aperture dimensions in cm (h/w/d): 177.2 - 178.8 / 56 - 57 / at least 55

Controls

MagicEye behind-the-door, key electronic
Digital temperature display

IK 3520
Comfort

Bio Cool

A++

Door-on-door/built-in appliance for integrated use
Energy efficiency class: $\lt; A^+$
Energy consumption year / 24 hrs: 117 / 0.319 kWh
Total net capacity: 325 litre
Noise output: 34 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Aperture dimensions in cm (h/w/d): 177.2 - 178.8 / 56 - 57 / at least 55

Controls

MagicEye behind-the-door, key electronic
Digital temperature display

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Integrated Frenchdoor fridge-freezer with BioFresh: EBN 6256

Bio
Fresh

No
Frost

Built-in

The 91 cm wide, Frenchdoor fridge-freezer is definitely a design highlight in any kitchen and, with Liebherr's BioFresh technology, it's a healthy choice too! BioFresh technology guarantees the best possible environment for lasting freshness, which is really important because the freshness and quality of the food that we eat plays a key role in our health and well-being. Integrated lighting

columns on either side of the appliance interior provide perfectly even illumination, and high-quality Glasline fittings lend elegance to the interior design. The two freezer drawers extend effortlessly on premium-quality telescopic rails, and the plumbed in IceMaker provides sophisticated ice cubes for whatever the occasion.



The **versatile bottle shelf** above the BioFresh drawers can be used either as a bottle shelf or a glass storage shelf, both are stored in the recess. The interior features two **integrated lighting columns** with multiple LEDs to evenly illuminate the interior. The lighting columns also facilitate the variable positioning of the glass shelves.



The **SoftSystem**, in pristine white, is integrated into the door to cushion movement as the door is shut, ensuring that the door closes gently, even with fully-loaded door shelves. The door closes automatically from an opening angle of approx. 30°.



ECBN 6256
PremiumPlus

Bio
Fresh

No
Frost

A++

Duo
Cooling

Ice
Maker

Soft
System

Door-on-door/built-in appliance for integrated use

Energy efficiency class: $\lt; A^+$

Energy consumption year / 24 hrs: 322/0.881 kWh

Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)

Noise output: 42 dB(A)

Climate rating: SN-T (+10°C to +43°C)

Aperture dimensions in cm (h/w/d): 203.2-207.2/91.5/at least 62.5

Controls

MagicEye behind-the-door, touch electronic

Digital temperature display for fridge and freezer compartments



The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The **NoFrost** technology keeps the freezer constantly frostfree.

You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



ECBN 6156 617 with left hand hinge
Stainless steel panels are not included. This appliance must be bracketed to the wall/floor.

Extra-wide BioFresh food storage centre: ECBN 6156

Bio Fresh No Frost Built-in

The 91-cm-wide, built-in BioFresh fridge-freezer is a real eyecatcher! Available with door-on-door installation that gives customised integration into kitchen design, and two freezer drawers that easily extend on premium-quality telescopic rails, this built-in masterpiece is a design highlight for any kitchen. The large refrigerator

compartment and adjacently arranged BioFresh drawers, together with the NoFrost freezer compartment offer optimum storage for all types of food. The high-quality and robust stainless steel rear panel and the premium Glasline storage surfaces and shelves round off the interior of the ECBN 6156 perfectly.



The innovative **electronic controls** ensure that the selected temperature is accurately maintained. Thanks to the ingenious touch interface, all functions can be set with ease. The temperature in the refrigeration and freezer compartments can be read from the MagicEye digital display on the LCD. The PremiumPlus interior features **LED light columns** integrated on either side of the compartment liner.



The professional **NoFrost technology** from Liebherr makes defrosting a thing of the past. The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



ECBN 6156
PremiumPlus

Bio Fresh No Frost A+ Duo Cooling Ice Maker

Door-on-door/built-in appliance for integrated use
Energy efficiency class: $\lt; A \gt$
Energy consumption year/24 hrs: 410/1.121 kWh
Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
Noise output: 42 dB(A)
Climate rating: SN-T (+10°C to +43°C)
Aperture dimensions in cm (h/w/d): 203.2-207.2/91.5/at least 62.5

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge and freezer compartments



BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0 °C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator.

It is necessary to specify Left Hand or Right Hand hinge when ordering: ECBN 6156 001 right hand hinge, ECBN 6156 617 left hand hinge. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.

Bio
FreshNo
Frost

Built-in

The innovative food storage centre: ECBN 5066

The 76-cm-wide ECBN 5066 food centre creates a stunning visual impact in any kitchen environment. As the doors open, the interior also reveals a host of innovative ideas, LED lighting, BioFresh drawers mounted on telescopic rails, together with the NoFrost freezer compartment offers optimum storage for all food types.

The integral IceMaker supplies ice for every occasion, whilst the integrated water filter ensures optimum ice quality. The four robust storage shelves in the cooling compartment are made of glass and can be divided and adjusted in height in some cases. The storage area on the inside of the door can also be adjusted variably.



BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0 °C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator. The DrySafe, with a low humidity level, is ideal for storing meat, fish and milk products.

ECBN 5066 comes with an **LED lighting column** on each side of the inner door, which incorporates multiple LEDs to evenly illuminate the appliance interior. A special satin-finish on the light cover creates an appealing and sophisticated lighting effect. The lighting column also facilitates the variable positioning of the glass shelves.

76 203

ECBN 5066
PremiumPlus

Bio
FreshNo
Frost

A++

Duo
CoolingIce
Maker

Door-on-door/built-in appliance for integrated use

Energy efficiency class: $\lt; A^+$

Energy consumption year / 24 hrs: 287 / 0.785 kWh

Total net capacity: 379 litre (Fridge: 276 litre including BioFresh compartment: 57 litre / Freezer compartment: 103 litre)

Noise output: 42 dB(A)

Climate rating: SN-T (+10°C to +43°C)

Aperture dimensions in cm (h/w/d): 203.2 - 207.2 / 76.2 / at least 61

Controls

MagicEye behind-the-door, touch electronic

Digital temperature display for fridge and freezer compartments



The two freezer compartment drawers extend on premium-quality **telescopic rails** and benefit from a self-closing mechanism, making them almost effortless to use. And Liebherr's professional **NoFrost** technology means there is no need to defrost the appliance and also ensures particularly low energy consumption.



ECBN 5066 617 with left hand hinge
This appliance must be bracketed to the wall/floor.

It is necessary to specify Left Hand or Right Hand hinge when ordering: ECBN 5066 001 right hand hinge, ECBN 5066 617 left hand hinge. You can find the full range of efficiency classes at page 3. According to (EU) 2017/1369 6a.



Side-by-Side fridge-freezers

Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating

Fridge and BioFresh compartments

Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

Freezer compartment

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe


Dimensions

Exterior dimensions in cm (h/w/d)

Key features

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

SBSes 8486 PremiumPlus



Energy efficiency class
Energy consumption year/24 hrs ²
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating


Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Exterior dimensions in cm (h/w/d)

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

SBSbs 8673 Premium



Energy efficiency class
Energy consumption year/24 hrs ²
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating

Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Exterior dimensions in cm (h/w/d)

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

SBSes 8663 Premium



Energy efficiency class
Energy consumption year/24 hrs ²
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating

Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Exterior dimensions in cm (h/w/d)

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

SBSes 8473 Premium



Energy efficiency class
Energy consumption year/24 hrs ²
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating


Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Exterior dimensions in cm (h/w/d)

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

SBSef 7343 Comfort



Energy efficiency class
Energy consumption year/24 hrs ²
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating

Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
BioCool
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioSafe/VarioBoxes

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Exterior dimensions in cm (h/w/d)

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

1 Commission Delegated Regulation (EU) No 1060/2010
 2 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.
 3 DIN norm bordeaux bottles NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

4 [****] freezer compartment with -18°C or colder
 5 Climate Ratings: SN +10°C to +32°C N +16°C to +32°C ST +16°C to +38°C T +16°C to +43°C

6 IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)



Side-by-Side fridge-freezers / Fridge-freezers

Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating

Fridge and BioFresh compartments

Defrosting
Interior light
BioFresh-Safes
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior

Freezer compartment

NoFrost/Defrosting
Drawers
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Dimensions

Exterior dimensions in cm (h/w/d)

Key features

SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening

Colour/material options:

SBSef 7242 Comfort



<A++A> ²
359/0.982 kWh ²
634 litre
381 litre
253 litre
★★★★
20 h
20 kg
2
SN-T (+10°C to +43°C)
43 dB(A)
220-240 V~/2.5 A
Automatic
LED ceiling lighting
2 on telescopic rails
Comfort
NoFrost/Automatic
8
•
185.2/121.0/63.0 ²
- / •
HardLine
•
SBS 7242 in white

SBSef 7222 Comfort



<A+A>
460/1.258 kWh
640 litre
383 litre
257 litre
★★★★
20 h
20 kg
2
SN-T (+10°C to +43°C)
42 dB(A)
220-230/220-240 V~/2.5 A
Automatic
LED ceiling lighting
2 on telescopic rails
Bottle shelf
Comfort
NoFrost/Automatic
8
•
185/121.0/63.0
- / •
SwingLine
•
SBS 7222 in white

SBSef 7212 Comfort



<A+A>
460/1.258 kWh
640 litre
383 litre
257 litre
★★★★
20 h
20 kg
2
SN-T (+10°C to +43°C)
42 dB(A)
220-240 V~/2.5 A
Automatic
LED ceiling lighting
2 on telescopic rails
Comfort
NoFrost/Automatic
8
•
185.2/121.0/63.0
- / •
SwingLine
•
SBS 7212 in white

CBNes 6256 PremiumPlus



<A+>
322/0.881 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
45 h
11 kg
3
SN-T (+10°C to +43°C)
43 dB(A)
220-240 V~/1.5 A
Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting
for variable use
Premium
NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg
•
203.9/91.0/61.5
HardLine
•
•

CBNbe 6256 PremiumPlus



<A+>
322/0.881 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
45 h
11 kg
3
SN-T (+10°C to +43°C)
43 dB(A)
220-240 V~/1.5 A
Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting
for variable use
Premium
NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg
•
203.9/91.0/61.5
HardLine
•
•

¹ Commission Delegated Regulation (EU) No 1060/2010

² To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

⁴ ★★★★★ freezer compartment with -18°C or colder

⁵ Climate Ratings: SN +10°C to +32°C N +16°C to +32°C ST +16°C to +38°C T +16°C to +43°C

⁶ IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)

Side-by-Side fridge-freezers for integrated use



Side-by-Side fridge-freezers for integrated use

Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Freezer compartment
Star coding ²
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ³
Noise output
Voltage/Connection rating

Fridge and BioFresh compartments

Defrosting
Interior light
BioFresh-Safes
VarioSafe
BioCool
Bottle shelf
GlassLine Door interior
VarioBoxes

Freezer compartment

NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁴
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe

Type of appliance

Door assembly


Dimensions

Aperture dimensions in cm (h/w/d)

Key features

SoftSystem

SBS 7014 Premium



Energy efficiency class	<A++>
Energy consumption year/24 hrs ¹	241/0.660 kWh
Total net capacity	209 litre
Fridge compartment	
Including BioFresh compartment	
Freezer compartment	209 litre
Star coding ²	★★★★
Temperature rise time	14 h
Freezing capacity in 24 hrs	18 kg
Temperature zones	
Climate rating ³	SN-T (+10°C to +43°C)
Noise output	37 dB(A)
Voltage/Connection rating	220-240 V~/1.3 A

Defrosting	
Interior light	
BioFresh-Safes	
VarioSafe	
BioCool	
Bottle shelf	
GlassLine Door interior	
VarioBoxes	

NoFrost/Defrosting	NoFrost/Automatic
Drawers	9/5 on telescopic rails with LED lighting
Cold storage accumulators	2
IceMaker ⁴	fixed 3/4" water connection
Ice cube production in 24 hrs	0.8 kg
Ice cube reservoir	1.5 kg
FrostSafe	•

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

left side: SIGN 3576 Premium



Energy efficiency class	<A+++>
Energy consumption year/24 hrs ¹	89/0.242 kWh
Total net capacity	301 litre
Fridge compartment	301 litre
Including BioFresh compartment	
Freezer compartment	90 litre
Star coding ²	
Temperature rise time	
Freezing capacity in 24 hrs	
Temperature zones	2
Climate rating ³	SN-T (+10°C to +43°C)
Noise output	34 dB(A)
Voltage/Connection rating	220-240 V~/1.2 A

Defrosting	Automatic
Interior light	LED light column on both sides
BioFresh-Safes	3 with SoftTelescopic with LED lighting
VarioSafe	•
BioCool	
Bottle shelf	for variable use
GlassLine Door interior	Premium
VarioBoxes	•

NoFrost/Defrosting	
Drawers	
Cold storage accumulators	
IceMaker ⁴	
Ice cube production in 24 hrs	
Ice cube reservoir	
FrostSafe	

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

right side: IKBP 3560 Premium

SBS 6613 Premium



Energy efficiency class	<A+>
Energy consumption year/24 hrs ¹	230/0.628 kWh
Total net capacity	255 litre
Fridge compartment	193 litre
Including BioFresh compartment	
Freezer compartment	62 litre
Star coding ²	★★★★
Temperature rise time	14 h
Freezing capacity in 24 hrs	10 kg
Temperature zones	2
Climate rating ³	SN-T (+10°C to +43°C)
Noise output	38 dB(A)
Voltage/Connection rating	220-240 V~/1.4 A

Defrosting	Automatic
Interior light	LED light column left
BioFresh-Safes	
VarioSafe	•
BioCool	
Bottle shelf	1 on telescopic rails with LED lighting
GlassLine Door interior	Premium
VarioBoxes	•

NoFrost/Defrosting	NoFrost/Automatic
Drawers	3/2 on roller tracks with LED lighting
Cold storage accumulators	2
IceMaker ⁴	
Ice cube production in 24 hrs	
Ice cube reservoir	
FrostSafe	•

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

left side: SICN 3386 Premium



Energy efficiency class	<A+>
Energy consumption year/24 hrs ¹	232/0.633 kWh
Total net capacity	255 litre
Fridge compartment	193 litre
Including BioFresh compartment	
Freezer compartment	62 litre
Star coding ²	★★★★
Temperature rise time	14 h
Freezing capacity in 24 hrs	10 kg
Temperature zones	3
Climate rating ³	SN-ST (+10°C to +38°C)
Noise output	34 dB(A)
Voltage/Connection rating	220-240 V~/1.4 A

Defrosting	Automatic
Interior light	LED light column on both sides
BioFresh-Safes	2 with SoftTelescopic with LED lighting
VarioSafe	•
BioCool	
Bottle shelf	for variable use
GlassLine Door interior	Premium
VarioBoxes	•

NoFrost/Defrosting	NoFrost/Automatic
Drawers	4/1 on roller tracks with LED lighting
Cold storage accumulators	2
IceMaker ⁴	fixed 3/4" water connection
Ice cube production in 24 hrs	0.8 kg
Ice cube reservoir	1.0 kg
FrostSafe	•

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

right side: ICBN 3386 Premium

SBS 6612 Premium



Energy efficiency class	<A+>
Energy consumption year/24 hrs ¹	230/0.628 kWh
Total net capacity	255 litre
Fridge compartment	193 litre
Including BioFresh compartment	
Freezer compartment	62 litre
Star coding ²	★★★★
Temperature rise time	14 h
Freezing capacity in 24 hrs	10 kg
Temperature zones	2
Climate rating ³	SN-T (+10°C to +43°C)
Noise output	38 dB(A)
Voltage/Connection rating	220-240 V~/1.4 A

Defrosting	Automatic
Interior light	LED light column left
BioFresh-Safes	
VarioSafe	•
BioCool	
Bottle shelf	1 on telescopic rails with LED lighting
GlassLine Door interior	Premium
VarioBoxes	•


NoFrost/Defrosting	NoFrost/Automatic
Drawers	3/2 on roller tracks with LED lighting
Cold storage accumulators	2
IceMaker ⁴	water tank
Ice cube production in 24 hrs	0.8 kg
Ice cube reservoir	1.0 kg
FrostSafe	•

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

left side: SICN 3386 Premium



Energy efficiency class	<A+>
Energy consumption year/24 hrs ¹	225/0.615 kWh
Total net capacity	248 litre
Fridge compartment	191 litre
Including BioFresh compartment	
Freezer compartment	57 litre
Star coding ²	★★★★
Temperature rise time	14 h
Freezing capacity in 24 hrs	10 kg
Temperature zones	2
Climate rating ³	SN-T (+10°C to +43°C)
Noise output	38 dB(A)
Voltage/Connection rating	220-240 V~/1.4 A

Defrosting	Automatic
Interior light	LED light column left
BioFresh-Safes	
VarioSafe	•
BioCool	
Bottle shelf	1 on telescopic rails with LED lighting
GlassLine Door interior	Premium
VarioBoxes	•

NoFrost/Defrosting	NoFrost/Automatic
Drawers	4/1 on roller tracks with LED lighting
Cold storage accumulators	2
IceMaker ⁴	water tank
Ice cube production in 24 hrs	0.8 kg
Ice cube reservoir	1.0 kg
FrostSafe	•

Door assembly	Door-on-door / built-in appliance for integrated use
---------------	--

Aperture dimensions in cm (h/w/d)	177.2 - 178.8/56 - 57/at least 55
-----------------------------------	-----------------------------------

SoftSystem	•
------------	---

right side: ICN 3386 Premium

¹ Commission Delegated Regulation (EU) No 1060/2010

² ★★★★★ freezer compartment with -18°C or colder

³ Climate Ratings: SN +10°C to +32°C N +16°C to +32°C ST +16°C to +38°C T +16°C to +43°C

⁴ IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)

Our catalogues

Find out everything you need to know about Liebherr Freestanding & Built-In refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as hard copy or PDF downloads from home.liebherr.com.



View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



biofresh.liebherr.com



nofrost.liebherr.com



wine.liebherr.com

Smart communication on all fronts



BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



IceCrusher App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.

apps.home.liebherr.com



Discover the world of Liebherr-Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!



Click the link to directly access our social media channels:

socialmedia.home.liebherr.com

Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle.

Subject to modification. Current data see home.liebherr.com.
Printed in Germany by Eberl/Print. 7943380-10/0718

