



CNbs 4315

#### Our catalogues

Find out everything you need to know about LIEBHERR Freestanding & Built-In refrigeration as well as Wine Cabinets. LIEBHERR also manufacture a comprehensive range of Commercial refrigeration. Available as hard copy or PDF downloads from [home.liebherr.com](http://home.liebherr.com).



View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



#### Smart communication on all fronts



**BioFresh App**  
Useful information about perfect food storage, as well as vitamin and mineral content.



**WineGuide App**  
A brief overview of Bordeaux wines and their producers, plus storage information.



**Kitchen Photo Designer App**  
Be your own interior designer: take a photo of your kitchen, select the Liebherr model of your choice and position it into your photo by swiping the screen.



**IceCrusher App**  
Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.  
[apps.home.liebherr.com](http://apps.home.liebherr.com)



**Freestanding appliances**

# BlackSteel

[home.liebherr.com](http://home.liebherr.com)

Subject to modification. Current data see [home.liebherr.com](http://home.liebherr.com).  
Printed by ralf mettlagroup 7945 838-0304/2017



# LIEBHERR

Quality, Design and Innovation

## Side-by-Side fridge-freezer SBSbs 8673



The **BlackSteel** is optically a highly attractive and unusual black stainless steel finish which catches every eye. Paired with the high quality SmartSteel finish, this new material lends the Side-by-Side fridge-freezer a hi-tech appeal whilst retaining a timeless elegance. The transverse polished finish creates an exclusive, visually appealing look, making the BlackSteel models a true highlight of every kitchen. The practical aluminium door handle, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



- 1** **TFT-colour display.** Maintains the selected temperature accurately; with digital display and touch interface.
- 2** **LED lighting.** Space saving positioning above the drawers. Advantages: excellent view of stored contents, energy efficient and fantastic durability.
- 3** **NoFrost.** 'No more defrosting' convenience in the freezer compartment.
- 4** **FrostSafe.** The removable drawers with transparent front are closed all the way round. They provide a perfect view of the contents and the best storage conditions for the frozen food.
- 5** **Plumbed-in IceMaker.** Top-quality ice cubes for all occasions.
- 6** **VarioSpace.** Removable drawers and glass shelves for storage of bulky frozen food items.
- 7** **PowerCooling.** Quickly chills stored food and maintains a constant internal cooling temperature.
- 8** **VarioBox.** Food can be stored in the refrigerator, ready for serving; with separate egg tray.
- 9** **LED rear wall lighting** evenly illuminates the whole interior.
- 10** **Premium GlassLine.** The storage racks in the door equipped with stainless steel rails are height adjustable; includes bottle shelf with adjustable bottle holder.
- 11** **GlassLine storage shelves.** All safety glass shelves can be positioned at different heights; one half of the split glass shelf can slide underneath the other for greater versatility.
- 12** **Practical aluminium door handles,** with integrated opening mechanism.
- 13** **Variable bottle shelf.** As an alternative, this can be swapped with the glass plate below to give extra storage space.
- 14** **BioFresh.** The perfect climate for long-lasting freshness of fruits and vegetables, meat, fish and dairy products in the DrySafe and HydroSafe.
- 15** **BlackSteel.** Liebherr's elegant BlackSteel with a SmartSteel finish is easy to clean and extremely scratch resistant.



## Fridge-freezer CBNPbs 4858



In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system.



The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir activated charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards allowing taller bottles to be stored. The **LED rear wall lighting** is integrated at the back of the dividing shelf.



The distinctive **GlassLine** equipment puts the finishing touches to the high quality interior. The shelves are made of safety glass. The sectioned, slide-under glass shelf lends itself to versatile use as it can be inserted at different heights, as required.



The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



**Premium GlassLine** door shelves with stainless steel trim. Curved stainless steel rods secure bottles and jars. The removable **VarioBoxes**, designed for convenient storage, can be rearranged in the door interior to suit your requirements. VarioBoxes hang on a steel rod and are detachable.



Freezer drawers and glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items. **LEDs** are integrated into the underside of the refrigerator compartment door to perfectly illuminate the freezer drawers when they are opened.



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



## Fridge KBbs 4350



In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. The BioFresh safes with **SoftTelescopic** provides a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



The high-resolution, high-contrast **2,4"** **touchscreen display** is integrated behind the door and enables intuitive temperature setting.



The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir activated charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards allowing taller bottles to be stored. The **LED rear wall lighting** is integrated at the back of the dividing shelf.



The distinctive **GlassLine** equipment puts the finishing touches to the high quality interior. The shelves are made of safety glass. The sectioned, slide-under glass shelf lends itself to versatile use as it can be inserted at different heights, as required.



The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



**Premium GlassLine** door shelves with stainless steel trim. Curved stainless steel rods secure bottles and jars. The removable **VarioBoxes**, designed for convenient storage, can be rearranged in the door interior to suit your requirements. VarioBoxes hang on a steel rod and are detachable.



The **VarioSafe** provides a clear view whilst creating order. It is the ideal space for smaller food packets, tubes and jars. The drawer can be positioned at various levels on the lighting column.



Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



**SBSbs 8673**  
Premium

Energy efficiency class: **A++**<sup>1</sup>  
Energy consumption year / 24 hrs: 255/0.696 kWh<sup>1</sup>  
Total net capacity: 629 litre (Fridge: 367 litre including BioFresh compartment:  
133 litre/Freezer compartment: 262 litre)  
Noise output: 38 dB(A)  
Climate rating: SN-T  
Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
Exterior dimensions in cm (h/w/d): 185/121/66.5<sup>1</sup>



**SBSbs 7353**  
Premium

Energy efficiency class: **A++**<sup>1</sup>  
Energy consumption year / 24 hrs: 383/1.048 kWh<sup>1</sup>  
Total net capacity: 654 litre (Fridge: 539 litre including BioFresh compartment:  
155 litre/Freezer compartment: 115 litre)  
Noise output: 39 dB(A)  
Climate rating: SN-T  
Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
Exterior dimensions in cm (h/w/d): 185.2/121/63<sup>1</sup>



**CBNPbs 4858**  
Premium

Energy efficiency class: **A++**<sup>1</sup>  
Energy consumption year / 24 hrs: 149/0.408 kWh<sup>1</sup>  
Total net capacity: 344 litre (Fridge: 243 litre including BioFresh compartment:  
97 litre/Freezer compartment: 101 litre)  
Noise output: 37 dB(A)  
Climate rating: SN-T  
Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
Exterior dimensions in cm (h/w/d): 201/60/66.5<sup>1</sup>



**CBNbs 4815**  
Comfort

Energy efficiency class: **A++**<sup>1</sup>  
Energy consumption year / 24 hrs: 186/0.507 kWh<sup>1</sup>  
Total net capacity: 343 litre (Fridge: 242 litre including BioFresh compartment:  
94 litre/Freezer compartment: 101 litre)  
Noise output: 38 dB(A)  
Climate rating: SN-T  
Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
Exterior dimensions in cm (h/w/d): 201/60/66.5<sup>1</sup>

Controls	Freezer compartment <b>****</b>
<ul style="list-style-type: none"> <li>· 2.4" TFT-colour display behind-the-door, touch electronic</li> <li>· Digital temperature display for fridge, BioFresh and freezer compartments</li> <li>· Automatic SuperCool (time restricted)</li> <li>· Automatic SuperFrost, quantity-controlled</li> <li>· Warning signal in case of fault: visual and acoustic</li> <li>· Door alarm: visual and acoustic</li> </ul>	<ul style="list-style-type: none"> <li>· 9 drawers, of which 6 set on roller tracks, VarioSpace</li> <li>· IceMaker with fixed 3/4" water connection</li> <li>· Ice cube production in 24 hrs: 0.8 kg</li> <li>· Ice cube reservoir: 0.8 kg</li> <li>· LED lighting</li> <li>· Temperature rise time: 20 h</li> <li>· Freezing capacity in 24 hrs: 18 kg</li> <li>· 2 Cold storage accumulators</li> <li>· Safety glass fittings</li> </ul>
Fridge and BioFresh compartments	
<ul style="list-style-type: none"> <li>· PowerCooling with FreshAir activated charcoal filter</li> <li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray</li> <li>· 4 GlassLine storage shelves, of which one is divided into two parts</li> <li>· VarioSafe</li> <li>· Variable bottle shelf</li> <li>· LED ceiling lighting with dimmer function</li> <li>· LED BioFresh lighting</li> <li>· LED rear wall lighting</li> <li>· 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to HydroSafe or DrySafe</li> </ul>	
Key features	
<ul style="list-style-type: none"> <li>· HardLine</li> <li>· Aluminium handles with integrated opening mechanism</li> <li>· Versatile installation due to front ventilation</li> <li>· Transport handles, front and at back</li> <li>· Height-adjustable feet at front, transport castors at back</li> <li>· Door hinge left fixed/right fixed</li> <li>· Replaceable door seal</li> <li>· Concealed hinge with restricted opening</li> </ul>	

Controls	Freezer compartment <b>****</b>
<ul style="list-style-type: none"> <li>· MagicEye behind-the-door, touch electronic</li> <li>· Digital temperature display for fridge, BioFresh and freezer compartments</li> <li>· Automatic SuperCool</li> <li>· Automatic SuperFrost, quantity-controlled</li> <li>· Warning signal in case of fault: visual and acoustic</li> <li>· Door alarm: acoustic</li> </ul>	<ul style="list-style-type: none"> <li>· 5 drawers, VarioSpace</li> <li>· IceMaker with fixed 3/4" water connection</li> <li>· Ice cube production in 24 hrs: 0.8 kg</li> <li>· Ice cube reservoir: 1.5 kg</li> <li>· Temperature rise time: 25 h</li> <li>· Freezing capacity in 24 hrs: 16 kg</li> <li>· 2 Cold storage accumulators</li> <li>· Safety glass fittings</li> </ul>
Fridge and BioFresh compartments	
<ul style="list-style-type: none"> <li>· PowerCooling</li> <li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray</li> <li>· 6 GlassLine storage shelves, of which one is divided into two parts</li> <li>· 2 GlassLine shelves in the BioFresh compartment</li> <li>· Bottle shelf, Champagne rack</li> <li>· LED ceiling lighting</li> <li>· LED BioFresh lighting</li> <li>· 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe</li> <li>· 2 fruit and vegetable drawers on telescopic rails</li> </ul>	
Key features	
<ul style="list-style-type: none"> <li>· HardLine</li> <li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray</li> <li>· 6 GlassLine storage shelves, of which one is divided into two parts</li> <li>· 2 GlassLine shelves in the BioFresh compartment</li> <li>· Bottle shelf, Champagne rack</li> <li>· LED ceiling lighting</li> <li>· LED BioFresh lighting</li> <li>· 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe</li> <li>· 2 fruit and vegetable drawers on telescopic rails</li> </ul>	

Controls	Freezer compartment <b>****</b>
<ul style="list-style-type: none"> <li>· 7" TFT-colour display in-the-door, touch electronic</li> <li>· Digital temperature display for fridge, BioFresh and freezer compartments</li> <li>· Automatic SuperCool (time restricted)</li> <li>· Automatic SuperFrost, quantity-controlled</li> <li>· Warning signal in case of fault: visual and acoustic</li> <li>· Door alarm: visual and acoustic</li> </ul>	<ul style="list-style-type: none"> <li>· 3 drawers, of which 2 set on roller tracks, VarioSpace</li> <li>· Ice cube tray</li> <li>· LED lighting</li> <li>· Temperature rise time: 24 h</li> <li>· Freezing capacity in 24 hrs: 16 kg</li> <li>· 2 Cold storage accumulators</li> <li>· Safety glass fittings</li> </ul>
Key features	
<ul style="list-style-type: none"> <li>· HardLine</li> <li>· Aluminium handles with integrated opening mechanism</li> <li>· Versatile installation due to front ventilation</li> <li>· Transport handles, front and at back</li> <li>· Height-adjustable feet at front, transport castors at back</li> <li>· Door hinge left fixed/right fixed</li> <li>· Replaceable door seal</li> <li>· Concealed hinge with restricted opening</li> </ul>	
Fridge and BioFresh compartments	
<ul style="list-style-type: none"> <li>· PowerCooling with FreshAir activated charcoal filter</li> <li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray</li> <li>· 3 GlassLine storage shelves, of which one is divided into two parts</li> <li>· Variable bottle shelf</li> <li>· LED ceiling lighting with dimmer function</li> <li>· LED BioFresh lighting</li> <li>· LED rear wall lighting</li> <li>· 2 BioFresh-Safes with SoftTelescopic set variably to either HydroSafe or DrySafe</li> </ul>	

Controls	Freezer compartment <b>****</b>
<ul style="list-style-type: none"> <li>· 2.4" TFT-monochrome display behind-the-door, touch electronic</li> <li>· Digital temperature display for fridge, BioFresh and freezer compartments</li> <li>· Automatic SuperCool (time restricted)</li> <li>· Automatic SuperFrost, time-controlled</li> <li>· Warning signal in case of fault: visual and acoustic</li> <li>· Door alarm: visual and acoustic</li> </ul>	<ul style="list-style-type: none"> <li>· 3 drawers, VarioSpace</li> <li>· Ice cube tray</li> <li>· LED lighting</li> <li>· Temperature rise time: 24 h</li> <li>· Freezing capacity in 24 hrs: 16 kg</li> <li>· Safety glass fittings</li> </ul>
Key features	
<ul style="list-style-type: none"> <li>· HardLine</li> <li>· Aluminium handles with integrated opening mechanism</li> <li>· Versatile installation due to front ventilation</li> <li>· Transport handles, front and at back</li> <li>· Height-adjustable feet at front, transport castors at back</li> <li>· Reversible door hinging</li> <li>· Replaceable door seal</li> <li>· Concealed hinge with restricted opening</li> </ul>	
Fridge and BioFresh compartments	
<ul style="list-style-type: none"> <li>· PowerCooling with FreshAir activated charcoal filter</li> <li>· Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray</li> <li>· 3 GlassLine storage shelves, of which one is divided into two parts</li> <li>· Height-adjustable feet at front, transport castors at back</li> <li>· Integrated bottle shelf</li> <li>· LED ceiling lighting</li> <li>· 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to HydroSafe or DrySafe</li> </ul>	

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances.  
If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

BLU  
Performance

◀60▶

CNPbs 3758

Bio Cool	No Frost	A+++ -20%	Duo Cooling	Soft System	Black Steel
----------	----------	--------------	-------------	-------------	-------------

Energy efficiency class: A+++<sup>1</sup>  
 Energy consumption year / 24 hrs: 125/0.340 kWh<sup>1</sup>  
 Total net capacity: 271 litre (Fridge: 170 litre/Freezer compartment: 101 litre)  
 Noise output: 37 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 165/60/66.5<sup>1</sup>

**Controls**

- 7" TFT-colour display in-the-door, touch electronic
  - Digital temperature display for fridge and freezer compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, quantity-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- PowerCooling with FreshAir activated charcoal filter
  - Premium GlassLine storage shelf with bottle holder, VarioBoxes, Egg tray
  - 3 GlassLine storage shelves, of which one is divided into two parts
  - Bottle shelf
  - LED ceiling lighting with dimmer function
  - 1 BioCool-Box on roller tracks

- Freezer compartment**
- 3 drawers, of which 2 set on roller tracks
  - Ice cube tray
  - LED lighting
  - Temperature rise time: 24 h
  - Freezing capacity in 24 hrs: 16 kg
  - 2 Cold storage accumulators
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handles with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles, front and at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - Concealed hinge with restricted opening

BLU  
Performance

◀60▶

CNbs 4315

Bio Cool	No Frost	A+++ -20%	Duo Cooling	Black Steel
----------	----------	--------------	-------------	-------------

Energy efficiency class: A+++<sup>1</sup>  
 Energy consumption year / 24 hrs: 165/0.451 kWh<sup>1</sup>  
 Total net capacity: 321 litre (Fridge: 220 litre/Freezer compartment: 101 litre)  
 Noise output: 38 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 185/60/66.5<sup>1</sup>

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge and freezer compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
  - Ice cube tray
  - Temperature rise time: 24 h
  - Freezing capacity in 24 hrs: 16 kg
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handles with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles, front and at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - LED ceiling lighting
  - 1 BioCool-Box on roller tracks

BLU  
Performance

◀60▶

CNbs 4015

No Frost	A++ -20%	Duo Cooling	Black Steel
----------	-------------	-------------	-------------

Energy efficiency class: A++<sup>1</sup>  
 Energy consumption year / 24 hrs: 252/0.688 kWh<sup>1</sup>  
 Total net capacity: 356 litre (Fridge: 269 litre/Freezer compartment: 87 litre)  
 Noise output: 39 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 201.1/60/62.5<sup>1</sup>

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge and freezer compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
  - Ice cube tray
  - Temperature rise time: 18 h
  - Freezing capacity in 24 hrs: 11 kg
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handles with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles, front and at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - LED ceiling lighting
  - 2 fruit and vegetable drawers on roller tracks

BLU  
Performance

◀60▶

CNbs 3915

No Frost	A++ -20%	Duo Cooling	Black Steel
----------	-------------	-------------	-------------

Energy efficiency class: A++<sup>1</sup>  
 Energy consumption year / 24 hrs: 263/0.718 kWh<sup>1</sup>  
 Total net capacity: 340 litre (Fridge: 221 litre/Freezer compartment: 119 litre)  
 Noise output: 39 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 201.1/60/62.5<sup>1</sup>

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge and freezer compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- 4 drawers, VarioSpace
  - Ice cube tray
  - Temperature rise time: 18 h
  - Freezing capacity in 24 hrs: 11 kg
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handles with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles, front and at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - LED ceiling lighting
  - 2 fruit and vegetable drawers on roller tracks

BLU  
Performance

◀60▶

Cbs 3425

Smart Frost	A++ -20%	Duo Cooling	Black Steel
-------------	-------------	-------------	-------------

Energy efficiency class: A++<sup>1</sup>  
 Energy consumption year / 24 hrs: 143/0.391 kWh<sup>1</sup>  
 Total net capacity: 272 litre (Fridge: 184 litre/Freezer compartment: 88 litre)  
 Noise output: 38 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 181.7/60/62.5<sup>1</sup>

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
  - Digital temperature display for fridge and BioFresh compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- 4 drawers, VarioSpace
  - Ice cube tray
  - Temperature rise time: 29 h
  - Freezing capacity in 24 hrs: 12 kg
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handles with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - LED rear wall lighting
  - 2 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably

BLU  
Performance

◀60▶

KBbs 4350

Bio Fresh	A++ -20%	Soft System	Soft Telescopic	Black Steel
-----------	-------------	-------------	-----------------	-------------

Energy efficiency class: A++<sup>1</sup>  
 Energy consumption year / 24 hrs: 90/0.244 kWh<sup>1</sup>  
 Total net capacity: 367 litre (Fridge: 367 litre including BioFresh compartment: 133 litre)  
 Noise output: 37 dB(A)  
 Climate rating: SN-T  
 Door / side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel  
 Exterior dimensions in cm (h/w/d): 185/60/66.5<sup>1</sup>

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
  - Digital temperature display for fridge and BioFresh compartments
  - Automatic SuperCool (time restricted)
  - Automatic SuperFrost, time-controlled
  - Warning signal in case of fault: visual and acoustic
  - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
  - Ice cube tray
  - Temperature rise time: 29 h
  - Freezing capacity in 24 hrs: 12 kg
  - Safety glass fittings

- Key features**
- HardLine
  - Aluminium handle with integrated opening mechanism
  - Versatile installation due to front ventilation
  - Transport handles at back
  - Height-adjustable feet at front, transport castors at back
  - Reversible door hinging
  - Replaceable door seal
  - LED rear wall lighting
  - 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably

<sup>1</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances.  
 If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.