

Our catalogues

Find out everything you need to know about LIEBHERR Freestanding & Built-In refrigeration as well as Wine Cabinets. LIEBHERR also manufacture a comprehensive range of Commercial refrigeration. Available as hard copy or PDF downloads from home.liebherr.com.



Smart communication on all fronts



BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



Kitchen Photo Designer App

Be your own interior designer: take a photo of your kitchen, select the Liebherr model of your choice and position it into your photo by swiping the screen.



IceCrusher App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.
apps.home.liebherr.com



Discover the world of Liebherr-Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!



Click the link to directly access our social media channels:
socialmedia.home.liebherr.com

View topic specific websites with in-depth information about BioFresh/NoFrost and wine cabinets via the QR code.



biofresh.liebherr.com



nofrost.liebherr.com



wine.liebherr.com

Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle.

Subject to modification.
Current data see home.liebherr.com.

Food Centres Special 2017



home.liebherr.com

LIEBHERR

Quality, Design and Innovation



Side-by-Side fridge-freezers Large capacity food centres

Healthy food is the current trend in a modern lifestyle. Our Side-by-Side appliances are the ideal solution for giving large capacity storage for your food. They offer ample space for large food stocks with various climate zones for perfect food storage. When refrigerating large amounts of food you have a choice of refrigerators, BioFresh, Freezer, Wine climate zone and IceMakers. The exclusive design makes our Side-by-Side fridge-freezers the healthy focal point of any kitchen.

Refrigeration

A spacious fridge compartment with an adjustable temperature range from +3°C to +9°C ensures constant freshness every day.

BioFresh

At a temperature of just over 0°C, large quantities of food, such as meat, fish, fruit, vegetables and dairy products, can be stored in the spacious BioFresh drawers significantly longer than in a conventional fridge compartment.

Freezing

The NoFrost freezer compartment with automatic IceMaker offers a continuous supply of ice. Food is frozen with refrigerated re-circulated air and the humidity is dissipated. This keeps the freezer compartment free of ice preventing the food from frosting over. Defrosting is no longer necessary.

Multi-temperature wine compartment

The multi-temperature wine compartment of the SBSes 7165 has two independently adjustable zones for storing wine at the exact temperature required, between +5°C and +20°C. Red wines, white wines and champagne can be stored together at their individual optimum drinking temperatures.





Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C. Each drawer can be used individually and provides ideal humidity – **HydroSafes** with high humidity or **DrySafes** with low humidity – for a versatile storage solution.



Soft System

The **SoftSystem** integrated in the door cushions the movement when the door is closed and ensures gentle closing even when the inside of the door is fully loaded. The door automatically closes from an angle of approx. 45°.



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past. Depending on the model, the freezer compartment is fitted with **LED lighting**.




The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.



Wine

The Side-by-Side fridge-freezer SBSes 7165 with six different climate zones offers a range of innovative solutions. The **wine compartment** has two independently adjustable zones for storing wine at the exact temperature required, between +5°C and +20°C.



BLU Performance

High quality materials, meticulous workmanship in every detail, and easy-to-use/precise touch-electronics define the new **BLU Performance**. The compact integration of refrigeration technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics.



Ice Maker

The **plumbed-in IceMaker** provides high-quality ice cubes. The two drawers hold all the ice you need for any occasion. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.



Smart Steel

Side-by-Side models with stainless steel or BlackSteel doors are equipped with a **SmartSteel** surface. SmartSteel significantly reduces the visibility of finger marks and thanks to the high-quality finish of the stainless steel, it is easy-to-clean and far more scratch-resistant.

The features shown are model dependent; the description applies to the relevant model.



Six climate zones in one appliance: SBSes 7165



The Side-by-Side fridge-freezer SBSes 7165 with six different climate zones boasts an array of innovative solutions. The multi-temperature wine compartment has two independently adjustable zones for storing wine at the exact temperature required, ranging from +5°C to +20°C. The NoFrost freezer compartment with automatic IceMaker provides professional freezing technology for long-term freshness, while a spacious fridge compartment keeps food fresh on a day-to-day basis. In the BioFresh

compartment, fruit, vegetables, meat and dairy products stay fresh for significantly longer at around 0°C. And thanks to BioFresh-Plus technology, the temperature in the upper BioFresh compartment can be lowered to an ideal -2°C for storing fish, or set to +6°C for exotic fruits. In short, the climate zones, refrigeration, BioFresh, freezing and wine, guarantee the optimal storage temperature for an array of produce.



You can choose to store red or white wine and champagne together or separately at their optimal drinking temperature in one and the same appliance. The tinted glazed door with UV protection makes an attractive focal point of your wine stock. For presentation, the LED interior light can be individually adjusted and has a continuous dimmer function. Since any heat generated by the LEDs is minimal, wines can be presented bathed in light for a longer period. The wooden shelves are mounted on telescopic rails and are foldable in some cases.



The BioFresh-Plus drawers are illuminated by LED technology for an optimal overview of the stored contents. They are also mounted on smooth-running telescopic rails and can be pulled out and removed at a door opening angle of just 90°. The BioFresh-Plus technology provides yet more flexibility for tailored storage. The separate BioFresh-Plus electronic control system allows the temperature in the top drawer to be lowered to -2°C for storing fish. Together with the DrySafe setting, fish is kept fresh even longer. Exotic fruits find ideal storage conditions in the top adjustable safe at +6°C and a high level of humidity.



SBSes 7165 PremiumPlus



Energy efficiency class: A++
Energy consumption year / 24 hrs: 431 / 1.178 kWh
Max. Bordeaux bottles 0.75 l: 41 ¹
Total net capacity: 591 litre (Fridge: 476 litre including BioFresh compartment: 110 litre including wine compartment: 126 litre / Freezer compartment: 115 litre)
Noise output: 42 dB(A)
Climate rating: SN-ST
Door / side walls: Stainless steel with SmartSteel / stainless steel
Exterior dimensions in cm (h/w/d): 185.2 / 121 / 63

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge, BioFresh, wine and freezer compartments



The IceMaker provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party – there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

¹ Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)




A optical highlight in BlackSteel: SBSbs 8673



The BluPerformance range is characterised by premium-quality materials, craftsmanship in every detail, and precision touchscreen electronic controls. The integration of all the refrigeration components into the base of the appliance, together with optimised electronic controls, ensures maximum energy efficiency, a greater

net capacity, and enhanced freezer compartment ergonomics. BioFresh technologie keep stored food fresher for longer. The elegant and timeless design of the BluPerformance range ensures that these appliances are a guaranteed highlight in any home and that they will satisfy for many years to come.




The **BlackSteel** is a highly attractive and unusual black stainless steel finish which catches every eye. Paired with the high quality SmartSteel finish, this new material lends the Side-by-Side fridge-freezer a hi-tech appeal whilst retaining a timeless elegance. The transverse polished finish creates an exclusive, visually appealing look, making the BlackSteel models a true highlight of every kitchen. The practical **aluminium door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The distinctive **Premium GlassLine** equipment puts the finishing touches to the overall impression of high quality conveyed by the interior. The shelves are made of safety glass, as are the racks with stainless steel trims in the door interior. The sectioned, slide-under glass shelf lends itself to versatile use as it can be inserted at different heights, as required. The **VarioSafe** drawer is the perfect place to keep smaller items. The drawer can be positioned at various levels elevations on the lighting columns.



SBSbs 8673 Premium



Energy efficiency class: $\langle A^{+++}/A^{+++} \rangle^1$
Energy consumption year / 24 hrs: 255 / 0.696 kWh ¹
Total net capacity: 629 litre (Fridge: 367 litre including BioFresh compartment: 133 litre / Freezer compartment: 262 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 121 / 66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments



In the **BioFresh** compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C.



¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



The new BluPerformance Side-by-Side fridge-freezer: SBSes 8663



With their elegant and timeless design, Liebherr Side-by-Side fridge-freezers meet the highest aesthetic demands. The design quality offered by our appliances is evident throughout: from the use of premium-quality materials to the detailed design. To consistently fulfil our high quality standards, we

evaluate every new design on the basis of its practicality and ease-of-use for our customers. The high-resolution, high-contrast 2.4" touchscreen display is located behind the door and can be read from any angle. The stored menu options are intuitive and easy-to-operate.



Maintenance-free and energy efficient: long-life LEDs provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity). The high-performance **PowerCooling** system ensures that freshly stored produce is rapidly cooled and that an even temperature is maintained throughout the appliance interior. The **FreshAir activated charcoal filter** that is integrated into the fan purifies circulating air and quickly traps odours.



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles. The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a homogeneous, high-quality lighting concept.



SBSes 8663 Premium



Energy efficiency class: $\langle A^{+++}/A^{+++} \rangle^1$
Energy consumption year / 24 hrs: 258 / 0.702 kWh ¹
Total net capacity: 635 litre (Fridge: 367 litre including BioFresh compartment: 133 litre / Freezer compartment: 268 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Door / side walls: Stainless steel with SmartSteel / Stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 185 / 121 / 66.5 ¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge, freezer and BioFresh compartments



The high-resolution, high-contrast **2.4" touchscreen display** is integrated behind the door and enables intuitive temperature setting.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

The Side-by-Side fridge-freezer with extra large BioFresh compartment: SBSes 7353

Bio Fresh

No Frost

Apart from a spacious refrigerator compartment, the Side-by-Side fridge-freezer SBSes 7353 also offers two large BioFresh drawers. Foods such as fruit, vegetables, meat, fish and dairy products stay fresher significantly longer in the BioFresh compartment

compared to the conventional refrigerator compartment. The NoFrost freezer technology provides frost free freezing for the safe long-term storage of food, making defrosting a thing of the past; with its automatic IceMaker providing a plentiful supply of ice for any occasion.



The **BioFresh drawers** provide the perfect climate for lasting food freshness. At a temperature of just over 0°C and ideal humidity, fruit and vegetables, meat and fish retain their healthy vitamins, their delicate aroma and their appetising appearance significantly longer than in a conventional refrigerator compartment.



The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party – there will always be enough ice cubes. The IceMaker with fixed water connection, which you can switch off at any time, automatically keeps your supplies topped up.

121

SBSes 7353
Premium

Bio Fresh No Frost A++ Ice Maker Smart Steel

Energy efficiency class: **A++**¹

Energy consumption year/24 hrs: 383/1.048 kWh¹

Total net capacity: 654 litre (Fridge: 539 litre including BioFresh compartment: 155 litre/Freezer compartment: 115 litre)

Noise output: 39 dB(A)

Climate rating: SN-T

Door / side walls: Stainless steel with SmartSteel / stainless steel

Exterior dimensions in cm (h/w/d): 185.2/121/63¹

Controls

MagicEye behind-the-door, touch electronic

Digital temperature display for fridge, freezer and BioFresh compartments

Colour / material options: **SBSes 7353** in BlackSteel



For storage of drinks, the **bottle shelf** offers a practical and elegant solution. Up to five bottles can be stored in this space-saving way.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



No Frost

Side-by-Side fridge-freezer with two temperature zones: SBSef 7242

With the eight drawer NoFrost freezer compartment, the Side-by-Side fridge-freezer SBSef 7242 gives you an extra-large capacity for freezing your food. In addition to improved freshness in the fridge compartment, the transparent vegetable bins provide a clear view of the stored food and slide

out effortlessly on the roller system. The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.



Models in the Comfort range now feature **Comfort GlassLine**: high quality glass shelving for the door interior. Comfort GlassLine comprises a robust satin-finished safety glass shelf, railings and an elegant plastic surround. The can/bottle racks have an adjustable holder for secure storage.



The removable, **extra-deep drawers with transparent front** are fully enclosed all the way round. They provide a perfect view of the contents and the best storage conditions for the frozen food. Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger produce.



SBSef 7242
Comfort

No Frost A++ Smart Steel

Energy efficiency class: **A++**¹
 Energy consumption year/24 hrs: 359/0.982 kWh¹
 Total net capacity: 634 litre (Fridge: 381 litre/Freezer compartment: 253 litre)
 Noise output: 41 dB(A)
 Climate rating: SN-T
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185.2/121/63¹

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments



The **LED ceiling light** creates a high-class ambience within the refrigerator. Its beautifully designed, space-efficient housing is centrally positioned to provide a delightfully even illumination.

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



Frenchdoor fridge-freezer with BioFresh and NoFrost: CBNes 6256

Bio Fresh No Frost

The Food Storage Centre CBNes 6256 with its elegant Frenchdoor concept is a focal point in any kitchen, open or closed. The interior presents a host of innovative ideas. Take the LED interior light and the automatic IceMaker with fixed water connection in the freezer compartment, for example. Or the two BioFresh drawers, which keep food fresh for significantly longer. Accurate and independent temperature control of

the fridge and freezer compartments is ensured by DuoCooling: two separately adjustable cooling circuits. There is no air exchange between the refrigerator and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out. In addition this model can be flush-fitted as the doors open within the width of the cabinet.




Both BioFresh drawers are mounted on telescopic rails which extend effortlessly providing a full view of your food, which is easily accessible. The lateral LED light spots ensure perfect illumination of the drawers. The versatile glass/bottle shelf can be used depending on your personal preference. The glass on top gives you shelf space, and the glass underneath gives you bottle space.



Our professional NoFrost technology makes defrosting a thing of the past. The CBNes 6256 NoFrost food centre is a highly energy efficient A++ rated appliance. The two pull-out freezer drawers are mounted on high-quality telescopic rails and can be effortlessly extended to provide a perfect view and ideal storage conditions.



CBNes 6256 PremiumPlus	Bio Fresh	No Frost	A++	Duo Cooling	Ice Maker
Energy efficiency class: <A++>					
Energy consumption year/24 hrs: 322/0.881 kWh					
Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre/ Freezer compartment: 114 litre)					
Noise output: 43 dB(A)					
Climate rating: SN-T					
Door / side walls: Stainless steel / stainless steel					
Exterior dimensions in cm (h/w/d): 203.9/91 /61.5					
Controls					
MagicEye behind-the-door, touch electronic					
Digital temperature display for fridge and freezer compartments					



The elegant, high quality GlassLine interior is adaptable to suit individual requirements. The satin-finish shelves and door racks with solid aluminium trims are height adjustable. The door interior accommodates tall bottles and wide containers.



Frenchdoor fridge-freezer with BioFresh and NoFrost: CBNbe 6256

Bio
Fresh

No
Frost

The Food Storage Centre CBNbe 6256 with its elegant Frenchdoor concept is a focal point in any kitchen, open or closed. The interior presents a host of innovative ideas. Take the LED interior light and the automatic IceMaker with fixed water connection in the freezer compartment, for example. Or the two BioFresh drawers, which keep food fresh for significantly longer. Accurate and independent temperature control of

the fridge and freezer compartments is ensured by DuoCooling: two separately adjustable cooling circuits. There is no air exchange between the refrigerator and freezer compartment, so that odours cannot be transferred and the stored food is prevented from drying out. In addition this model can be flush-fitted as the doors open within the width of the cabinet.



The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



The professional **NoFrost** technology from Liebherr makes defrosting a thing of the past. The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



CBNbe 6256 PremiumPlus

Bio
Fresh

No
Frost

A⁺⁺

Duo
Cooling

Ice
Maker

Energy efficiency class: $\lt; A^{++}$
 Energy consumption year/24 hrs: 322/0.881 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre/
 Freezer compartment: 114 litre)
 Noise output: 43 dB(A)
 Climate rating: SN-T
 Door/side walls: beige/beige
 Exterior dimensions in cm (h/w/d): 203.9/91/61.5

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments



The interior features **LED light columns** integrated on either side of the compartment liner, ensuring that the interior is evenly bathed in light to create a unique and dramatic effect within the appliance. The elegant, high quality **GlassLine interior** is adaptable to suit individual requirements.



Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately kept at just above 0°C. Each drawer can be used individually and provides ideal humidity – **HydroSafes** with high humidity or **DrySafes** with low humidity – for a versatile storage solution.



The elegant **Premium-electronics system** ensures that the selected temperature is precisely maintained. All functions can be easily and conveniently managed by gently tapping the touchscreen interface. The temperature is numerically displayed and can be read from the MagicEye's LC display.



No Frost

With **NoFrost**, chilled circulating air freezes the food and any moisture is expelled, which keeps the freezer compartment ice-free at all times and prevents food frosting over.



Premium models with BioFresh feature the new **VarioSafe** drawer, which enables organisation whilst providing a clear view. It is the perfect place to keep smaller items. The drawer can be positioned at various levels elevations on the lighting columns.



LED

LED light columns are integrated on one or both sides of the fridge compartment to uniformly illuminate the interior. The light gradually gets brighter when the door is opened. The satin finish on the light unit creates elegant lighting. The LED light columns also enable you to position the glass shelves at your convenience.



Soft Telescopic

Premium appliances have fully extendable BioFresh-Safes featuring **SoftTelescopic**, a self-retraction mechanism with soft closing, for practical, reliable and convenient everyday use. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°.



Ice Maker

The **plumbed-in IceMaker** provides high-quality ice cubes. The two drawers hold all the ice you need for any occasion. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up. If the quality of the mains water is poor or there is no plumbed-in connection, the ICN 3386 offers the **IceMaker with a water tank** supply. With a 1.2 l capacity and a practical handle, this can be easily removed and filled.



Side by Side

Many LIEBHERR built-in appliances can be positioned next to or on top of one another. The **Side-by-Side concept** makes it possible to position fridges, freezers and wine cabinets for your personal choice. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations.

The features shown are model dependent; the description applies to the relevant model.



Low energy integrated appliance: SBS 7014

Bio Fresh

No Frost

Built-in

Liebherr's SBS 7014 Side-by-Side unit comprise of a fully integrated refrigerator with BioFresh and a fully integrated freezer with IceMaker is the perfect combination for any kitchen. Hidden away behind custom cabinetry, enjoy features such as BioFresh safes, efficient LED lighting throughout, and flexible bottle

racks to maximize interior space. In the full freezer tower, transparent drawers on telescopic rails with safety glass shelf dividers efficiently organize the frozen foods kept FrostSafe with continual circulated air. Both sides incorporate SoftSystem technology for gentle closing of doors.



Maintenance-free and energy efficient: long-life LEDs provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space (it does not detract from the net capacity).



Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards allowing taller bottles to be stored. **BioFresh drawers** in the Premium models come with central **LED lighting** for an optimum view of the food stored. The LEDs are integrated into the partition plate to evenly and brightly illuminate the extended BioFresh drawers from directly above.

SBS 7014
Premium

Side
by
Side

178

178

SIGN 3576
Premium

No Frost

A++

LED

Ice Maker

Soft System

Telescopic Rails

Fixed door / Built-in appliance for integrated use
Energy efficiency class: $\lt; A^{++}$
Energy consumption year / 24 hrs: 241 / 0.660 kWh
Total net capacity: 209 litre
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for freezer compartment

IKBP 3560
Premium

Bio Fresh

A+++

Soft System

Soft Telescopic

Fixed door / Built-in appliance for integrated use
Energy efficiency class: $\lt; A^{+++}$
Energy consumption year / 24 hrs: 89 / 0.242 kWh
Total net capacity: 301 litre (Fridge: 301 litre including BioFresh compartment: 90 litre)
Noise output: 35 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge compartment



Double luxury for the kitchen: SBS 6613

Bio Fresh

No Frost

Built-in

This Side-by-Side provides the most sophisticated solution for cooling and freezing. It has a plenty space for all fresh produce and fits the needs of a modern family perfectly. Also if you want to store the shopping for the weekend or the frozen supply, in this Side-by-Side all can be stored comfortably and easily. The generosity in the SBS 6613 comes with a host of premium features.

The interior GlassLine fittings are stylishly designed and are of excellent quality. The door shelves come furnished with a satin-finished safety glass base, elegant plastic surround, stainless steel rails, bottle shelf with an adjustable bottle holder and BioCool. In addition the doors of this appliance is fitted with two different-sized, removable, transparent VarioBoxes with lids.



Premium BioFresh appliances have fully extendable BioFresh-Safes featuring **SoftTelescopic**, a self-retraction mechanism with soft closing, for practical, reliable and convenient everyday use. The drawers can be fully extended and completely removed, if required, from a door opening angle of 90°. **BioFresh** provides the perfect storage climate for long-lasting food storage freshness. When stored at just over 0°C and at the ideal humidity level, fruit, vegetables, meat and fish all retain their nutritious vitamins for longer.

The plumbed-in automatic **IceMaker** keeps you topped up with high-quality ice cubes for every occasion. Whether you need ice for a refreshing drink or a party with friends, with two drawers, the IceMaker holds all the ice cubes you'll need. Furthermore, it automatically keeps your supplies topped up and you can switch it off at any time.

SBS 6613
Premium



SICN 3386
Premium

Bio Cool No Frost A++ Duo Cooling Soft System

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 230/0.628 kWh
 Total net capacity: 255 litre (Fridge: 193 litre / Freezer compartment: 62 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls
 MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments

ICBN 3386
Premium

Bio Fresh No Frost A++ Duo Cooling Ice Maker Soft System Soft Telescopic

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: <A+>
 Energy consumption year / 24 hrs: 232/0.633 kWh
 Total net capacity: 233 litre (Fridge: 176 litre including BioFresh compartment: 67 litre / Freezer compartment: 57 litre)
 Noise output: 38 dB(A)
 Climate rating: SN-ST
 Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls
 MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments



Reliable, long-lasting freshness with BioCool: SBS 6612

Bio Cool

No Frost

Built-in

Liebherr's NoFrost technology provides professional-standard performance that guarantees long-lasting freshness. Chilled circulating air freezes the food and humidity is expelled so that the freezer is always ice-free and produce never frosts over. NoFrost means no more defrosting. If the quality of the mains water is poor or there

is no plumbed-in connection, the SBS 6612 offers the IceMaker with a water tank supply. With a 1.2 l capacity and a practical handle, this can be easily removed and filled. The BioCool-Box enables regulation of the humidity level in the fridge compartment to keep fruit and vegetables fresher for longer.



The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient-to-use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The stylish white SoftSystem mechanism, integrated in the door, conveniently cushions door movement to ensure extremely soft closure even when the door shelves are fully loaded. The door closes automatically from an opening angle of about 30°.

SBS 6612
Premium

Side
by
Side

178

178

SICN 3386
Premium

Bio Cool

No Frost

A++

Duo Cooling

Soft System

Fixed door / Built-in appliance for integrated use
Energy efficiency class: <A+>
Energy consumption year / 24 hrs: 230/0.628 kWh
Total net capacity: 255 litre (Fridge: 193 litre / Freezer compartment: 62 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge and freezer compartments

ICN 3386
Premium

Bio Cool

No Frost

A++

Duo Cooling

Ice Maker

Soft System

Fixed door / Built-in appliance for integrated use
Energy efficiency class: <A+>
Energy consumption year / 24 hrs: 225/0.615 kWh
Total net capacity: 248 litre (Fridge: 191 litre / Freezer compartment: 57 litre)
Noise output: 38 dB(A)
Climate rating: SN-T
Aperture dimensions in cm (h/w/d): 177.2-178.8/56-57 / min. 55

Controls

MagicEye behind-the-door, touch electronic
Digital temperature display for fridge and freezer compartments



Integrated Frenchdoor fridge-freezer with BioFresh: ECBN 6256

Bio Fresh	No Frost	Built-in
-----------	----------	----------

The 91 cm wide, Frenchdoor fridge-freezer is definitely a design highlight in any kitchen and, with LIEBHERR's BioFresh technology, it's a healthy choice too! BioFresh technology guarantees the best possible environment for lasting freshness, which is really important because the freshness and quality of the food that we eat plays a key role in our health and well-being. Integrated lighting

columns on either side of the appliance interior provide perfectly even illumination, and high-quality Glassline fittings lend elegance to the interior design. The two freezer drawers extend effortlessly on premium-quality telescopic rails, and the plumbed in IceMaker provides sophisticated ice cubes for whatever the occasion.



The versatile bottle shelf above the BioFresh drawers can be used either as a bottle shelf or a glass storage shelf, both are stored in the recess. The interior features two integrated lighting columns with multiple LEDs to evenly illuminate the interior. The lighting columns also facilitate the variable positioning of the glass shelves.



The SoftSystem, in pristine white, is integrated into the door to cushion movement as the door is shut, ensuring that the door closes gently, even with fully-loaded door shelves. The door closes automatically from an opening angle of approx. 30°.



ECBN 6256 PremiumPlus	Bio Fresh	No Frost	A++	Duo Cooling	Ice Maker	Soft System
Fixed door / Built-in appliance for integrated use						
Energy efficiency class: $\lt; A^{++}$						
Energy consumption year / 24 hrs: 322 / 0.881 kWh						
Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)						
Noise output: 43 dB(A)						
Climate rating: SN-T						
Aperture dimensions in cm (h/w/d): 203.2-203.3/91.5/min. 62.5						
Controls						
MagicEye behind-the-door, touch electronic						
Digital temperature display for fridge and freezer compartments						



The two freezer compartment drawers extend on premium-quality telescopic rails and benefit from a self-closing mechanism, making them almost effortless to use. And Liebherr's professional NoFrost technology means there is no need to defrost the appliance and also ensures particularly low energy consumption.

Extra-wide BioFresh food storage centre: ECBN 6156

Bio Fresh

No Frost

Built-in

The 91-cm-wide, built-in BioFresh fridge-freezer is a real eyecatcher! Available with door-on-door installation that gives customised integration into kitchen design, and two freezer drawers that easily extend on premium-quality telescopic rails, this built-in masterpiece is a design highlight for any kitchen. The large refrigerator

compartment and adjacently arranged BioFresh drawers, together with the NoFrost freezer compartment offer optimum storage for all types of food. The integral IceMaker supplies ice cubes for every occasion, whilst the integrated water filter ensures optimum ice quality.



The innovative **electronic controls** ensure that the selected temperature is accurately maintained. Thanks to the ingenious touch interface, all functions can be set with ease. The temperature in the refrigeration and freezer compartments can be read from the MagicEye digital display on the LCD. The PremiumPlus interior features **LED light columns** integrated on either side of the compartment liner.

The professional **NoFrost technology** from Liebherr makes defrosting a thing of the past. The **IceMaker** with fixed water connection provides you with a constant supply of ice cubes for every occasion. The two **pull-out freezer drawers** are mounted on high-quality **telescopic rails** and can be effortlessly extended to provide a perfect view and ideal storage conditions.



ECBN 6156 PremiumPlus

Bio Fresh No Frost A+ Duo Cooling Ice Maker

Fixed door / Built-in appliance for integrated use
 Energy efficiency class: <math>\lt; A \lt;/math>
 Energy consumption year / 24 hrs: 410 / 1.121 kWh
 Total net capacity: 471 litre (Fridge: 357 litre including BioFresh compartment: 68 litre / Freezer compartment: 114 litre)
 Noise output: 42 dB(A)
 Climate rating: SN-T
 Aperture dimensions in cm (h/w/d): 203.2/91.5/min. 62.5

Controls

MagicEye behind-the-door, touch electronic
 Digital temperature display for fridge and freezer compartments



BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0°C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator.

It is necessary to specify Left Hand or Right Hand hinge when ordering: ECBN 6156 001 right hand hinge, ECBN 6156 617 left hand hinge

ECBN 6156 617 with left hand hinge
 Stainless steel panels are not included. This appliance must be bracketed to the wall/floor.

Bio Fresh No Frost Built-in

The innovative food storage centre: ECBN 5066

The 76-cm-wide ECBN 5066 food centre creates a stunning visual impact in any kitchen environment. As the doors open, the interior also reveals a host of innovative ideas, LED lighting, BioFresh drawers mounted on telescopic rails, together with the NoFrost

freezer compartment offers optimum storage for all food types. The integral IceMaker supplies ice for every occasion, whilst the integrated water filter ensures optimum ice quality.




BioFresh drawers provide the perfect storage climate for you to enjoy long-lasting freshness. When stored at a temperature slightly above 0°C and at the correct humidity level, fruit and vegetables, meat, fish and dairy products all retain their vitamin content, delicate flavour and appetising appearance for significantly longer than in a standard refrigerator. The DrySafe, with a low humidity level, is ideal for storing meat, fish and milk products.



ECBN 5066 comes with an **LED lighting column** on each side of the inner door, which incorporates multiple LEDs to evenly illuminate the appliance interior. A special satin-finish on the light cover creates an appealing and sophisticated lighting effect. The lighting column also facilitates the variable positioning of the glass shelves.



ECBN 5066 PremiumPlus	Bio Fresh	No Frost	A++	Duo Cooling	Ice Maker
Fixed door / Built-in appliance for integrated use					
Energy efficiency class: $\lt; A^+$					
Energy consumption year / 24 hrs: 287 / 0.785 kWh					
Total net capacity: 379 litre (Fridge: 276 litre including BioFresh compartment: 57 litre / Freezer compartment: 103 litre)					
Noise output: 42 dB(A)					
Climate rating: SN-T					
Aperture dimensions in cm (h/w/d): 203.2/76.2/min. 61					
Controls					
MagicEye behind-the-door, touch electronic					
Digital temperature display for fridge and freezer compartments					



The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. This innovative technology creates a much larger storage capacity and keeps the freezer constantly frost-free, making defrosting a thing of the past.

It is necessary to specify Left Hand or Right Hand hinge when ordering: ECBN 5066 001 right hand hinge, ECBN 5066 617 left hand hinge

ECBN 5066 001 with right hand hinge
This appliance must be bracketed to the wall/floor.



Side-by-Side fridge-freezers

SBSes 7165 PremiumPlus



SBSbs 8673 Premium



SBSes 8663 Premium



SBSbs 7353 Premium



SBSef 7242 Comfort



Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Including Wine storage compartment
Freezer compartment
Star coding ⁴
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ⁵
Noise output
Voltage/Connection rating
Fridge and BioFresh compartments
Defrosting
Interior light
BioFresh-Safes
BioFresh-Plus, adjustable
Fruit and vegetable bins
Bottle shelf
GlassLine Door interior
VarioBoxes
Freezer compartment
NoFrost/Defrosting
Drawers
Cold storage accumulators
IceMaker ⁶
Ice cube production in 24 hrs
Ice cube reservoir
FrostSafe
Dimensions
Exterior dimensions in cm (h/w/d)
Key features
SoftSystem/SmartSteel
Design
Replaceable door seal
Concealed hinge with restricted opening
Colour/material options:

A++
431/1.178 kWh
591 litre
476 litre
110 litre
126 litre (Max. 41 Bordeaux bottles 0.75 Ltr.) ³
115 litre

25 h
16 kg
6
SN-ST
42 dB(A)
220-240V~/2.6 A
Automatic
LED light column on both sides
3 on telescopic rails with LED lighting
•
for variable use
Premium
•
NoFrost/Automatic
5
2
fixed 3/4" water connection
0.8 kg
1.5 kg
•
185.2/121/63
• / •
SwingLine
•
•

A+++ ²
255/0.696 kWh
629 litre
367 litre
133 litre
262 litre

20 h
18 kg
3
SN-T
38 dB(A)
220-240V~/2.5 A
Automatic
LED ceiling lighting with dimmer function
3 with SoftTelescopic with LED lighting
•
for variable use
Premium
•
NoFrost/Automatic
9/6 on roller tracks with LED lighting
2
fixed 3/4" water connection
0.8 kg
0.8 kg
•
185/121/66.5 ²
• / •
HardLine
•
•

A+++ ²
258/0.702 kWh
635 litre
367 litre
133 litre
268 litre

20 h
18 kg
3
SN-T
38 dB(A)
220-240V~/2.5 A
Automatic
LED ceiling lighting with dimmer function
3 with SoftTelescopic with LED lighting
•
for variable use
Premium
•
NoFrost/Automatic
8/7 on roller tracks with LED lighting
2
•
185/121/66.5 ²
• / •
HardLine
•
•

A++ ²
383/1.048 kWh
654 litre
539 litre
155 litre
115 litre

25 h
16 kg
3
SN-T
39 dB(A)
220-240V~/2.6 A
Automatic
LED ceiling lighting
2 on telescopic rails with LED lighting
•
2 on telescopic rail
Bottle shelf, Champagne rack
Premium
•
NoFrost/Automatic
5
2
fixed 3/4" water connection
0.8 kg
1.5 kg
•
185.2/121/63 ²
- / •
SwingLine
•
SBSes 7353 in Stainless steel

A++ ²
359/0.982 kWh
634 litre
381 litre
253 litre

24 h
20 kg
2
SN-T
41 dB(A)
220-240V~/2.5 A
Automatic
LED ceiling lighting
•
2 on telescopic rail
Comfort
•
NoFrost/Automatic
8
•
185.2/121/63 ²
- / •
HardLine
•

1 Commission Delegated Regulation (EU) No 1060/2010
 2 To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.
 3 DIN norm bordeaux bottles NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

4 ********* freezer compartment with -18°C or colder
 5 Climate Ratings: **SN** +10°C to +32°C **N** +16°C to +32°C **ST** +16°C to +38°C **T** +16°C to +43°C

6 IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)



Fridge-freezers



CBNes 6256 PremiumPlus



CBNbe 6256 PremiumPlus



Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Freezer compartment
Star coding ²
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ³
Noise output
Voltage/Connection rating

Fridge and BioFresh compartments
Defrosting
Interior light
BioFresh-Safes
Bottle shelf
GlassLine Door interior

Freezer compartment
NoFrost/Defrosting
Drawers
IceMaker ⁴
Ice cube production in 24 hrs
Ice cube reservoir

Dimensions
Exterior dimensions in cm (h/w/d)

Key features
Design
Concealed hinge with restricted opening

<A++>
322/0.881 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
45 h
11 kg
3
SN-T
43 dB(A)
220-240V~/1.5 A

Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting for variable use
Premium

NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg

203.9/91/61.5

HardLine
•

<A++>
322/0.881 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
45 h
11 kg
3
SN-T
43 dB(A)
220-240V~/1.5 A

Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting
for variable use
Premium

NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg

203.9/91/61.5

HardLine
•


¹ Commission Delegated Regulation (EU) No 1060/2010
² ★★★★★ freezer compartment with -18°C or colder

³ Climate Ratings: SN +10°C to +32°C N +16°C to +32°C ST +16°C to +38°C T+16°C to +43°C
⁴ IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)



Fridge-freezers for integrated use

ECBN 6256 PremiumPlus



Energy efficiency class
Energy consumption year/24 hrs ¹
Total net capacity
Fridge compartment
Including BioFresh compartment
Freezer compartment
Star coding ²
Temperature rise time
Freezing capacity in 24 hrs
Temperature zones
Climate rating ³
Noise output
Voltage/Connection rating
Fridge compartment
Defrosting
Interior light
BioFresh-Safes
Bottle shelf
GlassLine Door interior
Freezer compartment
NoFrost/Defrosting
Drawers
IceMaker ⁴
Ice cube production in 24 hrs
Ice cube reservoir
Type of appliance
Door assembly
Dimensions
Aperture dimensions in cm (h/w/d)
Key features
SoftSystem

<A>
322/0.881 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
40 h
11 kg
3
SN-T
43 dB(A)
220-240V~/1.5 A
Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting
for variable use
Premium
NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg
Door on Door/or integrated use
203.2-203.3/91.5/at least 62.5
•

ECBN 6156 PremiumPlus



<A>
410/1.121 kWh
471 litre
357 litre
68 litre
114 litre
★★★★
40 h
11 kg
3
SN-T
42 dB(A)
220-240V~/1.5 A
Automatic
LED light column on both sides and LED ceiling lighting
2 on telescopic rails with LED lighting
for variable use
Premium
NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.3 kg
2.7 kg
Door on Door/or integrated use
203.2/91.5/at least 62.5
right door hinges: ECBN 6156 001
left door hinges: ECBN 6156 617
It is necessary to specify Left Hand or Right Hand hinge when ordering

ECBN 5066 PremiumPlus



<A>
287/0.785 kWh
379 litre
276 litre
57 litre
103 litre
★★★★
30 h
12 kg
3
SN-T
42 dB(A)
220-240V~/1.5 A
Automatic
LED light column on both sides
2 on telescopic rails with LED lighting
for variable use
Premium
NoFrost/Automatic
2 on telescopic rails, self-retracting with LED lighting
fixed 3/4" water connection
1.0 kg
2.7 kg
Door on Door/or integrated use
203.2/76.2/at least 61
right door hinges: ECBN 5066 001
left door hinges: ECBN 5066 617
It is necessary to specify Left Hand or Right Hand hinge when ordering

¹ Commission Delegated Regulation (EU) No 1060/2010

² ★★★★★ freezer compartment with -18°C or colder

³ Climate Ratings: SN +10°C to +32°C N +16°C to +32°C ST +16°C to +38°C T+16°C to +43°C

⁴ IceMaker – automatic ice-cube maker (can be switched off) with fixed water connection 3/4" and solenoid valve (needs to be plumbed in)