

## Our catalogues

Find out everything you need to know about Liebherr appliances in the latest catalogues. Available in printed format from retailers or as a PDF download from [home.liebherr.com](http://home.liebherr.com)



## Smart communication on all fronts



### BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



### WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



### Kitchen Photo Designer App

Be your own interior designer: take a photo of your kitchen, select the Liebherr model of your choice and position it into your photo by swiping the screen.



### IceCrusher App

Playful fun; With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.  
[apps.home.liebherr.com](http://apps.home.liebherr.com)



Discover the world of Liebherr-Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!



Click the link to directly access our social media channels:  
[socialmedia.home.liebherr.com](http://socialmedia.home.liebherr.com)

Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle.

Subject to modification. Current data see [home.liebherr.com](http://home.liebherr.com).  
Printed in Germany by ralf mediagroup gmbh. 7943226-12/04.17



# Wine Special 2017





## Fully developed for the enjoyment of wine

Where wine is concerned, correct temperatures are always important. From the air temperature which ensures perfect growth of the grapes, to that which governs the aging processes in production, to the balanced temperature for storage of the finished wine. Above all, temperature ultimately defines a wine's taste and palate - the serving temperature will determine how much it is savoured and enjoyed.

EWTgw 2383



Scan the code with your Smartphone  
to find out more about wine.  
[wine.liebherr.com](http://wine.liebherr.com)



# Content

Ideal storage temperature	06
Optimum air quality	08
Best position for fine wines	10
Protection against UV light	12
The Vinidor range	16
Wine storage cabinet GrandCru	30
Humidor	37
Wine storage cabinets Vinothek	38
Multi-temperature Vinothek	44
Accessoires	46

# The ideal storage temperature for wine

\_\_\_ The ideal long term storage temperature for wine is between + 10°C and + 12°C. It is critical that the temperature is kept as constant as possible because this is the only way that a wine's natural harmony will be preserved. \_\_\_

**A**s the temperature rises, the wine molecules kinetic energy increases and this accelerates the aging process causing the wine to deteriorate. Consequently, storage temperatures of between +10°C and +12°C are recommended for storing wine over prolonged periods. Maintaining a constant temperature is most important, as fluctuations during storage will impair the quality of the wine. Furthermore, the temperature at which a wine is consumed also plays a crucial role in how it tastes. Red wines should be served at a warmer temperature than white wines because they contain more tannins (polyphenols).

Tannins react with oxygen more quickly at higher temperatures. This is what happens in the process of allowing a wine to »breathe«, when the full aroma and taste are only achieved once the wine has combined with oxygen. The length of time for which a wine should breathe depends on its variety and quality. Barolo, Rioja, Burgundy and Bordeaux each take a different amount of time to develop. In general, the longer a wine matured in the barrel, the more likely it is to need a longer breathing time for full enjoyment.

## Perfect storage and temperature control with Liebherr

**Electronic control system.** Liebherr's highly precise electronic control systems and advanced air conditioning technologies guarantee appliances maintain a constant interior temperature, even in the event of major fluctuations in the ambient temperature.

**Long-term storage.** With constant temperatures and a perfectly controlled climate, Liebherr's wine storage cabinets and Vinidor models provide the very best conditions for wine to age without disturbance, and to develop fully during storage.

**Optimum drinking temperature.** In our Vinidor wine cabinets, which offer two or three wine safes, different wines can be stored according to their ideal serving temperature. Each wine safe can be independently programmed to between +5°C and +20°C, giving great storage flexibility.

In the multi-temperature wine cabinets in our Vinothek range, specialised climate technology is used to achieve temperature stratification within the appliance. Lower temperatures in the bottom section are ideal for sparkling wines and champagne, whereas a temperature of about +18°C in the upper section is perfect for red wines. Meanwhile, the temperature in the middle section brings white wines to an ideal serving temperature.



# Optimum air quality

\_\_\_ The quality of the ambient air is essential if the wine is to develop fully and be enhanced during storage – any airborne contaminants can be transferred to the wine and spoil it. \_\_\_

Classic natural corks very adequately keep the wine in the bottle, but in no way do they hermetically seal it. As a result, air, which is far more than odourless oxygen, infiltrates the bottle passing down the edges of the cork. If the bottles are stored in a cardboard box, the wine can take on the odour of the cardboard. But food odours in particular present problems. When storing wine at home, especially in a kitchen

environment, wines will almost certainly lose their »terroir and type« characteristics – i.e. they will spoil! Although glass stoppers and screw caps provide airtight closures for bottles, wines inevitably age more slowly because only the oxygen in the bottle is available to them. Synthetic corks allow too much air into the bottle, making them much less suitable for long-term storage of wine altogether.

## Optimum air quality with Liebherr

**Optimum air-freshness.** All Liebherr wine cabinets are fitted with FreshAir activated-charcoal filters, which ensure optimum air quality within the appliance. The active-charcoal reacts with any contaminants, binding them to its surface, and thereby filtering them from the incoming-air. In the Vinidor appliances, each individual wine zone has a FreshAir activated charcoal filter. Only the Vinidor appliances UWT 1682 (TipOpen under-worktop appliance), UWTeS 1672 (under-worktop appliance) and WTes 1672 (table height, under-worktop) have one FreshAir activated charcoal filter in the divider to filter both zones. This prevents odours from the ambient air affecting the taste of the wines stored in the interior. Filters should ideally be replaced once a year. They can be ordered as an accessory and are easy to replace.

**Ideal humidity.** If wines are to be stored for prolonged periods, the correct humidity is essential. At humidity levels below 50%, even the best natural corks start to shrink. This allows more and more oxygen to penetrate the bottle, and evaporation to occur; and, as the fill level drops, oxidation increases. Wines become gradually sweeter until they spoil completely. However, with humidity levels of at least 50%, Liebherr wine cabinets ensure the best conditions for both corks and wine. Thanks to an impressive vaporiser system and specially regulated air circulation, high humidity levels are sustained in all wine storage cabinets.

Our Vinothek multi-temperature wine cabinets, with graduated temperature zones, are fitted with porous lava stone, which controls humidity within these appliances.



# Best environment for fine wines

\_\_\_ For perfect storage the wine should not be disturbed. \_\_\_

Even small vibrations caused by the noise of machinery, road traffic or frequent footfall can harm old wines. The wine is imperceptibly »shaken up«, and the sediment is disturbed. This leads to increased reactions between the different components of the wine, which then creates undesirable compounds that leave the wine tasting odd and

inharmonious – something like what is seen straight after the filling process. Wine bottles are usually stored lying down so that their corks are constantly moistened and cannot dry out. On the other hand, bottles with screw caps or glass stoppers can be stored upright without any problem as they provide an airtight seal for the wine.

## Optimum storage with Liebherr

**Protection against vibration.** The specially developed, low-vibration compressors used in Liebherr wine cabinets provide gentle storage conditions. In the new Vinidor wine cabinets, the entire refrigeration system is fully vibration dampened to minimise vibration transmission. Accordingly, appliances make very little operating noise, and the wine can be stored with minimal disturbance.

**Optimum position.** Wine is able to age in peace on stable, handcrafted wooden shelves. These shelves are unvarnished so that varnish vapours do not damage the wine. The wooden shelves are ideal for safely storing Bordeaux bottles, and positioning the wine bottles in opposite directions on the shelves allows optimum use of the appliance's capacity. In the Vinidor appliances, the wooden shelves are fitted to telescopic rails to provide a clear overview of the bottles, and to ensure easy access – even to those at the back. The presentation shelf is ideal for showcasing fine wines and also maintains opened bottles at a perfect temperature.

**Soft closing.** The door closes softly automatically from an opening angle of about 45° (freestanding wine cabinets) and 30° (integrated wine cabinets) to prevent any vibrations that could damage the wine.



# Protection against ultraviolet light

\_\_\_ Most wine bottles are tinted as ultraviolet rays pose a danger to all wines. \_\_\_

Light, in particular the invisible rays from the ultraviolet spectrum, is a common cause of undesirable chemical reactions in wines. The consequences of light-damage are visible to the eye: pale red wines, and white wines that take on a golden-yellow colour. »Light-strike« (or »Goût de Lumière« as the French know it) destroys the wine's balance and flattens its aroma and, to avoid it, most producers

bottle their wine in brown or green glass, which absorbs a great deal of the UV rays. However, this alone is not enough for bottles that are not stored in the dark. Slight temperature increases caused by light radiation can also damage the wine – they make it age quicker thereby altering the natural development processes, even to the extent that the wine can be permanently destroyed.

## UV protection with Liebherr

**Insulated glass doors with UV protection.** To minimise the effects of UV rays, Liebherr wine cabinets are fitted with special UV-resistant insulation glass. The UV protection is provided by a special dual-pane structure, which incorporates an inner, tinted-glass pane and an outer, metallised, low-E (low-emittance) pane. This glass composite reflects nearly all the damaging UV radiation and prevents any deterioration of the wine.

**LED lighting concept.** This innovative technology ensures that the interior of the appliance is evenly lit without any UV radiation, as the LED light spectrum does not contain any UV rays. Furthermore, because of minimal heat generation with LEDs, the wines can be illuminated and beautifully presented permanently without any localised heating of the bottles.





The perfect range for wine aficionados

## Vinidor range

 Vinidor Page 16

The Vinidor range offers ultimate flexibility and combines the advantages of both wine storage cabinets and multi-temperature wine cabinets in a single appliance. Appliances in the range come with either two or three temperature zones, which can be set independently to the required temperature between +5°C and +20°C. Accordingly, an appliance with three temperature zones can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature. Vinidor appliances also offer the perfect climate for long-term wine storage. The varying sizes of the temperature zones, together with the fully adjustable temperature controls, make these appliances suitable for just about any collection of wines.



## Wine storage cabinets

 GrandCru Page 30  Vinothek Page 38


Wine storage cabinets offer similar conditions to a wine cellar. They are therefore an ideal choice for both long-term storage and storage of large wine stocks, always achieving the perfect serving temperature. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.



## Multi-temperature wine cabinets

 Vinothek Page 44

Multi-temperature wine cabinets from the Vinothek range offer versatile storage for different types of wine, each at its perfect drinking temperature. The innovative climate technology that we use creates temperature graduation within the appliance. As a result red wine can be stored in the upper section at +18°C; in the lower section a temperature of +5°C is ideal for storing sparkling wine or champagne; and in the middle section the temperature is perfect for white wine.




## Vinidor range

The Vinidor range offers ultimate flexibility and combines the advantages of both wine storage cabinets and multi-temperature wine cabinets in a single appliance. Appliances in the range come with either two or three wine zones, which can be set independently to the required temperature between +5°C and +20°C. Accordingly, an appliance with three wine zones can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature. Vinidor appliances also offer the perfect climate for long-term wine storage. The varying sizes of the wine zones, together with the fully adjustable temperature controls, make these appliances suitable for just about any collection of wines. The spring-loaded door seal helps maintain precise independent temperature control in each climate zone.





The electronic LC-Display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



LED

The **LED lighting in the individual wine compartments can be dimmed** to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with this innovative, no-heat LED lighting concept. The LED lighting can also be adjusted to operate continuously or in conjunction with door openings.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical **aluminium door handle, with integrated opening mechanism**, allows the door of the appliance to be opened conveniently with a minimum of effort.



Tip Open

The **handle-free glazed door with TipOpen technology** guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines.



Telescopic Rails

The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. Storing the bottles in opposite directions permits full use of the capacity. The **clip-on labelling system** provides a quick and clear overview of your wine store.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the cabinet.



The fresh air supplied through the **FreshAir activated charcoal filter** and re-circulating air cooling system ensures optimal air quality. This is crucially important for the maturing process and preservation of the wine. FreshAir charcoal filters are easily accessible from the front and are replaceable.



Side by Side

The **Side-by-Side concept** makes it possible to position fridges, freezers and wine cabinets to meet your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations.



WTes 1672



Vinidor range	WTes 5872	WTes 5972	WTpes 5972	WTes 1672
	LED Soft System Telescopic Rails	LED Soft System Telescopic Rails	LED Telescopic Rails	LED Telescopic Rails
Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	178	211	155	34
Total gross/net capacity	578/496 litre	593/516 litre	593/516 litre	123/95 litre
Energy efficiency class	<A> <sup>5</sup>	<A> <sup>5</sup>	<A> <sup>5</sup>	<A>
Energy consumption year/24 hrs <sup>2</sup>	180/0.493 kWh <sup>5</sup>	182/0.498 kWh <sup>5</sup>	182/0.498 kWh <sup>5</sup>	137/0.375 kWh
Noise output	37 dB(A)	38 dB(A)	38 dB(A)	38 dB(A)
Climate rating <sup>3</sup>	SN-ST	SN-ST	SN-ST	SN-ST
Voltage/Connection rating	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/0.8 A
Door	Glass door with stainless steel frame			
Side walls	stainless steel	stainless steel	stainless steel	stainless steel
<b>Wine storage compartment</b>				
Temperature zones / -range	3/+5°C to +20°C	2/+5°C to +20°C	2/+5°C to +20°C	2/+5°C to +20°C
Adjustable cooling circuits	3	2	2	2
Type of control/display	LCD Display/internal digital	LCD Display/internal digital	LCD Display/internal digital	LCD Display/internal digital
Forced air system	•	•	•	•
Fresh air supply via FreshAir activ. charcoal filter	•	•	•	•
Humidity control via	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation
Interior light	LED	LED	LED	LED
permanently activated/dimmable	•/•	•/•	•/•	•/•
Shelf material	wooden shelf	wooden shelf	wooden shelf	wooden shelf
Storage shelves	13	10	6	5
running on telescopic rails	10	8	5	3
Presentation shelf	1	1		
Pull-out shelf for upright bottles			2	
Fault: warning signal	visual and audible	visual and audible	visual and audible	visual and audible
Door open: warning signal	audible	audible	audible	audible
Child lock function	•	•	•	•
<b>Dimensions</b>				
Exterior dimensions in cm (h/w/d <sup>4</sup> )	192/70/74.2 <sup>5</sup>	192/70/74.2 <sup>5</sup>	192/70/74.2 <sup>5</sup>	82.2/60/57.5
<b>Features</b>				
Design	HardLine	HardLine	HardLine	HardLine
SoftSystem	•	•		
Slimline door handle	Aluminium handle	Aluminium handle	Stainless steel slimline door handle	Stainless steel slimline door handle
with integrated opening mechanism	•	•		
Door hinges	right, reversible	right, reversible	right, reversible	right, reversible
Replaceable door seal	•	•	•	•
Concealed hinge with restricted opening	•	•		
Lock	•	•	•	•
<b>Accessories</b> (see page 46–47)				
	01, 04, 06, 09	01, 04, 06, 09	01, 06, 09	01, 06, 09

<sup>1/2/3/4</sup> Notes see pages 34/35

<sup>5</sup> To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.



EWTgb 3583



### Vinidor range

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>
Total gross/net capacity
Energy efficiency class
Energy consumption year /24 hrs <sup>2</sup>
Noise output
Climate rating <sup>3</sup>
Voltage / Connection rating
Door

#### Wine storage compartment

Temperature zones / -range
Adjustable cooling circuits
Type of control / display
Forced air system
Fresh air supply via FreshAir activ. charcoal filter
Humidity control via
Interior light
permanently activated / dimmable
Shelf material
Storage shelves
running on telescopic rails
Presentation shelf
Fault: warning signal
Door open: warning signal
Child lock function

#### Dimensions

Aperture dimensions in cm (h/w/d <sup>4</sup> )
-------------------------------------------------

#### Features

SoftSystem
TipOpen Technology
Door hinges

#### Accessories (see page 46–47)

### EWTgw 3583 Vinidor

LED
Tip Open
Soft System
Telescopic Rails
Built-in

83
307/271 litre
<A>
165/0.450 kWh
36 dB(A)
SN-ST
220-240V~/1.0 A
white insulated glass door, handle and frame free

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
10
8
1
visual and audible
audible
•

177.2-178.8/56-57 / at least 55
---------------------------------

•
•
right, reversible

01, 06
--------

Available 3rd quarter 2017

### EWTgb 3583 Vinidor

LED
Tip Open
Soft System
Telescopic Rails
Built-in

83
307/271 litre
<A>
165/0.450 kWh
36 dB(A)
SN-ST
220-240V~/1.0 A
black insulated glass door, handle and frame free

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
10
8
1
visual and audible
audible
•

177.2-178.8/56-57 / at least 55
---------------------------------

•
•
right, reversible

01, 06
--------

Available 3rd quarter 2017

### EWTdf 3553 Vinidor

LED
Soft System
Telescopic Rails
Built-in

80
289/254 litre
<A>
163/0.445 kWh
36 dB(A)
SN-ST
220-240V~/1.0 A
Insulated glass door prepared for cabinet door or stainless steel front

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
10
8
1
visual and audible
audible
•

177.2-178.8/56-57 / at least 55
---------------------------------

•
•
right, reversible

01, 06, 11
------------

Available 2nd quarter 2017

This special range of wine cabinets can either accept furniture overlay panels (supplied by your kitchen retailer) or the s/steel overlay accessory (at additional cost). See page 47.

Please check furniture cabinet weight limits with your kitchen retailer



EWTgw 2383



**Vinidor range**

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	51
Total gross/net capacity	195/169 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	153/0.419 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/1.0 A
Door	white insulated glass door, handle and frame free

**Wine storage compartment**

Temperature zones/-range	2/+5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	•/•
Shelf material	wooden shelf
Storage shelves	6
running on telescopic rails	4
Presentation shelf	1
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	122-123.6/56-57/at least 55
-------------------------------------------------	-----------------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Door hinges	right, reversible

**Accessories** (see page 46–47)

	01, 06
--	--------

**EWTgw 2383** Vinidor

LED	Tip Open	Soft System	Telescopic Rails	Built-in
-----	----------	-------------	------------------	----------

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	51
Total gross/net capacity	195/169 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	153/0.419 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/1.0 A
Door	white insulated glass door, handle and frame free

**Wine storage compartment**

Temperature zones/-range	2/+5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	•/•
Shelf material	wooden shelf
Storage shelves	6
running on telescopic rails	4
Presentation shelf	1
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	122-123.6/56-57/at least 55
-------------------------------------------------	-----------------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Door hinges	right, reversible

**Accessories** (see page 46–47)

	01, 06
--	--------

Available 3rd quarter 2017

**EWTgb 2383** Vinidor

LED	Tip Open	Soft System	Telescopic Rails	Built-in
-----	----------	-------------	------------------	----------

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	51
Total gross/net capacity	195/169 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	153/0.419 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/1.0 A
Door	black insulated glass door, handle and frame free

**Wine storage compartment**

Temperature zones/-range	2/+5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	•/•
Shelf material	wooden shelf
Storage shelves	6
running on telescopic rails	4
Presentation shelf	1
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	122-123.6/56-57/at least 55
-------------------------------------------------	-----------------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Door hinges	right, reversible

**Accessories** (see page 46–47)

	01, 06
--	--------

Available 3rd quarter 2017

**EWTdf 2353** Vinidor

LED	Soft System	Telescopic Rails	Built-in
-----	-------------	------------------	----------

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	48
Total gross/net capacity	183/158 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	152/0.416 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/1.0 A
Door	Insulated glass door prepared for cabinet door or stainless steel front

**Wine storage compartment**

Temperature zones/-range	2/+5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	•/•
Shelf material	wooden shelf
Storage shelves	6
running on telescopic rails	4
Presentation shelf	1
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	122-123.6/56-57/at least 55
-------------------------------------------------	-----------------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Door hinges	right, reversible

**Accessories** (see page 46–47)

	01, 06, 11
--	------------

Available 2nd quarter 2017

This special range of wine cabinets can either accept furniture overlay panels (supplied by your kitchen retailer) or the s/steel overlay accessory (at additional cost). See page 47.



EWTdf 1653



**Vinidor range**

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>
Total gross/net capacity
Energy efficiency class
Energy consumption year /24 hrs <sup>2</sup>
Noise output
Climate rating <sup>3</sup>
Voltage / Connection rating
Door

**Wine storage compartment**

Temperature zones / -range
Adjustable cooling circuits
Type of control / display
Forced air system
Fresh air supply via FreshAir activ. charcoal filter
Humidity control via
Interior light
permanently activated / dimmable
Shelf material
Storage shelves
running on telescopic rails
Presentation shelf
Fault: warning signal
Door open: warning signal
Child lock function

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )
-------------------------------------------------

**Features**

SoftSystem
TipOpen Technology
Door hinges

**Accessories** (see page 46–47)

**EWTgw 1683** Vinidor

LED
Tip Open
Soft System
Telescopic Rails
Built-in

33
125/104 litre
<A>
146/0.400 kWh
36 dB(A)
SN-ST
220-240V~/0.8 A
white insulated glass door, handle and frame free

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
4
2
1
visual and audible
audible
•

87.4-89/56-57 / at least 55
-----------------------------

•
•
right, reversible

01, 06
--------

Available 3rd quarter 2017

**EWTgb 1683** Vinidor

LED
Tip Open
Soft System
Telescopic Rails
Built-in

33
125/104 litre
<A>
146/0.400 kWh
36 dB(A)
SN-ST
220-240V~/0.8 A
black insulated glass door, handle and frame free

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
4
2
1
visual and audible
audible
•

87.4-89/56-57 / at least 55
-----------------------------

•
•
right, reversible

01, 06
--------

Available 3rd quarter 2017

**EWTdf 1653** Vinidor

LED
Soft System
Telescopic Rails
Built-in

30
117/97 litre
<A>
145/0.397 kWh
36 dB(A)
SN-ST
220-240V~/0.8 A
Insulated glass door prepared for cabinet door or stainless steel front

2/+5°C to +20°C
2
LCD Display / internal digital
•
switchable ventilation
LED
• / •
wooden shelf
4
2
1
visual and audible
audible
•

87.4-89/56-57 / at least 55
-----------------------------

•
•
right, reversible

01, 06, 11
------------

Available 2nd quarter 2017

This special range of wine cabinets can either accept furniture overlay panels (supplied by your kitchen retailer) or the s/steel overlay accessory (at additional cost). See page 47.



UWT 1682

Scan the code with your Smartphone to find out more about UWT 1682.



Liebherr's touch opening door with **TipOpen technology** integrates perfectly into kitchens with a handle-free design. The double-glazed door opens 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will activate and gently and quietly close the door again.



**Vinidor range**

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	34
Total gross/net capacity	123/94 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	144/0.392 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/0.8 A
Door	black insulated glass door, handle and frame free

**Wine storage compartment**

Temperature zones / -range	2/ +5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	• / •
Shelf material	wooden shelf
Storage shelves	5
running on telescopic rails	3
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	82-87/60/at least 58
-------------------------------------------------	----------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Slimline door handle	
Door hinges	right, reversible
Concealed hinge with restricted opening	•
Lock	•

**Accessories** (see page 46–47)

	01, 06
--	--------

**UWT 1682** Vinidor

LED	Tip Open	Soft System	Telescopic Rails	Built-in
-----	----------	-------------	------------------	----------

82-87  
Under-worktop appliance

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	34
Total gross/net capacity	123/94 litre
Energy efficiency class	<A>
Energy consumption year/24 hrs <sup>2</sup>	144/0.392 kWh
Noise output	36 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/0.8 A
Door	black insulated glass door, handle and frame free

**Wine storage compartment**

Temperature zones / -range	2/ +5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	LCD Display/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	• / •
Shelf material	wooden shelf
Storage shelves	5
running on telescopic rails	3
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	82-87/60/at least 58
-------------------------------------------------	----------------------

**Features**

SoftSystem	•
TipOpen Technology	•
Slimline door handle	
Door hinges	right, reversible
Concealed hinge with restricted opening	•
Lock	•

**Accessories** (see page 46–47)

	01, 06
--	--------

**UWTeS 1672** Vinidor

LED	Telescopic Rails	Built-in
-----	------------------	----------

82-87  
Under-worktop appliance

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	34
Total gross/net capacity	123/94 litre
Energy efficiency class	<B>
Energy consumption year/24 hrs <sup>2</sup>	196/0.535 kWh
Noise output	38 dB(A)
Climate rating <sup>3</sup>	SN-ST
Voltage/Connection rating	220-240V~/0.8 A
Door	Glass door with stainless steel frame

**Wine storage compartment**

Temperature zones / -range	2/ +5°C to +20°C
Adjustable cooling circuits	2
Type of control/display	MagicEye/internal digital
Forced air system	•
Fresh air supply via FreshAir activ. charcoal filter	•
Humidity control via	switchable ventilation
Interior light	LED
permanently activated/dimmable	• / •
Shelf material	wooden shelf
Storage shelves	5
running on telescopic rails	3
Fault: warning signal	visual and audible
Door open: warning signal	audible
Child lock function	•

**Dimensions**

Aperture dimensions in cm (h/w/d <sup>4</sup> )	82-87/60/at least 58
-------------------------------------------------	----------------------

**Features**


SoftSystem	•
TipOpen Technology	•
Slimline door handle	Stainless steel slimline door handle
Door hinges	right, reversible
Concealed hinge with restricted opening	•
Lock	•

**Accessories** (see page 46–47)

	01, 06, 09
--	------------

## Wine storage cabinets GrandCru


Wine storage cabinets can be set to exactly the temperature required within the range of +5°C to +20°C. This ensures that the selected temperature is maintained constantly and uniformly throughout the interior. Our wine storage cabinets are ideal for storing wines for long periods of time to allow them to mature to perfection. Depending on what temperature the appliances are set to, they can also be used for keeping white wine or red wine at exactly the right temperature for serving.



WKt 4552



The precision **electronic control system** is clearly arranged in the insulation plate. The digital temperature display can be read from the outside of appliances with glass doors. The door and temperature alarm alerts the user to any irregularities, e.g. a door that has been left open. The child lock prevents any inadvertent changes to the control system.



LED

The **LED lighting in the wine cooling compartment** can be dimmed to give a pleasing ambient light inside the appliance. For ideal presentation of your best wines, the interior light with separate switch in appliances with glazed door.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical **aluminium handle, with integrated opening mechanism**, allows the door of the appliance to be opened conveniently with a minimum of effort.



The integrated **lock** is exceedingly sturdy and protects against unauthorised access. A lock accessory is available when models are placed next to each other.




The **bottle shelves, made of untreated wood** are variably height-adjustable to provide an optimum overview and a clear storage layout. The bottles can be stored in opposite directions to make full use of the capacity. The wooden shelves are designed to safely hold Bordeaux bottles. The **clip-on labelling system** provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.



Tip Open


Liebherr's touch opening door with **TipOpen technology** integrates perfectly into kitchens with a handle-free design. When gently touched, the glass door automatically opens by about 5 cm, ready for full opening. If the door is not opened further within three seconds (approx.), the **SoftSystem** closing mechanism automatically shuts it again.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the rear.



The fresh air supplied through the **FreshAir activated charcoal filter** and recirculating air cooling system ensures optimal air quality. This is crucially important for the maturing process and preservation of the wine. FreshAir charcoal filters are easily accessible from the front and are replaceable.



Wine storage cabinets GrandCru	WKt 6451 GrandCru A++ LED	WKt 5552 GrandCru A+ LED	WKt 5551 GrandCru A++ LED	WKes 4552 GrandCru A+ LED	WKt 4552 GrandCru A+ LED	WKt 4551 GrandCru A++ LED	UWKes 1752 GrandCru LED Telescopic Rails Built-in Under-worktop appliance	WKes 653 GrandCru A++ LED Smart Steel
Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	312	253	253	201	201	201	46	12
Total gross/net capacity	666/625 litre	573/525 litre	547/499 litre	478/435 litre	478/435 litre	456/413 litre	135/110 litre	56/38 litre
Energy efficiency class	<A++	<A+	<A++	<A+	<A+	<A++	<A+	<A++
Energy consumption year / 24 hrs <sup>2</sup>	118/0.323 kWh	140/0.382 kWh	111/0.302 kWh	133/0.364 kWh	133/0.364 kWh	106/0.288 kWh	145/0.396 kWh	75/0.205 kWh
Noise output	41 dB(A)	41 dB(A)	39 dB(A)	41 dB(A)	41 dB(A)	39 dB(A)	38 dB(A)	40 dB(A)
Climate rating <sup>3</sup>	SN-T	SN-ST	SN-T	SN-ST	SN-ST	SN-T	SN-ST	SN
Voltage/Connection rating	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/0.8 A	220-240V~/1.0 A
Door	Full door, terra	Glass door, frame terra	Full door, terra	Glass door with stainless steel frame	Glass door, frame terra	Full door, terra	Glass door with stainless steel frame	Glass door with S/Steel frame/SmartSteel
Side walls	terra	terra	terra	stainless steel	terra	terra		stainless steel with SmartSteel
<b>Wine storage compartment</b>								
Temperature zones / -range	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C
Adjustable cooling circuits	1	1	1	1	1	1	1	1
Type of control / display	MagicEye/external digital	MagicEye/internal digital	MagicEye/internal digital	MagicEye/internal digital	MagicEye/internal digital	MagicEye/internal digital	MagicEye/internal digital	LCD Display/internal digital
Forced air system	•	•	•	•	•	•	•	•
Fresh air supply via FreshAir activ. charcoal filter	•	•	•	•	•	•	•	•
Humidity control via	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation	switchable ventilation
Interior light	LED	LED	LED	LED	LED	LED	LED	LED
permanently activated/dimmable	• / -	• / -	• / -	• / -	• / -	• / -	• / -	• / •
Shelf material	wooden shelf	wooden shelf	wooden shelf	wooden shelf	wooden shelf	wooden shelf	wooden shelf	wooden shelf
Storage shelves	7	7	7	6	6	6	4	3
running on telescopic rails							3	
Height-adjustable shelves	•	•	•	•	•	•	•	•
Fault: warning signal	visual and audible	visual and audible	visual and audible	visual and audible	visual and audible	visual and audible	visual and audible	visual and audible
Door open: warning signal	audible	audible	audible	audible	audible	audible	audible	audible
Child lock function	•	•	•	•	•	•	•	•
Drawers for accessories								1
<b>Dimensions</b>								
Exterior / Aperture dimensions in cm (h/w/d <sup>4</sup> )	193/74.7/75.9	192/70/74.2	192/70/74.2	165/70/74.2	165/70/74.2	165/70/74.2	82-87/60/at least 57.5	61.2/42.5/47.8
Interior dimensions in cm (w/d/h)	170/61.5/56	164/57.8/58.5	164/57.8/56	137/57.8/58.5	137/57.8/58.5	137/57.8/56		37/35/31
<b>Features</b>								
Design	SwingLine	HardLine	HardLine	HardLine	HardLine	HardLine		HardLine
Slimline door handle	Aluminium handle	Aluminium handle	Aluminium handle	Aluminium handle	Aluminium handle	Aluminium handle	Stainless steel slimline door handle	
with integrated opening mechanism	•	•	•	•	•	•		
Door hinges	right, reversible	right, reversible	right, reversible	right, reversible	right, reversible	right, reversible	right, reversible	right fixed
Replaceable door seal	•	•	•	•	•	•	•	•
Lock	•	•	•	•	•	•	•	•
<b>Accessories</b> (see page 46–47)	01, 06, 07	01, 03, 04, 06, 07	01, 03, 04, 06, 07	01, 03, 04, 06, 07, 09	01, 03, 04, 06, 07	01, 03, 04, 06, 07	01, 03, 06, 07, 09	01, 06, 08

<sup>1</sup> These models are only intended for storing wine  
Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> With +25°C ambient temperature, switched-off interior light and +12°C interior temperature.  
Commission Delegated Regulation (EU) No 1060/2010

<sup>3</sup> Climate Ratings: SN +10°C to +32°C N +16°C to +32°C  
ST +16°C to +38°C T +16°C to +43°C

<sup>4</sup> incl. distance from wall



The easy-glide accessories drawer can be used to store accessories directly below wine storage cabinets in the WKE 5 model range. This increases the 45 cm recess to 60 cm. Available in white glass (9792 449), black glass (9792 451) and stainless steel (9792 453).



**Built-in wine storage cabinets GrandCru**

	WKEgb 582 GrandCru	WKEgw 582 GrandCru	WKEes 553 GrandCru
Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	18	18	18
Total gross/net capacity	48/46 litre	48/46 litre	48/46 litre
Energy efficiency class	<A>	<A>	<A>
Energy consumption year / 24 hrs <sup>2</sup>	106/0.290 kWh	106/0.290 kWh	130/0.356 kWh
Noise output	34 dB(A)	34 dB(A)	32 dB(A)
Climate rating <sup>3</sup>	SN-ST	SN-ST	SN
Voltage/Connection rating	220-240V~/0.5 A	220-240V~/0.5 A	220-240V~/0.5 A
Door	black insulated glass door, handle and frame free	white insulated glass door, handle and frame free	Glass door with stainless steel frame
<b>Wine storage compartment</b>			
Temperature zones / -range	1 / +5°C to +20°C	1 / +5°C to +20°C	1 / +5°C to +20°C
Adjustable cooling circuits	1	1	1
Type of control / display	LCD Display / internal digital	LCD Display / internal digital	LCD Display / internal digital
Forced air system	•	•	•
Fresh air supply via FreshAir activ. charcoal filter	•	•	•
Humidity control via	switchable ventilation	switchable ventilation	switchable ventilation
Interior light	LED	LED	LED
permanently activated / dimmable	• / •	• / •	• / •
Shelf material	wooden shelf	wooden shelf	wooden shelf
Storage shelves	3	3	3
running on telescopic rails	2	2	2
Fault: warning signal	visual and audible	visual and audible	visual and audible
Door open: warning signal	audible	audible	audible
Child lock function	•	•	•
<b>Dimensions</b>			
Aperture dimensions in cm (h/w/d <sup>4</sup> )	45/56/at least 55	45/56/at least 55	45/56/at least 55
<b>Features</b>			
SoftSystem	•	•	
TipOpen Technology	•	•	
Drop down door / side opening door	• / -	• / -	- / •
Handle			recessed grip
Door hinges			right, reversible
Concealed hinge with restricted opening	•	•	
<b>Accessories</b> (see page 46-47)	01	01	01, 06, 09



	Humidor	ZKes 453 Humidor
Total gross/net capacity		43/39 litre
Energy efficiency class		
Energy consumption year / 24 hrs <sup>2</sup>		162/0.443 kWh
Noise output		40 dB(A)
Climate rating <sup>3</sup>		N
Voltage/Connection rating		220-240V~/0.5 A
Door		Glass door with S/Steel frame/SmartSteel
Side walls		stainless steel with SmartSteel
<b>Features</b>		
Temperature zones / -range		1 / +16°C to +20°C
Air humidity		68% to 75%
Adjustable cooling circuits		1
Type of control / display		LCD Display / internal digital
Forced air system		•
Fresh air supply via FreshAir activ. charcoal filter		•
Humidity control via		switchable ventilation
Interior light		LED
permanently activated / dimmable		• / •
Shelf material		Spanish cedar wood
Storage shelves		2
Fault: warning signal		visual and audible
Door open: warning signal		audible
Child lock function		•
Presentation boxes		2
Lock		•
Door hinges		right fixed
Wall mounting		possible
<b>Dimensions</b>		
Exterior dimensions in cm (h/w/d <sup>4</sup> )		61.2/42.5/47.8
Interior dimensions in cm (w/d/h)		34/30/27.4
<b>Accessories</b> (see page 46-47)		01, 08

<sup>1/2/3/4</sup> Notes see page 34/35

## Wine storage cabinets Vinothek

Wine storage cabinets offer similar conditions to a wine cellar. They are therefore an ideal choice for both long-term storage and storage of large wine stocks, always achieving the perfect serving temperature. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.



The precision **electronic control system** is located at the top of the cabinet housing. The digital temperature display can be read from the outside of appliances with glass doors. The door and temperature alarm alerts the user to any irregularities, e.g. a door that has been left open. The child lock prevents any inadvertent changes to the control system.



The appliances with glass doors feature an **interior light** which has a separate switch for

the ideal presentation of your best wines.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The **slimline door handle in black** is aesthetically pleasing and ergonomically designed for ease of opening.



The **untreated wooden storage shelves** are variably height-adjustable to provide an optimum overview and a clear storage layout. Storing the bottles in opposite directions on the pull-out shelves permits full use of the capacity. The wooden shelves are designed to safely hold Bordeaux bottles.



The **clip-on labelling system** provides a quick and clear overview of your wine store. The labelled

cards can be easily inserted into the clips which can be attached as required.



Environmental odours can have an impact on wine stored for longer periods. Fresh air is supplied to Liebherr wine cabinets through the easily replaceable **FreshAir activated charcoal filter** to ensure optimal air quality.



Wine storage cabinets Vinothek	WKb 4212 Vinothek	WKr 4211 Vinothek	WKb 3212 Vinothek	WKr 3211 Vinothek	WKb 1812 Vinothek	WKr 1811 Vinothek
Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>	200	200	164	164	66	66
Total gross/net capacity	427/395 litre	409/377 litre	336/309 litre	322/295 litre	145/134 litre	145/128 litre
Energy efficiency class	<A>	<A+>	<A>	<A+>	<A>	<A>
Energy consumption year / 24 hrs <sup>2</sup>	168/0.458 kWh	103/0.282 kWh	161/0.441 kWh	99/0.269 kWh	113/0.307 kWh	113/0.308 kWh
Noise output	41 dB(A)	39 dB(A)	39 dB(A)	39 dB(A)	38 dB(A)	38 dB(A)
Climate rating <sup>3</sup>	SN-ST	SN-T	SN-ST	SN-T	SN-ST	SN-T
Voltage/Connection rating	220-240V~/1.0 A	220-240V~/1.0 A	220-240V~/0.8 A	220-240V~/0.8 A	220-240V~/0.5 A	220-240V~/0.5 A
Door	Glass door, frame black	Full door, burgundy	Glass door, frame black	Full door, burgundy	Glass door, frame black	Full door, burgundy
Side walls	black	black	black	black	black	black
<b>Wine storage compartment</b>						
Temperature zones / -range	1 / +5°C to +20°C					
Adjustable cooling circuits	1	1	1	1	1	1
Type of control / display	MagicEye / external digital					
Forced air system	•	•	•	•	•	•
Fresh air supply via FreshAir activ. charcoal filter	•	•	•	•	•	•
Humidity control via	switchable ventilation					
Interior light	•	•	•	•	•	•
permanently activated / dimmable	• / -	• / -	• / -	• / -	• / -	• / -
Shelf material	wooden shelf	wooden shelf	wooden shelf	wooden shelf	zincd rails	zincd rails
Storage shelves	6	6	4	4	3	3
Height-adjustable shelves	•	•	•	•	•	•
Fault: warning signal	visual and audible					
Door open: warning signal	audible	audible	audible	audible	audible	audible
Child lock function	•	•	•	•	•	•
<b>Dimensions</b>						
Exterior dimensions in cm (h/w/d <sup>4</sup> )	165/60/73.9	165/60/73.9	135/60/73.9	135/60/73.9	89/60/61.3	89/60/61.3
Interior dimensions in cm (w/d/h)	146.6/50/56	146.6/50/56	116.6/50/56	116.6/50/56	71/50/44	71/50/44
<b>Features</b>						
Design	HardLine	HardLine	HardLine	HardLine	HardLine	HardLine
Slimline door handle	Slimline door handle black					
Door hinges	right, reversible					
Replaceable door seal	•	•	•	•	•	•
<b>Accessories</b> (see page 46–47)	01, 03, 06, 10	01, 03, 06, 10	01, 03, 06, 10	01, 03, 06, 10	01, 05, 06, 10	01, 05, 06, 10

<sup>1</sup> These models are only intended for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm)

<sup>2</sup> With +25°C ambient temperature, switched-off interior light and +12°C interior temperature. Commission Delegated Regulation (EU) No 1060/2010

<sup>3</sup> Climate Ratings: SN +10°C to +32°C N +16°C to +32°C  
ST +16°C to +38°C T +16°C to +43°C

<sup>4</sup> incl. distance from wall

# Multi-temperature wine cabinets Vinothek

Multi-temperature wine cabinets are especially suited for storing different types of wine at their respective drinking temperatures. These appliances incorporate a special climate control system that can layer the temperatures. In the upper zone, for example, red wine can be kept at +18°C while the lower zone, set at an ambient temperature of +5°C, will be particularly suitable for sparkling wine or champagne.



The wine cabinets are equipped with an accurate **electronic control system** with digital temperature display. These appliances incorporate a special climate control system that can layer the temperatures. In the upper zone, for example, red wine can be kept at +16°C to +18°C while the lower zone is set at an ambient temperature of +5°C to +7°C.



**Ideal humidity via Lava stone.** The humidity in the Vinothek models can be increased by using Lava stone.



## Multi-temperature wine cabinets Vinothek

Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>
Total gross/net capacity
Energy efficiency class
Energy consumption year/24 hrs <sup>2</sup>
Noise output
Climate rating <sup>3</sup>
Voltage/Connection rating
Door
Side walls

### Wine storage compartment

Temperature range
Adjustable cooling circuits
Type of control/display
Fresh air supply via FreshAir activ. charcoal filter
Humidity control via
Interior light
Shelf material
Storage shelves
Height-adjustable shelves
Fault: warning signal
Door open: warning signal
Child lock function

### Dimensions

Exterior dimensions in cm (h/w/d <sup>4</sup> )
Interior dimensions in cm (w/d/h)

### Features

Design
Slimline door handle
Door hinges
Replaceable door seal

### Accessories (see page 46–47)

## WTb 4212 Vinothek

200
427/395 litre
<A>
168/0.460 kWh
41 dB(A)
SN-ST
220-240V~/1.0 A
Glass door, frame black
black

+5°C to +18°C

1
MagicEye/external digital
•
Lava stone
•
• / –
wooden shelf
6
•
visual and audible
audible
•

165/60/73.9
146.6/50/56

HardLine
Slimline door handle black
right, reversible
•

01, 02, 03, 06, 10

## WTr 4211 Vinothek

200
409/377 litre
<A>
167/0.457 kWh
40 dB(A)
SN-ST
220-240V~/1.0 A
Full door, burgundy
black

+5°C to +18°C

1
MagicEye/external digital
•
Lava stone
•
• / –
wooden shelf
6
•
visual and audible
audible
•

165/60/73.9
146.6/50/56

HardLine
Slimline door handle black
right, reversible
•

01, 02, 03, 06, 10

## Optional Accessories

When ordering accessories, please ensure that you quote not only the order numbers shown below, but also the full appliance name/service number.

### 01 FreshAir active carbon filter

Odours from the surrounding air can impair the quality of wine. Liebherr wine cabinets are fitted with easy-to-replace FreshAir activated charcoal filters to ensure clean air, filter out odours and safeguard the quality of the wine.

WTes 1672; UWKes 1752; UWTes 1672, UWT 1682; WKEgb/gw 582, EWTdf/gw/gb	9881 289	WKes 653; ZKes 453	9881 287
		All other free-standing and built-in wine appliances	9881 291



### 02 Retrofit lava stone kit

The humidity in the Vinothek multi-temperature wine cabinets can be increased as required using lava stones.

WTb 4212; WTr 4211	9591 517
--------------------	----------



### 03 Wooden shelf

The handcrafted shelf, made from natural wood, is the perfect accessory for safely storing Bordeaux bottles. Positioning the bottles in opposite directions enables full use of the shelf's capacity.

UWKes 1752	7113 625	WKr 4211, 3211; WKb 4212, 3212; WTb 4212; WTr 4211	9881 263
WKT 5551, 5552, 4551, 4552; WKes 4552	9881 261		



### 04 Presentation shelf (wooden folding shelf)

The shelf can be used to present exquisite wines, or to safely store already-opened bottles.

WTes 5872, 5972	7112 043	WKT 5551, 5552, 4551, 4552; WKes 4552	7113 619
-----------------	----------	---------------------------------------	----------



### 05 Galvanised grill shelf

Grill shelf for additional requirements.

WKb 1812, WKr 1811	7112 035
--------------------	----------



### 06 Clip-on labelling system

The clip-on labelling system provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.

Clip-on labelling for grill shelves WKb/r 18 (2 pieces)	9086 723		
Clip-on labelling for wooden shelves EWT (2 pieces)	7420 248	For all other wooden shelves (5 pieces)	9094 559



### 07 Bottle holder

The practical bottle holder allows you to store even more bottles.

UWKes 1752, 1762; UKes 1752, 1762; WKes 4552; WKT 4551, 4552, 5551, 5552, 6451	7436 193
-----------------------------------------------------------------------------------	----------



### 08 Underside cover for wall mounting

Covers the underside, enabling compact appliances to be attractively wall mounted without their underside being visible.

WKes 653; ZKes 453	9590 519
--------------------	----------



### 09 Stainless steel polish

For polishing stainless steel surfaces after they have been cleaned (do not use on SmartSteel).

250 ml	8409 030
--------	----------



### 10 Lock

The lock prevents unwanted access. Simply assemble on the housing with Vinothek wine cabinets. If two wine cabinets are set up Side-by-Side, the operation of the sideways lock is limited. In this case an additional lock can be fitted below.

Vinothek wine appliances	9094 443
--------------------------	----------



### 11 Stainless steel frame with handle

The high-quality, easy-to-fit optional stainless steel accessory frame kit enables the model's integration into any kitchen. The robust stainless steel handle is easy to attach and makes opening of the door effortless. The stainless steel frame comes with pre-drilled holes for the stainless steel handle.

EWTdf 3553	9901 573		
EWTdf 2353	9901 575	EWTdf 1653	9901 577



### Mounting bracket accessory kit

Side-by-Side fitting kit	UWT; UWK	9901 647
--------------------------	----------	----------