

## Our catalogues

Find out everything you need to know about Liebherr appliances in the latest catalogues. Available in printed format from retailers or as a PDF download from [home.liebherr.com](http://home.liebherr.com)



## Smart communication on all fronts



### BioFresh App

Useful information about perfect food storage, as well as vitamin and mineral content.



### WineGuide App

A brief overview of Bordeaux wines and their producers, plus storage information.



### IceCrusher App

Playful fun! With just a tap, ice-cubes tumble down your screen and can be moved and crushed.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.  
[apps.home.liebherr.com](http://apps.home.liebherr.com)



Discover the world of Liebherr Appliances with the latest interesting news, stories, valuable tips and tricks on food storage, recipes and lots more besides!




Click the link to directly access our social media channels: [socialmedia.home.liebherr.com](http://socialmedia.home.liebherr.com)

Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle.



Subject to modification. Current data see [home.liebherr.com](http://home.liebherr.com).  
Printed in Germany by rati media group. 793226-13/06/18





EWTgw 2383



## Fully developed for the enjoyment of wine

Where wine is concerned, correct temperatures are always important. From the air temperature which ensures perfect growth of the grapes, to that which governs the aging processes in production, to the balanced temperature for storage of the finished wine. Above all, temperature ultimately defines a wine's taste and palate – the serving temperature will determine how much it is savoured and enjoyed.




Scan the code with your Smartphone  
to find out more about wine.  
[wine.liebherr.com](http://wine.liebherr.com)



# Content

|                                |    |
|--------------------------------|----|
| Ideal storage temperature      | 06 |
| Optimum air quality            | 08 |
| Best position for fine wines   | 10 |
| Protection against UV light    | 12 |
| The Vinidor range              | 16 |
| Wine storage cabinets GrandCru | 32 |
| Humidor                        | 39 |
| Wine storage cabinets Vinothek | 40 |
| Multi-temperature Vinothek     | 46 |
| Accessories                    | 48 |



## Extremely low energy consumption

Liebherr has always been committed to energy efficiency, which plays a key role from the design stage onward.

Precision electronic controllers combined with optimised refrigeration components, highly insulating materials and very efficient compressors ensure that our appliances provide excellent energy efficiency.

Once again, Liebherr is leading the way with its current range of refrigerators and freezers, offering an attractive selection of appliances in energy efficiency classes A+ to A+++/20%.

# The ideal storage temperature for wine

The ideal long term storage temperature for wine is between + 10 °C and + 12 °C. It is critical that the temperature is kept as constant as possible because this is the only way that a wine's natural harmony will be preserved.

As the temperature rises, the wine molecules kinetic energy increases and this accelerates the aging process causing the wine to deteriorate. Consequently, storage temperatures of between +10°C and +12°C are recommended for storing wine over prolonged periods. Maintaining a constant temperature is most important, as fluctuations during storage will impair the quality of the wine. Furthermore, the temperature at which a wine is consumed also plays a crucial role in how it tastes. Red wines should be served at a warmer temperature than white wines because they contain more tannins (polyphenols).

Tannins react with oxygen more quickly at higher temperatures. This is what happens in the process of allowing a wine to breathe, when the full aroma and taste are only achieved once the wine has combined with oxygen. The length of time for which a wine should breathe depends on its variety and quality. Barolo, Rioja, Burgundy and Bordeaux each take a different amount of time to develop. In general, the longer a wine matured in the barrel, the more likely it is to need a longer breathing time for full enjoyment.

## Perfect storage and temperature control with Liebherr

**Electronic control system.** Liebherr's highly precise electronic control systems and advanced air conditioning technologies guarantee appliances maintain a constant interior temperature, even in the event of major fluctuations in the ambient temperature.

**Long-term storage.** With constant temperatures and a perfectly controlled climate, Liebherr's wine storage cabinets and Vinidor models provide the very best conditions for wine to age without disturbance, and to develop fully during storage.

**Optimum drinking temperature.** In our Vinidor wine cabinets, which offer two or three wine safes, different wines can be stored according to their ideal serving temperature. Each wine safe can be independently programmed to between +5°C and +20°C, giving great storage flexibility.

In the multi-temperature wine cabinets in our Vinothek range, specialised climate technology is used to achieve temperature stratification within the appliance. Lower temperatures in the bottom section are ideal for sparkling wines and champagne, whereas a temperature of about +18°C in the upper section is perfect for red wines. Meanwhile, the temperature in the middle section brings white wines to an ideal serving temperature.



# Optimum air quality

The quality of the ambient air is essential if the wine is to develop fully and be enhanced during storage – any airborne contaminants can be transferred to the wine and spoil it.

Classic natural corks very adequately keep the wine in the bottle, but in no way do they hermetically seal it. As a result, air, which is rarely completely odourless, infiltrates the bottle passing down the edges of the cork. If the bottles are stored in a cardboard box, the wine can take on the odour of the cardboard. But food odours in particular present problems. When storing wine at home, especially in a kitchen

environment, wines will almost certainly lose their »terroir and type« characteristics – i.e. they will spoil! Although glass stoppers and screw caps provide airtight closures for bottles, wines inevitably age more slowly because only the oxygen in the bottle is available to them. Synthetic corks allow too much air into the bottle, making them much less suitable for long-term storage of wine altogether.

## Optimum air quality with Liebherr

**Optimum air-freshness.** All Liebherr wine cabinets are fitted with FreshAir activated-charcoal filters, which ensure optimum air quality within the appliance. The active-charcoal reacts with any contaminants, binding them to its surface, and thereby filtering them from the incoming-air. In the Vinidor appliances, each individual wine zone has a FreshAir activated charcoal filter. Only the Vinidor appliances UWT 1682 (TipOpen under-worktop appliance), UWTes 1672 (under-worktop appliance) and WTes 1672 (table height, under-worktop) have one FreshAir activated charcoal filter in the divider to filter both zones. This prevents odours from the ambient air affecting the taste of the wines stored in the interior. Filters should ideally be replaced once a year. They can be ordered as an accessory and are easy to replace.

**Ideal humidity.** If wines are to be stored for prolonged periods, the correct humidity is essential. At humidity levels below 50%, even the best natural corks start to shrink. This allows more and more oxygen to penetrate the bottle, and evaporation to occur; and, as the fill level drops, oxidation increases. Wines become gradually sweeter until they spoil completely. However, with humidity levels of at least 50%, Liebherr wine cabinets ensure the best conditions for both corks and wine. Thanks to an impressive vaporiser system and specially regulated air circulation, high humidity levels are sustained in all wine storage cabinets.

Our Vinothek multi-temperature wine cabinets, with graduated temperature zones, are fitted with porous lava stone, which controls humidity within these appliances.



# Best environment for fine wines

For perfect storage the wine should not be disturbed.

Even small vibrations caused by the noise of machinery, road traffic or frequent footfall can harm old wines. The wine is imperceptibly »shaken up«, and the sediment is disturbed. This leads to increased reactions between the different components of the wine, which then creates undesirable compounds that leave the wine tasting odd and

inharmonious – something like what is seen straight after the filling process. Wine bottles are usually stored lying down so that their corks are constantly moistened and cannot dry out. On the other hand, bottles with screw caps or glass stoppers can be stored upright without any problem as they provide an airtight seal for the wine.

## Optimum storage with Liebherr

**Protection against vibration.** The specially developed, low-vibration compressors used in Liebherr wine cabinets provide gentle storage conditions. In the new Vinidor wine cabinets, the entire refrigeration system is fully vibration damped to minimise vibration transmission. Accordingly, appliances make very little operating noise, and the wine can be stored with minimal disturbance.

**Optimum position.** Wine is able to age in peace on stable, handcrafted wooden shelves. These shelves are unvarnished so that varnish vapours do not damage the wine. The wooden shelves are ideal for safely storing Bordeaux bottles, and positioning the wine bottles in opposite directions on the shelves allows optimum use of the appliance's capacity. In the Vinidor appliances, the wooden shelves are fitted to telescopic rails to provide a clear overview of the bottles, and to ensure easy access – even to those at the back. The presentation shelf is ideal for showcasing fine wines and also maintains opened bottles at a perfect temperature.

**Soft closing.** The door closes softly automatically from an opening angle of about 45° (freestanding wine cabinets) and 30° (integrated wine cabinets) to prevent any vibrations that could damage the wine.



# Protection against ultraviolet light

Most wine bottles are tinted as ultraviolet rays pose a danger to all wines.

Light, in particular the invisible rays from the ultraviolet spectrum, is a common cause of undesirable chemical reactions in wines. The consequences of light-damage are visible to the eye: pale red wines, and white wines that take on a golden-yellow colour. »Light-strike« (or »Goût de Lumière« as the French know it) destroys the wine's balance and flattens its aroma and, to avoid it, most producers

bottle their wine in brown or green glass, which absorbs a great deal of the UV rays. However, this alone is not enough for bottles that are not stored in the dark. Slight temperature increases caused by light radiation can also damage the wine – they make it age quicker thereby altering the natural development processes, even to the extent that the wine can be permanently destroyed.

## UV protection with Liebherr

**Insulated glass doors with UV protection.** To minimise the effects of UV rays, Liebherr wine cabinets are fitted with special UV-resistant insulation glass. The UV protection is provided by a special dual-pane structure, which incorporates an inner, tinted-glass pane and an outer, metallised, low-E (low-emittance) pane. This glass composite reflects nearly all the damaging UV radiation and prevents any deterioration of the wine.

**LED lighting concept.** This innovative technology ensures that the interior of the appliance is evenly lit without any UV radiation, as the LED light spectrum does not contain any UV rays. Furthermore, because of minimal heat generation with LEDs, the wines can be illuminated and beautifully presented permanently without any localised heating of the bottles.





The perfect range for wine aficionados

## Vinidor range

The Vinidor range offers ultimate flexibility and combines the advantages of both wine storage cabinets and multi-temperature wine cabinets in a single appliance. Appliances in the range come with either two or three temperature zones, which can be set independently to the required temperature between +5°C and +20°C. Accordingly, an appliance with three temperature zones can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature. Vinidor appliances also offer the perfect climate for long-term wine storage. The varying sizes of the temperature zones, together with the fully adjustable temperature controls, make these appliances suitable for just about any collection of wines.




## Wine storage cabinets

Wine storage cabinets offer similar conditions to a wine cellar. They are therefore an ideal choice for both long-term storage and storage of large wine stocks, always achieving the perfect serving temperature. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.



## Multi-temperature wine cabinets

Multi-temperature wine cabinets from the Vinothek range offer versatile storage for different types of wine, each at its perfect drinking temperature. The innovative climate technology that we use creates temperature graduation within the appliance. As a result red wine can be stored in the upper section at +18°C; in the lower section a temperature of +5°C is ideal for storing sparkling wine or champagne; and in the middle section the temperature is perfect for white wine.



## Vinidor range

The Vinidor range offers ultimate flexibility and combines the advantages of both wine storage cabinets and multi-temperature wine cabinets in a single appliance. Appliances in the range come with either two or three wine zones, which can be set independently to the required temperature between +5°C and +20°C. Accordingly, an appliance with three wine zones can simultaneously store red wine, white wine, and champagne all at their optimum serving temperature. Vinidor appliances also offer the perfect climate for long-term wine storage. The varying sizes of the wine zones, together with the fully adjustable temperature controls, make these appliances suitable for just about any collection of wines. The spring-loaded door seal helps maintain precise independent temperature control in each climate zone.



WTes 5872

# Quality in every detail



The electronic LC-Display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



The **LED lighting in the individual wine compartments** can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with this innovative, no-heat LED lighting concept. The LED lighting can also be adjusted to operate continuously or in conjunction with door openings.



The practical **presentation shelf** of the Vinidor models fulfils both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the cabinet.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical **aluminium door handle, with integrated opening mechanism**, allows the door of the appliance to be opened conveniently with a minimum of effort.



The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. Storing the bottles in opposite directions permits full use of the capacity. The **clip-on labelling system** provides a quick and clear overview of your wine store.



The **handle-free glazed door with TipOpen technology** guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines.



The **Side-by-Side concept** makes it possible to position fridges, freezers and wine cabinets to meet your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations.

The features shown are model dependent; the description applies to the relevant model.



| Vinidor range  | WTes 5872 Vinidor                      | WTes 5972 Vinidor                      | WTpes 5972 Vinidor                    |
|--|--|--|---------------------------------------|
|  | LED<br>Soft System<br>Telescopic Rails | LED<br>Soft System<br>Telescopic Rails | LED<br>Telescopic Rails               |
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 178                                    | 211                                    | 155                                   |
| Total gross/net capacity                             | 578/496 litre                          | 593/516 litre                          | 593/516 litre                         |
| Energy efficiency class                              | ≤ A <sup>5</sup>                       | ≤ A <sup>5</sup>                       | ≤ A <sup>5</sup>                      |
| Energy consumption year/24 hrs <sup>2</sup>          | 180/0.493 kWh <sup>5</sup>             | 182/0.498 kWh <sup>5</sup>             | 182/0.498 kWh <sup>5</sup>            |
| Noise output   | 38 dB(A)                               | 38 dB(A)                               | 38 dB(A)                              |
| Climate rating <sup>3</sup>                          | SN-ST (+10°C to +38°C)                 | SN-ST (+10°C to +38°C)                 | SN-ST (+10°C to +38°C)                |
| Voltage/Connection rating                            | 220-240V~/1.0 A                        | 220-240V~/1.0 A                        | 220-240V~/1.0 A                       |
| Door   | Glass door with stainless steel frame  | Glass door with stainless steel frame  | Glass door with stainless steel frame |
| Side walls   | stainless steel                        | stainless steel                        | stainless steel                       |
| <b>Wine storage compartment</b>                      |  |  |                                       |
| Temperature zones/-range                             | 3/+5°C to +20°C                        | 2/+5°C to +20°C                        | 2/+5°C to +20°C                       |
| Adjustable cooling circuits                          | 3                                      | 2                                      | 2                                     |
| Type of control/display                              | LCD Display/internal digital           | LCD Display/internal digital           | LCD Display/internal digital          |
| Forced air system                                    | •                                      | •                                      | •                                     |
| Fresh air supply via FreshAir activ. charcoal filter | •                                      | •                                      | •                                     |
| Humidity control via                                 | switchable ventilation                 | switchable ventilation                 | switchable ventilation                |
| Interior light                                       | LED                                    | LED                                    | LED                                   |
| permanently activated/dimmable                       | • / •                                  | • / •                                  | • / •                                 |
| Shelf material                                       | wooden shelf                           | wooden shelf                           | wooden shelf                          |
| Storage shelves                                      | 13                                     | 10                                     | 6                                     |
| running on telescopic rails                          |  |  |                                       |
| Presentation shelf                                   | 10                                     | 8                                      | 5                                     |
| Pull-out shelf for upright bottles                   | 1                                      | 1                                      | 2                                     |
| Fault: warning signal                                | visual and audible                     | visual and audible                     | visual and audible                    |
| Door open: warning signal                            | audible                                | audible                                | audible                               |
| Child lock function                                  | •                                      | •                                      | •                                     |
| <b>Dimensions</b>                                    |  |  |                                       |
| Exterior dimensions in cm (h/w/d <sup>4</sup> )      | 192/70/74.2 <sup>5</sup>               | 192/70/74.2 <sup>5</sup>               | 192/70/74.2 <sup>5</sup>              |
| Interior dimensions in cm (h/w/d)                    | 169.5/56/52                            | 169.5/56/52                            | 169.5/56/52                           |
| <b>Features</b>                                      |  |  |                                       |
| Design   | HardLine                               | HardLine                               | HardLine                              |
| SoftSystem   | •                                      | •                                      |                                       |
| Slimline door handle                                 | Aluminium handle                       | Aluminium handle                       | Stainless steel slimline door handle  |
| with integrated opening mechanism                    | •                                      | •                                      |                                       |
| Door hinges  | right, reversible                      | right, reversible                      | right, reversible                     |
| Replaceable door seal                                | •                                      | •                                      | •                                     |
| Concealed hinge with restricted opening              | •                                      | •                                      |                                       |
| Lock   | •                                      | •                                      | •                                     |
| <b>Accessories (see page 48–51)</b>                  | 01, 02, 05, 07, 10, 11                 | 01, 02, 05, 07, 10, 11                 | 01, 02, 07, 10, 11                    |



The **LED lighting** in the wine cooling compartments can be dimmed to give a pleasing ambient light inside the appliance. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The electronic LCD display is an innovative design feature. Clear menu navigation and a **Touch-electronic control system** provides yet more information for tailored storage conditions. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.

#### Vinidor range

#### WTes 1672 Vinidor

|  |                                       |
|--|---------------------------------------|
| <b>LED</b>   | 34                                    |
| <b>Telescopic Rails</b>                              | 123/95 litre                          |
| <b>A</b>   | <A                                    |
|  | 137/0.375 kWh                         |
|  | 38 dB(A)                              |
|  | SN-ST (+10°C to +38°C)                |
|  | 220-240V~/0.8 A                       |
|  | Glass door with stainless steel frame |
|  | stainless steel                       |
| <b>Wine storage compartment</b>                      |                                       |
| Temperature zones / -range                           | 2/+5°C to +20°C                       |
| Adjustable cooling circuits                          | 2                                     |
| Type of control/display                              | MagicEye/internal digital             |
| Forced air system                                    | •                                     |
| Fresh air supply via FreshAir activ. charcoal filter | •                                     |
| Humidity control via                                 | switchable ventilation                |
| Interior light                                       | LED                                   |
|  | permanently activated/dimmable        |
| Shelf material                                       | wooden shelf                          |
| Storage shelves                                      | 5                                     |
|  | running on telescopic rails           |
| Fault: warning signal                                | 3                                     |
| Door open: warning signal                            | visual and audible                    |
| Child lock function                                  | audible                               |
| <b>Dimensions</b>                                    |                                       |
| Exterior dimensions in cm (h/w/d <sup>4</sup> )      | 82.2/59.8/57.8                        |
| Interior dimensions in cm (h/w/d)                    | 55/51/44                              |
| <b>Features</b>                                      |                                       |
| Design   | HardLine                              |
| Slimline door handle                                 | Aluminium handle                      |
| Door hinges  | right, reversible                     |
| Replaceable door seal                                | •                                     |
| Lock   | •                                     |
| <b>Accessories (see page 48–51)</b>                  | 01, 02, 07, 10, 11, 14                |



EWTgb 3583



The built-in wine cabinets EWTdf can be fitted with **individual panels** for perfect integration into the kitchen. The inner **profile frame made of aluminium** ensures a clean transition between the panel and insulating glass. Whether the panel is made of wood, metal or stone - the profile frame retouches unclean edges and cutting surfaces and perfectly accentuates each wine selection.



Liebherr's touch opening door with **TipOpen technology** integrates perfectly into kitchens with a handle-free design. The double-glazed door opens 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will activate and gently and quietly close the door again.

| Vinidor range  | EWTgw 3583 Vinidor                                |          |             |                  | EWTgb 3583 Vinidor |   |          |             | EWTdf 3553 Vinidor |          |   |             |                  |          |
|--|---|----------|-------------|------------------|--------------------|---|----------|-------------|--------------------|----------|---|-------------|------------------|----------|
|  | LED   | Tip Open | Soft System | Telescopic Rails | Built-in           | LED   | Tip Open | Soft System | Telescopic Rails   | Built-in | LED   | Soft System | Telescopic Rails | Built-in |
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 83  |          |             |                  | 178                | 83  |          |             |                    | 178      | 80  |             |                  |          |
| Total gross/net capacity                             | 307/271 litre                                     |          |             |                  |                    | 307/271 litre                                     |          |             |                    |          | 289/254 litre   |             |                  |          |
| Energy efficiency class                              | A   |          |             |                  |                    | A   |          |             |                    |          | A   |             |                  |          |
| Energy consumption year/24 hrs <sup>2</sup>          | 162/0.442 kWh                                     |          |             |                  |                    | 162/0.442 kWh                                     |          |             |                    |          | 162/0.443 kWh   |             |                  |          |
| Noise output   | 34 dB(A)  |          |             |                  |                    | 34 dB(A)  |          |             |                    |          | 34 dB(A)  |             |                  |          |
| Climate rating <sup>3</sup>                          | SN (+10°C to +32°C)                               |          |             |                  |                    | SN (+10°C to +32°C)                               |          |             |                    |          | SN-ST (+10°C to +38°C)  |             |                  |          |
| Voltage/Connection rating                            | 220-240V~/1.0 A                                   |          |             |                  |                    | 220-240V~/1.0 A                                   |          |             |                    |          | 220-240V~/1.0 A   |             |                  |          |
| Door   | white insulated glass door, handle and frame free |          |             |                  |                    | black insulated glass door, handle and frame free |          |             |                    |          | Insulated glass door prepared for cabinet door or stainless steel front |             |                  |          |
| <b>Wine storage compartment</b>                      |   |          |             |                  |                    |   |          |             |                    |          |   |             |                  |          |
| Temperature zones/-range                             | 2/+5°C to +20°C                                   |          |             |                  |                    | 2/+5°C to +20°C                                   |          |             |                    |          | 2/+5°C to +20°C   |             |                  |          |
| Adjustable cooling circuits                          | 2   |          |             |                  |                    | 2   |          |             |                    |          | 2   |             |                  |          |
| Type of control/display                              | LCD Display/internal digital                      |          |             |                  |                    | LCD Display/internal digital                      |          |             |                    |          | LCD Display/internal digital  |             |                  |          |
| Forced air system                                    | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| Fresh air supply via FreshAir activ. charcoal filter | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| Humidity control via                                 | switchable ventilation                            |          |             |                  |                    | switchable ventilation                            |          |             |                    |          | switchable ventilation  |             |                  |          |
| Interior light                                       | LED   |          |             |                  |                    | LED   |          |             |                    |          | LED   |             |                  |          |
| permanently activated/dimmable                       | • / •   |          |             |                  |                    | • / •   |          |             |                    |          | • / •   |             |                  |          |
| Shelf material                                       | wooden shelf                                      |          |             |                  |                    | wooden shelf                                      |          |             |                    |          | wooden shelf  |             |                  |          |
| Storage shelves                                      | 10  |          |             |                  |                    | 10  |          |             |                    |          | 10  |             |                  |          |
| running on telescopic rails                          | 8   |          |             |                  |                    | 8   |          |             |                    |          | 8   |             |                  |          |
| Presentation shelf                                   | 1   |          |             |                  |                    | 1   |          |             |                    |          | 1   |             |                  |          |
| Fault: warning signal                                | visual and audible                                |          |             |                  |                    | visual and audible                                |          |             |                    |          | visual and audible  |             |                  |          |
| Door open: warning signal                            | audible   |          |             |                  |                    | audible   |          |             |                    |          | audible   |             |                  |          |
| Child lock function                                  | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| <b>Dimensions</b>                                    |   |          |             |                  |                    |   |          |             |                    |          |   |             |                  |          |
| Aperture dimensions in cm (h/w/d <sup>4</sup> )      | 178/56/at least 55                                |          |             |                  |                    | 178/56/at least 55                                |          |             |                    |          | 178/56/at least 55  |             |                  |          |
| Interior dimensions in cm (h/w/d)                    | 159.9/46.4/39.3                                   |          |             |                  |                    | 159.9/46.4/39.3                                   |          |             |                    |          | 159.9/46.4/39.3   |             |                  |          |
| <b>Features</b>                                      |   |          |             |                  |                    |   |          |             |                    |          |   |             |                  |          |
| SoftSystem   | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| TipOpen Technology                                   | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| Door hinges  | right, reversible                                 |          |             |                  |                    | right, reversible                                 |          |             |                    |          | right, reversible   |             |                  |          |
| Concealed hinge with restricted opening              | •   |          |             |                  |                    | •   |          |             |                    |          | •   |             |                  |          |
| <b>Accessories</b> (see page 48–51)                  | 01, 02, 07  |          |             |                  |                    | 01, 02, 07  |          |             |                    |          | 01, 02, 07, 13, 15, 16  |             |                  |          |



EWTgw 2383

**Silent**



The **silent appliance** EWTgb 2383 is extremely quiet due to its design and low-noise components. Currently, it is among the quietest in its product group.



The practical **presentation shelf** of the Vinidor models fulfils both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.

| Vinidor range  | EWTgw 2383 Vinidor                                | EWTgb 2383 Vinidor                                | EWTdf 2353 Vinidor  |
|--|---|---|---|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 51  | 51  | 48  |
| Total gross/net capacity                             | 195/169 litre                                     | 195/169 litre                                     | 183/158 litre   |
| Energy efficiency class                              | ≤A  | ≤A  | ≤A  |
| Energy consumption year/24 hrs <sup>2</sup>          | 152/0.414 kWh                                     | 152/0.414 kWh                                     | 152/0.416 kWh   |
| Noise output   | 34 dB(A)  | 32 dB(A) Silent                                   | 34 dB(A)  |
| Climate rating <sup>3</sup>                          | SN (+10°C to +32°C)                               | SN (+10°C to +32°C)                               | SN-ST (+10°C to +38°C)  |
| Voltage/Connection rating                            | 220-240V~/1.0 A                                   | 220-240V~/1.0 A                                   | 220-240V~/1.0 A   |
| Door   | white insulated glass door, handle and frame free | black insulated glass door, handle and frame free | Insulated glass door prepared for cabinet door or stainless steel front |
| <b>Wine storage compartment</b>                      |   |   |   |
| Temperature zones/-range                             | 2/+5°C to +20°C                                   | 2/+5°C to +20°C                                   | 2/+5°C to +20°C   |
| Adjustable cooling circuits                          | 2   | 2   | 2   |
| Type of control/display                              | LCD Display/internal digital                      | LCD Display/internal digital                      | LCD Display/internal digital  |
| Forced air system                                    | •   | •   | •   |
| Fresh air supply via FreshAir activ. charcoal filter | •   | •   | •   |
| Humidity control via                                 | switchable ventilation                            | switchable ventilation                            | switchable ventilation  |
| Interior light                                       | LED   | LED   | LED   |
| permanently activated/dimmable                       | • / •   | • / •   | • / •   |
| Shelf material                                       | wooden shelf                                      | wooden shelf                                      | wooden shelf  |
| Storage shelves                                      | 6   | 6   | 6   |
| running on telescopic rails                          | 4   | 4   | 4   |
| Presentation shelf                                   | 1   | 1   | 1   |
| Fault: warning signal                                | visual and audible                                | visual and audible                                | visual and audible  |
| Door open: warning signal                            | audible   | audible   | audible   |
| Child lock function                                  | •   | •   | •   |
| <b>Dimensions</b>                                    |   |   |   |
| Aperture dimensions in cm (h/w/d <sup>4</sup> )      | 122/56/at least 55                                | 122/56/at least 55                                | 122/56/at least 55  |
| Interior dimensions in cm (h/w/d)                    | 104.7/46.4/39.3                                   | 104.7/46.4/39.3                                   | 104.7/46.4/39.3   |
| <b>Features</b>                                      |   |   |   |
| SoftSystem   | •   | •   | •   |
| TipOpen Technology                                   | •   | •   | •   |
| Door hinges  | right, reversible                                 | right, reversible                                 | right, reversible   |
| Concealed hinge with restricted opening              | •   | •   | •   |
| <b>Accessories</b> (see page 48–51)                  | 01, 02, 07  | 01, 02, 07  | 01, 02, 07, 13, 15, 16  |
|  |   |   |   |
|  |   |   |   |
|  |   |   |   |
|  |   |   |   |
|  |   |   |   |

<sup>1/2/3/4</sup> Notes see pages 36–37  
You can find the full range of efficiency classes at page 5. According to (EU) 2017/1369 6a.



EWTdf 1653

#### **Stainless steel frame with handle**

Further information see Optional Accessories page 51.

| Vinidor range  | EWTgw 1683  | Vinidor   | EWTgb 1683  | Vinidor   | EWTdf 1653 | Vinidor |
|--|---|---|---|---|------------|---------|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 33  | 33  | 33  | 30  |            |         |
| Total gross/net capacity                             | 125/104 litre                                     | 125/104 litre                                     | 125/104 litre                                     | 117/97 litre  |            |         |
| Energy efficiency class                              | ≤ A   | ≤ A   | ≤ A   | ≤ A   |            |         |
| Energy consumption year/24 hrs <sup>2</sup>          | 145/0.396 kWh                                     | 145/0.396 kWh                                     | 145/0.396 kWh                                     | 145/0.397 kWh   |            |         |
| Noise output   | 34 dB(A)  | 34 dB(A)  | 34 dB(A)  | 34 dB(A)  |            |         |
| Climate rating <sup>3</sup>                          | SN (+10°C to +32°C)                               | SN (+10°C to +32°C)                               | SN (+10°C to +32°C)                               | SN-ST (+10°C to +38°C)  |            |         |
| Voltage/Connection rating                            | 220-240V~/1.0 A                                   | 220-240V~/1.0 A                                   | 220-240V~/1.0 A                                   | 220-240V~/1.0 A   |            |         |
| Door   | white insulated glass door, handle and frame free | black insulated glass door, handle and frame free | black insulated glass door, handle and frame free | Insulated glass door prepared for cabinet door or stainless steel front |            |         |
| <b>Wine storage compartment</b>                      |   |   |   |   |            |         |
| Temperature zones/-range                             | 2/+5°C to +20°C                                   | 2/+5°C to +20°C                                   | 2/+5°C to +20°C                                   | 2/+5°C to +20°C   |            |         |
| Adjustable cooling circuits                          | 2   | 2   | 2   | 2   |            |         |
| Type of control/display                              | LCD Display/internal digital                      | LCD Display/internal digital                      | LCD Display/internal digital                      | LCD Display/internal digital  |            |         |
| Forced air system                                    | •   | •   | •   | •   |            |         |
| Fresh air supply via FreshAir activ. charcoal filter | •   | •   | •   | •   |            |         |
| Humidity control via                                 | switchable ventilation                            | switchable ventilation                            | switchable ventilation                            | switchable ventilation  |            |         |
| Interior light                                       | LED   | LED   | LED   | LED   |            |         |
| permanently activated/dimmable                       | • / •   | • / •   | • / •   | • / •   |            |         |
| Shelf material                                       | wooden shelf                                      | wooden shelf                                      | wooden shelf                                      | wooden shelf  |            |         |
| Storage shelves                                      | 4   | 4   | 4   | 4   |            |         |
| running on telescopic rails                          | 2   | 2   | 2   | 2   |            |         |
| Presentation shelf                                   | 1   | 1   | 1   | 1   |            |         |
| Fault: warning signal                                | visual and audible                                | visual and audible                                | visual and audible                                | visual and audible  |            |         |
| Door open: warning signal                            | audible   | audible   | audible   | audible   |            |         |
| Child lock function                                  | •   | •   | •   | •   |            |         |
| <b>Dimensions</b>                                    |   |   |   |   |            |         |
| Aperture dimensions in cm (h/w/d <sup>4</sup> )      | 88/56/at least 55                                 | 88/56/at least 55                                 | 88/56/at least 55                                 | 88/56/at least 55   |            |         |
| Interior dimensions in cm (h/w/d)                    | 70.1/46.4/39.3                                    | 70.1/46.4/39.3                                    | 70.1/46.4/39.3                                    | 70.1/46.4/39.3  |            |         |
| <b>Features</b>                                      |   |   |   |   |            |         |
| SoftSystem   | •   | •   | •   | •   |            |         |
| TipOpen Technology                                   | •   | •   | •   | •   |            |         |
| Door hinges  | right, reversible                                 | right, reversible                                 | right, reversible                                 | right, reversible   |            |         |
| Concealed hinge with restricted opening              | •   | •   | •   | •   |            |         |
| <b>Accessories</b> (see page 48–51)                  | 01, 02, 07  | 01, 02, 07  | 01, 02, 07  | 01, 02, 07, 13, 15, 16  |            |         |
|  |   |   |   |   |            |         |
|  |   |   |   |   |            |         |
|  |   |   |   |   |            |         |
|  |   |   |   |   |            |         |
|  |   |   |   |   |            |         |



Liebherr's touch opening door with **TipOpen technology** integrates perfectly into kitchens with a handle-free design. The double-glazed door opens 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will activate and gently and quietly close the door again.

| Vinidor range  | UWTgb 1682 Vinidor                                | UWTes 1672 Vinidor                    |
|--|---|---------------------------------------|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 34  | 34                                    |
| Total gross/net capacity                             | 123/94 litre                                      | 123/94 litre                          |
| Energy efficiency class                              | ≤A  | ≤B                                    |
| Energy consumption year/24 hrs <sup>2</sup>          | 144/0.392 kWh                                     | 196/0.535 kWh                         |
| Noise output   | 36 dB(A)  | 38 dB(A)                              |
| Climate rating <sup>3</sup>                          | SN-ST (+10°C to +38°C)                            | SN-ST (+10°C to +38°C)                |
| Voltage/Connection rating                            | 220-240V~/0.8 A                                   | 220-240V~/0.8 A                       |
| Door   | black insulated glass door, handle and frame free | Glass door with stainless steel frame |
| <b>Wine storage compartment</b>                      |   |                                       |
| Temperature zones/-range                             | 2/+5°C to +20°C                                   | 2/+5°C to +20°C                       |
| Adjustable cooling circuits                          | 2   | 2                                     |
| Type of control/display                              | LCD Display/internal digital                      | MagicEye/internal digital             |
| Forced air system                                    | •   | •                                     |
| Fresh air supply via FreshAir activ. charcoal filter | •   | •                                     |
| Humidity control via                                 | switchable ventilation                            | switchable ventilation                |
| Interior light                                       | LED   | LED                                   |
| permanently activated/dimmable                       | • / •   | • / •                                 |
| Shelf material                                       | wooden shelf                                      | wooden shelf                          |
| Storage shelves                                      | 5   | 5                                     |
| running on telescopic rails                          | 3   | 3                                     |
| Fault: warning signal                                | visual and audible                                | visual and audible                    |
| Door open: warning signal                            | audible   | audible                               |
| Child lock function                                  | •   | •                                     |
| <b>Dimensions</b>                                    |   |                                       |
| Aperture dimensions in cm (h/w/d <sup>4</sup> )      | 82-87/60/at least 58                              | 82-87/60/at least 58                  |
| Interior dimensions in cm (h/w/d)                    | 55/51/44  | 55/51/44                              |
| <b>Features</b>                                      |   |                                       |
| SoftSystem   | •   |                                       |
| TipOpen Technology                                   | •   |                                       |
| Slimline door handle                                 |   | Aluminium handle                      |
| Door hinges  | right, reversible                                 | right, reversible                     |
| Concealed hinge with restricted opening              | •   |                                       |
| Lock   |   | •                                     |
| <b>Accessories</b> (see page 48–51)                  | 01, 02, 07, 17                                    | 01, 02, 07, 10, 11, 14, 17            |

## Wine storage cabinets GrandCru


Wine storage cabinets can be set to exactly the temperature required within the range of +5°C to +20°C. This ensures that the selected temperature is maintained constantly and uniformly throughout the interior. Our wine storage cabinets are ideal for storing wines for long periods of time to allow them to mature to perfection. Depending on what temperature the appliances are set to, they can also be used for keeping white wine or red wine at exactly the right temperature for serving.



# Quality in every detail



The precision **electronic control system** is clearly arranged in the insulation plate. The digital temperature display can be read from the outside of appliances with glass doors. The door and temperature alarm alerts the user to any irregularities, e.g. a door that has been left open. The child lock prevents any inadvertent changes to the control system.



The **LED lighting in the wine cooling compartment** can be dimmed to give a pleasing ambient light inside the appliance. For ideal presentation of your best wines, the interior light with separate switch in appliances with glazed door.

**LED**



The **bottle shelves, made of untreated wood**, are variably height-adjustable to provide an optimum overview and a clear storage layout. The bottles can be stored in opposite directions to make full use of the capacity. The wooden shelves are designed to safely hold Bordeaux bottles. The **clip-on labelling system** provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical **aluminium handle, with integrated opening mechanism**, allows the door of the appliance to be opened conveniently with a minimum of effort.



Liebherr's touch opening door with **TipOpen technology** integrates perfectly into kitchens with a handle-free design. When gently touched, the glass door automatically opens by about 5 cm, ready for full opening. If the door is not opened further within three seconds (approx.), the **SoftSystem** closing mechanism automatically shuts it again.

**Tip  
Open**



The practical **presentation shelf** fulfils both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the rear.



The fresh air supplied through the **FreshAir activated charcoal filter** and recirculating air cooling system ensures optimal air quality. This is crucially important for the maturing process and preservation of the wine. FreshAir charcoal filters are easily accessible from the front and are replaceable.

The features shown are model dependent; the description applies to the relevant model.



| Wine storage cabinets<br>GrandCru                       | WKt 6451 GrandCru         | WKt 5552 GrandCru         | WKt 5551 GrandCru         | WKes 4552 GrandCru                    | WKt 4552 GrandCru         | WKt 4551 GrandCru         | UWKes 1752 GrandCru 82-87                             | WKes 653 GrandCru                        |
|---|---------------------------|---------------------------|---------------------------|---------------------------------------|---------------------------|---------------------------|---|--|
|   | A++ LED                   | A+ LED                    | A++ LED                   | A+ LED                                | A+ LED                    | A++ LED                   | LED Telescopic rails Built-in Under-worktop appliance | A++ LED Smart Steel                      |
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>      | 312                       | 253                       | 253                       | 201                                   | 201                       | 201                       | 46  | 12                                       |
| Total gross/net capacity                                | 666/625 litre             | 573/525 litre             | 547/499 litre             | 478/435 litre                         | 478/435 litre             | 456/413 litre             | 135/110 litre   | 56/38 litre                              |
| Energy efficiency class                                 |                           |                           |                           |                                       |                           |                           |   |  |
| Energy consumption year/24 hrs <sup>2</sup>             | 118/0.323 kWh             | 140/0.382 kWh             | 111/0.302 kWh             | 133/0.364 kWh                         | 133/0.364 kWh             | 106/0.288 kWh             | 145/0.396 kWh   | 75/0.205 kWh                             |
| Noise output  | 41 dB(A)                  | 41 dB(A)                  | 39 dB(A)                  | 41 dB(A)                              | 41 dB(A)                  | 39 dB(A)                  | 38 dB(A)  | 40 dB(A)                                 |
| Climate rating <sup>3</sup>                             | SN-T (+10°C to +43°C)     | SN-ST (+10°C to +38°C)    | SN-T (+10°C to +43°C)     | SN-ST (+10°C to +38°C)                | SN-ST (+10°C to +38°C)    | SN-T (+10°C to +43°C)     | SN-ST (+10°C to +38°C)                                | SN (+10°C to +32°C)                      |
| Voltage/Connection rating                               | 220-240V~/1.0 A           | 220-240V~/1.0 A           | 220-240V~/1.0 A           | 220-240V~/1.0 A                       | 220-240V~/1.0 A           | 220-240V~/1.0 A           | 220-240V~/0.8 A                                       | 220-240V~/1.0 A                          |
| Door  | Full door, terra          | Glass door, frame terra   | Full door, terra          | Glass door with stainless steel frame | Glass door, frame terra   | Full door, terra          | Glass door with stainless steel frame                 | Glass door with S/Steel frame/SmartSteel |
| Side walls  | terra                     | terra                     | terra                     | stainless steel                       | terra                     | terra                     |   | stainless steel with SmartSteel          |
| <b>Wine storage compartment</b>                         |                           |                           |                           |                                       |                           |                           |   |  |
| Temperature zones/-range                                | 1/+5°C to +20°C           | 1/+5°C to +20°C           | 1/+5°C to +20°C           | 1/+5°C to +20°C                       | 1/+5°C to +20°C           | 1/+5°C to +20°C           | 1/+5°C to +20°C                                       | 1/+5°C to +20°C                          |
| Adjustable cooling circuits                             | 1                         | 1                         | 1                         | 1                                     | 1                         | 1                         | 1   | 1  |
| Type of control/display                                 | MagicEye/external digital | MagicEye/internal digital | MagicEye/internal digital | MagicEye/internal digital             | MagicEye/internal digital | MagicEye/internal digital | MagicEye/internal digital                             | LCD Display/internal digital             |
| Forced air system                                       | •                         | •                         | •                         | •                                     | •                         | •                         | •   | •  |
| Fresh air supply via FreshAir activ. charcoal filter    | •                         | •                         | •                         | •                                     | •                         | •                         | •   | •  |
| Humidity control via                                    | switchable ventilation    | switchable ventilation    | switchable ventilation    | switchable ventilation                | switchable ventilation    | switchable ventilation    | switchable ventilation                                | switchable ventilation                   |
| Interior light  | LED                       | LED                       | LED                       | LED                                   | LED                       | LED                       | LED   | LED                                      |
| permanently activated/dimmable                          | • / -                     |                           |                           | • / -                                 | • / -                     | • / -                     | • / -   | • / •                                    |
| Shelf material  | wooden shelf              | wooden shelf              | wooden shelf              | wooden shelf                          | wooden shelf              | wooden shelf              | wooden shelf  | wooden shelf                             |
| Storage shelves   | 7                         | 7                         | 7                         | 6                                     | 6                         | 6                         | 4   | 3  |
| running on telescopic rails                             |                           |                           |                           |                                       |                           |                           | 3   |  |
| Height-adjustable shelves                               | •                         | •                         | •                         | •                                     | •                         | •                         |   |  |
| Fault: warning signal                                   | visual and audible        | visual and audible        | visual and audible        | visual and audible                    | visual and audible        | visual and audible        | visual and audible                                    | visual and audible                       |
| Door open: warning signal                               | audible                   | audible                   | audible                   | audible                               | audible                   | audible                   | audible   | audible                                  |
| Child lock function                                     | •                         | •                         | •                         | •                                     | •                         | •                         | •   | •  |
| Drawers for accessories                                 |                           |                           |                           |                                       |                           |                           |   | 1  |
| <b>Dimensions</b>                                       |                           |                           |                           |                                       |                           |                           |   |  |
| Exterior/Aperture dimensions in cm (h/w/d) <sup>4</sup> | 193/74.7/75.9             | 192/70/74.2               | 192/70/74.2               | 165/70/74.2                           | 165/70/74.2               | 165/70/74.2               | 82-87/60/at least 58                                  | 61.2/42.5/47.8                           |
| Interior dimensions in cm (h/w/d)                       | 170/61.5/56               | 164/57.8/58.5             | 164/57.8/56               | 137/57.8/58.5                         | 137/57.8/58.5             | 137/57.8/56               | 48.8/51/44  | 37/35/31                                 |
| <b>Features</b>   |                           |                           |                           |                                       |                           |                           |   |  |
| Design  | SwingLine                 | HardLine                  | HardLine                  | HardLine                              | HardLine                  | HardLine                  |   | HardLine                                 |
| Slimline door handle                                    | Aluminium handle          | Aluminium handle          | Aluminium handle          | Aluminium handle                      | Aluminium handle          | Aluminium handle          | Aluminium handle                                      | Aluminium handle                         |
| with integrated opening mechanism                       | •                         | •                         | •                         | •                                     | •                         | •                         |   |  |
| Door hinges   | right, reversible         | right, reversible         | right, reversible         | right, reversible                     | right, reversible         | right, reversible         | right, reversible                                     | right fixed                              |
| Replaceable door seal                                   | •                         |                           |                           | •                                     | •                         | •                         | •   | •  |
| Lock  | •                         | •                         | •                         | •                                     | •                         | •                         | •   | •  |
| <b>Accessories (see page 48–51)</b>                     | 01, 02, 07                | 01, 02, 04, 05, 07, 08    | 01, 02, 04, 05, 07, 08    | 01, 02, 04, 05, 07, 08, 10            | 01, 02, 04, 05, 07, 08    | 01, 02, 04, 05, 07, 08    | 01, 02, 07, 08, 10, 11, 14, 17                        | 01, 02, 07, 09                           |

## Wine storage cabinets

GrandCru



The easy-glide accessories drawer can be used to store accessories directly below wine storage cabinets in the WKE 5 model range. This increases the 45 cm recess to 60 cm. Available in white glass (9792 449), black glass (9792 451) and stainless steel (9792 453).




### Built-in wine storage cabinets GrandCru

|  | <b>WKEgb 582 GrandCru</b>                         | <b>WKEgw 582 GrandCru</b>                         | <b>WKEes 553 GrandCru</b>             |
|--|---|---|---------------------------------------|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 18  | 18  | 18                                    |
| Total gross/net capacity                             | 48/46 litre                                       | 48/46 litre                                       | 48/46 litre                           |
| Energy efficiency class                              | A <sup>2</sup>                                    | A <sup>2</sup>                                    | A <sup>2</sup>                        |
| Energy consumption year/24 hrs <sup>2</sup>          | 106/0.290 kWh                                     | 106/0.290 kWh                                     | 130/0.356 kWh                         |
| Noise output   | 34 dB(A)  | 34 dB(A)  | 34 dB(A)                              |
| Climate rating <sup>3</sup>                          | SN-ST (+10°C to +38°C)                            | SN-ST (+10°C to +38°C)                            | SN (+10°C to +32°C)                   |
| Voltage/Connection rating                            | 220-240V~/0.5 A                                   | 220-240V~/0.5 A                                   | 220-240V~/0.5 A                       |
| Door   | black insulated glass door, handle and frame free | white insulated glass door, handle and frame free | Glass door with stainless steel frame |
| <b>Wine storage compartment</b>                      |   |   |                                       |
| Temperature zones/-range                             | 1/+5°C to +20°C                                   | 1/+5°C to +20°C                                   | 1/+5°C to +20°C                       |
| Adjustable cooling circuits                          | 1   | 1   | 1                                     |
| Type of control/display                              | LCD Display/internal digital                      | LCD Display/internal digital                      | LCD Display/internal digital          |
| Forced air system                                    | •   | •   | •                                     |
| Fresh air supply via FreshAir activ. charcoal filter | •   | •   | •                                     |
| Humidity control via                                 | switchable ventilation                            | switchable ventilation                            | switchable ventilation                |
| Interior light                                       | LED   | LED   | LED                                   |
| permanently activated/dimmable                       | • / •   | • / •   | • / •                                 |
| Shelf material                                       | wooden shelf                                      | wooden shelf                                      | wooden shelf                          |
| Storage shelves                                      | 3   | 3   | 3                                     |
| running on telescopic rails                          | 2   | 2   | 2                                     |
| Fault: warning signal                                | visual and audible                                | visual and audible                                | visual and audible                    |
| Door open: warning signal                            | audible   | audible   | audible                               |
| Child lock function                                  | •   | •   | •                                     |
| <b>Dimensions</b>                                    |   |   |                                       |
| Aperture dimensions in cm (h/w/d <sup>4</sup> )      | 45/56/at least 55                                 | 45/56/at least 55                                 | 45/56/at least 55                     |
| Interior dimensions in cm (h/w/d)                    | 29.5/47/29  | 29.5/47/29  | 34/46/31                              |
| <b>Features</b>                                      |   |   |                                       |
| SoftSystem   | •   | •   |                                       |
| TipOpen Technology                                   | •   | •   |                                       |
| Drop down door/side opening door                     | • / -   | • / -   | - / •<br>recessed grip                |
| Handle   |   |   | right, reversible                     |
| Door hinges  |   |   |                                       |
| Concealed hinge with restricted opening              | •   | •   |                                       |
| <b>Accessories (see page 48–51)</b>                  | 01, 02  | 01, 02  | 01, 02, 07, 10, 11                    |

1/2/3/4 Notes see pages 36/37

You can find the full range of efficiency classes at page 5. According to (EU) 2017/1369 6a.



## Humidor



### Humidor

|  | <b>ZKes 453 Humidor</b>                  |
|--|--|
| Total gross/net capacity                             | 43/39 litre                              |
| Energy efficiency class                              | A++                                      |
| Energy consumption year/24 hrs <sup>2</sup>          | 162/0.443 kWh                            |
| Noise output   | 40 dB(A)                                 |
| Climate rating <sup>3</sup>                          | N (+16°C to +32°C)                       |
| Voltage/Connection rating                            | 220-240V~/0.5 A                          |
| Door   | Glass door with S/Steel frame/SmartSteel |
| Side walls   | stainless steel with SmartSteel          |
| <b>Features</b>                                      |  |
| Temperature zones/-range                             | 1/+16°C to +20°C                         |
| Air humidity   | 68% to 75%                               |
| Adjustable cooling circuits                          | 1  |
| Type of control/display                              | LCD Display/internal digital             |
| Forced air system                                    | •  |
| Fresh air supply via FreshAir activ. charcoal filter | •  |
| Humidity control via                                 | switchable ventilation                   |
| Interior light                                       | LED                                      |
| permanently activated/dimmable                       | • / •                                    |
| Shelf material                                       | Spanish cedar wood                       |
| Storage shelves                                      | 2  |
| Fault: warning signal                                | visual and audible                       |
| Door open: warning signal                            | audible                                  |
| Child lock function                                  | •  |
| Presentation boxes                                   | 2  |
| Lock   | •  |
| Door hinges  | right fixed                              |
| Wall mounting  | possible                                 |
| <b>Dimensions</b>                                    |  |
| Exterior dimensions in cm (h/w/d <sup>4</sup> )      | 61.2/42.5/47.8                           |
| Interior dimensions in cm (h/w/d)                    | 34/30/27.4                               |
| <b>Accessories (see page 48–51)</b>                  | 01, 09                                   |

1/2/3/4 Notes see pages 36/37



WKb 4212

## Wine storage cabinets Vinothek

Wine storage cabinets offer similar conditions to a wine cellar. They are therefore an ideal choice for both long-term storage and storage of large wine stocks, always achieving the perfect serving temperature. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.

# Quality in every detail



The precision **electronic control system** is located at the top of the cabinet housing. The digital temperature display can be read from the outside of appliances with glass doors. The door and temperature alarm alerts the user to any irregularities, e.g. a door that has been left open. The child lock prevents any inadvertent changes to the control system.



The **untreated wooden storage shelves** are variably height-adjustable to provide an optimum overview and a clear storage layout. Storing the bottles in opposite directions on the pull-out shelves permits full use of the capacity. The wooden shelves are designed to safely hold Bordeaux bottles.



The **clip-on labelling system** provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.



The appliances with glass doors feature an **interior light** which has a separate switch for the ideal presentation of your best wines.



The **tinted safety glass** in the Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The **slimline door handle in black** is aesthetically pleasing and ergonomically designed for ease of opening.



Environmental odours can have an impact on wine stored for longer periods. Fresh air is supplied to Liebherr wine cabinets through the easily replaceable **FreshAir activated charcoal filter** to ensure optimal air quality.

The features shown are model dependent; the description applies to the relevant model.



| Wine storage cabinets<br>Vinothek                    | WKb 4212 Vinothek          | WKr 4211 Vinothek<br>A <sup>++</sup> | WKb 3212 Vinothek          | WKr 3211 Vinothek<br>A <sup>++</sup> | WKb 1812 Vinothek<br>A <sup>+</sup> | WKr 1811 Vinothek<br>A <sup>+</sup> | WKb 1802 Vinothek                    |
|--|----------------------------|--------------------------------------|----------------------------|--------------------------------------|-------------------------------------|-------------------------------------|--------------------------------------|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 200                        | 200                                  | 164                        | 164                                  | 66                                  | 66                                  | 66                                   |
| Total gross/net capacity                             | 427/395 litre              | 409/377 litre                        | 336/309 litre              | 322/295 litre                        | 145/134 litre                       | 145/128 litre                       | 145/134 litre                        |
| Energy efficiency class                              | ≤ A                        | ≤ A <sup>+</sup>                     | ≤ A                        | ≤ A <sup>++</sup>                    | ≤ A                                 | ≤ A <sup>+</sup>                    | ≤ B                                  |
| Energy consumption year/24 hrs <sup>2</sup>          | 168/0.458 kWh              | 103/0.282 kWh                        | 161/0.441 kWh              | 99/0.269 kWh                         | 113/0.307 kWh                       | 113/0.308 kWh                       | 199/0.544 kWh                        |
| Noise output   | 41 dB(A)                   | 39 dB(A)                             | 39 dB(A)                   | 39 dB(A)                             | 38 dB(A)                            | 38 dB(A)                            | 41 dB(A)                             |
| Climate rating <sup>3</sup>                          | SN-ST (+10°C to +38°C)     | SN-T (+10°C to +43°C)                | SN-ST (+10°C to +38°C)     | SN-T (+10°C to +43°C)                | SN-ST (+10°C to +38°C)              | SN-T (+10°C to +43°C)               | N (+16°C to +32°C)                   |
| Voltage/Connection rating                            | 220-240V~/1.0 A            | 220-240V~/1.0 A                      | 220-240V~/0.8 A            | 220-240V~/0.8 A                      | 220-240V~/0.5 A                     | 220-240V~/0.5 A                     | 220-240V~/0.5 A                      |
| Door   | Glass door, frame black    | Full door, burgundy                  | Glass door, frame black    | Full door, burgundy                  | Glass door, frame black             | Full door, burgundy                 | Glass door, frame black              |
| Side walls   | black                      | black                                | black                      | black                                | black                               | black                               | black                                |
| <b>Wine storage compartment</b>                      |                            |                                      |                            |                                      |                                     |                                     |                                      |
| Temperature zones/-range                             | 1/+5°C to +20°C            | 1/+5°C to +20°C                      | 1/+5°C to +20°C            | 1/+5°C to +20°C                      | 1/+5°C to +20°C                     | 1/+5°C to +20°C                     | 1/+5°C to +20°C                      |
| Adjustable cooling circuits                          | 1                          | 1                                    | 1                          | 1                                    | 1                                   | 1                                   | 1                                    |
| Type of control/display                              | MagicEye/external digital  | MagicEye/external digital            | MagicEye/external digital  | MagicEye/external digital            | MagicEye/external digital           | MagicEye/external digital           | Mechanical controls/external digital |
| Forced air system                                    | •                          | •                                    | •                          | •                                    | •                                   | •                                   | •                                    |
| Fresh air supply via FreshAir activ. charcoal filter | •                          | •                                    | •                          | •                                    | •                                   | •                                   | •                                    |
| Humidity control via                                 | switchable ventilation     | switchable ventilation               | switchable ventilation     | switchable ventilation               | switchable ventilation              | switchable ventilation              | switchable ventilation               |
| Interior light                                       | •                          |                                      | •                          |                                      | •                                   |                                     | •                                    |
| permanently activated/dimmable                       | • / -                      |                                      | • / -                      |                                      | • / -                               |                                     | • / -                                |
| Shelf material                                       | wooden shelf               | wooden shelf                         | wooden shelf               | wooden shelf                         | zinced rails                        | zinced rails                        | zinced rails                         |
| Storage shelves                                      | 6                          | 6                                    | 4                          | 4                                    | 3                                   | 3                                   | 2                                    |
| Height-adjustable shelves                            | •                          | •                                    | •                          | •                                    | •                                   | •                                   | •                                    |
| Fault: warning signal                                | visual and audible         | visual and audible                   | visual and audible         | visual and audible                   | visual and audible                  | visual and audible                  |                                      |
| Door open: warning signal                            | audible                    | audible                              | audible                    | audible                              | audible                             | audible                             |                                      |
| Child lock function                                  | •                          | •                                    | •                          | •                                    | •                                   | •                                   |                                      |
| <b>Dimensions</b>                                    |                            |                                      |                            |                                      |                                     |                                     |                                      |
| Exterior dimensions in cm (h/w/d <sup>4</sup> )      | 165/60/73.9                | 165/60/73.9                          | 135/60/73.9                | 135/60/73.9                          | 89/60/61.3                          | 89/60/61.3                          | 90.1/59.7/61.2                       |
| Interior dimensions in cm (h/w/d)                    | 146.6/50/56                | 146.6/50/56                          | 116.6/50/56                | 116.6/50/56                          | 71/50/44                            | 71/50/44                            | 70.2/47/46.8                         |
| <b>Features</b>                                      |                            |                                      |                            |                                      |                                     |                                     |                                      |
| Design   | HardLine                   | HardLine                             | HardLine                   | HardLine                             | HardLine                            | HardLine                            | HardLine                             |
| Slimline door handle                                 | Slimline door handle black | Slimline door handle black           | Slimline door handle black | Slimline door handle black           | Slimline door handle black          | Slimline door handle black          | Slimline door handle black           |
| Door hinges  | right, reversible          | right, reversible                    | right, reversible          | right, reversible                    | right, reversible                   | right, reversible                   | right, reversible                    |
| Replaceable door seal                                | •                          |                                      | •                          |                                      | •                                   |                                     | •                                    |
| Accessories (see page 48–51)                         | 01, 02, 04, 07, 12         | 01, 02, 04, 07, 12                   | 01, 02, 04, 07, 12         | 01, 02, 04, 07, 12                   | 01, 02, 06, 07, 12                  | 01, 02, 06, 07, 12                  | 02                                   |

# Multi-temperature wine cabinets

## Vinothek

Multi-temperature wine cabinets are especially suited for storing different types of wine at their respective drinking temperatures.

These appliances incorporate a special climate control system that can layer the temperatures. In the upper zone, for example, red wine can be kept at +18°C while the lower zone, set at an ambient temperature of +5°C, will be particularly suitable for sparkling wine or champagne.



The wine cabinets are equipped with an accurate **electronic control system** with digital temperature display. These appliances incorporate a special climate control system that can layer the temperatures. In the upper zone, for example, red wine can be kept at +16°C to +18°C while the lower zone is set at an ambient temperature of +5°C to +7°C.



**Ideal humidity via Lava stone.** The humidity in the Vinothek models can be increased by using Lava stone.

| Multi-temperature wine cabinets Vinothek             | WTb 4212 Vinothek           | WTr 4211 Vinothek           |
|--|-----------------------------|-----------------------------|
| Max. No. of Bordeaux bottles 0.75 Ltr <sup>1</sup>   | 200                         | 200                         |
| Total gross/net capacity                             | 427 / 395 litre             | 409 / 377 litre             |
| Energy efficiency class                              | ≤ A                         | ≤ A                         |
| Energy consumption year/24 hrs <sup>2</sup>          | 168 / 0.460 kWh             | 167 / 0.457 kWh             |
| Noise output   | 41 dB(A)                    | 40 dB(A)                    |
| Climate rating <sup>3</sup>                          | SN-ST (+10°C to +38°C)      | SN-ST (+10°C to +38°C)      |
| Voltage/Connection rating                            | 220-240V~/1.0 A             | 220-240V~/1.0 A             |
| Door   | Glass door, frame black     | Full door, burgundy         |
| Side walls   | black                       | black                       |
| <b>Wine storage compartment</b>                      |                             |                             |
| Temperature range                                    | +5°C to +18°C               | +5°C to +18°C               |
| Adjustable cooling circuits                          | 1                           | 1                           |
| Type of control/display                              | MagicEye / external digital | MagicEye / external digital |
| Fresh air supply via FreshAir activ. charcoal filter | •                           | •                           |
| Humidity control via                                 | Lava stone                  | Lava stone                  |
| Interior light                                       | •                           |                             |
| permanently activated/dimmable                       | • / –                       |                             |
| Shelf material                                       | wooden shelf                | wooden shelf                |
| Storage shelves                                      | 6                           | 6                           |
| Height-adjustable shelves                            | •                           | •                           |
| Fault: warning signal                                | visual and audible          | visual and audible          |
| Door open: warning signal                            | audible                     | audible                     |
| Child lock function                                  | •                           | •                           |
| <b>Dimensions</b>                                    |                             |                             |
| Exterior dimensions in cm (h/w/d) <sup>4</sup>       | 165 / 60 / 73.9             | 165 / 60 / 73.9             |
| Interior dimensions in cm (h/w/d)                    | 146.6 / 50 / 56             | 146.6 / 50 / 56             |
| <b>Features</b>                                      |                             |                             |
| Design   | HardLine                    | HardLine                    |
| Slimline door handle                                 | Slimline door handle black  | Slimline door handle black  |
| Door hinges  | right, reversible           | right, reversible           |
| Replaceable door seal                                | •                           |                             |
| <b>Accessories</b> (see page 48–51)                  | 01, 03, 04, 07, 12          | 01, 03, 04, 07, 12          |
|  |                             |                             |
|  |                             |                             |
|  |                             |                             |
|  |                             |                             |
|  |                             |                             |

## Optional Accessories

01

### FreshAir active carbon filter

Odours from the surrounding air can impair the quality of wine. Liebherr wine cabinets are fitted with easy-to-replace FreshAir activated charcoal filters to ensure clean air, filter out odours and safeguard the quality of the wine.



WTes 1672; UWKes 1752; UWTes 1672,  
UWTgb 1682; WKEgb/gw 582, EWTdf/gw/gb 9881 289

WKes 653; ZKes 453  
All other free-standing and built-in wine appliances 9881 291

9881 287

02

### Lava stone box including lava stone

In order to protect wine corks from dehydration during long-term bottle storage, the humidity in the appliance can be increased using a damp lava stone. The lava stone is stored very conveniently and is visually appealing in a custom high-end red beech box. The lava stone box contains a removable plastic bowl into which the water is poured to increase the humidity. The lava stone box can be positioned anywhere in the appliance.



All wine models (except WTb 4212, WTr 4211)

9901 820

03

### Retrofit lava stone kit

The humidity in the Vinothek multi-temperature wine cabinets can be increased as required using lava stones.



WTb 4212; WTr 4211

9591 517

04

### Wooden shelf

The handcrafted shelf, made from natural wood, is the perfect accessory for safely storing Bordeaux bottles. Positioning the bottles in opposite directions enables full use of the shelf's capacity.



WKt 5552, 5551, 4552, 4551; WKes 4552 9881 261

9881 263

05

### Presentation shelf (wooden folding shelf)

The shelf can be used to present exquisite wines, or to safely store already-opened bottles.



WTes 5872, 5972 7112 043  
WKt 5552, 5551, 4552, 4551; WKes 4552 7113 619

06

### Galvanised grill shelf

Grill shelf for additional requirements.



WKb 1812, WKr 1811 7112 035

07

### Clip-on labelling system

The clip-on labelling system provides a quick and clear overview of your wine store. The labelled cards can be easily inserted into the clips which can be attached as required.



Clip-on labelling for grill shelves WKb/r 18 (2 pieces) 9086 723  
For all other wooden shelves (5 pieces) 9094 559  
Clip-on labelling for wooden shelves EWT; UWTgb 1682; UWTes 1672; UWKes 1752; WTes 1672 (2 pieces) 9094 397

08

### Bottle holder

The practical bottle holder allows you to store even more bottles.



WKt 5552, 5551, 4552, 4551; WKes 4552; UWkes 1752 7436 193

## Optional Accessories

09

### Underside cover for wall mounting

Covers the underside, enabling compact appliances to be attractively wall mounted without their underside being visible.

WKes 653; ZKes 453

9590 519



10

### Stainless steel polish

For polishing stainless steel surfaces after they have been cleaned (do not use on SmartSteel).

250 ml

8409 030



11

### Stainless steel cleaner

The stainless steel cleaner effectively and gently removes fingerprints, streaks and stains from stainless steel surfaces. (Not for SmartSteel fronts, apply to stainless steel fronts/frames only.)

250 ml

8409 022



12

### Lock

The lock prevents unwanted access. Simply assemble on the housing with Vinothek wine cabinets. If two wine cabinets are set up Side-by-Side, the operation of the sideways lock is limited. In this case an additional lock can be fitted below.

Vinothek wine appliances

9094 443



13

### Stainless steel frame with handle

The high-quality, easy-to-fit optional stainless steel accessory frame kit enables the model's integration into any kitchen. The robust stainless steel handle is easy to attach and makes opening of the door effortless. The stainless steel frame comes with pre-drilled holes for the stainless steel handle.

EWTdf 3553

9901 573

EWTdf 2353

9901 575

EWTdf 1653

9901 577



14

### Stainless steel bar handle for undercounter wine cabinet

To optimally fit the appliance into the intended kitchen environment, the sturdy aluminium handle can be replaced with a narrower bar handle. This is well-designed, brushed stainless steel that impresses with its good look and feel.

WTes 1672; UWTes 1672; UWKes 1752

9901 071



15

### Profile frame (aluminium)

Aluminium profile frame for: EWTdf 1653

EWTdf 2353

EWTdf 3553

19 mm 9901 075

9901 079

9901 080

22 mm 9901 081

9901 082

9901 083



16

### Aluminium handle

EWTdf 3553, EWTdf 2353, EWTdf 1653

9901 561



17

### Mounting bracket accessory kit

Side-by-Side fitting kit

UWT; UWK

9901 647