



SmartDevice App: The Smart-Device app lets you control your fridge from anywhere: Change the temperature of your appliance quickly and easily from anywhere or monitor all alerts and notifications at a glance.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.

Our catalogues

Find out everything you need to know about Liebherr Freestanding & Fully integrated refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as PDF downloads from home.liebherr.com



WarrantyPLUS

Benefit from many advantages of an extension of 2 or 7 years Warranty. Further information under home.liebherr.com/promotions or contact yours Liebherr specialist dealers Partner.



Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle

Liebherr-Hausgeräte Marica E00D
E-mail: home.see@liebherr.com

home.liebherr.com


Freestanding 2021 – Refrigeration

Freestanding 2021

Valid from 1 March 2021

LIEBHERR

Refrigeration



LIEBHERR

Subject to modification. Current data see home.liebherr.com.
Printed in Germany by raff media group. 02.2021





Contents

Quality, Design and Innovation	04
Flexible accessories	10
BluPerformance	12
The new EU energy label for electrical appliances	20
Food storage centres	22
Side-by-Side fridge-freezers	26
Frenchdoor fridge-freezer	32
Fridge-freezers	34
Fridges	68
Freezers	92
Chest freezers	112
Wine cabinets	116

Quality

For 60 years Liebherr has specialised in the manufacture of high quality, innovative fridges and freezers. From the initial stages of product design, and continuing through development, production and marketing, Liebherr focuses on manufacturing innovative products of the highest quality with timeless and elegant design. We consistently implement new ideas and improved technology to ensure optimum food storage and quality.

Quality fresh food storage: BioFresh

Liebherr's BioFresh technology preserves fresh food for longer. Stored in the BioFresh compartment, at just over 0 °C and at the ideal humidity level, food will retain its nutritional value for far longer than it would in a normal fridge compartment.

Professional quality

As a refrigeration specialist, Liebherr offers a wide range of professional appliances for commercial use. The demands of the professional sector are high; this sector wants reliable, top quality storage that guarantees safe food storage. As you use your Liebherr appliance in the home on a daily basis, you are benefiting from the expertise that Liebherr has accrued from decades in the commercial sector.

Quality assured

So that you can trust your fridge or freezer to perform 24 hours a day, 365 days a year, we check all components at every stage of their development to ensure that they will function reliably for many years. For instance, before our door hinges find their way into production, they have to successfully pass through at least 100.000 opening cycles, which equates to more than 15 years use. All components undergo similar testing.

Approved quality

Prior to packaging, every appliance is subject to a comprehensive quality inspection during which all components - refrigeration, mechanical and electronic systems - are tested. The quality of workmanship is also visually checked. All Liebherr production sites are certified according to international standards for quality management (ISO 9001) and environmental management (ISO 1400).

All newly manufactured domestic appliances from Liebherr comply with the requirements of standard IEC 60335-2-24 A2 §30 in terms of heat and fire resistance.

Guaranteed quality

We provide a three year warranty that covers all parts and labour costs to repair or replace any part of the appliance that proves to be defective in materials or workmanship. We also offer a ten year parts availability.

VCC compressor

Modern speed-controlled VCC compressors deliver perfect refrigeration performance and ensure that appliances benefit from optimum energy efficiency and cost effectiveness. They operate extremely quietly.





Design

Characterised by elegant and timeless design, Liebherr's fridges and freezers fulfil and surpass the highest aesthetic demands. Extensive detailing – as seen in the superb stainless steel craftsmanship, the choice of high quality materials, the stylish interior fittings, and the practical Glassline door interior – is typical in our appliances and reveals their design quality.

Design for every kitchen space

So you can enjoy a lifetime of pleasure owning your Liebherr appliance, and find the perfect appliance for you, we offer a wide range of designs including models in classic stainless steel, elegant BlackSteel or vibrant ColourLine finishes, all of which complement modern kitchen and living spaces.

install specially selected LEDs in order to achieve a harmonious, slightly bluish tinted lighting effect.

Award-winning design

The superb design quality of our appliances has seen them honoured with many prestigious, international design awards from the likes of Plus X Award, reddot, iF product design and Good Design.

Practical design for daily use

At Liebherr, design and functionality go hand-in-hand. To prevent finger marks on our stainless steel doors, we finish them with a SmartSteel surface. To make door opening easy and convenient, our ergonomically designed handles house an integrated opening mechanism. All GlassLine shelves are dishwasher safe.

Lighting design

Liebherr's fridges and freezers are fitted with modern LED lighting. Upon opening the appliance door, the interior becomes evenly illuminated. LEDs are long-life, energy efficient and generate very little heat. We take meticulous care to



Innovation

Liebherr was first to implement features that are now standard in today's fridges and freezers. For example: fully enclosed FrostSafe freezer drawers that prevent loss of chilled air when the appliance is opened; patented BioFresh technology; and convenient, SoftSystem cushioned door closure.

Innovative ideas

We place great importance on the continual development of our products. Therefore, at all of our production sites, we have state-of-the-art design centres with highly skilled employees. Our goal is to be 'Best in Class' in every respect. For example, Liebherr's current appliances are super-economical in terms of energy consumption thanks to the incorporation of advanced electronics and optimised refrigeration design.

Excellence in every detail

It couldn't be easier to set and adjust appliances with touch screen operation. The GlassLine storage shelves can be easily positioned for tailored use of the interior space. Drinks storage is provided in the door interior and, depending on the model, a bottle rack or versatile bottle shelf offer additional practical storage solutions.

Innovation for even greater freshness

The latest fridges and freezers offer the ideal climate zone for almost every type of food. So, in addition to the classic refrigerator compartment, Liebherr offers a range of features including the BioCool box: a fruit and vegetable compartment in which humidity can be regulated; BioFresh drawers, in which meat, fish, dairy products, and fruit/vegetables all find their ideal storage climate; and a NoFrost freezer compartment that offers professional quality frost free freezing.



1954

Liebherr home appliances founded in Germany



1971

First electronic control



1987

NoFrost Technology eliminating the need to defrost



1993

Conversion to CFC / HFC-free equipment program



1996

Patented BioFresh technology - system for extended storage-life



2004

Innovative LED lighting for energy efficient illumination



2006

Vinidor with adjustable temperature zones



2008

SoftSystem for gentle door closure



2009

SmartSteel finish reduces the visibility of finger prints



2010

DuoCooling for superior performance and efficiency



2013

Super efficient fully integrated appliances



2014

Under-worktop TipOpen appliance for seamless integration



2016

BluPerformance: A new dimension in freshness



2018

SmartDevice - Smart food management



2018

Design your fridge



2019

The new dimension for fully integrated appliances





Flexible accessories for your appliance

Discover the versatility of the Liebherr range of accessories for your fridge - and make your daily life a little bit easier.



Organisational systems

Set up your fridge how you want it: In addition to the VarioSafe and the VarioBoxes, we also offer optimal organisation with the variable egg tray and the FlexSystem. Thanks to our bottle shelves and the clip labelling system for your wine inventory, you can also keep track of your beverages.



Lifestyle features

Our butter dish offers space for a wide variety of butter sizes and fits perfectly into all shelves. The easy-to-fill ice cube tray is non-spill. Saving energy made easy: With the Vario energy-saving panel, you can reduce the energy consumption of your NoFrost freezer by up to 30% when not using all drawers.



Consumable accessories

Your fridge includes items that are to be replaced on a regular basis for optimal performance. Water and activated carbon filters can be conveniently purchased from your Liebherr retailer.

Matching accessories can be found online by desired model at: home.liebherr.com

BLU
Performance

BluPerformance – A new dimension in refrigeration design

High quality materials, meticulous workmanship in every detail, and easy-to-use, precise touch-electronics define the BluPerformance range. The compact integration of cooling technology into the appliance plinth and the use of precision electronic controls has enabled even greater energy efficiency, provided more usable volume, and improved freezer compartment ergonomics. BioFresh and BioCool ensure lasting quality and freshness for stored foods. In addition, these models are quieter than ever, so will not disturb your living environment.

With elegant and timeless design, BluPerformance appliances are a highlight in any kitchen and are guaranteed to be a pleasure to use for many years to come.




Greater performance



User-friendly touch operation



Greater freshness quality



Superb convenience



Perfect illumination



Better energy efficiency



High quality materials

Multifunction touch control

In the touch-electronic BluPerformance appliances all functions can be easily and conveniently set by gently touching the screen. The high-resolution 7" colour display enables individual settings. Preset programs such as: 'EnergySaver', 'MaxPerformance', 'Party' or 'Holiday' assist in achieving optimum food storage and minimum energy use.

Day-to-Day

The Day-to-Day program is aimed at meeting everyday requirements. It offers optimum refrigeration performance and efficiency using standard temperature settings in the fridge and freezer compartments.

EnergySaver

The EnergySaver program lowers energy consumption further, beyond standard settings. To save energy, the temperature in the fridge and freezer compartments is slightly raised. The touch-electronics screen displays useful energy saving tips to help you further reduce electricity costs.

Party


The Party program is ideal when preparing for celebrations: SuperCool and SuperFrost are activated for the short-term storage and chilling of larger quantities of food. The BottleTimer allows rapid chilling of drinks. Appliances with an IceMaker can increase ice cube production.

MaxPerformance

The MaxPerformance program allows the appliance to deliver its highest refrigeration performance. It selects lower temperature settings for the fridge and freezer compartments.

Holiday

The Holiday program minimises energy consumption during extended absences from the home. The fridge compartment is set to +15 °C, and the freezer compartment to -18 °C.



We are already providing what the future will bring

One thing is clear: Technology will get smarter and smarter in the future. But does a fridge need to be intelligent? It doesn't have to be. But we believe: Another cool head in the household can't do any harm. Thanks to many smart functions, our appliances have proven themselves to be reliable helpers behind the scenes.

Built-in progress

Your fridge thinks for you whenever it can. For example, it reminds you of forgotten drinks in the freezer – thanks to the integrated Bottle-Timer. So burst bottles are a thing of the past. When you're on holiday, simply switch your fridge to HolidayMode. That way you can save a lot of energy. And especially interesting for all those who are also drawn to the fridge at night: NightMode. The interior is then only illuminated with a dimmed light. So after a midnight snack, you can go back to bed quickly and are guaranteed not to fully wake up from your slumbers.

Always perfectly networked

All our freestanding appliances are either networked ex works or can be subsequently connected to WiFi via the SmartDeviceBox. This way you benefit from the many new possibilities of our SmartDevice app and connecting your fridge to an existing smart home environment. This allows you to easily control appliances via assistance services like Amazon Alexa or online services like IFTTT. Thanks to network-

ing, important status messages are also sent directly to your mobile phone. For example via DoorAlarm, if the fridge door is left open. But our SmartDevice app has even more to offer: You will also find helpful storage tips, access to operating instructions, warranty extensions, accessories and much more. In short, our appliances make you ready for tomorrow today.

We play it very, very safe

We take data protection very seriously. For this reason we have chosen a software partner who shares our high standards: Microsoft. Microsoft, as the first leading provider of cloud services, is certified in accordance with the international standard ISO/IEC 27018, which regulates data protection, and uses AES-256 – the same encryption technology employed in the banking sector.



Models with this label are already fitted with the SmartDeviceBox.



Learn how digitally networked refrigeration makes your everyday life easier:
home.liebherr.com/getsmart





BioFresh: enjoy lasting freshness

With BioFresh technology food keeps fresh for much longer. When stored at a temperature close to 0 °C and at the correct humidity level, many foods retain their nutrients, such as vitamins and minerals, for far longer than in a conventional fridge compartment.

Vitamins for a healthy diet

It goes without saying that it is extremely important for newly purchased and freshly harvested foods to be stored properly so that their nutrients are preserved for longer. The shelf life and freshness of most fruit and vegetables can be significantly extended by storing them in a fridge, particularly in a BioFresh compartment. The vitamin content of fruit and vegetables has been found to increase during storage in a BioFresh compartment.

The perfect climate

With high humidity, the HydroSafe setting offers a perfect storage climate for fruit and vegetables. The drier conditions of the DrySafe setting are ideal for storing meat, fish and dairy products. The moist HydroSafe climate can be changed to a dry DrySafe climate using the humidity slide control.




Find out more about
BioFresh:
biofresh.liebherr.com

The new EU energy label for electrical appliances

It is now once again possible to distinguish more easily between efficient and inefficient appliances. With the reform of the energy label, appliances will once again be rated from A to G on the efficiency scale. This will make things much clearer for you in future.

Technology is developing all the time. And we also never stand still

We are constantly working on features that make everyday work easier, optimise storage and reduce consumption. We were one of the first manufacturers in Europe to develop fridges and freezers in the highest efficiency class. And that is also our aim for the future. Fridges and freezers work around the clock and are responsible for up to 15 percent of the electricity bill. As our appliances consume less energy, they make an important contribution to climate protection.



- 1 The QR code for identifying the product in the EPREL (European Product Database for Energy Labeling) EU database.
- 2 The model identifier for identifying the product manually in the EPREL EU database, e.g. via the article number.
- 3 The new A to G efficiency scale. However G is only intended for wine coolers.
- 4 The sum of the volumes of the frozen compartment(s).
- 5 The sum of the volumes of the chill compartment(s) and the unfrozen compartment(s).
- 6 The noise level is now also classified into classes A to D.

Find out more about the new energy label:
home.liebherr.com/energylabel

Food storage centres



Quality in every detail



Wine

The Side-by-Side fridge-freezer **SBSes 8496** with six different climate zones offers a range of innovative solutions. The wine compartment has two independently adjustable zones for storing wine at the exact temperature required, between +5 °C and +20 °C.



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Bio Fresh

BioFresh guarantees the perfect climate for extra long freshness. A temperature slightly above 0 °C and ideal air humidity maintain the vitamin and mineral content and appetising appearance of fruit and vegetables, meat, fish and milk products significantly longer than in a standard fridge.

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe.



Find out more about BioFresh: biofresh.liebherr.com



Bio Fresh Plus



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 45°.



No Frost

The **NoFrost** system provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost free.



Find out more about NoFrost: nofrost.liebherr.com



Ice Maker

The **IceMaker** provides you with perfect ice cubes for every occasion. Whether for a cool drink or a big party - there will always be enough ice cubes. The IceMaker, which you can switch off at any time, automatically keeps your supplies topped up.

The features shown are model dependent; look for these features in your model choice.



SBSes 8496
PremiumPlus



←121→



SBNes 4285
Premium



←121→

SWTNes 4285
PremiumPlus

- Duo Cooling
- No Frost
- Soft System
- Ice Maker
- Smart Steel
- Smart Device ready
- Wine

Energy efficiency class:
Energy consumption year/24 hrs: 187/0.512 kWh ¹
Total volume ² : 289 l (Wine compartment: 156.4 l/Freezer compartment: 132.8 l)
Noise output/noise class: 37 dB(A)/C
Climate rating: SN-T (+10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 185/60/68.5 ¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display for wine and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperFrost, quantity-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
 - Child lock
- Wine compartment**
- 2 separately controllable temperature zones, which can be regulated between +5 °C to +20 °C
 - Tinted insulated glass door with UV protection
 - Convection cooling fresh air supply via FreshAir activated charcoal filter
 - Humidity regulation via adjustable fan
 - LED lighting permanently on, dimmable
 - Beech wood fittings
 - 4 Shelves, of which 4 set on telescopic rails, of which 2 are presentation shelves
- Freezer compartment**
- 5 drawers, of which 2 set on roller tracks, VarioSpace
 - IceMaker with fixed 3/4" water connection
 - Ice cube production in 24 hrs: 1.2 kg
 - Ice cube reservoir: 1.8 kg
 - LED lighting
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - 2 cold storage accumulators
 - Safety glass fittings
- Key features**
- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
 - HardLine
 - Aluminium handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front and back
 - Reversible door hinge, left
 - Replaceable door seal
 - Concealed hinge with restricted opening

SKBes 4380
PremiumPlus

- Bio Fresh Plus
- Soft System
- Smart Steel
- Smart Device ready
- Soft-Telescopic

Energy efficiency class:
Energy consumption year/24 hrs: 133/0.364 kWh ¹
Total volume ² : 371 l (Fridge: 235.7 l/BioFresh compartment: 135.8 l)
Noise output/noise class: 36 dB(A)/C
Climate rating: SN-T (+10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display for fridge and BioFresh compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Key features**
- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
 - HardLine
 - Aluminium handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
 - 4 GlassLine storage shelves, of which one is divided into two parts
 - VarioSafe
 - Variable bottle shelf
 - LED ceiling lighting with dimmer function
 - LED BioFresh lighting
 - LED rear wall lighting
 - BioFresh-Plus with Fish & Seafood-Box
 - 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

SBNes 4285
Premium

- Bio Fresh
- Duo Cooling
- No Frost
- Soft System
- Ice Maker
- Smart Steel
- Smart Device ready

Energy efficiency class:
Energy consumption year/24 hrs: 171/0.468 kWh ¹
Total volume ² : 311 l (BioFresh compartment: 179.1 l/Freezer compartment: 132.8 l)
Noise output/noise class: 36 dB(A)/C
Climate rating: SN-T (+10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display for BioFresh and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, quantity-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Freezer compartment**
- 5 drawers, of which 2 set on roller tracks, VarioSpace
 - IceMaker with fixed 3/4" water connection
 - Ice cube production in 24 hrs: 1.2 kg
 - Ice cube reservoir: 1.8 kg
 - LED lighting
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - 2 cold storage accumulators
 - Safety glass fittings
- Key features**
- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
 - HardLine
 - Aluminium handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinge, left
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - with bottle holder
 - 2 GlassLine shelves in the BioFresh compartment, of which 1 is divided into two parts
 - LED ceiling lighting with dimmer function
 - LED BioFresh lighting
 - 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe

SKes 4370
Premium

- Bio Cool
- Soft System
- Smart Steel
- Smart Device ready

Energy efficiency class:
Energy consumption year/24 hrs: 78/0.213 kWh ¹
Total volume ² : 395 l
Noise output/noise class: 36 dB(A)/C
Climate rating: SN-T (+10 °C to +43 °C)
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹

- Controls**
- 2.4" TFT-colour display behind-the-door, touch electronic
 - Digital temperature display
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Key features**
- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
 - HardLine
 - Aluminium handle with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge compartment**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
 - 6 GlassLine storage shelves, of which one is divided into two parts
 - VarioSafe
 - Bottle shelf
 - LED ceiling lighting with dimmer function
 - 2 BioCool-Boxes on telescopic rails

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBSes 8773
Premium



SKBes 4370
Premium



←121→



SGNBs 4385
Premium



←121→



SKBbs 4370
Premium

SGNes 4375
Premium



Energy efficiency class: ¹

Energy consumption year/24 hrs: 198/0.542 kWh¹

Total volume²: 276 l

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

Energy efficiency class: ¹

Energy consumption year/24 hrs: 133/0.364 kWh¹

Total volume²: 372 l (Fridge: 235.7 l/BioFresh compartment: 137.2 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

SGNBs 4385
Premium



Energy efficiency class: ¹

Energy consumption year/24 hrs: 198/0.542 kWh¹

Total volume²: 276 l

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 9 drawers, of which 5 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 0.8 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinge, left
- Replaceable door seal
- Concealed hinge with restricted opening

Energy efficiency class: ¹

Energy consumption year/24 hrs: 133/0.364 kWh¹

Total volume²: 372 l (Fridge: 235.7 l/BioFresh compartment: 137.2 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Key features

- Side wall heating left, suitable for combination with other refrigerators, freezers and/or wine appliances
- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Side-by-Side fridge-freezers



SBSesf 7212
Comfort



←121→

SBS 7212
Comfort



←121→

SGNesf 3063
Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 307/0.841 kWh

Total volume²: 268 l

Noise output/noise class: 41 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185.2/60/63

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Fixed door hinge, left

SKesf 4240
Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 151/0.413 kWh

Total volume²: 386 l

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185.2/60/63

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on telescopic rails

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Fixed door hinge, right

SGN 3063
Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 307/0.841 kWh

Total volume²: 268 l

Noise output/noise class: 41 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 185.2/60/63

Controls

- MagicEye, key electronic
- LED temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- Safety glass fittings

Key features

- Side wall heating right, suitable for combination with other refrigerators, freezers and/or wine appliances
- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Fixed door hinge, left

SK 4240
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 151/0.413 kWh

Total volume²: 386 l

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 185.2/60/63

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 7 GlassLine storage shelves, of which one is divided into two parts
- LED ceiling lighting
- 2 fruit and vegetable drawers on telescopic rails

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Fixed door hinge, right

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Frenchdoor fridge-freezer



CBNes 6256



Both **BioFresh drawers** are mounted on telescopic rails which extend effortlessly providing easy access to and a full view of your food. The lateral LED lights ensure perfect illumination of the drawers. The integrated glass shelf and bottle shelf provides dual purpose storage solutions depending on your requirements.



The **drawers on telescopic runners** are high-quality, smooth-running and convenient to use, even when heavily filled. They ensure an ideal overview and plenty of space for storage.



← 91 →

CBNes 6256 PremiumPlus



Energy efficiency class: **F**

Energy consumption year / 24 hrs: 341 / 0.934 kWh

Total volume²: 522 l

(Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 159.5 l)

Noise output / noise class: 42 dB(A) / D

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: Stainless steel / stainless steel

Exterior dimensions in cm (h / w / d): 203.9 / 91 / 61.5

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, adjustable egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

Key features

- HardLine
- Aluminium handles
- Front ventilation
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Door hinge left fixed / right fixed
- Replaceable door seal

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 Ga.

Fridge-freezers



CBNes 5778

Our fridge-freezers: an overview

Liebherr's extensive range of fridge-freezers offers the ideal solution for almost everyone – whatever your demands and needs are. Our fridge-freezers offer innovative features such as BioFresh or BioCool and NoFrost or SmartFrost. Once you have made your preferred choice, all of our appliances are available with a variety of fittings and come in various sizes and colours.

Bio Fresh

When stored under BioFresh conditions, at just above 0 °C and at the ideal humidity level, fruit, vegetables, meat, fish and dairy products retain their nutrients, delicate flavour, and appetising appearance for much longer than they do under normal fridge conditions.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient to use and it ensures that stored food is clearly visible.

No Frost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

SmartFrost offers great convenience: the freezer compartment seldom requires defrosting, and the interior and frozen food frost over far less. In addition, the smooth interior walls are easy to clean.



Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, longterm storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Find out more about NoFrost: nofrost.liebherr.com



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy to clean. Freezer drawers and glass shelves are made of safety glass and can be removed easily.



Bio Fresh

BioFresh guarantees the perfect climate for extra long freshness. A temperature slightly above 0 °C and ideal air humidity maintain the vitamin and mineral content and appetising appearance of fruit and vegetables, meat, fish and milk products significantly longer than in a standard fridge.

BioFresh-Plus offers even more flexibility for the individual storage of food. The adjustable temperature range of 0 °C and -2 °C keeps various food, such as fruit, vegetables, fish and seafood, as well as meat and dairy products, fresh for significantly longer than in a conventional refrigeration compartment. The BioFresh-Plus safe includes a versatile Fish & Seafood-Safe.



Find out more about BioFresh: biofresh.liebherr.com



Bio Fresh Plus



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



LED

Maintenance-free and energy efficient: long-life **LEDs** provide perfect illumination of the interior. LEDs emit very little heat, which ensures that fresh food is always optimally stored. The sophisticated integrated lighting design ensures maximum use of the interior space.



Bio Cool

The **BioCool-Box** allows regulation of the humidity level within the refrigerator compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clearly visible. The humidity level in the BioCool-Box is regulated using a slide control.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail




The **sturdy handle** with its refined, premium quality appearance and an **integrated opening mechanism** ensures easy and effortless opening of the door.



Duo Cooling

With two independently controlled cooling circuits, **DuoCooling** controls the temperature in fridge-freezers with precision. There is no air exchange between the fridge and freezer compartments, odour transfer is prevented and stored food does not dry out. Also, the refrigeration compartment can be switched off while the freezer compartment continues operating. This can be useful, for example, when going on holiday.



BLU Performance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

- 1. Power connection for appliance plug
- 2. Functional wall spacer to maintain wall clearance and allow connection
- 3. Variable speed compressor
- 4. Plinth fan with noise-damping
- 5. Condenser
- 6. Defrost water drain



Smart Steel

SmartSteel significantly reduces the visibility of fingerprints. The high-quality stainless steel finish makes SmartSteel surfaces particularly easy-to-clean and far more scratch-resistant.



Freezer drawers and toughened glass shelves can be removed. **VarioSpace** – the practical storage solution for larger items.



The **LED BioFresh lighting** is placed at the back of the dividing shelf. Energy-efficient, long-life and maintenance-free LEDs provide perfect illumination for the opened BioFresh drawers and guarantee that the stored food is clearly visible.



The high-resolution, high-contrast **7" TFT display** is integrated into the door and offers individual setting options thanks to an intuitive and user-friendly menu navigation system. Appliances can be adapted to specific customer requirements using preset programmes, thereby ensuring optimal food storage.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail

LED



Soft-Telescopic

The BioFresh safes with **SoftTelescopic** provide a convenient, self-retracting system with soft closing, making their daily use both practical and secure.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated charcoal filter that is integrated into the fan purifies circulating air and quickly traps odours.



The **LED rear wall lighting** is integrated at the back of the dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the refrigerator compartment, from top to bottom to completely illuminate the interior and provide a constant, perfectly lit storage environment.



Soft System

The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°. Furthermore, the opening angle of the doors on all BluPerformance models is restricted to 115° to prevent damage to adjacent furniture and to the doors themselves.



The high-resolution, high-contrast **2.4" touch-screen display** is integrated behind the door and enables accurate temperature settings.




Dual purpose storage with the **integrated glass shelf and bottle shelf**. One conveniently stores beneath the other when not in use. When using the bottle shelf, move the door rack upwards to allow the storage of taller bottles.



The automatic **SuperFrost function** makes freezing food simple and energy efficient. It rapidly lowers the temperature to -32 °C to create the coldness levels required to preserve vitamins during freezing. The automatic **SuperCool function** lowers the refrigerator temperature to +2 °C for a defined period of 3, 6, 9 or 12 hours, offering flexibility according to the amount of food stored.

The features shown are model dependent; look for these features in your model choice.

Fridge-freezers



CBNes 5778 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Smart Steel	Smart Device ready	Soft-Telescopic
Energy efficiency class: C ¹	Energy consumption year/24 hrs: 187/0.512 kWh ¹							
Total volume ² : 392 l	(Fridge: 168.5 l/BioFresh compartment: 112.6 l/Freezer compartment: 111.6 l)							
Noise output/noise class: 35 dB(A)/B SuperSilent	Climate rating: SN-T (+10 °C to +43 °C)							
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel	Exterior dimensions in cm (h/w/d): 201/70/66.5 ¹							

Controls	Freezer compartment ****
<ul style="list-style-type: none"> 7" TFT-colour display in-the-door, touch electronic Digital temperature display for fridge, BioFresh and freezer compartments SmartDeviceBox: as an optional accessory Automatic SuperCool (time restricted) Automatic SuperFrost, quantity-controlled FrostControl Warning signal in case of fault: visual and acoustic Door alarm: visual and acoustic 	<ul style="list-style-type: none"> 3 drawers, of which 2 set on roller tracks, VarioSpace Ice cube tray with lid LED lighting Temperature rise time: 16 h Freezing capacity in 24 hrs: 9 kg 2 cold storage accumulators Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling with FreshAir activated charcoal filter Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish 3 GlassLine storage shelves, of which one is divided into two parts Variable bottle shelf LED ceiling lighting with dimmer function LED BioFresh lighting LED rear wall lighting 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe 	<ul style="list-style-type: none"> HardLine Aluminium handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles, front and at back, transport castors at back Height-adjustable feet at front Reversible door hinging Replaceable door seal Concealed hinge with restricted opening
	Colour / material options: CBNbe 5778 in beige

CBNef 5735 Comfort	Bio Fresh	Duo Cooling	No Frost	Smart Steel	Smart Device ready
Energy efficiency class: D ¹	Energy consumption year/24 hrs: 234/0.641 kWh ¹				
Total volume ² : 392 l	(Fridge: 168.5 l/BioFresh compartment: 112.6 l/Freezer compartment: 111.6 l)				
Noise output/noise class: 36 dB(A)/C	Climate rating: SN-T (+10 °C to +43 °C)				
Door/side walls: Stainless steel with SmartSteel/silver	Exterior dimensions in cm (h/w/d): 201/70/66.5 ¹				

Controls	Freezer compartment ****
<ul style="list-style-type: none"> 2.4" TFT-monochrome display behind-the-door, touch electronic Digital temperature display for fridge, BioFresh and freezer compartments SmartDeviceBox: as an optional accessory Automatic SuperCool (time restricted) Automatic SuperFrost, time-controlled FrostControl Warning signal in case of fault: visual and acoustic Door alarm: visual and acoustic 	<ul style="list-style-type: none"> 3 drawers, VarioSpace Ice cube tray with lid Temperature rise time: 16 h Freezing capacity in 24 hrs: 9 kg Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling with FreshAir activated charcoal filter Comfort GlassLine storage shelf with bottle holder, egg tray 3 GlassLine storage shelves, of which one is divided into two parts Integrated bottle shelf LED ceiling lighting 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe 	<ul style="list-style-type: none"> HardLine Aluminium handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles, front and at back, transport castors at back Height-adjustable feet at front Reversible door hinging Replaceable door seal Concealed hinge with restricted opening

CBNes 4898 PremiumPlus	Bio Fresh Plus	Duo Cooling	No Frost	Super Silent	Soft System	Ice Maker	Smart Steel	Smart Device ready	Soft-Telescopic
Energy efficiency class: C ¹	Energy consumption year/24 hrs: 182/0.498 kWh ¹								
Total volume ² : 349 l	(Fridge: 147.5 l/BioFresh compartment: 97.9 l/Freezer compartment: 104.2 l)								
Noise output/noise class: 35 dB(A)/B SuperSilent	Climate rating: SN-T (+10 °C to +43 °C)								
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel	Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹								

Controls	Freezer compartment ****
<ul style="list-style-type: none"> 7" TFT-colour display in-the-door, touch electronic Digital temperature display for fridge, BioFresh and freezer compartments SmartDeviceBox: as an optional accessory Automatic SuperCool (time restricted) Automatic SuperFrost, quantity-controlled FrostControl Warning signal in case of fault: visual and acoustic Door alarm: visual and acoustic 	<ul style="list-style-type: none"> 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe, 1 FlexSystem 4 drawers, of which 1 set on roller tracks, VarioSpace IceMaker with fixed 3/4" water connection Ice cube production in 24 hrs: 1.2 kg Ice cube reservoir: 1.8 kg LED lighting Temperature rise time: 16 h Freezing capacity in 24 hrs: 9 kg 2 cold storage accumulators Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling with FreshAir activated charcoal filter Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish 3 GlassLine storage shelves, of which one is divided into two parts Variable bottle shelf LED ceiling lighting with dimmer function LED BioFresh lighting LED rear wall lighting BioFresh-Plus with Fish & Seafood-Box 	<ul style="list-style-type: none"> Aluminium handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles, front and at back, transport castors at back Height-adjustable feet at front Reversible door hinging Replaceable door seal Concealed hinge with restricted opening

CBNies 4878 Premium	Bio Fresh	Duo Cooling	No Frost	Super Silent	Soft System	Smart Steel	Smart Device	Soft-Telescopic
Energy efficiency class: C ¹	Energy consumption year/24 hrs: 182/0.498 kWh ¹							
Total volume ² : 351 l	(Fridge: 147.5 l/BioFresh compartment: 100.9 l/Freezer compartment: 103.5 l)							
Noise output/noise class: 35 dB(A)/B SuperSilent	Climate rating: SN-T (+10 °C to +43 °C)							
Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel	Exterior dimensions in cm (h/w/d): 201/60/66.5 ¹							

Controls	Freezer compartment ****
<ul style="list-style-type: none"> 7" TFT-colour display in-the-door, touch electronic Digital temperature display for fridge, BioFresh and freezer compartments SmartDeviceBox included Automatic SuperCool (time restricted) Automatic SuperFrost, quantity-controlled FrostControl Warning signal in case of fault: visual and acoustic Door alarm: visual and acoustic 	<ul style="list-style-type: none"> 3 drawers, of which 2 set on roller tracks, VarioSpace Ice cube tray with lid LED lighting Temperature rise time: 16 h Freezing capacity in 24 hrs: 9 kg 2 cold storage accumulators Safety glass fittings
Fridge and BioFresh compartments	Key features
<ul style="list-style-type: none"> PowerCooling with FreshAir activated charcoal filter Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish 3 GlassLine storage shelves, of which one is divided into two parts Variable bottle shelf LED ceiling lighting with dimmer function LED BioFresh lighting LED rear wall lighting 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe 	<ul style="list-style-type: none"> Aluminium handles with integrated opening mechanism Versatile installation due to front ventilation Transport handles, front and at back, transport castors at back Height-adjustable feet at front Reversible door hinging Replaceable door seal Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

CBNbs 4878
Premium

- Bio Fresh
- Duo Cooling
- No Frost
- Super Silent
- Soft System
- Black Steel
- Smart Device ready
- Soft-Telescopic

Energy efficiency class: ¹
 Energy consumption year / 24 hrs: 182 / 0.498 kWh ¹
 Total volume²: 351 l
 (Fridge: 147.5 l / BioFresh compartment: 100.9 l / Freezer compartment: 103.5 l)
 Noise output / noise class: 35 dB(A) / B SuperSilent
 Climate rating: SN-T (+10 °C to +43 °C)
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h / w / d): 201 / 60 / 66.5 ¹

- Controls**
- 7" TFT-colour display in-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, quantity-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, of which 2 set on roller tracks, VarioSpace
 - Ice cube tray with lid
 - LED lighting
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - 2 cold storage accumulators
 - Safety glass fittings
- Key features**
- HardLine
 - Aluminium handles with integrated opening mechanism
 - Versatile installation due to front ventilation
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Variable bottle shelf
 - LED ceiling lighting with dimmer function
 - LED BioFresh lighting
 - LED rear wall lighting
 - 2 BioFresh-Safes with SoftTelescopic, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe

CBNbs 4835
Comfort

- Bio Fresh
- Duo Cooling
- No Frost
- Super Silent
- Black Steel
- Smart Device ready

Energy efficiency class: ¹
 Energy consumption year / 24 hrs: 227 / 0.621 kWh ¹
 Total volume²: 351 l
 (Fridge: 149.2 l / BioFresh compartment: 99.1 l / Freezer compartment: 103.5 l)
 Noise output / noise class: 33 dB(A) / B SuperSilent
 Climate rating: SN-T (+10 °C to +43 °C)
 Door / side walls: BlackSteel with SmartSteel / BlackSteel with SmartSteel
 Exterior dimensions in cm (h / w / d): 201 / 60 / 66.5 ¹

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, time-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
 - Ice cube tray with lid
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - Safety glass fittings
- Key features**
- HardLine
 - Aluminium handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Comfort GlassLine storage shelf with bottle holder, egg tray
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Integrated bottle shelf
 - LED ceiling lighting
 - 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe

CBNeF 4835
Comfort

- Bio Fresh
- Duo Cooling
- No Frost
- Super Silent
- Smart Steel
- Smart Device ready

Energy efficiency class: ¹
 Energy consumption year / 24 hrs: 227 / 0.621 kWh ¹
 Total volume²: 351 l
 (Fridge: 149.2 l / BioFresh compartment: 99.1 l / Freezer compartment: 103.5 l)
 Noise output / noise class: 33 dB(A) / B SuperSilent
 Climate rating: SN-T (+10 °C to +43 °C)
 Door / side walls: Stainless steel with SmartSteel / silver
 Exterior dimensions in cm (h / w / d): 201 / 60 / 66.5 ¹

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, time-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
 - Ice cube tray with lid
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - Safety glass fittings
- Key features**
- HardLine
 - Aluminium handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Comfort GlassLine storage shelf with bottle holder, egg tray
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Integrated bottle shelf
 - LED ceiling lighting
 - 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe

CBN 4835
Comfort

- Bio Fresh
- Duo Cooling
- No Frost
- Super Silent
- Smart Device ready

Energy efficiency class: ¹
 Energy consumption year / 24 hrs: 227 / 0.621 kWh ¹
 Total volume²: 351 l
 (Fridge: 149.2 l / BioFresh compartment: 99.1 l / Freezer compartment: 103.5 l)
 Noise output / noise class: 33 dB(A) / B SuperSilent
 Climate rating: SN-T (+10 °C to +43 °C)
 Door / side walls: white / white
 Exterior dimensions in cm (h / w / d): 201 / 60 / 66.5 ¹

- Controls**
- 2.4" TFT-monochrome display behind-the-door, touch electronic
 - Digital temperature display for fridge, BioFresh and freezer compartments
 - SmartDeviceBox: as an optional accessory
 - Automatic SuperCool (time restricted)
 - Automatic SuperFrost, time-controlled
 - FrostControl
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: visual and acoustic
- Freezer compartment**
- 3 drawers, VarioSpace
 - Ice cube tray with lid
 - Temperature rise time: 16 h
 - Freezing capacity in 24 hrs: 9 kg
 - Safety glass fittings
- Key features**
- HardLine
 - Slimline handles with integrated opening mechanism
 - Versatile installation due to front ventilation
 - Transport handles, front and at back, transport castors at back
 - Height-adjustable feet at front
 - Reversible door hinging
 - Replaceable door seal
 - Concealed hinge with restricted opening
- Fridge and BioFresh compartments**
- PowerCooling with FreshAir activated charcoal filter
 - Comfort GlassLine storage shelf with bottle holder, egg tray
 - 3 GlassLine storage shelves, of which one is divided into two parts
 - Integrated bottle shelf
 - LED ceiling lighting
 - 2 BioFresh-Safes on telescopic rails, of which 1 can be set variably to Fruit & Vegetable-Safe or DrySafe

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 75 →



← 70 →



← 70 →



← 60 →



CNPesf 4613
Comfort

Bio Cool No Frost Smart Steel

Energy efficiency class: ¹

Energy consumption year/24 hrs: 281/0.769 kWh¹

Total volume²: 427 l (Fridge: 338.5 l/Freezer compartment: 88.6 l)

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 186/75/63¹

Controls

- MagicEye behind-the-door, key electronic
- LED temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- SwingLine design
- Stainless steel slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

CNeF 5745
Comfort

Bio Cool Duo Cooling No Frost Ice Maker Smart Steel Smart Device ready

Energy efficiency class: ¹

Energy consumption year/24 hrs: 210/0.575 kWh¹

Total volume²: 411 l (Fridge: 299.2 l/Freezer compartment: 112.2 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 201/70/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 3 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 2.2 kg
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

CNeF 5735
Comfort

Bio Cool Duo Cooling No Frost Smart Steel Smart Device ready

Energy efficiency class: ¹

Energy consumption year/24 hrs: 210/0.575 kWh¹

Total volume²: 410 l (Fridge: 299.2 l/Freezer compartment: 111.6 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 201/70/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

CNeF 4845
Comfort

Bio Cool Duo Cooling No Frost Ice Maker Smart Steel Smart Device ready

Energy efficiency class: ¹

Energy consumption year/24 hrs: 204/0.558 kWh¹

Total volume²: 366 l (Fridge: 262.3 l/Freezer compartment: 104.0 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 201/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 4 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 1.8 kg
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



CNbs 4015
Comfort

Duo Cooling No Frost Black Steel Smart Device ready

Energy efficiency class: **E**¹

Energy consumption year/24 hrs: 245/0.671 kWh¹

Total volume²: 365 l (Fridge: 270.5 l/Freezer compartment: 95.3 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 201.1/60/62.5¹

CNbe 4015
Comfort

Duo Cooling No Frost Smart Device ready

Energy efficiency class: **E**¹

Energy consumption year/24 hrs: 245/0.671 kWh¹

Total volume²: 365 l (Fridge: 270.5 l/Freezer compartment: 95.3 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: beige/beige

Exterior dimensions in cm (h/w/d): 201.1/60/62.5¹

CN 3915
Comfort

Duo Cooling No Frost Smart Device ready

Energy efficiency class: **E**¹

Energy consumption year/24 hrs: 260/0.712 kWh¹

Total volume²: 350 l (Fridge: 222.4 l/Freezer compartment: 128.3 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 201.1/60/62.5¹

CNfr 4335
Comfort

Bio Cool Duo Cooling No Frost Colour Line Smart Device ready

Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 200/0.547 kWh¹

Total volume²: 325 l (Fridge: 222.3 l/Freezer compartment: 103.5 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: FireRed/FireRed

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour/material options:
CNef 4015 with Stainless steel front

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Colour/material options:
CN 4015 in white

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 fruit and vegetable drawers on roller tracks

Freezer compartment ********

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on roller tracks

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- HardLine
- Aluminium handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

CNPel 4813



Energy efficiency class: **D**¹
 Energy consumption year/24 hrs: 201/0.550 kWh¹
 Total volume²: 344 l (Fridge: 243.2 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

CNef 4813



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 251/0.687 kWh¹
 Total volume²: 344 l (Fridge: 243.2 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

CNel 4813



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 251/0.687 kWh¹
 Total volume²: 344 l (Fridge: 243.2 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

CN 4813



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 251/0.687 kWh¹
 Total volume²: 344 l (Fridge: 243.2 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

CNPel 4313



Energy efficiency class: **D**¹
 Energy consumption year/24 hrs: 197/0.539 kWh¹
 Total volume²: 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 186.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

CNel 4313



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 246/0.674 kWh¹
 Total volume²: 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 186.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 8 kg

CNel 4213



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 248/0.679 kWh¹
 Total volume²: 300 l (Fridge: 165.6 l/Freezer compartment: 134.8 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 186.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

CN 4213



Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 248/0.679 kWh¹
 Total volume²: 300 l (Fridge: 165.6 l/Freezer compartment: 134.8 l)
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 186.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- Bottle shelf
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ********

- 4 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.





← 60 →



← 60 →



← 60 →



← 60 →

CNno 4313	Duo Cooling	No Frost	Colour Line
Energy efficiency class:			
Energy consumption year/24 hrs: 246/0.674 kWh ¹			
Total volume ² : 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)			
Noise output/noise class: 40 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: NeonOrange/NeonOrange			
Exterior dimensions in cm (h/w/d): 186.1/60/65.5 ¹			

CNkw 4313	Duo Cooling	No Frost	Colour Line
Energy efficiency class:			
Energy consumption year/24 hrs: 246/0.674 kWh ¹			
Total volume ² : 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)			
Noise output/noise class: 40 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: KiwiGreen/KiwiGreen			
Exterior dimensions in cm (h/w/d): 186.1/60/65.5 ¹			

CNfb 4313	Duo Cooling	No Frost	Colour Line
Energy efficiency class:			
Energy consumption year/24 hrs: 246/0.674 kWh ¹			
Total volume ² : 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)			
Noise output/noise class: 40 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: FrozenBlue/FrozenBlue			
Exterior dimensions in cm (h/w/d): 186.1/60/65.5 ¹			

CNbe 4313	Duo Cooling	No Frost	
Energy efficiency class:			
Energy consumption year/24 hrs: 246/0.674 kWh ¹			
Total volume ² : 310 l (Fridge: 209.4 l/Freezer compartment: 100.9 l)			
Noise output/noise class: 40 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: beige/beige			
Exterior dimensions in cm (h/w/d): 186.1/60/65.5 ¹			

Controls	Key features
<ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic 	<ul style="list-style-type: none"> · HardLine · Vertical recessed handles · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal
Fridge compartment	
<ul style="list-style-type: none"> · PowerCooling · Plastic door shelves with bottle holder, egg tray · 4 GlassLine storage shelves · Bottle shelf · LED ceiling lighting · 1 spacious fruit and vegetable drawer 	
Freezer compartment	
<ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 12 h · Freezing capacity in 24 hrs: 8 kg 	

Controls	Key features
<ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic 	<ul style="list-style-type: none"> · HardLine · Vertical recessed handles · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal
Fridge compartment	
<ul style="list-style-type: none"> · PowerCooling · Plastic door shelves with bottle holder, egg tray · 4 GlassLine storage shelves · Bottle shelf · LED ceiling lighting · 1 spacious fruit and vegetable drawer 	
Freezer compartment	
<ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 12 h · Freezing capacity in 24 hrs: 8 kg 	

Controls	Key features
<ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic 	<ul style="list-style-type: none"> · HardLine · Vertical recessed handles · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal
Fridge compartment	
<ul style="list-style-type: none"> · PowerCooling · Plastic door shelves with bottle holder, egg tray · 4 GlassLine storage shelves · Bottle shelf · LED ceiling lighting · 1 spacious fruit and vegetable drawer 	
Freezer compartment	
<ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 12 h · Freezing capacity in 24 hrs: 8 kg 	

Controls	Key features
<ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · Digital temperature display for fridge and freezer compartments · Automatic SuperFrost, time-controlled · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic 	<ul style="list-style-type: none"> · HardLine · Vertical recessed handles · Versatile installation due to front ventilation · Transport handles at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal
Fridge compartment	
<ul style="list-style-type: none"> · PowerCooling · Plastic door shelves with bottle holder, egg tray · 4 GlassLine storage shelves · Bottle shelf · LED ceiling lighting · 1 spacious fruit and vegetable drawer 	
Freezer compartment	Colour/material options: CN 4313 in white
<ul style="list-style-type: none"> · 3 drawers, VarioSpace · Ice cube tray · Temperature rise time: 12 h · Freezing capacity in 24 hrs: 8 kg 	

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Fridge-freezers



CPel 4813 Duo Cooling Smart Frost Stainless Steel Look

Energy efficiency class: D¹

Energy consumption year/24 hrs: 191/0.523 kWh¹

Total volume²: 343 l (Fridge: 243.2 l/Freezer compartment: 99.9 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 201.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Colour/material options:
CP 4813 in white

CPel 4313 Duo Cooling Smart Frost Stainless Steel Look

Energy efficiency class: D¹

Energy consumption year/24 hrs: 187/0.512 kWh¹

Total volume²: 309 l (Fridge: 209.4 l/Freezer compartment: 99.9 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 186.1/60/65.5¹

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Key features

- HardLine
- Vertical recessed handles
- Versatile installation due to front ventilation
- Transport handles at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

Fridge compartment

- PowerCooling
- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 15 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Colour/material options:
CP 4313 in white

CUef 331 Smart Frost Smart Steel

Energy efficiency class: F¹

Energy consumption year/24 hrs: 280/0.767 kWh¹

Total volume²: 296 l

(Fridge: 212.4 l/Freezer compartment: 84.1 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 181.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUel 331 Smart Frost Stainless Steel Look

Energy efficiency class: F¹

Energy consumption year/24 hrs: 280/0.767 kWh¹

Total volume²: 296 l

(Fridge: 212.4 l/Freezer compartment: 84.1 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 181.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CU 331 Smart Frost

Energy efficiency class: F¹

Energy consumption year/24 hrs: 280/0.767 kWh¹

Total volume²: 296 l

(Fridge: 212.4 l/Freezer compartment: 84.1 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 181.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ****

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.


Fridge-freezers



← 55 →



← 55 →



← 55 →

CUNo 2831



Energy efficiency class:
Energy consumption year/24 hrs: 240/0.657 kWh ¹
Total volume ² : 265 l
(Fridge: 212.4 l/Freezer compartment: 53.5 l)
Noise output/noise class: 38 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: NeonOrange/NeonOrange
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUkw 2831



Energy efficiency class:
Energy consumption year/24 hrs: 240/0.657 kWh ¹
Total volume ² : 265 l
(Fridge: 212.4 l/Freezer compartment: 53.5 l)
Noise output/noise class: 38 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: KiwiGreen/KiwiGreen
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CUfb 2831



Energy efficiency class:
Energy consumption year/24 hrs: 240/0.657 kWh ¹
Total volume ² : 265 l
(Fridge: 212.4 l/Freezer compartment: 53.5 l)
Noise output/noise class: 38 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: FrozenBlue/FrozenBlue
Exterior dimensions in cm (h/w/d): 161.2/55/63 ¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



CUel 281

Fridge-freezers



CUel 281



Energy efficiency class: **F**¹
 Energy consumption year/24 hrs: 240/0.657 kWh¹
 Total volume²: 265 l (Fridge: 212.4 l/Freezer compartment: 53.5 l)
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-ST (+10 °C to +38 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 161.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:

CU 281 in white

CUel 231



Energy efficiency class: **F**¹
 Energy consumption year/24 hrs: 241/0.660 kWh¹
 Total volume²: 210 l (Fridge: 156.5 l/Freezer compartment: 53.5 l)
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-ST (+10 °C to +38 °C)
 Door/side walls: Stainless steel look/silver
 Exterior dimensions in cm (h/w/d): 137.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 18 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features


- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:

CU 231 in white

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



CTPel 251 Smart Frost Stainless Steel Look

Energy efficiency class: ¹

Energy consumption year/24 hrs: 231/0.632 kWh¹

Total volume²: 270 l (Fridge: 218.6 l/Freezer compartment: 51.5 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 157.1/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- Ice cube tray
- Temperature rise time: 20 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:
CTPel 251 in white

CTPel 231 Smart Frost Stainless Steel Look

Energy efficiency class: ¹

Energy consumption year/24 hrs: 212/0.580 kWh¹

Total volume²: 233 l (Fridge: 189.5 l/Freezer compartment: 43.8 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel look/silver

Exterior dimensions in cm (h/w/d): 140.1/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- VarioSpace
- Ice cube tray
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

CTP 231 Smart Frost

Energy efficiency class: ¹

Energy consumption year/24 hrs: 212/0.580 kWh¹

Total volume²: 233 l (Fridge: 189.5 l/Freezer compartment: 43.8 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 140.1/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- VarioSpace
- Ice cube tray
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Height-adjustable feet at front
- Reversible door hinging

CTP 211 Smart Frost

Energy efficiency class: ¹

Energy consumption year/24 hrs: 198/0.542 kWh¹

Total volume²: 196 l (Fridge: 152.2 l/Freezer compartment: 43.8 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 124.1/55/63¹

Controls

- Mechanical control in the interior, control dial
- Individually regulated cooling circuits: 1

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 3 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- VarioSpace
- Ice cube tray
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- SwingLine design
- Recessed handles
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Fridges



KBbs 4370



Our fridges: an overview

Liebherr fridges excel with their impressive freshness technology. The range on offer extends from models featuring a classic vegetable compartment, to BioCool models with an adjustable humidity compartment, all the way to BioFresh appliances, which deliver the longest-lasting freshness. Whatever you're looking for, you're sure to find just the right fridge to meet your needs and requirements within Liebherr's comprehensive range - be it an upright or under counter appliance.

Bio Fresh

In the BioFresh compartments food retains its healthy vitamins, aroma and appetising appearance significantly longer than in a conventional fridge. Through its advanced technology the temperature is accurately maintained at around 0 °C.

Bio Cool

The BioCool-Box allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. It is convenient-to-use and it ensures that stored food is clear visibility.

Fridges



from page 76



from page 80

Under counter fridges



from page 87

Quality in every detail



The fresher your food, the better it is for a healthy diet. **BioFresh safes**, sited on telescopic rails, guarantee the perfect environment for greater freshness. When stored at a temperature of just over 0 °C and at just the right humidity level, fruit and vegetables, fish, meat and dairy products all retain their vitamins, delicate flavours and appetising appearance for far longer than in a conventional fridge compartment.



The high-performance **PowerCooling** system ensures that newly stored produce is quickly cooled and an even temperature is maintained throughout the interior. An electronic door switch turns off the fan when the door is opened, saving energy. The **FreshAir** activated charcoal filter that is integrated into the fan purifies circulating air and quickly traps odours.



The integrated **SoftSystem** mechanism cushions door closure even when the door shelves are fully stocked; it ensures gentle closing and prevents bottles, jars and packets or food from falling out of the door. The door closes automatically from an opening angle of about 35°.



The **BioCool-Box** allows regulation of the humidity level within the fridge compartment so that food keeps fresh for longer. The BioCool-Box is positioned on smooth-running telescopic rails; it is convenient to use and it ensures that stored food is clear visibility. The humidity level in the BioCool-Box is regulated using a slider.



The high-resolution, high-contrast **2.4" touch-screen display** is integrated behind the door and enables intuitive temperature setting.



The useful **VarioSafe** makes it easy to view and organise a variety of stored items: it is the ideal place to store smaller packets, tubes and glass jars. The VarioSafe can also be inserted at a different height to accommodate different containers.

The features shown are model dependent; look for these features in your model choice.


Quality in every detail



LED

The **LED rear wall lighting** is integrated into the rear section of the horizontal dividing shelf. Energy-efficient, environmentally friendly and maintenance-free LEDs optimally illuminate the back section of the fridge compartment, from top to bottom and provide high-quality illumination.

The features shown are model dependent; look for these features in your model choice.



BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug 2. Functional wall spacer to maintain wall clearance and allow connection
3. Variable speed compressor 4. Plinth fan with noise-damping 5. Condenser 6. Defrost water drain



The **replaceable door seal** helps to keep food safely stored and contributes to optimum hygiene. It is designed to match the appliance door or housing colour, and can be easily fitted, cleaned and replaced.



The distinctive **GlassLine** interior conveys build and finish quality. The shelves are made of safety glass. The split, slide-under glass shelf can be located at different heights as required.



← 60 →



← 60 →



← 60 →



← 60 →

KBbs 4374
Premium

Bio Fresh | Soft System | Black Steel | Smart Device ready | Soft-Telescopic

Energy efficiency class: **C**¹

Energy consumption year/24 hrs: 133/0.364 kWh¹

Total volume²: 344 l

(Fridge: 182.9 l/BioFresh compartment: 137.2 l/Freezer compartment: 24.1 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBes 4374
Premium

Bio Fresh | Soft System | Smart Steel | Smart Device ready | Soft-Telescopic

Energy efficiency class: **C**¹

Energy consumption year/24 hrs: 133/0.364 kWh¹

Total volume²: 344 l

(Fridge: 182.9 l/BioFresh compartment: 137.2 l/Freezer compartment: 24.1 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBies 4370
Premium

Bio Fresh | Soft System | Smart Steel | Smart Device | Soft-Telescopic

Energy efficiency class: **C**¹

Energy consumption year/24 hrs: 107/0.293 kWh¹

Total volume²: 372 l (Fridge: 235.7 l/BioFresh compartment: 137.2 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/Stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

KBbs 4370
Premium

Bio Fresh | Soft System | Black Steel | Smart Device ready | Soft-Telescopic

Energy efficiency class: **C**¹

Energy consumption year/24 hrs: 107/0.293 kWh¹

Total volume²: 372 l (Fridge: 235.7 l/BioFresh compartment: 137.2 l)

Noise output/noise class: 36 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: BlackSteel with SmartSteel/BlackSteel with SmartSteel

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Ice cube tray with lid
- Temperature rise time: 13 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Ice cube tray with lid
- Temperature rise time: 13 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Integrated bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED ceiling lighting with dimmer function
- LED BioFresh lighting
- LED rear wall lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

KBeF 4330
Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 133/0.364 kWh¹
 Total volume²: 371 l (Fridge: 234.5 l/BioFresh compartment: 137.2 l)
 Noise output/noise class: 37 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

KB 4330
Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 133/0.364 kWh¹
 Total volume²: 371 l (Fridge: 234.5 l/BioFresh compartment: 137.2 l)
 Noise output/noise class: 37 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

KBeF 3730
Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 131/0.358 kWh¹
 Total volume²: 323 l (Fridge: 186.5 l/BioFresh compartment: 137.2 l)
 Noise output/noise class: 37 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: Stainless steel with SmartSteel/silver
 Exterior dimensions in cm (h/w/d): 165/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Integrated bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

B 2830
Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 65/0.178 kWh¹
 Total volume²: 161 l
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 125/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

BioFresh compartment

- Ventilator
- LED lighting
- 5 BioFresh-Safes
- Cabinet can be adjusted from HydroSafe to DrySafe

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

Kef 4370 Premium	Bio Cool	Soft System	Smart Steel	Smart Device ready
Energy efficiency class:				
Energy consumption year/24 hrs: 78/0.213 kWh ¹				
Total volume ² : 395 l				
Noise output/noise class: 36 dB(A)/C				
Climate rating: SN-T (+10 °C to +43 °C)				
Door/side walls: Stainless steel with SmartSteel/silver				
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹				

Controls
<ul style="list-style-type: none"> · 2.4" TFT-colour display behind-the-door, touch electronic · Digital temperature display · SmartDeviceBox: as an optional accessory · Automatic SuperCool (time restricted) · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic
Fridge compartment
<ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Premium GlassLine storage shelf with bottle holder, VarioBoxes, adjustable egg tray, butter dish · 6 GlassLine storage shelves, of which one is divided into two parts · VarioSafe · Bottle shelf · LED ceiling lighting with dimmer function · 2 BioCool-Boxes on telescopic rails
Key features
<ul style="list-style-type: none"> · HardLine · Aluminium handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back, transport castors at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening

Kief 4330 Comfort	Bio Cool	Smart Steel	Smart Device
Energy efficiency class:			
Energy consumption year/24 hrs: 98/0.268 kWh ¹			
Total volume ² : 395 l			
Noise output/noise class: 37 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: Stainless steel with SmartSteel/silver			
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹			

Controls
<ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display · SmartDeviceBox included · Automatic SuperCool (time restricted) · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic
Fridge compartment
<ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, egg tray · 6 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 2 BioCool-Boxes on telescopic rails
Key features
<ul style="list-style-type: none"> · HardLine · Aluminium handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back, transport castors at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening

Kef 4330 Comfort	Bio Cool	Smart Steel	Smart Device ready
Energy efficiency class:			
Energy consumption year/24 hrs: 98/0.268 kWh ¹			
Total volume ² : 395 l			
Noise output/noise class: 37 dB(A)/C			
Climate rating: SN-T (+10 °C to +43 °C)			
Door/side walls: Stainless steel with SmartSteel/silver			
Exterior dimensions in cm (h/w/d): 185/60/66.5 ¹			

Controls
<ul style="list-style-type: none"> · 2.4" TFT-monochrome display behind-the-door, touch electronic · Digital temperature display · SmartDeviceBox: as an optional accessory · Automatic SuperCool (time restricted) · Warning signal in case of fault: visual and acoustic · Door alarm: visual and acoustic
Fridge compartment
<ul style="list-style-type: none"> · PowerCooling with FreshAir activated charcoal filter · Comfort GlassLine storage shelf with bottle holder, adjustable egg tray · 6 GlassLine storage shelves, of which one is divided into two parts · Bottle shelf · LED ceiling lighting · 2 BioCool-Boxes on telescopic rails
Key features
<ul style="list-style-type: none"> · HardLine · Aluminium handle with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles, front and at back, transport castors at back · Height-adjustable feet at front · Reversible door hinging · Replaceable door seal · Concealed hinge with restricted opening

K 4220 Comfort
Energy efficiency class:
Energy consumption year/24 hrs: 151/0.413 kWh
Total volume ² : 386 l
Noise output/noise class: 38 dB(A)/C
Climate rating: SN-T (+10 °C to +43 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 185.2/60/63

Controls
<ul style="list-style-type: none"> · MagicEye behind-the-door, key electronic · LED temperature display · Automatic SuperCool
Fridge compartment
<ul style="list-style-type: none"> · PowerCooling · Comfort GlassLine storage shelf with bottle holder, egg tray · 7 GlassLine storage shelves, of which one is divided into two parts · LED ceiling lighting · 2 fruit and vegetable drawers on telescopic rails
Key features
<ul style="list-style-type: none"> · SwingLine design · Slimline handles with integrated opening mechanism · Versatile installation due to front ventilation · Transport handles at back, transport castors at back · Height-adjustable feet at front · Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 60 →

Kef 3730
Comfort

Bio Cool Smart Steel Smart Device ready

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 93 / 0.254 kWh ¹

Total volume²: 346 l

Noise output / noise class: 37 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: Stainless steel with SmartSteel / silver

Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5 ¹

K 3730
Comfort

Bio Cool Smart Device ready

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 93 / 0.254 kWh ¹

Total volume²: 346 l

Noise output / noise class: 37 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 165 / 60 / 66.5 ¹

K 3130
Comfort

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 139 / 0.380 kWh ¹

Total volume²: 297 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: white / white

Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63.1 ¹

Ksl 3130
Comfort

Silver

Energy efficiency class: ¹

Energy consumption year / 24 hrs: 139 / 0.380 kWh ¹

Total volume²: 297 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: silver / silver

Exterior dimensions in cm (h / w / d): 144.7 / 60 / 63.1 ¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on telescopic rails

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool (time restricted)
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 1 BioCool-Box on telescopic rails

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 55 →



← 55 →



← 60 →



← 55 →

Ksl 2834
Comfort

Silver

Energy efficiency class:

Energy consumption year/24 hrs: 197/0.539 kWh¹

Total volume²: 250 l (Fridge: 229.8 l/Freezer compartment: 21.1 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: silver/silver

Exterior dimensions in cm (h/w/d): 140.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- SwingLine design
- Stainless steel slimline handle with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

KP 290
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 197/0.539 kWh¹

Total volume²: 250 l (Fridge: 229.8 l/Freezer compartment: 21.1 l)

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 140.2/55/63¹

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 4 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- 4-star freezer compartment
- Ice cube tray
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

K 2630
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 131/0.358 kWh¹

Total volume²: 248 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 125/60/63.1¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperCool

Fridge compartment

- PowerCooling
- Comfort GlassLine storage shelf with bottle holder, egg tray
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

Colour/material options:

Ksl 2630 in silver

K 230
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 126/0.345 kWh

Total volume²: 214 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 114/55/63

Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Plastic door shelves with bottle holder, egg tray
- 5 GlassLine storage shelves
- Bottle shelf
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingLine design
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



TP 1724

Under counter fridges



← 60 →



← 60 →



← 60 →

TP 1724 Comfort

Energy efficiency class:
Energy consumption year/24 hrs: 146/0.400 kWh ¹
Total volume ² : 143 l
(Fridge: 126.0 l/Freezer compartment: 17.6 l)
Noise output/noise class: 37 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/60.1/62.8 ¹

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

TP 1720 Comfort



Energy efficiency class:
Energy consumption year/24 hrs: 92/0.252 kWh ¹
Total volume ² : 145 l
Noise output/noise class: 35 dB(A)/B SuperSilent
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/60.1/62.8 ¹

Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

TPesf 1714 Comfort

Energy efficiency class:
Energy consumption year/24 hrs: 183/0.501 kWh ¹
Total volume ² : 143 l
(Fridge: 126.0 l/Freezer compartment: 17.6 l)
Noise output/noise class: 37 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: Stainless steel/silver
Exterior dimensions in cm (h/w/d): 85/60.1/60.8 ¹

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 60 →



← 60 →



← 60 →



← 55 →



← 55 →



← 55 →

TPesf 1710
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 115/0.315 kWh¹

Total volume²: 145 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: Stainless steel/silver

Exterior dimensions in cm (h/w/d): 85/60.1/60.8¹

T 1810
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 118/0.323 kWh

Total volume²: 161 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8

T 1714
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 183/0.501 kWh

Total volume²: 143 l

(Fridge: 126.0 l/Freezer compartment: 17.6 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/60.1/62.8

TP 1434
Comfort

Energy efficiency class:

Energy consumption year/24 hrs: 141/0.386 kWh¹

Total volume²: 120 l

(Fridge: 106.3 l/Freezer compartment: 14.5 l)

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/55.4/62.3¹

T 1700

Energy efficiency class:

Energy consumption year/24 hrs: 116/0.317 kWh

Total volume²: 149 l

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/55.4/62.3

T 1504

Energy efficiency class:

Energy consumption year/24 hrs: 180/0.493 kWh

Total volume²: 133 l

(Fridge: 116.9 l/Freezer compartment: 16.5 l)

Noise output/noise class: 40 dB(A)/C

Climate rating: SN-ST (+10 °C to +38 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85/55.4/62.3

Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- HardLine
- Stainless steel slimline door handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 2 GlassLine storage shelves, of which one is divided into two parts
- LED lighting
- 2 fruit and vegetable drawers

Freezer compartment

- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 5 kg

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Plastic door shelves, egg tray
- 4 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

Controls

- Mechanical control in the interior, control dial
- CoolPlus function

Fridge compartment

- Plastic door shelves, egg tray
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer

Freezer compartment

- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 5 kg

Key features

- SwingDesign
- Recessed handle
- Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 50 →



← 50 →



← 50 →



← 50 →



← 50 →



← 55 →

TP 1424 Comfort
Energy efficiency class:
Energy consumption year/24 hrs: 141/0.386 kWh ¹
Total volume ² : 120 l
(Fridge: 106.3 l/Freezer compartment: 14.5 l)
Noise output/noise class: 38 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/50.1/62 ¹

Tsl 1414 Comfort	
Energy efficiency class:	
Energy consumption year/24 hrs: 176/0.482 kWh	
Total volume ² : 120 l	
(Fridge: 106.3 l/Freezer compartment: 14.5 l)	
Noise output/noise class: 40 dB(A)/C	
Climate rating: SN-ST (+10 °C to +38 °C)	
Door/side walls: silver/silver	
Exterior dimensions in cm (h/w/d): 85/50.1/62	

T 1404
Energy efficiency class:
Energy consumption year/24 hrs: 176/0.482 kWh
Total volume ² : 120 l
(Fridge: 106.3 l/Freezer compartment: 14.5 l)
Noise output/noise class: 40 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/50.1/62

Tb 1400
Energy efficiency class:
Energy consumption year/24 hrs: 114/0.312 kWh
Total volume ² : 136 l
Noise output/noise class: 36 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: black/black
Exterior dimensions in cm (h/w/d): 85/50.1/62

T 1400
Energy efficiency class:
Energy consumption year/24 hrs: 114/0.312 kWh
Total volume ² : 136 l
Noise output/noise class: 36 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 85/50.1/62

TX 1021 Comfort
Energy efficiency class:
Energy consumption year/24 hrs: 131/0.358 kWh
Total volume ² : 98 l (0-star freezer: 6.0 l)
Noise output/noise class: 37 dB(A)/C
Climate rating: SN-ST (+10 °C to +38 °C)
Door/side walls: white/white
Exterior dimensions in cm (h/w/d): 63/55.4/62.4

Controls
· Mechanical control in the interior, control dial
· CoolPlus function
Fridge compartment
· Comfort GlassLine storage shelf with bottle holder, egg tray
· 2 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Freezer compartment
· Temperature rise time: 9 h
· Freezing capacity in 24 hrs: 5 kg
Key features
· SwingDesign
· Ergonomically designed slimline handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

Controls
· Mechanical control in the interior, control dial
· CoolPlus function
Fridge compartment
· Comfort GlassLine storage shelf with bottle holder, egg tray
· 2 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Freezer compartment
· Temperature rise time: 9 h
· Freezing capacity in 24 hrs: 5 kg
Key features
· SwingDesign
· Stainless steel slimline door handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

Controls
· Mechanical control in the interior, control dial
· CoolPlus function
Fridge compartment
· Plastic door shelves, egg tray
· 2 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Freezer compartment
· Temperature rise time: 9 h
· Freezing capacity in 24 hrs: 5 kg
Key features
· SwingDesign
· Recessed handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

Controls
· Mechanical control in the interior, control dial
Fridge compartment
· Plastic door shelves with bottle holder, egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Key features
· SwingDesign
· Recessed handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

Controls
· Mechanical control in the interior, control dial
Fridge compartment
· Plastic door shelves, egg tray
· 4 GlassLine storage shelves
· LED lighting
· 1 spacious fruit and vegetable drawer
Key features
· SwingDesign
· Recessed handle
· Under-worktop installation compatible due to front ventilation (exhaust ventilation via grills in worktop) and removable tabletop
· Height-adjustable feet at front
· Reversible door hinging

Controls
· Mechanical control in the interior, control dial
Fridge compartment
· Comfort GlassLine storage shelf with bottle holder, egg tray
· 2 GlassLine storage shelves
· LED lighting
· 2 fruit and vegetable drawers
· 0-star compartment (0 °C to -6 °C)
· Ice cube tray
Key features
· SwingDesign
· Ergonomically designed slimline handle
· Height-adjustable feet at front
· Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Freezers



GN 5275

Our freezers: an overview

Featuring options such as NoFrost, SmartFrost, StopFrost and FrostProtect – Liebherr freezers offer maximum convenience. With tall, under counter and chest freezers available – Liebherr has just the right appliance whatever your requirements. Choose from a variety of sizes and select your preferred fittings.

No Frost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.

Smart Frost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean offering additional capacity.

Stop Frost

Frosting over of the freezer and frozen food is reduced, reducing the number of times you need to defrost the freezer. StopFrost prevents a vacuum from building up in our chest freezers, ensuring the lid opens easily.

Frost Protect

FrostProtect models will work in ambient temperatures as low as $-15\text{ }^{\circ}\text{C}$ for example in an unheated garage or outbuilding.

Freezers



No Frost

from page 100



Smart Frost

from page 108

Under counter freezers



Smart Frost

from page 109

Chest freezers



Stop Frost

from page 112

Quality in every detail



No Frost

The **NoFrost** system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, long-term storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free to make defrosting a thing of the past.



Smart Frost

With the **SmartFrost** technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are smooth and easy-to-clean offering additional capacity. Freezer drawers and glass shelves made of safety glass can be removed easily.



The **status indicator** is discretely integrated into the appliance door, allowing for quick and easy assessment of the appliance status, even if the door is closed. A blue light indicates that the appliance is working properly. In the case of any other status, a red light and an audible tone are emitted.



The high-resolution, high-contrast **2.4" touch-screen display** is integrated behind the door and enables individual temperature setting.



Frost Protect

Many freezers are kept outside of the normal household environment, so Liebherr has developed **FrostProtect** on selected models to enable these models to function in low ambient temperatures. Models indicated as FrostProtect will work in ambient temperatures as low as -15°C .



So that food can be conveniently accessed with minimal effort, even if the drawers are fully stocked, all BluPerformance freezer **drawers** are sited on smooth-running **roller tracks**. For convenient removal and storage of food, the top drawer tilts slightly downwards when opened – an especially helpful feature in taller appliances. The position and size of the bottom drawer make it ideal for storing ice cream, herbs or other small items.

The features shown are model dependent; look for these features in your model choice.

Quality in every detail



The automatic **SuperFrost** function makes freezing food simple and energy efficient. It rapidly lowers the temperature to $-32\text{ }^{\circ}\text{C}$ to create the temperature levels required to preserve vitamins and enhance the flavour and texture of the food when consumed.



The elegant **MagicEye control system** with the innovative, user-friendly Touch-electronic feature ensures that the temperature in the fridge compartment and freezer compartment is kept to the selected temperature. All the functions can be simply and conveniently operated at the touch of a finger.



Telescopic Rails

The transparent freezer drawers on **telescopic rails** are easy to access and use even when filled with heavy contents. They ensure both great visibility and optimum storage. The **FrostSafe** fully enclosed drawers prevent cold air from escaping, thereby reducing energy consumption.



BLU
Performance

BluPerformance models have their refrigeration technology compactly integrated in the plinth, minimising operating noise and saving space. Maximum performance thereby comes hand-in-hand with a considerably larger net capacity and greater energy efficiency.

1. Power connection for appliance plug 2. Functional wall spacer to maintain wall clearance and allow connection 3. Variable speed compressor 4. Plinth fan with noise-damping 5. Condenser 6. Defrost water drain




The freezer drawers in the BluPerformance appliances can be easily opened on **roller tracks**. The drawers and intervening glass shelves in all appliances can be removed to create **VarioSpace** – a no-fuss system for quickly creating extra storage space.



If you are not using the entire freezer space, unused drawers can be switched off with the optional **Vario Energy-Saving Panel**. Energy consumption can then be reduced again by up to 30%.

The features shown are model dependent; look for these features in your model choice.

Freezers



BLU
Performance

← 70 →



BLU
Performance

← 70 →



BLU
Performance

← 70 →



BLU
Performance

← 70 →

GN 5275 Premium



Energy efficiency class: **C**¹

Energy consumption year/24 hrs: 179/0.490 kWh¹

Total volume²: 369 l

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 195/70/75¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 5235 Comfort



Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 224/0.613 kWh¹

Total volume²: 369 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 195/70/75¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4635 Comfort



Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 210/0.575 kWh¹

Total volume²: 320 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 175/70/75¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 7 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 17 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4135 Comfort



Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 197/0.539 kWh¹

Total volume²: 270 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 155/70/75¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 6 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening


¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



BLU
Performance

← 70 →



BLU
Performance

← 60 →



BLU
Performance

← 60 →



BLU
Performance

← 60 →

GN 3835
Comfort

No Frost LED Smart Device ready

Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 183/0.501 kWh¹

Total volume²: 221 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 135/70/75¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 5 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 15 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GN 4375
Premium

No Frost LED Smart Device ready Telescopic Rails

Energy efficiency class: **D**¹

Energy consumption year/24 hrs: 198/0.542 kWh¹

Total volume²: 276 l

Noise output/noise class: 37 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-colour display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, of which 6 set on telescopic rails, of which 1 set on roller tracks, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNi 4335
Comfort

No Frost LED Smart Device

Energy efficiency class: **E**¹

Energy consumption year/24 hrs: 248/0.679 kWh¹

Total volume²: 276 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox included
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNef 4335
Comfort

No Frost LED Smart Steel Smart Device ready

Energy efficiency class: **E**¹

Energy consumption year/24 hrs: 248/0.679 kWh¹

Total volume²: 276 l

Noise output/noise class: 38 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 185/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 8 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 18 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 1.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Freezers



GNP 3013



← 60 →



← 60 →



← 60 →

BLU
Performance

GNP 3013 Comfort

No Frost

Energy efficiency class: **F**¹
 Energy consumption year/24 hrs: 307/0.841 kWh¹
 Total volume²: 268 l
 Noise output/noise class: 41 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 184.1/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 8 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 14 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

GN 3735 Comfort

No Frost

LED

Smart Device ready

Energy efficiency class: **E**¹
 Energy consumption year/24 hrs: 235/0.643 kWh¹
 Total volume²: 238 l
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 165/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 7 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 17 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNP 2713 Comfort

No Frost

Energy efficiency class: **F**¹
 Energy consumption year/24 hrs: 291/0.797 kWh¹
 Total volume²: 231 l
 Noise output/noise class: 41 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 164.4/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment ********

- 7 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 13 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



BLU
Performance

← 60 →



← 60 →



BLU
Performance

← 60 →



← 60 →

GN 3235

Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 221/0.605 kWh¹
 Total volume²: 200 l
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 145/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 6 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 16 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNP 2303

Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 275/0.753 kWh¹
 Total volume²: 195 l
 Noise output/noise class: 41 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 144.7/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment

- 6 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 13 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal

GN 2835

Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 208/0.569 kWh¹
 Total volume²: 161 l
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 125/60/66.5¹

Controls

- 2.4" TFT-monochrome display behind-the-door, touch electronic
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- 5 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Status indicator
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 15 kg
- 1 cold storage accumulator
- Safety glass fittings

Key features

- HardLine
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles, front and at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening

GNP 1913

Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 258/0.706 kWh¹
 Total volume²: 158 l
 Noise output/noise class: 40 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 125/60/63¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment

- 5 drawers, of which 1 herb and berry tray, VarioSpace
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 12 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm and 1.5 cm at BluPerformance-appliances. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



←60→



←60→



←60→



←60→



←60→



←55→

GP 2733

Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 262/0.717 kWh¹Total volume²: 224 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 164.4/60/63¹**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 7 drawers, VarioSpace
- Temperature rise time: 19 h
- Freezing capacity in 24 hrs: 11 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

GP 2433

Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 249/0.682 kWh¹Total volume²: 191 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 144.7/60/63¹**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 6 drawers, VarioSpace
- Temperature rise time: 19 h
- Freezing capacity in 24 hrs: 10 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

GP 2033

Comfort



Energy efficiency class:

Energy consumption year/24 hrs: 235/0.643 kWh¹Total volume²: 157 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 125/60/63¹**Controls**

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 5 drawers, VarioSpace
- Temperature rise time: 19 h
- Freezing capacity in 24 hrs: 9 kg
- Safety glass fittings

Key features

- SwingLine design
- Slimline handles with integrated opening mechanism
- Versatile installation due to front ventilation
- Transport handles at back, transport castors at back
- Height-adjustable feet at front
- Reversible door hinging

GPesf 1476

Premium



Energy efficiency class:

Energy consumption year/24 hrs: 171/0.468 kWh¹Total volume²: 102 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: Stainless steel with SmartSteel/silver

Exterior dimensions in cm (h/w/d): 85.1/60.2/61¹**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- HardLine
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GP 1476

Premium



Energy efficiency class:

Energy consumption year/24 hrs: 171/0.468 kWh¹Total volume²: 102 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/60.2/62.8¹**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GP 1386

Premium



Energy efficiency class:

Energy consumption year/24 hrs: 171/0.468 kWh¹Total volume²: 102 l

Noise output/noise class: 39 dB(A)/C

Climate rating: SN-T (+10 °C to +43 °C)

Designed to operate in ambient temperatures as low as -15 °C

Door/side walls: white/white

Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4¹**Controls**

- MagicEye on front, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic

Freezer compartment

- 4 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 55 →



← 55 →



← 55 →



← 55 →

GP 1223
Comfort



Energy efficiency class: ¹
 Energy consumption year/24 hrs: 170/0.465 kWh¹
 Total volume²: 97 l
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4¹

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

Gsl 1223
Comfort



Energy efficiency class: ²
 Energy consumption year/24 hrs: 213/0.583 kWh
 Total volume²: 97 l
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: silver/silver
 Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Stainless steel slimline door handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

G 1223
Comfort



Energy efficiency class: ²
 Energy consumption year/24 hrs: 213/0.583 kWh
 Total volume²: 97 l
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 85.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment

- 3 drawers, VarioSpace
- Temperature rise time: 17 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

GX 823
Comfort



Energy efficiency class: ²
 Energy consumption year/24 hrs: 199/0.545 kWh
 Total volume²: 68 l
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 63.1/55.3/62.4

Controls

- MagicEye on front, key electronic
- Graphic temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual

Freezer compartment

- 2 drawers, VarioSpace
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings


Key features

- SwingDesign
- Ergonomically designed slimline handle
- Versatile installation due to front ventilation
- Height-adjustable feet at front
- Reversible door hinging

¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Quality in every detail



Stop Frost

StopFrost prevents a vacuum from building up, ensuring the lid opens easily. Frosting over of the freezer and frozen food is reduced, which limits the number of times you need to defrost the freezer.



The bright **LED interior light** allows a clear view of all your stored products even in low ambient lighting conditions. The one piece chest freezer lid and body is coated to ensure an excellent finish resilience and to prevent corrosion.



Chest freezers in the premium range benefit from the **SoftSystem** closing mechanism, a convenient and desirable feature for everyday use. Integrated into the hinges on the freezer lid, SoftSystem allows the lid to close gently and prevents slamming.



←168→



←168→

CFd 2505 Plus

- Stop Frost
- Soft System
- LED
- Frost Protect

Energy efficiency class: **D**
 Energy consumption year/24 hrs: 188/0.515 kWh
 Total volume²: 359 l
 Noise output/noise class: 38 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 82.5/167.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 15 kg
- 1 cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 5 Suspension baskets as standard, 1 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

CFF 2500 Pure

- Stop Frost
- LED
- Frost Protect

Energy efficiency class: **F**
 Energy consumption year/24 hrs: 324/0.887 kWh
 Total volume²: 497 l
 Noise output/noise class: 39 dB(A)/C
 Climate rating: SN-T (+10 °C to +43 °C)
 Designed to operate in ambient temperatures as low as -15 °C
 Door/side walls: white/white
 Exterior dimensions in cm (h/w/d): 82.5/167.5/72.2

Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 20 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 5 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

The features shown are model dependent; look for these features in your model choice.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Chest freezers



←126→



←126→



←105→

CFd 2085 Plus



Energy efficiency class:
Energy consumption year / 24 hrs: 162 / 0.443 kWh
Total volume ² : 248 l
Noise output / noise class: 38 dB(A) / C
Climate rating: SN-T (+10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C
Door / side walls: white / white
Exterior dimensions in cm (h/w/d): 82.5 / 125.5 / 72.2

Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 50 h
- Freezing capacity in 24 hrs: 10 kg
- 1 cold storage accumulator
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 3 Suspension baskets as standard, 1 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

Cff 2080 Pure



Energy efficiency class:
Energy consumption year / 24 hrs: 274 / 0.750 kWh
Total volume ² : 353 l
Noise output / noise class: 39 dB(A) / C
Climate rating: SN-T (+10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C
Door / side walls: white / white
Exterior dimensions in cm (h/w/d): 82.5 / 125.5 / 72.2

Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 15 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 3 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

Cff 1870 Pure



Energy efficiency class:
Energy consumption year / 24 hrs: 249 / 0.682 kWh
Total volume ² : 281 l
Noise output / noise class: 39 dB(A) / C
Climate rating: SN-T (+10 °C to +43 °C)
Designed to operate in ambient temperatures as low as -15 °C
Door / side walls: white / white
Exterior dimensions in cm (h/w/d): 82.5 / 104.5 / 72.2

Controls

- Electronic controls in the casing, key electronic
- Thermometer with digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment

- Low vibration, low noise, easy-to-clean foam-embedded condenser
- LED lighting
- Temperature rise time: 40 h
- Freezing capacity in 24 hrs: 10 kg
- Defrost drain
- Removable freezer tray as partition wall – can be used as a drip tray
- 2 Suspension baskets as standard, 2 retrofittable

Key features

- Recessed handle
- Replaceable door seal
- Concealed hinge with restricted opening

CFf 2080

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Wine cabinets



WTes 5872

Our wine cabinets: an overview



Vinidor range

The Vinidor range offers maximum flexibility with two separately controlled temperature zones. The temperature of these can be set independently between +5 °C and +20 °C. This means that red and white wines can be stored at their ideal serving temperatures in the same cabinet. These cabinets not only provide the ideal climate conditions for long-term storage of wine, but with differently sized zones and fully adjustable temperature controls, they are suitable for every wine collection.



GrandCru and Vinothek range

Wine storage cabinets offer similar conditions to a wine cellar. This range facilitates the storage of red and white wines at the correct long term storage temperatures or individual serving temperatures. The temperature can be adjusted from +5 °C to +20 °C as appropriate, and is both even and constant throughout the entire appliance interior.



Vinothek range

Multi-temperature wine cabinets from the Vinothek range offer versatile storage for different types of wine, each at its perfect drinking temperature. The innovative climate technology that we use creates a graduated temperature zone from up to +18 °C and down to +5 °C. In this way a variety of wines can be stored at the various correct serving temperatures.

Wine lovers have the most stringent demands when it comes to storing their favourite wines. Many like to be able to enjoy their fine wines on the spur of the moment; others prefer to establish a collection of wines over the longer term; and some want the best of both worlds. Liebherr offers premium wine storage cabinets that guarantee perfect long term wine storage and serving temperatures, whatever your requirements. With heating and cooling circuits and air filtration, our wine cabinets offer unsurpassed wine storage conditions.



Vinidor - from page 122



GrandCru - from page 124



Vinothek - from page 128



Humidor - from page 130


Quality in every detail



The electronic LCD display offers clear menu navigation and a **Touch-electronic control system** provides bespoke storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



The Vinidor appliances are equipped with solid **wooden shelves mounted on telescopic rails**. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The **clip-on labelling system** provides a quick and clear overview of your wine store.



LED

The **LED lighting** in the wine storage compartments can be dimmed to give a pleasing ambient light inside the appliance. All Vinidor appliances are equipped with no-heat LED lighting. The LED lighting system can be adjusted to activate during door openings or to be on continuously at various intensity settings (depending on model).



The **tinted safety glass** in Liebherr wine cabinets guarantees the essential UV protection for your fine wines. The practical aluminium **door handle**, with integrated opening mechanism, allows the door of the appliance to be opened conveniently with a minimum of effort.



The practical **presentation shelf** of the Vinidor models fulfills both bottle storage and bottle presentation functions. The bottles can be stored horizontally at the back of the interior.



Soft System

The **SoftSystem** feature provides added safety and convenience. Integrated within the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 45°.

The features shown are model dependent; look for these features in your model choice.

Wine storage cabinets Vinidor



← 70 →



← 70 →



← 70 →



← 60 →

WTes 5872

Vinidor



Energy efficiency class: **G**¹

Energy consumption year / 24 hrs: 206 / 0.564 kWh¹

Max. Bordeaux bottles 0.75 l: 178³

Total volume²: 503 l

Noise output / noise class: 35 dB(A) / B SuperSilent

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 192 / 70.0 / 74.2¹

Controls

- LCD display in the interior, touch electronic
- Digital temperature display for 3 wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment


- 3 Temperature zones, which can set from +5 °C to +20 °C
- 3 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 13 Shelves, of which 10 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

WTes 5972

Vinidor



Energy efficiency class: **G**¹

Energy consumption year / 24 hrs: 191 / 0.523 kWh¹

Max. Bordeaux bottles 0.75 l: 211³

Total volume²: 521 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 192 / 70.0 / 74.2¹

Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening
- Lock

WTpes 5972

Vinidor



Energy efficiency class: **G**¹

Energy consumption year / 24 hrs: 191 / 0.523 kWh¹

Max. Bordeaux bottles 0.75 l: 155³

Total volume²: 521 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 192 / 70.0 / 74.2¹

Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 6 Shelves, of which 5 set on telescopic rails, of which 2 are pull-out baskets

Key features

- HardLine
- Stainless steel slimline door handle
- Reversible door hinging
- Replaceable door seal
- Lock

WTes 1672

Vinidor



Energy efficiency class: **G**¹

Energy consumption year / 24 hrs: 147 / 0.402 kWh

Max. Bordeaux bottles 0.75 l: 34³

Total volume²: 95 l

Noise output / noise class: 36 dB(A) / C

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door with stainless steel frame / stainless steel

Exterior dimensions in cm (h/w/d): 82.2 / 59.8 / 57.5

Controls

- MagicEye in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

Key features

- HardLine
- Aluminium handle
- Reversible door hinging
- Replaceable door seal
- Lock


¹ To achieve the indicated energy consumption level, the wall spacers provided with the appliance must be used. These increase the appliance depth by approximately 3.5 cm. If the wall spacers are not used, the appliance will remain fully functional, but will have a slightly higher energy consumption level.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

³ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.

Wine storage cabinets GrandCru



← 75 →



← 70 →



← 70 →



← 70 →

WKt 6451 GrandCru

Wine LED

Energy efficiency class: **F**

Energy consumption year / 24 hrs: 125 / 0.342 kWh

Max. Bordeaux bottles 0.75 l: 312³

Total volume²: 614 l

Noise output / noise class: 39 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: Full door, terra / terra

Exterior dimensions in cm (h / w / d): 193 / 74.7 / 75.9

Controls

- MagicEye on front, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood fittings
- 7 Shelves

Key features

- SwingLine design
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Lock

WKt 5552 GrandCru

Wine LED

Energy efficiency class: **G**

Energy consumption year / 24 hrs: 147 / 0.402 kWh

Max. Bordeaux bottles 0.75 l: 253³

Total volume²: 526 l

Noise output / noise class: 39 dB(A) / C

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door, frame terra / terra

Exterior dimensions in cm (h / w / d): 192 / 70.0 / 74.2

Controls

- MagicEye in the interior, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on
- Adjustable beech wood fittings
- 7 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

WKt 5551 GrandCru

Wine LED

Energy efficiency class: **E**

Energy consumption year / 24 hrs: 94 / 0.257 kWh

Max. Bordeaux bottles 0.75 l: 253³

Total volume²: 500 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-T (+10 °C to +43 °C)

Door / side walls: Full door, terra / terra

Exterior dimensions in cm (h / w / d): 192 / 70.0 / 74.2

Controls

- MagicEye in the interior, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting
- Adjustable beech wood fittings
- 7 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

WKt 4552 GrandCru

Wine LED

Energy efficiency class: **F**

Energy consumption year / 24 hrs: 117 / 0.320 kWh

Max. Bordeaux bottles 0.75 l: 201³

Total volume²: 436 l

Noise output / noise class: 38 dB(A) / C

Climate rating: SN-ST (+10 °C to +38 °C)

Door / side walls: Glass door, frame terra / terra

Exterior dimensions in cm (h / w / d): 165 / 70.0 / 74.2

Controls

- MagicEye in the interior, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on
- Adjustable beech wood fittings
- 6 Shelves

Key features

- HardLine
- Aluminium handle with integrated opening mechanism
- Reversible door hinging
- Replaceable door seal
- Lock

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

³ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



← 70 →



← 70 →



The WKes 653 is fitted with **LED lighting** which can be adjusted and dimmed for optimal presentation of the best wines. Because the LEDs generate only minimal heat emission and no UV radiation, the wines can be displayed in the right light over an extended period without coming to harm.



← 43 →

WKt 4551
GrandCru



Energy efficiency class:
Energy consumption year / 24 hrs: 94 / 0.257 kWh
Max. Bordeaux bottles 0.75 l: 201 ³
Total volume ² : 414 l
Noise output / noise class: 38 dB(A) / C
Climate rating: SN-T (+10 °C to +43 °C)
Door / side walls: Full door, terra / terra
Exterior dimensions in cm (h / w / d): 165 / 70.0 / 74.2

- Controls**
- MagicEye in the interior, key electronic
 - Digital temperature display
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: acoustic
 - Child lock

- Wine compartment**
- 1 Temperature zone, which can set from +5 °C to +20 °C
 - Convection cooling, Fresh air supply via FreshAir activated charcoal filter
 - Humidity regulation via adjustable fan
 - LED interior lighting
 - Adjustable beech wood fittings
 - 6 Shelves

- Key features**
- HardLine
 - Aluminium handle with integrated opening mechanism
 - Reversible door hinging
 - Replaceable door seal
 - Lock

WKes 4552
GrandCru



Energy efficiency class:
Energy consumption year / 24 hrs: 117 / 0.320 kWh
Max. Bordeaux bottles 0.75 l: 201 ³
Total volume ² : 436 l
Noise output / noise class: 38 dB(A) / C
Climate rating: SN-ST (+10 °C to +38 °C)
Door / side walls: Glass door with stainless steel frame / stainless steel
Exterior dimensions in cm (h / w / d): 165 / 70.0 / 74.2

- Controls**
- MagicEye in the interior, key electronic
 - Digital temperature display
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: acoustic
 - Child lock

- Wine compartment**
- 1 Temperature zone, which can set from +5 °C to +20 °C
 - Convection cooling, Fresh air supply via FreshAir activated charcoal filter
 - Humidity regulation via adjustable fan
 - LED interior lighting permanently on
 - Adjustable beech wood fittings
 - 6 Shelves

- Key features**
- HardLine
 - Aluminium handle with integrated opening mechanism
 - Reversible door hinging
 - Replaceable door seal
 - Lock

WKes 653
GrandCru



Energy efficiency class:
Energy consumption year / 24 hrs: 78 / 0.213 kWh
Max. Bordeaux bottles 0.75 l: 12 ³
Total volume ² : 48 l
Noise output / noise class: 37 dB(A) / C
Climate rating: SN (+10 °C to +32 °C)
Door / side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel
Exterior dimensions in cm (h / w / d): 61.2 / 42.5 / 47.8

- Controls**
- LCD display in the interior, touch electronic
 - Digital temperature display
 - Warning signal in case of fault: visual and acoustic
 - Door alarm: acoustic
 - Child lock

- Wine compartment**
- 1 Temperature zone, which can set from +5 °C to +20 °C
 - Convection cooling, Fresh air supply via FreshAir activated charcoal filter
 - Humidity regulation via adjustable fan
 - LED interior lighting permanently on, dimmable
 - Beech wood fittings
 - 3 Shelves
 - Utensil drawer

- Key features**
- HardLine
 - Suitable for wall mounting
 - Fixed door hinge, right
 - Replaceable door seal
 - Lock



The practical **utensil compartment** can be used for storing wine utensils or small complementary items such as chocolate and pralines which can also be served at the perfect temperature for full enjoyment of the wine.

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

³ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



<p>WKb 4212 Vinothek</p> <p>Wine</p>	<p>WKr 4211 Vinothek</p> <p>Wine</p>	<p>WKb 3212 Vinothek</p> <p>Wine</p>	<p>WKr 3211 Vinothek</p> <p>Wine</p>	<p>WKb 1812 Vinothek</p> <p>Wine</p>	<p>WKr 1811 Vinothek</p> <p>Wine</p>
<p>Energy efficiency class: G²</p> <p>Energy consumption year/24 hrs: 177/0.484 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 200³</p> <p>Total volume²: 402 l</p> <p>Noise output/noise class: 39 dB(A)/C</p> <p>Climate rating: SN-ST (+10 °C to +38 °C)</p> <p>Door /side walls: Glass door, frame black/black</p> <p>Exterior dimensions in cm (h/w/d): 165/60.0/73.9</p>	<p>Energy efficiency class: F²</p> <p>Energy consumption year/24 hrs: 108/0.295 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 200³</p> <p>Total volume²: 383 l</p> <p>Noise output/noise class: 37 dB(A)/C</p> <p>Climate rating: SN-T (+10 °C to +43 °C)</p> <p>Door /side walls: Full door, burgundy/black</p> <p>Exterior dimensions in cm (h/w/d): 165/60.0/73.9</p>	<p>Energy efficiency class: G²</p> <p>Energy consumption year/24 hrs: 171/0.468 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 164³</p> <p>Total volume²: 315 l</p> <p>Noise output/noise class: 37 dB(A)/C</p> <p>Climate rating: SN-ST (+10 °C to +38 °C)</p> <p>Door /side walls: Glass door, frame black/black</p> <p>Exterior dimensions in cm (h/w/d): 135/60.0/73.9</p>	<p>Energy efficiency class: E²</p> <p>Energy consumption year/24 hrs: 92/0.252 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 164³</p> <p>Total volume²: 300 l</p> <p>Noise output/noise class: 37 dB(A)/C</p> <p>Climate rating: SN-T (+10 °C to +43 °C)</p> <p>Door /side walls: Full door, burgundy/black</p> <p>Exterior dimensions in cm (h/w/d): 135/60.0/73.9</p>	<p>Energy efficiency class: G²</p> <p>Energy consumption year/24 hrs: 123/0.337 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 66³</p> <p>Total volume²: 135 l</p> <p>Noise output/noise class: 38 dB(A)/C</p> <p>Climate rating: SN-ST (+10 °C to +38 °C)</p> <p>Door /side walls: Glass door, frame black/black</p> <p>Exterior dimensions in cm (h/w/d): 89/60.0/61.3</p>	<p>Energy efficiency class: E²</p> <p>Energy consumption year/24 hrs: 76/0.208 kWh</p> <p>Max. Bordeaux bottles 0.75 l: 66³</p> <p>Total volume²: 128 l</p> <p>Noise output/noise class: 37 dB(A)/C</p> <p>Climate rating: SN-T (+10 °C to +43 °C)</p> <p>Door /side walls: Full door, burgundy/black</p> <p>Exterior dimensions in cm (h/w/d): 89/60.0/61.3</p>
<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Interior lighting permanently on · Adjustable beech wood fittings · 6 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging · Replaceable door seal 	<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Adjustable beech wood fittings · 6 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging 	<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Interior lighting permanently on · Adjustable beech wood fittings · 4 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging · Replaceable door seal 	<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Adjustable beech wood fittings · 4 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging 	<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Interior lighting permanently on · Adjustable Galvanised grid shelves · 3 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging · Replaceable door seal 	<p>Controls</p> <ul style="list-style-type: none"> · MagicEye on front, key electronic · Digital temperature display · Warning signal in case of fault: visual and acoustic · Door alarm: acoustic · Child lock <p>Wine compartment</p> <ul style="list-style-type: none"> · 1 Temperature zone, which can set from +5 °C to +20 °C · Convection cooling, Fresh air supply via FreshAir activated charcoal filter · Humidity regulation via adjustable fan · Adjustable Galvanised grid shelves · 3 Shelves <p>Key features</p> <ul style="list-style-type: none"> · HardLine · Ergonomically designed slimline handle, black · Reversible door hinging

² In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

³ These models are only bound for storing wine. Maximum DIN norm bordeaux bottles capacity (0.75 l) as per norm NF H 35-124 (H: 300.5 mm, Ø 76.1 mm).

You can find the full range of efficiency classes at pages 20–21. According to (EU) 2017/1369 6a.



ZKes 453

Humidor



← 43 →

ZKes 453 Humidor

LED Smart Steel Cigar

Energy consumption year /24 hrs: 162/0.443 kWh

Total volume: 39 l

Noise output: 40 dB(A)

Climate rating: N (+16 °C to +32 °C)

Door /side walls: Glass door with stainless steel frame and SmartSteel / stainless steel with SmartSteel

Exterior dimensions in cm (h/w/d): 61.2/42.5/47.8

Controls

- LCD display in the interior, touch electronic
- Digital display of temperature and humidity
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Humidor

- 1 Temperature zone, which can set from +16 °C to +20 °C
- Humidity range, adjustable between 68 % to 75 %
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Spanish cedar wood fittings
- 2 Shelves

Key features

- HardLine
- Suitable for wall mounting
- Fixed door hinge, right
- 2 presentation boxes
- Replaceable door seal
- Lock



The precision **electronic control system** allows the temperature to be set within a range of +16 °C to +20 °C. The humidity can also be set between 68 % and 75 %. The temperature alarm alerts the user to any irregularities within the interior.



Liebherr's humidor has **LED lighting**, with dimmer function, incorporated in the glass door. As the LEDs emit virtually no heat, the cigars can be showcased bathed in light for lengthy periods, without compromising their quality.