
Fully integrated appliances 2021

Valid from 1 March 2021

LIEBHERR

Refrigeration





Contents

Choosing the correct model	4
Quality	6
Freshness technology	8
Comfort & flexibility	10
Design	12
Performance in balance	14
EU energy label	15
Connectivity	16
OpenStage	18
Water & ice	20
Series	22
Accessories	24
Side-by-Side concept	26
Food and Wine Centre combinations	28
Fridge-freezers	30
Fridges	54
Freezers	86
Under-worktop	96
Wine cabinets	104
Glossary	118
Diagrams	120

Our model groups.

Fully integrated appliances


These appliances are designed for easy installation behind the kitchen unit door and can therefore be integrated perfectly into your kitchen. Two different types of unit door installation are available:

Door-on-door installation (1)

the kitchen unit door and the appliance door are connected by attaching the unit door to the appliance door.

Door-slider installation (2)

the unit door is directly attached to the cabinet and connected to the appliance door via sliding rails. When opened and closed, the unit door slides along the rails.



Food Storage Centres	from page 37	
Side-by-Side Food Storage Centres	from page 41	
Fridge-freezers	from page 46	from page 53
Fridges	from page 60	from page 69
Freezers	from page 90	from page 91

Integrated under-worktop appliances

Being able to integrate an under-worktop refrigeration appliance behind a unit door maintains a visually uniform kitchen. A door-on-door attachment connects the appliance and unit doors. As air intake and ventilation take place at the appliance plinth, no ventilation slots need to be cut in the worktop. The Vario plinth can be adapted to the height and depth of the kitchen units.



Fridges	from page 99
Freezers	from page 103



Before we think about fridges, we think about you.

Fridges are supposed to cool. But what else should modern appliances be capable of today? How can they better meet customer needs? How can their design be more efficient, intuitive and modern?

We think about all these questions every day, because for us a fridge is not just an appliance. Instead, it should be a partner who supports us where it can ... who thinks in harmony with us, takes on tasks and makes work easier. In order to achieve this, we are constantly developing our appliances. Because the smarter and more helpful they are, the more time you have for all the other important things in life.

Achieving the highest quality is our standard.

We have been manufacturing high-quality fridges and freezers and selling them around the world since 1954. Yet at heart we are still a family business and have our roots firmly based in Germany. We continue to develop our products here. German engineering – from an enduring connection with our founder and in the knowledge that engineering expertise has been pooled here for generations.

Built to last.

You can experience our quality standards in the smallest of details. For example, before a door hinge is approved by us, it must pass through at least 100,000 opening cycles. This corresponds to a usage period of more than 15 years. We also test all other functional parts to ensure that they can last just as long. We have leveling bars to ensure that your fully integrated appliance works perfectly over this long period and stands firmly in place, even when the wood in the kitchen unit settles. They harmoniously compensate for any unevenness between the floor and the appliance, so that the fridge door always closes tightly. It may sound simple, but this is crucial for avoiding condensation and increased energy consumption.

And if, contrary to expectations, a small detail no longer meets your requirements, you or your expert service partner can usually correct it quickly, because all of our appliances are extremely easy to repair. We keep all essential spare parts in stock for well over 10 years. This saves you money for minor repairs or the purchase of a new appliance – and it is also sustainable.

We don't just say it. We also guarantee it.

During production, we take a very close look at all of our fridge components and test them far more thoroughly and more often than required by law – right up until the packaging stage. Only then may our appliances take a little rest. All our production sites are certified according to international ISO 9001 standard for quality and ISO 14001 standard for environmental management. Therefore it is wholly natural for us to guarantee you that for at least two years our products will be free of material and manufacturing defects and are particularly easy to install. With Warranty-Plus, you can easily extend this warranty for another 10 years.

One thing is certain in any case: Your Liebherr will be reliable companion for a very long time.



Taste that stands the test of time: Freshness is a question of technology.

Storing groceries in ideal climatic conditions not only ensures extra-long freshness and storage time, it also makes a substantial contribution to avoiding food waste. With our appliances this is possible – thanks to the perfect combination of integrated freshness technologies.

DuoCooling. No drying out.

Our basic technology in all fridge-freezers is called DuoCooling. Thanks to two completely separate refrigeration circuits, it ensures that there is no exchange of air between the fridge and freezer compartments. The food neither dries out nor are odours transferred – so that only the Camembert smells and tastes like Camembert.

EasyFresh. Ideal for fruit and vegetables.

The freshness guarantee in your Liebherr fridge. Unpacked fruit and vegetables feel right at home here. At the same temperature as in the fridge compartment and air-tight, lettuce, for example, remains crisp and fresh even after 10 days.

BioFresh. Our all-rounder.

With the proven BioFresh technology, food is stored at a much cooler temperature than in the rest of the appliance. At temperatures just over 0°C and with perfect humidity, BioFresh offers the ideal storage conditions. The air-tight Fruit & Vegetable safe is the ideal environment for fresh produce. Meat, fish and dairy products are in good hands in the Meat & Dairy safe.

BioFresh Professional. Refrigerate like the professionals.

A special innovation can be found in the BioFresh Professional and the brand new HydroBreeze feature. Every time the door is opened and after every 90 minutes, a fresh, cold mist is produced, which covers the fruit and vegetables like a balm. The mist ensures crisp freshness and improves the structure – coating the fruit and veg with a special wow effect.

Fresh. Sustainable. Healthy.

The storage climate: We could write so much about it. To put it briefly, there are three main reasons that motivate us to keep perfecting it. First: An ideal climate contributes to keeping your food fresh for longer. You can enjoy it fresh for longer. Second: This prevents unnecessary food waste and means you have to go shopping less frequently. Three: Optimal storage helps to protect vitamins and nutrients. And this contributes to a healthy diet.



HydroBreeze – the cold fresh mist.

We found inspiration for the HydroBreeze in Salinas Valley in California. Due to the proximity to the cool Pacific Ocean, in the summer a fine humid mist covers the valley and the fields. This prevents the vegetables grown here from drying out.

Hydro
Breeze





Fits exactly to your needs.

Fridges and freezers are used daily. They have long been an essential part of our lives. And they should be as simple to use and convenient for you as possible. That's why we develop fully integrated appliance that impress with their ease of use, clarity and flexibility – from the first door opening to the smallest features. In this way they adapt perfectly to meeting your needs.

Life is a request show.

The features of the new fully integrated appliance give you more freedom: The divisible glass shelf, with its effortless one-handed operation, creates space for tall containers and carafes. Do you like things to be well organised? With the VarioBox and the VarioSafe you can store smaller objects neatly in the door or interior – always exactly at the height you like.

How about a cold drink? The glass shelf above the BioFresh safe transforms into a bottle shelf in the blink of an eye. The freezer compartment also ensures you are well prepared with an appliance from our new fully-integrated series: VarioSpace creates space for the largest turkey or the highest ice cream cake. Speaking of cake: For all those who love baking, our fridges and fridge-freezers offer enough space for a full baking tray.

Full of food. And convenience.

To ensure that all your food is always perfectly accessible, our appliances have telescopic rails in the fridge and freezer compartments which enable the drawers to slide back and forth with ease. And even once you have found all the ingredients, there is still further convenience. Thanks to the SoftSystem. This means that our doors always close gently and quietly, even if the force applied is a little too strong.



Timeless and elegant. Design for every kitchen.

Hidden behind the panels of your built-in kitchen, your Liebherr is inconspicuous and lets the design of the kitchen take the spotlight. But once you open it, it's immediately apparent that behind the door lies something very special.

Design meets functionality.

Puristic and timeless on the one hand. Elegant and exclusive on the other. The new design language blends design and functionality. The high quality glass and stainless steel components are impressive. The precise craftsmanship, an eye for detail and the harmonious combination of materials, shapes and colours create an aesthetically pleasing whole. This is subtly highlighted by the new lighting concept.



The new LightTower lighting concept evenly illuminates the interior while supporting the glass shelves. Flexible, space-saving, unique.



Just a fan? Not at all: the new fan with ambient lighting ensures almost uniform temperature distribution and also includes the FreshAir activated charcoal filter. Functionality at its best.



Perfectly balanced: a powerful, complete package.

A good fridge is a real all-rounder: In addition to low power consumption and low noise levels, it should also offer plenty of space for food and have power reserves for when they are needed. For this reason we don't pay attention to just one factor, instead we have all usage situations in mind at once. The result: our appliances offer a balanced, perfectly coordinated complete package of energy efficiency, volume, noise level and cooling performance. So all good things come in fours for us.

Energy efficiency

Our new fully integrated appliances occupy top positions in efficiency rankings. In this way, they protect the precious resources of our environment and, thanks to low electricity costs, your wallet too.

Volume

We have the perfect appliance for all family sizes, lifestyles and niche heights. From extra-large drawers to the smallest details, we make sure that no liter of volume goes to waste. For example, through space-saving lighting solutions recessed into the housing.

Noise level

Kitchen and living spaces are merging more and more in modern home design concepts. This underlines the importance of particularly quiet fridges. Our new fully-integrated range therefore offers a wide selection of extremely quiet appliances. Some even achieve the ultra-quiet level of 29 dB.

Refrigeration

Intelligent sensor technology constantly adapts the cooling performance to the current use – our fully integrated appliance are very energy-efficient and economical in everyday use. At the same time, they offer considerable power reserves. For example, to cool a larger amount of food after the weekly shop and they are especially good for spontaneous visits. Drinks can be brought to a pleasant drinking temperature extremely quickly at the touch of a button.



The new EU energy label for electrical appliances.

It is now once again possible to distinguish more easily between efficient and inefficient appliances. With the reform of the energy label, appliances will once again be rated from A to G on the efficiency scale. This will make things much clearer for you in future.

Technology is developing all the time. And we also never stand still.

We are constantly working on features that make everyday work easier, optimise storage and reduce consumption. We were one of the first manufacturers in Europe to develop fridges and freezers in the highest efficiency class. And that is also our aim for the future. Fridges and freezers work around the clock and are responsible for up to 15 percent of the electricity bill. As our appliances consume less energy, they make an important contribution to climate protection.



- 1 The QR code for identifying the product in the EPREL (European Product Database for Energy Labeling) EU database.
- 2 The model identifier for identifying the product manually in the EPREL EU database, e.g. via the article number.
- 3 The new A to G efficiency scale. However G is only intended for wine coolers.
- 4 The sum of the volumes of the frozen compartment(s).
- 5 The sum of the volumes of the chill compartment(s) and the unfrozen compartment(s).
- 6 The noise level is now also classified into classes A to D.



We are already providing what the future will bring.

One thing is clear: Technology will get smarter and smarter in the future. But does a fridge need to be intelligent? It doesn't have to be. But we believe: Another cool head in the household can't do any harm. Thanks to many smart functions, our appliances have proven themselves to be reliable helpers behind the scenes.



Built-in progress.

Your fridge thinks for you whenever it can. For example, it reminds you of forgotten drinks in the freezer – thanks to the integrated BottleTimer. So burst bottles are a thing of the past.

When you're on holiday, simply switch your fridge to HolidayMode. That way you can save a lot of energy.

And especially interesting for all those who are also drawn to the fridge at night: NightMode. The interior is then only illuminated with a dimmed light. So after a midnight snack, you can go back to bed quickly and are guaranteed not to fully wake up from your slumbers.



Learn how digitally networked refrigeration makes your everyday life easier: home.liebherr.com/getsmart

You can download the SmartDevice app here:



Always perfectly networked.

All our new fully-integrated models are either networked ex works or can be subsequently connected to WiFi via the SmartDeviceBox.

This way you benefit from the many new possibilities of our SmartDevice app and connecting your fridge to an existing smart home environment. This allows you to easily control appliances via assistance services like Amazon Alexa or online services like IFTTT.

Thanks to networking, important status messages are also sent directly to your mobile phone. For example via DoorAlarm, if the fridge door is left open. But our SmartDevice app has even more to offer: You will also find helpful storage tips, access to operating instructions, warranty extensions, accessories and much more.

In short, our appliances make you ready for tomorrow today.

We play it very, very safe.

We take data protection very seriously. For this reason we have chosen a software partner who shares our high standards: Microsoft. Microsoft, as the first leading provider of cloud services, is certified in accordance with the international standard ISO/IEC 27018, which regulates data protection, and uses AES-256 – the same encryption technology employed in the banking sector.



OpenStage

The kitchen becomes a market stand: with the new OpenStage drawers.

Now there's a clear view of everything: With the transparent OpenStage drawers we are setting new standards in ease of use and design. Inspired by display cases in fine delicatessens, the OpenStage concept showcases all your food at a glance. The drawers are reminiscent of market stands and present the complete contents of the fridge in an optimally clear and ergonomically ideal way.



The captivating design has a full stainless steel panel on the rear wall and in the interior door as well as a fan with discreet ambient lighting. In this way, you will feel something special every time you open the door.



You can store a large number of drinks in the practical drawers and remove them easily. High-quality railings ensure stability. When closing the drawers you will also enjoy the highest level of convenience, thanks to the gentle self-closing mechanism.

It's raining ice cubes. Automatically.

Spontaneous party? Not a problem. The IceMaker produces up to 130 ice cubes a day, providing plenty of ice for aperitifs, cocktails and soft drinks – for a truly memorable summer garden party. With the MaxIce feature, you can further speed up ice cube production if you have invited lots of guests over.



Flexible installation.

The IceMaker is available with a direct connection to the drinking water supply. If such a connection is not available, there are also models with a water tank in the fridge compartment. So you can enjoy convenient ice cube production even without a fixed tap water connection.




This spring has its source in the fridge.

Our InfinitySpring brings a crystal-clear source of water into the heart of your kitchen. Because water is healthy. Now lugging heavy crates and plastic bottles full of water are history. This means less strain on your back and also has our environment in mind. Simple and sustainable.

Ice-cold water on tap with no heavy lifting.

The flush-mounted water dispenser is always there when it is needed and almost invisible when its not. It is suitable for containers of almost any size, also for carafes or bottles for the water carbonator. The integrated filter system ensures perfect water quality. By the way, in contrast to conventional table water filters, it only needs to be replaced every six months.




For a clear overview.
Even before you
open the fridge.

○ Pure ◇ Plus ◻ Prime △ Peak

Which appliance is right for me?
A customer question that is not always
easy to answer. That's why we have made
it even simpler for you choose what's
right for you by dividing our product range
into four easy to understand series.

○ Pure series

The Pure series is our basic class. Simple, clear and perfectly equipped for all essential needs. The Pure series has been reduced to the essentials. But full to the brim with the highest level of Liebherr quality.



◇ Plus series

The Plus series builds on our Pure series and has many impressive additional details. Above all, plus means a plus in comfort. The appliances not only provide first-class refrigerating and freezing, they are also just that little bit smarter. They help make much of the handling a little easier.

◻ Prime series

With the Prime series things get much more classy. It makes an unmistakable mark in terms of design and material. Above all, genuine materials are used inside the appliances, such as stainless steel. But also special lighting solutions make the appliances in this series particularly appealing.



△ Peak series

The Peak series sits at the top of our series. Here the best is combined with the best. There is no compromise. Innovative Liebherr technology meets high-end design and comfort solutions that are simply first in its class. Appliances in this series are for those who want everything.



Flexible accessories for your appliance

Discover the versatility of the Liebherr range of accessories for your fridge – and make your daily life a little bit easier.



Useful help of all kinds

From the handy butter dish to the easy-fill ice cube tray, from the freezer tray to the Vario energy-saving panel, our range of accessories offers plenty of smart solutions for serving food and keeping it fresh.



Perfect installation – perfect appearance

Connecting sets, stainless steel frames and fronts with matching handles or drawers for accessories: the product range features many accessories that can help integrate a built-in appliance in the kitchen in an individual and visually perfect fashion.

Organisational systems


Set up your fridge how you want it: In addition to the VarioSafe and the VarioBoxes, we also offer optimal organisation with the variable egg tray and the FlexSystem. Thanks to our bottle shelves and the clip labelling system for your wine inventory, you can also keep track of your beverages.

Matching accessories can be found online by desired model at: home.liebherr.com

Creating an individually designed Food and Wine Centre.


Liebherr appliances designed for incorporation into our Side-by-Side food centres feature an integrated heating system in their ceiling and / or side walls. This heating prevents condensation forming between appliances running at 0°C and colder – especially if there is a large temperature differential, as with a fridge and freezer.

Different Liebherr appliances can be combined in the food and wine storage (horizontally and vertically) without problems, with both the appliances and kitchen furniture being fully protected against condensation.



Freezers with heated ceiling

This allows freezers (niche height: 72 cm and 88 cm) to be vertically combined with a refrigerator or wine cabinet of any niche height.



Heated side walls on both sides

This allows under-worktop freezers to be positioned on either side of appliances, SIGN freezers (niche height: 140 cm and 178 cm) can be positioned on either side of appliances of any niche height.




Heated ceiling and side walls

These allow the full-space BioFresh SIBP 1650 refrigerator to be combined vertically with appliances of any niche height. Combinations up to a niche height of 178 cm are possible on both sides.



Combination examples



Food and Wine Centre combinations.

As an alternative to the individual composition of your FrischeCenters, you can also choose a combination of the three most popular models for the 178 niche.

The arrangement of the models next to each other is variable, if necessary with door hinge change.




SBSWdf 9915 here with optional stainless steel fronts and frame and stainless steel handles (available as accessory)

SBSWdf 9915 consisting of:




With optional stainless steel fronts and frame and stainless steel handles (accessories)

SBSWgw 9915 consisting of:



SBSWgb 9915 consisting of:



Fridge-freezers



Fridge-freezers



○ Pure series



◇ Plus series



◊ Prime series



△ Peak series

	○ Pure series	◇ Plus series	◊ Prime series	△ Peak series
Freshness technology	EasyFresh	EasyFresh	EasyFresh on telescopic rails	EasyFresh on telescopic rails
		BioFresh on telescopic rails	BioFresh with SoftTelescopic	BioFresh Professional with SoftTelescopic
	DuoCooling	DuoCooling	DuoCooling	DuoCooling
	FreshAir filter	FreshAir filter	FreshAir filter	FreshAir filter
	SmartFrost	SmartFrost	SmartFrost	SmartFrost
	NoFrost	NoFrost	NoFrost	NoFrost on telescopic rails
Comfort & flexibility		Divisible glass shelf	Divisible glass shelf	Divisible glass shelf
		SoftSystem soft stop mechanism	SoftSystem soft stop mechanism	SoftSystem soft stop mechanism
		VarioSafe	VarioSafe	VarioSafe
			VarioBoxes	VarioBoxes
			Butter dish	Butter dish
	Egg tray	Egg tray	Adjustable egg tray	Adjustable egg tray
		Bottle shelf	Bottle shelf	Bottle shelf
		Ice cube tray	Ice cube tray with lid	Ice cube tray with lid
				FlexSystem
				Freezer tray
Design	Top fridge compartment lighting	Top fridge compartment lighting	LightTower	LightTower
			Lighting BioFresh safe	Lighting BioFresh safe
			Freezer compartment lighting	Freezer compartment lighting
				IceMaker lighting
				Fan lighting
			SmartSteel rear wall	SmartSteel rear wall
				SmartSteel door interior
	Transparent glass	Transparent glass	Satin finish glass	Satin finish glass
	Stainless steel look shelves	Stainless steel look shelves	Glass & stainless steel rack	Glass & stainless steel rack
	Touch display	Touch display	Touch & Swipe display	Touch & Swipe display
Connectivity (SmartDeviceBox)	Can be retrofitted	Can be retrofitted or integrated ("i" models)	Can be retrofitted or integrated ("i" models)	Can be retrofitted or integrated ("i" models)
Water & ice		IceMaker	IceMaker	IceMaker
				InfinitySpring

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

Unique features



BioFresh

At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



NoFrost

When you open your freezer, you want to see frozen food – and certainly not ice and frost. NoFrost protects the freezer compartment from unwanted icing, which consumes a lot of energy and can be expensive. NoFrost means no more tedious and time-consuming defrosting of the freezer compartment, more time for other things – and saving money.



Touch display

Fingertip control: the touch display enables easy and intuitive operation of your Liebherr. All functions are clearly arranged on the display. By gently tapping a finger, for example, you can easily select the functions or check the current temperature of your refrigerator.



Side-by-Side concept

The side-by-side concept makes it possible to position fridges, freezers and wine cabinets to suit your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. More information see page 26 – 29.



Versatile bottle shelf

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



DuoCooling

DuoCooling uses two completely separate refrigeration circuits to ensure no air is exchanged between the fridge and freezer compartments. The food neither dries out nor is odour transferred. This means throwing less away, shopping less often, but saving more and greater enjoyment.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



GlassLine

Made from safety glass, the stylish GlassLine fittings add the finishing touches to the high-quality interior design. These satin-finished glass shelves, with premium quality stainless steel edging, are scratch-resistant and easy to clean. The sectioned, slide-under glass shelf offers outstanding flexibility of use.



SoftSystem

From breakfast to a midnight snack – a fridge needs to be open and closed on many occasions. And your Liebherr makes this a lot of fun. With the SoftSystem, your fridge door closes softly and safely, and in a way which is pleasantly quiet and light. Bottles stored in the inside door remain securely in place – nothing rattles or wobbles.



3 bottle shelf

Now your bottles stay where they should. The 3 bottle shelf securely holds three bottles in your fridge ready to be used. The bottle shelf fits on every glass shelf and is therefore very flexible. And if you need the space for other reasons, simply take the shelf out of the fridge.



IceMaker

Are there any ice cubes left? An IceMaker means you never have to ask. With the IceMaker with fixed water connection, the water comes directly from the tap. The MaxIce function allows you to produce up to 1.5 kg of ice cubes a day. The ice cube separator helps to divide the drawer into any size you want – for example, ice cubes on the left, ice cream on the right – or just for ice cubes.



ECBN 6256



← 91 →

↑
203
↓

ECBN 6256
PremiumPlus

Door-on-door / fully integrated appliance

Energy efficiency class:	F
Energy consumption year / 24 hrs:	341 / 0.934 kWh
Total volume ¹ :	522 l
Volume:	Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 159.5 l
Noise output / noise class:	40 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	203.2 - 207.2 / 91.5 / at least 61.0
Special fitting depth see installation diagram	



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ********

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

Key features

- Height-adjustable feet at front and back
- Door hinge left fixed/right fixed



LED light columns

The LED light columns integrated on both sides ensure even illumination of the refrigeration compartment. The special satin finish of the light cover creates an elegant, high-quality lighting mood. The gentle increase in brightness when you open the appliance is particularly pleasant.



Versatile bottle shelf

The versatile bottle shelf is an innovative feature in all BioFresh Premium models. It can be positioned above or below the glass shelf to suite individual requirements.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.



ECBN 5066



ECBN 6156
PremiumPlus

Door-on-door / fully integrated appliance

Energy efficiency class:	F A G
Energy consumption year / 24 hrs:	414 / 1.134 kWh
Total volume ¹ :	522 l
Volume: Fridge: 292.2 l / BioFresh compartment: 70.6 l / Freezer compartment: 159.5 l	
Noise output / noise class:	41 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	203.2 - 207.2 / 91.5 / at least 61.0
Special fitting depth see installation diagram	



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves
- Variable use bottle trays
- LED light column on both sides and LED ceiling lighting
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ****

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.9 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 12 h
- Freezing capacity in 24 hrs: 10 kg

Key features

- Height-adjustable feet at front and back
- Choose from left (617) or right (001) hand hinge, fixed



ECBN 5066
PremiumPlus

Door-on-door / fully integrated appliance

Energy efficiency class:	F A G
Energy consumption year / 24 hrs:	326 / 0.893 kWh
Total volume ¹ :	402 l
Volume: Fridge: 215.3 l / BioFresh compartment: 62.1 l / Freezer compartment: 124.6 l	
Noise output / noise class:	42 dB(A) / D
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	203.2 - 207.2 / 76.2 / at least 61.0
Special fitting depth see installation diagram	



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge and freezer compartments
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, egg tray
- 3 GlassLine storage shelves, of which one is divided into two parts
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes on telescopic rails set variably to either HydroSafe or DrySafe

Freezer compartment ****

- 2 drawers on telescopic rails, self-retracting
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 0.8 kg
- Ice cube reservoir: 2.7 kg
- LED lighting
- Temperature rise time: 16 h
- Freezing capacity in 24 hrs: 6 kg

Key features

- Height-adjustable feet at front and back
- Choose from left (617) or right (001) hand hinge, fixed



IceMaker

The IceMaker with fixed water connection provides you with a constant supply of ice cubes for every occasion. An integrated water filter ensures optimum water quality at all times. The electronic display indicates when the water filter needs replacing. The NoFrost technology keeps the freezer constantly frostfree.



Drawers on telescopic runners

The drawers on telescopic runners are high-quality, smooth-running and convenient to use, even when heavily filled. They ensure an ideal overview and plenty of space for storage.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.



Side
by
Side
178



178

SBS 7014 Premium

Door-on-door / fully integrated appliance	SIGN 3576
Energy efficiency class:	F A G
Energy consumption year / 24 hrs:	298 / 0.816 kWh
Total volume ¹ :	216 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0

- No Frost
- Soft System
- LED
- Ice Maker
- Telescopic Rails

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **E4 *****

- 9 drawers, of which 5 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube reservoir: 1.5 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 11 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinge, left

Door-on-door / fully integrated appliance	IKBP 3560
Energy efficiency class:	D A G
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume ¹ :	309 l
Volume:	Fridge: 215.2 l / BioFresh compartment: 94.1 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0

- Bio Fresh
- Super Silent
- Soft System
- Soft-Telescopic

Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Door alarm: acoustic

Fridge and BioFresh compartments

- PowerCooling
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Variable bottle shelf
- LED light column on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, of which 2 can be set variably to Fruit & Vegetable-Safe or DrySafe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging

Also available as:


IKB 3560 with 156 / 0.427 kWh

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.

Overview of product range according to recess and series







- △ Peak series
- ◻ Prime series
- ◇ Plus series
- Pure series

Fridge-freezers



Door-on-door		
BioFresh Professional/NoFrost	ICBNdi 5183	
BioFresh Professional/SmartFrost	ICBdi 5182	
BioFresh/NoFrost	ICBNd 5163	
	ICBNd 5153	
	ICBNei 5123	
	ICBb 5152	
BioFresh/SmartFrost	ICBdi 5122	
	EasyFresh/NoFrost	ICNdi 5173
		ICNdi 5153
ICNe 5133		
EasyFresh/SmartFrost	ICNd 5123	
	ICd 5123	
	Sliding door	
BioFresh/SmartFrost	ICBSd 5122	
EasyFresh/SmartFrost	ICSe 5122	
	ICSe 5103	

Fridges



Door-on-door						
BioFresh Professional	IRBdi 5180					
	IRBdi 5171		IRBd 4571	IRBd 4171		
BioFresh/OpenStage			IRBd 4570	IRBb 4170		
	IRBPdi 5170					
BioFresh	IRBdi 5151	IRBe 4851	IRBd 4551	IRBd 4151		
	IRBdi 5150		IRBd 4550	IRBd 4150	IRBd 4050	
	IRBe 5121		IRBd 4521	IRBd 4121		
	IRBe 5120		IRBd 4520	IRBd 4120	IRBd 4020	
EasyFresh				IRd 4151		IRd 3951
				IRd 4150		IRd 3950
					IRe 4021	IRe 3921
					IRe 4020	IRe 3920
Cellar compartment/ BioFresh	IRf 5101					IRf 3901
	IRe 5100					IRf 3900
	IRCBf 5121					
	IRCF 5121					
Bottle pull-out/ EasyFresh	IRDe 5121					
	IRDe 5120					
Sliding door						
EasyFresh				IRSe 4101		IRSF 3901
				IRSe 4100		IRSF 3900



IXCC 5165
Prime

Door-on-door / fully integrated appliance	SICNd 5153
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	181 / 0.495 kWh
Total volume ¹ :	254 l
Volume:	Fridge: 184.4 l / Freezer compartment: 69.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinge, left
- Dry rear wall in stainless steel with SmartSteel

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails



Door-on-door / fully integrated appliance	ICBNd 5163
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	208 / 0.569 kWh
Total volume ¹ :	246 l
Volume:	Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 70.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 5.0 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe



IXCC 5155
Prime

Door-on-door / fully integrated appliance	SICNd 5153
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	181 / 0.495 kWh
Total volume ¹ :	254 l
Volume:	Fridge: 184.4 l / Freezer compartment: 69.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinge, left
- Dry rear wall in stainless steel with SmartSteel

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails



Door-on-door / fully integrated appliance	ICBNd 5153
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	207 / 0.567 kWh
Total volume ¹ :	245 l
Volume:	Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 69.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe



178

ICBNdi 5183
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	208 / 0.569 kWh
Total volume ¹ :	246 l
Volume: Fridge: 104.5 l / BioFresh compartment: 70.7 l / Freezer compartment: 70.9 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem

- InfinitySpring with fixed 3/4" water connection

Freezer compartment ********

- 3 drawers, of which 2 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 5.0 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel



178

ICBNd 5163
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	208 / 0.569 kWh
Total volume ¹ :	246 l
Volume: Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 70.9 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 3 drawers, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 5.0 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



178

ICBNd 5153
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	207 / 0.567 kWh
Total volume ¹ :	245 l
Volume: Fridge: 104.1 l / BioFresh compartment: 71.2 l / Freezer compartment: 69.9 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



178

ICBNei 5123
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	259 / 0.709 kWh
Total volume ¹ :	244 l
Volume: Fridge: 103.3 l / BioFresh compartment: 70.9 l / Freezer compartment: 69.9 l	
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



ICBdi 5182
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	182 / 0.498 kWh
Total volume ¹ :	256 l
Volume: Fridge: 131.6 l / BioFresh compartment: 70.7 l / Freezer compartment: 54.4 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting

- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem
- InfinitySpring with fixed 3/4" water connection

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel



ICBb 5152
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	B
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Total volume ¹ :	256 l
Volume: Fridge: 131.0 l / BioFresh compartment: 71.2 l / Freezer compartment: 54.4 l	
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge, BioFresh and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting

- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



ICBdi 5122
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	182 / 0.498 kWh
Total volume ¹ :	255 l
Volume: Fridge: 130.0 l / BioFresh compartment: 70.9 l / Freezer compartment: 54.4 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging



ICBSd 5122
Plus

Sliding door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	182 / 0.498 kWh
Total volume ¹ :	255 l
Volume: Fridge: 130.0 l / BioFresh compartment: 70.9 l / Freezer compartment: 54.4 l	
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging



ICNdi 5173
Peak

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	183 / 0.501 kWh
Total volume ¹ :	255 l
Volume:	Fridge: 184.4 l / Freezer compartment: 70.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails

Freezer compartment ********

- 3 drawers, of which 2 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection, LED lighting
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 5.0 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel



ICNdi 5153
Prime

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	181 / 0.495 kWh
Total volume ¹ :	254 l
Volume:	Fridge: 184.4 l / Freezer compartment: 69.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox included
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



ICNe 5133
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	228 / 0.624 kWh
Total volume ¹ :	254 l
Volume:	Fridge: 183.3 l / Freezer compartment: 70.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

Freezer compartment ********

- 3 drawers, VarioSpace
- IceMaker with water tank
- Ice cube production in 24 hrs: 1.2 kg
- Ice cube reservoir: 5.0 kg
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging



ICNd 5123
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	181 / 0.495 kWh
Total volume ¹ :	253 l
Volume:	Fridge: 183.3 l / Freezer compartment: 69.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging



178

ICSe 5122
Plus

Sliding door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	199 / 0.545 kWh
Total volume ¹ :	266 l
Volume:	Fridge: 211.7 l / Freezer compartment: 54.4 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 2 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails



178

ICd 5123
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	183 / 0.501 kWh
Total volume ¹ :	264 l
Volume:	Fridge: 183.3 l / Freezer compartment: 81.1 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Ice cube tray
- Temperature rise time: 11 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails



178

ICSe 5103
Pure

Sliding door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	228 / 0.624 kWh
Total volume ¹ :	264 l
Volume:	Fridge: 183.3 l / Freezer compartment: 81.1 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and freezer compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Automatic SuperFrost, quantity-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 3 drawers, VarioSpace
- Temperature rise time: 11 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails



122

ICTS 2231
Comfort

Sliding door / fully integrated appliance

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	232 / 0.635 kWh
Total volume ¹ :	197 l
Volume:	Fridge: 155.1 l / Freezer compartment: 42.7 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	ST (+16 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	122 - 122.5 / 56 - 57 / at least 55.0



Controls

- Mechanical control in the interior, control dial

Fridge compartment

- Comfort GlassLine storage shelf with bottle holder, adjustable egg tray
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- Interior lighting
- 2 BioCool-Boxes

Freezer compartment ********

- Ice cube tray with lid
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 3 kg
- Safety glass fittings

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridges



Fridges



○ Pure series



◇ Plus series



◊ Prime series



△ Peak series

	○ Pure series	◇ Plus series	◊ Prime series	△ Peak series
Freshness technology	EasyFresh	EasyFresh	EasyFresh on telescopic rails	EasyFresh on telescopic rails
		BioFresh on telescopic rails	BioFresh with SoftTelescopic	BioFresh Professional with SoftTelescopic
	FreshAir filter	FreshAir filter	FreshAir filter	FreshAir filter
Comfort & flexibility		Divisible glass shelf	Divisible glass shelf	Divisible glass shelf
		SoftSystem soft stop mechanism	SoftSystem soft stop mechanism	SoftSystem soft stop mechanism
		VarioSafe	VarioSafe	VarioSafe
			VarioBoxes	VarioBoxes
			Butter dish	Butter dish
	Egg tray	Egg tray	Adjustable egg tray	Adjustable egg tray
		Bottle shelf	Bottle shelf	Bottle shelf
		Ice cube tray	Ice cube tray with lid	Ice cube tray with lid
				FlexSystem
				OpenStage drawers
Design	Top or side fridge compartment lighting	Top or side fridge compartment lighting	LightTower	LightTower
			Lighting BioFresh safe	Lighting BioFresh safe
				Fan lighting
			SmartSteel rear wall	SmartSteel rear wall
				SmartSteel door interior
	Transparent glass	Transparent glass	Satin finish glass	Satin finish glass
	Stainless steel look shelves	Stainless steel look shelves	Glass & stainless steel rack	Glass & stainless steel rack
Touch display	Touch display	Touch & Swipe display	Touch & Swipe display	
Connectivity (SmartDeviceBox)	Can be retrofitted	Can be retrofitted or integrated ("i" models)	Can be retrofitted or integrated ("i" models)	Can be retrofitted or integrated ("i" models)
Water & ice				InfinitySpring

The standard features mentioned above may vary depending on the model. Details can be found in the model description.

Unique features



BioFresh

At a temperature of just over 0°C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment.



EasyFresh

The guarantee of market freshness in the home is our EasyFresh-Safe. Whether it's unpackaged vegetables or fruit, this ensures optimal storage for everything. Thanks to the air-tight closure, the food causes the humidity in the safe to rise. This keeps the food fresh for a long time.



LED

For a quick overview of everything in the refrigerator: the LED side lighting helps you to keep your food in view. The LEDs are positioned so that the light beams go up and down. And the LEDs integrated flush into the side walls mean that the valuable usable area is fully maintained.



InfinitySpring

A source of fresh, cool drinking water in your kitchen. InfinitySpring sounds like something from a fairy tale. The water dispenser enables drip-free water dispensing and provides fresh, cold water. Simply press the panel with the carafe or glass, and enjoy the water. This enables you to save on purchasing bottles of water and to live more sustainably.



Side-by-Side concept

The side-by-side concept makes it possible to position fridges, freezers and wine cabinets to suit your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. More information see page 26 – 29.



Versatile bottle shelf

Expecting guests and want to chill a few more drinks than usual? The bottle shelf above the BioFresh safes exists for this very reason. Simply remove the glass shelf above the bottle shelf in one easy step – and you can now safely store and cool bottles of various sizes.



VarioBoxes

Where did I put that little packet of yeast? And where's the tube of mustard? To easily find the small items in the fridge, there are the VarioBoxes. They keep everything clearly arranged and organised in the inside door. Their transparent design means you immediately see what's inside. The boxes are easy to remove – and thanks to the pull-out stop, nothing will fall to the floor- guaranteed.



PowerCooling

Do you want to be sure that the cold is distributed as evenly as possible in your refrigerator? If so, the PowerCooling system is what you need. The fan – as powerful as it is quiet – distributes the cold air efficiently throughout the entire refrigeration compartment.



Freezer compartment

Do you want to avoid spending time changing the door hinge of the freezer compartment when installing your Liebherr in the furniture niche? The slider control means this can be done in seconds and without any manual skills. Simply slide the slider on the freezer compartment from right to left – that's it, done! This saves you a lot of time.



SoftTelescopic

Look forward to opening your BioFresh safes. And this is not just because of the fresh food – but also because opening is so easy, and closing is automatic and cushioned. The telescopic rails slide the safe gently towards you. And because these extend fully, you have the best overview of the contents.



FlexSystem

Small and delicate fruit in the refrigerator can easily roll out of sight or become crushed. That's why your Liebherr comes with the FlexSystem. Two flexibly positionable boxes in the BioFresh safe ensure everything is clearly arranged and organised. And they also safely protect even the smallest raspberry from bruising or from being mixed up with other foods.



Versatile egg shelf

Do you like chicken eggs? So does your Liebherr – that's why it has the 2in1 egg tray. This not only provides space for up to 20 chicken eggs, but also for up to 24 quail eggs. The egg tray consists of an outer and an inner part which can be slid into each other in different ways. By turning the tray over, the quail egg holes can be used.



IRBPdi 5170



IRBPdi 5170
Peak

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume ¹ :	297 l
Volume:	Fridge: 199.0 l / BioFresh compartment: 98.4 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Butter dish
- 5 GlassLine OpenStage drawers on fully extendible telescopic rails with SoftTelescopic
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel

Available 4th quarter 2021



IRBdi 5180
Peak

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume ¹ :	296 l
Volume:	Fridge: 198.1 l / BioFresh compartment: 97.9 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, of which one is with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem

- InfinitySpring with fixed 3/4" water connection

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.



IRBdi 5171
Peak

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	164 / 0.449 kWh
Total volume ¹ :	276 l
Volume:	Fridge: 151.6 l / BioFresh compartment: 97.9 l / Freezer compartment: 27.1 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, of which one is with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel



OpenStage

Now there's a clear view of everything. The different heights of the drawers make it easy to store food of different sizes. In the bottom drawer, practical dividers ensure bottles are held securely in place. And, thanks to the transparent GlassLine drawers, you have a clear view of everything from bottom to top.



IRBdi 5150
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	125 / 0.342 kWh
Total volume ¹ :	296 l
Volume:	Fridge: 197.7 l / BioFresh compartment: 98.4 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



IRBdi 5151
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	164 / 0.449 kWh
Total volume ¹ :	276 l
Volume:	Fridge: 151.3 l / BioFresh compartment: 98.4 l / Freezer compartment: 27.1 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox included
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 3 BioFresh-Safes with SoftTelescopic, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

Freezer compartment **4******

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



IRBe 5120
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	156 / 0.427 kWh
Total volume ¹ :	294 l
Volume:	Fridge: 195.8 l / BioFresh compartment: 98.2 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 6 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 3 BioFresh-Safes on telescopic rails, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRBe 5121
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	204 / 0.558 kWh
Total volume ¹ :	275 l
Volume:	Fridge: 150.2 l / BioFresh compartment: 98.2 l / Freezer compartment: 27.1 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- Light on both sides
- 3 BioFresh-Safes on telescopic rails, 2 Fruit & Vegetable-Safes, 1 Meat & Dairy-Safe

Freezer compartment **4******

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging

You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



IRCBf 5121



IRCBf 5121
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	F A G
Energy consumption year / 24 hrs:	221 / 0.605 kWh
Total volume ¹ :	265 l
Volume:	Fridge: 83.0 l / BioFresh compartment: 70.9 l / Cellar compartment: 95.9 l / Freezer compartment: 15.9 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



IRCF 5121
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	F A G
Energy consumption year / 24 hrs:	190 / 0.520 kWh
Total volume ¹ :	274 l
Volume:	Fridge: 162.2 l / Cellar compartment: 95.9 l / Freezer compartment: 15.9 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 – 178.8 / 56 – 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and cellar compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 2 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- Light on both sides
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Cellar compartment

- Fully extendible pull-out drawer, with SoftTelescopic
- Independently regulated cellar compartment temperature (6 °C to 14 °C)
- Removable bottle basket

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge and cellar compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- Light on both sides
- 1 EasyFresh-Safe on running rails

Cellar compartment

- Fully extendible pull-out drawer, with SoftTelescopic
- Cellar compartment temperature about 5 °C above fridge temperature
- Removable bottle basket

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



BioFresh

At a temperature of just over 0 °C and with the ideal humidity, fresh food can keep its appetising appearance and retain healthy vitamins and minerals for considerably longer than in a normal fridge compartment.



Cellar compartment

Simply store supplies such as potatoes or drinks in your Liebherr's cellar-temperature compartment. It contains a removable basket, a storage tray and a drawer. The cellar-temperature compartment moves out gently on telescopic rails and closes using a self-closing mechanism with soft stop. The temperature is adjustable between 6 °C and 14 °C – depending on the food being stored.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.

Integrated fridges



IRDe 5120
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	309 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- LED ceiling lighting
- 1 EasyFresh-Safe on telescopic rails
- Pull-out drawer with partial extension on telescopic rails
- 2 removable bottle baskets

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRDe 5121
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E
Energy consumption year / 24 hrs:	171 / 0.468 kWh
Total volume ¹ :	286 l
Volume:	Fridge: 259.2 l / Freezer compartment: 27.1 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Light on both sides
- 1 EasyFresh-Safe on telescopic rails
- Pull-out drawer with partial extension on telescopic rails
- 2 removable bottle baskets

Freezer compartment **E4*****

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRDe 5121



Bottle baskets

Do your family and party guests love cold drinks? Often the inside door of the refrigerator isn't enough for bottle cooling. However, your Liebherr will be happy to help. There's plenty of room in the bottle baskets for bottles and Tetrapaks – or even a whole crate of beer. The shelves of the baskets rest on telescopic rails and slide out gently for easy removal.



Pull-out shelf

Without the bottle baskets the pull-out shelf offers space for a commercial bottle crate. The smooth-running telescopic rails ensure easy access to the large stock of chilled drinks.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



178

IRe 5100
Pure

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	308 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 7 GlassLine storage shelves
- LED ceiling lighting
- 1 EasyFresh-Safe on telescopic rails

Key features

- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.



178

IRf 5101
Pure

Door-on-door / fully integrated appliance

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	214 / 0.586 kWh
Total volume ¹ :	286 l
Volume:	Fridge: 259.0 l / Freezer compartment: 27.1 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves
- Light on both sides
- 1 EasyFresh-Safe on telescopic rails

Freezer compartment ******

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



158

IRBe 4851
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	194 / 0.531 kWh
Total volume ¹ :	238 l
Volume:	Fridge: 144.2 l / BioFresh compartment: 67.0 l / Freezer compartment: 27.1 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	157.4 - 159 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment ******

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 14 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



140

IRBd 4570
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	224 l
Volume:	Fridge: 158.0 l / BioFresh compartment: 66.6 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel

You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



140

IRBd 4571
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	145 / 0.397 kWh
Total volume ¹ :	207 l
Volume: Fridge: 125.4 l / BioFresh compartment: 66.6 l / Freezer compartment: 15.9 l	
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem

Freezer compartment

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel



140

IRBd 4550
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	224 l
Volume: Fridge: 157.6 l / BioFresh compartment: 67.0 l	
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



140

IRBd 4551
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	145 / 0.397 kWh
Total volume ¹ :	207 l
Volume: Fridge: 125.0 l / BioFresh compartment: 67.0 l / Freezer compartment: 15.9 l	
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



140

IRBd 4520
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	223 l
Volume: Fridge: 156.2 l / BioFresh compartment: 66.8 l	
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



140

IRBd 4521
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	145 / 0.397 kWh
Total volume ¹ :	206 l
Volume:	Fridge: 124.1 l / BioFresh compartment: 66.8 l / Freezer compartment: 15.9 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- Light on both sides
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe



122

IRBb 4170
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	B
Energy consumption year / 24 hrs:	72 / 0.197 kWh
Total volume ¹ :	191 l
Volume:	Fridge: 124.4 l / BioFresh compartment: 66.6 l
Noise output / noise class:	29 dB(A) / A UltraSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem



122

IRBd 4171
Peak

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	148 / 0.405 kWh
Total volume ¹ :	174 l
Volume:	Fridge: 91.8 l / BioFresh compartment: 66.6 l / Freezer compartment: 15.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall and door panel in stainless steel with SmartSteel

Fridge and BioFresh compartments

- PowerCooling with Ambilight with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe with HydroBreeze, 1 Meat & Dairy-Safe, 1 FlexSystem



122

IRBd 4150
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	191 l
Volume:	Fridge: 124.1 l / BioFresh compartment: 67.0 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe



IRBd 4120



Space for baking tray

Do you want to keep that home-baked fruit pie fresh? Or maybe a prepared pizza to be baked later on? If so, simply slide your baking tray into your Liebherr – it has plenty of space for storing a baking tray. Really convenient – you can slide the baking tray in and out when the door is opened at 90°.



↑
122
↓

IRBd 4151
Prime

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	148 / 0.405 kWh
Total volume ¹ :	174 l
Volume:	Fridge: 91.5 l / BioFresh compartment: 67.0 l / Freezer compartment: 15.9 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 – 123.6 / 56 – 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment **4******

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



↑
122
↓

IRBd 4120
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	189 l
Volume:	Fridge: 123.0 l / BioFresh compartment: 66.8 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 – 123.6 / 56 – 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



↑
122
↓

IRBd 4121
Plus

Door-on-door / fully integrated appliance	
Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	148 / 0.405 kWh
Total volume ¹ :	173 l
Volume:	Fridge: 90.9 l / BioFresh compartment: 66.8 l / Freezer compartment: 15.9 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 – 123.6 / 56 – 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- Light on both sides
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Freezer compartment **4******

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



IRd 4150
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	81 / 0.221 kWh
Total volume ¹ :	203 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray
- 6 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRd 4151
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	119 / 0.326 kWh
Total volume ¹ :	183 l
Volume:	Fridge: 167.3 l / Freezer compartment: 15.9 l
Noise output / noise class:	29 dB(A) / A UltraSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED light panel on both sides
- 1 EasyFresh-Safe on telescopic rails

Freezer compartment ****

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRSe 4100
Pure

Sliding door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	102 / 0.279 kWh
Total volume ¹ :	201 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 5 GlassLine storage shelves
- LED ceiling lighting
- 1 EasyFresh-Safe on running rails

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRSe 4101
Pure

Sliding door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	149 / 0.408 kWh
Total volume ¹ :	182 l
Volume:	Fridge: 166.5 l / Freezer compartment: 15.9 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- Light on both sides
- 1 EasyFresh-Safe on running rails

Freezer compartment ****

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.

You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



102

IRBd 4050
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Total volume ¹ :	157 l
Volume:	Fridge: 88.6 l / BioFresh compartment: 69.0 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	102.4 - 104 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge and BioFresh compartments
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Premium GlassLine storage shelf with bottle holder, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED light panel on both sides
- LED BioFresh lighting
- 2 BioFresh-Safes with SoftTelescopic, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Dry rear wall in stainless steel with SmartSteel



102

IRBd 4020
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Total volume ¹ :	156 l
Volume:	Fridge: 88.0 l / BioFresh compartment: 68.7 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	102.4 - 104 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge and BioFresh compartments

- PowerCooling with FreshAir activated charcoal filter
- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- Bottle shelf
- LED ceiling lighting
- 2 BioFresh-Safes on telescopic rails, 1 Fruit & Vegetable-Safe, 1 Meat & Dairy-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



102

IRe 4020
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	97 / 0.265 kWh
Total volume ¹ :	166 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	102.4 - 104 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



102

IRe 4021
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	147 / 0.402 kWh
Total volume ¹ :	146 l
Volume:	Fridge: 130.9 l / Freezer compartment: 15.9 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	102.4 - 104 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- 1 EasyFresh-Safe

Freezer compartment ********

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



Side
by
Side

The Mix and Match food storage centre concept.
For more information about the Side-by-Side concept
see pages 26 – 29.

Integrated full BioFresh fridge



Key electronics

The key electronics enable all BioFresh drawers to be set to 'Dry' for a dry environment for storing meat, fish and dairy products or 'Hydro' for a humid environment for storing fruit and vegetables.



SoftSystem

The SoftSystem feature provides added safety and convenience. Integrated on the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.



SIBP 1650 Premium

Door-on-door / fully integrated appliance

Energy efficiency class:	C
Energy consumption year / 24 hrs:	99 / 0.271 kWh
Total volume ¹ :	86 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

BioFresh compartment

- PowerCooling
- 4 BioFresh-Safes, of which 3 on roller tracks, 1 FlexSystem
- Cabinet can be adjusted from HydroSafe to DrySafe

Key features

- Side wall heating and ceiling heating, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point.
You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



88

IRd 3950
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	75 / 0.205 kWh
Total volume ¹ :	136 l
Noise output / noise class:	29 dB(A) / A UltraSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



88

IRd 3951
Prime

Door-on-door / fully integrated appliance

Energy efficiency class:	D <small>A G</small>
Energy consumption year / 24 hrs:	118 / 0.323 kWh
Total volume ¹ :	117 l
Volume:	Fridge: 101.6 l / Freezer compartment: 15.9 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- 2.4" TFT-colour display, Touch & Swipe
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 3 GlassLine storage shelves, of which one is divided into two parts
- 3 bottle shelf
- 1 EasyFresh-Safe

Freezer compartment ****

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



88

IRe 3920
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	94 / 0.257 kWh
Total volume ¹ :	136 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves, of which one is divided into two parts
- VarioSafe
- 3 bottle shelf
- LED ceiling lighting
- 1 EasyFresh-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



88

IRe 3921
Plus

Door-on-door / fully integrated appliance

Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	147 / 0.402 kWh
Total volume ¹ :	117 l
Volume:	Fridge: 101.6 l / Freezer compartment: 15.9 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves, of which one is divided into two parts
- 3 bottle shelf
- 1 EasyFresh-Safe

Freezer compartment ****

- 4-star freezer compartment, reversible door hinging
- Ice cube tray
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRf 3900
Pure

Door-on-door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	117 / 0.320 kWh
Total volume ¹ :	136 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 EasyFresh-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRf 3901
Pure

Door-on-door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	184 / 0.504 kWh
Total volume ¹ :	117 l
Volume:	Fridge: 101.6 l / Freezer compartment: 15.9 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves
- 1 EasyFresh-Safe

Freezer compartment

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRSf 3900
Pure

Sliding door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	117 / 0.320 kWh
Total volume ¹ :	136 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 4 GlassLine storage shelves
- LED ceiling lighting
- 1 EasyFresh-Safe

Key features

- Height-adjustable feet at front
- Reversible door hinging



IRSf 3901
Pure

Sliding door / fully integrated appliance

Energy efficiency class:	
Energy consumption year / 24 hrs:	184 / 0.504 kWh
Total volume ¹ :	117 l
Volume:	Fridge: 101.6 l / Freezer compartment: 15.9 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- LCD display monochrome, Touch electronics
- Digital temperature display for fridge compartment
- SmartDeviceBox: as an optional accessory
- Automatic SuperCool
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Fridge compartment

- Plastic door shelves with bottle holder
- 3 GlassLine storage shelves
- 1 EasyFresh-Safe

Freezer compartment

- 4-star freezer compartment, reversible door hinging
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 2 kg

Key features

- Height-adjustable feet at front
- Reversible door hinging

Freezers

Side
by
Side

All Liebherr freezers with aperture heights of 140 and 178 cm can be perfectly combined side by side with fridges and wine cabinets in various recesses to form a Mix and Match food centre. For more information about the Side-by-Side concept see pages 26 – 29.



Unique features



Freezer drawers

The extra high freezer drawers which run on castors can be conveniently pulled out when fully loaded. The drawers guarantee an excellent overview due to their transparent design and can be easily removed and cleaned.



Ice cube tray

The large ice cube tray is easy to fill with water thanks to its convenient fill opening. The lid seals on tightly so that the tray can be safely moved and placed in the appliance without spills.



IceMaker

The plumbed-in automatic IceMaker keeps you topped up with high-quality ice cubes for every occasion. Whether you need ice for a refreshing drink or a party with friends, with two drawers, the IceMaker holds all the ice cubes you'll need. Furthermore, it automatically keeps your supplies topped up and you can switch it off at any time.



SoftSystem

The stylish SoftSystem mechanism is integrated into the door and matches the colour of the interior door; it conveniently cushions movement to ensure extremely soft closure even when the door shelves are fully stocked. The door closes automatically from an opening angle of about 30°.



FrostSafe

With FrostSafe, the extra high and removable drawers are closed all the way around. This means the cold is not able to escape so quickly when opening the appliance. The transparent front to the compartments ensures an optimal overview of the frozen food.



Premium-electronics

The elegant Premium-electronics system ensures that the selected temperature is precisely maintained. All functions can be easily and conveniently managed by gently tapping the touchscreen. The temperature is displayed and can be read from the MagicEye's LCD display.



NoFrost

The NoFrost system from Liebherr provides rapid, fan-assisted, frost-free freezing for the safe, longterm storage of food. The NoFrost technology creates a much larger storage capacity and keeps the freezer constantly frost-free.



Side-by-Side concept

The side-by-side concept makes it possible to position fridges, freezers and wine cabinets to suit your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. More information see page 26 – 29.



LED lighting

The LED lighting is positioned above the drawers in order to save space. It ensures the best overview of your goods, saves energy and has a long life.



VarioSpace

All freezers with NoFrost and SmartFrost benefit from our practical VarioSpace concept – their drawers and the intervening Safety glass shelves can be conveniently removed to create extra storage space so that bulkier items can be stored.



FlexSystem

The freezer drawers are mounted on high-quality, smooth-running telescopic rails for ease of use, even when heavily filled. The drawers offer ample storage space and have a single-piece design for easy removal and cleaning.



SIGN 3576
Premium

Door-on-door / fully integrated appliance

Energy efficiency class:	F
Energy consumption year / 24 hrs:	298 / 0.816 kWh
Total volume ¹ :	216 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 9 drawers, of which 5 set on telescopic rails, VarioSpace
- IceMaker with fixed 3/4" water connection
- Ice cube reservoir: 1.5 kg
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 11 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinge, left



SIGN 3556
Premium

Door-on-door / fully integrated appliance

Energy efficiency class:	E
Energy consumption year / 24 hrs:	239 / 0.654 kWh
Total volume ¹ :	216 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 8 drawers, of which 6 set on telescopic rails, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 14 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinging



SIGN 3524
Comfort

Door-on-door / fully integrated appliance

Energy efficiency class:	F
Energy consumption year / 24 hrs:	298 / 0.816 kWh
Total volume ¹ :	216 l
Noise output / noise class:	39 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	177.2 - 178.8 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 8 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 14 kg
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinge, left



SIGN 2756
Premium

Door-on-door / fully integrated appliance

Energy efficiency class:	F
Energy consumption year / 24 hrs:	272 / 0.745 kWh
Total volume ¹ :	158 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	139.7 - 141.3 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, touch electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 6 drawers, of which 4 set on telescopic rails, VarioSpace
- Ice cube tray with lid
- LED lighting
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 10 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front
- Reversible door hinging



Side
by
Side

The freezers with niche heights of 72 and 88 cm can be perfectly combined with fridges and wine cabinets in various niches to create an individual Mix and Match combination. For more information about the Side-by-Side concept see pages 26 – 29.



IGX 1664
Premium

Door-on-door / fully integrated appliance

Energy efficiency class:	E A G
Energy consumption year / 24 hrs:	192 / 0.526 kWh
Total volume ¹ :	86 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10°C to +43°C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0

No Frost
Soft System

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 4 drawers, of which 3 set on roller tracks, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 8 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging



IGX 1624
Comfort

Door-on-door / fully integrated appliance

Energy efficiency class:	E A G
Energy consumption year / 24 hrs:	192 / 0.526 kWh
Total volume ¹ :	86 l
Noise output / noise class:	37 dB(A) / C
Climate rating:	SN-T (+10°C to +43°C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0

No Frost

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4*****

- 4 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 8 kg
- Safety glass fittings

Key features

- Ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.



IGN 1064



SmartFrost

With the SmartFrost technology, ice build-up is greatly reduced. This makes defrosting rarely necessary. The interior walls of the freezer compartment are very smooth and easy-to-clean. Freezer drawers and glass shelves made of safety glass can be removed easily.



IGS 1624
Comfort

Sliding door / fully integrated appliance	
Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	223 / 0.611 kWh
Total volume ¹ :	100 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **4******

- 4 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 5 kg
- Safety glass fittings

Key features

- Ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging



IGN 1064
Premium

Door-on-door / fully integrated appliance	
Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	183 / 0.501 kWh
Total volume ¹ :	65 l
Noise output / noise class:	36 dB(A) / C
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	71.4 - 73 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **3******

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 8 h
- Freezing capacity in 24 hrs: 5 kg
- 2 cold storage accumulators
- Safety glass fittings

Key features

- Ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging



IG 1024
Comfort

Door-on-door / fully integrated appliance	
Energy efficiency class:	E <small>A G</small>
Energy consumption year / 24 hrs:	171 / 0.468 kWh
Total volume ¹ :	73 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	71.4 - 73 / 56 - 57 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic

Freezer compartment **3******

- 3 drawers, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 4 kg
- Safety glass fittings

Key features

- Ceiling heating for Side-by-Side concept
- Height-adjustable feet at front
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.

Under-worktop





UIKo 1560
(Bottle case available as an optional accessory)



UIKo 1560 Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	132 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperCool
- Door alarm: visual and acoustic

Fridge compartment

- Butter dish
- 2 Premium GlassLine storage shelves, extendible, with variable egg tray
- Bottle compartment integrated in lower pull-out unit
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer
- LiftUp-Box

Key features

- Height-adjustable feet at front and back
- Fully extendible pull-out drawer with full extension



UIKo 1550 Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	F <small>A G</small>
Energy consumption year / 24 hrs:	114 / 0.312 kWh
Total volume ¹ :	132 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperCool
- Door alarm: visual and acoustic

Fridge compartment

- Butter dish
- 2 Premium GlassLine storage shelves, extendible, with variable egg tray
- Bottle compartment integrated in lower pull-out unit
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer

Key features

- Height-adjustable feet at front and back
- Fully extendible pull-out drawer with full extension



LiftUp Box

The LiftUp Box allows you to fully utilise the storage space below the pull-out drawer. It is ergonomically attached, easy to take out and can hold up to 4 kg. When pulled out, the LiftUp Box pushes up out of the base recess, allowing the food to be removed easily.



Bottle baskets

If more space is needed for beverages, removable bottle baskets (optional accessory) can be inserted*. They provide plenty of space for bottles (up to 1.5 l) and drinks packages. The integrated handle makes them easy to carry and the adjustable holders ensure the bottles are held securely. *In exchange for a removable storage shelf.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.

Integrated under-worktop fridges



UIKP 1550
Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	92 / 0.252 kWh
Total volume ¹ :	136 l
Noise output / noise class:	34 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0

Super
Silent

Soft
System

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperCool
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf, extra deep, with bottle holder, removable VarioBox, adjustable egg tray, butter dish
- 3 GlassLine storage shelves
- LED ceiling lighting
- 1 spacious fruit and vegetable drawer
- Sliding box

Key features

- Height-adjustable feet at front and back
- Reversible door hinging



UIKP 1554
Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	141 / 0.386 kWh
Total volume ¹ :	119 l
Volume:	Fridge: 104.8 l / Freezer compartment: 14.7 l
Noise output / noise class:	33 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0

Super
Silent

Soft
System

Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display for fridge compartment
- Automatic SuperCool
- Door alarm: visual and acoustic

Fridge compartment

- Premium GlassLine storage shelf, extra deep, with bottle holder, removable VarioBoxes, adjustable egg tray, butter dish
- 2 GlassLine storage shelves
- LED lighting
- 1 spacious fruit and vegetable drawer
- Sliding box

Freezer compartment **** ** ***

- Hinged 4-star freezer compartment door
- Ice cube tray
- Temperature rise time: 7 h
- Freezing capacity in 24 hrs: 3 kg

Key features

- Height-adjustable feet at front and back
- Reversible door hinging



UIKP 1550



Deep shelves

A lot of goods can be stored on the deep shelves, reducing the need to bend down when storing and removing items. The items are delivered to the customer. This is a great ergonomic advantage, especially for under-worktop appliances that are installed below the table edge.



Side-by-Side

UIKP 1550 is suitable for the Side-by-Side combination with the under-worktop freezer SUIGN 1554 (or SUIG 1514) and/or the full BioFresh under-worktop fridge SUIB 1550.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.

Integrated under-worktop full BioFresh fridge



SUIB 1550



Tray inserted into the base recess

The tray inserted into the base recess enables the optimal use of the lower space in the appliance. It can be easily removed and with a capacity of approx. 4 litres offers sufficient space for smaller goods.



SUIB 1550 Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	C
Energy consumption year / 24 hrs:	96 / 0.263 kWh
Total volume ¹ :	79 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Door alarm: visual and acoustic

BioFresh compartment

- 2 GlassLine storage shelves
- 3 BioFresh-Safes, 1 FlexSystem
- Cabinet can be adjusted from HydroSafe to DrySafe
- Removable tray (4 litres in the base recess)

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front and back
- Reversible door hinging



SUIGN 1554 Premium

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	181 / 0.495 kWh
Total volume ¹ :	79 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, quantity-controlled
- FrostControl
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment **4*****

- 3 drawers, of which 2 set on roller tracks, VarioSpace
- Ice cube tray with lid
- Temperature rise time: 9 h
- Freezing capacity in 24 hrs: 8 kg
- 2 cold storage accumulators
- Safety glass fittings
- Removable tray (4 litres in the base recess)

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front and back
- Reversible door hinging

Integrated under-worktop freezers



SUIG 1514 Comfort

Door-on-door / under-worktop appliance for integrated use

Energy efficiency class:	E
Energy consumption year / 24 hrs:	168 / 0.460 kWh
Total volume ¹ :	95 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-T (+10 °C to +43 °C)
Aperture dimensions in cm (h / w / d):	82 - 88 / 60 / at least 55.0



Controls

- MagicEye behind-the-door, key electronic
- Digital temperature display
- Automatic SuperFrost, time-controlled
- Warning signal in case of fault: visual and acoustic
- Door alarm: visual and acoustic

Freezer compartment **4*****

- 3 drawers, VarioSpace
- Temperature rise time: 10 h
- Freezing capacity in 24 hrs: 6 kg
- Safety glass fittings

Key features

- Side wall heating on both sides, suitable for combination with other refrigerators, freezers and/or wine appliances
- Height-adjustable feet at front and back
- Reversible door hinging

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



An overview of our wine cabinets




Vinidor range



The Vinidor range offers maximum flexibility with two separately controlled temperature zones. The temperature of these can be set independently between +5°C and +20°C. This means that red and white wines can be stored at their ideal serving temperatures in the same cabinet.

from page 108



GrandCru range



Wine storage cabinets offer similar conditions to a wine cellar. This range facilitates the storage of red and white wines at the correct long term storage temperatures or individual serving temperatures. The temperature can be adjusted from +5°C to +20°C as appropriate, and is both even and constant throughout the entire appliance interior.

from page 115

Unique features



Touch-electronic control system

The electronic LCD display offers clear menu navigation and a Touch-electronic control system provides bespoke storage conditions. The digital temperature display can be read from the outside of appliances with glass doors. The Touch-electronic navigation ensures easy selection and use of the numerous control functions.



LED lighting

All wine cabinets feature dimmable LED lighting, which evenly illuminates the interior and can be left on permanently if desired. Because LEDs generate minimal heat, wines can be sympathetically illuminated and beautifully presented for an extended period of time.



Side-by-side concept

The side-by-side concept makes it possible to position fridges, freezers and wine cabinets to meet your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. More information see page 26 – 29.



Stainless steel frame and handle

The high-quality, easy-to-fit stainless steel frame and handle enables all EWTdf models to be elegantly integrated into any kitchen. The robust stainless steel handle makes opening the door effortless. Available as an optional accessory kit.



FreshAir activated charcoal filter

The integrated FreshAir activated charcoal filter purifies the internal air and traps unpleasant odours. It is easy to replace and guarantees optimum air quality.



Presentation shelf

The presentation shelf is ideal for keeping open bottles at the perfect temperature and without the risk of spills.



Wooden shelves mounted on telescopic rails

The Vinidor appliances are equipped with solid wooden shelves mounted on telescopic rails. The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access. The clip-on labelling system provides a quick and clear overview of your wine store.



TipOpen technology

The handle-free glazed door guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines. The TipOpen technology opens the glazed door 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will shut it again.



SoftSystem

The SoftSystem feature provides added safety and convenience. Integrated within the door, the SoftSystem cushions movement when the door is closed. This SoftSystem ensures that the door closes gently even when fully loaded inside. The door automatically closes from an angle of approximately 30°.



Accessories drawer

The easy-glide accessories drawer can be used to store accessories directly below wine storage cabinets in the WKE 5 model range. This increases the 45 cm recess to a 60 cm one. Available in white glass (9792 449), black glass (9792 451) and stainless steel (9792 453).



Flexible clip-on labelling system

The flexible clip-on labelling system can be directly written on to provide a quick and well-organised overview of the wine collection.



Glazed door

The handle-free glazed door guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines.



EWTdf 3553 with stainless steel frame/-handle (Accessories)



FreshAir activated charcoal filter

The integrated FreshAir activated charcoal filter purifies the internal air and traps unpleasant odours. It is easy to replace and guarantees optimum air quality.

Vinidor dual zone wine cabinets



EWTgb 3583
Vinidor

Flush-fitted insulated glass door / fully integrated appliance	
Energy efficiency class:	G <small>A G</small>
Energy consumption year / 24 hrs:	178 / 0.487 kWh
Max. Bordeaux bottles 0.75 l:	83
Total volume ¹ :	271 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening



↑
178
↓



EWTgw 3583
Vinidor

Flush-fitted insulated glass door / fully integrated appliance	
Energy efficiency class:	G <small>A G</small>
Energy consumption year / 24 hrs:	178 / 0.487 kWh
Max. Bordeaux bottles 0.75 l:	83
Total volume ¹ :	271 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock


Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening

↑
178
↓



EWTdf 3553
Vinidor

Insulated glass door / fully integrated panel-ready appliance	
Energy efficiency class:	G <small>A G</small>
Energy consumption year / 24 hrs:	178 / 0.487 kWh
Max. Bordeaux bottles 0.75 l:	80
Total volume ¹ :	254 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	177.2 - 178 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 10 Shelves, of which 8 set on telescopic rails, of which 1 is a presentation shelf

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening



↑
178
↓

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



122

EWTgb 2383 Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	160 / 0.438 kWh
Max. Bordeaux bottles 0.75 l:	51
Total volume ¹ :	169 l
Noise output / noise class:	31 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 6 Shelves, of which 4 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening



Silent appliances

The silent appliances are extremely quiet due to their design and low-noise components.



Presentation shelf

The presentation shelf is ideal for keeping open bottles at the perfect temperature and without the risk of spills.



122

EWTgw 2383 Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	160 / 0.438 kWh
Max. Bordeaux bottles 0.75 l:	51
Total volume ¹ :	169 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 6 Shelves, of which 4 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening



122

EWTdf 2353 Vinidor

Insulated glass door / fully integrated panel-ready appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	158 / 0.432 kWh
Max. Bordeaux bottles 0.75 l:	48
Total volume ¹ :	158 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	122 - 123.6 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 6 Shelves, of which 4 set on telescopic rails, of which 1 is a presentation shelf

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Concealed hinge with restricted opening

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.



EWTgb 1683



88

EWTgb 1683
Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	151 / 0.413 kWh
Max. Bordeaux bottles 0.75 l:	33
Total volume ¹ :	104 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 4 Shelves, of which 2 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening



88

EWTgw 1683
Vinidor

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	151 / 0.413 kWh
Max. Bordeaux bottles 0.75 l:	33
Total volume ¹ :	104 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 4 Shelves, of which 2 set on telescopic rails, of which 1 is a presentation shelf

Key features

- TipOpen
- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening



88

EWTdf 1653
Vinidor

Insulated glass door / fully integrated panel-ready appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	150 / 0.411 kWh
Max. Bordeaux bottles 0.75 l:	30
Total volume ¹ :	97 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Will accept an overlay furniture panel or a s/steel overlay kit accessory
Aperture dimensions in cm (h / w / d):	87.4 - 89 / 56 - 57 / at least 55



Controls


- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED Interior lighting with on/off function, dimmable
- Beech wood fittings
- 4 Shelves, of which 2 set on telescopic rails, of which 1 is a presentation shelf

Key features

- Height-adjustable feet at front
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening



Side-by-side concept

The side-by-side concept makes it possible to position fridges, freezers and wine cabinets to meet your needs. Special technology for controlling the environment between appliances with major temperature differences enables numerous combinations. More information see page 26 – 29.

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.



TipOpen technology

The handle-free glazed door guarantees perfect integration into a handle-free kitchen. Not only provides UV protection you can trust but also ensures superb visibility of the stored wines.

The TipOpen technology opens the glazed door 7 cm when tapped and, if the door is not opened further within three seconds, the soft-closing system will shut it again.



Telescopic rails

The Vinidor appliances are equipped with solid wooden shelves mounted on telescopic rails.

The handcrafted shelves made from untreated wood are ideal for storing Bordeaux bottles safely, providing a clear view and easy access.



UWTgb 1682
Vinidor

Flush / under-worktop appliance	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	146 / 0.400 kWh
Max. Bordeaux bottles 0.75 l:	34
Total volume ¹ :	94 l
Noise output / noise class:	35 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 / at least 58



Controls

- LCD display in the interior, touch electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

Key features

- TipOpen
- Height-adjustable feet at front and back
- Reversible door hinging
- Replaceable door seal
- Concealed hinge with restricted opening



UWTes 1672
Vinidor

Flush / under-worktop appliance	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	142 / 0.389 kWh
Max. Bordeaux bottles 0.75 l:	34
Total volume ¹ :	94 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Insulated glass door with stainless steel frame
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 / at least 58



Controls

- MagicEye in the interior, key electronic
- Digital temperature display for both wine zones
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 2 Temperature zones, which can set from +5 °C to +20 °C
- 2 independently controllable zones
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 5 Shelves, of which 3 set on telescopic rails

Key features

- Aluminium handle
- Height-adjustable feet at front and back
- Reversible door hinging
- Replaceable door seal
- Lock



UWKes 1752
GrandCru

Flush / under-worktop appliance	
Energy efficiency class:	G
Energy consumption year / 24 hrs:	139 / 0.380 kWh
Max. Bordeaux bottles 0.75 l:	46
Total volume ¹ :	110 l
Noise output / noise class:	38 dB(A) / C
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Insulated glass door with stainless steel frame
Aperture dimensions in cm (h / w / d):	82 - 87 / 60 - 61 / at least 58



Controls

- MagicEye in the interior, key electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on
- Beech wood fittings
- 4 Shelves, of which 3 set on telescopic rails

Key features

- Aluminium handle
- Height-adjustable feet at front and back
- Reversible door hinging
- Replaceable door seal
- Lock

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to [EU] 2017/1369 6a.

GrandCru range



45

WKEgb 582 GrandCru

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Max. Bordeaux bottles 0.75 l:	18*
Total volume ¹ :	47 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	Black insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	45.2 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves, of which 2 set on telescopic rails

Key features

- Folding door with TipOpen technology
- Concealed hinge with restricted opening

* Max. 18 Bordeaux bottles for front to back storage.
Taller bottles can be stored side on (max. 12 Bordeaux bottles).



45

WKEgw 582 GrandCru

Flush-fitted insulated glass door / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	116 / 0.317 kWh
Max. Bordeaux bottles 0.75 l:	18*
Total volume ¹ :	47 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN-ST (+10 °C to +38 °C)
Door:	White insulated glass door, handle and frame-free
Aperture dimensions in cm (h / w / d):	45.2 / 56 - 57 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves, of which 2 set on telescopic rails

Key features

- Folding door with TipOpen technology
- Replaceable door seal
- Concealed hinge with restricted opening

* Max. 18 Bordeaux bottles for front to back storage.
Taller bottles can be stored side on (max. 12 Bordeaux bottles).



45

WKEes 553 GrandCru

Flush / fully integrated appliance

Energy efficiency class:	G
Energy consumption year / 24 hrs:	140 / 0.383 kWh
Max. Bordeaux bottles 0.75 l:	18**
Total volume ¹ :	51 l
Noise output / noise class:	32 dB(A) / B SuperSilent
Climate rating:	SN (+10 °C to +32 °C)
Door:	Insulated glass door with stainless steel frame, recessed handle
Aperture dimensions in cm (h / w / d):	45 / 56 / at least 55



Controls

- LCD display in the interior, touch electronic
- Digital temperature display
- Warning signal in case of fault: visual and acoustic
- Door alarm: acoustic
- Child lock

Wine compartment

- 1 Temperature zone, which can set from +5 °C to +20 °C
- Convection cooling, Fresh air supply via FreshAir activated charcoal filter
- Humidity regulation via adjustable fan
- LED interior lighting permanently on, dimmable
- Beech wood fittings
- 3 Shelves, of which 2 set on telescopic rails

Key features

- Recessed handle
- Reversible door hinging
- Replaceable door seal

** Max. 18 Bordeaux bottles for front to back storage.
Taller bottles can be stored side on using the brackets provided (max. 12 Bordeaux bottles).



WKEes 553 with drawer as accessory (optional accessory)





Accessories drawer

The easy-glide accessories drawer (incl. 2-part insert set for 6 wine glasses and sommelier accessories) can be used to store accessories directly below wine storage cabinets in the WKE model range. Available in white glass (9792 449), black glass (9792 451) and stainless steel (9792 453).

¹ In accordance with Regulation EU 2019/2016 we indicate the total volume to the nearest integer (rounded off) and the volume of the frozen compartments and refrigeration compartments to one place after the decimal point. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.




SN	from +10 °C to +32 °C
ST	from +16 °C to +38 °C
N	from +16 °C to +32 °C
T	from +16 °C to +43 °C



Aperture dimensions

The dimensions for fully integrated appliances are industry standard. The aperture dimensions provide information about the appliance size or height. The exact dimensions of each appliance can be seen in the installation diagrams on the pages that follow.



Climate class

The climate rating specifies the ambient temperature for which the appliances are guaranteed to work normally. The following climate ratings have been defined (pursuant to DIN EN ISO 15502):

Outstanding energy efficiency

By combining state-of-the-art, precision electronics and highly efficient refrigeration systems, Liebherr offers an attractive and ultra-economical range of appliances in the best energy efficiency classes across all product groups. Liebherr offers products with the greatest possible energy savings. You can find the full range of efficiency classes on page 15. According to (EU) 2017/1369 6a.

Four-point attachment

So that our fully integrated fridges can be installed correctly, we provide special four-point fixing as standard for all our door-on-door appliances. The fixing points are attractively concealed with covers and the attachment brackets create a depth stop at the top and bottom. This alignment device ensures that the appliance is correctly positioned within the kitchen unit. Taller appliances with a height of 140 cm or more also come with two height-adjustable positioning feet at the front.

Vario plinth

The Vario plinth makes it possible to adapt under-worktop models (UIK, SUIG, UWT and UWK) to the height and depth of the kitchen units. All four positioning feet can be adjusted by up to 50 mm from the front. The position of the ventilation grille can also be adjusted to match the front of the kitchen units; it can be moved by up to 55 mm.


Levelling bars

Taller appliances with a height of 140 cm or more have two levelling bars on the left and right of the base. These make it possible to correctly level position the appliance and thereby ensure that the door closes correctly so that the appliance works properly.



Décor panel / equaliser trims

On décor panel appliances, a décor panel, up to 4 mm thick, that matches the kitchen finish can be inserted into the décor frame on the appliance door. The décor panel is aluminium coloured as standard, but brown and white frames are also available as optional accessories. If the existing décor panel is too small for the replacement appliance, it can be adapted using equaliser trims that match the colour of the décor frame. Depending on the dimensions, or for aesthetic reasons, one or two equaliser trims (top and /or bottom) can be used. The equaliser trims are available in three heights (16, 41 and 60 mm) and three different colours (brown, white and aluminium coloured).



Front air intake and ventilation












To ensure that the refrigeration system is cooled and the appliance operates correctly, fully integrated appliances must be adequately ventilated. Depending on the model and the installation location:

- 1 - Fully integrated appliances in non-ceiling height kitchen units. Front air intake in the plinth, venting via the back wall of the kitchen unit.
- 2 - Fully integrated appliances in ceiling height kitchen units. Front air intake in the plinth, venting via ventilation slots at the top.
- 3 - In the case of individual fully integrated appliances installed one above the other (Freshness Centre / SBS Concept, see pages 26 - 29) ventilation takes place as described in 1 and 2.
- 4 - Fully integrated appliances with both air intake and venting at the front.
- 5 - Under-worktop appliances with front air intake in the plinth. Venting via ventilation slots at the top.
- 6 - Under-worktop appliances with both air intake and venting at the front. Please note: All ventilation slots must be at least 200 cm².







Diagrams

















Whether you want to redesign your kitchen, or replace your current appliance: Liebherr's extensive fully integrated range offers the right appliance for all of your needs. Liebherr, the refrigeration specialist offers you premium-quality appliances with all the advantages of the latest refrigeration technology.







Diagrams















Diagrams








Diagrams



Diagrams



Diagrams





Our catalogues

Find out everything you need to know about Liebherr Freestanding & Fully integrated refrigeration as well as Wine Cabinets. Liebherr also manufacture a comprehensive range of Commercial refrigeration. Available as PDF downloads from home.liebherr.com



SmartDevice App: The Smart-Device app lets you control your fridge from anywhere: Change the temperature of your appliance quickly and easily from anywhere or monitor all alerts and notifications at a glance.



Find out which app is available for which operating system (Apple, Android etc.), and which device type.



WarrantyPLUS

Benefit from many advantages of an extension of 2 or 7 years Warranty. Further information under home.liebherr.com/promotions or contact yours Liebherr specialist dealers Partner.



Your local Liebherr authorised dealer will help you make the right choice of refrigeration for your lifestyle

Liebherr-Hausgeräte Marica EOOD
E-mail: home.see@liebherr.com

home.liebherr.com

Subject to modification. Current data see home.liebherr.com.
Printed in Germany by Raff & Wuzel Druck GmbH, 03.2021

